

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010944

Luminaire Tested: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010944
REPORT IS A COMBINATION OF REPORTS P993410 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3554.0 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010944

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1010944

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65
1	100	96	92	89	93	90	87	84	78	76	74	68	66	64	58	57	55
2	92	84	78	73	85	79	74	69	69	65	62	60	57	54	51	49	47
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41
4	77	66	58	52	72	62	55	50	55	49	45	48	43	40	41	38	35
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	34	31
6	65	53	45	39	61	50	43	38	44	39	34	39	34	31	34	30	27
7	61	48	40	35	56	46	38	33	40	35	30	36	31	27	31	27	25
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22
9	52	40	33	28	49	38	31	27	34	28	24	30	26	22	26	23	20
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10038	10038	10038
5°	10055	9684	9658
10°	9977	9319	9136
15°	9846	8869	8564
20°	9677	8380	7926
25°	9501	7871	7321
30°	9277	7330	6607
35°	9045	6799	5956
40°	8827	6221	5236
45°	8548	5657	4590
50°	8241	5055	3920
55°	7922	4409	3306
60°	7616	3748	2683
65°	7223	3070	2095
70°	6726	2320	1496
75°	6014	1572	1186
80°	5130	1093	833
85°	3852	590	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8548 cd/sqm

TEST NUMBER: P1010944

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	2.5
10°-20°	243.9	6.9
20°-30°	351.2	9.9
30°-40°	395.5	11.1
40°-50°	378.3	10.6
50°-60°	309.7	8.7
60°-70°	208.8	5.9
70°-80°	104.7	2.9
80°-90°	28.3	0.8
90°-100°	16.7	0.5
100°-110°	80.9	2.3
110°-120°	198.2	5.6
120°-130°	251.6	7.1
130°-140°	268.8	7.6
140°-150°	251.3	7.1
150°-160°	202.7	5.7
160°-170°	130.8	3.7
170°-180°	45.1	1.3
0°-30°	682.7	19.2
0°-40°	1078.2	30.3
0°-60°	1766.1	49.7
0°-90°	2107.9	59.3
90°-120°	295.8	8.3
90°-150°	1067.4	30.0
90°-180°	1446.0	40.7
0°-180°	3554.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	933	933	933	933	933	
5°	933	929	920	927	925	88
15°	890	881	860	856	851	251
25°	809	790	756	740	731	372
35°	700	673	626	594	580	438
45°	576	542	483	440	422	444
55°	437	400	336	292	277	392
65°	299	257	198	161	153	296
75°	158	122	80	73	71	168
85°	40	23	21	20	20	44
90°	0	4	8	10	11	4
95°	22	7	11	13	13	26
105°	105	109	77	15	16	111
115°	197	199	202	206	207	195
125°	278	280	282	283	283	248
135°	346	348	349	350	349	266
145°	399	401	402	403	403	250
155°	439	439	439	441	439	202
165°	463	462	462	465	462	131
175°	474	473	473	475	473	45
180°	474	474	474	474	474	

TEST NUMBER: P1010944

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	932.6	932.6	932.6	932.6	932.6
2.5°	936.4	933.4	924.3	932.6	931.1
5°	932.6	928.9	919.8	926.6	925.1
7.5°	925.8	922.1	910.7	915.2	913.0
10°	916.8	911.5	897.8	898.6	894.8
12.5°	903.9	897.8	880.4	879.7	875.2
15°	889.5	881.2	860.0	856.2	850.9
17.5°	872.1	863.1	836.6	829.0	821.4
20°	852.5	840.4	811.6	801.8	792.7
22.5°	830.5	816.2	785.1	772.3	764.0
25°	809.3	790.4	755.6	739.8	731.4
27.5°	783.6	763.2	725.4	704.2	691.3
30°	757.2	734.5	692.1	666.4	654.3
32.5°	730.7	704.2	658.8	630.1	617.2
35°	700.4	673.2	626.3	593.8	580.2
37.5°	670.2	640.7	591.5	555.2	538.6
40°	641.4	608.1	554.4	515.1	497.7
42.5°	608.9	575.6	519.6	475.8	460.6
45°	575.6	541.6	483.3	440.2	422.1
47.5°	543.1	505.3	447.8	400.9	385.0
50°	506.8	471.2	410.0	363.1	345.7
52.5°	474.3	434.9	374.4	325.3	310.1
55°	437.2	400.1	335.8	292.0	276.8
57.5°	403.9	363.8	298.8	257.2	244.3
60°	369.1	327.5	264.7	223.9	211.0
62.5°	334.3	292.7	229.9	192.1	178.5
65°	298.8	257.2	198.2	161.1	152.8
67.5°	263.2	220.9	163.4	135.4	126.3
70°	228.4	187.6	134.6	108.2	99.8
72.5°	193.6	153.5	106.7	86.2	84.0
75°	158.1	121.8	80.2	72.6	71.1
77.5°	125.6	92.3	62.8	58.2	56.7
80°	94.5	63.5	47.7	45.4	43.9
82.5°	65.1	39.3	34.0	31.8	31.8
85°	40.1	23.4	21.2	19.7	19.7
87.5°	18.2	9.8	9.8	9.1	8.3
90°	0.4	3.9	8.5	9.9	10.6
92.5°	8.1	6.0	9.2	11.6	12.0
95°	21.5	7.0	10.9	13.4	13.4
97.5°	39.1	29.2	11.3	14.1	14.4
100°	59.6	66.6	11.6	14.4	14.8
102.5°	82.8	87.4	26.1	14.4	15.2
105°	105.0	108.9	77.2	14.8	15.5
107.5°	128.6	131.8	137.1	82.8	36.7
110°	152.2	155.1	158.9	147.3	96.9

TEST NUMBER: P1010944

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.8	177.3	181.1	184.3	183.6
115°	197.0	199.1	202.3	205.8	207.2
117.5°	218.8	221.3	223.1	225.9	226.2
120°	238.9	242.1	243.2	246.0	246.0
122.5°	259.4	261.8	263.2	265.0	265.4
125°	277.7	280.5	281.9	282.6	283.3
127.5°	296.0	298.8	300.6	301.7	301.0
130°	312.9	315.8	317.2	318.6	317.9
132.5°	329.1	332.0	333.0	334.4	333.4
135°	345.7	347.8	349.2	350.3	349.2
137.5°	359.8	362.6	363.3	365.1	364.4
140°	373.9	376.0	377.1	378.5	377.8
142.5°	386.9	389.1	390.1	391.2	390.1
145°	398.9	401.4	402.1	402.8	402.8
147.5°	410.6	412.3	413.0	413.7	412.0
150°	421.1	422.2	422.9	423.6	422.5
152.5°	430.6	431.0	431.3	432.8	431.0
155°	439.4	438.7	439.1	440.9	438.7
157.5°	446.5	446.5	446.1	448.3	445.4
160°	452.8	452.5	452.1	454.2	451.8
162.5°	458.8	457.8	457.4	459.9	457.8
165°	463.4	462.4	462.0	464.8	462.4
167.5°	467.3	465.9	465.9	468.7	465.9
170°	470.5	469.0	469.0	471.9	469.0
172.5°	472.6	470.8	471.2	474.0	470.8
175°	474.3	472.6	472.9	475.4	472.6
177.5°	475.0	473.3	473.6	476.5	472.9
180°	474.3	474.3	474.3	474.3	474.3

(END OF REPORT)