

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010945

Luminaire Tested: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010945
REPORT IS A COMBINATION OF REPORTS P993411 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3585.0 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010945

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010945

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	59		
1	100	96	92	89	93	90	87	84	78	76	74	68	66	64	58	57	55	51		
2	92	84	78	73	85	79	74	69	69	65	62	60	57	54	51	49	47	43		
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41	37		
4	77	66	58	52	72	62	55	50	55	49	45	48	43	40	41	38	35	32		
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	34	31	28		
6	65	53	45	39	61	50	43	38	44	39	34	39	34	31	34	30	27	25		
7	61	48	40	35	56	46	38	33	40	35	30	36	31	27	31	27	25	22		
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22	20		
9	52	40	33	28	49	38	31	27	34	28	24	30	26	22	26	23	20	18		
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10125	10125	10125
5°	10141	9766	9740
10°	10061	9399	9214
15°	9930	8946	8638
20°	9759	8451	7994
25°	9583	7939	7384
30°	9356	7393	6663
35°	9123	6857	6006
40°	8903	6275	5281
45°	8621	5706	4629
50°	8311	5098	3953
55°	7989	4447	3335
60°	7682	3780	2706
65°	7284	3096	2113
70°	6785	2341	1510
75°	6063	1586	1196
80°	5179	1103	838
85°	3881	596	439

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8621 cd/sqm

TEST NUMBER: P1010945

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.4	2.5
10°-20°	246.0	6.9
20°-30°	354.2	9.9
30°-40°	398.8	11.1
40°-50°	381.5	10.6
50°-60°	312.3	8.7
60°-70°	210.6	5.9
70°-80°	105.6	2.9
80°-90°	28.6	0.8
90°-100°	16.9	0.5
100°-110°	81.6	2.3
110°-120°	200.0	5.6
120°-130°	253.8	7.1
130°-140°	271.2	7.6
140°-150°	253.6	7.1
150°-160°	204.5	5.7
160°-170°	132.0	3.7
170°-180°	45.5	1.3
0°-30°	688.6	19.2
0°-40°	1087.4	30.3
0°-60°	1781.2	49.7
0°-90°	2126.0	59.3
90°-120°	298.5	8.3
90°-150°	1077.0	30.0
90°-180°	1459.0	40.7
0°-180°	3585.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	941	941	941	941	941	
5°	941	937	928	934	933	89
15°	897	889	867	864	858	253
25°	816	797	762	746	738	375
35°	706	679	632	599	585	442
45°	580	546	488	444	426	448
55°	441	404	339	294	279	395
65°	301	259	200	162	154	298
75°	159	123	81	73	72	170
85°	40	24	21	20	20	44
90°	0	4	8	10	11	4
95°	22	7	11	14	14	26
105°	106	110	78	15	16	112
115°	199	201	204	208	209	196
125°	280	283	284	285	286	250
135°	349	351	352	353	352	269
145°	402	405	406	406	406	252
155°	443	443	443	445	443	204
165°	468	466	466	469	466	132
175°	479	477	477	480	477	46
180°	479	479	479	479	479	

TEST NUMBER: P1010945

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	940.6	940.6	940.6	940.6	940.6
2.5°	944.4	941.4	932.2	940.6	939.1
5°	940.6	936.8	927.6	934.5	933.0
7.5°	933.7	929.9	918.5	923.1	920.8
10°	924.6	919.2	905.5	906.3	902.5
12.5°	911.6	905.5	888.0	887.2	882.6
15°	897.1	888.7	867.4	863.6	858.2
17.5°	879.6	870.4	843.7	836.1	828.5
20°	859.7	847.5	818.5	808.6	799.5
22.5°	837.6	823.1	791.8	778.9	770.5
25°	816.3	797.2	762.1	746.1	737.7
27.5°	790.3	769.7	731.6	710.2	697.3
30°	763.6	740.7	698.0	672.1	659.9
32.5°	736.9	710.2	664.5	635.5	622.5
35°	706.4	678.9	631.6	598.8	585.1
37.5°	675.9	646.1	596.6	559.9	543.2
40°	646.9	613.3	559.2	519.5	502.0
42.5°	614.1	580.5	524.1	479.8	464.6
45°	580.5	546.2	487.5	444.0	425.7
47.5°	547.7	509.6	451.6	404.3	388.3
50°	511.1	475.3	413.5	366.2	348.6
52.5°	478.3	438.6	377.6	328.0	312.8
55°	440.9	403.6	338.7	294.5	279.2
57.5°	407.4	366.9	301.3	259.4	246.4
60°	372.3	330.3	267.0	225.8	212.8
62.5°	337.2	295.2	231.9	193.8	180.0
65°	301.3	259.4	199.9	162.5	154.1
67.5°	265.5	222.8	164.8	136.6	127.4
70°	230.4	189.2	135.8	109.1	100.7
72.5°	195.3	154.9	107.6	87.0	84.7
75°	159.4	122.8	80.9	73.2	71.7
77.5°	126.6	93.1	63.3	58.7	57.2
80°	95.4	64.1	48.1	45.8	44.2
82.5°	65.6	39.7	34.3	32.0	32.0
85°	40.4	23.6	21.4	19.8	19.8
87.5°	18.3	9.9	9.9	9.2	8.4
90°	0.4	3.9	8.5	10.0	10.7
92.5°	8.2	6.0	9.2	11.7	12.1
95°	21.7	7.1	11.0	13.5	13.5
97.5°	39.5	29.5	11.4	14.2	14.6
100°	60.1	67.2	11.7	14.6	14.9
102.5°	83.6	88.2	26.3	14.6	15.3
105°	106.0	109.9	77.9	14.9	15.6
107.5°	129.8	133.0	138.3	83.6	37.0
110°	153.6	156.5	160.4	148.6	97.8



TEST NUMBER: P1010945

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	176.4	178.9	182.8	186.0	185.3
115°	198.8	200.9	204.1	207.7	209.1
117.5°	220.8	223.3	225.1	227.9	228.3
120°	241.1	244.3	245.3	248.2	248.2
122.5°	261.7	264.2	265.6	267.4	267.7
125°	280.2	283.0	284.5	285.2	285.9
127.5°	298.7	301.5	303.3	304.4	303.7
130°	315.7	318.6	320.0	321.4	320.7
132.5°	332.1	334.9	336.0	337.4	336.4
135°	348.8	350.9	352.4	353.4	352.4
137.5°	363.0	365.9	366.6	368.4	367.7
140°	377.3	379.4	380.5	381.9	381.2
142.5°	390.4	392.5	393.6	394.7	393.6
145°	402.5	405.0	405.7	406.4	406.4
147.5°	414.2	416.0	416.7	417.4	415.7
150°	424.9	426.0	426.7	427.4	426.3
152.5°	434.5	434.9	435.2	436.6	434.9
155°	443.4	442.7	443.0	444.8	442.7
157.5°	450.5	450.5	450.2	452.3	449.4
160°	456.9	456.6	456.2	458.3	455.8
162.5°	463.0	461.9	461.5	464.0	461.9
165°	467.6	466.5	466.2	469.0	466.5
167.5°	471.5	470.1	470.1	472.9	470.1
170°	474.7	473.3	473.3	476.1	473.3
172.5°	476.8	475.0	475.4	478.2	475.0
175°	478.6	476.8	477.2	479.7	476.8
177.5°	479.3	477.5	477.9	480.7	477.2
180°	478.6	478.6	478.6	478.6	478.6

(END OF REPORT)