

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010948

Luminaire Tested: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010948
REPORT IS A COMBINATION OF REPORTS P993414 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3447.0 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010948

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010948

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65
1	100	96	92	89	93	90	87	84	78	76	74	68	66	64	58	57	55
2	92	84	78	73	85	79	74	69	69	65	62	60	57	54	51	49	47
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41
4	77	66	58	52	72	62	55	50	55	49	45	48	43	40	41	38	35
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	34	31
6	65	53	45	39	61	50	43	38	44	39	34	39	34	31	34	30	27
7	61	48	40	35	56	46	38	33	40	35	30	36	31	27	31	27	25
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22
9	52	40	33	28	49	38	31	27	34	28	24	30	26	22	26	23	20
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9734	9734	9734
5°	9750	9389	9364
10°	9673	9037	8858
15°	9547	8600	8305
20°	9383	8126	7685
25°	9213	7632	7099
30°	8996	7108	6406
35°	8771	6593	5774
40°	8559	6033	5077
45°	8288	5486	4450
50°	7991	4901	3801
55°	7681	4275	3206
60°	7385	3634	2602
65°	7003	2977	2032
70°	6523	2250	1451
75°	5831	1523	1149
80°	4978	1059	806
85°	3737	571	423

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8288 cd/sqm

TEST NUMBER: P1010948

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.0	2.5
10°-20°	236.5	6.9
20°-30°	340.5	9.9
30°-40°	383.4	11.1
40°-50°	366.8	10.6
50°-60°	300.2	8.7
60°-70°	202.4	5.9
70°-80°	101.5	2.9
80°-90°	27.5	0.8
90°-100°	16.2	0.5
100°-110°	78.5	2.3
110°-120°	192.3	5.6
120°-130°	244.1	7.1
130°-140°	260.8	7.6
140°-150°	243.8	7.1
150°-160°	196.7	5.7
160°-170°	126.9	3.7
170°-180°	43.7	1.3
0°-30°	662.0	19.2
0°-40°	1045.4	30.3
0°-60°	1712.5	49.7
0°-90°	2043.9	59.3
90°-120°	287.0	8.3
90°-150°	1035.7	30.0
90°-180°	1403.0	40.7
0°-180°	3447.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	904	904	904	904	904	
5°	904	901	892	898	897	86
15°	862	854	834	830	825	243
25°	785	766	733	717	709	361
35°	679	653	607	576	562	425
45°	558	525	469	427	409	431
55°	424	388	326	283	268	380
65°	290	249	192	156	148	287
75°	153	118	78	70	69	163
85°	39	23	20	19	19	43
90°	0	4	8	10	10	4
95°	21	7	11	13	13	25
105°	102	106	75	14	15	108
115°	191	193	196	200	201	189
125°	269	272	274	274	275	241
135°	335	338	339	340	339	258
145°	387	390	390	391	391	242
155°	426	426	426	428	426	196
165°	450	449	448	451	449	127
175°	460	458	459	461	458	44
180°	460	460	460	460	460	

TEST NUMBER: P1010948

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	904.3	904.3	904.3	904.3	904.3
2.5°	908.0	905.0	896.2	904.3	902.8
5°	904.3	900.6	891.8	898.4	897.0
7.5°	897.7	894.0	883.0	887.4	885.2
10°	888.9	883.8	870.6	871.3	867.6
12.5°	876.4	870.6	853.7	853.0	848.6
15°	862.5	854.4	833.9	830.2	825.1
17.5°	845.6	836.8	811.2	803.8	796.5
20°	826.6	814.8	787.0	777.4	768.6
22.5°	805.3	791.4	761.3	748.8	740.8
25°	784.8	766.4	732.7	717.3	709.2
27.5°	759.8	740.0	703.4	682.8	670.3
30°	734.2	712.2	671.1	646.1	634.4
32.5°	708.5	682.8	638.8	610.9	598.5
35°	679.2	652.7	607.3	575.7	562.5
37.5°	649.8	621.2	573.5	538.3	522.2
40°	621.9	589.7	537.6	499.5	482.6
42.5°	590.4	558.1	503.9	461.3	446.7
45°	558.1	525.1	468.7	426.9	409.3
47.5°	526.6	489.9	434.2	388.7	373.3
50°	491.4	456.9	397.5	352.0	335.2
52.5°	459.9	421.7	363.0	315.4	300.7
55°	423.9	388.0	325.6	283.1	268.4
57.5°	391.6	352.8	289.7	249.4	236.9
60°	357.9	317.6	256.7	217.1	204.6
62.5°	324.2	283.8	223.0	186.3	173.1
65°	289.7	249.4	192.2	156.2	148.2
67.5°	255.2	214.2	158.4	131.3	122.5
70°	221.5	181.9	130.5	104.9	96.8
72.5°	187.8	148.9	103.4	83.6	81.4
75°	153.3	118.1	77.7	70.4	68.9
77.5°	121.7	89.5	60.9	56.5	55.0
80°	91.7	61.6	46.2	44.0	42.5
82.5°	63.1	38.1	33.0	30.8	30.8
85°	38.9	22.7	20.5	19.1	19.1
87.5°	17.6	9.5	9.5	8.8	8.1
90°	0.3	3.8	8.2	9.6	10.3
92.5°	7.9	5.8	8.9	11.3	11.6
95°	20.9	6.8	10.6	13.0	13.0
97.5°	38.0	28.4	10.9	13.7	14.0
100°	57.8	64.6	11.3	14.0	14.4
102.5°	80.4	84.8	25.3	14.0	14.7
105°	101.9	105.7	74.9	14.4	15.0
107.5°	124.8	127.9	133.0	80.4	35.6
110°	147.7	150.4	154.2	142.9	94.0



TEST NUMBER: P1010948

CATALOG NUMBER: S123RDIP-B560D365UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	169.6	172.0	175.8	178.8	178.1
115°	191.1	193.2	196.3	199.7	201.1
117.5°	212.3	214.7	216.4	219.2	219.5
120°	231.8	234.9	235.9	238.7	238.7
122.5°	251.7	254.1	255.4	257.1	257.5
125°	269.4	272.2	273.5	274.2	274.9
127.5°	287.2	290.0	291.7	292.7	292.0
130°	303.6	306.4	307.7	309.1	308.4
132.5°	319.4	322.1	323.1	324.5	323.5
135°	335.4	337.5	338.9	339.9	338.9
137.5°	349.1	351.8	352.5	354.2	353.6
140°	362.8	364.8	365.9	367.2	366.6
142.5°	375.4	377.5	378.5	379.5	378.5
145°	387.1	389.5	390.1	390.8	390.8
147.5°	398.4	400.1	400.7	401.4	399.7
150°	408.6	409.6	410.3	411.0	410.0
152.5°	417.8	418.2	418.5	419.9	418.2
155°	426.4	425.7	426.0	427.8	425.7
157.5°	433.2	433.2	432.9	434.9	432.2
160°	439.4	439.0	438.7	440.7	438.4
162.5°	445.2	444.2	443.8	446.2	444.2
165°	449.6	448.6	448.3	451.0	448.6
167.5°	453.4	452.0	452.0	454.8	452.0
170°	456.5	455.1	455.1	457.8	455.1
172.5°	458.5	456.8	457.2	459.9	456.8
175°	460.2	458.5	458.9	461.3	458.5
177.5°	460.9	459.2	459.6	462.3	458.9
180°	460.2	460.2	460.2	460.2	460.2

(END OF REPORT)