

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010955

Luminaire Tested: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010955
REPORT IS A COMBINATION OF REPORTS P993451 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4472.0 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010955

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010955

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39
3	81	72	65	59	75	67	61	56	56	52	48	47	44	41	38	36	34
4	75	64	56	50	68	59	53	47	50	45	41	42	38	35	34	32	29
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23
7	59	46	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20
8	54	42	35	29	50	39	33	28	34	28	25	29	24	21	24	21	18
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17
10	47	35	28	24	44	33	27	22	29	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10125	10125	10125
5°	10141	9766	9740
10°	10061	9399	9214
15°	9930	8946	8638
20°	9759	8451	7994
25°	9583	7939	7384
30°	9356	7393	6663
35°	9123	6857	6006
40°	8903	6275	5281
45°	8621	5706	4629
50°	8311	5098	3953
55°	7989	4447	3335
60°	7682	3780	2706
65°	7284	3096	2113
70°	6785	2341	1510
75°	6063	1586	1196
80°	5179	1103	838
85°	3881	596	439

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8621 cd/sqm

TEST NUMBER: P1010955

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.4	2.0
10°-20°	246.0	5.5
20°-30°	354.2	7.9
30°-40°	398.8	8.9
40°-50°	381.5	8.5
50°-60°	312.3	7.0
60°-70°	210.6	4.7
70°-80°	105.6	2.4
80°-90°	29.1	0.7
90°-100°	27.1	0.6
100°-110°	131.2	2.9
110°-120°	321.4	7.2
120°-130°	408.1	9.1
130°-140°	435.9	9.7
140°-150°	407.6	9.1
150°-160°	328.8	7.4
160°-170°	212.2	4.7
170°-180°	73.1	1.6
0°-30°	688.6	15.4
0°-40°	1087.4	24.3
0°-60°	1781.2	39.8
0°-90°	2126.5	47.6
90°-120°	479.7	10.7
90°-150°	1731.3	38.7
90°-180°	2345.0	52.4
0°-180°	4472.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	941	941	941	941	941	
5°	941	937	928	934	933	89
15°	897	889	867	864	858	253
25°	816	797	762	746	738	375
35°	706	679	632	599	585	442
45°	580	546	488	444	426	448
55°	441	404	339	294	279	395
65°	301	259	200	162	154	298
75°	159	123	81	73	72	170
85°	40	24	21	20	20	44
90°	1	6	14	16	17	4
95°	35	11	18	22	22	42
105°	170	177	125	24	25	181
115°	320	323	328	334	336	316
125°	450	455	457	458	460	402
135°	561	564	566	568	566	432
145°	647	651	652	653	653	405
155°	713	712	712	715	712	328
165°	752	750	749	754	750	212
175°	769	766	767	771	766	73
180°	769	769	769	769	769	

TEST NUMBER: P1010955

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	940.6	940.6	940.6	940.6	940.6
2.5°	944.4	941.4	932.2	940.6	939.1
5°	940.6	936.8	927.6	934.5	933.0
7.5°	933.7	929.9	918.5	923.1	920.8
10°	924.6	919.2	905.5	906.3	902.5
12.5°	911.6	905.5	888.0	887.2	882.6
15°	897.1	888.7	867.4	863.6	858.2
17.5°	879.6	870.4	843.7	836.1	828.5
20°	859.7	847.5	818.5	808.6	799.5
22.5°	837.6	823.1	791.8	778.9	770.5
25°	816.3	797.2	762.1	746.1	737.7
27.5°	790.3	769.7	731.6	710.2	697.3
30°	763.6	740.7	698.0	672.1	659.9
32.5°	736.9	710.2	664.5	635.5	622.5
35°	706.4	678.9	631.6	598.8	585.1
37.5°	675.9	646.1	596.6	559.9	543.2
40°	646.9	613.3	559.2	519.5	502.0
42.5°	614.1	580.5	524.1	479.8	464.6
45°	580.5	546.2	487.5	444.0	425.7
47.5°	547.7	509.6	451.6	404.3	388.3
50°	511.1	475.3	413.5	366.2	348.6
52.5°	478.3	438.6	377.6	328.0	312.8
55°	440.9	403.6	338.7	294.5	279.2
57.5°	407.4	366.9	301.3	259.4	246.4
60°	372.3	330.3	267.0	225.8	212.8
62.5°	337.2	295.2	231.9	193.8	180.0
65°	301.3	259.4	199.9	162.5	154.1
67.5°	265.5	222.8	164.8	136.6	127.4
70°	230.4	189.2	135.8	109.1	100.7
72.5°	195.3	154.9	107.6	87.0	84.7
75°	159.4	122.8	80.9	73.2	71.7
77.5°	126.6	93.1	63.3	58.7	57.2
80°	95.4	64.1	48.1	45.8	44.2
82.5°	65.6	39.7	34.3	32.0	32.0
85°	40.4	23.6	21.4	19.8	19.8
87.5°	18.3	9.9	9.9	9.2	8.4
90°	0.6	6.3	13.7	16.0	17.1
92.5°	13.1	9.7	14.9	18.9	19.4
95°	34.9	11.4	17.7	21.7	21.7
97.5°	63.4	47.4	18.3	22.9	23.4
100°	96.6	108.0	18.9	23.4	24.0
102.5°	134.3	141.8	42.3	23.4	24.6
105°	170.3	176.6	125.2	24.0	25.2
107.5°	208.6	213.8	222.3	134.3	59.4
110°	246.9	251.5	257.8	238.9	157.2



TEST NUMBER: P1010955

CATALOG NUMBER: S123RDIP-B560D585UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	283.5	287.5	293.8	298.9	297.8
115°	319.5	322.9	328.1	333.8	336.1
117.5°	355.0	359.0	361.8	366.4	367.0
120°	387.5	392.7	394.4	399.0	399.0
122.5°	420.7	424.7	427.0	429.8	430.4
125°	450.4	455.0	457.3	458.4	459.6
127.5°	480.1	484.7	487.6	489.3	488.1
130°	507.6	512.1	514.4	516.7	515.6
132.5°	533.9	538.4	540.2	542.4	540.7
135°	560.7	564.2	566.4	568.2	566.4
137.5°	583.6	588.2	589.3	592.2	591.0
140°	606.5	609.9	611.6	613.9	612.7
142.5°	627.6	631.0	632.8	634.5	632.8
145°	647.0	651.0	652.2	653.3	653.3
147.5°	665.9	668.8	669.9	671.0	668.2
150°	683.1	684.8	685.9	687.1	685.3
152.5°	698.5	699.1	699.6	701.9	699.1
155°	712.8	711.6	712.2	715.1	711.6
157.5°	724.2	724.2	723.6	727.1	722.5
160°	734.5	733.9	733.4	736.8	732.8
162.5°	744.2	742.5	741.9	745.9	742.5
165°	751.6	749.9	749.4	753.9	749.9
167.5°	757.9	755.6	755.6	760.2	755.6
170°	763.1	760.8	760.8	765.4	760.8
172.5°	766.5	763.6	764.2	768.8	763.6
175°	769.4	766.5	767.1	771.1	766.5
177.5°	770.5	767.6	768.2	772.8	767.1
180°	769.4	769.4	769.4	769.4	769.4

(END OF REPORT)