

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011263

Luminaire Tested: S123DIP-B1165D1025UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011263
REPORT IS A COMBINATION OF REPORTS P989359 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D1025UB35-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8292.0 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011263

CATALOG NUMBER: S123DIP-B1165D1025UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011263

CATALOG NUMBER: S123DIP-B1165D1025UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	99	95	91	88	93	89	85	82	77	74	72	66	64	62	56	55	53
2	91	83	77	71	84	78	72	67	67	63	60	58	55	52	49	47	45
3	83	73	65	60	77	68	62	56	59	54	50	51	47	44	43	41	38
4	76	65	57	50	70	60	53	48	53	47	43	46	41	38	39	36	33
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	29
6	64	52	43	37	59	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19807	19807	19807
5°	19856	19123	19094
10°	19680	18476	18287
15°	19406	17803	17406
20°	19092	17055	16532
25°	18686	16267	15600
30°	18242	15451	14618
35°	17776	14618	13643
40°	17290	13742	12683
45°	16754	12889	11681
50°	16209	11939	10675
55°	15510	10948	9656
60°	14789	9857	8571
65°	14113	8675	7440
70°	13140	7364	6120
75°	11735	5832	4751
80°	10136	4098	3361
85°	7905	2203	1682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16754 cd/sqm

TEST NUMBER: P1011263

CATALOG NUMBER: S123DIP-B1165D1025UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.5	2.1
10°-20°	489.8	5.9
20°-30°	723.4	8.7
30°-40°	844.9	10.2
40°-50°	849.4	10.2
50°-60°	746.1	9.0
60°-70°	555.7	6.7
70°-80°	316.2	3.8
80°-90°	92.6	1.1
90°-100°	81.3	1.0
100°-110°	246.1	3.0
110°-120°	419.0	5.1
120°-130°	551.2	6.6
130°-140°	619.6	7.5
140°-150°	609.2	7.3
150°-160°	512.8	6.2
160°-170°	341.4	4.1
170°-180°	119.6	1.4
0°-30°	1386.7	16.7
0°-40°	2231.6	26.9
0°-60°	3827.2	46.2
0°-90°	4791.7	57.8
90°-120°	746.5	9.0
90°-150°	2526.5	30.5
90°-180°	3500.0	42.2
0°-180°	8292.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1840	1840	1840	1840	1840	
5°	1842	1834	1816	1832	1829	175
15°	1753	1747	1726	1739	1729	494
25°	1592	1582	1562	1563	1558	733
35°	1376	1367	1346	1337	1329	861
45°	1128	1122	1101	1082	1074	871
55°	856	854	834	816	808	767
65°	584	576	560	547	543	576
75°	308	302	298	290	285	330
85°	82	79	79	76	76	88
90°	1	11	24	28	30	10
95°	58	66	73	77	77	65
105°	223	225	234	234	236	239
115°	422	425	423	424	423	417
125°	617	620	618	614	610	550
135°	801	807	806	802	800	617
145°	972	974	976	976	972	607
155°	1112	1112	1113	1117	1110	512
165°	1212	1209	1209	1215	1208	342
175°	1260	1256	1256	1262	1255	120
180°	1263	1263	1263	1263	1263	

TEST NUMBER: P1011263

CATALOG NUMBER: S123DIP-B1165D1025UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1840.1	1840.1	1840.1	1840.1	1840.1
2.5°	1848.0	1841.7	1824.3	1840.1	1838.5
5°	1841.7	1833.8	1816.4	1832.2	1829.0
7.5°	1827.5	1819.5	1802.1	1816.4	1814.8
10°	1808.5	1800.6	1780.0	1794.2	1791.1
12.5°	1783.2	1776.8	1757.8	1767.3	1765.7
15°	1753.1	1746.8	1726.2	1738.9	1729.4
17.5°	1719.9	1712.0	1691.4	1700.9	1697.7
20°	1681.9	1672.4	1651.8	1658.2	1653.4
22.5°	1639.2	1629.7	1609.1	1613.9	1607.5
25°	1591.7	1582.2	1561.6	1563.2	1558.5
27.5°	1542.7	1533.2	1511.0	1512.6	1507.8
30°	1488.9	1481.0	1458.8	1458.8	1447.7
32.5°	1435.1	1424.0	1408.2	1397.1	1392.3
35°	1376.5	1367.0	1346.5	1337.0	1329.1
37.5°	1318.0	1305.3	1284.8	1273.7	1268.9
40°	1256.3	1246.8	1224.6	1212.0	1205.6
42.5°	1194.6	1183.5	1161.3	1148.7	1142.4
45°	1128.1	1121.8	1101.2	1082.2	1074.3
47.5°	1063.2	1053.8	1034.8	1015.8	1009.5
50°	996.8	988.9	968.3	950.9	941.4
52.5°	927.2	922.4	900.3	886.0	876.5
55°	856.0	854.4	833.8	816.4	808.5
57.5°	789.5	783.2	767.4	751.6	742.1
60°	716.7	715.2	696.2	681.9	674.0
62.5°	651.9	647.1	628.1	613.9	609.2
65°	583.8	575.9	560.1	547.4	542.7
67.5°	511.1	504.7	492.1	481.0	474.7
70°	446.2	436.7	427.2	416.1	408.2
72.5°	378.1	371.8	360.7	351.3	348.1
75°	308.5	302.2	297.5	289.5	284.8
77.5°	246.8	243.7	237.3	231.0	231.0
80°	186.7	182.0	178.8	177.2	177.2
82.5°	128.2	128.2	128.2	125.0	123.4
85°	82.3	79.1	79.1	75.9	75.9
87.5°	41.1	36.4	34.8	33.2	33.2
90°	1.0	10.9	23.8	27.8	29.8
92.5°	29.8	35.7	41.7	44.7	42.7
95°	58.5	65.5	73.4	77.4	77.4
97.5°	96.3	101.2	107.2	112.1	111.1
100°	135.0	140.9	145.9	148.9	150.8
102.5°	179.6	182.6	189.5	192.5	191.5
105°	223.3	225.3	234.2	234.2	236.2
107.5°	274.9	275.9	279.8	282.8	281.8
110°	322.5	324.5	326.5	330.5	328.5



TEST NUMBER: P1011263

CATALOG NUMBER: S123DIP-B1165D1025UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.1	373.1	373.1	378.1	378.1
115°	421.8	424.7	422.7	423.7	422.7
117.5°	472.4	473.4	471.4	471.4	468.4
120°	519.0	525.0	520.0	519.0	517.0
122.5°	567.6	571.6	569.6	566.6	563.7
125°	617.3	620.2	618.2	614.3	610.3
127.5°	662.9	668.9	666.9	660.9	656.9
130°	708.6	716.5	713.5	709.5	702.6
132.5°	754.2	762.1	760.2	755.2	750.2
135°	800.8	806.8	805.8	801.8	799.8
137.5°	843.5	848.5	851.5	846.5	843.5
140°	888.2	893.1	894.1	893.1	886.2
142.5°	928.9	933.8	935.8	934.8	929.8
145°	971.5	973.5	976.5	975.5	971.5
147.5°	1008.2	1012.2	1015.2	1015.2	1009.2
150°	1046.9	1048.9	1050.9	1050.9	1045.0
152.5°	1078.7	1081.7	1082.7	1084.7	1079.7
155°	1112.4	1112.4	1113.4	1117.4	1110.5
157.5°	1141.2	1140.2	1141.2	1145.2	1139.2
160°	1168.0	1166.0	1166.0	1171.0	1167.0
162.5°	1191.8	1188.9	1189.8	1194.8	1187.9
165°	1211.7	1208.7	1208.7	1214.7	1207.7
167.5°	1228.6	1224.6	1225.6	1231.5	1225.6
170°	1242.4	1238.5	1238.5	1245.4	1238.5
172.5°	1253.4	1249.4	1249.4	1255.3	1248.4
175°	1260.3	1256.3	1256.3	1262.3	1255.3
177.5°	1264.3	1260.3	1260.3	1266.3	1259.3
180°	1263.3	1263.3	1263.3	1263.3	1263.3

(END OF REPORT)