

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010988

Luminaire Tested: S123RDIP-B775D1195UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010988
REPORT IS A COMBINATION OF REPORTS P993574 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D1195UB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7403.0 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010988

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010988

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	95	91	88	84	86	83	80	77	68	65	63	53	52	51	40	39	39
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33
3	80	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	29	26	25
5	67	56	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21
6	62	50	42	36	56	46	39	34	38	33	29	30	27	24	24	21	19
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	22	19	17
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14
10	46	34	27	22	42	31	25	21	26	22	18	22	18	15	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13431	13431	13431
5°	13453	12956	12921
10°	13347	12468	12223
15°	13174	11866	11459
20°	12946	11212	10605
25°	12712	10531	9795
30°	12412	9808	8839
35°	12102	9096	7968
40°	11811	8324	7005
45°	11437	7570	6140
50°	11025	6763	5245
55°	10598	5900	4424
60°	10191	5015	3590
65°	9662	4106	2802
70°	9000	3105	2003
75°	8045	2103	1587
80°	6868	1462	1113
85°	5149	788	583

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11437 cd/sqm

TEST NUMBER: P1010988

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.3	1.6
10°-20°	326.3	4.4
20°-30°	469.8	6.3
30°-40°	529.1	7.1
40°-50°	506.1	6.8
50°-60°	414.3	5.6
60°-70°	279.3	3.8
70°-80°	140.1	1.9
80°-90°	39.6	0.5
90°-100°	53.0	0.7
100°-110°	256.2	3.5
110°-120°	627.8	8.5
120°-130°	797.0	10.8
130°-140°	851.4	11.5
140°-150°	796.2	10.8
150°-160°	642.2	8.7
160°-170°	414.4	5.6
170°-180°	142.8	1.9
0°-30°	913.4	12.3
0°-40°	1442.6	19.5
0°-60°	2363.0	31.9
0°-90°	2822.0	38.1
90°-120°	937.0	12.7
90°-150°	3381.6	45.7
90°-180°	4581.0	61.9
0°-180°	7403.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1248	1248	1248	1248	1248	
5°	1248	1243	1231	1240	1238	118
15°	1190	1179	1151	1146	1138	335
25°	1083	1058	1011	990	979	498
35°	937	901	838	794	776	587
45°	770	725	647	589	565	594
55°	585	535	449	391	370	525
65°	400	344	265	216	204	396
75°	212	163	107	97	95	225
85°	54	31	28	26	26	59
90°	1	12	27	31	34	7
95°	68	22	35	42	42	81
105°	333	345	244	47	49	353
115°	624	631	641	652	656	616
125°	880	889	893	895	898	786
135°	1095	1102	1106	1110	1106	843
145°	1264	1272	1274	1276	1276	791
155°	1392	1390	1391	1397	1390	641
165°	1468	1465	1464	1472	1465	415
175°	1503	1497	1498	1506	1497	143
180°	1503	1503	1503	1503	1503	

TEST NUMBER: P1010988

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1247.8	1247.8	1247.8	1247.8	1247.8
2.5°	1252.9	1248.8	1236.7	1247.8	1245.8
5°	1247.8	1242.7	1230.6	1239.7	1237.7
7.5°	1238.7	1233.6	1218.5	1224.5	1221.5
10°	1226.5	1219.5	1201.2	1202.3	1197.2
12.5°	1209.3	1201.2	1178.0	1177.0	1170.9
15°	1190.1	1179.0	1150.6	1145.6	1138.5
17.5°	1166.8	1154.7	1119.3	1109.2	1099.0
20°	1140.5	1124.3	1085.9	1072.7	1060.6
22.5°	1111.2	1092.0	1050.5	1033.3	1022.1
25°	1082.8	1057.5	1011.0	989.7	978.6
27.5°	1048.4	1021.1	970.5	942.2	925.0
30°	1013.0	982.7	926.0	891.6	875.4
32.5°	977.6	942.2	881.5	843.0	825.8
35°	937.1	900.7	837.9	794.4	776.2
37.5°	896.6	857.2	791.4	742.8	720.5
40°	858.2	813.7	741.8	689.2	665.9
42.5°	814.7	770.1	695.2	636.5	616.3
45°	770.1	724.6	646.7	589.0	564.7
47.5°	726.6	676.0	599.1	536.4	515.1
50°	678.0	630.5	548.5	485.8	462.5
52.5°	634.5	581.9	500.9	435.2	414.9
55°	584.9	535.3	449.3	390.6	370.4
57.5°	540.4	486.8	399.7	344.1	326.9
60°	493.9	438.2	354.2	299.6	282.3
62.5°	447.3	391.6	307.6	257.0	238.8
65°	399.7	344.1	265.1	215.6	204.4
67.5°	352.2	295.5	218.6	181.1	169.0
70°	305.6	251.0	180.1	144.7	133.6
72.5°	259.1	205.4	142.7	115.4	112.3
75°	211.5	162.9	107.3	97.2	95.1
77.5°	168.0	123.5	84.0	77.9	75.9
80°	126.5	85.0	63.8	60.7	58.7
82.5°	87.0	52.6	45.5	42.5	42.5
85°	53.6	31.4	28.3	26.3	26.3
87.5°	24.3	13.2	13.2	12.1	11.1
90°	1.1	12.3	26.8	31.3	33.5
92.5°	25.7	19.0	29.0	36.8	38.0
95°	68.1	22.3	34.6	42.4	42.4
97.5°	123.9	92.7	35.7	44.7	45.8
100°	188.7	211.0	36.8	45.8	46.9
102.5°	262.4	276.9	82.6	45.8	48.0
105°	332.7	345.0	244.5	46.9	49.1
107.5°	407.5	417.5	434.3	262.4	116.1
110°	482.3	491.2	503.5	466.7	307.0

TEST NUMBER: P1010988

CATALOG NUMBER: S123RDIP-B775D1195UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	553.7	561.5	573.8	583.9	581.6
115°	624.1	630.8	640.8	652.0	656.4
117.5°	693.3	701.1	706.7	715.6	716.7
120°	756.9	767.0	770.3	779.2	779.2
122.5°	821.7	829.5	833.9	839.5	840.6
125°	879.7	888.6	893.1	895.3	897.6
127.5°	937.8	946.7	952.3	955.6	953.4
130°	991.4	1000.3	1004.8	1009.2	1007.0
132.5°	1042.7	1051.6	1055.0	1059.5	1056.1
135°	1095.2	1101.9	1106.3	1109.7	1106.3
137.5°	1139.8	1148.8	1151.0	1156.6	1154.3
140°	1184.5	1191.2	1194.5	1199.0	1196.8
142.5°	1225.8	1232.5	1235.8	1239.2	1235.8
145°	1263.8	1271.6	1273.8	1276.0	1276.0
147.5°	1300.6	1306.2	1308.4	1310.6	1305.1
150°	1334.1	1337.4	1339.7	1341.9	1338.6
152.5°	1364.2	1365.3	1366.5	1370.9	1365.3
155°	1392.1	1389.9	1391.0	1396.6	1389.9
157.5°	1414.5	1414.5	1413.4	1420.1	1411.1
160°	1434.6	1433.4	1432.3	1439.0	1431.2
162.5°	1453.5	1450.2	1449.1	1456.9	1450.2
165°	1468.1	1464.7	1463.6	1472.5	1464.7
167.5°	1480.3	1475.9	1475.9	1484.8	1475.9
170°	1490.4	1485.9	1485.9	1494.8	1485.9
172.5°	1497.1	1491.5	1492.6	1501.5	1491.5
175°	1502.7	1497.1	1498.2	1506.0	1497.1
177.5°	1504.9	1499.3	1500.4	1509.4	1498.2
180°	1502.7	1502.7	1502.7	1502.7	1502.7

(END OF REPORT)