

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1010997

Luminaire Tested: S123RDIP-B775D365UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1010997
REPORT IS A COMBINATION OF REPORTS P993613 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D365UB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4366.0 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1010997

CATALOG NUMBER: S123RDIP-B775D365UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1010997

CATALOG NUMBER: S123RDIP-B775D365UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67		
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	64	63	61	57		
2	93	86	80	75	88	81	76	71	72	68	65	64	61	58	57	54	52	49		
3	85	76	69	63	80	72	65	60	64	59	55	57	53	50	51	48	45	42		
4	78	68	60	54	74	64	57	51	57	52	47	51	47	43	46	42	39	36		
5	72	60	52	46	68	57	50	44	52	46	41	46	41	38	41	37	34	32		
6	67	54	46	40	63	52	44	39	47	41	36	42	37	33	38	34	30	28		
7	62	49	41	36	58	47	40	34	43	36	32	38	33	30	34	30	27	25		
8	57	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25	22		
9	54	41	34	29	51	39	32	28	36	30	26	33	28	24	29	25	22	20		
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	27	23	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13889	13889	13889
5°	13911	13397	13361
10°	13802	12894	12640
15°	13622	12271	11849
20°	13388	11594	10966
25°	13145	10890	10129
30°	12834	10141	9140
35°	12514	9407	8239
40°	12213	8608	7244
45°	11827	7827	6349
50°	11401	6993	5423
55°	10960	6101	4574
60°	10538	5186	3713
65°	9993	4247	2898
70°	9306	3212	2071
75°	8319	2174	1642
80°	7101	1511	1151
85°	5331	816	603

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11827 cd/sqm

TEST NUMBER: P1010997

CATALOG NUMBER: S123RDIP-B775D365UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.3	2.8
10°-20°	337.4	7.7
20°-30°	485.8	11.1
30°-40°	547.1	12.5
40°-50°	523.3	12.0
50°-60°	428.4	9.8
60°-70°	288.8	6.6
70°-80°	144.9	3.3
80°-90°	38.8	0.9
90°-100°	16.8	0.4
100°-110°	81.1	1.9
110°-120°	198.7	4.6
120°-130°	252.3	5.8
130°-140°	269.5	6.2
140°-150°	252.0	5.8
150°-160°	203.3	4.7
160°-170°	131.2	3.0
170°-180°	45.2	1.0
0°-30°	944.5	21.6
0°-40°	1491.7	34.2
0°-60°	2443.4	56.0
0°-90°	2916.0	66.8
90°-120°	296.6	6.8
90°-150°	1070.4	24.5
90°-180°	1450.0	33.2
0°-180°	4366.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1290	1290	1290	1290	1290	
5°	1290	1285	1272	1282	1280	122
15°	1231	1219	1190	1185	1177	347
25°	1120	1094	1045	1023	1012	515
35°	969	931	866	822	803	607
45°	796	749	669	609	584	615
55°	605	554	465	404	383	542
65°	413	356	274	223	211	409
75°	219	168	111	100	98	233
85°	56	32	29	27	27	61
90°	0	4	8	10	11	5
95°	22	7	11	13	13	26
105°	105	109	77	15	16	112
115°	198	200	203	206	208	195
125°	278	281	283	283	284	249
135°	347	349	350	351	350	267
145°	400	402	403	404	404	250
155°	441	440	440	442	440	203
165°	465	464	463	466	464	131
175°	476	474	474	477	474	45
180°	476	476	476	476	476	

TEST NUMBER: P1010997

CATALOG NUMBER: S123RDIP-B775D365UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1290.3	1290.3	1290.3	1290.3	1290.3
2.5°	1295.5	1291.3	1278.8	1290.3	1288.2
5°	1290.3	1285.1	1272.5	1281.9	1279.8
7.5°	1280.9	1275.6	1259.9	1266.2	1263.1
10°	1268.3	1261.0	1242.2	1243.2	1238.0
12.5°	1250.5	1242.2	1218.1	1217.0	1210.8
15°	1230.6	1219.1	1189.8	1184.6	1177.3
17.5°	1206.6	1194.0	1157.4	1146.9	1136.5
20°	1179.4	1162.6	1122.9	1109.3	1096.7
22.5°	1149.0	1129.1	1086.2	1068.4	1056.9
25°	1119.7	1093.6	1045.4	1023.4	1011.9
27.5°	1084.1	1055.9	1003.6	974.3	956.5
30°	1047.5	1016.1	957.5	921.9	905.2
32.5°	1010.9	974.3	911.5	871.7	853.9
35°	969.0	931.4	866.5	821.5	802.6
37.5°	927.2	886.4	818.3	768.1	745.1
40°	887.4	841.4	767.1	712.6	688.6
42.5°	842.4	796.4	718.9	658.2	637.3
45°	796.4	749.3	668.7	609.0	583.9
47.5°	751.4	699.0	619.5	554.6	532.7
50°	701.1	651.9	567.2	502.3	478.2
52.5°	656.1	601.7	518.0	450.0	429.1
55°	604.9	553.6	464.6	403.9	383.0
57.5°	558.8	503.4	413.4	355.8	338.0
60°	510.7	453.1	366.3	309.8	292.0
62.5°	462.5	405.0	318.1	265.8	247.0
65°	413.4	355.8	274.2	222.9	211.4
67.5°	364.2	305.6	226.0	187.3	174.8
70°	316.0	259.5	186.3	149.6	138.1
72.5°	267.9	212.4	147.6	119.3	116.2
75°	218.7	168.5	110.9	100.5	98.4
77.5°	173.7	127.7	86.9	80.6	78.5
80°	130.8	87.9	65.9	62.8	60.7
82.5°	90.0	54.4	47.1	44.0	44.0
85°	55.5	32.4	29.3	27.2	27.2
87.5°	25.1	13.6	13.6	12.6	11.5
90°	0.4	3.9	8.5	9.9	10.6
92.5°	8.1	6.0	9.2	11.7	12.0
95°	21.6	7.1	11.0	13.4	13.4
97.5°	39.2	29.3	11.3	14.1	14.5
100°	59.7	66.8	11.7	14.5	14.8
102.5°	83.0	87.6	26.1	14.5	15.2
105°	105.3	109.2	77.4	14.8	15.5
107.5°	129.0	132.2	137.5	83.0	36.8
110°	152.7	155.5	159.4	147.7	97.2

TEST NUMBER: P1010997

CATALOG NUMBER: S123RDIP-B775D365UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.3	177.7	181.6	184.8	184.1
115°	197.5	199.7	202.8	206.4	207.8
117.5°	219.4	221.9	223.7	226.5	226.9
120°	239.6	242.8	243.8	246.7	246.7
122.5°	260.1	262.6	264.0	265.7	266.1
125°	278.5	281.3	282.7	283.4	284.1
127.5°	296.8	299.7	301.4	302.5	301.8
130°	313.8	316.6	318.0	319.5	318.7
132.5°	330.1	332.9	333.9	335.4	334.3
135°	346.7	348.8	350.2	351.3	350.2
137.5°	360.8	363.6	364.3	366.1	365.4
140°	374.9	377.1	378.1	379.5	378.8
142.5°	388.0	390.1	391.2	392.2	391.2
145°	400.0	402.5	403.2	403.9	403.9
147.5°	411.7	413.5	414.2	414.9	413.1
150°	422.3	423.3	424.1	424.8	423.7
152.5°	431.8	432.2	432.5	433.9	432.2
155°	440.7	440.0	440.3	442.1	440.0
157.5°	447.7	447.7	447.4	449.5	446.7
160°	454.1	453.7	453.4	455.5	453.0
162.5°	460.1	459.0	458.7	461.2	459.0
165°	464.7	463.6	463.3	466.1	463.6
167.5°	468.6	467.2	467.2	470.0	467.2
170°	471.8	470.3	470.3	473.2	470.3
172.5°	473.9	472.1	472.5	475.3	472.1
175°	475.6	473.9	474.2	476.7	473.9
177.5°	476.4	474.6	474.9	477.8	474.2
180°	475.6	475.6	475.6	475.6	475.6

(END OF REPORT)