

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011017

Luminaire Tested: S123RDIP-B775D805UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011017
REPORT IS A COMBINATION OF REPORTS P993693 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D805UB2750-4F0-XX-W2A-F_4000K
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6032.0 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011017

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1011017

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55
1	98	94	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	41	40
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	39	36	34
4	75	64	56	51	69	60	53	47	51	45	41	42	39	35	35	32	30
5	69	57	49	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	31	35	30	27	29	25	23
7	59	47	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17
10	47	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13889	13889	13889
5°	13911	13397	13361
10°	13802	12894	12640
15°	13622	12271	11849
20°	13388	11594	10966
25°	13145	10890	10129
30°	12834	10141	9140
35°	12514	9407	8239
40°	12213	8608	7244
45°	11827	7827	6349
50°	11401	6993	5423
55°	10960	6101	4574
60°	10538	5186	3713
65°	9993	4247	2898
70°	9306	3212	2071
75°	8319	2174	1642
80°	7101	1511	1151
85°	5331	816	603

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11827 cd/sqm

TEST NUMBER: P1011017

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.3	2.0
10°-20°	337.4	5.6
20°-30°	485.8	8.1
30°-40°	547.1	9.1
40°-50°	523.3	8.7
50°-60°	428.4	7.1
60°-70°	288.8	4.8
70°-80°	144.9	2.4
80°-90°	39.9	0.7
90°-100°	36.0	0.6
100°-110°	174.2	2.9
110°-120°	426.9	7.1
120°-130°	541.9	9.0
130°-140°	578.9	9.6
140°-150°	541.4	9.0
150°-160°	436.7	7.2
160°-170°	281.8	4.7
170°-180°	97.1	1.6
0°-30°	944.5	15.7
0°-40°	1491.7	24.7
0°-60°	2443.4	40.5
0°-90°	2917.1	48.4
90°-120°	637.1	10.6
90°-150°	2299.4	38.1
90°-180°	3115.0	51.6
0°-180°	6032.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1290	1290	1290	1290	1290	
5°	1290	1285	1272	1282	1280	122
15°	1231	1219	1190	1185	1177	347
25°	1120	1094	1045	1023	1012	515
35°	969	931	866	822	803	607
45°	796	749	669	609	584	615
55°	605	554	465	404	383	542
65°	413	356	274	223	211	409
75°	219	168	111	100	98	233
85°	56	32	29	27	27	61
90°	1	8	18	21	23	6
95°	46	15	24	29	29	55
105°	226	235	166	32	33	240
115°	424	429	436	443	446	419
125°	598	604	607	609	610	534
135°	745	749	752	755	752	573
145°	859	865	866	868	868	538
155°	947	945	946	950	945	436
165°	998	996	995	1001	996	282
175°	1022	1018	1019	1024	1018	97
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P1011017

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1290.3	1290.3	1290.3	1290.3	1290.3
2.5°	1295.5	1291.3	1278.8	1290.3	1288.2
5°	1290.3	1285.1	1272.5	1281.9	1279.8
7.5°	1280.9	1275.6	1259.9	1266.2	1263.1
10°	1268.3	1261.0	1242.2	1243.2	1238.0
12.5°	1250.5	1242.2	1218.1	1217.0	1210.8
15°	1230.6	1219.1	1189.8	1184.6	1177.3
17.5°	1206.6	1194.0	1157.4	1146.9	1136.5
20°	1179.4	1162.6	1122.9	1109.3	1096.7
22.5°	1149.0	1129.1	1086.2	1068.4	1056.9
25°	1119.7	1093.6	1045.4	1023.4	1011.9
27.5°	1084.1	1055.9	1003.6	974.3	956.5
30°	1047.5	1016.1	957.5	921.9	905.2
32.5°	1010.9	974.3	911.5	871.7	853.9
35°	969.0	931.4	866.5	821.5	802.6
37.5°	927.2	886.4	818.3	768.1	745.1
40°	887.4	841.4	767.1	712.6	688.6
42.5°	842.4	796.4	718.9	658.2	637.3
45°	796.4	749.3	668.7	609.0	583.9
47.5°	751.4	699.0	619.5	554.6	532.7
50°	701.1	651.9	567.2	502.3	478.2
52.5°	656.1	601.7	518.0	450.0	429.1
55°	604.9	553.6	464.6	403.9	383.0
57.5°	558.8	503.4	413.4	355.8	338.0
60°	510.7	453.1	366.3	309.8	292.0
62.5°	462.5	405.0	318.1	265.8	247.0
65°	413.4	355.8	274.2	222.9	211.4
67.5°	364.2	305.6	226.0	187.3	174.8
70°	316.0	259.5	186.3	149.6	138.1
72.5°	267.9	212.4	147.6	119.3	116.2
75°	218.7	168.5	110.9	100.5	98.4
77.5°	173.7	127.7	86.9	80.6	78.5
80°	130.8	87.9	65.9	62.8	60.7
82.5°	90.0	54.4	47.1	44.0	44.0
85°	55.5	32.4	29.3	27.2	27.2
87.5°	25.1	13.6	13.6	12.6	11.5
90°	0.8	8.4	18.2	21.3	22.8
92.5°	17.5	12.9	19.7	25.1	25.8
95°	46.3	15.2	23.5	28.8	28.8
97.5°	84.3	63.0	24.3	30.4	31.1
100°	128.3	143.5	25.1	31.1	31.9
102.5°	178.4	188.3	56.2	31.1	32.6
105°	226.2	234.6	166.2	31.9	33.4
107.5°	277.1	283.9	295.3	178.4	78.9
110°	327.9	334.0	342.4	317.3	208.8

TEST NUMBER: P1011017

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.5	381.8	390.2	397.0	395.5
115°	424.3	428.9	435.7	443.3	446.4
117.5°	471.4	476.7	480.5	486.6	487.4
120°	514.7	521.5	523.8	529.9	529.9
122.5°	558.7	564.0	567.1	570.9	571.6
125°	598.2	604.3	607.3	608.8	610.3
127.5°	637.7	643.7	647.5	649.8	648.3
130°	674.1	680.2	683.2	686.2	684.7
132.5°	709.0	715.1	717.4	720.4	718.1
135°	744.7	749.2	752.3	754.6	752.3
137.5°	775.1	781.1	782.7	786.4	784.9
140°	805.4	810.0	812.3	815.3	813.8
142.5°	833.5	838.1	840.3	842.6	840.3
145°	859.3	864.6	866.2	867.7	867.7
147.5°	884.4	888.2	889.7	891.2	887.4
150°	907.1	909.4	910.9	912.5	910.2
152.5°	927.6	928.4	929.2	932.2	928.4
155°	946.6	945.1	945.9	949.7	945.1
157.5°	961.8	961.8	961.0	965.6	959.5
160°	975.5	974.7	973.9	978.5	973.2
162.5°	988.4	986.1	985.3	990.6	986.1
165°	998.2	996.0	995.2	1001.3	996.0
167.5°	1006.6	1003.6	1003.6	1009.6	1003.6
170°	1013.4	1010.4	1010.4	1016.5	1010.4
172.5°	1018.0	1014.2	1014.9	1021.0	1014.2
175°	1021.8	1018.0	1018.7	1024.0	1018.0
177.5°	1023.3	1019.5	1020.3	1026.3	1018.7
180°	1021.8	1021.8	1021.8	1021.8	1021.8

(END OF REPORT)