

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011018

Luminaire Tested: S123RDIP-B775D805UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011018
REPORT IS A COMBINATION OF REPORTS P993694 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D805UB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5834.0 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011018

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1011018

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55
1	98	94	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	41	40
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	39	36	34
4	75	64	56	51	69	60	53	47	51	45	41	42	39	35	35	32	30
5	69	57	49	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	31	35	30	27	29	25	23
7	59	47	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17
10	47	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13431	13431	13431
5°	13453	12956	12921
10°	13347	12468	12223
15°	13174	11866	11459
20°	12946	11212	10605
25°	12712	10531	9795
30°	12412	9808	8839
35°	12102	9096	7968
40°	11811	8324	7005
45°	11437	7570	6140
50°	11025	6763	5245
55°	10598	5900	4424
60°	10191	5015	3590
65°	9662	4106	2802
70°	9000	3105	2003
75°	8045	2103	1587
80°	6868	1462	1113
85°	5149	788	583

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11437 cd/sqm

TEST NUMBER: P1011018

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.3	2.0
10°-20°	326.3	5.6
20°-30°	469.8	8.1
30°-40°	529.1	9.1
40°-50°	506.1	8.7
50°-60°	414.3	7.1
60°-70°	279.3	4.8
70°-80°	140.1	2.4
80°-90°	38.6	0.7
90°-100°	34.9	0.6
100°-110°	168.5	2.9
110°-120°	412.9	7.1
120°-130°	524.2	9.0
130°-140°	560.0	9.6
140°-150°	523.6	9.0
150°-160°	422.4	7.2
160°-170°	272.6	4.7
170°-180°	93.9	1.6
0°-30°	913.4	15.7
0°-40°	1442.6	24.7
0°-60°	2363.0	40.5
0°-90°	2821.0	48.4
90°-120°	616.3	10.6
90°-150°	2224.1	38.1
90°-180°	3013.0	51.6
0°-180°	5834.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1248	1248	1248	1248	1248	
5°	1248	1243	1231	1240	1238	118
15°	1190	1179	1151	1146	1138	335
25°	1083	1058	1011	990	979	498
35°	937	901	838	794	776	587
45°	770	725	647	589	565	594
55°	585	535	449	391	370	525
65°	400	344	265	216	204	396
75°	212	163	107	97	95	225
85°	54	31	28	26	26	59
90°	1	8	18	21	22	6
95°	45	15	23	28	28	54
105°	219	227	161	31	32	232
115°	410	415	422	429	432	405
125°	579	584	587	589	590	517
135°	720	725	728	730	728	555
145°	831	836	838	839	839	520
155°	916	914	915	919	914	422
165°	966	963	963	968	963	273
175°	988	985	985	990	985	94
180°	988	988	988	988	988	

TEST NUMBER: P1011018

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1247.8	1247.8	1247.8	1247.8	1247.8
2.5°	1252.9	1248.8	1236.7	1247.8	1245.8
5°	1247.8	1242.7	1230.6	1239.7	1237.7
7.5°	1238.7	1233.6	1218.5	1224.5	1221.5
10°	1226.5	1219.5	1201.2	1202.3	1197.2
12.5°	1209.3	1201.2	1178.0	1177.0	1170.9
15°	1190.1	1179.0	1150.6	1145.6	1138.5
17.5°	1166.8	1154.7	1119.3	1109.2	1099.0
20°	1140.5	1124.3	1085.9	1072.7	1060.6
22.5°	1111.2	1092.0	1050.5	1033.3	1022.1
25°	1082.8	1057.5	1011.0	989.7	978.6
27.5°	1048.4	1021.1	970.5	942.2	925.0
30°	1013.0	982.7	926.0	891.6	875.4
32.5°	977.6	942.2	881.5	843.0	825.8
35°	937.1	900.7	837.9	794.4	776.2
37.5°	896.6	857.2	791.4	742.8	720.5
40°	858.2	813.7	741.8	689.2	665.9
42.5°	814.7	770.1	695.2	636.5	616.3
45°	770.1	724.6	646.7	589.0	564.7
47.5°	726.6	676.0	599.1	536.4	515.1
50°	678.0	630.5	548.5	485.8	462.5
52.5°	634.5	581.9	500.9	435.2	414.9
55°	584.9	535.3	449.3	390.6	370.4
57.5°	540.4	486.8	399.7	344.1	326.9
60°	493.9	438.2	354.2	299.6	282.3
62.5°	447.3	391.6	307.6	257.0	238.8
65°	399.7	344.1	265.1	215.6	204.4
67.5°	352.2	295.5	218.6	181.1	169.0
70°	305.6	251.0	180.1	144.7	133.6
72.5°	259.1	205.4	142.7	115.4	112.3
75°	211.5	162.9	107.3	97.2	95.1
77.5°	168.0	123.5	84.0	77.9	75.9
80°	126.5	85.0	63.8	60.7	58.7
82.5°	87.0	52.6	45.5	42.5	42.5
85°	53.6	31.4	28.3	26.3	26.3
87.5°	24.3	13.2	13.2	12.1	11.1
90°	0.7	8.1	17.6	20.6	22.0
92.5°	16.9	12.5	19.1	24.2	25.0
95°	44.8	14.7	22.8	27.9	27.9
97.5°	81.5	60.9	23.5	29.4	30.1
100°	124.1	138.8	24.2	30.1	30.8
102.5°	172.6	182.1	54.3	30.1	31.6
105°	218.8	226.9	160.8	30.8	32.3
107.5°	268.0	274.6	285.6	172.6	76.4
110°	317.2	323.1	331.2	306.9	201.9

TEST NUMBER: P1011018

CATALOG NUMBER: S123RDIP-B775D805UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	364.2	369.3	377.4	384.0	382.6
115°	410.5	414.9	421.5	428.8	431.8
117.5°	456.0	461.1	464.8	470.7	471.4
120°	497.8	504.4	506.7	512.5	512.5
122.5°	540.4	545.6	548.5	552.2	552.9
125°	578.6	584.5	587.4	588.9	590.4
127.5°	616.8	622.7	626.3	628.5	627.1
130°	652.0	657.9	660.8	663.8	662.3
132.5°	685.8	691.7	693.9	696.8	694.6
135°	720.3	724.7	727.7	729.9	727.7
137.5°	749.7	755.6	757.0	760.7	759.2
140°	779.1	783.5	785.7	788.6	787.1
142.5°	806.2	810.6	812.8	815.0	812.8
145°	831.2	836.3	837.8	839.3	839.3
147.5°	855.4	859.1	860.6	862.0	858.4
150°	877.5	879.7	881.1	882.6	880.4
152.5°	897.3	898.0	898.8	901.7	898.0
155°	915.6	914.2	914.9	918.6	914.2
157.5°	930.3	930.3	929.6	934.0	928.1
160°	943.5	942.8	942.1	946.5	941.3
162.5°	956.0	953.8	953.1	958.2	953.8
165°	965.6	963.4	962.6	968.5	963.4
167.5°	973.7	970.7	970.7	976.6	970.7
170°	980.3	977.3	977.3	983.2	977.3
172.5°	984.7	981.0	981.7	987.6	981.0
175°	988.3	984.7	985.4	990.5	984.7
177.5°	989.8	986.1	986.9	992.7	985.4
180°	988.3	988.3	988.3	988.3	988.3

(END OF REPORT)