

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011306

Luminaire Tested: S123DIP-B1165D1195UB35-4F0-XX-W2A-D4

Issue Date: 5/7/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1011306  
REPORT IS A COMBINATION OF REPORTS P989417 AND P1007351  
Test Lab: INNOVATION CENTER  
Issue Date: 5/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-B1165D1195UB35-4F0-XX-W2A-D4  
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9227.1 lumens  
Efficiency: N/A  
Efficacy: 95.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37  
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 96.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1011306

CATALOG NUMBER: S123DIP-B1165D1195UB35-4F0-XX-W2A-D4

### Luminous Intensity Polar Plot



TEST NUMBER: P1011306

CATALOG NUMBER: S123DIP-B1165D1195UB35-4F0-XX-W2A-D4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |    |    |    |    |  |    |    |    |  |    |    |    |  |    |    |    |
|-----|-----|-----|-----|-----|----|----|----|----|--|----|----|----|--|----|----|----|--|----|----|----|
| RF  | 20  |     |     |     | 20 |    |    |    |  | 20 |    |    |  |    | 20 |    |  |    |    | 20 |
| RC  | 80  |     |     |     | 70 |    |    |    |  | 50 |    |    |  |    | 30 |    |  |    |    | 0  |
| RW  | 70  | 50  | 30  | 10  | 70 | 50 | 30 | 10 |  | 50 | 30 | 10 |  | 50 | 30 | 10 |  | 50 | 30 | 10 |
| RCR |     |     |     |     |    |    |    |    |  |    |    |    |  |    |    |    |  |    |    |    |
| 0   | 107 | 107 | 107 | 107 | 98 | 98 | 98 | 98 |  | 83 | 83 | 83 |  | 68 | 68 | 68 |  | 55 | 55 | 55 |
| 1   | 96  | 92  | 87  | 84  | 88 | 84 | 81 | 77 |  | 71 | 68 | 66 |  | 58 | 56 | 55 |  | 47 | 45 | 44 |
| 2   | 87  | 79  | 73  | 67  | 80 | 73 | 67 | 63 |  | 61 | 57 | 54 |  | 51 | 47 | 45 |  | 41 | 38 | 36 |
| 3   | 79  | 70  | 62  | 56  | 73 | 64 | 57 | 52 |  | 54 | 49 | 45 |  | 44 | 41 | 37 |  | 36 | 33 | 31 |
| 4   | 73  | 61  | 53  | 47  | 66 | 57 | 49 | 44 |  | 48 | 42 | 38 |  | 39 | 35 | 32 |  | 32 | 29 | 26 |
| 5   | 66  | 54  | 46  | 40  | 61 | 50 | 43 | 37 |  | 42 | 37 | 32 |  | 35 | 31 | 27 |  | 28 | 25 | 23 |
| 6   | 61  | 49  | 40  | 34  | 56 | 45 | 38 | 32 |  | 38 | 32 | 28 |  | 32 | 27 | 24 |  | 26 | 22 | 20 |
| 7   | 56  | 44  | 36  | 30  | 52 | 41 | 33 | 28 |  | 35 | 29 | 25 |  | 29 | 24 | 21 |  | 23 | 20 | 17 |
| 8   | 52  | 40  | 32  | 26  | 48 | 37 | 30 | 25 |  | 31 | 26 | 22 |  | 26 | 22 | 19 |  | 21 | 18 | 16 |
| 9   | 49  | 36  | 29  | 24  | 45 | 34 | 27 | 22 |  | 29 | 23 | 19 |  | 24 | 20 | 17 |  | 20 | 16 | 14 |
| 10  | 46  | 33  | 26  | 21  | 42 | 31 | 24 | 20 |  | 26 | 21 | 17 |  | 22 | 18 | 15 |  | 18 | 15 | 13 |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°    | 45°   | 90°   |
|-----|-------|-------|-------|
| 0°  | 15632 | 15632 | 15632 |
| 5°  | 15675 | 15174 | 15162 |
| 10° | 15529 | 14763 | 14650 |
| 15° | 15323 | 14310 | 14108 |
| 20° | 15032 | 13803 | 13526 |
| 25° | 14672 | 13234 | 12922 |
| 30° | 14306 | 12718 | 12317 |
| 35° | 13893 | 12177 | 11822 |
| 40° | 13500 | 11682 | 11301 |
| 45° | 13063 | 11204 | 10872 |
| 50° | 12632 | 10728 | 10406 |
| 55° | 12154 | 10242 | 9976  |
| 60° | 11687 | 9744  | 9537  |
| 65° | 11204 | 9214  | 9022  |
| 70° | 10484 | 8617  | 8492  |
| 75° | 9567  | 7939  | 7945  |
| 80° | 8502  | 7252  | 7320  |
| 85° | 7444  | 6697  | 6873  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13063 cd/sqm

TEST NUMBER: P1011306

CATALOG NUMBER: S123DIP-B1165D1195UB35-4F0-XX-W2A-D4

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 137.8  | 1.5       |
| 10°-20°   | 392.8  | 4.3       |
| 20°-30°   | 587.3  | 6.4       |
| 30°-40°   | 701.2  | 7.6       |
| 40°-50°   | 733.7  | 8.0       |
| 50°-60°   | 688.5  | 7.5       |
| 60°-70°   | 575.1  | 6.2       |
| 70°-80°   | 411.2  | 4.5       |
| 80°-90°   | 247.9  | 2.7       |
| 90°-100°  | 481.1  | 5.2       |
| 100°-110° | 1028.0 | 11.1      |
| 110°-120° | 967.6  | 10.5      |
| 120°-130° | 753.4  | 8.2       |
| 130°-140° | 580.1  | 6.3       |
| 140°-150° | 422.4  | 4.6       |
| 150°-160° | 291.9  | 3.2       |
| 160°-170° | 171.5  | 1.9       |
| 170°-180° | 55.8   | 0.6       |
| 0°-30°    | 1117.9 | 12.1      |
| 0°-40°    | 1819.1 | 19.7      |
| 0°-60°    | 3241.3 | 35.1      |
| 0°-90°    | 4475.5 | 48.5      |
| 90°-120°  | 2476.6 | 26.8      |
| 90°-150°  | 4232.5 | 45.9      |
| 90°-180°  | 4752.0 | 51.5      |
| 0°-180°   | 9227.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|------|------|-------|------|-------|------|------|
| 0°   | 1452 | 1452  | 1452 | 1452  | 1452 |      |
| 5°   | 1454 | 1451  | 1441 | 1454  | 1452 | 138  |
| 15°  | 1384 | 1389  | 1388 | 1403  | 1402 | 390  |
| 25°  | 1250 | 1266  | 1270 | 1291  | 1291 | 576  |
| 35°  | 1076 | 1101  | 1122 | 1145  | 1152 | 673  |
| 45°  | 880  | 918   | 957  | 987   | 1000 | 678  |
| 55°  | 671  | 723   | 780  | 823   | 835  | 601  |
| 65°  | 464  | 525   | 595  | 642   | 658  | 458  |
| 75°  | 252  | 326   | 405  | 457   | 476  | 269  |
| 85°  | 78   | 157   | 240  | 294   | 310  | 80   |
| 90°  | 23   | 112   | 208  | 265   | 282  | 18   |
| 95°  | 57   | 208   | 848  | 407   | 357  | 56   |
| 105° | 148  | 251   | 1056 | 1802  | 1660 | 156  |
| 115° | 247  | 325   | 801  | 1694  | 1938 | 245  |
| 125° | 337  | 397   | 720  | 1296  | 1517 | 300  |
| 135° | 393  | 466   | 679  | 1046  | 1209 | 303  |
| 145° | 446  | 509   | 652  | 832   | 920  | 279  |
| 155° | 505  | 545   | 631  | 717   | 747  | 232  |
| 165° | 552  | 567   | 604  | 641   | 652  | 155  |
| 175° | 575  | 575   | 580  | 588   | 586  | 55   |
| 180° | 576  | 576   | 576  | 576   | 576  |      |

TEST NUMBER: P1011306

CATALOG NUMBER: S123DIP-B1165D1195UB35-4F0-XX-W2A-D4

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|--------|--------|--------|--------|--------|--------|
| 0°     | 1452.3 | 1452.3 | 1452.3 | 1452.3 | 1452.3 |
| 2.5°   | 1460.3 | 1455.5 | 1442.8 | 1455.5 | 1453.9 |
| 5°     | 1453.9 | 1450.8 | 1441.3 | 1453.9 | 1452.3 |
| 7.5°   | 1442.8 | 1442.8 | 1433.4 | 1449.2 | 1447.6 |
| 10°    | 1427.0 | 1430.2 | 1422.3 | 1438.1 | 1434.9 |
| 12.5°  | 1408.0 | 1412.8 | 1408.0 | 1422.3 | 1419.1 |
| 15°    | 1384.3 | 1389.1 | 1387.5 | 1403.3 | 1401.7 |
| 17.5°  | 1355.8 | 1365.3 | 1363.7 | 1378.0 | 1374.8 |
| 20°    | 1324.2 | 1333.7 | 1336.8 | 1351.1 | 1352.7 |
| 22.5°  | 1291.0 | 1300.5 | 1305.2 | 1324.2 | 1322.6 |
| 25°    | 1249.8 | 1265.7 | 1270.4 | 1291.0 | 1291.0 |
| 27.5°  | 1210.3 | 1227.7 | 1237.2 | 1254.6 | 1256.2 |
| 30°    | 1167.6 | 1188.1 | 1200.8 | 1219.8 | 1219.8 |
| 32.5°  | 1120.1 | 1143.8 | 1161.2 | 1181.8 | 1186.6 |
| 35°    | 1075.8 | 1101.1 | 1121.7 | 1145.4 | 1151.7 |
| 37.5°  | 1028.3 | 1056.8 | 1080.6 | 1107.4 | 1112.2 |
| 40°    | 980.9  | 1009.4 | 1041.0 | 1067.9 | 1074.2 |
| 42.5°  | 928.7  | 965.1  | 998.3  | 1028.3 | 1037.8 |
| 45°    | 879.6  | 917.6  | 957.2  | 987.2  | 999.9  |
| 47.5°  | 827.4  | 870.1  | 914.4  | 947.7  | 957.2  |
| 50°    | 776.8  | 821.1  | 870.1  | 906.5  | 917.6  |
| 52.5°  | 723.0  | 770.5  | 825.8  | 863.8  | 878.0  |
| 55°    | 670.8  | 723.0  | 780.0  | 822.7  | 835.3  |
| 57.5°  | 620.2  | 674.0  | 735.7  | 778.4  | 792.6  |
| 60°    | 566.4  | 623.3  | 688.2  | 732.5  | 749.9  |
| 62.5°  | 515.8  | 574.3  | 643.9  | 688.2  | 704.0  |
| 65°    | 463.5  | 525.2  | 594.9  | 642.3  | 658.1  |
| 67.5°  | 411.3  | 476.2  | 545.8  | 598.0  | 610.7  |
| 70°    | 356.0  | 424.0  | 499.9  | 550.6  | 566.4  |
| 72.5°  | 305.3  | 373.4  | 452.5  | 504.7  | 520.5  |
| 75°    | 251.5  | 325.9  | 405.0  | 457.2  | 476.2  |
| 77.5°  | 205.7  | 280.0  | 359.1  | 414.5  | 428.7  |
| 80°    | 156.6  | 234.1  | 316.4  | 370.2  | 386.0  |
| 82.5°  | 113.9  | 193.0  | 276.9  | 330.7  | 346.5  |
| 85°    | 77.5   | 156.6  | 240.5  | 294.3  | 310.1  |
| 87.5°  | 47.5   | 126.6  | 207.3  | 261.0  | 276.9  |
| 90°    | 22.9   | 112.1  | 208.0  | 265.2  | 282.2  |
| 92.5°  | 36.5   | 157.0  | 383.0  | 292.4  | 294.4  |
| 95°    | 57.0   | 208.0  | 848.0  | 407.4  | 356.8  |
| 97.5°  | 78.8   | 220.3  | 1210.5 | 701.8  | 487.9  |
| 100°   | 100.5  | 227.6  | 1241.8 | 1244.6 | 930.4  |
| 102.5° | 123.5  | 237.2  | 1156.5 | 1593.2 | 1346.2 |
| 105°   | 148.0  | 250.6  | 1056.2 | 1802.4 | 1660.4 |
| 107.5° | 172.0  | 267.6  | 966.2  | 1887.6 | 1861.5 |
| 110°   | 198.4  | 285.2  | 891.9  | 1880.9 | 1971.6 |

TEST NUMBER: P1011306

CATALOG NUMBER: S123DIP-B1165D1195UB35-4F0-XX-W2A-D4

**CANDELA DISTRIBUTION (continued):**

|        | 0°    | 22.5° | 45°   | 67.5°  | 90°    |
|--------|-------|-------|-------|--------|--------|
| 112.5° | 224.0 | 303.8 | 838.0 | 1804.0 | 1986.7 |
| 115°   | 246.9 | 324.8 | 800.9 | 1694.2 | 1938.3 |
| 117.5° | 271.4 | 343.0 | 771.7 | 1577.4 | 1847.2 |
| 120°   | 295.5 | 361.1 | 750.8 | 1466.4 | 1728.8 |
| 122.5° | 317.6 | 379.8 | 734.8 | 1377.0 | 1619.1 |
| 125°   | 337.0 | 397.0 | 719.9 | 1296.4 | 1517.4 |
| 127.5° | 353.3 | 416.6 | 708.5 | 1228.8 | 1428.6 |
| 130°   | 368.5 | 435.2 | 697.1 | 1165.6 | 1352.4 |
| 132.5° | 378.7 | 452.2 | 688.0 | 1106.0 | 1280.2 |
| 135°   | 392.6 | 466.2 | 679.0 | 1046.2 | 1208.6 |
| 137.5° | 405.5 | 479.1 | 670.3 | 987.8  | 1135.0 |
| 140°   | 416.7 | 490.8 | 662.8 | 932.0  | 1059.4 |
| 142.5° | 430.7 | 499.6 | 654.1 | 878.8  | 987.0  |
| 145°   | 445.9 | 509.0 | 651.8 | 831.8  | 920.3  |
| 147.5° | 459.4 | 518.8 | 648.3 | 793.6  | 863.5  |
| 150°   | 474.6 | 527.0 | 643.6 | 762.0  | 813.6  |
| 152.5° | 489.7 | 535.8 | 637.8 | 738.6  | 775.4  |
| 155°   | 504.9 | 544.6 | 630.8 | 717.1  | 747.4  |
| 157.5° | 516.5 | 552.1 | 625.0 | 696.1  | 720.6  |
| 160°   | 530.5 | 558.6 | 618.0 | 676.9  | 694.9  |
| 162.5° | 541.0 | 563.2 | 611.0 | 658.8  | 671.6  |
| 165°   | 551.5 | 567.2 | 604.0 | 640.7  | 651.8  |
| 167.5° | 559.7 | 570.8 | 597.0 | 625.0  | 632.0  |
| 170°   | 566.7 | 572.5 | 590.0 | 611.0  | 614.5  |
| 172.5° | 571.3 | 574.2 | 584.2 | 598.8  | 598.2  |
| 175°   | 574.8 | 575.4 | 579.5 | 587.7  | 586.5  |
| 177.5° | 577.2 | 576.0 | 576.0 | 580.7  | 578.3  |
| 180°   | 576.0 | 576.0 | 576.0 | 576.0  | 576.0  |

(END OF REPORT)