

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011062

Luminaire Tested: S123DIP-B1000D1025UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011062
REPORT IS A COMBINATION OF REPORTS P989077 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D1025UB50-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7291.0 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011062

CATALOG NUMBER: S123DIP-B1000D1025UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011062

CATALOG NUMBER: S123DIP-B1000D1025UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	94	90	87	91	88	84	81	75	72	70	63	62	60	53	52	50
2	90	82	76	71	83	76	71	66	66	62	58	56	53	50	46	44	42
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31
5	69	57	49	43	64	53	46	40	46	40	36	39	35	31	33	30	27
6	63	51	43	37	59	48	40	35	41	36	31	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16283	16283	16283
5°	16323	15721	15697
10°	16178	15189	15033
15°	15953	14635	14309
20°	15696	14022	13592
25°	15362	13373	12824
30°	14997	12702	12018
35°	14614	12016	11216
40°	14214	11298	10428
45°	13773	10596	9603
50°	13326	9815	8776
55°	12751	9001	7939
60°	12158	8103	7047
65°	11603	7132	6116
70°	10802	6054	5032
75°	9647	4793	3906
80°	8333	3369	2763
85°	6493	1810	1383

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13773 cd/sqm

TEST NUMBER: P1011062

CATALOG NUMBER: S123DIP-B1000D1025UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.6	2.0
10°-20°	402.7	5.5
20°-30°	594.7	8.2
30°-40°	694.6	9.5
40°-50°	698.3	9.6
50°-60°	613.4	8.4
60°-70°	456.8	6.3
70°-80°	260.0	3.6
80°-90°	76.5	1.0
90°-100°	77.9	1.1
100°-110°	235.7	3.2
110°-120°	401.2	5.5
120°-130°	527.8	7.2
130°-140°	593.3	8.1
140°-150°	583.2	8.0
150°-160°	491.0	6.7
160°-170°	326.9	4.5
170°-180°	114.5	1.6
0°-30°	1140.0	15.6
0°-40°	1834.6	25.2
0°-60°	3146.3	43.2
0°-90°	3939.6	54.0
90°-120°	714.7	9.8
90°-150°	2419.0	33.2
90°-180°	3351.0	46.0
0°-180°	7291.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1513	1513	1513	1513	1513	
5°	1514	1508	1493	1506	1504	144
15°	1441	1436	1419	1430	1422	406
25°	1308	1301	1284	1285	1281	603
35°	1132	1124	1107	1099	1093	708
45°	927	922	905	890	883	716
55°	704	702	686	671	665	630
65°	480	474	460	450	446	474
75°	254	248	244	238	234	271
85°	68	65	65	62	62	73
90°	1	10	23	27	28	9
95°	56	63	70	74	74	62
105°	214	216	224	224	226	229
115°	404	407	405	406	405	400
125°	591	594	592	588	584	527
135°	767	772	772	768	766	591
145°	930	932	935	934	930	581
155°	1065	1065	1066	1070	1063	490
165°	1160	1157	1157	1163	1156	327
175°	1207	1203	1203	1209	1202	115
180°	1210	1210	1210	1210	1210	

TEST NUMBER: P1011062

CATALOG NUMBER: S123DIP-B1000D1025UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1512.7	1512.7	1512.7	1512.7	1512.7
2.5°	1519.2	1514.0	1499.7	1512.7	1511.4
5°	1514.0	1507.5	1493.2	1506.2	1503.6
7.5°	1502.3	1495.8	1481.5	1493.2	1491.9
10°	1486.7	1480.2	1463.3	1475.0	1472.4
12.5°	1465.9	1460.7	1445.1	1452.9	1451.6
15°	1441.2	1436.0	1419.1	1429.5	1421.7
17.5°	1413.9	1407.4	1390.5	1398.3	1395.7
20°	1382.7	1374.9	1358.0	1363.2	1359.3
22.5°	1347.6	1339.7	1322.8	1326.7	1321.5
25°	1308.5	1300.7	1283.8	1285.1	1281.2
27.5°	1268.2	1260.4	1242.2	1243.5	1239.6
30°	1224.0	1217.5	1199.3	1199.3	1190.2
32.5°	1179.8	1170.7	1157.6	1148.5	1144.6
35°	1131.6	1123.8	1106.9	1099.1	1092.6
37.5°	1083.5	1073.1	1056.2	1047.1	1043.2
40°	1032.8	1025.0	1006.8	996.4	991.2
42.5°	982.0	972.9	954.7	944.3	939.1
45°	927.4	922.2	905.3	889.7	883.2
47.5°	874.1	866.3	850.7	835.1	829.9
50°	819.5	813.0	796.0	781.7	773.9
52.5°	762.2	758.3	740.1	728.4	720.6
55°	703.7	702.4	685.5	671.2	664.7
57.5°	649.1	643.9	630.9	617.8	610.0
60°	589.2	587.9	572.3	560.6	554.1
62.5°	535.9	532.0	516.4	504.7	500.8
65°	480.0	473.5	460.5	450.1	446.1
67.5°	420.1	414.9	404.5	395.4	390.2
70°	366.8	359.0	351.2	342.1	335.6
72.5°	310.9	305.7	296.6	288.8	286.2
75°	253.6	248.4	244.5	238.0	234.1
77.5°	202.9	200.3	195.1	189.9	189.9
80°	153.5	149.6	147.0	145.7	145.7
82.5°	105.4	105.4	105.4	102.8	101.5
85°	67.6	65.0	65.0	62.4	62.4
87.5°	33.8	29.9	28.6	27.3	27.3
90°	1.0	10.5	22.8	26.6	28.5
92.5°	28.5	34.2	39.9	42.8	40.9
95°	56.1	62.7	70.3	74.1	74.1
97.5°	92.2	96.9	102.6	107.4	106.4
100°	129.2	134.9	139.7	142.5	144.4
102.5°	172.0	174.8	181.5	184.3	183.4
105°	213.8	215.7	224.2	224.2	226.1
107.5°	263.2	264.1	267.9	270.8	269.8
110°	308.8	310.7	312.6	316.4	314.5



TEST NUMBER: P1011062

CATALOG NUMBER: S123DIP-B1000D1025UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	356.3	357.3	357.3	362.0	362.0
115°	403.8	406.7	404.8	405.7	404.8
117.5°	452.3	453.2	451.3	451.3	448.5
120°	496.9	502.6	497.9	496.9	495.0
122.5°	543.5	547.3	545.4	542.5	539.7
125°	591.0	593.8	591.9	588.1	584.3
127.5°	634.7	640.4	638.5	632.8	629.0
130°	678.4	686.0	683.2	679.4	672.7
132.5°	722.1	729.7	727.8	723.1	718.3
135°	766.8	772.5	771.5	767.7	765.8
137.5°	807.6	812.4	815.2	810.5	807.6
140°	850.4	855.1	856.1	855.1	848.5
142.5°	889.3	894.1	896.0	895.0	890.3
145°	930.2	932.1	935.0	934.0	930.2
147.5°	965.4	969.2	972.0	972.0	966.3
150°	1002.4	1004.3	1006.2	1006.2	1000.5
152.5°	1032.8	1035.7	1036.6	1038.5	1033.8
155°	1065.1	1065.1	1066.1	1069.9	1063.2
157.5°	1092.7	1091.7	1092.7	1096.5	1090.8
160°	1118.3	1116.4	1116.4	1121.2	1117.4
162.5°	1141.1	1138.3	1139.2	1144.0	1137.3
165°	1160.1	1157.3	1157.3	1163.0	1156.3
167.5°	1176.3	1172.5	1173.4	1179.1	1173.4
170°	1189.6	1185.8	1185.8	1192.4	1185.8
172.5°	1200.0	1196.2	1196.2	1201.9	1195.3
175°	1206.7	1202.9	1202.9	1208.6	1201.9
177.5°	1210.5	1206.7	1206.7	1212.4	1205.7
180°	1209.5	1209.5	1209.5	1209.5	1209.5

(END OF REPORT)