

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011387

Luminaire Tested: S123DIP-B1165D585UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011387
REPORT IS A COMBINATION OF REPORTS P989531 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D585UB30-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6897.9 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011387

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011387

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74
1	102	98	93	90	96	92	89	85	82	80	77	73	71	69	65	64	62
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	55	52
3	85	75	67	61	80	71	64	59	64	58	54	57	53	49	51	47	44
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	45	41	38
5	71	59	51	45	67	56	49	43	51	44	40	46	40	36	41	37	33
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29
7	61	48	40	34	57	46	38	33	42	35	31	38	32	28	34	29	26
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	24	21
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	27	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19719	19719	19719
5°	19769	19039	19011
10°	19593	18395	18206
15°	19321	17724	17330
20°	19008	16981	16460
25°	18604	16196	15531
30°	18162	15383	14554
35°	17699	14553	13583
40°	17214	13682	12629
45°	16681	12833	11630
50°	16138	11887	10629
55°	15441	10901	9615
60°	14725	9813	8534
65°	14052	8636	7407
70°	13081	7331	6093
75°	11686	5806	4730
80°	10092	4080	3345
85°	7867	2194	1676

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16681 cd/sqm

TEST NUMBER: P1011387

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.7	2.5
10°-20°	487.7	7.1
20°-30°	720.3	10.4
30°-40°	841.2	12.2
40°-50°	845.7	12.3
50°-60°	742.9	10.8
60°-70°	553.3	8.0
70°-80°	314.9	4.6
80°-90°	91.1	1.3
90°-100°	160.4	2.3
100°-110°	448.4	6.5
110°-120°	437.2	6.3
120°-130°	348.1	5.0
130°-140°	274.8	4.0
140°-150°	205.0	3.0
150°-160°	143.0	2.1
160°-170°	84.0	1.2
170°-180°	27.3	0.4
0°-30°	1380.7	20.0
0°-40°	2221.8	32.2
0°-60°	3810.4	55.2
0°-90°	4769.6	69.1
90°-120°	1046.0	15.2
90°-150°	1874.0	27.2
90°-180°	2128.0	30.8
0°-180°	6897.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1832	1832	1832	1832	1832	
5°	1834	1826	1808	1824	1821	174
15°	1745	1739	1719	1731	1722	492
25°	1585	1575	1555	1556	1552	730
35°	1370	1361	1341	1331	1323	857
45°	1123	1117	1096	1078	1070	867
55°	852	851	830	813	805	763
65°	581	573	558	545	540	573
75°	307	301	296	288	284	328
85°	82	79	79	76	76	88
90°	1	7	14	16	17	7
95°	19	63	339	99	66	21
105°	66	98	459	803	727	70
115°	117	146	351	771	884	116
125°	163	192	328	594	697	145
135°	191	228	323	489	565	147
145°	218	249	319	401	442	136
155°	247	267	309	351	366	114
165°	270	278	296	314	319	76
175°	282	282	284	288	287	27
180°	282	282	282	282	282	

TEST NUMBER: P1011387

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1832.0	1832.0	1832.0	1832.0	1832.0
2.5°	1839.9	1833.6	1816.3	1832.0	1830.5
5°	1833.6	1825.7	1808.4	1824.2	1821.0
7.5°	1819.4	1811.6	1794.2	1808.4	1806.8
10°	1800.5	1792.7	1772.2	1786.4	1783.2
12.5°	1775.3	1769.0	1750.1	1759.6	1758.0
15°	1745.4	1739.1	1718.6	1731.2	1721.8
17.5°	1712.3	1704.4	1684.0	1693.4	1690.3
20°	1674.5	1665.1	1644.6	1650.9	1646.2
22.5°	1632.0	1622.5	1602.1	1606.8	1600.5
25°	1584.7	1575.3	1554.8	1556.4	1551.6
27.5°	1535.9	1526.4	1504.4	1506.0	1501.2
30°	1482.3	1474.5	1452.4	1452.4	1441.4
32.5°	1428.8	1417.7	1402.0	1391.0	1386.2
35°	1370.5	1361.0	1340.6	1331.1	1323.2
37.5°	1312.2	1299.6	1279.1	1268.1	1263.4
40°	1250.8	1241.3	1219.3	1206.7	1200.4
42.5°	1189.3	1178.3	1156.3	1143.6	1137.3
45°	1123.2	1116.9	1096.4	1077.5	1069.6
47.5°	1058.6	1049.1	1030.2	1011.3	1005.0
50°	992.4	984.5	964.1	946.7	937.3
52.5°	923.1	918.4	896.3	882.2	872.7
55°	852.2	850.6	830.2	812.8	805.0
57.5°	786.1	779.8	764.0	748.3	738.8
60°	713.6	712.0	693.1	678.9	671.1
62.5°	649.0	644.3	625.4	611.2	606.5
65°	581.3	573.4	557.6	545.0	540.3
67.5°	508.8	502.5	489.9	478.9	472.6
70°	444.2	434.8	425.3	414.3	406.4
72.5°	376.5	370.2	359.2	349.7	346.6
75°	307.2	300.9	296.2	288.3	283.5
77.5°	245.7	242.6	236.3	230.0	230.0
80°	185.9	181.2	178.0	176.4	176.4
82.5°	127.6	127.6	127.6	124.4	122.9
85°	81.9	78.8	78.8	75.6	75.6
87.5°	41.0	36.2	34.7	33.1	33.1
90°	1.1	6.8	14.3	16.0	16.6
92.5°	8.6	34.2	106.3	36.3	30.3
95°	19.4	63.2	338.9	98.8	66.3
97.5°	30.9	72.3	521.2	248.6	136.0
100°	42.3	79.8	541.2	520.0	358.3
102.5°	54.3	88.3	504.0	696.3	567.4
105°	66.3	98.0	459.4	803.4	726.9
107.5°	78.9	109.4	420.0	850.6	830.9
110°	92.6	121.1	387.4	852.0	890.3

TEST NUMBER: P1011387

CATALOG NUMBER: S123DIP-B1165D585UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	105.1	133.4	365.7	819.8	902.3
115°	117.1	146.0	351.4	770.6	884.0
117.5°	129.1	158.0	341.7	718.0	844.0
120°	141.7	170.0	335.4	668.3	791.4
122.5°	152.6	181.4	331.4	629.2	742.3
125°	162.9	192.3	328.0	594.3	697.2
127.5°	170.9	202.6	326.3	565.8	658.3
130°	178.3	211.7	324.6	539.4	626.3
132.5°	184.0	220.0	324.0	514.9	594.9
135°	190.9	227.7	323.4	489.4	565.2
137.5°	197.1	234.0	322.3	465.4	533.7
140°	203.4	239.8	321.7	442.0	500.6
142.5°	210.3	244.8	320.6	420.6	469.7
145°	217.7	249.4	319.4	401.4	441.7
147.5°	225.1	254.3	317.7	386.6	417.7
150°	232.6	258.2	315.4	373.4	397.2
152.5°	240.0	262.5	312.6	362.0	380.0
155°	247.4	266.9	309.2	351.4	366.3
157.5°	253.1	270.5	306.3	341.2	353.2
160°	260.0	273.8	302.9	331.7	340.6
162.5°	265.1	276.0	299.4	322.9	329.2
165°	270.3	278.0	296.0	314.0	319.4
167.5°	274.3	279.8	292.6	306.3	309.7
170°	277.7	280.6	289.2	299.4	301.2
172.5°	280.0	281.4	286.3	293.4	293.2
175°	281.7	282.0	284.0	288.0	287.4
177.5°	282.9	282.3	282.3	284.6	283.4
180°	282.3	282.3	282.3	282.3	282.3

(END OF REPORT)