

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011395

Luminaire Tested: S123DIP-B1165D585UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011395
REPORT IS A COMBINATION OF REPORTS P989539 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D585UB35-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6815.0 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011395

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011395

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70		
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	64	63	59		
2	93	85	79	74	88	81	75	70	73	68	64	65	62	59	58	55	53	49		
3	85	75	67	61	80	71	64	59	64	59	54	58	53	50	51	48	45	42		
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39	36		
5	71	59	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34	31		
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30	27		
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27	24		
8	57	44	36	30	54	42	35	29	38	32	28	35	30	26	32	27	24	22		
9	53	40	32	27	50	39	31	26	35	29	25	32	27	23	29	25	22	20		
10	50	37	30	25	47	35	29	24	33	27	22	30	25	21	27	23	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19807	19807	19807
5°	19856	19123	19094
10°	19680	18476	18287
15°	19406	17803	17406
20°	19092	17055	16532
25°	18686	16267	15600
30°	18242	15451	14618
35°	17776	14618	13643
40°	17290	13742	12683
45°	16754	12889	11681
50°	16209	11939	10675
55°	15510	10948	9656
60°	14789	9857	8571
65°	14113	8675	7440
70°	13140	7364	6120
75°	11735	5832	4751
80°	10136	4098	3361
85°	7905	2203	1682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16754 cd/sqm

TEST NUMBER: P1011395

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.5	2.5
10°-20°	489.8	7.2
20°-30°	723.4	10.6
30°-40°	844.9	12.4
40°-50°	849.4	12.5
50°-60°	746.1	10.9
60°-70°	555.7	8.2
70°-80°	316.2	4.6
80°-90°	91.5	1.3
90°-100°	47.0	0.7
100°-110°	142.4	2.1
110°-120°	242.3	3.6
120°-130°	318.8	4.7
130°-140°	358.4	5.3
140°-150°	352.3	5.2
150°-160°	296.6	4.4
160°-170°	197.5	2.9
170°-180°	69.1	1.0
0°-30°	1386.7	20.3
0°-40°	2231.6	32.7
0°-60°	3827.2	56.2
0°-90°	4790.5	70.3
90°-120°	431.8	6.3
90°-150°	1461.2	21.4
90°-180°	2024.0	29.7
0°-180°	6815.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1840	1840	1840	1840	1840	
5°	1842	1834	1816	1832	1829	175
15°	1753	1747	1726	1739	1729	494
25°	1592	1582	1562	1563	1558	733
35°	1376	1367	1346	1337	1329	861
45°	1128	1122	1101	1082	1074	871
55°	856	854	834	816	808	767
65°	584	576	560	547	543	576
75°	308	302	298	290	285	330
85°	82	79	79	76	76	88
90°	1	6	14	16	17	8
95°	34	38	42	45	45	37
105°	129	130	136	136	137	138
115°	244	246	244	245	244	241
125°	357	359	358	355	353	318
135°	463	467	466	464	463	357
145°	562	563	565	564	562	351
155°	643	643	644	646	642	296
165°	701	699	699	702	698	198
175°	729	727	727	730	726	69
180°	731	731	731	731	731	

TEST NUMBER: P1011395

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1840.1	1840.1	1840.1	1840.1	1840.1
2.5°	1848.0	1841.7	1824.3	1840.1	1838.5
5°	1841.7	1833.8	1816.4	1832.2	1829.0
7.5°	1827.5	1819.5	1802.1	1816.4	1814.8
10°	1808.5	1800.6	1780.0	1794.2	1791.1
12.5°	1783.2	1776.8	1757.8	1767.3	1765.7
15°	1753.1	1746.8	1726.2	1738.9	1729.4
17.5°	1719.9	1712.0	1691.4	1700.9	1697.7
20°	1681.9	1672.4	1651.8	1658.2	1653.4
22.5°	1639.2	1629.7	1609.1	1613.9	1607.5
25°	1591.7	1582.2	1561.6	1563.2	1558.5
27.5°	1542.7	1533.2	1511.0	1512.6	1507.8
30°	1488.9	1481.0	1458.8	1458.8	1447.7
32.5°	1435.1	1424.0	1408.2	1397.1	1392.3
35°	1376.5	1367.0	1346.5	1337.0	1329.1
37.5°	1318.0	1305.3	1284.8	1273.7	1268.9
40°	1256.3	1246.8	1224.6	1212.0	1205.6
42.5°	1194.6	1183.5	1161.3	1148.7	1142.4
45°	1128.1	1121.8	1101.2	1082.2	1074.3
47.5°	1063.2	1053.8	1034.8	1015.8	1009.5
50°	996.8	988.9	968.3	950.9	941.4
52.5°	927.2	922.4	900.3	886.0	876.5
55°	856.0	854.4	833.8	816.4	808.5
57.5°	789.5	783.2	767.4	751.6	742.1
60°	716.7	715.2	696.2	681.9	674.0
62.5°	651.9	647.1	628.1	613.9	609.2
65°	583.8	575.9	560.1	547.4	542.7
67.5°	511.1	504.7	492.1	481.0	474.7
70°	446.2	436.7	427.2	416.1	408.2
72.5°	378.1	371.8	360.7	351.3	348.1
75°	308.5	302.2	297.5	289.5	284.8
77.5°	246.8	243.7	237.3	231.0	231.0
80°	186.7	182.0	178.8	177.2	177.2
82.5°	128.2	128.2	128.2	125.0	123.4
85°	82.3	79.1	79.1	75.9	75.9
87.5°	41.1	36.4	34.8	33.2	33.2
90°	0.6	6.3	13.8	16.1	17.2
92.5°	17.2	20.7	24.1	25.8	24.7
95°	33.9	37.9	42.5	44.8	44.8
97.5°	55.7	58.5	62.0	64.9	64.3
100°	78.1	81.5	84.4	86.1	87.2
102.5°	103.9	105.6	109.6	111.3	110.8
105°	129.1	130.3	135.5	135.5	136.6
107.5°	159.0	159.6	161.9	163.6	163.0
110°	186.5	187.7	188.8	191.1	190.0

TEST NUMBER: P1011395

CATALOG NUMBER: S123DIP-B1165D585UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	215.2	215.8	215.8	218.7	218.7
115°	243.9	245.6	244.5	245.1	244.5
117.5°	273.2	273.8	272.6	272.6	270.9
120°	300.2	303.6	300.7	300.2	299.0
122.5°	328.3	330.6	329.4	327.7	326.0
125°	357.0	358.7	357.6	355.3	353.0
127.5°	383.4	386.8	385.7	382.2	380.0
130°	409.8	414.4	412.7	410.4	406.4
132.5°	436.2	440.8	439.6	436.8	433.9
135°	463.2	466.6	466.0	463.7	462.6
137.5°	487.9	490.7	492.4	489.6	487.9
140°	513.7	516.6	517.1	516.6	512.5
142.5°	537.2	540.1	541.2	540.7	537.8
145°	561.9	563.0	564.8	564.2	561.9
147.5°	583.1	585.4	587.1	587.1	583.7
150°	605.5	606.7	607.8	607.8	604.4
152.5°	623.9	625.6	626.2	627.3	624.5
155°	643.4	643.4	644.0	646.3	642.2
157.5°	660.0	659.5	660.0	662.3	658.9
160°	675.5	674.4	674.4	677.3	675.0
162.5°	689.3	687.6	688.2	691.0	687.0
165°	700.8	699.1	699.1	702.5	698.5
167.5°	710.5	708.3	708.8	712.3	708.8
170°	718.6	716.3	716.3	720.3	716.3
172.5°	724.9	722.6	722.6	726.0	722.0
175°	728.9	726.6	726.6	730.1	726.0
177.5°	731.2	728.9	728.9	732.4	728.3
180°	730.6	730.6	730.6	730.6	730.6

(END OF REPORT)