

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011135

Luminaire Tested: S123DIP-B1000D365UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011135
REPORT IS A COMBINATION OF REPORTS P989180 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D365UB35-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5444.1 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011135

CATALOG NUMBER: S123DIP-B1000D365UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011135

CATALOG NUMBER: S123DIP-B1000D365UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	98	98	98	88	88	88	80	80	80
1	103	99	95	91	98	94	91	87	86	83	80	78	75	73	70	69	67
2	94	86	80	74	89	82	77	72	75	70	66	68	65	61	62	59	56
3	86	76	68	62	81	73	66	60	66	61	56	60	56	52	55	51	48
4	79	67	59	53	75	64	57	51	59	53	48	54	49	44	49	45	41
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36
6	67	54	46	39	63	52	44	38	48	41	36	44	38	34	40	35	32
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	37	32	28
8	58	45	37	31	55	43	35	30	40	33	29	37	31	27	34	29	25
9	54	41	33	28	51	39	32	27	36	30	26	34	28	24	31	26	23
10	50	38	30	25	48	36	29	24	34	28	23	31	26	22	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17011	17011	17011
5°	17053	16424	16400
10°	16902	15868	15705
15°	16666	15289	14948
20°	16397	14649	14199
25°	16048	13971	13398
30°	15667	13270	12555
35°	15267	12554	11718
40°	14848	11803	10894
45°	14389	11071	10033
50°	13921	10253	9168
55°	13321	9403	8294
60°	12702	8465	7362
65°	12121	7450	6390
70°	11285	6325	5257
75°	10080	5009	4081
80°	8703	3521	2886
85°	6791	1891	1445

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14389 cd/sqm

TEST NUMBER: P1011135

CATALOG NUMBER: S123DIP-B1000D365UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.0	2.7
10°-20°	420.7	7.7
20°-30°	621.3	11.4
30°-40°	725.6	13.3
40°-50°	729.5	13.4
50°-60°	640.8	11.8
60°-70°	477.3	8.8
70°-80°	271.6	5.0
80°-90°	78.2	1.4
90°-100°	100.2	1.8
100°-110°	280.2	5.1
110°-120°	273.2	5.0
120°-130°	217.6	4.0
130°-140°	171.7	3.2
140°-150°	128.1	2.4
150°-160°	89.4	1.6
160°-170°	52.5	1.0
170°-180°	17.1	0.3
0°-30°	1191.0	21.9
0°-40°	1916.6	35.2
0°-60°	3286.9	60.4
0°-90°	4114.0	75.6
90°-120°	653.7	12.0
90°-150°	1171.1	21.5
90°-180°	1330.0	24.4
0°-180°	5444.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1580	1580	1580	1580	1580	
5°	1582	1575	1560	1574	1571	150
15°	1506	1500	1482	1493	1485	425
25°	1367	1359	1341	1343	1338	630
35°	1182	1174	1156	1148	1142	740
45°	969	963	946	930	923	748
55°	735	734	716	701	694	659
65°	501	495	481	470	466	495
75°	265	260	256	249	245	283
85°	71	68	68	65	65	76
90°	1	4	9	10	10	6
95°	12	39	212	62	41	13
105°	41	61	287	502	454	44
115°	73	91	220	482	552	72
125°	102	120	205	371	436	90
135°	119	142	202	306	353	92
145°	136	156	200	251	276	85
155°	155	167	193	220	229	71
165°	169	174	185	196	200	48
175°	176	176	178	180	180	17
180°	176	176	176	176	176	

TEST NUMBER: P1011135

CATALOG NUMBER: S123DIP-B1000D365UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1580.4	1580.4	1580.4	1580.4	1580.4
2.5°	1587.2	1581.7	1566.8	1580.4	1579.0
5°	1581.7	1574.9	1560.0	1573.6	1570.9
7.5°	1569.5	1562.7	1547.8	1560.0	1558.6
10°	1553.2	1546.4	1528.7	1541.0	1538.2
12.5°	1531.4	1526.0	1509.7	1517.9	1516.5
15°	1505.6	1500.2	1482.5	1493.4	1485.2
17.5°	1477.1	1470.3	1452.6	1460.8	1458.1
20°	1444.5	1436.3	1418.7	1424.1	1420.0
22.5°	1407.8	1399.6	1382.0	1386.1	1380.6
25°	1367.0	1358.9	1341.2	1342.6	1338.5
27.5°	1324.9	1316.7	1297.7	1299.1	1295.0
30°	1278.7	1271.9	1252.9	1252.9	1243.4
32.5°	1232.5	1223.0	1209.4	1199.9	1195.8
35°	1182.2	1174.1	1156.4	1148.2	1141.5
37.5°	1131.9	1121.1	1103.4	1093.9	1089.8
40°	1078.9	1070.8	1051.8	1040.9	1035.5
42.5°	1025.9	1016.4	997.4	986.5	981.1
45°	968.9	963.4	945.8	929.5	922.7
47.5°	913.2	905.0	888.7	872.4	867.0
50°	856.1	849.3	831.6	816.7	808.5
52.5°	796.3	792.2	773.2	761.0	752.8
55°	735.2	733.8	716.1	701.2	694.4
57.5°	678.1	672.6	659.1	645.5	637.3
60°	615.6	614.2	597.9	585.7	578.9
62.5°	559.9	555.8	539.5	527.2	523.2
65°	501.4	494.6	481.0	470.2	466.1
67.5°	438.9	433.5	422.6	413.1	407.7
70°	383.2	375.0	366.9	357.4	350.6
72.5°	324.8	319.3	309.8	301.7	299.0
75°	265.0	259.5	255.5	248.7	244.6
77.5°	212.0	209.3	203.8	198.4	198.4
80°	160.3	156.3	153.6	152.2	152.2
82.5°	110.1	110.1	110.1	107.4	106.0
85°	70.7	67.9	67.9	65.2	65.2
87.5°	35.3	31.3	29.9	28.5	28.5
90°	0.7	4.2	8.9	10.0	10.4
92.5°	5.4	21.4	66.4	22.6	18.9
95°	12.1	39.4	211.8	61.8	41.4
97.5°	19.3	45.2	325.7	155.4	85.0
100°	26.4	49.8	338.2	325.0	223.9
102.5°	33.9	55.2	315.0	435.2	354.6
105°	41.4	61.2	287.1	502.2	454.3
107.5°	49.3	68.4	262.5	531.6	519.3
110°	57.9	75.7	242.1	532.5	556.4



TEST NUMBER: P1011135

CATALOG NUMBER: S123DIP-B1000D365UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.7	83.4	228.6	512.2	563.9
115°	73.2	91.2	219.6	481.6	552.5
117.5°	80.7	98.8	213.6	448.7	527.5
120°	88.6	106.2	209.6	417.6	494.6
122.5°	95.4	113.4	207.1	393.2	463.9
125°	101.8	120.2	205.0	371.4	435.7
127.5°	106.8	126.6	203.9	353.6	411.4
130°	111.4	132.3	202.8	337.2	391.4
132.5°	115.0	137.4	202.5	321.8	371.8
135°	119.3	142.3	202.1	305.8	353.2
137.5°	123.2	146.2	201.4	290.9	333.5
140°	127.1	149.8	201.1	276.2	312.8
142.5°	131.4	153.0	200.3	262.8	293.6
145°	136.1	155.9	199.6	250.9	276.1
147.5°	140.7	158.9	198.6	241.6	261.1
150°	145.3	161.4	197.1	233.4	248.2
152.5°	150.0	164.1	195.3	226.2	237.5
155°	154.6	166.8	193.2	219.6	228.9
157.5°	158.2	169.1	191.4	213.2	220.7
160°	162.5	171.0	189.3	207.4	212.8
162.5°	165.7	172.5	187.1	201.8	205.7
165°	168.9	173.8	185.0	196.2	199.6
167.5°	171.4	174.8	182.8	191.4	193.6
170°	173.6	175.4	180.7	187.2	188.2
172.5°	175.0	175.9	178.9	183.4	183.2
175°	176.1	176.2	177.5	180.0	179.6
177.5°	176.8	176.4	176.4	177.8	177.1
180°	176.4	176.4	176.4	176.4	176.4

(END OF REPORT)