

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011138

Luminaire Tested: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011138
REPORT IS A COMBINATION OF REPORTS P989183 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D365UB40-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5505.0 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	80	80	80	76		
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	70	69	65		
2	95	88	81	76	90	84	78	73	76	72	68	70	66	63	63	61	58	55		
3	87	77	70	64	83	74	67	62	68	62	58	62	58	54	57	53	50	47		
4	80	69	61	55	76	66	59	53	61	54	50	55	51	47	51	47	43	41		
5	74	62	53	47	70	59	52	46	54	48	43	50	45	41	46	42	38	35		
6	68	56	47	41	65	53	46	40	49	43	38	45	40	36	42	37	34	31		
7	63	50	42	36	60	48	41	35	45	38	34	41	36	32	38	34	30	28		
8	59	46	38	32	56	44	37	32	41	35	30	38	32	28	35	30	27	25		
9	55	42	34	29	52	41	33	28	38	31	27	35	30	26	32	28	24	22		
10	51	39	31	26	49	37	30	26	35	29	24	32	27	23	30	25	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14944	14944	14944	14944
5°	14953	17217	14997	12850
10°	14858	20835	14872	11221
15°	14653	24709	14772	10100
20°	14476	28448	14507	9294
25°	14213	29165	14245	8874
30°	14026	24096	14026	8598
35°	13794	16115	13707	8355
40°	13515	11633	13348	7982
45°	13166	9215	12785	7518
50°	12316	7826	11879	7063
55°	11383	6877	10921	6555
60°	10437	5987	9882	6022
65°	9399	5127	8942	5311
70°	8319	4255	7766	4477
75°	7113	3210	6653	3457
80°	5624	2143	5185	2270
85°	3881	984	3103	895

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 24100 cd/sqm

TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.5	2.5
10°-20°	438.5	8.0
20°-30°	737.9	13.4
30°-40°	833.9	15.1
40°-50°	746.8	13.6
50°-60°	602.9	11.0
60°-70°	420.1	7.6
70°-80°	220.5	4.0
80°-90°	53.8	1.0
90°-100°	94.8	1.7
100°-110°	277.5	5.0
110°-120°	271.0	4.9
120°-130°	215.8	3.9
130°-140°	170.3	3.1
140°-150°	127.0	2.3
150°-160°	88.6	1.6
160°-170°	52.0	0.9
170°-180°	16.9	0.3
0°-30°	1312.9	23.8
0°-40°	2146.8	39.0
0°-60°	3496.5	63.5
0°-90°	4191.0	76.1
90°-120°	643.3	11.7
90°-150°	1156.5	21.0
90°-180°	1314.0	23.9
0°-180°	5505.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1388	1388	1388	1388	1388	
5°	1387	1649	1391	1231	1387	132
15°	1324	2455	1334	1004	1324	374
25°	1211	2914	1213	886	1211	559
35°	1068	1570	1061	814	1068	668
45°	886	848	861	691	886	678
55°	628	576	603	549	628	562
65°	389	374	370	387	389	387
75°	187	192	175	207	187	201
85°	40	44	32	40	40	46
90°	1	10	1	10	1	4
95°	12	41	12	41	12	13
105°	41	450	41	450	41	44
115°	72	547	72	547	72	72
125°	101	431	101	431	101	90
135°	118	350	118	350	118	91
145°	135	273	135	273	135	84
155°	153	227	153	227	153	70
165°	167	198	167	198	167	47
175°	174	178	174	178	174	17
180°	175	175	175	175	175	

TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1392.3	1403.1	1408.4	1416.5	1424.6	1436.7	1440.7	1447.5	1444.8	1450.1	1452.8
5°	1386.9	1405.8	1421.9	1442.1	1460.9	1474.4	1487.8	1509.3	1525.5	1528.2	1540.3
7.5°	1377.5	1404.4	1432.7	1460.9	1497.2	1518.7	1543.0	1572.6	1596.8	1635.8	1650.6
10°	1365.4	1403.1	1443.4	1482.4	1532.2	1565.8	1595.4	1645.2	1695.0	1735.3	1773.0
12.5°	1346.6	1393.6	1446.1	1504.0	1568.5	1607.5	1647.9	1713.8	1789.1	1851.0	1891.4
15°	1323.7	1382.9	1450.1	1512.0	1583.3	1656.0	1699.0	1773.0	1880.6	1938.5	2042.0
17.5°	1304.9	1365.4	1432.7	1529.5	1626.4	1699.0	1729.9	1865.8	1939.8	2036.7	2153.7
20°	1275.3	1351.9	1438.0	1534.9	1660.0	1704.4	1767.6	1904.8	1996.3	2122.8	2266.7
22.5°	1244.3	1326.4	1430.0	1530.9	1670.8	1717.8	1803.9	1912.9	2058.2	2183.3	2342.0
25°	1210.7	1299.5	1404.4	1524.1	1661.3	1729.9	1810.7	1945.2	2102.6	2260.0	2406.6
27.5°	1177.1	1273.9	1382.9	1502.6	1635.8	1716.5	1797.2	1937.1	2138.9	2309.7	2496.7
30°	1144.8	1241.6	1350.6	1473.0	1612.9	1690.9	1767.6	1942.5	2167.1	2359.5	2547.8
32.5°	1109.8	1209.3	1323.7	1425.9	1567.2	1650.6	1736.7	1942.5	2184.6	2389.1	2561.3
35°	1068.1	1170.3	1268.5	1370.8	1510.7	1603.5	1700.4	1929.0	2200.8	2398.5	2504.8
37.5°	1027.7	1117.9	1202.6	1302.2	1448.8	1548.3	1660.0	1912.9	2192.7	2358.2	2387.8
40°	982.0	1072.1	1140.7	1233.6	1388.3	1504.0	1616.9	1891.4	2157.7	2262.7	2176.6
42.5°	937.6	1008.9	1068.1	1158.2	1326.4	1439.4	1561.8	1852.4	2089.1	2110.6	1916.9
45°	886.5	937.6	990.1	1092.3	1259.1	1374.8	1510.7	1795.9	1978.8	1916.9	1672.1
47.5°	820.6	866.3	924.2	1018.3	1187.8	1307.5	1436.7	1723.2	1818.7	1689.6	1421.9
50°	757.4	796.4	850.2	941.7	1112.5	1229.5	1366.7	1608.9	1656.0	1452.8	1225.5
52.5°	694.1	723.7	776.2	867.7	1038.5	1151.5	1276.6	1491.8	1464.9	1247.0	1045.2
55°	628.2	653.8	703.5	793.7	952.4	1060.0	1179.8	1347.9	1278.0	1070.8	909.4
57.5°	563.6	590.5	641.7	717.0	866.3	971.2	1066.8	1198.6	1093.7	928.2	785.6
60°	505.8	528.7	567.7	641.7	777.5	862.3	949.7	1039.9	952.4	792.3	683.4
62.5°	445.3	466.8	503.1	570.4	687.4	762.7	832.7	906.7	809.8	692.8	595.9
65°	388.8	406.3	439.9	501.8	597.3	659.2	715.7	766.8	688.8	581.1	508.5
67.5°	337.6	352.4	380.7	435.8	516.6	561.0	606.7	649.7	583.8	497.7	435.8
70°	282.5	294.6	320.2	360.5	425.1	470.8	504.5	536.7	477.6	408.9	367.2
72.5°	234.1	246.2	262.3	304.0	348.4	376.7	413.0	430.5	396.8	340.3	298.6
75°	187.0	196.4	211.2	238.1	279.8	298.6	321.5	335.0	304.0	266.4	240.8
77.5°	146.6	150.7	161.4	180.3	208.5	230.0	247.5	255.6	234.1	209.9	188.3
80°	103.6	109.0	117.0	133.2	154.7	161.4	172.2	181.6	168.2	146.6	133.2
82.5°	68.6	75.3	79.4	86.1	99.5	107.6	110.3	118.4	106.3	98.2	92.8
85°	40.4	43.0	44.4	48.4	55.2	59.2	63.2	64.6	61.9	60.5	55.2
87.5°	20.2	20.2	20.2	22.9	24.2	26.9	28.2	28.2	28.2	26.9	25.6
90°	0.7	1.4	2.1	3.2	3.9	4.2	4.6	5.7	6.7	7.8	8.8
92.5°	5.3	7.8	11.3	14.5	18.0	21.2	24.4	35.7	54.5	72.8	65.8
95°	12.0	13.1	17.0	23.0	32.2	39.1	46.0	76.0	128.7	186.7	209.7
97.5°	19.1	19.4	22.6	27.9	37.1	44.7	52.3	82.0	143.2	240.8	322.5
100°	26.2	26.5	29.0	33.9	42.4	49.3	56.2	81.0	133.3	226.3	334.9
102.5°	33.6	34.3	36.4	41.0	48.4	54.6	60.8	82.4	124.8	205.1	311.9
105°	41.0	42.1	44.2	48.4	55.2	60.6	66.1	85.2	121.6	188.5	284.3
107.5°	48.8	49.9	52.0	56.2	62.6	67.7	72.8	89.8	120.9	176.5	259.9
110°	57.3	58.3	60.1	64.0	70.0	75.0	79.9	95.8	122.7	170.1	239.8

TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	65.1	66.1	67.9	71.8	77.8	82.6	87.3	101.8	126.2	166.6	226.3
115°	72.5	73.9	76.0	79.6	85.6	90.4	95.1	108.6	130.1	166.2	217.5
117.5°	79.9	81.7	83.5	86.6	93.4	97.8	102.2	115.6	135.1	166.6	211.5
120°	87.7	88.8	90.5	94.1	100.8	105.2	109.6	122.4	140.7	168.0	207.6
122.5°	94.4	95.5	97.2	101.1	107.5	112.2	117.0	129.4	146.0	170.4	205.1
125°	100.8	101.5	103.6	107.5	114.2	119.0	123.8	136.1	151.7	172.9	203.0
127.5°	105.7	106.8	109.3	113.2	120.6	125.4	130.1	142.2	156.3	175.8	201.9
130°	110.3	111.4	114.6	118.8	126.2	131.0	135.8	147.5	160.9	178.6	200.9
132.5°	113.9	115.3	118.8	124.1	131.5	136.1	140.7	152.1	165.1	180.7	200.5
135°	118.1	119.5	123.4	128.7	136.1	140.9	145.7	156.7	168.7	182.8	200.2
137.5°	122.0	123.4	127.3	133.0	140.4	144.8	149.2	159.8	171.5	184.2	199.4
140°	125.9	127.7	131.2	136.9	143.9	148.4	152.8	163.0	173.6	185.7	199.1
142.5°	130.1	131.5	135.4	140.4	147.5	151.6	155.6	165.5	175.8	186.7	198.4
145°	134.7	135.8	139.0	144.3	150.3	154.4	158.4	167.6	177.2	187.1	197.7
147.5°	139.3	140.0	143.2	147.8	153.8	157.4	160.9	169.4	178.2	187.1	196.6
150°	143.9	144.3	147.1	151.7	156.7	159.8	163.0	171.2	178.6	187.1	195.2
152.5°	148.5	148.5	151.4	155.2	159.5	162.5	165.5	172.2	179.3	186.0	193.4
155°	153.1	153.1	155.2	158.8	162.7	165.1	167.6	173.6	179.3	185.3	191.3
157.5°	156.7	157.0	158.8	162.0	165.5	167.4	169.4	174.3	179.6	184.2	189.5
160°	160.9	160.9	162.3	165.1	167.6	169.4	171.2	175.4	179.6	183.5	187.4
162.5°	164.1	164.1	165.1	167.3	169.4	170.8	172.2	175.8	179.3	182.1	185.3
165°	167.3	166.9	167.6	169.4	170.8	172.0	173.3	176.1	178.6	180.7	183.2
167.5°	169.7	169.4	169.7	171.2	172.2	173.1	174.0	176.1	178.2	179.3	181.1
170°	171.9	171.2	171.5	172.6	173.3	173.6	174.0	175.8	177.2	177.9	178.9
172.5°	173.3	172.9	172.9	173.6	174.0	174.2	174.3	175.8	176.8	176.8	177.2
175°	174.3	174.0	173.6	174.3	174.3	174.5	174.7	175.4	176.1	175.8	175.8
177.5°	175.0	174.7	174.3	174.7	174.7	174.7	174.7	175.0	175.8	175.0	174.7
180°	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7

TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1462.2	1464.9	1474.4	1481.1	1494.5	1493.2	1493.2	1491.8	1487.8	1494.5	1498.6
5°	1564.5	1587.4	1590.0	1619.6	1621.0	1633.1	1641.2	1634.4	1650.6	1649.2	1637.1
7.5°	1690.9	1721.9	1736.7	1764.9	1797.2	1789.1	1820.1	1825.5	1822.8	1836.2	1845.6
10°	1829.5	1883.3	1921.0	1973.4	1986.9	1995.0	2015.1	2032.6	2067.6	2040.7	2058.2
12.5°	1988.2	2027.2	2077.0	2160.4	2202.1	2229.0	2238.4	2250.5	2274.8	2260.0	2261.3
15°	2121.4	2173.9	2258.6	2362.2	2374.3	2407.9	2399.9	2472.5	2507.5	2455.0	2484.6
17.5°	2260.0	2329.9	2430.8	2520.9	2572.1	2594.9	2616.4	2686.4	2683.7	2675.6	2682.4
20°	2348.7	2463.1	2588.2	2707.9	2722.7	2740.2	2798.0	2827.6	2822.3	2845.1	2859.9
22.5°	2473.9	2594.9	2728.1	2807.5	2841.1	2861.3	2907.0	2925.8	2933.9	2939.3	2929.9
25°	2578.8	2707.9	2806.1	2876.1	2896.2	2907.0	2921.8	2927.2	2923.2	2913.7	2921.8
27.5°	2650.1	2753.7	2820.9	2853.2	2842.4	2825.0	2796.7	2777.9	2736.2	2716.0	2740.2
30°	2679.7	2725.4	2745.6	2691.8	2638.0	2594.9	2541.1	2441.6	2363.5	2386.4	2355.5
32.5°	2632.6	2603.0	2506.1	2367.6	2325.9	2255.9	2103.9	1986.9	1990.9	1929.0	1954.6
35°	2494.0	2359.5	2176.6	1966.7	1911.6	1873.9	1707.1	1681.5	1627.7	1569.9	1586.0
37.5°	2249.2	2052.8	1830.8	1676.1	1594.1	1512.0	1417.9	1361.4	1329.1	1304.9	1323.7
40°	1950.6	1711.1	1528.2	1389.6	1319.7	1267.2	1202.6	1146.1	1109.8	1105.8	1112.5
42.5°	1657.3	1455.5	1287.4	1155.5	1132.7	1070.8	1029.1	984.7	973.9	956.4	965.9
45°	1403.1	1238.9	1100.4	992.8	965.9	949.7	898.6	870.4	858.2	847.5	863.6
47.5°	1218.8	1046.6	945.7	881.1	854.2	827.3	799.1	780.2	770.8	772.2	770.8
50°	1041.2	914.7	826.0	776.2	760.0	741.2	718.3	706.2	702.2	690.1	699.5
52.5°	895.9	804.4	742.6	695.5	683.4	669.9	651.1	644.4	634.9	632.3	632.3
55°	778.9	707.6	657.8	626.9	612.1	601.3	590.5	582.5	575.8	575.8	575.8
57.5°	687.4	625.5	589.2	562.3	556.9	546.2	534.1	534.1	524.6	523.3	527.3
60°	609.4	554.2	526.0	503.1	495.0	492.3	480.2	480.2	477.6	470.8	476.2
62.5°	530.0	489.7	465.4	448.0	439.9	439.9	430.5	423.7	423.7	425.1	422.4
65°	457.4	427.8	406.3	392.8	388.8	383.4	382.0	376.7	372.6	374.0	372.6
67.5°	392.8	369.9	355.1	344.4	337.6	335.0	330.9	330.9	328.2	329.6	322.9
70°	335.0	312.1	300.0	289.2	286.5	286.5	281.2	282.5	279.8	283.8	281.2
72.5°	275.8	258.3	248.9	244.8	242.1	240.8	238.1	235.4	234.1	236.8	235.4
75°	223.3	208.5	201.8	199.1	196.4	196.4	195.1	193.7	192.4	192.4	192.4
77.5°	173.5	164.1	156.0	158.7	154.7	156.0	152.0	152.0	153.4	152.0	152.0
80°	127.8	121.1	121.1	118.4	113.0	115.7	115.7	111.7	110.3	113.0	109.0
82.5°	84.7	83.4	80.7	79.4	76.7	78.0	76.7	75.3	74.0	76.7	74.0
85°	49.8	49.8	48.4	45.7	48.4	47.1	45.7	45.7	44.4	44.4	44.4
87.5°	25.6	22.9	22.9	21.5	22.9	20.2	21.5	20.2	18.8	20.2	18.8
90°	8.5	8.8	9.2	9.5	9.9	10.3	9.9	10.3	10.6	10.3	10.6
92.5°	49.2	35.0	27.2	23.7	22.4	21.2	20.5	19.1	19.4	18.7	19.4
95°	170.1	127.3	86.3	67.5	61.2	54.8	48.1	44.9	42.4	41.0	42.4
97.5°	333.5	292.4	220.7	174.0	153.8	133.7	110.0	96.5	88.1	84.2	88.1
100°	404.5	416.9	388.3	346.9	321.8	296.7	261.0	235.2	221.4	221.7	221.4
102.5°	408.1	458.3	464.3	444.5	430.9	417.3	391.5	372.4	361.4	351.1	361.4
105°	385.8	459.7	495.1	501.8	497.2	492.6	476.3	462.9	451.6	449.8	451.6
107.5°	354.0	438.5	494.0	521.6	526.4	531.1	529.0	522.7	518.1	514.2	518.1
110°	324.3	405.3	470.3	514.9	527.2	539.6	549.5	552.4	551.7	550.9	551.7

TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	298.5	372.4	439.2	490.5	507.3	524.1	544.2	554.5	558.0	558.4	558.0
115°	278.7	344.1	405.6	457.6	476.8	496.1	522.7	538.2	545.3	547.1	545.3
117.5°	265.6	322.2	376.6	424.3	444.3	464.3	491.9	509.2	519.8	522.3	519.8
120°	255.7	305.5	353.3	395.7	413.6	431.4	459.4	479.2	487.6	489.8	487.6
122.5°	247.5	292.4	334.5	373.1	389.4	405.6	429.7	447.0	456.5	459.4	456.5
125°	240.8	281.1	319.7	353.6	367.8	381.9	404.5	420.1	428.9	431.4	428.9
127.5°	234.5	270.9	305.9	337.0	350.1	363.2	383.7	397.1	405.3	407.4	405.3
130°	229.5	261.3	293.2	321.8	333.8	345.8	364.6	377.3	384.7	387.6	384.7
132.5°	224.9	252.5	281.1	307.3	318.6	329.9	347.3	360.0	366.4	368.1	366.4
135°	221.0	244.7	269.8	292.8	302.9	313.0	330.3	340.9	347.3	349.7	347.3
137.5°	217.5	237.3	258.5	279.0	288.0	297.0	311.9	322.9	328.2	330.3	328.2
140°	214.3	230.9	249.0	265.9	273.5	281.1	294.6	304.5	310.1	309.8	310.1
142.5°	211.5	224.9	239.8	253.9	260.2	266.6	277.6	286.1	291.0	290.7	291.0
145°	209.0	220.3	232.0	243.3	248.4	253.5	262.4	269.8	272.6	273.4	272.6
147.5°	206.5	216.4	226.0	235.5	239.2	242.9	250.0	255.3	258.1	258.5	258.1
150°	204.0	212.2	220.3	227.7	231.1	234.5	239.8	243.6	245.8	245.8	245.8
152.5°	201.2	208.3	215.0	221.4	224.0	226.7	230.6	234.1	235.2	235.2	235.2
155°	198.4	204.4	210.1	215.4	217.5	219.6	222.8	225.6	226.3	226.7	226.3
157.5°	195.2	200.2	205.1	209.3	211.1	212.9	215.7	217.8	218.5	218.5	218.5
160°	192.0	196.6	200.5	204.0	205.2	206.5	209.0	211.1	211.1	210.8	211.1
162.5°	188.8	192.4	195.6	198.7	199.8	200.9	202.3	204.0	204.0	203.7	204.0
165°	186.0	188.8	191.0	193.4	194.3	195.2	196.6	198.0	197.7	197.7	197.7
167.5°	183.2	185.7	187.4	188.8	189.5	190.2	191.0	192.0	191.7	191.7	191.7
170°	180.7	182.5	183.5	184.9	185.3	185.7	186.0	186.7	186.4	186.4	186.4
172.5°	178.2	179.6	180.3	181.4	181.6	181.8	181.8	182.5	181.8	181.4	181.8
175°	176.5	177.2	177.5	178.2	178.2	178.2	178.2	178.6	178.2	177.9	178.2
177.5°	175.0	175.4	175.8	176.1	176.1	176.1	175.8	176.1	175.4	175.4	175.4
180°	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7

TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1487.8	1491.8	1481.1	1478.4	1478.4	1483.8	1479.7	1443.4	1450.1	1442.1	1439.4
5°	1651.9	1643.9	1633.1	1627.7	1621.0	1602.2	1600.8	1559.1	1551.0	1524.1	1512.0
7.5°	1832.2	1825.5	1793.2	1789.1	1786.4	1769.0	1724.6	1680.2	1647.9	1616.9	1587.4
10°	2038.0	2017.8	2003.0	1973.4	1958.6	1934.4	1876.6	1834.9	1779.7	1732.6	1670.8
12.5°	2285.5	2262.7	2212.9	2191.4	2172.5	2105.3	2047.4	2000.3	1892.7	1860.4	1783.8
15°	2467.1	2418.7	2413.3	2366.2	2363.5	2289.6	2179.2	2128.1	2044.7	1926.3	1847.0
17.5°	2663.5	2620.5	2586.9	2530.4	2522.3	2452.3	2371.6	2246.5	2155.0	2042.0	1941.1
20°	2807.5	2784.6	2726.8	2703.9	2656.8	2597.6	2514.2	2359.5	2247.9	2134.9	2011.1
22.5°	2921.8	2898.9	2853.2	2822.3	2795.4	2718.7	2619.1	2487.3	2333.9	2186.0	2058.2
25°	2920.5	2913.7	2894.9	2880.1	2859.9	2803.4	2720.0	2593.6	2422.7	2260.0	2082.4
27.5°	2755.0	2773.8	2806.1	2822.3	2818.2	2810.2	2763.1	2656.8	2503.4	2309.7	2110.6
30°	2410.6	2479.2	2539.8	2620.5	2644.7	2703.9	2730.8	2670.3	2547.8	2367.6	2147.0
32.5°	1999.0	2098.5	2230.4	2274.8	2351.4	2465.8	2593.6	2616.4	2539.8	2401.2	2169.8
35°	1639.8	1721.9	1824.1	1894.1	1962.7	2148.3	2309.7	2449.6	2475.2	2383.7	2164.5
37.5°	1357.3	1415.2	1505.3	1564.5	1627.7	1786.4	2012.4	2194.0	2321.8	2324.5	2149.7
40°	1152.9	1178.4	1256.4	1299.5	1360.0	1497.2	1699.0	1935.8	2122.8	2208.8	2110.6
42.5°	976.6	1010.3	1074.8	1107.1	1146.1	1265.8	1399.0	1623.7	1855.1	2039.3	2038.0
45°	871.7	895.9	925.5	952.4	996.8	1068.1	1220.1	1388.3	1610.2	1818.7	1900.8
47.5°	778.9	801.7	831.3	839.4	869.0	936.3	1029.1	1175.7	1382.9	1590.0	1744.7
50°	700.9	719.7	739.9	754.7	768.1	823.3	893.2	1017.0	1182.4	1382.9	1575.2
52.5°	640.3	653.8	671.3	679.3	691.4	731.8	785.6	877.1	1012.9	1195.9	1382.9
55°	583.8	593.2	604.0	617.5	622.8	652.4	694.1	772.2	873.0	1037.2	1214.7
57.5°	531.4	535.4	542.1	550.2	556.9	582.5	618.8	671.3	760.0	886.5	1054.6
60°	472.2	482.9	487.0	495.0	499.1	519.3	547.5	591.9	660.5	769.5	895.9
62.5°	422.4	429.1	435.8	439.9	449.3	456.0	478.9	519.3	575.8	656.5	770.8
65°	378.0	380.7	384.7	388.8	391.5	399.5	421.1	448.0	491.0	562.3	651.1
67.5°	326.9	329.6	335.0	336.3	339.0	349.8	361.9	384.7	421.1	474.9	547.5
70°	277.1	281.2	283.8	286.5	290.6	294.6	308.1	326.9	355.1	392.8	449.3
72.5°	234.1	238.1	238.1	240.8	239.4	244.8	258.3	271.7	290.6	321.5	371.3
75°	191.0	191.0	193.7	195.1	196.4	201.8	207.2	217.9	232.7	256.9	287.9
77.5°	150.7	149.3	152.0	152.0	152.0	156.0	161.4	166.8	176.2	193.7	217.9
80°	110.3	110.3	113.0	114.3	111.7	113.0	115.7	121.1	127.8	139.9	153.4
82.5°	72.6	78.0	76.7	78.0	76.7	79.4	80.7	82.1	84.7	90.1	99.5
85°	44.4	44.4	44.4	45.7	44.4	45.7	45.7	45.7	47.1	49.8	53.8
87.5°	18.8	18.8	18.8	20.2	18.8	18.8	20.2	18.8	20.2	20.2	21.5
90°	10.3	9.9	10.3	9.9	9.5	9.2	8.8	8.5	8.8	7.8	6.7
92.5°	19.1	20.5	21.2	22.4	23.7	27.2	35.0	49.2	65.8	72.8	54.5
95°	44.9	48.1	54.8	61.2	67.5	86.3	127.3	170.1	209.7	186.7	128.7
97.5°	96.5	110.0	133.7	153.8	174.0	220.7	292.4	333.5	322.5	240.8	143.2
100°	235.2	261.0	296.7	321.8	346.9	388.3	416.9	404.5	334.9	226.3	133.3
102.5°	372.4	391.5	417.3	430.9	444.5	464.3	458.3	408.1	311.9	205.1	124.8
105°	462.9	476.3	492.6	497.2	501.8	495.1	459.7	385.8	284.3	188.5	121.6
107.5°	522.7	529.0	531.1	526.4	521.6	494.0	438.5	354.0	259.9	176.5	120.9
110°	552.4	549.5	539.6	527.2	514.9	470.3	405.3	324.3	239.8	170.1	122.7

TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	554.5	544.2	524.1	507.3	490.5	439.2	372.4	298.5	226.3	166.6	126.2
115°	538.2	522.7	496.1	476.8	457.6	405.6	344.1	278.7	217.5	166.2	130.1
117.5°	509.2	491.9	464.3	444.3	424.3	376.6	322.2	265.6	211.5	166.6	135.1
120°	479.2	459.4	431.4	413.6	395.7	353.3	305.5	255.7	207.6	168.0	140.7
122.5°	447.0	429.7	405.6	389.4	373.1	334.5	292.4	247.5	205.1	170.4	146.0
125°	420.1	404.5	381.9	367.8	353.6	319.7	281.1	240.8	203.0	172.9	151.7
127.5°	397.1	383.7	363.2	350.1	337.0	305.9	270.9	234.5	201.9	175.8	156.3
130°	377.3	364.6	345.8	333.8	321.8	293.2	261.3	229.5	200.9	178.6	160.9
132.5°	360.0	347.3	329.9	318.6	307.3	281.1	252.5	224.9	200.5	180.7	165.1
135°	340.9	330.3	313.0	302.9	292.8	269.8	244.7	221.0	200.2	182.8	168.7
137.5°	322.9	311.9	297.0	288.0	279.0	258.5	237.3	217.5	199.4	184.2	171.5
140°	304.5	294.6	281.1	273.5	265.9	249.0	230.9	214.3	199.1	185.7	173.6
142.5°	286.1	277.6	266.6	260.2	253.9	239.8	224.9	211.5	198.4	186.7	175.8
145°	269.8	262.4	253.5	248.4	243.3	232.0	220.3	209.0	197.7	187.1	177.2
147.5°	255.3	250.0	242.9	239.2	235.5	226.0	216.4	206.5	196.6	187.1	178.2
150°	243.6	239.8	234.5	231.1	227.7	220.3	212.2	204.0	195.2	187.1	178.6
152.5°	234.1	230.6	226.7	224.0	221.4	215.0	208.3	201.2	193.4	186.0	179.3
155°	225.6	222.8	219.6	217.5	215.4	210.1	204.4	198.4	191.3	185.3	179.3
157.5°	217.8	215.7	212.9	211.1	209.3	205.1	200.2	195.2	189.5	184.2	179.6
160°	211.1	209.0	206.5	205.2	204.0	200.5	196.6	192.0	187.4	183.5	179.6
162.5°	204.0	202.3	200.9	199.8	198.7	195.6	192.4	188.8	185.3	182.1	179.3
165°	198.0	196.6	195.2	194.3	193.4	191.0	188.8	186.0	183.2	180.7	178.6
167.5°	192.0	191.0	190.2	189.5	188.8	187.4	185.7	183.2	181.1	179.3	178.2
170°	186.7	186.0	185.7	185.3	184.9	183.5	182.5	180.7	178.9	177.9	177.2
172.5°	182.5	181.8	181.8	181.6	181.4	180.3	179.6	178.2	177.2	176.8	176.8
175°	178.6	178.2	178.2	178.2	178.2	177.5	177.2	176.5	175.8	175.8	176.1
177.5°	176.1	175.8	176.1	176.1	176.1	175.8	175.4	175.0	174.7	175.0	175.8
180°	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7

TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1425.9	1421.9	1421.9	1419.2	1411.1	1396.3	1395.0	1397.7	1389.6	1381.5	1369.4
5°	1495.9	1470.3	1462.2	1454.2	1438.0	1411.1	1400.4	1391.0	1376.2	1358.7	1339.8
7.5°	1555.1	1518.7	1508.0	1493.2	1460.9	1423.2	1399.0	1378.8	1358.7	1334.5	1311.6
10°	1629.1	1576.6	1551.0	1529.5	1485.1	1432.7	1396.3	1366.7	1334.5	1304.9	1275.3
12.5°	1712.5	1627.7	1619.6	1567.2	1516.1	1438.0	1393.6	1350.6	1307.5	1271.2	1240.3
15°	1782.4	1689.6	1656.0	1621.0	1522.8	1425.9	1382.9	1334.5	1284.7	1245.7	1199.9
17.5°	1826.8	1750.1	1678.8	1631.7	1529.5	1443.4	1360.0	1304.9	1252.4	1198.6	1160.9
20°	1880.6	1769.0	1707.1	1643.9	1543.0	1430.0	1346.6	1278.0	1213.4	1165.0	1119.2
22.5°	1934.4	1783.8	1732.6	1664.0	1545.7	1416.5	1322.3	1253.7	1179.8	1131.3	1081.6
25°	1929.0	1805.3	1720.5	1662.7	1518.7	1404.4	1294.1	1213.4	1144.8	1082.9	1033.1
27.5°	1933.1	1781.1	1695.0	1627.7	1499.9	1386.9	1264.5	1179.8	1108.5	1043.9	991.4
30°	1934.4	1744.7	1669.4	1588.7	1464.9	1345.2	1230.9	1144.8	1069.4	999.5	952.4
32.5°	1930.4	1715.2	1621.0	1548.3	1409.8	1304.9	1191.9	1100.4	1023.7	959.1	914.7
35°	1921.0	1680.2	1571.2	1479.7	1353.3	1247.0	1155.5	1061.4	979.3	920.1	869.0
37.5°	1895.4	1642.5	1518.7	1428.6	1287.4	1179.8	1099.0	1021.0	941.7	871.7	828.7
40°	1876.6	1591.4	1466.3	1368.1	1216.1	1111.1	1043.9	969.9	891.9	828.7	787.0
42.5°	1833.5	1543.0	1412.5	1295.4	1146.1	1038.5	975.3	916.1	848.8	787.0	749.3
45°	1763.6	1490.5	1346.6	1228.2	1069.4	967.2	909.4	860.9	801.7	742.6	704.9
47.5°	1665.4	1415.2	1276.6	1158.2	994.1	890.5	832.7	796.4	749.3	699.5	667.2
50°	1559.1	1333.1	1205.3	1088.3	921.5	820.6	764.1	730.5	699.5	653.8	622.8
52.5°	1420.5	1245.7	1123.3	1011.6	843.5	746.6	696.8	672.6	640.3	608.0	581.1
55°	1286.0	1132.7	1031.8	925.5	766.8	676.6	628.2	602.7	583.8	556.9	535.4
57.5°	1130.0	1027.7	934.9	838.1	695.5	613.4	567.7	536.7	524.6	512.5	492.3
60°	986.0	908.0	832.7	752.0	621.5	547.5	503.1	478.9	466.8	458.7	445.3
62.5°	854.2	793.7	729.1	664.5	546.2	478.9	445.3	421.1	410.3	408.9	396.8
65°	727.8	684.7	632.3	569.0	476.2	417.0	384.7	369.9	357.8	357.8	348.4
67.5°	601.3	571.7	530.0	485.6	413.0	357.8	328.2	314.8	308.1	308.1	301.3
70°	500.4	480.2	442.6	403.6	340.3	298.6	275.8	263.7	259.6	261.0	255.6
72.5°	406.3	384.7	353.8	325.5	278.5	247.5	231.4	217.9	211.2	212.5	211.2
75°	314.8	304.0	277.1	255.6	217.9	196.4	181.6	174.9	169.5	170.8	168.2
77.5°	236.8	220.6	205.8	191.0	168.2	150.7	138.6	131.8	127.8	127.8	127.8
80°	161.4	158.7	146.6	138.6	119.7	106.3	96.9	95.5	91.5	91.5	91.5
82.5°	104.9	98.2	91.5	86.1	75.3	67.3	63.2	60.5	59.2	57.8	60.5
85°	57.8	53.8	51.1	45.7	41.7	37.7	33.6	32.3	30.9	32.3	30.9
87.5°	22.9	18.8	18.8	17.5	16.1	14.8	14.8	12.1	12.1	10.8	10.8
90°	5.7	4.6	4.2	3.9	3.2	2.1	1.4	0.7	1.4	2.1	3.2
92.5°	35.7	24.4	21.2	18.0	14.5	11.3	7.8	5.3	7.8	11.3	14.5
95°	76.0	46.0	39.1	32.2	23.0	17.0	13.1	12.0	13.1	17.0	23.0
97.5°	82.0	52.3	44.7	37.1	27.9	22.6	19.4	19.1	19.4	22.6	27.9
100°	81.0	56.2	49.3	42.4	33.9	29.0	26.5	26.2	26.5	29.0	33.9
102.5°	82.4	60.8	54.6	48.4	41.0	36.4	34.3	33.6	34.3	36.4	41.0
105°	85.2	66.1	60.6	55.2	48.4	44.2	42.1	41.0	42.1	44.2	48.4
107.5°	89.8	72.8	67.7	62.6	56.2	52.0	49.9	48.8	49.9	52.0	56.2
110°	95.8	79.9	75.0	70.0	64.0	60.1	58.3	57.3	58.3	60.1	64.0

TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	101.8	87.3	82.6	77.8	71.8	67.9	66.1	65.1	66.1	67.9	71.8
115°	108.6	95.1	90.4	85.6	79.6	76.0	73.9	72.5	73.9	76.0	79.6
117.5°	115.6	102.2	97.8	93.4	86.6	83.5	81.7	79.9	81.7	83.5	86.6
120°	122.4	109.6	105.2	100.8	94.1	90.5	88.8	87.7	88.8	90.5	94.1
122.5°	129.4	117.0	112.2	107.5	101.1	97.2	95.5	94.4	95.5	97.2	101.1
125°	136.1	123.8	119.0	114.2	107.5	103.6	101.5	100.8	101.5	103.6	107.5
127.5°	142.2	130.1	125.4	120.6	113.2	109.3	106.8	105.7	106.8	109.3	113.2
130°	147.5	135.8	131.0	126.2	118.8	114.6	111.4	110.3	111.4	114.6	118.8
132.5°	152.1	140.7	136.1	131.5	124.1	118.8	115.3	113.9	115.3	118.8	124.1
135°	156.7	145.7	140.9	136.1	128.7	123.4	119.5	118.1	119.5	123.4	128.7
137.5°	159.8	149.2	144.8	140.4	133.0	127.3	123.4	122.0	123.4	127.3	133.0
140°	163.0	152.8	148.4	143.9	136.9	131.2	127.7	125.9	127.7	131.2	136.9
142.5°	165.5	155.6	151.6	147.5	140.4	135.4	131.5	130.1	131.5	135.4	140.4
145°	167.6	158.4	154.4	150.3	144.3	139.0	135.8	134.7	135.8	139.0	144.3
147.5°	169.4	160.9	157.4	153.8	147.8	143.2	140.0	139.3	140.0	143.2	147.8
150°	171.2	163.0	159.8	156.7	151.7	147.1	144.3	143.9	144.3	147.1	151.7
152.5°	172.2	165.5	162.5	159.5	155.2	151.4	148.5	148.5	148.5	151.4	155.2
155°	173.6	167.6	165.1	162.7	158.8	155.2	153.1	153.1	153.1	155.2	158.8
157.5°	174.3	169.4	167.4	165.5	162.0	158.8	157.0	156.7	157.0	158.8	162.0
160°	175.4	171.2	169.4	167.6	165.1	162.3	160.9	160.9	160.9	162.3	165.1
162.5°	175.8	172.2	170.8	169.4	167.3	165.1	164.1	164.1	164.1	165.1	167.3
165°	176.1	173.3	172.0	170.8	169.4	167.6	166.9	167.3	166.9	167.6	169.4
167.5°	176.1	174.0	173.1	172.2	171.2	169.7	169.4	169.7	169.4	169.7	171.2
170°	175.8	174.0	173.6	173.3	172.6	171.5	171.2	171.9	171.2	171.5	172.6
172.5°	175.8	174.3	174.2	174.0	173.6	172.9	172.9	173.3	172.9	172.9	173.6
175°	175.4	174.7	174.5	174.3	174.3	173.6	174.0	174.3	174.0	173.6	174.3
177.5°	175.0	174.7	174.7	174.7	174.7	174.3	174.7	175.0	174.7	174.3	174.7
180°	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7

TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1366.7	1365.4	1368.1	1360.0	1346.6	1339.8	1321.0	1317.0	1315.6	1317.0	1318.3
5°	1329.1	1327.7	1323.7	1310.2	1294.1	1282.0	1259.1	1257.8	1249.7	1241.6	1245.7
7.5°	1292.8	1287.4	1279.3	1261.8	1240.3	1226.8	1208.0	1194.6	1183.8	1177.1	1171.7
10°	1256.4	1248.4	1240.3	1217.4	1190.5	1170.3	1147.5	1136.7	1124.6	1119.2	1113.8
12.5°	1209.3	1201.3	1186.5	1159.6	1143.4	1117.9	1095.0	1084.2	1077.5	1066.8	1060.0
15°	1171.7	1155.5	1147.5	1119.2	1085.6	1082.9	1041.2	1038.5	1025.1	1025.1	1014.3
17.5°	1128.6	1116.5	1101.7	1073.5	1049.3	1025.1	1003.5	995.5	983.4	980.7	975.3
20°	1086.9	1070.8	1065.4	1037.2	1011.6	982.0	959.1	951.1	945.7	940.3	944.3
22.5°	1043.9	1030.4	1017.0	991.4	972.6	943.0	929.5	921.5	913.4	910.7	912.1
25°	1002.2	990.1	976.6	951.1	930.9	906.7	894.6	890.5	886.5	886.5	885.2
27.5°	961.8	949.7	937.6	914.7	894.6	877.1	867.7	863.6	859.6	862.3	865.0
30°	920.1	909.4	898.6	878.4	862.3	846.1	840.8	838.1	836.7	843.5	843.5
32.5°	882.5	873.0	865.0	846.1	830.0	816.5	812.5	813.9	815.2	819.2	821.9
35°	843.5	836.7	828.7	812.5	799.1	787.0	788.3	788.3	791.0	797.7	803.1
37.5°	808.5	799.1	792.3	778.9	768.1	757.4	761.4	765.4	768.1	776.2	778.9
40°	766.8	762.7	757.4	743.9	734.5	733.1	734.5	737.2	742.6	746.6	750.6
42.5°	733.1	727.8	721.0	710.3	702.2	703.5	704.9	707.6	710.3	717.0	721.0
45°	695.5	691.4	686.1	676.6	669.9	671.3	672.6	672.6	675.3	683.4	686.1
47.5°	653.8	655.1	648.4	639.0	634.9	634.9	634.9	637.6	644.4	647.0	648.4
50°	613.4	610.7	609.4	600.0	597.3	595.9	597.3	598.6	608.0	606.7	610.7
52.5°	570.4	570.4	569.0	563.6	559.6	559.6	556.9	563.6	566.3	569.0	573.1
55°	528.7	524.6	523.3	520.6	515.2	513.9	516.6	524.6	527.3	530.0	534.1
57.5°	482.9	482.9	480.2	476.2	476.2	476.2	476.2	481.6	485.6	488.3	496.4
60°	441.2	435.8	431.8	431.8	431.8	430.5	438.5	438.5	446.6	448.0	450.6
62.5°	391.5	388.8	386.1	387.4	386.1	388.8	391.5	396.8	398.2	402.2	406.3
65°	344.4	344.4	341.7	349.8	344.4	344.4	351.1	351.1	353.8	357.8	363.2
67.5°	298.6	300.0	297.3	297.3	300.0	301.3	302.7	308.1	309.4	314.8	321.5
70°	251.6	254.2	255.6	252.9	255.6	258.3	261.0	262.3	267.7	270.4	274.4
72.5°	209.9	212.5	208.5	209.9	211.2	213.9	215.2	217.9	220.6	228.7	231.4
75°	168.2	166.8	165.5	170.8	168.2	173.5	174.9	174.9	177.6	184.3	187.0
77.5°	129.1	129.1	130.5	127.8	131.8	130.5	131.8	135.9	139.9	139.9	150.7
80°	90.1	92.8	92.8	92.8	94.2	95.5	92.8	99.5	100.9	100.9	104.9
82.5°	57.8	59.2	57.8	60.5	60.5	63.2	61.9	63.2	65.9	68.6	70.0
85°	30.9	30.9	33.6	33.6	32.3	33.6	32.3	33.6	36.3	36.3	37.7
87.5°	10.8	10.8	10.8	10.8	12.1	10.8	12.1	12.1	10.8	10.8	14.8
90°	3.9	4.2	4.6	5.7	6.7	7.8	8.8	8.5	8.8	9.2	9.5
92.5°	18.0	21.2	24.4	35.7	54.5	72.8	65.8	49.2	35.0	27.2	23.7
95°	32.2	39.1	46.0	76.0	128.7	186.7	209.7	170.1	127.3	86.3	67.5
97.5°	37.1	44.7	52.3	82.0	143.2	240.8	322.5	333.5	292.4	220.7	174.0
100°	42.4	49.3	56.2	81.0	133.3	226.3	334.9	404.5	416.9	388.3	346.9
102.5°	48.4	54.6	60.8	82.4	124.8	205.1	311.9	408.1	458.3	464.3	444.5
105°	55.2	60.6	66.1	85.2	121.6	188.5	284.3	385.8	459.7	495.1	501.8
107.5°	62.6	67.7	72.8	89.8	120.9	176.5	259.9	354.0	438.5	494.0	521.6
110°	70.0	75.0	79.9	95.8	122.7	170.1	239.8	324.3	405.3	470.3	514.9

TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	77.8	82.6	87.3	101.8	126.2	166.6	226.3	298.5	372.4	439.2	490.5
115°	85.6	90.4	95.1	108.6	130.1	166.2	217.5	278.7	344.1	405.6	457.6
117.5°	93.4	97.8	102.2	115.6	135.1	166.6	211.5	265.6	322.2	376.6	424.3
120°	100.8	105.2	109.6	122.4	140.7	168.0	207.6	255.7	305.5	353.3	395.7
122.5°	107.5	112.2	117.0	129.4	146.0	170.4	205.1	247.5	292.4	334.5	373.1
125°	114.2	119.0	123.8	136.1	151.7	172.9	203.0	240.8	281.1	319.7	353.6
127.5°	120.6	125.4	130.1	142.2	156.3	175.8	201.9	234.5	270.9	305.9	337.0
130°	126.2	131.0	135.8	147.5	160.9	178.6	200.9	229.5	261.3	293.2	321.8
132.5°	131.5	136.1	140.7	152.1	165.1	180.7	200.5	224.9	252.5	281.1	307.3
135°	136.1	140.9	145.7	156.7	168.7	182.8	200.2	221.0	244.7	269.8	292.8
137.5°	140.4	144.8	149.2	159.8	171.5	184.2	199.4	217.5	237.3	258.5	279.0
140°	143.9	148.4	152.8	163.0	173.6	185.7	199.1	214.3	230.9	249.0	265.9
142.5°	147.5	151.6	155.6	165.5	175.8	186.7	198.4	211.5	224.9	239.8	253.9
145°	150.3	154.4	158.4	167.6	177.2	187.1	197.7	209.0	220.3	232.0	243.3
147.5°	153.8	157.4	160.9	169.4	178.2	187.1	196.6	206.5	216.4	226.0	235.5
150°	156.7	159.8	163.0	171.2	178.6	187.1	195.2	204.0	212.2	220.3	227.7
152.5°	159.5	162.5	165.5	172.2	179.3	186.0	193.4	201.2	208.3	215.0	221.4
155°	162.7	165.1	167.6	173.6	179.3	185.3	191.3	198.4	204.4	210.1	215.4
157.5°	165.5	167.4	169.4	174.3	179.6	184.2	189.5	195.2	200.2	205.1	209.3
160°	167.6	169.4	171.2	175.4	179.6	183.5	187.4	192.0	196.6	200.5	204.0
162.5°	169.4	170.8	172.2	175.8	179.3	182.1	185.3	188.8	192.4	195.6	198.7
165°	170.8	172.0	173.3	176.1	178.6	180.7	183.2	186.0	188.8	191.0	193.4
167.5°	172.2	173.1	174.0	176.1	178.2	179.3	181.1	183.2	185.7	187.4	188.8
170°	173.3	173.6	174.0	175.8	177.2	177.9	178.9	180.7	182.5	183.5	184.9
172.5°	174.0	174.2	174.3	175.8	176.8	176.8	177.2	178.2	179.6	180.3	181.4
175°	174.3	174.5	174.7	175.4	176.1	175.8	175.8	176.5	177.2	177.5	178.2
177.5°	174.7	174.7	174.7	175.0	175.8	175.0	174.7	175.0	175.4	175.8	176.1
180°	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7

TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1317.0	1318.3	1312.9	1308.9	1319.7	1312.9	1312.9	1314.3	1311.6	1315.6	1314.3
5°	1243.0	1244.3	1234.9	1237.6	1232.2	1230.9	1229.5	1237.6	1236.3	1234.9	1237.6
7.5°	1170.3	1170.3	1166.3	1163.6	1163.6	1159.6	1165.0	1163.6	1166.3	1166.3	1170.3
10°	1109.8	1112.5	1105.8	1099.0	1097.7	1099.0	1099.0	1100.4	1101.7	1111.1	1109.8
12.5°	1060.0	1056.0	1054.6	1050.6	1043.9	1041.2	1038.5	1053.3	1049.3	1049.3	1049.3
15°	1004.9	1014.3	1012.9	1000.8	998.2	1003.5	1000.8	1000.8	1014.3	1012.9	1011.6
17.5°	975.3	972.6	969.9	963.2	964.5	963.2	964.5	964.5	972.6	972.6	972.6
20°	941.7	936.3	936.3	933.6	933.6	929.5	934.9	936.3	941.7	941.7	943.0
22.5°	912.1	908.0	908.0	906.7	909.4	904.0	909.4	910.7	910.7	914.7	914.7
25°	886.5	883.8	883.8	886.5	886.5	886.5	886.5	891.9	887.8	889.2	887.8
27.5°	863.6	865.0	866.3	867.7	866.3	867.7	869.0	871.7	873.0	871.7	869.0
30°	842.1	846.1	847.5	847.5	850.2	851.5	852.9	852.9	854.2	850.2	852.9
32.5°	826.0	826.0	828.7	830.0	832.7	834.0	834.0	836.7	835.4	831.3	832.7
35°	803.1	803.1	808.5	811.2	815.2	813.9	815.2	815.2	816.5	813.9	809.8
37.5°	780.2	782.9	782.9	788.3	789.6	791.0	789.6	792.3	791.0	788.3	787.0
40°	753.3	752.0	753.3	757.4	758.7	758.7	758.7	761.4	761.4	761.4	760.0
42.5°	719.7	723.7	722.4	726.4	725.1	725.1	727.8	730.5	731.8	727.8	729.1
45°	687.4	687.4	690.1	690.1	691.4	691.4	696.8	694.1	696.8	694.1	695.5
47.5°	652.4	653.8	653.8	655.1	657.8	660.5	657.8	659.2	659.2	660.5	657.8
50°	613.4	613.4	616.1	620.1	625.5	622.8	621.5	626.9	622.8	622.8	620.1
52.5°	573.1	577.1	578.4	582.5	586.5	587.9	589.2	586.5	587.9	583.8	585.2
55°	534.1	535.4	540.8	544.8	548.8	548.8	547.5	548.8	550.2	544.8	544.8
57.5°	495.0	499.1	504.5	504.5	509.8	509.8	508.5	508.5	509.8	505.8	504.5
60°	453.3	457.4	464.1	464.1	472.2	473.5	470.8	468.1	468.1	464.1	465.4
62.5°	408.9	413.0	417.0	423.7	429.1	426.4	431.8	426.4	427.8	419.7	419.7
65°	369.9	371.3	378.0	384.7	384.7	387.4	384.7	386.1	382.0	382.0	376.7
67.5°	324.2	324.2	330.9	337.6	344.4	344.4	344.4	340.3	340.3	336.3	336.3
70°	283.8	282.5	289.2	293.3	297.3	298.6	295.9	294.6	291.9	287.9	286.5
72.5°	234.1	236.8	243.5	246.2	252.9	251.6	258.3	250.2	250.2	243.5	242.1
75°	189.7	192.4	199.1	203.1	207.2	207.2	211.2	207.2	201.8	199.1	197.7
77.5°	150.7	149.3	154.7	161.4	162.8	161.4	164.1	162.8	157.4	157.4	154.7
80°	107.6	111.7	117.0	115.7	121.1	119.7	119.7	117.0	117.0	113.0	115.7
82.5°	71.3	75.3	76.7	75.3	76.7	79.4	80.7	79.4	79.4	76.7	78.0
85°	37.7	37.7	40.4	41.7	40.4	40.4	41.7	45.7	43.0	40.4	43.0
87.5°	12.1	10.8	10.8	12.1	10.8	10.8	12.1	12.1	13.5	13.5	13.5
90°	9.9	10.3	9.9	10.3	10.6	10.3	10.6	10.3	9.9	10.3	9.9
92.5°	22.4	21.2	20.5	19.1	19.4	18.7	19.4	19.1	20.5	21.2	22.4
95°	61.2	54.8	48.1	44.9	42.4	41.0	42.4	44.9	48.1	54.8	61.2
97.5°	153.8	133.7	110.0	96.5	88.1	84.2	88.1	96.5	110.0	133.7	153.8
100°	321.8	296.7	261.0	235.2	221.4	221.7	221.4	235.2	261.0	296.7	321.8
102.5°	430.9	417.3	391.5	372.4	361.4	351.1	361.4	372.4	391.5	417.3	430.9
105°	497.2	492.6	476.3	462.9	451.6	449.8	451.6	462.9	476.3	492.6	497.2
107.5°	526.4	531.1	529.0	522.7	518.1	514.2	518.1	522.7	529.0	531.1	526.4
110°	527.2	539.6	549.5	552.4	551.7	550.9	551.7	552.4	549.5	539.6	527.2

TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	507.3	524.1	544.2	554.5	558.0	558.4	558.0	554.5	544.2	524.1	507.3
115°	476.8	496.1	522.7	538.2	545.3	547.1	545.3	538.2	522.7	496.1	476.8
117.5°	444.3	464.3	491.9	509.2	519.8	522.3	519.8	509.2	491.9	464.3	444.3
120°	413.6	431.4	459.4	479.2	487.6	489.8	487.6	479.2	459.4	431.4	413.6
122.5°	389.4	405.6	429.7	447.0	456.5	459.4	456.5	447.0	429.7	405.6	389.4
125°	367.8	381.9	404.5	420.1	428.9	431.4	428.9	420.1	404.5	381.9	367.8
127.5°	350.1	363.2	383.7	397.1	405.3	407.4	405.3	397.1	383.7	363.2	350.1
130°	333.8	345.8	364.6	377.3	384.7	387.6	384.7	377.3	364.6	345.8	333.8
132.5°	318.6	329.9	347.3	360.0	366.4	368.1	366.4	360.0	347.3	329.9	318.6
135°	302.9	313.0	330.3	340.9	347.3	349.7	347.3	340.9	330.3	313.0	302.9
137.5°	288.0	297.0	311.9	322.9	328.2	330.3	328.2	322.9	311.9	297.0	288.0
140°	273.5	281.1	294.6	304.5	310.1	309.8	310.1	304.5	294.6	281.1	273.5
142.5°	260.2	266.6	277.6	286.1	291.0	290.7	291.0	286.1	277.6	266.6	260.2
145°	248.4	253.5	262.4	269.8	272.6	273.4	272.6	269.8	262.4	253.5	248.4
147.5°	239.2	242.9	250.0	255.3	258.1	258.5	258.1	255.3	250.0	242.9	239.2
150°	231.1	234.5	239.8	243.6	245.8	245.8	245.8	243.6	239.8	234.5	231.1
152.5°	224.0	226.7	230.6	234.1	235.2	235.2	235.2	234.1	230.6	226.7	224.0
155°	217.5	219.6	222.8	225.6	226.3	226.7	226.3	225.6	222.8	219.6	217.5
157.5°	211.1	212.9	215.7	217.8	218.5	218.5	218.5	217.8	215.7	212.9	211.1
160°	205.2	206.5	209.0	211.1	211.1	210.8	211.1	211.1	209.0	206.5	205.2
162.5°	199.8	200.9	202.3	204.0	204.0	203.7	204.0	204.0	202.3	200.9	199.8
165°	194.3	195.2	196.6	198.0	197.7	197.7	197.7	198.0	196.6	195.2	194.3
167.5°	189.5	190.2	191.0	192.0	191.7	191.7	191.7	192.0	191.0	190.2	189.5
170°	185.3	185.7	186.0	186.7	186.4	186.4	186.4	186.7	186.0	185.7	185.3
172.5°	181.6	181.8	181.8	182.5	181.8	181.4	181.8	182.5	181.8	181.8	181.6
175°	178.2	178.2	178.2	178.6	178.2	177.9	178.2	178.6	178.2	178.2	178.2
177.5°	176.1	176.1	175.8	176.1	175.4	175.4	175.4	176.1	175.8	176.1	176.1
180°	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7

TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1318.3	1321.0	1322.3	1317.0	1312.9	1319.7	1329.1	1335.8	1341.2	1347.9	1351.9
5°	1240.3	1249.7	1249.7	1252.4	1256.4	1263.2	1280.6	1292.8	1303.5	1311.6	1318.3
7.5°	1174.4	1181.1	1185.1	1191.9	1198.6	1208.0	1228.2	1245.7	1261.8	1271.2	1282.0
10°	1115.2	1120.6	1127.3	1131.3	1143.4	1156.9	1182.4	1197.2	1216.1	1230.9	1244.3
12.5°	1058.7	1077.5	1081.6	1080.2	1091.0	1105.8	1131.3	1154.2	1174.4	1189.2	1204.0
15°	1018.3	1025.1	1033.1	1031.8	1054.6	1058.7	1080.2	1107.1	1134.0	1143.4	1156.9
17.5°	973.9	984.7	992.8	996.8	1003.5	1018.3	1038.5	1058.7	1093.7	1095.0	1130.0
20°	939.0	949.7	955.1	960.5	964.5	982.0	999.5	1022.4	1050.6	1065.4	1084.2
22.5°	916.1	921.5	925.5	929.5	934.9	944.3	965.9	991.4	1010.3	1026.4	1038.5
25°	889.2	894.6	899.9	902.6	906.7	912.1	928.2	948.4	975.3	986.0	998.2
27.5°	870.4	870.4	873.0	873.0	878.4	883.8	895.9	914.7	936.3	949.7	965.9
30°	850.2	848.8	850.2	848.8	847.5	855.6	866.3	882.5	897.3	913.4	924.2
32.5°	830.0	828.7	828.7	830.0	824.6	828.7	834.0	848.8	865.0	873.0	885.2
35°	808.5	805.8	805.8	805.8	803.1	800.4	805.8	819.2	830.0	840.8	850.2
37.5°	787.0	782.9	782.9	780.2	777.5	773.5	773.5	784.3	799.1	803.1	815.2
40°	757.4	757.4	754.7	753.3	750.6	747.9	743.9	753.3	766.8	770.8	780.2
42.5°	727.8	723.7	722.4	722.4	722.4	718.3	715.7	722.4	730.5	737.2	742.6
45°	694.1	691.4	692.8	691.4	688.8	687.4	686.1	688.8	698.2	700.9	707.6
47.5°	657.8	656.5	656.5	655.1	653.8	655.1	649.7	656.5	659.2	661.8	667.2
50°	620.1	618.8	617.5	616.1	616.1	617.5	616.1	616.1	621.5	624.2	629.6
52.5°	582.5	578.4	578.4	577.1	577.1	574.4	577.1	578.4	581.1	583.8	586.5
55°	542.1	542.1	538.1	538.1	535.4	535.4	536.7	535.4	540.8	543.5	543.5
57.5°	503.1	497.7	499.1	496.4	493.7	492.3	492.3	495.0	497.7	497.7	500.4
60°	461.4	456.0	454.7	449.3	452.0	448.0	449.3	449.3	454.7	452.0	454.7
62.5°	419.7	413.0	408.9	406.3	406.3	407.6	404.9	403.6	406.3	408.9	414.3
65°	375.3	371.3	367.2	363.2	363.2	361.9	364.6	360.5	359.2	360.5	363.2
67.5°	329.6	325.5	321.5	317.5	318.8	314.8	312.1	316.1	313.4	314.8	317.5
70°	285.2	282.5	274.4	271.7	270.4	271.7	270.4	267.7	271.7	270.4	271.7
72.5°	240.8	238.1	234.1	227.3	227.3	226.0	224.7	224.7	223.3	223.3	223.3
75°	197.7	192.4	188.3	187.0	184.3	182.9	181.6	178.9	180.3	181.6	178.9
77.5°	153.4	146.6	145.3	145.3	141.2	141.2	142.6	141.2	139.9	139.9	139.9
80°	113.0	107.6	107.6	104.9	102.2	102.2	102.2	102.2	100.9	99.5	100.9
82.5°	72.6	71.3	70.0	70.0	72.6	67.3	70.0	68.6	67.3	67.3	65.9
85°	40.4	41.7	40.4	41.7	39.0	40.4	40.4	40.4	39.0	40.4	37.7
87.5°	14.8	14.8	14.8	16.1	16.1	16.1	16.1	16.1	17.5	16.1	16.1
90°	9.5	9.2	8.8	8.5	8.8	7.8	6.7	5.7	4.6	4.2	3.9
92.5°	23.7	27.2	35.0	49.2	65.8	72.8	54.5	35.7	24.4	21.2	18.0
95°	67.5	86.3	127.3	170.1	209.7	186.7	128.7	76.0	46.0	39.1	32.2
97.5°	174.0	220.7	292.4	333.5	322.5	240.8	143.2	82.0	52.3	44.7	37.1
100°	346.9	388.3	416.9	404.5	334.9	226.3	133.3	81.0	56.2	49.3	42.4
102.5°	444.5	464.3	458.3	408.1	311.9	205.1	124.8	82.4	60.8	54.6	48.4
105°	501.8	495.1	459.7	385.8	284.3	188.5	121.6	85.2	66.1	60.6	55.2
107.5°	521.6	494.0	438.5	354.0	259.9	176.5	120.9	89.8	72.8	67.7	62.6
110°	514.9	470.3	405.3	324.3	239.8	170.1	122.7	95.8	79.9	75.0	70.0

TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	490.5	439.2	372.4	298.5	226.3	166.6	126.2	101.8	87.3	82.6	77.8
115°	457.6	405.6	344.1	278.7	217.5	166.2	130.1	108.6	95.1	90.4	85.6
117.5°	424.3	376.6	322.2	265.6	211.5	166.6	135.1	115.6	102.2	97.8	93.4
120°	395.7	353.3	305.5	255.7	207.6	168.0	140.7	122.4	109.6	105.2	100.8
122.5°	373.1	334.5	292.4	247.5	205.1	170.4	146.0	129.4	117.0	112.2	107.5
125°	353.6	319.7	281.1	240.8	203.0	172.9	151.7	136.1	123.8	119.0	114.2
127.5°	337.0	305.9	270.9	234.5	201.9	175.8	156.3	142.2	130.1	125.4	120.6
130°	321.8	293.2	261.3	229.5	200.9	178.6	160.9	147.5	135.8	131.0	126.2
132.5°	307.3	281.1	252.5	224.9	200.5	180.7	165.1	152.1	140.7	136.1	131.5
135°	292.8	269.8	244.7	221.0	200.2	182.8	168.7	156.7	145.7	140.9	136.1
137.5°	279.0	258.5	237.3	217.5	199.4	184.2	171.5	159.8	149.2	144.8	140.4
140°	265.9	249.0	230.9	214.3	199.1	185.7	173.6	163.0	152.8	148.4	143.9
142.5°	253.9	239.8	224.9	211.5	198.4	186.7	175.8	165.5	155.6	151.6	147.5
145°	243.3	232.0	220.3	209.0	197.7	187.1	177.2	167.6	158.4	154.4	150.3
147.5°	235.5	226.0	216.4	206.5	196.6	187.1	178.2	169.4	160.9	157.4	153.8
150°	227.7	220.3	212.2	204.0	195.2	187.1	178.6	171.2	163.0	159.8	156.7
152.5°	221.4	215.0	208.3	201.2	193.4	186.0	179.3	172.2	165.5	162.5	159.5
155°	215.4	210.1	204.4	198.4	191.3	185.3	179.3	173.6	167.6	165.1	162.7
157.5°	209.3	205.1	200.2	195.2	189.5	184.2	179.6	174.3	169.4	167.4	165.5
160°	204.0	200.5	196.6	192.0	187.4	183.5	179.6	175.4	171.2	169.4	167.6
162.5°	198.7	195.6	192.4	188.8	185.3	182.1	179.3	175.8	172.2	170.8	169.4
165°	193.4	191.0	188.8	186.0	183.2	180.7	178.6	176.1	173.3	172.0	170.8
167.5°	188.8	187.4	185.7	183.2	181.1	179.3	178.2	176.1	174.0	173.1	172.2
170°	184.9	183.5	182.5	180.7	178.9	177.9	177.2	175.8	174.0	173.6	173.3
172.5°	181.4	180.3	179.6	178.2	177.2	176.8	176.8	175.8	174.3	174.2	174.0
175°	178.2	177.5	177.2	176.5	175.8	175.8	176.1	175.4	174.7	174.5	174.3
177.5°	176.1	175.8	175.4	175.0	174.7	175.0	175.8	175.0	174.7	174.7	174.7
180°	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7

TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1388.3	1388.3	1388.3	1388.3
2.5°	1358.7	1362.7	1376.2	1392.3
5°	1331.8	1342.5	1361.4	1386.9
7.5°	1302.2	1318.3	1345.2	1377.5
10°	1268.5	1291.4	1325.0	1365.4
12.5°	1232.2	1261.8	1304.9	1346.6
15°	1209.3	1238.9	1278.0	1323.7
17.5°	1165.0	1199.9	1240.3	1304.9
20°	1119.2	1158.2	1210.7	1275.3
22.5°	1084.2	1125.9	1175.7	1244.3
25°	1042.5	1085.6	1139.4	1210.7
27.5°	998.2	1041.2	1101.7	1177.1
30°	964.5	1006.2	1064.1	1144.8
32.5°	924.2	964.5	1025.1	1109.8
35°	878.4	924.2	982.0	1068.1
37.5°	843.5	885.2	945.7	1027.7
40°	805.8	842.1	901.3	982.0
42.5°	765.4	805.8	856.9	937.6
45°	727.8	757.4	809.8	886.5
47.5°	687.4	721.0	761.4	820.6
50°	644.4	672.6	717.0	757.4
52.5°	602.7	625.5	663.2	694.1
55°	558.3	581.1	609.4	628.2
57.5°	516.6	532.7	551.5	563.6
60°	465.4	481.6	493.7	505.8
62.5°	419.7	431.8	438.5	445.3
65°	372.6	379.4	383.4	388.8
67.5°	321.5	328.2	329.6	337.6
70°	274.4	275.8	278.5	282.5
72.5°	230.0	232.7	231.4	234.1
75°	184.3	187.0	184.3	187.0
77.5°	139.9	142.6	142.6	146.6
80°	100.9	102.2	103.6	103.6
82.5°	65.9	70.0	67.3	68.6
85°	37.7	39.0	39.0	40.4
87.5°	17.5	18.8	17.5	20.2
90°	3.2	2.1	1.4	0.7
92.5°	14.5	11.3	7.8	5.3
95°	23.0	17.0	13.1	12.0
97.5°	27.9	22.6	19.4	19.1
100°	33.9	29.0	26.5	26.2
102.5°	41.0	36.4	34.3	33.6
105°	48.4	44.2	42.1	41.0
107.5°	56.2	52.0	49.9	48.8
110°	64.0	60.1	58.3	57.3

TEST NUMBER: P1011138

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	71.8	67.9	66.1	65.1
115°	79.6	76.0	73.9	72.5
117.5°	86.6	83.5	81.7	79.9
120°	94.1	90.5	88.8	87.7
122.5°	101.1	97.2	95.5	94.4
125°	107.5	103.6	101.5	100.8
127.5°	113.2	109.3	106.8	105.7
130°	118.8	114.6	111.4	110.3
132.5°	124.1	118.8	115.3	113.9
135°	128.7	123.4	119.5	118.1
137.5°	133.0	127.3	123.4	122.0
140°	136.9	131.2	127.7	125.9
142.5°	140.4	135.4	131.5	130.1
145°	144.3	139.0	135.8	134.7
147.5°	147.8	143.2	140.0	139.3
150°	151.7	147.1	144.3	143.9
152.5°	155.2	151.4	148.5	148.5
155°	158.8	155.2	153.1	153.1
157.5°	162.0	158.8	157.0	156.7
160°	165.1	162.3	160.9	160.9
162.5°	167.3	165.1	164.1	164.1
165°	169.4	167.6	166.9	167.3
167.5°	171.2	169.7	169.4	169.7
170°	172.6	171.5	171.2	171.9
172.5°	173.6	172.9	172.9	173.3
175°	174.3	173.6	174.0	174.3
177.5°	174.7	174.3	174.7	175.0
180°	174.7	174.7	174.7	174.7

(END OF REPORT)