

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011142

Luminaire Tested: S123DIP-B1000D365UB40-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011142
REPORT IS A COMBINATION OF REPORTS P989187 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D365UB40-4F0-XX-W2A-F
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5523.0 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011142

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1011142

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78
1	103	99	94	91	98	94	90	87	85	82	79	76	74	72	69	67	66
2	94	86	80	74	89	82	76	71	74	70	66	67	64	60	61	58	55
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	54	50	47
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	41
5	72	60	51	45	68	57	49	44	52	46	41	48	42	38	43	39	35
6	66	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28
8	57	44	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16841	16841	16841
5°	16884	16260	16236
10°	16733	15710	15549
15°	16500	15138	14799
20°	16234	14502	14058
25°	15889	13832	13264
30°	15511	13138	12430
35°	15115	12429	11601
40°	14701	11685	10784
45°	14245	10959	9933
50°	13783	10151	9078
55°	13187	9310	8211
60°	12575	8380	7288
65°	12000	7375	6326
70°	11173	6261	5204
75°	9978	4958	4041
80°	8616	3484	2858
85°	6724	1874	1432

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14245 cd/sqm

TEST NUMBER: P1011142

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.5	2.7
10°-20°	416.5	7.5
20°-30°	615.1	11.1
30°-40°	718.4	13.0
40°-50°	722.2	13.1
50°-60°	634.4	11.5
60°-70°	472.5	8.6
70°-80°	268.9	4.9
80°-90°	77.4	1.4
90°-100°	16.8	0.3
100°-110°	81.1	1.5
110°-120°	198.7	3.6
120°-130°	252.3	4.6
130°-140°	269.5	4.9
140°-150°	252.0	4.6
150°-160°	203.3	3.7
160°-170°	131.2	2.4
170°-180°	45.2	0.8
0°-30°	1179.1	21.3
0°-40°	1897.5	34.4
0°-60°	3254.2	58.9
0°-90°	4073.0	73.7
90°-120°	296.6	5.4
90°-150°	1070.4	19.4
90°-180°	1450.0	26.3
0°-180°	5523.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1565	1565	1565	1565	1565	
5°	1566	1559	1544	1558	1555	149
15°	1491	1485	1468	1478	1470	420
25°	1353	1345	1328	1329	1325	623
35°	1170	1162	1145	1137	1130	732
45°	959	954	936	920	914	741
55°	728	726	709	694	688	652
65°	496	490	476	466	461	490
75°	262	257	253	246	242	280
85°	70	67	67	65	65	75
90°	0	4	8	10	11	6
95°	22	7	11	13	13	26
105°	105	109	77	15	16	112
115°	198	200	203	206	208	195
125°	278	281	283	283	284	249
135°	347	349	350	351	350	267
145°	400	402	403	404	404	250
155°	441	440	440	442	440	203
165°	465	464	463	466	464	131
175°	476	474	474	477	474	45
180°	476	476	476	476	476	

TEST NUMBER: P1011142

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1564.6	1564.6	1564.6	1564.6	1564.6
2.5°	1571.3	1566.0	1551.2	1564.6	1563.3
5°	1566.0	1559.2	1544.4	1557.9	1555.2
7.5°	1553.9	1547.1	1532.3	1544.4	1543.1
10°	1537.7	1531.0	1513.5	1525.6	1522.9
12.5°	1516.2	1510.8	1494.7	1502.7	1501.4
15°	1490.6	1485.2	1467.8	1478.5	1470.4
17.5°	1462.4	1455.6	1438.2	1446.2	1443.5
20°	1430.1	1422.0	1404.5	1409.9	1405.9
22.5°	1393.8	1385.7	1368.2	1372.2	1366.9
25°	1353.4	1345.3	1327.8	1329.2	1325.1
27.5°	1311.7	1303.6	1284.8	1286.1	1282.1
30°	1266.0	1259.2	1240.4	1240.4	1231.0
32.5°	1220.2	1210.8	1197.3	1187.9	1183.9
35°	1170.4	1162.4	1144.9	1136.8	1130.1
37.5°	1120.7	1109.9	1092.4	1083.0	1079.0
40°	1068.2	1060.1	1041.3	1030.5	1025.1
42.5°	1015.7	1006.3	987.5	976.7	971.3
45°	959.2	953.8	936.3	920.2	913.5
47.5°	904.1	896.0	879.8	863.7	858.3
50°	847.6	840.8	823.3	808.5	800.5
52.5°	788.4	784.3	765.5	753.4	745.3
55°	727.8	726.5	709.0	694.2	687.5
57.5°	671.3	665.9	652.5	639.0	631.0
60°	609.4	608.1	591.9	579.8	573.1
62.5°	554.3	550.2	534.1	522.0	518.0
65°	496.4	489.7	476.2	465.5	461.4
67.5°	434.5	429.2	418.4	409.0	403.6
70°	379.4	371.3	363.2	353.8	347.1
72.5°	321.5	316.2	306.7	298.7	296.0
75°	262.3	257.0	252.9	246.2	242.2
77.5°	209.9	207.2	201.8	196.4	196.4
80°	158.7	154.7	152.0	150.7	150.7
82.5°	109.0	109.0	109.0	106.3	104.9
85°	70.0	67.3	67.3	64.6	64.6
87.5°	35.0	30.9	29.6	28.3	28.3
90°	0.4	3.9	8.5	9.9	10.6
92.5°	8.1	6.0	9.2	11.7	12.0
95°	21.6	7.1	11.0	13.4	13.4
97.5°	39.2	29.3	11.3	14.1	14.5
100°	59.7	66.8	11.7	14.5	14.8
102.5°	83.0	87.6	26.1	14.5	15.2
105°	105.3	109.2	77.4	14.8	15.5
107.5°	129.0	132.2	137.5	83.0	36.8
110°	152.7	155.5	159.4	147.7	97.2

TEST NUMBER: P1011142

CATALOG NUMBER: S123DIP-B1000D365UB40-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.3	177.7	181.6	184.8	184.1
115°	197.5	199.7	202.8	206.4	207.8
117.5°	219.4	221.9	223.7	226.5	226.9
120°	239.6	242.8	243.8	246.7	246.7
122.5°	260.1	262.6	264.0	265.7	266.1
125°	278.5	281.3	282.7	283.4	284.1
127.5°	296.8	299.7	301.4	302.5	301.8
130°	313.8	316.6	318.0	319.5	318.7
132.5°	330.1	332.9	333.9	335.4	334.3
135°	346.7	348.8	350.2	351.3	350.2
137.5°	360.8	363.6	364.3	366.1	365.4
140°	374.9	377.1	378.1	379.5	378.8
142.5°	388.0	390.1	391.2	392.2	391.2
145°	400.0	402.5	403.2	403.9	403.9
147.5°	411.7	413.5	414.2	414.9	413.1
150°	422.3	423.3	424.1	424.8	423.7
152.5°	431.8	432.2	432.5	433.9	432.2
155°	440.7	440.0	440.3	442.1	440.0
157.5°	447.7	447.7	447.4	449.5	446.7
160°	454.1	453.7	453.4	455.5	453.0
162.5°	460.1	459.0	458.7	461.2	459.0
165°	464.7	463.6	463.3	466.1	463.6
167.5°	468.6	467.2	467.2	470.0	467.2
170°	471.8	470.3	470.3	473.2	470.3
172.5°	473.9	472.1	472.5	475.3	472.1
175°	475.6	473.9	474.2	476.7	473.9
177.5°	476.4	474.6	474.9	477.8	474.2
180°	475.6	475.6	475.6	475.6	475.6

(END OF REPORT)