

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011440

Luminaire Tested: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011440
REPORT IS A COMBINATION OF REPORTS P989602 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D805UB40-4F0-XX-W2A-A1
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7559.0 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	70	70	70	65		
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	61	59	55		
2	93	85	79	74	87	80	75	70	71	67	63	63	60	57	55	53	51	47		
3	85	75	68	62	79	71	64	59	63	58	54	56	52	48	49	46	43	40		
4	78	67	59	53	73	63	56	51	56	51	46	50	45	42	44	41	38	34		
5	71	60	52	45	67	57	49	44	51	45	40	45	40	36	40	36	33	30		
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	27		
7	61	49	41	35	57	46	39	34	42	35	31	37	32	28	33	29	26	24		
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21		
9	53	40	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21	19		
10	49	37	30	25	47	35	29	24	32	26	22	29	24	21	26	22	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17400	17400	17400	17400
5°	17412	20048	17463	14963
10°	17301	24262	17319	13067
15°	17062	28772	17201	11762
20°	16857	33127	16892	10823
25°	16551	33962	16587	10333
30°	16332	28058	16332	10011
35°	16061	18765	15961	9728
40°	15738	13546	15543	9295
45°	15331	10730	14888	8754
50°	14341	9113	13832	8225
55°	13254	8007	12716	7633
60°	12154	6972	11506	7012
65°	10943	5970	10414	6184
70°	9686	4955	9041	5213
75°	8281	3737	7745	4024
80°	6547	2496	6037	2644
85°	4515	1146	3612	1042

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 28063 cd/sqm

TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.0	2.1
10°-20°	510.6	6.8
20°-30°	859.2	11.4
30°-40°	971.0	12.8
40°-50°	869.7	11.5
50°-60°	702.0	9.3
60°-70°	489.2	6.5
70°-80°	256.8	3.4
80°-90°	63.6	0.8
90°-100°	62.2	0.8
100°-110°	188.3	2.5
110°-120°	320.6	4.2
120°-130°	421.7	5.6
130°-140°	474.0	6.3
140°-150°	466.0	6.2
150°-160°	392.4	5.2
160°-170°	261.2	3.5
170°-180°	91.5	1.2
0°-30°	1528.8	20.2
0°-40°	2499.8	33.1
0°-60°	4071.5	53.9
0°-90°	4881.0	64.6
90°-120°	571.1	7.6
90°-150°	1932.9	25.6
90°-180°	2678.0	35.4
0°-180°	7559.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1616	1616	1616	1616	1616	
5°	1615	1920	1620	1433	1615	153
15°	1541	2859	1554	1169	1541	436
25°	1410	3393	1413	1032	1410	650
35°	1244	1828	1236	948	1244	778
45°	1032	987	1002	805	1032	790
55°	732	670	702	639	732	655
65°	453	436	431	451	453	451
75°	218	224	204	241	218	233
85°	47	52	38	47	47	54
90°	1	23	1	23	1	7
95°	45	59	45	59	45	49
105°	171	181	171	181	171	183
115°	323	323	323	323	323	319
125°	472	467	472	467	472	421
135°	613	612	613	612	613	472
145°	743	743	743	743	743	464
155°	851	850	851	850	851	392
165°	927	924	927	924	927	261
175°	964	960	964	960	964	92
180°	966	966	966	966	966	

TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1621.2	1633.8	1640.0	1649.4	1658.8	1672.9	1677.6	1685.5	1682.3	1688.6	1691.7
5°	1615.0	1636.9	1655.7	1679.2	1701.1	1716.8	1732.5	1757.5	1776.3	1779.5	1793.6
7.5°	1604.0	1635.3	1668.2	1701.1	1743.4	1768.5	1796.7	1831.1	1859.3	1904.8	1922.0
10°	1589.9	1633.8	1680.8	1726.2	1784.2	1823.3	1857.8	1915.7	1973.7	2020.7	2064.5
12.5°	1568.0	1622.8	1683.9	1751.3	1826.4	1871.9	1918.9	1995.6	2083.3	2155.4	2202.4
15°	1541.4	1610.3	1688.6	1760.7	1843.7	1928.3	1978.4	2064.5	2189.9	2257.2	2377.8
17.5°	1519.4	1589.9	1668.2	1781.0	1893.8	1978.4	2014.4	2172.6	2258.8	2371.6	2507.8
20°	1485.0	1574.3	1674.5	1787.3	1933.0	1984.7	2058.3	2218.1	2324.6	2471.8	2639.4
22.5°	1448.9	1544.5	1665.1	1782.6	1945.5	2000.3	2100.6	2227.5	2396.6	2542.3	2727.1
25°	1409.8	1513.2	1635.3	1774.8	1934.5	2014.4	2108.4	2265.0	2448.3	2631.6	2802.3
27.5°	1370.6	1483.4	1610.3	1749.7	1904.8	1998.8	2092.7	2255.6	2490.6	2689.5	2907.3
30°	1333.0	1445.8	1572.7	1715.2	1878.1	1969.0	2058.3	2261.9	2523.5	2747.5	2966.8
32.5°	1292.3	1408.2	1541.4	1660.4	1824.9	1922.0	2022.3	2261.9	2543.9	2782.0	2982.5
35°	1243.7	1362.8	1477.1	1596.2	1759.1	1867.2	1980.0	2246.2	2562.7	2792.9	2916.7
37.5°	1196.7	1301.7	1400.4	1516.3	1687.0	1803.0	1933.0	2227.5	2553.3	2745.9	2780.4
40°	1143.5	1248.4	1328.3	1436.4	1616.5	1751.3	1882.8	2202.4	2512.5	2634.7	2534.5
42.5°	1091.8	1174.8	1243.7	1348.7	1544.5	1676.1	1818.6	2157.0	2432.7	2457.7	2232.2
45°	1032.3	1091.8	1152.9	1271.9	1466.2	1600.9	1759.1	2091.2	2304.2	2232.2	1947.1
47.5°	955.5	1008.8	1076.1	1185.8	1383.2	1522.6	1672.9	2006.6	2117.8	1967.4	1655.7
50°	881.9	927.3	990.0	1096.5	1295.4	1431.7	1591.5	1873.4	1928.3	1691.7	1427.0
52.5°	808.3	842.7	903.8	1010.3	1209.3	1340.9	1486.5	1737.2	1705.8	1452.1	1217.1
55°	731.5	761.3	819.2	924.2	1109.0	1234.3	1373.8	1569.6	1488.1	1246.9	1058.9
57.5°	656.3	687.7	747.2	834.9	1008.8	1131.0	1242.2	1395.7	1273.5	1080.8	914.8
60°	589.0	615.6	661.0	747.2	905.4	1004.1	1105.9	1210.8	1109.0	922.6	795.7
62.5°	518.5	543.5	585.8	664.2	800.4	888.2	969.6	1055.8	943.0	806.7	693.9
65°	452.7	473.1	512.2	584.3	695.5	767.5	833.3	892.9	802.0	676.7	592.1
67.5°	393.2	410.4	443.3	507.5	601.5	653.2	706.5	756.6	679.8	579.6	507.5
70°	328.9	343.0	372.8	419.8	495.0	548.2	587.4	625.0	556.1	476.2	427.6
72.5°	272.6	286.7	305.5	354.0	405.7	438.6	480.9	501.3	462.1	396.3	347.7
75°	217.7	228.7	245.9	277.3	325.8	347.7	374.4	390.0	354.0	310.2	280.4
77.5°	170.7	175.4	188.0	209.9	242.8	267.9	288.2	297.6	272.6	244.4	219.3
80°	120.6	126.9	136.3	155.1	180.1	188.0	200.5	211.5	195.8	170.7	155.1
82.5°	79.9	87.7	92.4	100.3	115.9	125.3	128.4	137.8	123.7	114.3	108.1
85°	47.0	50.1	51.7	56.4	64.2	68.9	73.6	75.2	72.1	70.5	64.2
87.5°	23.5	23.5	23.5	26.6	28.2	31.3	32.9	32.9	32.9	31.3	29.8
90°	0.8	2.5	4.2	5.9	7.6	8.4	9.5	11.7	13.8	16.0	18.2
92.5°	22.8	23.8	24.8	25.8	26.8	27.3	27.8	28.8	29.9	30.9	31.9
95°	44.8	46.0	47.2	48.3	49.5	50.1	50.8	52.1	53.5	54.8	56.2
97.5°	73.6	74.4	75.3	76.1	77.0	77.4	77.9	78.9	80.0	81.0	82.0
100°	103.3	104.3	105.3	106.3	107.3	107.8	108.2	109.1	109.9	110.8	111.6
102.5°	137.4	137.9	138.4	138.9	139.4	139.7	140.3	141.5	142.6	143.8	145.0
105°	170.8	171.1	171.5	171.8	172.1	172.3	173.1	174.6	176.1	177.7	179.2
107.5°	210.3	210.5	210.7	210.8	211.0	211.1	211.4	212.1	212.8	213.4	214.1
110°	246.7	247.1	247.4	247.8	248.1	248.3	248.5	248.8	249.1	249.5	249.8

TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	284.7	284.9	285.1	285.2	285.4	285.5	285.5	285.5	285.5	285.5	285.5
115°	322.7	323.2	323.7	324.2	324.7	324.9	324.7	324.4	324.1	323.7	323.4
117.5°	361.4	361.6	361.7	361.9	362.0	362.1	361.9	361.6	361.3	360.9	360.6
120°	397.1	398.1	399.1	400.1	401.1	401.6	401.2	400.3	399.5	398.6	397.8
122.5°	434.3	435.0	435.6	436.3	437.0	437.3	437.1	436.8	436.5	436.1	435.8
125°	472.2	472.7	473.2	473.7	474.2	474.5	474.3	474.0	473.7	473.3	473.0
127.5°	507.2	508.2	509.2	510.2	511.2	511.7	511.5	511.2	510.9	510.5	510.2
130°	542.1	543.5	544.8	546.2	547.5	548.2	547.9	547.4	546.9	546.4	545.9
132.5°	577.0	578.4	579.7	581.1	582.4	583.1	582.9	582.6	582.3	581.9	581.6
135°	612.7	613.7	614.7	615.7	616.7	617.2	617.1	617.0	616.8	616.7	616.5
137.5°	645.3	646.1	647.0	647.8	648.7	649.1	649.4	649.9	650.4	650.9	651.4
140°	679.5	680.3	681.2	682.0	682.9	683.3	683.4	683.6	683.7	683.9	684.1
142.5°	710.6	711.4	712.3	713.1	714.0	714.4	714.6	714.9	715.2	715.6	715.9
145°	743.3	743.6	744.0	744.3	744.6	744.8	745.1	745.6	746.1	746.6	747.1
147.5°	771.4	772.1	772.7	773.4	774.1	774.4	774.7	775.2	775.7	776.2	776.7
150°	801.0	801.3	801.7	802.0	802.3	802.5	802.7	803.0	803.3	803.7	804.0
152.5°	825.3	825.8	826.3	826.8	827.3	827.5	827.6	827.8	827.9	828.1	828.3
155°	851.1	851.1	851.1	851.1	851.1	851.1	851.2	851.3	851.5	851.6	851.8
157.5°	873.1	872.9	872.7	872.6	872.4	872.3	872.4	872.6	872.7	872.9	873.1
160°	893.6	893.3	892.9	892.6	892.3	892.1	892.1	892.1	892.1	892.1	892.1
162.5°	911.8	911.3	910.8	910.3	909.8	909.5	909.6	909.8	909.9	910.1	910.3
165°	927.0	926.5	926.0	925.5	925.0	924.7	924.7	924.7	924.7	924.7	924.7
167.5°	939.9	939.2	938.6	937.9	937.2	936.9	937.0	937.1	937.3	937.4	937.6
170°	950.5	949.8	949.2	948.5	947.8	947.5	947.5	947.5	947.5	947.5	947.5
172.5°	958.9	958.2	957.6	956.9	956.2	955.9	955.9	955.9	955.9	955.9	955.9
175°	964.2	963.5	962.9	962.2	961.5	961.2	961.2	961.2	961.2	961.2	961.2
177.5°	967.2	966.5	965.9	965.2	964.5	964.2	964.2	964.2	964.2	964.2	964.2
180°	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5

TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1702.7	1705.8	1716.8	1724.6	1740.3	1738.7	1738.7	1737.2	1732.5	1740.3	1745.0
5°	1821.7	1848.4	1851.5	1886.0	1887.5	1901.6	1911.0	1903.2	1922.0	1920.4	1906.3
7.5°	1969.0	2005.0	2022.3	2055.1	2092.7	2083.3	2119.4	2125.6	2122.5	2138.2	2149.1
10°	2130.3	2193.0	2236.9	2297.9	2313.6	2323.0	2346.5	2366.9	2407.6	2376.3	2396.6
12.5°	2315.2	2360.6	2418.6	2515.7	2564.2	2595.6	2606.5	2620.6	2648.8	2631.6	2633.2
15°	2470.2	2531.3	2630.0	2750.6	2764.7	2803.9	2794.5	2879.1	2919.8	2858.7	2893.2
17.5°	2631.6	2713.0	2830.5	2935.5	2995.0	3021.6	3046.7	3128.1	3125.0	3115.6	3123.4
20°	2735.0	2868.1	3013.8	3153.2	3170.4	3190.8	3258.2	3292.6	3286.4	3313.0	3330.2
22.5°	2880.7	3021.6	3176.7	3269.1	3308.3	3331.8	3385.0	3407.0	3416.4	3422.6	3411.7
25°	3002.8	3153.2	3267.6	3349.0	3372.5	3385.0	3402.3	3408.5	3403.8	3392.9	3402.3
27.5°	3085.9	3206.5	3284.8	3322.4	3309.8	3289.5	3256.6	3234.7	3186.1	3162.6	3190.8
30°	3120.3	3173.6	3197.1	3134.4	3071.8	3021.6	2959.0	2843.1	2752.2	2778.8	2742.8
32.5°	3065.5	3031.0	2918.2	2756.9	2708.3	2626.9	2449.9	2313.6	2318.3	2246.2	2276.0
35°	2904.1	2747.5	2534.5	2290.1	2225.9	2182.0	1987.8	1958.0	1895.4	1828.0	1846.8
37.5°	2619.1	2390.4	2131.9	1951.8	1856.2	1760.7	1651.0	1585.2	1547.6	1519.4	1541.4
40°	2271.3	1992.5	1779.5	1618.1	1536.7	1475.6	1400.4	1334.6	1292.3	1287.6	1295.4
42.5°	1929.8	1694.9	1499.1	1345.6	1318.9	1246.9	1198.3	1146.6	1134.1	1113.7	1124.7
45°	1633.8	1442.7	1281.3	1156.0	1124.7	1105.9	1046.4	1013.5	999.4	986.8	1005.6
47.5°	1419.2	1218.7	1101.2	1026.0	994.7	963.3	930.5	908.5	897.6	899.1	897.6
50°	1212.4	1065.2	961.8	903.8	885.0	863.1	836.5	822.4	817.7	803.6	814.5
52.5°	1043.2	936.7	864.7	809.8	795.7	780.1	758.1	750.3	739.4	736.2	736.2
55°	907.0	823.9	766.0	730.0	712.7	700.2	687.7	678.3	670.4	670.4	670.4
57.5°	800.4	728.4	686.1	654.8	648.5	636.0	621.9	621.9	610.9	609.3	614.0
60°	709.6	645.4	612.5	585.8	576.4	573.3	559.2	559.2	556.1	548.2	554.5
62.5°	617.2	570.2	542.0	521.6	512.2	512.2	501.3	493.4	493.4	495.0	491.9
65°	532.6	498.1	473.1	457.4	452.7	446.4	444.9	438.6	433.9	435.5	433.9
67.5°	457.4	430.8	413.5	401.0	393.2	390.0	385.3	385.3	382.2	383.8	375.9
70°	390.0	363.4	349.3	336.8	333.6	333.6	327.4	328.9	325.8	330.5	327.4
72.5°	321.1	300.8	289.8	285.1	282.0	280.4	277.3	274.1	272.6	275.7	274.1
75°	260.0	242.8	235.0	231.8	228.7	228.7	227.1	225.6	224.0	224.0	224.0
77.5°	202.1	191.1	181.7	184.8	180.1	181.7	177.0	177.0	178.6	177.0	177.0
80°	148.8	141.0	141.0	137.8	131.6	134.7	134.7	130.0	128.4	131.6	126.9
82.5°	98.7	97.1	94.0	92.4	89.3	90.9	89.3	87.7	86.2	89.3	86.2
85°	58.0	58.0	56.4	53.3	56.4	54.8	53.3	53.3	51.7	51.7	51.7
87.5°	29.8	26.6	26.6	25.1	26.6	23.5	25.1	23.5	21.9	23.5	21.9
90°	18.9	19.6	20.3	21.0	21.3	21.5	21.8	22.1	22.5	22.8	22.5
92.5°	32.4	32.9	33.4	33.9	34.2	34.0	33.7	33.3	33.0	32.6	33.0
95°	56.9	57.5	58.2	58.9	59.2	59.2	59.2	59.2	59.2	59.2	59.2
97.5°	82.8	83.7	84.5	85.4	85.8	85.7	85.5	85.4	85.2	85.0	85.2
100°	112.1	112.6	113.1	113.6	113.9	114.1	114.4	114.7	115.1	115.4	115.1
102.5°	145.5	146.0	146.5	147.0	147.3	147.2	147.0	146.9	146.7	146.5	146.7
105°	179.2	179.2	179.2	179.2	179.2	179.4	179.7	180.0	180.4	180.7	180.4
107.5°	214.6	215.1	215.6	216.1	216.4	216.3	216.1	216.0	215.8	215.6	215.8
110°	250.5	251.1	251.8	252.5	252.8	252.6	252.3	252.0	251.6	251.3	251.6

TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	286.3	287.2	288.0	288.9	289.3	289.3	289.3	289.3	289.3	289.3	289.3
115°	323.6	323.8	323.9	324.1	324.2	324.1	323.9	323.8	323.6	323.4	323.6
117.5°	360.6	360.6	360.6	360.6	360.6	360.4	359.9	359.4	358.9	358.4	358.9
120°	397.6	397.5	397.3	397.2	397.1	396.9	396.6	396.3	395.9	395.6	395.9
122.5°	435.3	434.8	434.3	433.8	433.5	433.2	432.7	432.2	431.7	431.2	431.7
125°	472.3	471.7	471.0	470.3	470.0	469.7	469.0	468.3	467.6	466.9	467.6
127.5°	509.2	508.2	507.1	506.1	505.6	505.3	504.6	503.9	503.3	502.6	503.3
130°	545.2	544.5	543.8	543.1	542.8	542.2	541.0	539.9	538.7	537.5	538.7
132.5°	580.8	579.9	579.1	578.2	577.8	577.4	576.5	575.7	574.8	574.0	574.8
135°	615.8	615.1	614.4	613.7	613.4	613.2	612.9	612.6	612.2	611.9	612.2
137.5°	650.6	649.7	648.9	648.0	647.6	647.3	646.8	646.3	645.8	645.3	645.8
140°	683.9	683.7	683.6	683.4	683.3	682.7	681.5	680.4	679.2	678.0	679.2
142.5°	715.7	715.6	715.4	715.3	715.2	714.8	713.9	713.1	712.2	711.4	712.2
145°	746.9	746.7	746.6	746.4	746.3	746.0	745.3	744.6	744.0	743.3	744.0
147.5°	776.7	776.7	776.7	776.7	776.7	776.2	775.2	774.1	773.1	772.1	773.1
150°	804.0	804.0	804.0	804.0	804.0	803.5	802.5	801.5	800.5	799.5	800.5
152.5°	828.6	829.0	829.3	829.6	829.8	829.4	828.5	827.7	826.8	826.0	826.8
155°	852.5	853.2	853.9	854.6	854.9	854.3	853.1	852.0	850.8	849.6	850.8
157.5°	873.8	874.4	875.1	875.8	876.1	875.6	874.6	873.6	872.6	871.6	872.6
160°	892.9	893.8	894.6	895.5	895.9	895.6	894.9	894.2	893.5	892.8	893.5
162.5°	911.1	912.0	912.8	913.7	914.1	913.5	912.3	911.2	910.0	908.8	910.0
165°	925.7	926.7	927.8	928.8	929.3	928.7	927.5	926.4	925.2	924.0	925.2
167.5°	938.6	939.6	940.7	941.7	942.2	941.7	940.7	939.6	938.6	937.6	938.6
170°	948.7	949.9	951.0	952.2	952.8	952.2	951.0	949.9	948.7	947.5	948.7
172.5°	956.9	957.9	958.9	959.9	960.4	959.8	958.6	957.5	956.3	955.1	956.3
175°	962.2	963.2	964.2	965.2	965.7	965.1	963.9	962.8	961.6	960.4	961.6
177.5°	965.2	966.2	967.3	968.3	968.8	968.2	967.0	965.8	964.6	963.4	964.6
180°	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5

TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1732.5	1737.2	1724.6	1721.5	1721.5	1727.8	1723.1	1680.8	1688.6	1679.2	1676.1
5°	1923.6	1914.2	1901.6	1895.4	1887.5	1865.6	1864.0	1815.5	1806.1	1774.8	1760.7
7.5°	2133.5	2125.6	2088.0	2083.3	2080.2	2059.8	2008.2	1956.5	1918.9	1882.8	1848.4
10°	2373.1	2349.6	2332.4	2297.9	2280.7	2252.5	2185.2	2136.6	2072.4	2017.6	1945.5
12.5°	2661.4	2634.7	2576.8	2551.7	2529.8	2451.5	2384.1	2329.3	2204.0	2166.4	2077.1
15°	2872.8	2816.4	2810.2	2755.3	2752.2	2666.1	2537.6	2478.1	2381.0	2243.1	2150.7
17.5°	3101.5	3051.4	3012.2	2946.4	2937.0	2855.6	2761.6	2615.9	2509.4	2377.8	2260.3
20°	3269.1	3242.5	3175.1	3148.5	3093.7	3024.8	2927.6	2747.5	2617.5	2485.9	2341.8
22.5°	3402.3	3375.6	3322.4	3286.4	3255.0	3165.7	3049.8	2896.3	2717.7	2545.4	2396.6
25°	3400.7	3392.9	3370.9	3353.7	3330.2	3264.4	3167.3	3020.1	2821.1	2631.6	2424.8
27.5°	3208.0	3230.0	3267.6	3286.4	3281.7	3272.3	3217.4	3093.7	2915.1	2689.5	2457.7
30°	2807.0	2886.9	2957.4	3051.4	3079.6	3148.5	3179.8	3109.3	2966.8	2756.9	2500.0
32.5°	2327.7	2443.6	2597.1	2648.8	2738.1	2871.3	3020.1	3046.7	2957.4	2796.1	2526.6
35°	1909.5	2005.0	2124.1	2205.5	2285.4	2501.6	2689.5	2852.5	2882.2	2775.7	2520.4
37.5°	1580.5	1647.9	1752.8	1821.7	1895.4	2080.2	2343.4	2554.8	2703.6	2706.8	2503.1
40°	1342.4	1372.2	1463.0	1513.2	1583.7	1743.4	1978.4	2254.1	2471.8	2572.1	2457.7
42.5°	1137.2	1176.4	1251.6	1289.2	1334.6	1474.0	1629.1	1890.7	2160.1	2374.7	2373.1
45°	1015.0	1043.2	1077.7	1109.0	1160.7	1243.7	1420.7	1616.5	1875.0	2117.8	2213.4
47.5°	907.0	933.6	968.0	977.4	1011.9	1090.2	1198.3	1369.1	1610.3	1851.5	2031.6
50°	816.1	838.0	861.5	878.8	894.4	958.7	1040.1	1184.2	1376.9	1610.3	1834.3
52.5°	745.6	761.3	781.6	791.0	805.1	852.1	914.8	1021.3	1179.5	1392.5	1610.3
55°	679.8	690.8	703.3	719.0	725.3	759.7	808.3	899.1	1016.6	1207.7	1414.5
57.5°	618.7	623.4	631.3	640.7	648.5	678.3	720.6	781.6	885.0	1032.3	1228.1
60°	549.8	562.3	567.0	576.4	581.1	604.6	637.5	689.2	769.1	896.0	1043.2
62.5°	491.9	499.7	507.5	512.2	523.2	531.0	557.6	604.6	670.4	764.4	897.6
65°	440.2	443.3	448.0	452.7	455.8	465.2	490.3	521.6	571.7	654.8	758.1
67.5°	380.6	383.8	390.0	391.6	394.7	407.3	421.4	448.0	490.3	552.9	637.5
70°	322.7	327.4	330.5	333.6	338.3	343.0	358.7	380.6	413.5	457.4	523.2
72.5°	272.6	277.3	277.3	280.4	278.8	285.1	300.8	316.4	338.3	374.4	432.3
75°	222.4	222.4	225.6	227.1	228.7	235.0	241.2	253.8	271.0	299.2	335.2
77.5°	175.4	173.9	177.0	177.0	177.0	181.7	188.0	194.2	205.2	225.6	253.8
80°	128.4	128.4	131.6	133.1	130.0	131.6	134.7	141.0	148.8	162.9	178.6
82.5°	84.6	90.9	89.3	90.9	89.3	92.4	94.0	95.6	98.7	105.0	115.9
85°	51.7	51.7	51.7	53.3	51.7	53.3	53.3	53.3	54.8	58.0	62.7
87.5°	21.9	21.9	21.9	23.5	21.9	21.9	23.5	21.9	23.5	23.5	25.1
90°	22.1	21.8	21.5	21.3	21.0	20.3	19.6	18.9	18.2	16.0	13.8
92.5°	33.3	33.7	34.0	34.2	33.9	33.4	32.9	32.4	31.9	30.9	29.9
95°	59.2	59.2	59.2	59.2	58.9	58.2	57.5	56.9	56.2	54.8	53.5
97.5°	85.4	85.5	85.7	85.8	85.4	84.5	83.7	82.8	82.0	81.0	80.0
100°	114.7	114.4	114.1	113.9	113.6	113.1	112.6	112.1	111.6	110.8	109.9
102.5°	146.9	147.0	147.2	147.3	147.0	146.5	146.0	145.5	145.0	143.8	142.6
105°	180.0	179.7	179.4	179.2	179.2	179.2	179.2	179.2	179.2	177.7	176.1
107.5°	216.0	216.1	216.3	216.4	216.1	215.6	215.1	214.6	214.1	213.4	212.8
110°	252.0	252.3	252.6	252.8	252.5	251.8	251.1	250.5	249.8	249.5	249.1

TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	289.3	289.3	289.3	289.3	288.9	288.0	287.2	286.3	285.5	285.5	285.5
115°	323.8	323.9	324.1	324.2	324.1	323.9	323.8	323.6	323.4	323.7	324.1
117.5°	359.4	359.9	360.4	360.6	360.6	360.6	360.6	360.6	360.6	360.9	361.3
120°	396.3	396.6	396.9	397.1	397.2	397.3	397.5	397.6	397.8	398.6	399.5
122.5°	432.2	432.7	433.2	433.5	433.8	434.3	434.8	435.3	435.8	436.1	436.5
125°	468.3	469.0	469.7	470.0	470.3	471.0	471.7	472.3	473.0	473.3	473.7
127.5°	503.9	504.6	505.3	505.6	506.1	507.1	508.2	509.2	510.2	510.5	510.9
130°	539.9	541.0	542.2	542.8	543.1	543.8	544.5	545.2	545.9	546.4	546.9
132.5°	575.7	576.5	577.4	577.8	578.2	579.1	579.9	580.8	581.6	581.9	582.3
135°	612.6	612.9	613.2	613.4	613.7	614.4	615.1	615.8	616.5	616.7	616.8
137.5°	646.3	646.8	647.3	647.6	648.0	648.9	649.7	650.6	651.4	650.9	650.4
140°	680.4	681.5	682.7	683.3	683.4	683.6	683.7	683.9	684.1	683.9	683.7
142.5°	713.1	713.9	714.8	715.2	715.3	715.4	715.6	715.7	715.9	715.6	715.2
145°	744.6	745.3	746.0	746.3	746.4	746.6	746.7	746.9	747.1	746.6	746.1
147.5°	774.1	775.2	776.2	776.7	776.7	776.7	776.7	776.7	776.7	776.2	775.7
150°	801.5	802.5	803.5	804.0	804.0	804.0	804.0	804.0	804.0	803.7	803.3
152.5°	827.7	828.5	829.4	829.8	829.6	829.3	829.0	828.6	828.3	828.1	827.9
155°	852.0	853.1	854.3	854.9	854.6	853.9	853.2	852.5	851.8	851.6	851.5
157.5°	873.6	874.6	875.6	876.1	875.8	875.1	874.4	873.8	873.1	872.9	872.7
160°	894.2	894.9	895.6	895.9	895.5	894.6	893.8	892.9	892.1	892.1	892.1
162.5°	911.2	912.3	913.5	914.1	913.7	912.8	912.0	911.1	910.3	910.1	909.9
165°	926.4	927.5	928.7	929.3	928.8	927.8	926.7	925.7	924.7	924.7	924.7
167.5°	939.6	940.7	941.7	942.2	941.7	940.7	939.6	938.6	937.6	937.4	937.3
170°	949.9	951.0	952.2	952.8	952.2	951.0	949.9	948.7	947.5	947.5	947.5
172.5°	957.5	958.6	959.8	960.4	959.9	958.9	957.9	956.9	955.9	955.9	955.9
175°	962.8	963.9	965.1	965.7	965.2	964.2	963.2	962.2	961.2	961.2	961.2
177.5°	965.8	967.0	968.2	968.8	968.3	967.3	966.2	965.2	964.2	964.2	964.2
180°	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5

TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1660.4	1655.7	1655.7	1652.6	1643.2	1625.9	1624.4	1627.5	1618.1	1608.7	1594.6
5°	1741.9	1712.1	1702.7	1693.3	1674.5	1643.2	1630.6	1619.7	1602.4	1582.1	1560.2
7.5°	1810.8	1768.5	1756.0	1738.7	1701.1	1657.3	1629.1	1605.6	1582.1	1553.9	1527.3
10°	1896.9	1835.8	1806.1	1781.0	1729.3	1668.2	1625.9	1591.5	1553.9	1519.4	1485.0
12.5°	1994.1	1895.4	1886.0	1824.9	1765.4	1674.5	1622.8	1572.7	1522.6	1480.3	1444.2
15°	2075.5	1967.4	1928.3	1887.5	1773.2	1660.4	1610.3	1553.9	1495.9	1450.5	1397.2
17.5°	2127.2	2037.9	1954.9	1900.1	1781.0	1680.8	1583.7	1519.4	1458.3	1395.7	1351.8
20°	2189.9	2059.8	1987.8	1914.2	1796.7	1665.1	1568.0	1488.1	1412.9	1356.5	1303.3
22.5°	2252.5	2077.1	2017.6	1937.7	1799.8	1649.4	1539.8	1459.9	1373.8	1317.4	1259.4
25°	2246.2	2102.1	2003.5	1936.1	1768.5	1635.3	1506.9	1412.9	1333.0	1261.0	1203.0
27.5°	2250.9	2073.9	1973.7	1895.4	1746.6	1615.0	1472.4	1373.8	1290.7	1215.5	1154.5
30°	2252.5	2031.6	1943.9	1849.9	1705.8	1566.4	1433.3	1333.0	1245.3	1163.9	1109.0
32.5°	2247.8	1997.2	1887.5	1803.0	1641.6	1519.4	1387.8	1281.3	1192.0	1116.9	1065.2
35°	2236.9	1956.5	1829.6	1723.1	1575.8	1452.1	1345.6	1235.9	1140.4	1071.4	1011.9
37.5°	2207.1	1912.6	1768.5	1663.5	1499.1	1373.8	1279.8	1188.9	1096.5	1015.0	964.9
40°	2185.2	1853.1	1707.4	1593.1	1416.0	1293.9	1215.5	1129.4	1038.5	964.9	916.4
42.5°	2135.0	1796.7	1644.7	1508.5	1334.6	1209.3	1135.7	1066.7	988.4	916.4	872.5
45°	2053.6	1735.6	1568.0	1430.1	1245.3	1126.3	1058.9	1002.5	933.6	864.7	820.8
47.5°	1939.2	1647.9	1486.5	1348.7	1157.6	1037.0	969.6	927.3	872.5	814.5	776.9
50°	1815.5	1552.3	1403.5	1267.2	1073.0	955.5	889.7	850.6	814.5	761.3	725.3
52.5°	1654.1	1450.5	1308.0	1177.9	982.1	869.4	811.4	783.2	745.6	708.0	676.7
55°	1497.5	1318.9	1201.4	1077.7	892.9	787.9	731.5	701.8	679.8	648.5	623.4
57.5°	1315.8	1196.7	1088.7	975.9	809.8	714.3	661.0	625.0	610.9	596.8	573.3
60°	1148.2	1057.3	969.6	875.6	723.7	637.5	585.8	557.6	543.5	534.1	518.5
62.5°	994.7	924.2	849.0	773.8	636.0	557.6	518.5	490.3	477.8	476.2	462.1
65°	847.4	797.3	736.2	662.6	554.5	485.6	448.0	430.8	416.7	416.7	405.7
67.5°	700.2	665.7	617.2	565.5	480.9	416.7	382.2	366.5	358.7	358.7	350.9
70°	582.7	559.2	515.4	469.9	396.3	347.7	321.1	307.0	302.3	303.9	297.6
72.5°	473.1	448.0	412.0	379.1	324.2	288.2	269.4	253.8	245.9	247.5	245.9
75°	366.5	354.0	322.7	297.6	253.8	228.7	211.5	203.6	197.4	198.9	195.8
77.5°	275.7	256.9	239.7	222.4	195.8	175.4	161.3	153.5	148.8	148.8	148.8
80°	188.0	184.8	170.7	161.3	139.4	123.7	112.8	111.2	106.5	106.5	106.5
82.5°	122.2	114.3	106.5	100.3	87.7	78.3	73.6	70.5	68.9	67.4	70.5
85°	67.4	62.7	59.5	53.3	48.6	43.9	39.2	37.6	36.0	37.6	36.0
87.5°	26.6	21.9	21.9	20.4	18.8	17.2	17.2	14.1	14.1	12.5	12.5
90°	11.7	9.5	8.4	7.6	5.9	4.2	2.5	0.8	2.5	4.2	5.9
92.5°	28.8	27.8	27.3	26.8	25.8	24.8	23.8	22.8	23.8	24.8	25.8
95°	52.1	50.8	50.1	49.5	48.3	47.2	46.0	44.8	46.0	47.2	48.3
97.5°	78.9	77.9	77.4	77.0	76.1	75.3	74.4	73.6	74.4	75.3	76.1
100°	109.1	108.2	107.8	107.3	106.3	105.3	104.3	103.3	104.3	105.3	106.3
102.5°	141.5	140.3	139.7	139.4	138.9	138.4	137.9	137.4	137.9	138.4	138.9
105°	174.6	173.1	172.3	172.1	171.8	171.5	171.1	170.8	171.1	171.5	171.8
107.5°	212.1	211.4	211.1	211.0	210.8	210.7	210.5	210.3	210.5	210.7	210.8
110°	248.8	248.5	248.3	248.1	247.8	247.4	247.1	246.7	247.1	247.4	247.8

TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	285.5	285.5	285.5	285.4	285.2	285.1	284.9	284.7	284.9	285.1	285.2
115°	324.4	324.7	324.9	324.7	324.2	323.7	323.2	322.7	323.2	323.7	324.2
117.5°	361.6	361.9	362.1	362.0	361.9	361.7	361.6	361.4	361.6	361.7	361.9
120°	400.3	401.2	401.6	401.1	400.1	399.1	398.1	397.1	398.1	399.1	400.1
122.5°	436.8	437.1	437.3	437.0	436.3	435.6	435.0	434.3	435.0	435.6	436.3
125°	474.0	474.3	474.5	474.2	473.7	473.2	472.7	472.2	472.7	473.2	473.7
127.5°	511.2	511.5	511.7	511.2	510.2	509.2	508.2	507.2	508.2	509.2	510.2
130°	547.4	547.9	548.2	547.5	546.2	544.8	543.5	542.1	543.5	544.8	546.2
132.5°	582.6	582.9	583.1	582.4	581.1	579.7	578.4	577.0	578.4	579.7	581.1
135°	617.0	617.1	617.2	616.7	615.7	614.7	613.7	612.7	613.7	614.7	615.7
137.5°	649.9	649.4	649.1	648.7	647.8	647.0	646.1	645.3	646.1	647.0	647.8
140°	683.6	683.4	683.3	682.9	682.0	681.2	680.3	679.5	680.3	681.2	682.0
142.5°	714.9	714.6	714.4	714.0	713.1	712.3	711.4	710.6	711.4	712.3	713.1
145°	745.6	745.1	744.8	744.6	744.3	744.0	743.6	743.3	743.6	744.0	744.3
147.5°	775.2	774.7	774.4	774.1	773.4	772.7	772.1	771.4	772.1	772.7	773.4
150°	803.0	802.7	802.5	802.3	802.0	801.7	801.3	801.0	801.3	801.7	802.0
152.5°	827.8	827.6	827.5	827.3	826.8	826.3	825.8	825.3	825.8	826.3	826.8
155°	851.3	851.2	851.1	851.1	851.1	851.1	851.1	851.1	851.1	851.1	851.1
157.5°	872.6	872.4	872.3	872.4	872.6	872.7	872.9	873.1	872.9	872.7	872.6
160°	892.1	892.1	892.1	892.3	892.6	892.9	893.3	893.6	893.3	892.9	892.6
162.5°	909.8	909.6	909.5	909.8	910.3	910.8	911.3	911.8	911.3	910.8	910.3
165°	924.7	924.7	924.7	925.0	925.5	926.0	926.5	927.0	926.5	926.0	925.5
167.5°	937.1	937.0	936.9	937.2	937.9	938.6	939.2	939.9	939.2	938.6	937.9
170°	947.5	947.5	947.5	947.8	948.5	949.2	949.8	950.5	949.8	949.2	948.5
172.5°	955.9	955.9	955.9	956.2	956.9	957.6	958.2	958.9	958.2	957.6	956.9
175°	961.2	961.2	961.2	961.5	962.2	962.9	963.5	964.2	963.5	962.9	962.2
177.5°	964.2	964.2	964.2	964.5	965.2	965.9	966.5	967.2	966.5	965.9	965.2
180°	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5

TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1591.5	1589.9	1593.1	1583.7	1568.0	1560.2	1538.2	1533.5	1532.0	1533.5	1535.1
5°	1547.6	1546.1	1541.4	1525.7	1506.9	1492.8	1466.2	1464.6	1455.2	1445.8	1450.5
7.5°	1505.3	1499.1	1489.7	1469.3	1444.2	1428.6	1406.6	1391.0	1378.5	1370.6	1364.4
10°	1463.0	1453.6	1444.2	1417.6	1386.3	1362.8	1336.2	1323.6	1309.5	1303.3	1297.0
12.5°	1408.2	1398.8	1381.6	1350.3	1331.5	1301.7	1275.1	1262.5	1254.7	1242.2	1234.3
15°	1364.4	1345.6	1336.2	1303.3	1264.1	1261.0	1212.4	1209.3	1193.6	1193.6	1181.1
17.5°	1314.2	1300.1	1282.9	1250.0	1221.8	1193.6	1168.6	1159.2	1145.1	1141.9	1135.7
20°	1265.7	1246.9	1240.6	1207.7	1177.9	1143.5	1116.9	1107.5	1101.2	1094.9	1099.6
22.5°	1215.5	1199.9	1184.2	1154.5	1132.5	1098.1	1082.4	1073.0	1063.6	1060.5	1062.0
25°	1167.0	1152.9	1137.2	1107.5	1084.0	1055.8	1041.7	1037.0	1032.3	1032.3	1030.7
27.5°	1120.0	1105.9	1091.8	1065.2	1041.7	1021.3	1010.3	1005.6	1000.9	1004.1	1007.2
30°	1071.4	1058.9	1046.4	1022.9	1004.1	985.3	979.0	975.9	974.3	982.1	982.1
32.5°	1027.6	1016.6	1007.2	985.3	966.5	950.8	946.1	947.7	949.3	954.0	957.1
35°	982.1	974.3	964.9	946.1	930.5	916.4	917.9	917.9	921.1	928.9	935.2
37.5°	941.4	930.5	922.6	907.0	894.4	881.9	886.6	891.3	894.4	903.8	907.0
40°	892.9	888.2	881.9	866.2	855.3	853.7	855.3	858.4	864.7	869.4	874.1
42.5°	853.7	847.4	839.6	827.1	817.7	819.2	820.8	823.9	827.1	834.9	839.6
45°	809.8	805.1	798.9	787.9	780.1	781.6	783.2	783.2	786.3	795.7	798.9
47.5°	761.3	762.8	755.0	744.1	739.4	739.4	739.4	742.5	750.3	753.4	755.0
50°	714.3	711.2	709.6	698.6	695.5	693.9	695.5	697.1	708.0	706.5	711.2
52.5°	664.2	664.2	662.6	656.3	651.6	651.6	648.5	656.3	659.5	662.6	667.3
55°	615.6	610.9	609.3	606.2	599.9	598.4	601.5	610.9	614.0	617.2	621.9
57.5°	562.3	562.3	559.2	554.5	554.5	554.5	554.5	560.8	565.5	568.6	578.0
60°	513.8	507.5	502.8	502.8	502.8	501.3	510.7	510.7	520.1	521.6	524.8
62.5°	455.8	452.7	449.6	451.1	449.6	452.7	455.8	462.1	463.7	468.4	473.1
65°	401.0	401.0	397.9	407.3	401.0	401.0	408.8	408.8	412.0	416.7	422.9
67.5°	347.7	349.3	346.2	346.2	349.3	350.9	352.4	358.7	360.3	366.5	374.4
70°	292.9	296.1	297.6	294.5	297.6	300.8	303.9	305.5	311.7	314.9	319.6
72.5°	244.4	247.5	242.8	244.4	245.9	249.1	250.6	253.8	256.9	266.3	269.4
75°	195.8	194.2	192.7	198.9	195.8	202.1	203.6	203.6	206.8	214.6	217.7
77.5°	150.4	150.4	151.9	148.8	153.5	151.9	153.5	158.2	162.9	162.9	175.4
80°	105.0	108.1	108.1	108.1	109.6	111.2	108.1	115.9	117.5	117.5	122.2
82.5°	67.4	68.9	67.4	70.5	70.5	73.6	72.1	73.6	76.8	79.9	81.5
85°	36.0	36.0	39.2	39.2	37.6	39.2	37.6	39.2	42.3	42.3	43.9
87.5°	12.5	12.5	12.5	12.5	14.1	12.5	14.1	14.1	12.5	12.5	17.2
90°	7.6	8.4	9.5	11.7	13.8	16.0	18.2	18.9	19.6	20.3	21.0
92.5°	26.8	27.3	27.8	28.8	29.9	30.9	31.9	32.4	32.9	33.4	33.9
95°	49.5	50.1	50.8	52.1	53.5	54.8	56.2	56.9	57.5	58.2	58.9
97.5°	77.0	77.4	77.9	78.9	80.0	81.0	82.0	82.8	83.7	84.5	85.4
100°	107.3	107.8	108.2	109.1	109.9	110.8	111.6	112.1	112.6	113.1	113.6
102.5°	139.4	139.7	140.3	141.5	142.6	143.8	145.0	145.5	146.0	146.5	147.0
105°	172.1	172.3	173.1	174.6	176.1	177.7	179.2	179.2	179.2	179.2	179.2
107.5°	211.0	211.1	211.4	212.1	212.8	213.4	214.1	214.6	215.1	215.6	216.1
110°	248.1	248.3	248.5	248.8	249.1	249.5	249.8	250.5	251.1	251.8	252.5

TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	285.4	285.5	285.5	285.5	285.5	285.5	285.5	286.3	287.2	288.0	288.9
115°	324.7	324.9	324.7	324.4	324.1	323.7	323.4	323.6	323.8	323.9	324.1
117.5°	362.0	362.1	361.9	361.6	361.3	360.9	360.6	360.6	360.6	360.6	360.6
120°	401.1	401.6	401.2	400.3	399.5	398.6	397.8	397.6	397.5	397.3	397.2
122.5°	437.0	437.3	437.1	436.8	436.5	436.1	435.8	435.3	434.8	434.3	433.8
125°	474.2	474.5	474.3	474.0	473.7	473.3	473.0	472.3	471.7	471.0	470.3
127.5°	511.2	511.7	511.5	511.2	510.9	510.5	510.2	509.2	508.2	507.1	506.1
130°	547.5	548.2	547.9	547.4	546.9	546.4	545.9	545.2	544.5	543.8	543.1
132.5°	582.4	583.1	582.9	582.6	582.3	581.9	581.6	580.8	579.9	579.1	578.2
135°	616.7	617.2	617.1	617.0	616.8	616.7	616.5	615.8	615.1	614.4	613.7
137.5°	648.7	649.1	649.4	649.9	650.4	650.9	651.4	650.6	649.7	648.9	648.0
140°	682.9	683.3	683.4	683.6	683.7	683.9	684.1	683.9	683.7	683.6	683.4
142.5°	714.0	714.4	714.6	714.9	715.2	715.6	715.9	715.7	715.6	715.4	715.3
145°	744.6	744.8	745.1	745.6	746.1	746.6	747.1	746.9	746.7	746.6	746.4
147.5°	774.1	774.4	774.7	775.2	775.7	776.2	776.7	776.7	776.7	776.7	776.7
150°	802.3	802.5	802.7	803.0	803.3	803.7	804.0	804.0	804.0	804.0	804.0
152.5°	827.3	827.5	827.6	827.8	827.9	828.1	828.3	828.6	829.0	829.3	829.6
155°	851.1	851.1	851.2	851.3	851.5	851.6	851.8	852.5	853.2	853.9	854.6
157.5°	872.4	872.3	872.4	872.6	872.7	872.9	873.1	873.8	874.4	875.1	875.8
160°	892.3	892.1	892.1	892.1	892.1	892.1	892.1	892.9	893.8	894.6	895.5
162.5°	909.8	909.5	909.6	909.8	909.9	910.1	910.3	911.1	912.0	912.8	913.7
165°	925.0	924.7	924.7	924.7	924.7	924.7	924.7	925.7	926.7	927.8	928.8
167.5°	937.2	936.9	937.0	937.1	937.3	937.4	937.6	938.6	939.6	940.7	941.7
170°	947.8	947.5	947.5	947.5	947.5	947.5	947.5	948.7	949.9	951.0	952.2
172.5°	956.2	955.9	955.9	955.9	955.9	955.9	955.9	956.9	957.9	958.9	959.9
175°	961.5	961.2	961.2	961.2	961.2	961.2	961.2	962.2	963.2	964.2	965.2
177.5°	964.5	964.2	964.2	964.2	964.2	964.2	964.2	965.2	966.2	967.3	968.3
180°	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5

TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1533.5	1535.1	1528.8	1524.1	1536.7	1528.8	1528.8	1530.4	1527.3	1532.0	1530.4
5°	1447.4	1448.9	1438.0	1441.1	1434.8	1433.3	1431.7	1441.1	1439.5	1438.0	1441.1
7.5°	1362.8	1362.8	1358.1	1355.0	1355.0	1350.3	1356.5	1355.0	1358.1	1358.1	1362.8
10°	1292.3	1295.4	1287.6	1279.8	1278.2	1279.8	1279.8	1281.3	1282.9	1293.9	1292.3
12.5°	1234.3	1229.6	1228.1	1223.4	1215.5	1212.4	1209.3	1226.5	1221.8	1221.8	1221.8
15°	1170.1	1181.1	1179.5	1165.4	1162.3	1168.6	1165.4	1165.4	1181.1	1179.5	1177.9
17.5°	1135.7	1132.5	1129.4	1121.6	1123.1	1121.6	1123.1	1123.1	1132.5	1132.5	1132.5
20°	1096.5	1090.2	1090.2	1087.1	1087.1	1082.4	1088.7	1090.2	1096.5	1096.5	1098.1
22.5°	1062.0	1057.3	1057.3	1055.8	1058.9	1052.6	1058.9	1060.5	1060.5	1065.2	1065.2
25°	1032.3	1029.1	1029.1	1032.3	1032.3	1032.3	1032.3	1038.5	1033.8	1035.4	1033.8
27.5°	1005.6	1007.2	1008.8	1010.3	1008.8	1010.3	1011.9	1015.0	1016.6	1015.0	1011.9
30°	980.6	985.3	986.8	986.8	990.0	991.5	993.1	993.1	994.7	990.0	993.1
32.5°	961.8	961.8	964.9	966.5	969.6	971.2	971.2	974.3	972.7	968.0	969.6
35°	935.2	935.2	941.4	944.6	949.3	947.7	949.3	949.3	950.8	947.7	943.0
37.5°	908.5	911.7	911.7	917.9	919.5	921.1	919.5	922.6	921.1	917.9	916.4
40°	877.2	875.6	877.2	881.9	883.5	883.5	883.5	886.6	886.6	886.6	885.0
42.5°	838.0	842.7	841.2	845.9	844.3	844.3	847.4	850.6	852.1	847.4	849.0
45°	800.4	800.4	803.6	803.6	805.1	805.1	811.4	808.3	811.4	808.3	809.8
47.5°	759.7	761.3	761.3	762.8	766.0	769.1	766.0	767.5	767.5	769.1	766.0
50°	714.3	714.3	717.4	722.1	728.4	725.3	723.7	730.0	725.3	725.3	722.1
52.5°	667.3	672.0	673.6	678.3	683.0	684.5	686.1	683.0	684.5	679.8	681.4
55°	621.9	623.4	629.7	634.4	639.1	639.1	637.5	639.1	640.7	634.4	634.4
57.5°	576.4	581.1	587.4	587.4	593.7	593.7	592.1	592.1	593.7	589.0	587.4
60°	527.9	532.6	540.4	540.4	549.8	551.4	548.2	545.1	545.1	540.4	542.0
62.5°	476.2	480.9	485.6	493.4	499.7	496.6	502.8	496.6	498.1	488.7	488.7
65°	430.8	432.3	440.2	448.0	448.0	451.1	448.0	449.6	444.9	444.9	438.6
67.5°	377.5	377.5	385.3	393.2	401.0	401.0	401.0	396.3	396.3	391.6	391.6
70°	330.5	328.9	336.8	341.5	346.2	347.7	344.6	343.0	339.9	335.2	333.6
72.5°	272.6	275.7	283.5	286.7	294.5	292.9	300.8	291.4	291.4	283.5	282.0
75°	220.9	224.0	231.8	236.5	241.2	241.2	245.9	241.2	235.0	231.8	230.3
77.5°	175.4	173.9	180.1	188.0	189.5	188.0	191.1	189.5	183.3	183.3	180.1
80°	125.3	130.0	136.3	134.7	141.0	139.4	139.4	136.3	136.3	131.6	134.7
82.5°	83.0	87.7	89.3	87.7	89.3	92.4	94.0	92.4	92.4	89.3	90.9
85°	43.9	43.9	47.0	48.6	47.0	47.0	48.6	53.3	50.1	47.0	50.1
87.5°	14.1	12.5	12.5	14.1	12.5	12.5	14.1	14.1	15.7	15.7	15.7
90°	21.3	21.5	21.8	22.1	22.5	22.8	22.5	22.1	21.8	21.5	21.3
92.5°	34.2	34.0	33.7	33.3	33.0	32.6	33.0	33.3	33.7	34.0	34.2
95°	59.2	59.2	59.2	59.2	59.2	59.2	59.2	59.2	59.2	59.2	59.2
97.5°	85.8	85.7	85.5	85.4	85.2	85.0	85.2	85.4	85.5	85.7	85.8
100°	113.9	114.1	114.4	114.7	115.1	115.4	115.1	114.7	114.4	114.1	113.9
102.5°	147.3	147.2	147.0	146.9	146.7	146.5	146.7	146.9	147.0	147.2	147.3
105°	179.2	179.4	179.7	180.0	180.4	180.7	180.4	180.0	179.7	179.4	179.2
107.5°	216.4	216.3	216.1	216.0	215.8	215.6	215.8	216.0	216.1	216.3	216.4
110°	252.8	252.6	252.3	252.0	251.6	251.3	251.6	252.0	252.3	252.6	252.8

TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	289.3	289.3	289.3	289.3	289.3	289.3	289.3	289.3	289.3	289.3	289.3
115°	324.2	324.1	323.9	323.8	323.6	323.4	323.6	323.8	323.9	324.1	324.2
117.5°	360.6	360.4	359.9	359.4	358.9	358.4	358.9	359.4	359.9	360.4	360.6
120°	397.1	396.9	396.6	396.3	395.9	395.6	395.9	396.3	396.6	396.9	397.1
122.5°	433.5	433.2	432.7	432.2	431.7	431.2	431.7	432.2	432.7	433.2	433.5
125°	470.0	469.7	469.0	468.3	467.6	466.9	467.6	468.3	469.0	469.7	470.0
127.5°	505.6	505.3	504.6	503.9	503.3	502.6	503.3	503.9	504.6	505.3	505.6
130°	542.8	542.2	541.0	539.9	538.7	537.5	538.7	539.9	541.0	542.2	542.8
132.5°	577.8	577.4	576.5	575.7	574.8	574.0	574.8	575.7	576.5	577.4	577.8
135°	613.4	613.2	612.9	612.6	612.2	611.9	612.2	612.6	612.9	613.2	613.4
137.5°	647.6	647.3	646.8	646.3	645.8	645.3	645.8	646.3	646.8	647.3	647.6
140°	683.3	682.7	681.5	680.4	679.2	678.0	679.2	680.4	681.5	682.7	683.3
142.5°	715.2	714.8	713.9	713.1	712.2	711.4	712.2	713.1	713.9	714.8	715.2
145°	746.3	746.0	745.3	744.6	744.0	743.3	744.0	744.6	745.3	746.0	746.3
147.5°	776.7	776.2	775.2	774.1	773.1	772.1	773.1	774.1	775.2	776.2	776.7
150°	804.0	803.5	802.5	801.5	800.5	799.5	800.5	801.5	802.5	803.5	804.0
152.5°	829.8	829.4	828.5	827.7	826.8	826.0	826.8	827.7	828.5	829.4	829.8
155°	854.9	854.3	853.1	852.0	850.8	849.6	850.8	852.0	853.1	854.3	854.9
157.5°	876.1	875.6	874.6	873.6	872.6	871.6	872.6	873.6	874.6	875.6	876.1
160°	895.9	895.6	894.9	894.2	893.5	892.8	893.5	894.2	894.9	895.6	895.9
162.5°	914.1	913.5	912.3	911.2	910.0	908.8	910.0	911.2	912.3	913.5	914.1
165°	929.3	928.7	927.5	926.4	925.2	924.0	925.2	926.4	927.5	928.7	929.3
167.5°	942.2	941.7	940.7	939.6	938.6	937.6	938.6	939.6	940.7	941.7	942.2
170°	952.8	952.2	951.0	949.9	948.7	947.5	948.7	949.9	951.0	952.2	952.8
172.5°	960.4	959.8	958.6	957.5	956.3	955.1	956.3	957.5	958.6	959.8	960.4
175°	965.7	965.1	963.9	962.8	961.6	960.4	961.6	962.8	963.9	965.1	965.7
177.5°	968.8	968.2	967.0	965.8	964.6	963.4	964.6	965.8	967.0	968.2	968.8
180°	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5

TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1535.1	1538.2	1539.8	1533.5	1528.8	1536.7	1547.6	1555.5	1561.7	1569.6	1574.3
5°	1444.2	1455.2	1455.2	1458.3	1463.0	1470.9	1491.2	1505.3	1517.9	1527.3	1535.1
7.5°	1367.5	1375.3	1380.0	1387.8	1395.7	1406.6	1430.1	1450.5	1469.3	1480.3	1492.8
10°	1298.6	1304.8	1312.7	1317.4	1331.5	1347.1	1376.9	1394.1	1416.0	1433.3	1448.9
12.5°	1232.8	1254.7	1259.4	1257.8	1270.4	1287.6	1317.4	1344.0	1367.5	1384.7	1401.9
15°	1185.8	1193.6	1203.0	1201.4	1228.1	1232.8	1257.8	1289.2	1320.5	1331.5	1347.1
17.5°	1134.1	1146.6	1156.0	1160.7	1168.6	1185.8	1209.3	1232.8	1273.5	1275.1	1315.8
20°	1093.4	1105.9	1112.2	1118.4	1123.1	1143.5	1163.9	1190.5	1223.4	1240.6	1262.5
22.5°	1066.7	1073.0	1077.7	1082.4	1088.7	1099.6	1124.7	1154.5	1176.4	1195.2	1209.3
25°	1035.4	1041.7	1047.9	1051.1	1055.8	1062.0	1080.8	1104.3	1135.7	1148.2	1162.3
27.5°	1013.5	1013.5	1016.6	1016.6	1022.9	1029.1	1043.2	1065.2	1090.2	1105.9	1124.7
30°	990.0	988.4	990.0	988.4	986.8	996.2	1008.8	1027.6	1044.8	1063.6	1076.1
32.5°	966.5	964.9	964.9	966.5	960.2	964.9	971.2	988.4	1007.2	1016.6	1030.7
35°	941.4	938.3	938.3	938.3	935.2	932.0	938.3	954.0	966.5	979.0	990.0
37.5°	916.4	911.7	911.7	908.5	905.4	900.7	900.7	913.2	930.5	935.2	949.3
40°	881.9	881.9	878.8	877.2	874.1	870.9	866.2	877.2	892.9	897.6	908.5
42.5°	847.4	842.7	841.2	841.2	841.2	836.5	833.3	841.2	850.6	858.4	864.7
45°	808.3	805.1	806.7	805.1	802.0	800.4	798.9	802.0	813.0	816.1	823.9
47.5°	766.0	764.4	764.4	762.8	761.3	762.8	756.6	764.4	767.5	770.7	776.9
50°	722.1	720.6	719.0	717.4	717.4	719.0	717.4	717.4	723.7	726.8	733.1
52.5°	678.3	673.6	673.6	672.0	672.0	668.9	672.0	673.6	676.7	679.8	683.0
55°	631.3	631.3	626.6	626.6	623.4	623.4	625.0	623.4	629.7	632.8	632.8
57.5°	585.8	579.6	581.1	578.0	574.9	573.3	573.3	576.4	579.6	579.6	582.7
60°	537.3	531.0	529.5	523.2	526.3	521.6	523.2	523.2	529.5	526.3	529.5
62.5°	488.7	480.9	476.2	473.1	473.1	474.6	471.5	469.9	473.1	476.2	482.5
65°	437.0	432.3	427.6	422.9	422.9	421.4	424.5	419.8	418.2	419.8	422.9
67.5°	383.8	379.1	374.4	369.7	371.2	366.5	363.4	368.1	365.0	366.5	369.7
70°	332.1	328.9	319.6	316.4	314.9	316.4	314.9	311.7	316.4	314.9	316.4
72.5°	280.4	277.3	272.6	264.7	264.7	263.2	261.6	261.6	260.0	260.0	260.0
75°	230.3	224.0	219.3	217.7	214.6	213.0	211.5	208.3	209.9	211.5	208.3
77.5°	178.6	170.7	169.2	169.2	164.5	164.5	166.0	164.5	162.9	162.9	162.9
80°	131.6	125.3	125.3	122.2	119.0	119.0	119.0	119.0	117.5	115.9	117.5
82.5°	84.6	83.0	81.5	81.5	84.6	78.3	81.5	79.9	78.3	78.3	76.8
85°	47.0	48.6	47.0	48.6	45.4	47.0	47.0	47.0	45.4	47.0	43.9
87.5°	17.2	17.2	17.2	18.8	18.8	18.8	18.8	18.8	20.4	18.8	18.8
90°	21.0	20.3	19.6	18.9	18.2	16.0	13.8	11.7	9.5	8.4	7.6
92.5°	33.9	33.4	32.9	32.4	31.9	30.9	29.9	28.8	27.8	27.3	26.8
95°	58.9	58.2	57.5	56.9	56.2	54.8	53.5	52.1	50.8	50.1	49.5
97.5°	85.4	84.5	83.7	82.8	82.0	81.0	80.0	78.9	77.9	77.4	77.0
100°	113.6	113.1	112.6	112.1	111.6	110.8	109.9	109.1	108.2	107.8	107.3
102.5°	147.0	146.5	146.0	145.5	145.0	143.8	142.6	141.5	140.3	139.7	139.4
105°	179.2	179.2	179.2	179.2	179.2	177.7	176.1	174.6	173.1	172.3	172.1
107.5°	216.1	215.6	215.1	214.6	214.1	213.4	212.8	212.1	211.4	211.1	211.0
110°	252.5	251.8	251.1	250.5	249.8	249.5	249.1	248.8	248.5	248.3	248.1

TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	288.9	288.0	287.2	286.3	285.5	285.5	285.5	285.5	285.5	285.5	285.4
115°	324.1	323.9	323.8	323.6	323.4	323.7	324.1	324.4	324.7	324.9	324.7
117.5°	360.6	360.6	360.6	360.6	360.6	360.9	361.3	361.6	361.9	362.1	362.0
120°	397.2	397.3	397.5	397.6	397.8	398.6	399.5	400.3	401.2	401.6	401.1
122.5°	433.8	434.3	434.8	435.3	435.8	436.1	436.5	436.8	437.1	437.3	437.0
125°	470.3	471.0	471.7	472.3	473.0	473.3	473.7	474.0	474.3	474.5	474.2
127.5°	506.1	507.1	508.2	509.2	510.2	510.5	510.9	511.2	511.5	511.7	511.2
130°	543.1	543.8	544.5	545.2	545.9	546.4	546.9	547.4	547.9	548.2	547.5
132.5°	578.2	579.1	579.9	580.8	581.6	581.9	582.3	582.6	582.9	583.1	582.4
135°	613.7	614.4	615.1	615.8	616.5	616.7	616.8	617.0	617.1	617.2	616.7
137.5°	648.0	648.9	649.7	650.6	651.4	650.9	650.4	649.9	649.4	649.1	648.7
140°	683.4	683.6	683.7	683.9	684.1	683.9	683.7	683.6	683.4	683.3	682.9
142.5°	715.3	715.4	715.6	715.7	715.9	715.6	715.2	714.9	714.6	714.4	714.0
145°	746.4	746.6	746.7	746.9	747.1	746.6	746.1	745.6	745.1	744.8	744.6
147.5°	776.7	776.7	776.7	776.7	776.7	776.2	775.7	775.2	774.7	774.4	774.1
150°	804.0	804.0	804.0	804.0	804.0	803.7	803.3	803.0	802.7	802.5	802.3
152.5°	829.6	829.3	829.0	828.6	828.3	828.1	827.9	827.8	827.6	827.5	827.3
155°	854.6	853.9	853.2	852.5	851.8	851.6	851.5	851.3	851.2	851.1	851.1
157.5°	875.8	875.1	874.4	873.8	873.1	872.9	872.7	872.6	872.4	872.3	872.4
160°	895.5	894.6	893.8	892.9	892.1	892.1	892.1	892.1	892.1	892.1	892.3
162.5°	913.7	912.8	912.0	911.1	910.3	910.1	909.9	909.8	909.6	909.5	909.8
165°	928.8	927.8	926.7	925.7	924.7	924.7	924.7	924.7	924.7	924.7	925.0
167.5°	941.7	940.7	939.6	938.6	937.6	937.4	937.3	937.1	937.0	936.9	937.2
170°	952.2	951.0	949.9	948.7	947.5	947.5	947.5	947.5	947.5	947.5	947.8
172.5°	959.9	958.9	957.9	956.9	955.9	955.9	955.9	955.9	955.9	955.9	956.2
175°	965.2	964.2	963.2	962.2	961.2	961.2	961.2	961.2	961.2	961.2	961.5
177.5°	968.3	967.3	966.2	965.2	964.2	964.2	964.2	964.2	964.2	964.2	964.5
180°	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5

TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1616.5	1616.5	1616.5	1616.5
2.5°	1582.1	1586.8	1602.4	1621.2
5°	1550.8	1563.3	1585.2	1615.0
7.5°	1516.3	1535.1	1566.4	1604.0
10°	1477.1	1503.8	1542.9	1589.9
12.5°	1434.8	1469.3	1519.4	1568.0
15°	1408.2	1442.7	1488.1	1541.4
17.5°	1356.5	1397.2	1444.2	1519.4
20°	1303.3	1348.7	1409.8	1485.0
22.5°	1262.5	1311.1	1369.1	1448.9
25°	1214.0	1264.1	1326.8	1409.8
27.5°	1162.3	1212.4	1282.9	1370.6
30°	1123.1	1171.7	1239.0	1333.0
32.5°	1076.1	1123.1	1193.6	1292.3
35°	1022.9	1076.1	1143.5	1243.7
37.5°	982.1	1030.7	1101.2	1196.7
40°	938.3	980.6	1049.5	1143.5
42.5°	891.3	938.3	997.8	1091.8
45°	847.4	881.9	943.0	1032.3
47.5°	800.4	839.6	886.6	955.5
50°	750.3	783.2	834.9	881.9
52.5°	701.8	728.4	772.2	808.3
55°	650.1	676.7	709.6	731.5
57.5°	601.5	620.3	642.2	656.3
60°	542.0	560.8	574.9	589.0
62.5°	488.7	502.8	510.7	518.5
65°	433.9	441.7	446.4	452.7
67.5°	374.4	382.2	383.8	393.2
70°	319.6	321.1	324.2	328.9
72.5°	267.9	271.0	269.4	272.6
75°	214.6	217.7	214.6	217.7
77.5°	162.9	166.0	166.0	170.7
80°	117.5	119.0	120.6	120.6
82.5°	76.8	81.5	78.3	79.9
85°	43.9	45.4	45.4	47.0
87.5°	20.4	21.9	20.4	23.5
90°	5.9	4.2	2.5	0.8
92.5°	25.8	24.8	23.8	22.8
95°	48.3	47.2	46.0	44.8
97.5°	76.1	75.3	74.4	73.6
100°	106.3	105.3	104.3	103.3
102.5°	138.9	138.4	137.9	137.4
105°	171.8	171.5	171.1	170.8
107.5°	210.8	210.7	210.5	210.3
110°	247.8	247.4	247.1	246.7

TEST NUMBER: P1011440

CATALOG NUMBER: S123DIP-B1165D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	285.2	285.1	284.9	284.7
115°	324.2	323.7	323.2	322.7
117.5°	361.9	361.7	361.6	361.4
120°	400.1	399.1	398.1	397.1
122.5°	436.3	435.6	435.0	434.3
125°	473.7	473.2	472.7	472.2
127.5°	510.2	509.2	508.2	507.2
130°	546.2	544.8	543.5	542.1
132.5°	581.1	579.7	578.4	577.0
135°	615.7	614.7	613.7	612.7
137.5°	647.8	647.0	646.1	645.3
140°	682.0	681.2	680.3	679.5
142.5°	713.1	712.3	711.4	710.6
145°	744.3	744.0	743.6	743.3
147.5°	773.4	772.7	772.1	771.4
150°	802.0	801.7	801.3	801.0
152.5°	826.8	826.3	825.8	825.3
155°	851.1	851.1	851.1	851.1
157.5°	872.6	872.7	872.9	873.1
160°	892.6	892.9	893.3	893.6
162.5°	910.3	910.8	911.3	911.8
165°	925.5	926.0	926.5	927.0
167.5°	937.9	938.6	939.2	939.9
170°	948.5	949.2	949.8	950.5
172.5°	956.9	957.6	958.2	958.9
175°	962.2	962.9	963.5	964.2
177.5°	965.2	965.9	966.5	967.2
180°	966.5	966.5	966.5	966.5

(END OF REPORT)