

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011464

Luminaire Tested: S123DIP-B340D1025UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011464
REPORT IS A COMBINATION OF REPORTS P989626 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1025UB27-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4819.0 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011464

CATALOG NUMBER: S123DIP-B340D1025UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011464

CATALOG NUMBER: S123DIP-B340D1025UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	79	76	73	62	60	58	46	45	44	32	31	30
2	85	77	71	66	75	69	64	60	54	51	48	41	39	37	28	27	26
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22
4	70	60	52	47	63	54	47	42	43	38	34	32	29	26	22	20	19
5	64	53	45	40	57	48	41	36	38	33	29	29	25	23	20	18	16
6	59	48	40	34	53	43	36	31	34	29	26	26	22	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	13
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5628	5628	5628
5°	5643	5435	5427
10°	5593	5251	5197
15°	5515	5060	4947
20°	5426	4847	4699
25°	5311	4623	4433
30°	5184	4391	4154
35°	5052	4155	3877
40°	4913	3905	3604
45°	4761	3664	3320
50°	4607	3393	3033
55°	4408	3112	2745
60°	4203	2800	2437
65°	4010	2466	2114
70°	3734	2093	1739
75°	3336	1656	1350
80°	2883	1164	956
85°	2248	627	479

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4761 cd/sqm

TEST NUMBER: P1011464

CATALOG NUMBER: S123DIP-B340D1025UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.3	1.0
10°-20°	139.2	2.9
20°-30°	205.6	4.3
30°-40°	240.1	5.0
40°-50°	241.4	5.0
50°-60°	212.1	4.4
60°-70°	157.9	3.3
70°-80°	89.9	1.9
80°-90°	28.2	0.6
90°-100°	80.3	1.7
100°-110°	243.0	5.0
110°-120°	413.6	8.6
120°-130°	544.2	11.3
130°-140°	611.7	12.7
140°-150°	601.3	12.5
150°-160°	506.3	10.5
160°-170°	337.0	7.0
170°-180°	118.0	2.4
0°-30°	394.1	8.2
0°-40°	634.2	13.2
0°-60°	1087.7	22.6
0°-90°	1363.6	28.3
90°-120°	736.9	15.3
90°-150°	2494.0	51.8
90°-180°	3455.0	71.7
0°-180°	4819.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	523	523	523	523	523	
5°	523	521	516	521	520	50
15°	498	496	491	494	492	140
25°	452	450	444	444	443	208
35°	391	388	383	380	378	245
45°	321	319	313	308	305	248
55°	243	243	237	232	230	218
65°	166	164	159	156	154	164
75°	88	86	84	82	81	94
85°	23	22	22	22	22	25
90°	1	11	24	27	29	6
95°	58	65	72	76	76	64
105°	220	222	231	231	233	236
115°	416	419	417	418	417	412
125°	609	612	610	606	602	543
135°	791	796	796	792	790	609
145°	959	961	964	963	959	599
155°	1098	1098	1099	1103	1096	506
165°	1196	1193	1193	1199	1192	337
175°	1244	1240	1240	1246	1239	118
180°	1247	1247	1247	1247	1247	

TEST NUMBER: P1011464

CATALOG NUMBER: S123DIP-B340D1025UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	522.9	522.9	522.9	522.9	522.9
2.5°	525.2	523.4	518.5	522.9	522.5
5°	523.4	521.1	516.2	520.7	519.8
7.5°	519.4	517.1	512.2	516.2	515.8
10°	514.0	511.7	505.9	509.9	509.0
12.5°	506.8	505.0	499.6	502.3	501.8
15°	498.2	496.4	490.6	494.2	491.5
17.5°	488.8	486.5	480.7	483.4	482.5
20°	478.0	475.3	469.4	471.2	469.9
22.5°	465.8	463.1	457.3	458.6	456.8
25°	452.4	449.7	443.8	444.3	442.9
27.5°	438.4	435.7	429.4	429.9	428.5
30°	423.1	420.9	414.6	414.6	411.4
32.5°	407.8	404.7	400.2	397.0	395.7
35°	391.2	388.5	382.7	380.0	377.7
37.5°	374.6	371.0	365.1	362.0	360.6
40°	357.0	354.3	348.0	344.4	342.6
42.5°	339.5	336.3	330.0	326.4	324.6
45°	320.6	318.8	313.0	307.6	305.3
47.5°	302.2	299.5	294.1	288.7	286.9
50°	283.3	281.0	275.2	270.2	267.5
52.5°	263.5	262.1	255.9	251.8	249.1
55°	243.3	242.8	237.0	232.0	229.8
57.5°	224.4	222.6	218.1	213.6	210.9
60°	203.7	203.2	197.8	193.8	191.6
62.5°	185.3	183.9	178.5	174.5	173.1
65°	165.9	163.7	159.2	155.6	154.2
67.5°	145.2	143.4	139.8	136.7	134.9
70°	126.8	124.1	121.4	118.3	116.0
72.5°	107.5	105.7	102.5	99.8	98.9
75°	87.7	85.9	84.5	82.3	80.9
77.5°	70.1	69.2	67.4	65.6	65.6
80°	53.1	51.7	50.8	50.4	50.4
82.5°	36.4	36.4	36.4	35.5	35.1
85°	23.4	22.5	22.5	21.6	21.6
87.5°	11.7	10.3	9.9	9.4	9.4
90°	1.0	10.8	23.5	27.4	29.4
92.5°	29.4	35.3	41.1	44.1	42.1
95°	57.8	64.7	72.5	76.4	76.4
97.5°	95.0	99.9	105.8	110.7	109.7
100°	133.2	139.1	144.0	146.9	148.9
102.5°	177.3	180.2	187.1	190.0	189.1
105°	220.4	222.4	231.2	231.2	233.1
107.5°	271.4	272.3	276.3	279.2	278.2
110°	318.4	320.3	322.3	326.2	324.3

TEST NUMBER: P1011464

CATALOG NUMBER: S123DIP-B340D1025UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	367.4	368.3	368.3	373.2	373.2
115°	416.3	419.3	417.3	418.3	417.3
117.5°	466.3	467.3	465.3	465.3	462.4
120°	512.3	518.2	513.3	512.3	510.4
122.5°	560.3	564.3	562.3	559.4	556.4
125°	609.3	612.3	610.3	606.4	602.5
127.5°	654.4	660.3	658.3	652.4	648.5
130°	699.4	707.3	704.3	700.4	693.6
132.5°	744.5	752.3	750.4	745.5	740.6
135°	790.6	796.4	795.5	791.5	789.6
137.5°	832.7	837.6	840.5	835.6	832.7
140°	876.8	881.7	882.6	881.7	874.8
142.5°	916.9	921.8	923.8	922.8	917.9
145°	959.0	961.0	963.9	963.0	959.0
147.5°	995.3	999.2	1002.2	1002.2	996.3
150°	1033.5	1035.5	1037.4	1037.4	1031.5
152.5°	1064.8	1067.8	1068.8	1070.7	1065.8
155°	1098.2	1098.2	1099.1	1103.1	1096.2
157.5°	1126.6	1125.6	1126.6	1130.5	1124.6
160°	1153.0	1151.1	1151.1	1156.0	1152.0
162.5°	1176.5	1173.6	1174.6	1179.5	1172.6
165°	1196.1	1193.2	1193.2	1199.1	1192.2
167.5°	1212.8	1208.9	1209.8	1215.7	1209.8
170°	1226.5	1222.6	1222.6	1229.4	1222.6
172.5°	1237.3	1233.3	1233.3	1239.2	1232.4
175°	1244.1	1240.2	1240.2	1246.1	1239.2
177.5°	1248.0	1244.1	1244.1	1250.0	1243.1
180°	1247.1	1247.1	1247.1	1247.1	1247.1

(END OF REPORT)