

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011185

Luminaire Tested: S123DIP-B1000D585UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011185
REPORT IS A COMBINATION OF REPORTS P989248 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D585UB40-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6078.0 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011185

CATALOG NUMBER: S123DIP-B1000D585UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011185

CATALOG NUMBER: S123DIP-B1000D585UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	102	97	93	89	96	92	88	85	81	79	76	72	70	68	63	62	61
2	92	85	78	73	87	80	74	70	71	67	63	63	60	57	56	53	51
3	84	75	67	61	79	70	64	58	63	57	53	56	52	48	49	46	43
4	77	66	58	52	72	63	55	49	56	50	45	50	45	41	44	40	37
5	71	59	50	44	67	56	48	43	50	44	39	45	40	36	40	36	33
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	29
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	25
8	56	44	36	30	53	41	34	29	38	31	27	34	29	25	30	26	23
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16841	16841	16841
5°	16884	16260	16236
10°	16733	15710	15549
15°	16500	15138	14799
20°	16234	14502	14058
25°	15889	13832	13264
30°	15511	13138	12430
35°	15115	12429	11601
40°	14701	11685	10784
45°	14245	10959	9933
50°	13783	10151	9078
55°	13187	9310	8211
60°	12575	8380	7288
65°	12000	7375	6326
70°	11173	6261	5204
75°	9978	4958	4041
80°	8616	3484	2858
85°	6724	1874	1432

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14245 cd/sqm

TEST NUMBER: P1011185

CATALOG NUMBER: S123DIP-B1000D585UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.5	2.4
10°-20°	416.5	6.9
20°-30°	615.1	10.1
30°-40°	718.4	11.8
40°-50°	722.2	11.9
50°-60°	634.4	10.4
60°-70°	472.5	7.8
70°-80°	268.9	4.4
80°-90°	78.0	1.3
90°-100°	46.6	0.8
100°-110°	141.0	2.3
110°-120°	240.0	3.9
120°-130°	315.7	5.2
130°-140°	354.8	5.8
140°-150°	348.8	5.7
150°-160°	293.7	4.8
160°-170°	195.5	3.2
170°-180°	68.5	1.1
0°-30°	1179.1	19.4
0°-40°	1897.5	31.2
0°-60°	3254.2	53.5
0°-90°	4073.5	67.0
90°-120°	427.5	7.0
90°-150°	1446.8	23.8
90°-180°	2004.0	33.0
0°-180°	6078.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1565	1565	1565	1565	1565	
5°	1566	1559	1544	1558	1555	149
15°	1491	1485	1468	1478	1470	420
25°	1353	1345	1328	1329	1325	623
35°	1170	1162	1145	1137	1130	732
45°	959	954	936	920	914	741
55°	728	726	709	694	688	652
65°	496	490	476	466	461	490
75°	262	257	253	246	242	280
85°	70	67	67	65	65	75
90°	1	6	14	16	17	7
95°	34	38	42	44	44	37
105°	128	129	134	134	135	137
115°	242	243	242	243	242	239
125°	354	355	354	352	350	315
135°	459	462	461	459	458	353
145°	556	558	559	559	556	347
155°	637	637	638	640	636	293
165°	694	692	692	696	692	196
175°	722	719	719	723	719	69
180°	723	723	723	723	723	

TEST NUMBER: P1011185

CATALOG NUMBER: S123DIP-B1000D585UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1564.6	1564.6	1564.6	1564.6	1564.6
2.5°	1571.3	1566.0	1551.2	1564.6	1563.3
5°	1566.0	1559.2	1544.4	1557.9	1555.2
7.5°	1553.9	1547.1	1532.3	1544.4	1543.1
10°	1537.7	1531.0	1513.5	1525.6	1522.9
12.5°	1516.2	1510.8	1494.7	1502.7	1501.4
15°	1490.6	1485.2	1467.8	1478.5	1470.4
17.5°	1462.4	1455.6	1438.2	1446.2	1443.5
20°	1430.1	1422.0	1404.5	1409.9	1405.9
22.5°	1393.8	1385.7	1368.2	1372.2	1366.9
25°	1353.4	1345.3	1327.8	1329.2	1325.1
27.5°	1311.7	1303.6	1284.8	1286.1	1282.1
30°	1266.0	1259.2	1240.4	1240.4	1231.0
32.5°	1220.2	1210.8	1197.3	1187.9	1183.9
35°	1170.4	1162.4	1144.9	1136.8	1130.1
37.5°	1120.7	1109.9	1092.4	1083.0	1079.0
40°	1068.2	1060.1	1041.3	1030.5	1025.1
42.5°	1015.7	1006.3	987.5	976.7	971.3
45°	959.2	953.8	936.3	920.2	913.5
47.5°	904.1	896.0	879.8	863.7	858.3
50°	847.6	840.8	823.3	808.5	800.5
52.5°	788.4	784.3	765.5	753.4	745.3
55°	727.8	726.5	709.0	694.2	687.5
57.5°	671.3	665.9	652.5	639.0	631.0
60°	609.4	608.1	591.9	579.8	573.1
62.5°	554.3	550.2	534.1	522.0	518.0
65°	496.4	489.7	476.2	465.5	461.4
67.5°	434.5	429.2	418.4	409.0	403.6
70°	379.4	371.3	363.2	353.8	347.1
72.5°	321.5	316.2	306.7	298.7	296.0
75°	262.3	257.0	252.9	246.2	242.2
77.5°	209.9	207.2	201.8	196.4	196.4
80°	158.7	154.7	152.0	150.7	150.7
82.5°	109.0	109.0	109.0	106.3	104.9
85°	70.0	67.3	67.3	64.6	64.6
87.5°	35.0	30.9	29.6	28.3	28.3
90°	0.6	6.3	13.6	15.9	17.0
92.5°	17.0	20.5	23.9	25.6	24.4
95°	33.5	37.5	42.1	44.3	44.3
97.5°	55.1	58.0	61.4	64.2	63.6
100°	77.3	80.7	83.5	85.2	86.4
102.5°	102.9	104.6	108.5	110.2	109.7
105°	127.9	129.0	134.1	134.1	135.3
107.5°	157.4	158.0	160.3	162.0	161.4
110°	184.7	185.8	187.0	189.2	188.1



TEST NUMBER: P1011185

CATALOG NUMBER: S123DIP-B1000D585UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.1	213.7	213.7	216.5	216.5
115°	241.5	243.2	242.1	242.7	242.1
117.5°	270.5	271.1	269.9	269.9	268.2
120°	297.2	300.6	297.8	297.2	296.1
122.5°	325.1	327.3	326.2	324.5	322.8
125°	353.5	355.2	354.0	351.8	349.5
127.5°	379.6	383.0	381.9	378.5	376.2
130°	405.8	410.3	408.6	406.3	402.3
132.5°	431.9	436.4	435.3	432.5	429.6
135°	458.6	462.0	461.4	459.2	458.0
137.5°	483.0	485.9	487.6	484.7	483.0
140°	508.6	511.5	512.0	511.5	507.5
142.5°	531.9	534.8	535.9	535.3	532.5
145°	556.3	557.5	559.2	558.6	556.3
147.5°	577.4	579.6	581.4	581.4	577.9
150°	599.5	600.7	601.8	601.8	598.4
152.5°	617.7	619.4	620.0	621.1	618.3
155°	637.0	637.0	637.6	639.9	635.9
157.5°	653.5	653.0	653.5	655.8	652.4
160°	668.9	667.7	667.7	670.6	668.3
162.5°	682.5	680.8	681.4	684.2	680.2
165°	693.9	692.2	692.2	695.6	691.6
167.5°	703.5	701.3	701.8	705.2	701.8
170°	711.5	709.2	709.2	713.2	709.2
172.5°	717.7	715.5	715.5	718.9	714.9
175°	721.7	719.4	719.4	722.9	718.9
177.5°	724.0	721.7	721.7	725.1	721.1
180°	723.4	723.4	723.4	723.4	723.4

(END OF REPORT)