

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011202

Luminaire Tested: S123DIP-B1000D805UB27-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011202
REPORT IS A COMBINATION OF REPORTS P989265 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D805UB27-4F0-XX-W2A-F
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7168.0 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011202

CATALOG NUMBER: S123DIP-B1000D805UB27-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1011202

CATALOG NUMBER: S123DIP-B1000D805UB27-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	99	95	91	87	92	88	85	82	76	74	71	65	63	62	55	54	52
2	90	83	77	71	84	77	72	67	67	63	59	57	54	51	48	46	44
3	82	73	65	59	76	68	61	56	59	54	50	51	47	43	43	40	38
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32
5	69	57	49	43	64	54	46	41	47	41	37	40	36	32	34	31	28
6	64	52	43	37	59	48	41	36	42	36	32	37	32	28	31	28	25
7	59	47	38	33	55	44	36	31	38	32	28	33	29	25	29	25	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	23	20
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	21	18
10	48	35	28	23	44	33	27	22	30	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16792	16792	16792
5°	16833	16212	16188
10°	16684	15663	15503
15°	16451	15092	14756
20°	16186	14460	14016
25°	15842	13791	13225
30°	15465	13098	12392
35°	15071	12392	11566
40°	14657	11650	10753
45°	14204	10928	9903
50°	13742	10122	9050
55°	13149	9282	8186
60°	12537	8356	7267
65°	11966	7354	6308
70°	11140	6244	5189
75°	9951	4944	4027
80°	8594	3475	2849
85°	6705	1869	1427

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14204 cd/sqm

TEST NUMBER: P1011202

CATALOG NUMBER: S123DIP-B1000D805UB27-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.1	2.1
10°-20°	415.3	5.8
20°-30°	613.3	8.6
30°-40°	716.3	10.0
40°-50°	720.1	10.0
50°-60°	632.6	8.8
60°-70°	471.1	6.6
70°-80°	268.1	3.7
80°-90°	78.3	1.1
90°-100°	35.9	0.5
100°-110°	173.7	2.4
110°-120°	425.7	5.9
120°-130°	540.4	7.5
130°-140°	577.3	8.1
140°-150°	539.8	7.5
150°-160°	435.4	6.1
160°-170°	281.0	3.9
170°-180°	96.8	1.4
0°-30°	1175.6	16.4
0°-40°	1891.9	26.4
0°-60°	3244.6	45.3
0°-90°	4062.1	56.7
90°-120°	635.3	8.9
90°-150°	2292.7	32.0
90°-180°	3106.0	43.3
0°-180°	7168.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1560	1560	1560	1560	1560	
5°	1561	1555	1540	1553	1551	148
15°	1486	1481	1463	1474	1466	419
25°	1349	1341	1324	1325	1321	622
35°	1167	1159	1142	1134	1127	730
45°	956	951	934	918	911	738
55°	726	724	707	692	685	650
65°	495	488	475	464	460	488
75°	262	256	252	246	241	279
85°	70	67	67	64	64	75
90°	1	8	18	21	23	7
95°	46	15	24	29	29	55
105°	226	234	166	32	33	239
115°	423	428	434	442	445	418
125°	596	602	606	607	609	533
135°	742	747	750	752	750	572
145°	857	862	864	865	865	536
155°	944	942	943	947	942	435
165°	995	993	992	998	993	281
175°	1019	1015	1016	1021	1015	97
180°	1019	1019	1019	1019	1019	

TEST NUMBER: P1011202

CATALOG NUMBER: S123DIP-B1000D805UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1560.0	1560.0	1560.0	1560.0	1560.0
2.5°	1566.7	1561.3	1546.6	1560.0	1558.7
5°	1561.3	1554.6	1539.9	1553.3	1550.6
7.5°	1549.3	1542.6	1527.8	1539.9	1538.5
10°	1533.2	1526.5	1509.0	1521.1	1518.4
12.5°	1511.7	1506.3	1490.3	1498.3	1497.0
15°	1486.2	1480.9	1463.4	1474.2	1466.1
17.5°	1458.1	1451.4	1433.9	1442.0	1439.3
20°	1425.9	1417.8	1400.4	1405.7	1401.7
22.5°	1389.7	1381.6	1364.2	1368.2	1362.8
25°	1349.4	1341.4	1323.9	1325.3	1321.2
27.5°	1307.8	1299.8	1281.0	1282.3	1278.3
30°	1262.2	1255.5	1236.7	1236.7	1227.3
32.5°	1216.6	1207.2	1193.8	1184.4	1180.4
35°	1167.0	1158.9	1141.5	1133.5	1126.7
37.5°	1117.4	1106.6	1089.2	1079.8	1075.8
40°	1065.0	1057.0	1038.2	1027.5	1022.1
42.5°	1012.7	1003.3	984.6	973.8	968.5
45°	956.4	951.0	933.6	917.5	910.8
47.5°	901.4	893.3	877.3	861.2	855.8
50°	845.1	838.4	820.9	806.2	798.1
52.5°	786.0	782.0	763.2	751.2	743.1
55°	725.7	724.3	706.9	692.1	685.4
57.5°	669.3	664.0	650.6	637.1	629.1
60°	607.6	606.3	590.2	578.1	571.4
62.5°	552.6	548.6	532.5	520.4	516.4
65°	495.0	488.3	474.8	464.1	460.1
67.5°	433.3	427.9	417.2	407.8	402.4
70°	378.3	370.2	362.2	352.8	346.1
72.5°	320.6	315.2	305.8	297.8	295.1
75°	261.6	256.2	252.2	245.5	241.4
77.5°	209.3	206.6	201.2	195.8	195.8
80°	158.3	154.3	151.6	150.2	150.2
82.5°	108.7	108.7	108.7	106.0	104.6
85°	69.8	67.1	67.1	64.4	64.4
87.5°	34.9	30.9	29.5	28.2	28.2
90°	0.8	8.3	18.2	21.2	22.7
92.5°	17.4	12.9	19.7	25.0	25.7
95°	46.2	15.1	23.5	28.8	28.8
97.5°	84.0	62.8	24.2	30.3	31.0
100°	127.9	143.1	25.0	31.0	31.8
102.5°	177.9	187.7	56.0	31.0	32.5
105°	225.6	233.9	165.8	31.8	33.3
107.5°	276.3	283.1	294.4	177.9	78.7
110°	327.0	333.0	341.4	316.4	208.2

TEST NUMBER: P1011202

CATALOG NUMBER: S123DIP-B1000D805UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.4	380.7	389.1	395.9	394.4
115°	423.1	427.7	434.5	442.0	445.1
117.5°	470.1	475.3	479.1	485.2	485.9
120°	513.2	520.0	522.3	528.3	528.3
122.5°	557.1	562.4	565.4	569.2	570.0
125°	596.5	602.5	605.5	607.1	608.6
127.5°	635.8	641.9	645.7	647.9	646.4
130°	672.2	678.2	681.2	684.3	682.7
132.5°	707.0	713.0	715.3	718.3	716.1
135°	742.5	747.1	750.1	752.4	750.1
137.5°	772.8	778.9	780.4	784.2	782.7
140°	803.1	807.6	809.9	812.9	811.4
142.5°	831.1	835.6	837.9	840.2	837.9
145°	856.8	862.1	863.7	865.2	865.2
147.5°	881.8	885.6	887.1	888.6	884.8
150°	904.5	906.8	908.3	909.8	907.6
152.5°	925.0	925.7	926.5	929.5	925.7
155°	943.9	942.4	943.1	946.9	942.4
157.5°	959.0	959.0	958.3	962.8	956.8
160°	972.6	971.9	971.1	975.7	970.4
162.5°	985.5	983.2	982.5	987.8	983.2
165°	995.4	993.1	992.3	998.4	993.1
167.5°	1003.7	1000.7	1000.7	1006.7	1000.7
170°	1010.5	1007.5	1007.5	1013.5	1007.5
172.5°	1015.0	1011.3	1012.0	1018.1	1011.3
175°	1018.8	1015.0	1015.8	1021.1	1015.0
177.5°	1020.3	1016.6	1017.3	1023.4	1015.8
180°	1018.8	1018.8	1018.8	1018.8	1018.8

(END OF REPORT)