

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011491

Luminaire Tested: S123DIP-B340D1025UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011491
REPORT IS A COMBINATION OF REPORTS P989668 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1025UB40-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4834.0 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011491

CATALOG NUMBER: S123DIP-B340D1025UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011491

CATALOG NUMBER: S123DIP-B340D1025UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	79	76	73	62	60	58	46	45	44	32	31	30
2	85	77	71	66	75	69	64	60	54	51	48	41	39	37	28	27	26
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22
4	70	60	52	47	63	54	47	42	43	38	34	32	29	26	22	20	19
5	64	53	45	40	57	48	41	36	38	33	29	29	25	23	20	18	16
6	59	48	40	34	53	43	36	31	34	29	25	26	22	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	13
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5646	5646	5646
5°	5659	5450	5442
10°	5610	5266	5212
15°	5531	5074	4961
20°	5442	4861	4713
25°	5326	4637	4446
30°	5200	4404	4166
35°	5066	4167	3888
40°	4928	3917	3615
45°	4775	3674	3329
50°	4620	3403	3043
55°	4421	3121	2752
60°	4216	2809	2443
65°	4022	2472	2121
70°	3746	2100	1745
75°	3344	1662	1355
80°	2888	1169	958
85°	2257	627	479

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4775 cd/sqm

TEST NUMBER: P1011491

CATALOG NUMBER: S123DIP-B340D1025UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.4	1.0
10°-20°	139.6	2.9
20°-30°	206.2	4.3
30°-40°	240.8	5.0
40°-50°	242.1	5.0
50°-60°	212.7	4.4
60°-70°	158.4	3.3
70°-80°	90.1	1.9
80°-90°	28.3	0.6
90°-100°	80.5	1.7
100°-110°	243.7	5.0
110°-120°	415.0	8.6
120°-130°	545.9	11.3
130°-140°	613.6	12.7
140°-150°	603.2	12.5
150°-160°	507.9	10.5
160°-170°	338.1	7.0
170°-180°	118.4	2.4
0°-30°	395.3	8.2
0°-40°	636.1	13.2
0°-60°	1090.8	22.6
0°-90°	1367.6	28.3
90°-120°	739.2	15.3
90°-150°	2502.0	51.8
90°-180°	3466.0	71.7
0°-180°	4834.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	524	524	524	524	524	
5°	525	523	518	522	521	50
15°	500	498	492	496	493	141
25°	454	451	445	446	444	209
35°	392	390	384	381	379	245
45°	322	320	314	308	306	248
55°	244	244	238	233	230	219
65°	166	164	160	156	155	164
75°	88	86	85	82	81	94
85°	24	22	22	22	22	25
90°	1	11	24	28	30	6
95°	58	65	73	77	77	64
105°	221	223	232	232	234	237
115°	418	421	419	420	419	413
125°	611	614	612	608	604	545
135°	793	799	798	794	792	611
145°	962	964	967	966	962	601
155°	1102	1102	1103	1107	1100	507
165°	1200	1197	1197	1203	1196	338
175°	1248	1244	1244	1250	1243	119
180°	1251	1251	1251	1251	1251	

TEST NUMBER: P1011491

CATALOG NUMBER: S123DIP-B340D1025UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	524.5	524.5	524.5	524.5	524.5
2.5°	526.7	524.9	520.0	524.5	524.0
5°	524.9	522.7	517.7	522.2	521.3
7.5°	520.9	518.6	513.7	517.7	517.3
10°	515.5	513.2	507.3	511.4	510.5
12.5°	508.2	506.4	501.0	503.7	503.3
15°	499.7	497.9	492.0	495.6	492.9
17.5°	490.2	488.0	482.1	484.8	483.9
20°	479.4	476.7	470.8	472.6	471.3
22.5°	467.2	464.5	458.6	460.0	458.2
25°	453.7	451.0	445.1	445.6	444.2
27.5°	439.7	437.0	430.7	431.1	429.8
30°	424.4	422.1	415.8	415.8	412.6
32.5°	409.0	405.9	401.4	398.2	396.9
35°	392.3	389.6	383.8	381.1	378.8
37.5°	375.7	372.1	366.2	363.0	361.7
40°	358.1	355.4	349.1	345.4	343.6
42.5°	340.5	337.3	331.0	327.4	325.6
45°	321.5	319.7	313.9	308.5	306.2
47.5°	303.1	300.3	294.9	289.5	287.7
50°	284.1	281.9	276.0	271.0	268.3
52.5°	264.3	262.9	256.6	252.5	249.8
55°	244.0	243.5	237.7	232.7	230.4
57.5°	225.0	223.2	218.7	214.2	211.5
60°	204.3	203.8	198.4	194.4	192.1
62.5°	185.8	184.4	179.0	175.0	173.6
65°	166.4	164.2	159.6	156.0	154.7
67.5°	145.7	143.9	140.3	137.1	135.3
70°	127.2	124.5	121.8	118.6	116.4
72.5°	107.8	106.0	102.8	100.1	99.2
75°	87.9	86.1	84.8	82.5	81.2
77.5°	70.4	69.5	67.6	65.8	65.8
80°	53.2	51.9	51.0	50.5	50.5
82.5°	36.5	36.5	36.5	35.6	35.2
85°	23.5	22.5	22.5	21.6	21.6
87.5°	11.7	10.4	9.9	9.5	9.5
90°	1.0	10.8	23.6	27.5	29.5
92.5°	29.5	35.4	41.3	44.2	42.3
95°	58.0	64.9	72.7	76.7	76.7
97.5°	95.3	100.2	106.1	111.0	110.1
100°	133.7	139.5	144.5	147.4	149.4
102.5°	177.9	180.8	187.7	190.7	189.7
105°	221.1	223.1	231.9	231.9	233.9
107.5°	272.2	273.2	277.1	280.1	279.1
110°	319.4	321.4	323.3	327.3	325.3

TEST NUMBER: P1011491

CATALOG NUMBER: S123DIP-B340D1025UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	368.5	369.5	369.5	374.4	374.4
115°	417.7	420.6	418.6	419.6	418.6
117.5°	467.8	468.8	466.8	466.8	463.9
120°	514.0	519.9	515.0	514.0	512.0
122.5°	562.1	566.1	564.1	561.1	558.2
125°	611.3	614.2	612.2	608.3	604.4
127.5°	656.5	662.4	660.4	654.5	650.6
130°	701.7	709.5	706.6	702.7	695.8
132.5°	746.9	754.7	752.8	747.9	742.9
135°	793.1	799.0	798.0	794.1	792.1
137.5°	835.3	840.2	843.2	838.3	835.3
140°	879.5	884.5	885.4	884.5	877.6
142.5°	919.8	924.8	926.7	925.7	920.8
145°	962.1	964.1	967.0	966.0	962.1
147.5°	998.5	1002.4	1005.3	1005.3	999.4
150°	1036.8	1038.8	1040.7	1040.7	1034.8
152.5°	1068.2	1071.2	1072.2	1074.1	1069.2
155°	1101.6	1101.6	1102.6	1106.6	1099.7
157.5°	1130.1	1129.2	1130.1	1134.1	1128.2
160°	1156.7	1154.7	1154.7	1159.6	1155.7
162.5°	1180.3	1177.3	1178.3	1183.2	1176.3
165°	1199.9	1197.0	1197.0	1202.9	1196.0
167.5°	1216.6	1212.7	1213.7	1219.6	1213.7
170°	1230.4	1226.5	1226.5	1233.3	1226.5
172.5°	1241.2	1237.3	1237.3	1243.2	1236.3
175°	1248.1	1244.1	1244.1	1250.0	1243.2
177.5°	1252.0	1248.1	1248.1	1254.0	1247.1
180°	1251.0	1251.0	1251.0	1251.0	1251.0

(END OF REPORT)