

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011207

Luminaire Tested: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011207
REPORT IS A COMBINATION OF REPORTS P989285 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D805UB30-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7053.0 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56
2	92	84	78	73	85	79	74	69	69	65	62	60	57	54	52	49	47
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41
4	77	66	58	52	71	62	55	50	55	49	45	48	43	40	41	38	35
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	34	31
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27
7	60	48	40	34	56	45	38	33	40	34	30	35	31	27	31	27	24
8	56	44	36	30	52	41	34	29	37	31	27	32	28	24	28	25	22
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20
10	49	37	29	24	46	35	28	24	31	25	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15029	15029	15029	15029
5°	15039	17316	15082	12923
10°	14943	20955	14958	11285
15°	14737	24851	14856	10158
20°	14559	28611	14590	9348
25°	14294	29332	14326	8925
30°	14106	24234	14106	8647
35°	13872	16208	13786	8402
40°	13592	11700	13425	8027
45°	13241	9267	12860	7561
50°	12386	7870	11945	7103
55°	11448	6916	10982	6593
60°	10497	6022	9937	6056
65°	9452	5156	8995	5341
70°	8366	4281	7810	4503
75°	7155	3228	6691	3475
80°	5657	2154	5217	2283
85°	3900	989	3122	900

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 24237 cd/sqm

TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.3	1.9
10°-20°	441.0	6.3
20°-30°	742.1	10.5
30°-40°	838.6	11.9
40°-50°	751.1	10.6
50°-60°	606.3	8.6
60°-70°	422.5	6.0
70°-80°	221.8	3.1
80°-90°	55.2	0.8
90°-100°	204.7	2.9
100°-110°	599.2	8.5
110°-120°	585.1	8.3
120°-130°	466.0	6.6
130°-140°	367.6	5.2
140°-150°	274.3	3.9
150°-160°	191.2	2.7
160°-170°	112.3	1.6
170°-180°	36.5	0.5
0°-30°	1320.4	18.7
0°-40°	2159.1	30.6
0°-60°	3516.5	49.9
0°-90°	4216.1	59.8
90°-120°	1388.9	19.7
90°-150°	2496.8	35.4
90°-180°	2837.0	40.2
0°-180°	7053.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1396	1396	1396	1396	1396	
5°	1395	1659	1399	1238	1395	132
15°	1331	2469	1342	1009	1331	376
25°	1218	2930	1220	892	1218	562
35°	1074	1579	1068	818	1074	672
45°	892	852	866	695	892	682
55°	632	579	606	552	632	566
65°	391	376	372	390	391	389
75°	188	194	176	208	188	202
85°	41	45	32	41	41	47
90°	2	22	2	22	2	5
95°	26	89	26	89	26	28
105°	89	971	89	971	89	94
115°	156	1181	156	1181	156	155
125°	218	931	218	931	218	193
135°	255	755	255	755	255	197
145°	291	590	291	590	291	182
155°	331	489	331	489	331	152
165°	361	427	361	427	361	102
175°	376	384	376	384	376	36
180°	377	377	377	377	377	

TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1400.3	1411.1	1416.5	1424.6	1432.7	1444.9	1449.0	1455.7	1453.0	1458.4	1461.2
5°	1394.9	1413.8	1430.0	1450.3	1469.3	1482.8	1496.3	1518.0	1534.2	1536.9	1549.1
7.5°	1385.4	1412.4	1440.9	1469.3	1505.8	1527.4	1551.8	1581.6	1605.9	1645.2	1660.0
10°	1373.2	1411.1	1451.7	1490.9	1541.0	1574.8	1604.6	1654.6	1704.7	1745.3	1783.2
12.5°	1354.3	1401.6	1454.4	1512.6	1577.5	1616.7	1657.3	1723.6	1799.4	1861.6	1902.2
15°	1331.3	1390.8	1458.4	1520.7	1592.4	1665.4	1708.7	1783.2	1891.4	1949.6	2053.7
17.5°	1312.3	1373.2	1440.9	1538.3	1635.7	1708.7	1739.9	1876.5	1950.9	2048.3	2166.0
20°	1282.6	1359.7	1446.3	1543.7	1669.5	1714.2	1777.7	1915.7	2007.7	2134.9	2279.7
22.5°	1251.5	1334.0	1438.2	1539.6	1680.3	1727.7	1814.3	1923.9	2070.0	2195.8	2355.4
25°	1217.6	1306.9	1412.4	1532.9	1670.9	1739.9	1821.0	1956.3	2114.6	2272.9	2420.4
27.5°	1183.8	1281.2	1390.8	1511.2	1645.2	1726.3	1807.5	1948.2	2151.1	2323.0	2511.0
30°	1151.3	1248.7	1358.3	1481.4	1622.2	1700.6	1777.7	1953.6	2179.6	2373.0	2562.4
32.5°	1116.2	1216.3	1331.3	1434.1	1576.2	1660.0	1746.6	1953.6	2197.1	2402.8	2576.0
35°	1074.2	1177.0	1275.8	1378.6	1519.3	1612.7	1710.1	1940.1	2213.4	2412.3	2519.1
37.5°	1033.6	1124.3	1209.5	1309.6	1457.1	1557.2	1669.5	1923.9	2205.3	2371.7	2401.4
40°	987.6	1078.3	1147.3	1240.6	1396.2	1512.6	1626.2	1902.2	2170.1	2275.6	2189.0
42.5°	943.0	1014.7	1074.2	1164.9	1334.0	1447.6	1570.7	1863.0	2101.1	2122.7	1927.9
45°	891.6	943.0	995.7	1098.6	1266.3	1382.7	1519.3	1806.1	1990.1	1927.9	1681.7
47.5°	825.3	871.3	929.5	1024.2	1194.6	1315.0	1444.9	1733.1	1829.1	1699.3	1430.0
50°	761.7	800.9	855.0	947.0	1118.9	1236.6	1374.6	1618.1	1665.4	1461.2	1232.5
52.5°	698.1	727.9	780.6	872.6	1044.5	1158.1	1283.9	1500.4	1473.3	1254.2	1051.2
55°	631.8	657.5	707.6	798.2	957.9	1066.1	1186.5	1355.6	1285.3	1076.9	914.6
57.5°	566.9	593.9	645.3	721.1	871.3	976.8	1072.9	1205.5	1099.9	933.5	790.1
60°	508.7	531.7	570.9	645.3	782.0	867.2	955.2	1045.8	957.9	796.9	687.3
62.5°	447.8	469.5	506.0	573.6	691.3	767.1	837.5	911.9	814.5	696.8	599.3
65°	391.0	408.6	442.4	504.6	600.7	662.9	719.8	771.2	692.7	584.5	511.4
67.5°	339.6	354.5	382.9	438.3	519.5	564.2	610.2	653.5	587.2	500.6	438.3
70°	284.1	296.3	322.0	362.6	427.5	473.5	507.3	539.8	480.3	411.3	369.3
72.5°	235.4	247.6	263.8	305.8	350.4	378.8	415.3	432.9	399.1	342.3	300.3
75°	188.1	197.5	212.4	239.5	281.4	300.3	323.3	336.9	305.8	267.9	242.2
77.5°	147.5	151.5	162.4	181.3	209.7	231.3	248.9	257.1	235.4	211.1	189.4
80°	104.2	109.6	117.7	133.9	155.6	162.4	173.2	182.6	169.1	147.5	133.9
82.5°	69.0	75.8	79.8	86.6	100.1	108.2	110.9	119.1	106.9	98.8	93.4
85°	40.6	43.3	44.6	48.7	55.5	59.5	63.6	64.9	62.2	60.9	55.5
87.5°	20.3	20.3	20.3	23.0	24.4	27.1	28.4	28.4	28.4	27.1	25.7
90°	1.5	3.1	4.6	6.9	8.4	9.2	9.9	12.2	14.5	16.8	19.1
92.5°	11.5	16.8	24.4	31.3	38.9	45.8	52.7	77.1	117.6	157.3	142.0
95°	26.0	28.2	36.6	49.6	69.5	84.4	99.2	164.1	277.9	403.1	452.7
97.5°	41.2	42.0	48.9	60.3	80.2	96.6	113.0	177.1	309.2	519.9	696.3
100°	56.5	57.3	62.6	73.3	91.6	106.5	121.4	174.8	287.8	488.6	723.0
102.5°	72.5	74.1	78.6	88.6	104.6	118.0	131.3	177.9	269.5	442.8	673.4
105°	88.6	90.9	95.4	104.6	119.1	131.0	142.8	184.0	262.6	406.9	613.8
107.5°	105.4	107.6	112.2	121.4	135.1	146.2	157.3	193.9	261.1	381.0	561.1
110°	123.7	126.0	129.8	138.2	151.2	161.8	172.5	206.9	264.9	367.2	517.6

TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	140.5	142.8	146.6	155.0	168.0	178.3	188.6	219.9	272.6	359.6	488.6
115°	156.5	159.6	164.1	171.8	184.8	195.1	205.4	234.4	280.9	358.8	469.5
117.5°	172.5	176.4	180.2	187.0	201.6	211.1	220.6	249.6	291.6	359.6	456.5
120°	189.3	191.6	195.4	203.1	217.6	227.2	236.7	264.2	303.9	362.6	448.1
122.5°	203.8	206.1	209.9	218.3	232.1	242.4	252.7	279.4	315.3	368.0	442.8
125°	217.6	219.1	223.7	232.1	246.6	256.9	267.2	293.9	327.5	373.3	438.2
127.5°	228.3	230.6	235.9	244.3	260.3	270.6	280.9	306.9	337.4	379.4	435.9
130°	238.2	240.5	247.4	256.5	272.6	282.9	293.2	318.4	347.4	385.5	433.6
132.5°	245.8	248.9	256.5	268.0	284.0	294.0	303.9	328.3	356.5	390.1	432.9
135°	255.0	258.0	266.4	277.9	293.9	304.2	314.5	338.2	364.2	394.7	432.1
137.5°	263.4	266.4	274.8	287.1	303.1	312.6	322.2	345.1	370.3	397.8	430.6
140°	271.8	275.6	283.2	295.5	310.7	320.2	329.8	351.9	374.9	400.8	429.8
142.5°	280.9	284.0	292.4	303.1	318.4	327.2	335.9	357.3	379.4	403.1	428.3
145°	290.9	293.2	300.0	311.5	324.5	333.2	342.0	361.9	382.5	403.9	426.8
147.5°	300.8	302.3	309.2	319.1	332.1	339.8	347.4	365.7	384.8	403.9	424.5
150°	310.7	311.5	317.6	327.5	338.2	345.0	351.9	369.5	385.5	403.9	421.4
152.5°	320.6	320.6	326.8	335.2	344.3	350.8	357.3	371.8	387.1	401.6	417.6
155°	330.6	330.6	335.2	342.8	351.2	356.5	361.9	374.9	387.1	400.0	413.0
157.5°	338.2	339.0	342.8	349.7	357.3	361.5	365.7	376.4	387.8	397.8	409.2
160°	347.4	347.4	350.4	356.5	361.9	365.7	369.5	378.7	387.8	396.2	404.6
162.5°	354.2	354.2	356.5	361.1	365.7	368.8	371.8	379.4	387.1	393.2	400.0
165°	361.1	360.3	361.9	365.7	368.7	371.4	374.1	380.2	385.5	390.1	395.5
167.5°	366.5	365.7	366.5	369.5	371.8	373.7	375.6	380.2	384.8	387.1	390.9
170°	371.0	369.5	370.3	372.6	374.1	374.8	375.6	379.4	382.5	384.0	386.3
172.5°	374.1	373.3	373.3	374.9	375.6	376.0	376.4	379.4	381.7	381.7	382.5
175°	376.4	375.6	374.9	376.4	376.4	376.8	377.1	378.7	380.2	379.4	379.4
177.5°	377.9	377.1	376.4	377.1	377.1	377.1	377.1	377.9	379.4	377.9	377.1
180°	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1

TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1470.6	1473.3	1482.8	1489.6	1503.1	1501.7	1501.7	1500.4	1496.3	1503.1	1507.2
5°	1573.4	1596.4	1599.2	1628.9	1630.3	1642.4	1650.6	1643.8	1660.0	1658.7	1646.5
7.5°	1700.6	1731.7	1746.6	1775.0	1807.5	1799.4	1830.5	1835.9	1833.2	1846.7	1856.2
10°	1840.0	1894.1	1932.0	1984.7	1998.3	2006.4	2026.7	2044.3	2079.4	2052.4	2070.0
12.5°	1999.6	2038.9	2088.9	2172.8	2214.7	2241.8	2251.3	2263.4	2287.8	2272.9	2274.3
15°	2133.6	2186.3	2271.6	2375.7	2387.9	2421.7	2413.6	2486.7	2521.8	2469.1	2498.8
17.5°	2272.9	2343.3	2444.7	2535.4	2586.8	2609.8	2631.4	2701.8	2699.1	2691.0	2697.7
20°	2362.2	2477.2	2603.0	2723.4	2738.3	2755.9	2814.1	2843.8	2838.4	2861.4	2876.3
22.5°	2488.0	2609.8	2743.7	2823.5	2857.4	2877.7	2923.7	2942.6	2950.7	2956.1	2946.7
25°	2593.5	2723.4	2822.2	2892.5	2912.8	2923.7	2938.5	2944.0	2939.9	2930.4	2938.5
27.5°	2665.3	2769.4	2837.1	2869.5	2858.7	2841.1	2812.7	2793.8	2751.8	2731.5	2755.9
30°	2695.0	2741.0	2761.3	2707.2	2653.1	2609.8	2555.7	2455.6	2377.1	2400.1	2369.0
32.5°	2647.7	2617.9	2520.5	2381.1	2339.2	2268.8	2116.0	1998.3	2002.3	1940.1	1965.8
35°	2508.3	2373.0	2189.0	1978.0	1922.5	1884.6	1716.9	1691.2	1637.0	1578.9	1595.1
37.5°	2262.1	2064.6	1841.3	1685.7	1603.2	1520.7	1426.0	1369.2	1336.7	1312.3	1331.3
40°	1961.7	1720.9	1536.9	1397.6	1327.2	1274.5	1209.5	1152.7	1116.2	1112.1	1118.9
42.5°	1666.8	1463.9	1294.7	1162.2	1139.2	1076.9	1035.0	990.3	979.5	961.9	971.4
45°	1411.1	1246.0	1106.7	998.5	971.4	955.2	903.8	875.3	863.2	852.3	868.6
47.5°	1225.7	1052.6	951.1	886.2	859.1	832.0	803.6	784.7	775.2	776.6	775.2
50°	1047.2	920.0	830.7	780.6	764.4	745.5	722.5	710.3	706.2	694.0	703.5
52.5°	901.0	809.0	746.8	699.5	687.3	673.8	654.8	648.0	638.6	635.9	635.9
55°	783.3	711.6	661.6	630.5	615.6	604.8	593.9	585.8	579.1	579.1	579.1
57.5°	691.3	629.1	592.6	565.5	560.1	549.3	537.1	537.1	527.6	526.3	530.3
60°	612.9	557.4	529.0	506.0	497.9	495.2	483.0	483.0	480.3	473.5	478.9
62.5°	533.1	492.5	468.1	450.5	442.4	442.4	432.9	426.2	426.2	427.5	424.8
65°	460.0	430.2	408.6	395.1	391.0	385.6	384.2	378.8	374.8	376.1	374.8
67.5°	395.1	372.1	357.2	346.3	339.6	336.9	332.8	332.8	330.1	331.5	324.7
70°	336.9	313.9	301.7	290.9	288.2	288.2	282.8	284.1	281.4	285.5	282.8
72.5°	277.3	259.8	250.3	246.2	243.5	242.2	239.5	236.8	235.4	238.1	236.8
75°	224.6	209.7	202.9	200.2	197.5	197.5	196.2	194.8	193.5	193.5	193.5
77.5°	174.5	165.1	156.9	159.6	155.6	156.9	152.9	152.9	154.2	152.9	152.9
80°	128.5	121.8	121.8	119.1	113.6	116.4	116.4	112.3	110.9	113.6	109.6
82.5°	85.2	83.9	81.2	79.8	77.1	78.5	77.1	75.8	74.4	77.1	74.4
85°	50.1	50.1	48.7	46.0	48.7	47.4	46.0	46.0	44.6	44.6	44.6
87.5°	25.7	23.0	23.0	21.6	23.0	20.3	21.6	20.3	18.9	20.3	18.9
90°	18.3	19.1	19.8	20.6	21.4	22.1	21.4	22.1	22.9	22.1	22.9
92.5°	106.1	75.6	58.8	51.2	48.5	45.8	44.3	41.2	42.0	40.5	42.0
95°	367.2	274.8	186.3	145.8	132.0	118.3	103.8	97.0	91.6	88.6	91.6
97.5°	719.9	631.4	476.4	375.6	332.1	288.6	237.4	208.4	190.1	181.7	190.1
100°	873.4	900.1	838.3	748.9	694.7	640.5	563.4	507.7	477.9	478.7	477.9
102.5°	881.0	989.4	1002.4	959.7	930.3	900.9	845.1	803.9	780.2	758.1	780.2
105°	832.9	992.5	1068.8	1083.3	1073.4	1063.5	1028.4	999.4	974.9	971.1	974.9
107.5°	764.2	946.7	1066.5	1126.1	1136.4	1146.7	1142.1	1128.4	1118.5	1110.1	1118.5
110°	700.1	874.9	1015.4	1111.6	1138.3	1165.0	1186.4	1192.5	1191.0	1189.5	1191.0

TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	644.4	803.9	948.2	1058.9	1095.2	1131.4	1174.9	1197.1	1204.7	1205.5	1204.7
115°	601.6	742.8	875.7	987.9	1029.5	1071.1	1128.4	1162.0	1177.2	1181.1	1177.2
117.5°	573.3	695.5	813.1	916.1	959.2	1002.4	1062.0	1099.4	1122.3	1127.6	1122.3
120°	552.0	659.6	762.7	854.3	892.8	931.4	991.7	1034.5	1052.8	1057.4	1052.8
122.5°	534.4	631.4	722.2	805.4	840.6	875.7	927.6	965.0	985.6	991.7	985.6
125°	519.9	606.9	690.2	763.4	794.0	824.5	873.4	907.0	926.1	931.4	926.1
127.5°	506.2	584.8	660.4	727.6	755.8	784.1	828.3	857.4	874.9	879.5	874.9
130°	495.5	564.2	632.9	694.7	720.7	746.7	787.1	814.6	830.6	836.7	830.6
132.5°	485.6	545.1	606.9	663.4	687.8	712.3	749.7	777.2	790.9	794.7	790.9
135°	477.2	528.3	582.5	632.1	653.9	675.7	713.1	736.0	749.7	755.1	749.7
137.5°	469.5	512.3	558.1	602.4	621.8	641.3	673.4	697.0	708.5	713.1	708.5
140°	462.6	498.5	537.5	574.1	590.5	606.9	636.0	657.3	669.5	668.8	669.5
142.5°	456.5	485.6	517.6	548.2	561.9	575.6	599.3	617.6	628.3	627.6	628.3
145°	451.2	475.6	500.8	525.3	536.3	547.4	566.5	582.5	588.6	590.1	588.6
147.5°	445.9	467.2	487.8	508.5	516.5	524.5	539.8	551.2	557.3	558.1	557.3
150°	440.5	458.1	475.6	491.7	499.0	506.2	517.6	526.0	530.6	530.6	530.6
152.5°	434.4	449.7	464.2	477.9	483.6	489.4	497.8	505.4	507.7	507.7	507.7
155°	428.3	441.3	453.5	464.9	469.5	474.1	481.0	487.1	488.6	489.4	488.6
157.5°	421.4	432.1	442.8	452.0	455.8	459.6	465.7	470.3	471.8	471.8	471.8
160°	414.6	424.5	432.9	440.5	443.2	445.9	451.2	455.8	455.8	455.0	455.8
162.5°	407.7	415.3	422.2	429.1	431.4	433.6	436.7	440.5	440.5	439.7	440.5
165°	401.6	407.7	412.3	417.6	419.5	421.4	424.5	427.5	426.8	426.8	426.8
167.5°	395.5	400.8	404.6	407.7	409.2	410.7	412.3	414.6	413.8	413.8	413.8
170°	390.1	393.9	396.2	399.3	400.0	400.8	401.6	403.1	402.3	402.3	402.3
172.5°	384.8	387.8	389.4	391.6	392.0	392.4	392.4	393.9	392.4	391.6	392.4
175°	381.0	382.5	383.3	384.8	384.8	384.8	384.8	385.5	384.8	384.0	384.8
177.5°	377.9	378.7	379.4	380.2	380.2	380.2	379.4	380.2	378.7	378.7	378.7
180°	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1

TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1496.3	1500.4	1489.6	1486.9	1486.9	1492.3	1488.2	1451.7	1458.4	1450.3	1447.6
5°	1661.4	1653.3	1642.4	1637.0	1630.3	1611.3	1610.0	1568.0	1559.9	1532.9	1520.7
7.5°	1842.7	1835.9	1803.4	1799.4	1796.7	1779.1	1734.4	1689.8	1657.3	1626.2	1596.4
10°	2049.7	2029.4	2014.5	1984.7	1969.9	1945.5	1887.3	1845.4	1789.9	1742.6	1680.3
12.5°	2298.6	2275.6	2225.6	2203.9	2185.0	2117.3	2059.1	2011.8	1903.6	1871.1	1794.0
15°	2481.3	2432.6	2427.1	2379.8	2377.1	2302.7	2191.7	2140.3	2056.4	1937.4	1857.6
17.5°	2678.8	2635.5	2601.7	2544.8	2536.7	2466.4	2385.2	2259.4	2167.4	2053.7	1952.3
20°	2823.5	2800.5	2742.4	2719.4	2672.0	2612.5	2528.6	2373.0	2260.7	2147.1	2022.6
22.5°	2938.5	2915.5	2869.5	2838.4	2811.4	2734.3	2634.1	2501.6	2347.3	2198.5	2070.0
25°	2937.2	2930.4	2911.5	2896.6	2876.3	2819.5	2735.6	2608.4	2436.6	2272.9	2094.3
27.5°	2770.8	2789.7	2822.2	2838.4	2834.4	2826.3	2778.9	2672.0	2517.8	2323.0	2122.7
30°	2424.4	2493.4	2554.3	2635.5	2659.8	2719.4	2746.4	2685.5	2562.4	2381.1	2159.3
32.5°	2010.4	2110.6	2243.1	2287.8	2364.9	2479.9	2608.4	2631.4	2554.3	2415.0	2182.3
35°	1649.2	1731.7	1834.6	1904.9	1973.9	2160.6	2323.0	2463.7	2489.4	2397.4	2176.9
37.5°	1365.1	1423.3	1513.9	1573.4	1637.0	1796.7	2024.0	2206.6	2335.1	2337.8	2162.0
40°	1159.5	1185.2	1263.6	1306.9	1367.8	1505.8	1708.7	1946.9	2134.9	2221.5	2122.7
42.5°	982.2	1016.0	1081.0	1113.5	1152.7	1273.1	1407.0	1633.0	1865.7	2051.0	2049.7
45°	876.7	901.0	930.8	957.9	1002.5	1074.2	1227.1	1396.2	1619.4	1829.1	1911.7
47.5°	783.3	806.3	836.1	844.2	874.0	941.6	1035.0	1182.5	1390.8	1599.2	1754.7
50°	704.9	723.8	744.1	759.0	772.5	828.0	898.3	1022.8	1189.2	1390.8	1584.3
52.5°	644.0	657.5	675.1	683.2	695.4	736.0	790.1	882.1	1018.7	1202.7	1390.8
55°	587.2	596.6	607.5	621.0	626.4	656.2	698.1	776.6	878.0	1043.1	1221.7
57.5°	534.4	538.5	545.2	553.3	560.1	585.8	622.3	675.1	764.4	891.6	1060.7
60°	474.9	485.7	489.8	497.9	501.9	522.2	550.6	595.3	664.3	773.9	901.0
62.5°	424.8	431.6	438.3	442.4	451.9	458.6	481.6	522.2	579.1	660.2	775.2
65°	380.2	382.9	386.9	391.0	393.7	401.8	423.5	450.5	493.8	565.5	654.8
67.5°	328.8	331.5	336.9	338.2	340.9	351.8	363.9	386.9	423.5	477.6	550.6
70°	278.7	282.8	285.5	288.2	292.2	296.3	309.8	328.8	357.2	395.1	451.9
72.5°	235.4	239.5	239.5	242.2	240.8	246.2	259.8	273.3	292.2	323.3	373.4
75°	192.1	192.1	194.8	196.2	197.5	202.9	208.3	219.2	234.1	258.4	289.5
77.5°	151.5	150.2	152.9	152.9	152.9	156.9	162.4	167.8	177.2	194.8	219.2
80°	110.9	110.9	113.6	115.0	112.3	113.6	116.4	121.8	128.5	140.7	154.2
82.5°	73.1	78.5	77.1	78.5	77.1	79.8	81.2	82.5	85.2	90.6	100.1
85°	44.6	44.6	44.6	46.0	44.6	46.0	46.0	46.0	47.4	50.1	54.1
87.5°	18.9	18.9	18.9	20.3	18.9	18.9	20.3	18.9	20.3	20.3	21.6
90°	22.1	21.4	22.1	21.4	20.6	19.8	19.1	18.3	19.1	16.8	14.5
92.5°	41.2	44.3	45.8	48.5	51.2	58.8	75.6	106.1	142.0	157.3	117.6
95°	97.0	103.8	118.3	132.0	145.8	186.3	274.8	367.2	452.7	403.1	277.9
97.5°	208.4	237.4	288.6	332.1	375.6	476.4	631.4	719.9	696.3	519.9	309.2
100°	507.7	563.4	640.5	694.7	748.9	838.3	900.1	873.4	723.0	488.6	287.8
102.5°	803.9	845.1	900.9	930.3	959.7	1002.4	989.4	881.0	673.4	442.8	269.5
105°	999.4	1028.4	1063.5	1073.4	1083.3	1068.8	992.5	832.9	613.8	406.9	262.6
107.5°	1128.4	1142.1	1146.7	1136.4	1126.1	1066.5	946.7	764.2	561.1	381.0	261.1
110°	1192.5	1186.4	1165.0	1138.3	1111.6	1015.4	874.9	700.1	517.6	367.2	264.9

TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1197.1	1174.9	1131.4	1095.2	1058.9	948.2	803.9	644.4	488.6	359.6	272.6
115°	1162.0	1128.4	1071.1	1029.5	987.9	875.7	742.8	601.6	469.5	358.8	280.9
117.5°	1099.4	1062.0	1002.4	959.2	916.1	813.1	695.5	573.3	456.5	359.6	291.6
120°	1034.5	991.7	931.4	892.8	854.3	762.7	659.6	552.0	448.1	362.6	303.9
122.5°	965.0	927.6	875.7	840.6	805.4	722.2	631.4	534.4	442.8	368.0	315.3
125°	907.0	873.4	824.5	794.0	763.4	690.2	606.9	519.9	438.2	373.3	327.5
127.5°	857.4	828.3	784.1	755.8	727.6	660.4	584.8	506.2	435.9	379.4	337.4
130°	814.6	787.1	746.7	720.7	694.7	632.9	564.2	495.5	433.6	385.5	347.4
132.5°	777.2	749.7	712.3	687.8	663.4	606.9	545.1	485.6	432.9	390.1	356.5
135°	736.0	713.1	675.7	653.9	632.1	582.5	528.3	477.2	432.1	394.7	364.2
137.5°	697.0	673.4	641.3	621.8	602.4	558.1	512.3	469.5	430.6	397.8	370.3
140°	657.3	636.0	606.9	590.5	574.1	537.5	498.5	462.6	429.8	400.8	374.9
142.5°	617.6	599.3	575.6	561.9	548.2	517.6	485.6	456.5	428.3	403.1	379.4
145°	582.5	566.5	547.4	536.3	525.3	500.8	475.6	451.2	426.8	403.9	382.5
147.5°	551.2	539.8	524.5	516.5	508.5	487.8	467.2	445.9	424.5	403.9	384.8
150°	526.0	517.6	506.2	499.0	491.7	475.6	458.1	440.5	421.4	403.9	385.5
152.5°	505.4	497.8	489.4	483.6	477.9	464.2	449.7	434.4	417.6	401.6	387.1
155°	487.1	481.0	474.1	469.5	464.9	453.5	441.3	428.3	413.0	400.0	387.1
157.5°	470.3	465.7	459.6	455.8	452.0	442.8	432.1	421.4	409.2	397.8	387.8
160°	455.8	451.2	445.9	443.2	440.5	432.9	424.5	414.6	404.6	396.2	387.8
162.5°	440.5	436.7	433.6	431.4	429.1	422.2	415.3	407.7	400.0	393.2	387.1
165°	427.5	424.5	421.4	419.5	417.6	412.3	407.7	401.6	395.5	390.1	385.5
167.5°	414.6	412.3	410.7	409.2	407.7	404.6	400.8	395.5	390.9	387.1	384.8
170°	403.1	401.6	400.8	400.0	399.3	396.2	393.9	390.1	386.3	384.0	382.5
172.5°	393.9	392.4	392.4	392.0	391.6	389.4	387.8	384.8	382.5	381.7	381.7
175°	385.5	384.8	384.8	384.8	384.8	383.3	382.5	381.0	379.4	379.4	380.2
177.5°	380.2	379.4	380.2	380.2	380.2	379.4	378.7	377.9	377.1	377.9	379.4
180°	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1

TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1434.1	1430.0	1430.0	1427.3	1419.2	1404.3	1403.0	1405.7	1397.6	1389.5	1377.3
5°	1504.4	1478.7	1470.6	1462.5	1446.3	1419.2	1408.4	1398.9	1384.0	1366.5	1347.5
7.5°	1564.0	1527.4	1516.6	1501.7	1469.3	1431.4	1407.0	1386.7	1366.5	1342.1	1319.1
10°	1638.4	1585.6	1559.9	1538.3	1493.6	1440.9	1404.3	1374.6	1342.1	1312.3	1282.6
12.5°	1722.3	1637.0	1628.9	1576.2	1524.7	1446.3	1401.6	1358.3	1315.0	1278.5	1247.4
15°	1792.6	1699.3	1665.4	1630.3	1531.5	1434.1	1390.8	1342.1	1292.0	1252.8	1206.8
17.5°	1837.3	1760.2	1688.4	1641.1	1538.3	1451.7	1367.8	1312.3	1259.6	1205.5	1167.6
20°	1891.4	1779.1	1716.9	1653.3	1551.8	1438.2	1354.3	1285.3	1220.3	1171.6	1125.6
22.5°	1945.5	1794.0	1742.6	1673.6	1554.5	1424.6	1329.9	1260.9	1186.5	1137.8	1087.7
25°	1940.1	1815.6	1730.4	1672.2	1527.4	1412.4	1301.5	1220.3	1151.3	1089.1	1039.0
27.5°	1944.1	1791.3	1704.7	1637.0	1508.5	1394.9	1271.7	1186.5	1114.8	1049.9	997.1
30°	1945.5	1754.7	1679.0	1597.8	1473.3	1352.9	1237.9	1151.3	1075.6	1005.2	957.9
32.5°	1941.4	1725.0	1630.3	1557.2	1417.9	1312.3	1198.7	1106.7	1029.6	964.6	920.0
35°	1932.0	1689.8	1580.2	1488.2	1361.0	1254.2	1162.2	1067.5	984.9	925.4	874.0
37.5°	1906.3	1651.9	1527.4	1436.8	1294.7	1186.5	1105.3	1026.9	947.0	876.7	833.4
40°	1887.3	1600.5	1474.7	1375.9	1223.0	1117.5	1049.9	975.5	897.0	833.4	791.5
42.5°	1844.0	1551.8	1420.6	1302.9	1152.7	1044.5	980.9	921.3	853.7	791.5	753.6
45°	1773.7	1499.0	1354.3	1235.2	1075.6	972.8	914.6	865.9	806.3	746.8	708.9
47.5°	1674.9	1423.3	1283.9	1164.9	999.8	895.6	837.5	800.9	753.6	703.5	671.0
50°	1568.0	1340.7	1212.2	1094.5	926.8	825.3	768.5	734.6	703.5	657.5	626.4
52.5°	1428.7	1252.8	1129.7	1017.4	848.3	750.9	700.8	676.5	644.0	611.5	584.5
55°	1293.4	1139.2	1037.7	930.8	771.2	680.5	631.8	606.1	587.2	560.1	538.5
57.5°	1136.5	1033.6	940.3	842.9	699.5	616.9	570.9	539.8	527.6	515.5	495.2
60°	991.7	913.2	837.5	756.3	625.0	550.6	506.0	481.6	469.5	461.3	447.8
62.5°	859.1	798.2	733.3	668.3	549.3	481.6	447.8	423.5	412.6	411.3	399.1
65°	731.9	688.6	635.9	572.3	478.9	419.4	386.9	372.1	359.9	359.9	350.4
67.5°	604.8	575.0	533.1	488.4	415.3	359.9	330.1	316.6	309.8	309.8	303.1
70°	503.3	483.0	445.1	405.9	342.3	300.3	277.3	265.2	261.1	262.5	257.1
72.5°	408.6	386.9	355.8	327.4	280.1	248.9	232.7	219.2	212.4	213.8	212.4
75°	316.6	305.8	278.7	257.1	219.2	197.5	182.6	175.9	170.5	171.8	169.1
77.5°	238.1	221.9	207.0	192.1	169.1	151.5	139.4	132.6	128.5	128.5	128.5
80°	162.4	159.6	147.5	139.4	120.4	106.9	97.4	96.1	92.0	92.0	92.0
82.5°	105.5	98.8	92.0	86.6	75.8	67.6	63.6	60.9	59.5	58.2	60.9
85°	58.2	54.1	51.4	46.0	41.9	37.9	33.8	32.5	31.1	32.5	31.1
87.5°	23.0	18.9	18.9	17.6	16.2	14.9	14.9	12.2	12.2	10.8	10.8
90°	12.2	9.9	9.2	8.4	6.9	4.6	3.1	1.5	3.1	4.6	6.9
92.5°	77.1	52.7	45.8	38.9	31.3	24.4	16.8	11.5	16.8	24.4	31.3
95°	164.1	99.2	84.4	69.5	49.6	36.6	28.2	26.0	28.2	36.6	49.6
97.5°	177.1	113.0	96.6	80.2	60.3	48.9	42.0	41.2	42.0	48.9	60.3
100°	174.8	121.4	106.5	91.6	73.3	62.6	57.3	56.5	57.3	62.6	73.3
102.5°	177.9	131.3	118.0	104.6	88.6	78.6	74.1	72.5	74.1	78.6	88.6
105°	184.0	142.8	131.0	119.1	104.6	95.4	90.9	88.6	90.9	95.4	104.6
107.5°	193.9	157.3	146.2	135.1	121.4	112.2	107.6	105.4	107.6	112.2	121.4
110°	206.9	172.5	161.8	151.2	138.2	129.8	126.0	123.7	126.0	129.8	138.2

TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	219.9	188.6	178.3	168.0	155.0	146.6	142.8	140.5	142.8	146.6	155.0
115°	234.4	205.4	195.1	184.8	171.8	164.1	159.6	156.5	159.6	164.1	171.8
117.5°	249.6	220.6	211.1	201.6	187.0	180.2	176.4	172.5	176.4	180.2	187.0
120°	264.2	236.7	227.2	217.6	203.1	195.4	191.6	189.3	191.6	195.4	203.1
122.5°	279.4	252.7	242.4	232.1	218.3	209.9	206.1	203.8	206.1	209.9	218.3
125°	293.9	267.2	256.9	246.6	232.1	223.7	219.1	217.6	219.1	223.7	232.1
127.5°	306.9	280.9	270.6	260.3	244.3	235.9	230.6	228.3	230.6	235.9	244.3
130°	318.4	293.2	282.9	272.6	256.5	247.4	240.5	238.2	240.5	247.4	256.5
132.5°	328.3	303.9	294.0	284.0	268.0	256.5	248.9	245.8	248.9	256.5	268.0
135°	338.2	314.5	304.2	293.9	277.9	266.4	258.0	255.0	258.0	266.4	277.9
137.5°	345.1	322.2	312.6	303.1	287.1	274.8	266.4	263.4	266.4	274.8	287.1
140°	351.9	329.8	320.2	310.7	295.5	283.2	275.6	271.8	275.6	283.2	295.5
142.5°	357.3	335.9	327.2	318.4	303.1	292.4	284.0	280.9	284.0	292.4	303.1
145°	361.9	342.0	333.2	324.5	311.5	300.0	293.2	290.9	293.2	300.0	311.5
147.5°	365.7	347.4	339.8	332.1	319.1	309.2	302.3	300.8	302.3	309.2	319.1
150°	369.5	351.9	345.0	338.2	327.5	317.6	311.5	310.7	311.5	317.6	327.5
152.5°	371.8	357.3	350.8	344.3	335.2	326.8	320.6	320.6	320.6	326.8	335.2
155°	374.9	361.9	356.5	351.2	342.8	335.2	330.6	330.6	330.6	335.2	342.8
157.5°	376.4	365.7	361.5	357.3	349.7	342.8	339.0	338.2	339.0	342.8	349.7
160°	378.7	369.5	365.7	361.9	356.5	350.4	347.4	347.4	347.4	350.4	356.5
162.5°	379.4	371.8	368.8	365.7	361.1	356.5	354.2	354.2	354.2	356.5	361.1
165°	380.2	374.1	371.4	368.7	365.7	361.9	360.3	361.1	360.3	361.9	365.7
167.5°	380.2	375.6	373.7	371.8	369.5	366.5	365.7	366.5	365.7	366.5	369.5
170°	379.4	375.6	374.8	374.1	372.6	370.3	369.5	371.0	369.5	370.3	372.6
172.5°	379.4	376.4	376.0	375.6	374.9	373.3	373.3	374.1	373.3	373.3	374.9
175°	378.7	377.1	376.8	376.4	376.4	374.9	375.6	376.4	375.6	374.9	376.4
177.5°	377.9	377.1	377.1	377.1	377.1	376.4	377.1	377.9	377.1	376.4	377.1
180°	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1

TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1374.6	1373.2	1375.9	1367.8	1354.3	1347.5	1328.6	1324.5	1323.2	1324.5	1325.9
5°	1336.7	1335.3	1331.3	1317.7	1301.5	1289.3	1266.3	1265.0	1256.9	1248.7	1252.8
7.5°	1300.2	1294.7	1286.6	1269.0	1247.4	1233.9	1214.9	1201.4	1190.6	1183.8	1178.4
10°	1263.6	1255.5	1247.4	1224.4	1197.3	1177.0	1154.0	1143.2	1131.0	1125.6	1120.2
12.5°	1216.3	1208.2	1193.3	1166.2	1150.0	1124.3	1101.3	1090.5	1083.7	1072.9	1066.1
15°	1178.4	1162.2	1154.0	1125.6	1091.8	1089.1	1047.2	1044.5	1030.9	1030.9	1020.1
17.5°	1135.1	1122.9	1108.0	1079.6	1055.3	1030.9	1009.3	1001.2	989.0	986.3	980.9
20°	1093.2	1076.9	1071.5	1043.1	1017.4	987.6	964.6	956.5	951.1	945.7	949.8
22.5°	1049.9	1036.3	1022.8	997.1	978.2	948.4	934.9	926.8	918.6	915.9	917.3
25°	1007.9	995.7	982.2	956.5	936.2	911.9	899.7	895.6	891.6	891.6	890.2
27.5°	967.3	955.2	943.0	920.0	899.7	882.1	872.6	868.6	864.5	867.2	869.9
30°	925.4	914.6	903.8	883.5	867.2	851.0	845.6	842.9	841.5	848.3	848.3
32.5°	887.5	878.0	869.9	851.0	834.8	821.2	817.2	818.5	819.9	823.9	826.6
35°	848.3	841.5	833.4	817.2	803.6	791.5	792.8	792.8	795.5	802.3	807.7
37.5°	813.1	803.6	796.9	783.3	772.5	761.7	765.8	769.8	772.5	780.6	783.3
40°	771.2	767.1	761.7	748.2	738.7	737.3	738.7	741.4	746.8	750.9	754.9
42.5°	737.3	731.9	725.2	714.3	706.2	707.6	708.9	711.6	714.3	721.1	725.2
45°	699.5	695.4	690.0	680.5	673.8	675.1	676.5	676.5	679.2	687.3	690.0
47.5°	657.5	658.9	652.1	642.6	638.6	638.6	638.6	641.3	648.0	650.8	652.1
50°	616.9	614.2	612.9	603.4	600.7	599.3	600.7	602.0	611.5	610.2	614.2
52.5°	573.6	573.6	572.3	566.9	562.8	562.8	560.1	566.9	569.6	572.3	576.3
55°	531.7	527.6	526.3	523.6	518.2	516.8	519.5	527.6	530.3	533.1	537.1
57.5°	485.7	485.7	483.0	478.9	478.9	478.9	478.9	484.3	488.4	491.1	499.2
60°	443.8	438.3	434.3	434.3	434.3	432.9	441.1	441.1	449.2	450.5	453.2
62.5°	393.7	391.0	388.3	389.6	388.3	391.0	393.7	399.1	400.5	404.5	408.6
65°	346.3	346.3	343.6	351.8	346.3	346.3	353.1	353.1	355.8	359.9	365.3
67.5°	300.3	301.7	299.0	299.0	301.7	303.1	304.4	309.8	311.2	316.6	323.3
70°	253.0	255.7	257.1	254.3	257.1	259.8	262.5	263.8	269.2	271.9	276.0
72.5°	211.1	213.8	209.7	211.1	212.4	215.1	216.5	219.2	221.9	230.0	232.7
75°	169.1	167.8	166.4	171.8	169.1	174.5	175.9	175.9	178.6	185.4	188.1
77.5°	129.9	129.9	131.2	128.5	132.6	131.2	132.6	136.6	140.7	140.7	151.5
80°	90.6	93.4	93.4	93.4	94.7	96.1	93.4	100.1	101.5	101.5	105.5
82.5°	58.2	59.5	58.2	60.9	60.9	63.6	62.2	63.6	66.3	69.0	70.4
85°	31.1	31.1	33.8	33.8	32.5	33.8	32.5	33.8	36.5	36.5	37.9
87.5°	10.8	10.8	10.8	10.8	12.2	10.8	12.2	12.2	10.8	10.8	14.9
90°	8.4	9.2	9.9	12.2	14.5	16.8	19.1	18.3	19.1	19.8	20.6
92.5°	38.9	45.8	52.7	77.1	117.6	157.3	142.0	106.1	75.6	58.8	51.2
95°	69.5	84.4	99.2	164.1	277.9	403.1	452.7	367.2	274.8	186.3	145.8
97.5°	80.2	96.6	113.0	177.1	309.2	519.9	696.3	719.9	631.4	476.4	375.6
100°	91.6	106.5	121.4	174.8	287.8	488.6	723.0	873.4	900.1	838.3	748.9
102.5°	104.6	118.0	131.3	177.9	269.5	442.8	673.4	881.0	989.4	1002.4	959.7
105°	119.1	131.0	142.8	184.0	262.6	406.9	613.8	832.9	992.5	1068.8	1083.3
107.5°	135.1	146.2	157.3	193.9	261.1	381.0	561.1	764.2	946.7	1066.5	1126.1
110°	151.2	161.8	172.5	206.9	264.9	367.2	517.6	700.1	874.9	1015.4	1111.6

TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	168.0	178.3	188.6	219.9	272.6	359.6	488.6	644.4	803.9	948.2	1058.9
115°	184.8	195.1	205.4	234.4	280.9	358.8	469.5	601.6	742.8	875.7	987.9
117.5°	201.6	211.1	220.6	249.6	291.6	359.6	456.5	573.3	695.5	813.1	916.1
120°	217.6	227.2	236.7	264.2	303.9	362.6	448.1	552.0	659.6	762.7	854.3
122.5°	232.1	242.4	252.7	279.4	315.3	368.0	442.8	534.4	631.4	722.2	805.4
125°	246.6	256.9	267.2	293.9	327.5	373.3	438.2	519.9	606.9	690.2	763.4
127.5°	260.3	270.6	280.9	306.9	337.4	379.4	435.9	506.2	584.8	660.4	727.6
130°	272.6	282.9	293.2	318.4	347.4	385.5	433.6	495.5	564.2	632.9	694.7
132.5°	284.0	294.0	303.9	328.3	356.5	390.1	432.9	485.6	545.1	606.9	663.4
135°	293.9	304.2	314.5	338.2	364.2	394.7	432.1	477.2	528.3	582.5	632.1
137.5°	303.1	312.6	322.2	345.1	370.3	397.8	430.6	469.5	512.3	558.1	602.4
140°	310.7	320.2	329.8	351.9	374.9	400.8	429.8	462.6	498.5	537.5	574.1
142.5°	318.4	327.2	335.9	357.3	379.4	403.1	428.3	456.5	485.6	517.6	548.2
145°	324.5	333.2	342.0	361.9	382.5	403.9	426.8	451.2	475.6	500.8	525.3
147.5°	332.1	339.8	347.4	365.7	384.8	403.9	424.5	445.9	467.2	487.8	508.5
150°	338.2	345.0	351.9	369.5	385.5	403.9	421.4	440.5	458.1	475.6	491.7
152.5°	344.3	350.8	357.3	371.8	387.1	401.6	417.6	434.4	449.7	464.2	477.9
155°	351.2	356.5	361.9	374.9	387.1	400.0	413.0	428.3	441.3	453.5	464.9
157.5°	357.3	361.5	365.7	376.4	387.8	397.8	409.2	421.4	432.1	442.8	452.0
160°	361.9	365.7	369.5	378.7	387.8	396.2	404.6	414.6	424.5	432.9	440.5
162.5°	365.7	368.8	371.8	379.4	387.1	393.2	400.0	407.7	415.3	422.2	429.1
165°	368.7	371.4	374.1	380.2	385.5	390.1	395.5	401.6	407.7	412.3	417.6
167.5°	371.8	373.7	375.6	380.2	384.8	387.1	390.9	395.5	400.8	404.6	407.7
170°	374.1	374.8	375.6	379.4	382.5	384.0	386.3	390.1	393.9	396.2	399.3
172.5°	375.6	376.0	376.4	379.4	381.7	381.7	382.5	384.8	387.8	389.4	391.6
175°	376.4	376.8	377.1	378.7	380.2	379.4	379.4	381.0	382.5	383.3	384.8
177.5°	377.1	377.1	377.1	377.9	379.4	377.9	377.1	377.9	378.7	379.4	380.2
180°	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1

TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1324.5	1325.9	1320.5	1316.4	1327.2	1320.5	1320.5	1321.8	1319.1	1323.2	1321.8
5°	1250.1	1251.5	1242.0	1244.7	1239.3	1237.9	1236.6	1244.7	1243.3	1242.0	1244.7
7.5°	1177.0	1177.0	1173.0	1170.3	1170.3	1166.2	1171.6	1170.3	1173.0	1173.0	1177.0
10°	1116.2	1118.9	1112.1	1105.3	1104.0	1105.3	1105.3	1106.7	1108.0	1117.5	1116.2
12.5°	1066.1	1062.0	1060.7	1056.6	1049.9	1047.2	1044.5	1059.3	1055.3	1055.3	1055.3
15°	1010.6	1020.1	1018.7	1006.6	1003.9	1009.3	1006.6	1006.6	1020.1	1018.7	1017.4
17.5°	980.9	978.2	975.5	968.7	970.0	968.7	970.0	970.0	978.2	978.2	978.2
20°	947.0	941.6	941.6	938.9	938.9	934.9	940.3	941.6	947.0	947.0	948.4
22.5°	917.3	913.2	913.2	911.9	914.6	909.2	914.6	915.9	915.9	920.0	920.0
25°	891.6	888.9	888.9	891.6	891.6	891.6	891.6	897.0	892.9	894.3	892.9
27.5°	868.6	869.9	871.3	872.6	871.3	872.6	874.0	876.7	878.0	876.7	874.0
30°	846.9	851.0	852.3	852.3	855.0	856.4	857.8	857.8	859.1	855.0	857.8
32.5°	830.7	830.7	833.4	834.8	837.5	838.8	838.8	841.5	840.2	836.1	837.5
35°	807.7	807.7	813.1	815.8	819.9	818.5	819.9	819.9	821.2	818.5	814.5
37.5°	784.7	787.4	787.4	792.8	794.2	795.5	794.2	796.9	795.5	792.8	791.5
40°	757.6	756.3	757.6	761.7	763.0	763.0	763.0	765.8	765.8	765.8	764.4
42.5°	723.8	727.9	726.5	730.6	729.2	729.2	731.9	734.6	736.0	731.9	733.3
45°	691.3	691.3	694.0	694.0	695.4	695.4	700.8	698.1	700.8	698.1	699.5
47.5°	656.2	657.5	657.5	658.9	661.6	664.3	661.6	662.9	662.9	664.3	661.6
50°	616.9	616.9	619.6	623.7	629.1	626.4	625.0	630.5	626.4	626.4	623.7
52.5°	576.3	580.4	581.8	585.8	589.9	591.2	592.6	589.9	591.2	587.2	588.5
55°	537.1	538.5	543.9	547.9	552.0	552.0	550.6	552.0	553.3	547.9	547.9
57.5°	497.9	501.9	507.3	507.3	512.8	512.8	511.4	511.4	512.8	508.7	507.3
60°	455.9	460.0	466.8	466.8	474.9	476.2	473.5	470.8	470.8	466.8	468.1
62.5°	411.3	415.3	419.4	426.2	431.6	428.9	434.3	428.9	430.2	422.1	422.1
65°	372.1	373.4	380.2	386.9	386.9	389.6	386.9	388.3	384.2	384.2	378.8
67.5°	326.1	326.1	332.8	339.6	346.3	346.3	346.3	342.3	342.3	338.2	338.2
70°	285.5	284.1	290.9	294.9	299.0	300.3	297.6	296.3	293.6	289.5	288.2
72.5°	235.4	238.1	244.9	247.6	254.3	253.0	259.8	251.6	251.6	244.9	243.5
75°	190.8	193.5	200.2	204.3	208.3	208.3	212.4	208.3	202.9	200.2	198.9
77.5°	151.5	150.2	155.6	162.4	163.7	162.4	165.1	163.7	158.3	158.3	155.6
80°	108.2	112.3	117.7	116.4	121.8	120.4	120.4	117.7	117.7	113.6	116.4
82.5°	71.7	75.8	77.1	75.8	77.1	79.8	81.2	79.8	79.8	77.1	78.5
85°	37.9	37.9	40.6	41.9	40.6	40.6	41.9	46.0	43.3	40.6	43.3
87.5°	12.2	10.8	10.8	12.2	10.8	10.8	12.2	12.2	13.5	13.5	13.5
90°	21.4	22.1	21.4	22.1	22.9	22.1	22.9	22.1	21.4	22.1	21.4
92.5°	48.5	45.8	44.3	41.2	42.0	40.5	42.0	41.2	44.3	45.8	48.5
95°	132.0	118.3	103.8	97.0	91.6	88.6	91.6	97.0	103.8	118.3	132.0
97.5°	332.1	288.6	237.4	208.4	190.1	181.7	190.1	208.4	237.4	288.6	332.1
100°	694.7	640.5	563.4	507.7	477.9	478.7	477.9	507.7	563.4	640.5	694.7
102.5°	930.3	900.9	845.1	803.9	780.2	758.1	780.2	803.9	845.1	900.9	930.3
105°	1073.4	1063.5	1028.4	999.4	974.9	971.1	974.9	999.4	1028.4	1063.5	1073.4
107.5°	1136.4	1146.7	1142.1	1128.4	1118.5	1110.1	1118.5	1128.4	1142.1	1146.7	1136.4
110°	1138.3	1165.0	1186.4	1192.5	1191.0	1189.5	1191.0	1192.5	1186.4	1165.0	1138.3

TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1095.2	1131.4	1174.9	1197.1	1204.7	1205.5	1204.7	1197.1	1174.9	1131.4	1095.2
115°	1029.5	1071.1	1128.4	1162.0	1177.2	1181.1	1177.2	1162.0	1128.4	1071.1	1029.5
117.5°	959.2	1002.4	1062.0	1099.4	1122.3	1127.6	1122.3	1099.4	1062.0	1002.4	959.2
120°	892.8	931.4	991.7	1034.5	1052.8	1057.4	1052.8	1034.5	991.7	931.4	892.8
122.5°	840.6	875.7	927.6	965.0	985.6	991.7	985.6	965.0	927.6	875.7	840.6
125°	794.0	824.5	873.4	907.0	926.1	931.4	926.1	907.0	873.4	824.5	794.0
127.5°	755.8	784.1	828.3	857.4	874.9	879.5	874.9	857.4	828.3	784.1	755.8
130°	720.7	746.7	787.1	814.6	830.6	836.7	830.6	814.6	787.1	746.7	720.7
132.5°	687.8	712.3	749.7	777.2	790.9	794.7	790.9	777.2	749.7	712.3	687.8
135°	653.9	675.7	713.1	736.0	749.7	755.1	749.7	736.0	713.1	675.7	653.9
137.5°	621.8	641.3	673.4	697.0	708.5	713.1	708.5	697.0	673.4	641.3	621.8
140°	590.5	606.9	636.0	657.3	669.5	668.8	669.5	657.3	636.0	606.9	590.5
142.5°	561.9	575.6	599.3	617.6	628.3	627.6	628.3	617.6	599.3	575.6	561.9
145°	536.3	547.4	566.5	582.5	588.6	590.1	588.6	582.5	566.5	547.4	536.3
147.5°	516.5	524.5	539.8	551.2	557.3	558.1	557.3	551.2	539.8	524.5	516.5
150°	499.0	506.2	517.6	526.0	530.6	530.6	530.6	526.0	517.6	506.2	499.0
152.5°	483.6	489.4	497.8	505.4	507.7	507.7	507.7	505.4	497.8	489.4	483.6
155°	469.5	474.1	481.0	487.1	488.6	489.4	488.6	487.1	481.0	474.1	469.5
157.5°	455.8	459.6	465.7	470.3	471.8	471.8	471.8	470.3	465.7	459.6	455.8
160°	443.2	445.9	451.2	455.8	455.8	455.0	455.8	455.8	451.2	445.9	443.2
162.5°	431.4	433.6	436.7	440.5	440.5	439.7	440.5	440.5	436.7	433.6	431.4
165°	419.5	421.4	424.5	427.5	426.8	426.8	426.8	427.5	424.5	421.4	419.5
167.5°	409.2	410.7	412.3	414.6	413.8	413.8	413.8	414.6	412.3	410.7	409.2
170°	400.0	400.8	401.6	403.1	402.3	402.3	402.3	403.1	401.6	400.8	400.0
172.5°	392.0	392.4	392.4	393.9	392.4	391.6	392.4	393.9	392.4	392.4	392.0
175°	384.8	384.8	384.8	385.5	384.8	384.0	384.8	385.5	384.8	384.8	384.8
177.5°	380.2	380.2	379.4	380.2	378.7	378.7	378.7	380.2	379.4	380.2	380.2
180°	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1

TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2	1396.2
2.5°	1325.9	1328.6	1329.9	1324.5	1320.5	1327.2	1336.7	1343.5	1348.9	1355.6	1359.7
5°	1247.4	1256.9	1256.9	1259.6	1263.6	1270.4	1288.0	1300.2	1311.0	1319.1	1325.9
7.5°	1181.1	1187.9	1191.9	1198.7	1205.5	1214.9	1235.2	1252.8	1269.0	1278.5	1289.3
10°	1121.6	1127.0	1133.7	1137.8	1150.0	1163.5	1189.2	1204.1	1223.0	1237.9	1251.5
12.5°	1064.7	1083.7	1087.7	1086.4	1097.2	1112.1	1137.8	1160.8	1181.1	1196.0	1210.9
15°	1024.2	1030.9	1039.0	1037.7	1060.7	1064.7	1086.4	1113.5	1140.5	1150.0	1163.5
17.5°	979.5	990.3	998.5	1002.5	1009.3	1024.2	1044.5	1064.7	1099.9	1101.3	1136.5
20°	944.3	955.2	960.6	966.0	970.0	987.6	1005.2	1028.2	1056.6	1071.5	1090.5
22.5°	921.3	926.8	930.8	934.9	940.3	949.8	971.4	997.1	1016.0	1032.3	1044.5
25°	894.3	899.7	905.1	907.8	911.9	917.3	933.5	953.8	980.9	991.7	1003.9
27.5°	875.3	875.3	878.0	878.0	883.5	888.9	901.0	920.0	941.6	955.2	971.4
30°	855.0	853.7	855.0	853.7	852.3	860.5	871.3	887.5	902.4	918.6	929.5
32.5°	834.8	833.4	833.4	834.8	829.3	833.4	838.8	853.7	869.9	878.0	890.2
35°	813.1	810.4	810.4	810.4	807.7	805.0	810.4	823.9	834.8	845.6	855.0
37.5°	791.5	787.4	787.4	784.7	782.0	777.9	777.9	788.8	803.6	807.7	819.9
40°	761.7	761.7	759.0	757.6	754.9	752.2	748.2	757.6	771.2	775.2	784.7
42.5°	731.9	727.9	726.5	726.5	726.5	722.5	719.8	726.5	734.6	741.4	746.8
45°	698.1	695.4	696.8	695.4	692.7	691.3	690.0	692.7	702.2	704.9	711.6
47.5°	661.6	660.2	660.2	658.9	657.5	658.9	653.5	660.2	662.9	665.6	671.0
50°	623.7	622.3	621.0	619.6	619.6	621.0	619.6	619.6	625.0	627.8	633.2
52.5°	585.8	581.8	581.8	580.4	580.4	577.7	580.4	581.8	584.5	587.2	589.9
55°	545.2	545.2	541.2	541.2	538.5	538.5	539.8	538.5	543.9	546.6	546.6
57.5°	506.0	500.6	501.9	499.2	496.5	495.2	495.2	497.9	500.6	500.6	503.3
60°	464.1	458.6	457.3	451.9	454.6	450.5	451.9	451.9	457.3	454.6	457.3
62.5°	422.1	415.3	411.3	408.6	408.6	409.9	407.2	405.9	408.6	411.3	416.7
65°	377.5	373.4	369.3	365.3	365.3	363.9	366.6	362.6	361.2	362.6	365.3
67.5°	331.5	327.4	323.3	319.3	320.6	316.6	313.9	317.9	315.2	316.6	319.3
70°	286.8	284.1	276.0	273.3	271.9	273.3	271.9	269.2	273.3	271.9	273.3
72.5°	242.2	239.5	235.4	228.6	228.6	227.3	225.9	225.9	224.6	224.6	224.6
75°	198.9	193.5	189.4	188.1	185.4	184.0	182.6	179.9	181.3	182.6	179.9
77.5°	154.2	147.5	146.1	146.1	142.1	142.1	143.4	142.1	140.7	140.7	140.7
80°	113.6	108.2	108.2	105.5	102.8	102.8	102.8	102.8	101.5	100.1	101.5
82.5°	73.1	71.7	70.4	70.4	73.1	67.6	70.4	69.0	67.6	67.6	66.3
85°	40.6	41.9	40.6	41.9	39.2	40.6	40.6	40.6	39.2	40.6	37.9
87.5°	14.9	14.9	14.9	16.2	16.2	16.2	16.2	16.2	17.6	16.2	16.2
90°	20.6	19.8	19.1	18.3	19.1	16.8	14.5	12.2	9.9	9.2	8.4
92.5°	51.2	58.8	75.6	106.1	142.0	157.3	117.6	77.1	52.7	45.8	38.9
95°	145.8	186.3	274.8	367.2	452.7	403.1	277.9	164.1	99.2	84.4	69.5
97.5°	375.6	476.4	631.4	719.9	696.3	519.9	309.2	177.1	113.0	96.6	80.2
100°	748.9	838.3	900.1	873.4	723.0	488.6	287.8	174.8	121.4	106.5	91.6
102.5°	959.7	1002.4	989.4	881.0	673.4	442.8	269.5	177.9	131.3	118.0	104.6
105°	1083.3	1068.8	992.5	832.9	613.8	406.9	262.6	184.0	142.8	131.0	119.1
107.5°	1126.1	1066.5	946.7	764.2	561.1	381.0	261.1	193.9	157.3	146.2	135.1
110°	1111.6	1015.4	874.9	700.1	517.6	367.2	264.9	206.9	172.5	161.8	151.2

TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1058.9	948.2	803.9	644.4	488.6	359.6	272.6	219.9	188.6	178.3	168.0
115°	987.9	875.7	742.8	601.6	469.5	358.8	280.9	234.4	205.4	195.1	184.8
117.5°	916.1	813.1	695.5	573.3	456.5	359.6	291.6	249.6	220.6	211.1	201.6
120°	854.3	762.7	659.6	552.0	448.1	362.6	303.9	264.2	236.7	227.2	217.6
122.5°	805.4	722.2	631.4	534.4	442.8	368.0	315.3	279.4	252.7	242.4	232.1
125°	763.4	690.2	606.9	519.9	438.2	373.3	327.5	293.9	267.2	256.9	246.6
127.5°	727.6	660.4	584.8	506.2	435.9	379.4	337.4	306.9	280.9	270.6	260.3
130°	694.7	632.9	564.2	495.5	433.6	385.5	347.4	318.4	293.2	282.9	272.6
132.5°	663.4	606.9	545.1	485.6	432.9	390.1	356.5	328.3	303.9	294.0	284.0
135°	632.1	582.5	528.3	477.2	432.1	394.7	364.2	338.2	314.5	304.2	293.9
137.5°	602.4	558.1	512.3	469.5	430.6	397.8	370.3	345.1	322.2	312.6	303.1
140°	574.1	537.5	498.5	462.6	429.8	400.8	374.9	351.9	329.8	320.2	310.7
142.5°	548.2	517.6	485.6	456.5	428.3	403.1	379.4	357.3	335.9	327.2	318.4
145°	525.3	500.8	475.6	451.2	426.8	403.9	382.5	361.9	342.0	333.2	324.5
147.5°	508.5	487.8	467.2	445.9	424.5	403.9	384.8	365.7	347.4	339.8	332.1
150°	491.7	475.6	458.1	440.5	421.4	403.9	385.5	369.5	351.9	345.0	338.2
152.5°	477.9	464.2	449.7	434.4	417.6	401.6	387.1	371.8	357.3	350.8	344.3
155°	464.9	453.5	441.3	428.3	413.0	400.0	387.1	374.9	361.9	356.5	351.2
157.5°	452.0	442.8	432.1	421.4	409.2	397.8	387.8	376.4	365.7	361.5	357.3
160°	440.5	432.9	424.5	414.6	404.6	396.2	387.8	378.7	369.5	365.7	361.9
162.5°	429.1	422.2	415.3	407.7	400.0	393.2	387.1	379.4	371.8	368.8	365.7
165°	417.6	412.3	407.7	401.6	395.5	390.1	385.5	380.2	374.1	371.4	368.7
167.5°	407.7	404.6	400.8	395.5	390.9	387.1	384.8	380.2	375.6	373.7	371.8
170°	399.3	396.2	393.9	390.1	386.3	384.0	382.5	379.4	375.6	374.8	374.1
172.5°	391.6	389.4	387.8	384.8	382.5	381.7	381.7	379.4	376.4	376.0	375.6
175°	384.8	383.3	382.5	381.0	379.4	379.4	380.2	378.7	377.1	376.8	376.4
177.5°	380.2	379.4	378.7	377.9	377.1	377.9	379.4	377.9	377.1	377.1	377.1
180°	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1

TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1396.2	1396.2	1396.2	1396.2
2.5°	1366.5	1370.5	1384.0	1400.3
5°	1339.4	1350.2	1369.2	1394.9
7.5°	1309.6	1325.9	1352.9	1385.4
10°	1275.8	1298.8	1332.6	1373.2
12.5°	1239.3	1269.0	1312.3	1354.3
15°	1216.3	1246.0	1285.3	1331.3
17.5°	1171.6	1206.8	1247.4	1312.3
20°	1125.6	1164.9	1217.6	1282.6
22.5°	1090.5	1132.4	1182.5	1251.5
25°	1048.5	1091.8	1145.9	1217.6
27.5°	1003.9	1047.2	1108.0	1183.8
30°	970.0	1012.0	1070.2	1151.3
32.5°	929.5	970.0	1030.9	1116.2
35°	883.5	929.5	987.6	1074.2
37.5°	848.3	890.2	951.1	1033.6
40°	810.4	846.9	906.5	987.6
42.5°	769.8	810.4	861.8	943.0
45°	731.9	761.7	814.5	891.6
47.5°	691.3	725.2	765.8	825.3
50°	648.0	676.5	721.1	761.7
52.5°	606.1	629.1	667.0	698.1
55°	561.5	584.5	612.9	631.8
57.5°	519.5	535.8	554.7	566.9
60°	468.1	484.3	496.5	508.7
62.5°	422.1	434.3	441.1	447.8
65°	374.8	381.5	385.6	391.0
67.5°	323.3	330.1	331.5	339.6
70°	276.0	277.3	280.1	284.1
72.5°	231.3	234.1	232.7	235.4
75°	185.4	188.1	185.4	188.1
77.5°	140.7	143.4	143.4	147.5
80°	101.5	102.8	104.2	104.2
82.5°	66.3	70.4	67.6	69.0
85°	37.9	39.2	39.2	40.6
87.5°	17.6	18.9	17.6	20.3
90°	6.9	4.6	3.1	1.5
92.5°	31.3	24.4	16.8	11.5
95°	49.6	36.6	28.2	26.0
97.5°	60.3	48.9	42.0	41.2
100°	73.3	62.6	57.3	56.5
102.5°	88.6	78.6	74.1	72.5
105°	104.6	95.4	90.9	88.6
107.5°	121.4	112.2	107.6	105.4
110°	138.2	129.8	126.0	123.7

TEST NUMBER: P1011207

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	155.0	146.6	142.8	140.5
115°	171.8	164.1	159.6	156.5
117.5°	187.0	180.2	176.4	172.5
120°	203.1	195.4	191.6	189.3
122.5°	218.3	209.9	206.1	203.8
125°	232.1	223.7	219.1	217.6
127.5°	244.3	235.9	230.6	228.3
130°	256.5	247.4	240.5	238.2
132.5°	268.0	256.5	248.9	245.8
135°	277.9	266.4	258.0	255.0
137.5°	287.1	274.8	266.4	263.4
140°	295.5	283.2	275.6	271.8
142.5°	303.1	292.4	284.0	280.9
145°	311.5	300.0	293.2	290.9
147.5°	319.1	309.2	302.3	300.8
150°	327.5	317.6	311.5	310.7
152.5°	335.2	326.8	320.6	320.6
155°	342.8	335.2	330.6	330.6
157.5°	349.7	342.8	339.0	338.2
160°	356.5	350.4	347.4	347.4
162.5°	361.1	356.5	354.2	354.2
165°	365.7	361.9	360.3	361.1
167.5°	369.5	366.5	365.7	366.5
170°	372.6	370.3	369.5	371.0
172.5°	374.9	373.3	373.3	374.1
175°	376.4	374.9	375.6	376.4
177.5°	377.1	376.4	377.1	377.9
180°	377.1	377.1	377.1	377.1

(END OF REPORT)