

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011494

Luminaire Tested: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011494
REPORT IS A COMBINATION OF REPORTS P989671 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1025UB50-4F0-XX-W2A-A1
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4712.0 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31
2	85	78	72	67	76	70	65	61	55	52	49	42	39	37	29	28	27
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20
5	65	54	46	40	58	49	42	37	39	34	30	29	26	24	21	19	17
6	60	48	40	35	53	44	37	32	35	30	26	27	23	21	19	17	15
7	55	43	36	30	49	39	33	28	31	27	23	24	21	18	17	15	13
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12
9	47	36	29	24	43	32	26	22	26	21	18	20	17	14	15	12	11
10	44	33	26	21	40	30	24	19	24	19	16	19	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4843	4843	4843	4843
5°	4846	5580	4860	4164
10°	4815	6753	4821	3637
15°	4749	8009	4788	3273
20°	4692	9220	4702	3013
25°	4607	9453	4617	2876
30°	4546	7809	4546	2787
35°	4471	5223	4443	2708
40°	4381	3770	4326	2587
45°	4267	2987	4143	2437
50°	3992	2537	3849	2290
55°	3689	2229	3539	2125
60°	3382	1941	3202	1952
65°	3046	1662	2898	1722
70°	2698	1379	2518	1451
75°	2305	1039	2157	1119
80°	1824	694	1683	736
85°	1258	319	1009	290

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 7810 cd/sqm

TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.3	0.9
10°-20°	142.1	3.0
20°-30°	239.1	5.1
30°-40°	270.3	5.7
40°-50°	242.1	5.1
50°-60°	195.4	4.1
60°-70°	136.2	2.9
70°-80°	71.5	1.5
80°-90°	19.7	0.4
90°-100°	77.9	1.7
100°-110°	235.6	5.0
110°-120°	401.2	8.5
120°-130°	527.8	11.2
130°-140°	593.3	12.6
140°-150°	583.2	12.4
150°-160°	491.0	10.4
160°-170°	326.9	6.9
170°-180°	114.5	2.4
0°-30°	425.5	9.0
0°-40°	695.8	14.8
0°-60°	1133.2	24.1
0°-90°	1360.6	28.9
90°-120°	714.7	15.2
90°-150°	2419.0	51.3
90°-180°	3351.0	71.1
0°-180°	4712.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	450	450	450	450	450	
5°	450	534	451	399	450	43
15°	429	796	432	325	429	121
25°	392	944	393	287	392	181
35°	346	509	344	264	346	217
45°	287	275	279	224	287	220
55°	204	187	195	178	204	182
65°	126	121	120	126	126	125
75°	61	62	57	67	61	65
85°	13	14	10	13	13	15
90°	1	28	1	28	1	5
95°	56	74	56	74	56	62
105°	214	226	214	226	214	229
115°	404	405	404	405	404	400
125°	591	584	591	584	591	527
135°	767	766	767	766	767	591
145°	930	930	930	930	930	581
155°	1065	1063	1065	1063	1065	490
165°	1160	1156	1160	1156	1160	327
175°	1207	1202	1207	1202	1207	115
180°	1210	1210	1210	1210	1210	

TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	451.3	454.7	456.5	459.1	461.7	465.6	466.9	469.1	468.3	470.0	470.9
5°	449.5	455.6	460.8	467.4	473.5	477.8	482.2	489.2	494.4	495.3	499.2
7.5°	446.5	455.2	464.3	473.5	485.3	492.2	500.1	509.7	517.5	530.2	535.0
10°	442.5	454.7	467.8	480.5	496.6	507.5	517.1	533.2	549.3	562.4	574.6
12.5°	436.4	451.7	468.7	487.4	508.4	521.0	534.1	555.5	579.9	599.9	613.0
15°	429.0	448.2	470.0	490.1	513.2	536.7	550.7	574.6	609.5	628.3	661.8
17.5°	422.9	442.5	464.3	495.7	527.1	550.7	560.7	604.7	628.7	660.1	698.0
20°	413.3	438.2	466.1	497.5	538.0	552.4	572.9	617.4	647.0	688.0	734.6
22.5°	403.3	429.9	463.5	496.2	541.5	556.8	584.7	620.0	667.1	707.6	759.1
25°	392.4	421.2	455.2	494.0	538.4	560.7	586.8	630.4	681.5	732.5	780.0
27.5°	381.5	412.9	448.2	487.0	530.2	556.3	582.5	627.8	693.2	748.6	809.2
30°	371.0	402.4	437.7	477.4	522.8	548.0	572.9	629.6	702.4	764.7	825.8
32.5°	359.7	392.0	429.0	462.2	507.9	535.0	562.9	629.6	708.0	774.3	830.1
35°	346.2	379.3	411.1	444.3	489.6	519.7	551.1	625.2	713.3	777.4	811.8
37.5°	333.1	362.3	389.8	422.0	469.6	501.8	538.0	620.0	710.7	764.3	773.9
40°	318.3	347.5	369.7	399.8	449.9	487.4	524.1	613.0	699.3	733.3	705.4
42.5°	303.9	327.0	346.2	375.4	429.9	466.5	506.2	600.4	677.1	684.1	621.3
45°	287.3	303.9	320.9	354.0	408.1	445.6	489.6	582.0	641.3	621.3	541.9
47.5°	266.0	280.8	299.5	330.0	385.0	423.8	465.6	558.5	589.5	547.6	460.8
50°	245.5	258.1	275.5	305.2	360.6	398.5	443.0	521.4	536.7	470.9	397.2
52.5°	225.0	234.6	251.6	281.2	336.6	373.2	413.8	483.5	474.8	404.2	338.8
55°	203.6	211.9	228.0	257.2	308.7	343.6	382.4	436.9	414.2	347.0	294.7
57.5°	182.7	191.4	208.0	232.4	280.8	314.8	345.7	388.5	354.5	300.8	254.6
60°	163.9	171.3	184.0	208.0	252.0	279.5	307.8	337.0	308.7	256.8	221.5
62.5°	144.3	151.3	163.1	184.9	222.8	247.2	269.9	293.9	262.5	224.5	193.1
65°	126.0	131.7	142.6	162.6	193.6	213.6	231.9	248.5	223.2	188.3	164.8
67.5°	109.4	114.2	123.4	141.3	167.4	181.8	196.6	210.6	189.2	161.3	141.3
70°	91.6	95.5	103.8	116.8	137.8	152.6	163.5	174.0	154.8	132.5	119.0
72.5°	75.9	79.8	85.0	98.5	112.9	122.1	133.8	139.5	128.6	110.3	96.8
75°	60.6	63.7	68.5	77.2	90.7	96.8	104.2	108.6	98.5	86.3	78.0
77.5°	47.5	48.8	52.3	58.4	67.6	74.6	80.2	82.8	75.9	68.0	61.0
80°	33.6	35.3	37.9	43.2	50.1	52.3	55.8	58.9	54.5	47.5	43.2
82.5°	22.2	24.4	25.7	27.9	32.3	34.9	35.8	38.4	34.4	31.8	30.1
85°	13.1	14.0	14.4	15.7	17.9	19.2	20.5	20.9	20.1	19.6	17.9
87.5°	6.5	6.5	6.5	7.4	7.8	8.7	9.2	9.2	9.2	8.7	8.3
90°	1.0	3.1	5.2	7.3	9.4	10.5	11.9	14.6	17.3	20.1	22.8
92.5°	28.5	29.8	31.0	32.3	33.6	34.2	34.8	36.1	37.4	38.6	39.9
95°	56.1	57.6	59.0	60.5	62.0	62.7	63.5	65.2	66.9	68.6	70.3
97.5°	92.2	93.2	94.3	95.3	96.4	96.9	97.5	98.8	100.1	101.3	102.6
100°	129.2	130.5	131.7	133.0	134.3	134.9	135.4	136.5	137.6	138.6	139.7
102.5°	172.0	172.6	173.2	173.9	174.5	174.8	175.5	177.0	178.5	180.0	181.5
105°	213.8	214.2	214.6	215.1	215.5	215.7	216.6	218.5	220.4	222.3	224.2
107.5°	263.2	263.4	263.6	263.8	264.0	264.1	264.5	265.4	266.2	267.1	267.9
110°	308.8	309.2	309.6	310.1	310.5	310.7	310.9	311.3	311.8	312.2	312.6

TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	356.3	356.5	356.7	357.0	357.2	357.3	357.3	357.3	357.3	357.3	357.3
115°	403.8	404.4	405.1	405.7	406.4	406.7	406.5	406.1	405.6	405.2	404.8
117.5°	452.3	452.5	452.7	452.9	453.1	453.2	453.0	452.6	452.1	451.7	451.3
120°	496.9	498.2	499.4	500.7	502.0	502.6	502.1	501.0	500.0	498.9	497.9
122.5°	543.5	544.3	545.2	546.0	546.9	547.3	547.1	546.7	546.2	545.8	545.4
125°	591.0	591.6	592.2	592.9	593.5	593.8	593.6	593.2	592.7	592.3	591.9
127.5°	634.7	636.0	637.2	638.5	639.8	640.4	640.2	639.8	639.3	638.9	638.5
130°	678.4	680.1	681.8	683.5	685.2	686.0	685.7	685.1	684.4	683.8	683.2
132.5°	722.1	723.8	725.5	727.2	728.9	729.7	729.5	729.1	728.6	728.2	727.8
135°	766.8	768.1	769.3	770.6	771.9	772.5	772.4	772.2	771.9	771.7	771.5
137.5°	807.6	808.7	809.7	810.8	811.9	812.4	812.7	813.3	814.0	814.6	815.2
140°	850.4	851.4	852.5	853.5	854.6	855.1	855.2	855.4	855.7	855.9	856.1
142.5°	889.3	890.4	891.4	892.5	893.6	894.1	894.3	894.7	895.2	895.6	896.0
145°	930.2	930.6	931.0	931.5	931.9	932.1	932.4	933.1	933.7	934.4	935.0
147.5°	965.4	966.2	967.1	967.9	968.8	969.2	969.5	970.1	970.8	971.4	972.0
150°	1002.4	1002.8	1003.2	1003.7	1004.1	1004.3	1004.5	1004.9	1005.4	1005.8	1006.2
152.5°	1032.8	1033.4	1034.1	1034.7	1035.4	1035.7	1035.8	1036.0	1036.2	1036.4	1036.6
155°	1065.1	1065.1	1065.1	1065.1	1065.1	1065.1	1065.2	1065.4	1065.7	1065.9	1066.1
157.5°	1092.7	1092.5	1092.3	1092.0	1091.8	1091.7	1091.8	1092.0	1092.3	1092.5	1092.7
160°	1118.3	1117.9	1117.5	1117.0	1116.6	1116.4	1116.4	1116.4	1116.4	1116.4	1116.4
162.5°	1141.1	1140.5	1139.9	1139.2	1138.6	1138.3	1138.4	1138.6	1138.8	1139.0	1139.2
165°	1160.1	1159.5	1158.9	1158.2	1157.6	1157.3	1157.3	1157.3	1157.3	1157.3	1157.3
167.5°	1176.3	1175.5	1174.6	1173.8	1172.9	1172.5	1172.6	1172.8	1173.0	1173.2	1173.4
170°	1189.6	1188.8	1187.9	1187.1	1186.2	1185.8	1185.8	1185.8	1185.8	1185.8	1185.8
172.5°	1200.0	1199.2	1198.3	1197.5	1196.6	1196.2	1196.2	1196.2	1196.2	1196.2	1196.2
175°	1206.7	1205.9	1205.0	1204.2	1203.3	1202.9	1202.9	1202.9	1202.9	1202.9	1202.9
177.5°	1210.5	1209.7	1208.8	1208.0	1207.1	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7
180°	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5

TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	473.9	474.8	477.8	480.0	484.4	484.0	484.0	483.5	482.2	484.4	485.7
5°	507.1	514.5	515.3	524.9	525.4	529.3	531.9	529.7	535.0	534.5	530.6
7.5°	548.0	558.1	562.9	572.0	582.5	579.9	589.9	591.6	590.8	595.1	598.2
10°	592.9	610.4	622.6	639.6	644.0	646.6	653.1	658.8	670.1	661.4	667.1
12.5°	644.4	657.0	673.2	700.2	713.7	722.4	725.5	729.4	737.3	732.5	732.9
15°	687.6	704.6	732.0	765.6	769.5	780.4	777.8	801.4	812.7	795.7	805.3
17.5°	732.5	755.1	787.8	817.0	833.6	841.0	848.0	870.7	869.8	867.2	869.4
20°	761.2	798.3	838.8	877.7	882.4	888.1	906.9	916.5	914.7	922.1	926.9
22.5°	801.8	841.0	884.2	909.9	920.8	927.4	942.2	948.3	950.9	952.6	949.6
25°	835.8	877.7	909.5	932.1	938.7	942.2	947.0	948.7	947.4	944.4	947.0
27.5°	858.9	892.5	914.3	924.7	921.2	915.6	906.4	900.3	886.8	880.3	888.1
30°	868.5	883.3	889.9	872.4	855.0	841.0	823.6	791.3	766.0	773.4	763.4
32.5°	853.2	843.6	812.3	767.3	753.8	731.2	681.9	644.0	645.3	625.2	633.5
35°	808.3	764.7	705.4	637.4	619.5	607.3	553.3	545.0	527.5	508.8	514.0
37.5°	729.0	665.3	593.4	543.2	516.6	490.1	459.5	441.2	430.8	422.9	429.0
40°	632.2	554.6	495.3	450.4	427.7	410.7	389.8	371.5	359.7	358.4	360.6
42.5°	537.1	471.7	417.2	374.5	367.1	347.0	333.5	319.1	315.7	310.0	313.0
45°	454.7	401.5	356.6	321.8	313.0	307.8	291.2	282.1	278.2	274.7	279.9
47.5°	395.0	339.2	306.5	285.6	276.9	268.1	259.0	252.9	249.8	250.3	249.8
50°	337.5	296.5	267.7	251.6	246.3	240.2	232.8	228.9	227.6	223.7	226.7
52.5°	290.4	260.7	240.7	225.4	221.5	217.1	211.0	208.8	205.8	204.9	204.9
55°	252.4	229.3	213.2	203.2	198.4	194.9	191.4	188.8	186.6	186.6	186.6
57.5°	222.8	202.7	191.0	182.2	180.5	177.0	173.1	173.1	170.0	169.6	170.9
60°	197.5	179.6	170.5	163.1	160.4	159.6	155.6	155.6	154.8	152.6	154.3
62.5°	171.8	158.7	150.9	145.2	142.6	142.6	139.5	137.3	137.3	137.8	136.9
65°	148.2	138.6	131.7	127.3	126.0	124.3	123.8	122.1	120.8	121.2	120.8
67.5°	127.3	119.9	115.1	111.6	109.4	108.6	107.3	107.3	106.4	106.8	104.6
70°	108.6	101.1	97.2	93.7	92.9	92.9	91.1	91.6	90.7	92.0	91.1
72.5°	89.4	83.7	80.7	79.4	78.5	78.0	77.2	76.3	75.9	76.7	76.3
75°	72.4	67.6	65.4	64.5	63.7	63.7	63.2	62.8	62.3	62.3	62.3
77.5°	56.2	53.2	50.6	51.4	50.1	50.6	49.3	49.3	49.7	49.3	49.3
80°	41.4	39.2	39.2	38.4	36.6	37.5	37.5	36.2	35.8	36.6	35.3
82.5°	27.5	27.0	26.2	25.7	24.9	25.3	24.9	24.4	24.0	24.9	24.0
85°	16.1	16.1	15.7	14.8	15.7	15.3	14.8	14.8	14.4	14.4	14.4
87.5°	8.3	7.4	7.4	7.0	7.4	6.5	7.0	6.5	6.1	6.5	6.1
90°	23.6	24.5	25.3	26.2	26.6	26.8	27.2	27.7	28.1	28.5	28.1
92.5°	40.5	41.2	41.8	42.5	42.8	42.6	42.2	41.7	41.3	40.9	41.3
95°	71.1	72.0	72.8	73.7	74.1	74.1	74.1	74.1	74.1	74.1	74.1
97.5°	103.7	104.7	105.8	106.9	107.4	107.3	107.1	106.8	106.6	106.4	106.6
100°	140.3	140.9	141.6	142.2	142.5	142.7	143.1	143.6	144.0	144.4	144.0
102.5°	182.1	182.7	183.4	184.0	184.3	184.2	184.0	183.8	183.6	183.4	183.6
105°	224.2	224.2	224.2	224.2	224.2	224.4	224.8	225.3	225.7	226.1	225.7
107.5°	268.5	269.2	269.8	270.5	270.8	270.7	270.5	270.2	270.0	269.8	270.0
110°	313.4	314.3	315.1	316.0	316.4	316.2	315.8	315.3	314.9	314.5	314.9

TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	358.3	359.4	360.4	361.5	362.0	362.0	362.0	362.0	362.0	362.0	362.0
115°	405.0	405.2	405.4	405.6	405.7	405.6	405.4	405.2	405.0	404.8	405.0
117.5°	451.3	451.3	451.3	451.3	451.3	451.0	450.4	449.7	449.1	448.5	449.1
120°	497.7	497.5	497.2	497.0	496.9	496.7	496.3	495.8	495.4	495.0	495.4
122.5°	544.8	544.1	543.5	542.8	542.5	542.2	541.6	540.9	540.3	539.7	540.3
125°	591.1	590.2	589.4	588.5	588.1	587.7	586.8	586.0	585.1	584.3	585.1
127.5°	637.2	636.0	634.7	633.4	632.8	632.4	631.5	630.7	629.8	629.0	629.8
130°	682.4	681.5	680.7	679.8	679.4	678.7	677.2	675.7	674.2	672.7	674.2
132.5°	726.8	725.7	724.7	723.6	723.1	722.6	721.5	720.4	719.4	718.3	719.4
135°	770.7	769.8	769.0	768.1	767.7	767.5	767.1	766.6	766.2	765.8	766.2
137.5°	814.2	813.1	812.1	811.0	810.5	810.2	809.5	808.9	808.2	807.6	808.2
140°	855.9	855.7	855.4	855.2	855.1	854.4	852.9	851.4	850.0	848.5	850.0
142.5°	895.8	895.6	895.3	895.1	895.0	894.5	893.4	892.4	891.3	890.3	891.3
145°	934.8	934.6	934.3	934.1	934.0	933.6	932.7	931.9	931.0	930.2	931.0
147.5°	972.0	972.0	972.0	972.0	972.0	971.4	970.1	968.8	967.6	966.3	967.6
150°	1006.2	1006.2	1006.2	1006.2	1006.2	1005.6	1004.3	1003.0	1001.8	1000.5	1001.8
152.5°	1037.0	1037.4	1037.9	1038.3	1038.5	1038.0	1036.9	1035.9	1034.8	1033.8	1034.8
155°	1066.9	1067.8	1068.6	1069.5	1069.9	1069.2	1067.7	1066.2	1064.7	1063.2	1064.7
157.5°	1093.5	1094.4	1095.2	1096.1	1096.5	1095.9	1094.6	1093.3	1092.1	1090.8	1092.1
160°	1117.5	1118.5	1119.6	1120.7	1121.2	1120.8	1119.9	1119.1	1118.2	1117.4	1118.2
162.5°	1140.3	1141.3	1142.4	1143.5	1144.0	1143.3	1141.8	1140.3	1138.8	1137.3	1138.8
165°	1158.6	1159.8	1161.1	1162.4	1163.0	1162.3	1160.8	1159.3	1157.8	1156.3	1157.8
167.5°	1174.7	1175.9	1177.2	1178.5	1179.1	1178.5	1177.2	1175.9	1174.7	1173.4	1174.7
170°	1187.3	1188.7	1190.2	1191.7	1192.4	1191.7	1190.2	1188.7	1187.3	1185.8	1187.3
172.5°	1197.5	1198.7	1200.0	1201.3	1201.9	1201.2	1199.7	1198.2	1196.8	1195.3	1196.8
175°	1204.2	1205.4	1206.7	1208.0	1208.6	1207.9	1206.4	1204.9	1203.4	1201.9	1203.4
177.5°	1208.0	1209.2	1210.5	1211.8	1212.4	1211.7	1210.2	1208.7	1207.2	1205.7	1207.2
180°	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5

TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	482.2	483.5	480.0	479.2	479.2	480.9	479.6	467.8	470.0	467.4	466.5
5°	535.4	532.8	529.3	527.5	525.4	519.3	518.8	505.3	502.7	494.0	490.1
7.5°	593.8	591.6	581.2	579.9	579.0	573.3	558.9	544.6	534.1	524.1	514.5
10°	660.5	654.0	649.2	639.6	634.8	627.0	608.2	594.7	576.8	561.6	541.5
12.5°	740.7	733.3	717.2	710.2	704.1	682.3	663.6	648.3	613.4	603.0	578.1
15°	799.6	783.9	782.2	766.9	766.0	742.1	706.3	689.7	662.7	624.3	598.6
17.5°	863.3	849.3	838.4	820.1	817.5	794.8	768.7	728.1	698.5	661.8	629.1
20°	909.9	902.5	883.8	876.3	861.1	841.9	814.9	764.7	728.5	691.9	651.8
22.5°	947.0	939.6	924.7	914.7	906.0	881.1	848.9	806.1	756.4	708.5	667.1
25°	946.5	944.4	938.3	933.5	926.9	908.6	881.6	840.6	785.2	732.5	674.9
27.5°	892.9	899.0	909.5	914.7	913.4	910.8	895.5	861.1	811.4	748.6	684.1
30°	781.3	803.5	823.2	849.3	857.2	876.3	885.1	865.4	825.8	767.3	695.8
32.5°	647.9	680.1	722.9	737.3	762.1	799.2	840.6	848.0	823.2	778.2	703.3
35°	531.5	558.1	591.2	613.9	636.1	696.3	748.6	793.9	802.2	772.6	701.5
37.5°	439.9	458.7	487.9	507.1	527.5	579.0	652.2	711.1	752.5	753.4	696.7
40°	373.6	381.9	407.2	421.2	440.8	485.3	550.7	627.4	688.0	715.9	684.1
42.5°	316.5	327.4	348.4	358.8	371.5	410.3	453.4	526.2	601.2	661.0	660.5
45°	282.5	290.4	300.0	308.7	323.1	346.2	395.4	449.9	521.9	589.5	616.1
47.5°	252.4	259.9	269.4	272.1	281.7	303.4	333.5	381.1	448.2	515.3	565.5
50°	227.2	233.3	239.8	244.6	249.0	266.8	289.5	329.6	383.2	448.2	510.5
52.5°	207.5	211.9	217.6	220.2	224.1	237.2	254.6	284.3	328.3	387.6	448.2
55°	189.2	192.3	195.8	200.1	201.9	211.5	225.0	250.3	283.0	336.1	393.7
57.5°	172.2	173.5	175.7	178.3	180.5	188.8	200.6	217.6	246.3	287.3	341.8
60°	153.0	156.5	157.8	160.4	161.8	168.3	177.4	191.8	214.1	249.4	290.4
62.5°	136.9	139.1	141.3	142.6	145.6	147.8	155.2	168.3	186.6	212.8	249.8
65°	122.5	123.4	124.7	126.0	126.9	129.5	136.5	145.2	159.1	182.2	211.0
67.5°	105.9	106.8	108.6	109.0	109.9	113.4	117.3	124.7	136.5	153.9	177.4
70°	89.8	91.1	92.0	92.9	94.2	95.5	99.8	105.9	115.1	127.3	145.6
72.5°	75.9	77.2	77.2	78.0	77.6	79.4	83.7	88.1	94.2	104.2	120.3
75°	61.9	61.9	62.8	63.2	63.7	65.4	67.1	70.6	75.4	83.3	93.3
77.5°	48.8	48.4	49.3	49.3	49.3	50.6	52.3	54.1	57.1	62.8	70.6
80°	35.8	35.8	36.6	37.1	36.2	36.6	37.5	39.2	41.4	45.3	49.7
82.5°	23.5	25.3	24.9	25.3	24.9	25.7	26.2	26.6	27.5	29.2	32.3
85°	14.4	14.4	14.4	14.8	14.4	14.8	14.8	14.8	15.3	16.1	17.4
87.5°	6.1	6.1	6.1	6.5	6.1	6.1	6.5	6.1	6.5	6.5	7.0
90°	27.7	27.2	26.8	26.6	26.2	25.3	24.5	23.6	22.8	20.1	17.3
92.5°	41.7	42.2	42.6	42.8	42.5	41.8	41.2	40.5	39.9	38.6	37.4
95°	74.1	74.1	74.1	74.1	73.7	72.8	72.0	71.1	70.3	68.6	66.9
97.5°	106.8	107.1	107.3	107.4	106.9	105.8	104.7	103.7	102.6	101.3	100.1
100°	143.6	143.1	142.7	142.5	142.2	141.6	140.9	140.3	139.7	138.6	137.6
102.5°	183.8	184.0	184.2	184.3	184.0	183.4	182.7	182.1	181.5	180.0	178.5
105°	225.3	224.8	224.4	224.2	224.2	224.2	224.2	224.2	224.2	222.3	220.4
107.5°	270.2	270.5	270.7	270.8	270.5	269.8	269.2	268.5	267.9	267.1	266.2
110°	315.3	315.8	316.2	316.4	316.0	315.1	314.3	313.4	312.6	312.2	311.8

TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	362.0	362.0	362.0	362.0	361.5	360.4	359.4	358.3	357.3	357.3	357.3
115°	405.2	405.4	405.6	405.7	405.6	405.4	405.2	405.0	404.8	405.2	405.6
117.5°	449.7	450.4	451.0	451.3	451.3	451.3	451.3	451.3	451.3	451.7	452.1
120°	495.8	496.3	496.7	496.9	497.0	497.2	497.5	497.7	497.9	498.9	500.0
122.5°	540.9	541.6	542.2	542.5	542.8	543.5	544.1	544.8	545.4	545.8	546.2
125°	586.0	586.8	587.7	588.1	588.5	589.4	590.2	591.1	591.9	592.3	592.7
127.5°	630.7	631.5	632.4	632.8	633.4	634.7	636.0	637.2	638.5	638.9	639.3
130°	675.7	677.2	678.7	679.4	679.8	680.7	681.5	682.4	683.2	683.8	684.4
132.5°	720.4	721.5	722.6	723.1	723.6	724.7	725.7	726.8	727.8	728.2	728.6
135°	766.6	767.1	767.5	767.7	768.1	769.0	769.8	770.7	771.5	771.7	771.9
137.5°	808.9	809.5	810.2	810.5	811.0	812.1	813.1	814.2	815.2	814.6	814.0
140°	851.4	852.9	854.4	855.1	855.2	855.4	855.7	855.9	856.1	855.9	855.7
142.5°	892.4	893.4	894.5	895.0	895.1	895.3	895.6	895.8	896.0	895.6	895.2
145°	931.9	932.7	933.6	934.0	934.1	934.3	934.6	934.8	935.0	934.4	933.7
147.5°	968.8	970.1	971.4	972.0	972.0	972.0	972.0	972.0	972.0	971.4	970.8
150°	1003.0	1004.3	1005.6	1006.2	1006.2	1006.2	1006.2	1006.2	1006.2	1005.8	1005.4
152.5°	1035.9	1036.9	1038.0	1038.5	1038.3	1037.9	1037.4	1037.0	1036.6	1036.4	1036.2
155°	1066.2	1067.7	1069.2	1069.9	1069.5	1068.6	1067.8	1066.9	1066.1	1065.9	1065.7
157.5°	1093.3	1094.6	1095.9	1096.5	1096.1	1095.2	1094.4	1093.5	1092.7	1092.5	1092.3
160°	1119.1	1119.9	1120.8	1121.2	1120.7	1119.6	1118.5	1117.5	1116.4	1116.4	1116.4
162.5°	1140.3	1141.8	1143.3	1144.0	1143.5	1142.4	1141.3	1140.3	1139.2	1139.0	1138.8
165°	1159.3	1160.8	1162.3	1163.0	1162.4	1161.1	1159.8	1158.6	1157.3	1157.3	1157.3
167.5°	1175.9	1177.2	1178.5	1179.1	1178.5	1177.2	1175.9	1174.7	1173.4	1173.2	1173.0
170°	1188.7	1190.2	1191.7	1192.4	1191.7	1190.2	1188.7	1187.3	1185.8	1185.8	1185.8
172.5°	1198.2	1199.7	1201.2	1201.9	1201.3	1200.0	1198.7	1197.5	1196.2	1196.2	1196.2
175°	1204.9	1206.4	1207.9	1208.6	1208.0	1206.7	1205.4	1204.2	1202.9	1202.9	1202.9
177.5°	1208.7	1210.2	1211.7	1212.4	1211.8	1210.5	1209.2	1208.0	1206.7	1206.7	1206.7
180°	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5

TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	462.2	460.8	460.8	460.0	457.4	452.6	452.1	453.0	450.4	447.8	443.8
5°	484.8	476.5	473.9	471.3	466.1	457.4	453.9	450.8	446.0	440.4	434.2
7.5°	504.0	492.2	488.7	484.0	473.5	461.3	453.4	446.9	440.4	432.5	425.1
10°	528.0	511.0	502.7	495.7	481.3	464.3	452.6	443.0	432.5	422.9	413.3
12.5°	555.0	527.5	524.9	507.9	491.4	466.1	451.7	437.7	423.8	412.0	402.0
15°	577.7	547.6	536.7	525.4	493.5	462.2	448.2	432.5	416.4	403.7	388.9
17.5°	592.1	567.2	544.1	528.9	495.7	467.8	440.8	422.9	405.9	388.5	376.3
20°	609.5	573.3	553.3	532.8	500.1	463.5	436.4	414.2	393.3	377.6	362.7
22.5°	627.0	578.1	561.6	539.3	501.0	459.1	428.6	406.3	382.4	366.7	350.5
25°	625.2	585.1	557.6	538.9	492.2	455.2	419.4	393.3	371.0	351.0	334.8
27.5°	626.5	577.3	549.3	527.5	486.1	449.5	409.8	382.4	359.3	338.3	321.3
30°	627.0	565.5	541.1	514.9	474.8	436.0	398.9	371.0	346.6	323.9	308.7
32.5°	625.6	555.9	525.4	501.8	456.9	422.9	386.3	356.6	331.8	310.9	296.5
35°	622.6	544.6	509.2	479.6	438.6	404.2	374.5	344.0	317.4	298.2	281.7
37.5°	614.3	532.3	492.2	463.0	417.2	382.4	356.2	330.9	305.2	282.5	268.6
40°	608.2	515.8	475.2	443.4	394.1	360.1	338.3	314.3	289.1	268.6	255.1
42.5°	594.3	500.1	457.8	419.9	371.5	336.6	316.1	296.9	275.1	255.1	242.8
45°	571.6	483.1	436.4	398.1	346.6	313.5	294.7	279.0	259.9	240.7	228.5
47.5°	539.8	458.7	413.8	375.4	322.2	288.6	269.9	258.1	242.8	226.7	216.3
50°	505.3	432.1	390.6	352.7	298.7	266.0	247.6	236.7	226.7	211.9	201.9
52.5°	460.4	403.7	364.1	327.9	273.4	242.0	225.8	218.0	207.5	197.1	188.3
55°	416.8	367.1	334.4	300.0	248.5	219.3	203.6	195.3	189.2	180.5	173.5
57.5°	366.2	333.1	303.0	271.6	225.4	198.8	184.0	174.0	170.0	166.1	159.6
60°	319.6	294.3	269.9	243.7	201.4	177.4	163.1	155.2	151.3	148.7	144.3
62.5°	276.9	257.2	236.3	215.4	177.0	155.2	144.3	136.5	133.0	132.5	128.6
65°	235.9	221.9	204.9	184.4	154.3	135.2	124.7	119.9	116.0	116.0	112.9
67.5°	194.9	185.3	171.8	157.4	133.8	116.0	106.4	102.0	99.8	99.8	97.7
70°	162.2	155.6	143.4	130.8	110.3	96.8	89.4	85.5	84.1	84.6	82.8
72.5°	131.7	124.7	114.7	105.5	90.3	80.2	75.0	70.6	68.5	68.9	68.5
75°	102.0	98.5	89.8	82.8	70.6	63.7	58.9	56.7	54.9	55.4	54.5
77.5°	76.7	71.5	66.7	61.9	54.5	48.8	44.9	42.7	41.4	41.4	41.4
80°	52.3	51.4	47.5	44.9	38.8	34.4	31.4	31.0	29.6	29.6	29.6
82.5°	34.0	31.8	29.6	27.9	24.4	21.8	20.5	19.6	19.2	18.7	19.6
85°	18.7	17.4	16.6	14.8	13.5	12.2	10.9	10.5	10.0	10.5	10.0
87.5°	7.4	6.1	6.1	5.7	5.2	4.8	4.8	3.9	3.9	3.5	3.5
90°	14.6	11.9	10.5	9.4	7.3	5.2	3.1	1.0	3.1	5.2	7.3
92.5°	36.1	34.8	34.2	33.6	32.3	31.0	29.8	28.5	29.8	31.0	32.3
95°	65.2	63.5	62.7	62.0	60.5	59.0	57.6	56.1	57.6	59.0	60.5
97.5°	98.8	97.5	96.9	96.4	95.3	94.3	93.2	92.2	93.2	94.3	95.3
100°	136.5	135.4	134.9	134.3	133.0	131.7	130.5	129.2	130.5	131.7	133.0
102.5°	177.0	175.5	174.8	174.5	173.9	173.2	172.6	172.0	172.6	173.2	173.9
105°	218.5	216.6	215.7	215.5	215.1	214.6	214.2	213.8	214.2	214.6	215.1
107.5°	265.4	264.5	264.1	264.0	263.8	263.6	263.4	263.2	263.4	263.6	263.8
110°	311.3	310.9	310.7	310.5	310.1	309.6	309.2	308.8	309.2	309.6	310.1

TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	357.3	357.3	357.3	357.2	357.0	356.7	356.5	356.3	356.5	356.7	357.0
115°	406.1	406.5	406.7	406.4	405.7	405.1	404.4	403.8	404.4	405.1	405.7
117.5°	452.6	453.0	453.2	453.1	452.9	452.7	452.5	452.3	452.5	452.7	452.9
120°	501.0	502.1	502.6	502.0	500.7	499.4	498.2	496.9	498.2	499.4	500.7
122.5°	546.7	547.1	547.3	546.9	546.0	545.2	544.3	543.5	544.3	545.2	546.0
125°	593.2	593.6	593.8	593.5	592.9	592.2	591.6	591.0	591.6	592.2	592.9
127.5°	639.8	640.2	640.4	639.8	638.5	637.2	636.0	634.7	636.0	637.2	638.5
130°	685.1	685.7	686.0	685.2	683.5	681.8	680.1	678.4	680.1	681.8	683.5
132.5°	729.1	729.5	729.7	728.9	727.2	725.5	723.8	722.1	723.8	725.5	727.2
135°	772.2	772.4	772.5	771.9	770.6	769.3	768.1	766.8	768.1	769.3	770.6
137.5°	813.3	812.7	812.4	811.9	810.8	809.7	808.7	807.6	808.7	809.7	810.8
140°	855.4	855.2	855.1	854.6	853.5	852.5	851.4	850.4	851.4	852.5	853.5
142.5°	894.7	894.3	894.1	893.6	892.5	891.4	890.4	889.3	890.4	891.4	892.5
145°	933.1	932.4	932.1	931.9	931.5	931.0	930.6	930.2	930.6	931.0	931.5
147.5°	970.1	969.5	969.2	968.8	967.9	967.1	966.2	965.4	966.2	967.1	967.9
150°	1004.9	1004.5	1004.3	1004.1	1003.7	1003.2	1002.8	1002.4	1002.8	1003.2	1003.7
152.5°	1036.0	1035.8	1035.7	1035.4	1034.7	1034.1	1033.4	1032.8	1033.4	1034.1	1034.7
155°	1065.4	1065.2	1065.1	1065.1	1065.1	1065.1	1065.1	1065.1	1065.1	1065.1	1065.1
157.5°	1092.0	1091.8	1091.7	1091.8	1092.0	1092.3	1092.5	1092.7	1092.5	1092.3	1092.0
160°	1116.4	1116.4	1116.4	1116.6	1117.0	1117.5	1117.9	1118.3	1117.9	1117.5	1117.0
162.5°	1138.6	1138.4	1138.3	1138.6	1139.2	1139.9	1140.5	1141.1	1140.5	1139.9	1139.2
165°	1157.3	1157.3	1157.3	1157.6	1158.2	1158.9	1159.5	1160.1	1159.5	1158.9	1158.2
167.5°	1172.8	1172.6	1172.5	1172.9	1173.8	1174.6	1175.5	1176.3	1175.5	1174.6	1173.8
170°	1185.8	1185.8	1185.8	1186.2	1187.1	1187.9	1188.8	1189.6	1188.8	1187.9	1187.1
172.5°	1196.2	1196.2	1196.2	1196.6	1197.5	1198.3	1199.2	1200.0	1199.2	1198.3	1197.5
175°	1202.9	1202.9	1202.9	1203.3	1204.2	1205.0	1205.9	1206.7	1205.9	1205.0	1204.2
177.5°	1206.7	1206.7	1206.7	1207.1	1208.0	1208.8	1209.7	1210.5	1209.7	1208.8	1208.0
180°	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5

TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	443.0	442.5	443.4	440.8	436.4	434.2	428.1	426.8	426.4	426.8	427.3
5°	430.8	430.3	429.0	424.7	419.4	415.5	408.1	407.7	405.0	402.4	403.7
7.5°	419.0	417.2	414.6	409.0	402.0	397.6	391.5	387.2	383.7	381.5	379.7
10°	407.2	404.6	402.0	394.6	385.9	379.3	371.9	368.4	364.5	362.7	361.0
12.5°	392.0	389.3	384.5	375.8	370.6	362.3	354.9	351.4	349.2	345.7	343.6
15°	379.7	374.5	371.9	362.7	351.8	351.0	337.5	336.6	332.2	332.2	328.7
17.5°	365.8	361.9	357.1	347.9	340.1	332.2	325.2	322.6	318.7	317.8	316.1
20°	352.3	347.0	345.3	336.1	327.9	318.3	310.9	308.2	306.5	304.8	306.1
22.5°	338.3	334.0	329.6	321.3	315.2	305.6	301.3	298.7	296.0	295.2	295.6
25°	324.8	320.9	316.5	308.2	301.7	293.9	289.9	288.6	287.3	287.3	286.9
27.5°	311.7	307.8	303.9	296.5	289.9	284.3	281.2	279.9	278.6	279.5	280.3
30°	298.2	294.7	291.2	284.7	279.5	274.2	272.5	271.6	271.2	273.4	273.4
32.5°	286.0	283.0	280.3	274.2	269.0	264.6	263.3	263.8	264.2	265.5	266.4
35°	273.4	271.2	268.6	263.3	259.0	255.1	255.5	255.5	256.4	258.5	260.3
37.5°	262.0	259.0	256.8	252.4	249.0	245.5	246.8	248.1	249.0	251.6	252.4
40°	248.5	247.2	245.5	241.1	238.1	237.6	238.1	238.9	240.7	242.0	243.3
42.5°	237.6	235.9	233.7	230.2	227.6	228.0	228.5	229.3	230.2	232.4	233.7
45°	225.4	224.1	222.4	219.3	217.1	217.6	218.0	218.0	218.9	221.5	222.4
47.5°	211.9	212.3	210.1	207.1	205.8	205.8	205.8	206.7	208.8	209.7	210.1
50°	198.8	197.9	197.5	194.5	193.6	193.1	193.6	194.0	197.1	196.6	197.9
52.5°	184.9	184.9	184.4	182.7	181.4	181.4	180.5	182.7	183.6	184.4	185.7
55°	171.3	170.0	169.6	168.7	167.0	166.5	167.4	170.0	170.9	171.8	173.1
57.5°	156.5	156.5	155.6	154.3	154.3	154.3	154.3	156.1	157.4	158.3	160.9
60°	143.0	141.3	140.0	140.0	140.0	139.5	142.1	142.1	144.7	145.2	146.1
62.5°	126.9	126.0	125.1	125.6	125.1	126.0	126.9	128.6	129.1	130.4	131.7
65°	111.6	111.6	110.7	113.4	111.6	111.6	113.8	113.8	114.7	116.0	117.7
67.5°	96.8	97.2	96.4	96.4	97.2	97.7	98.1	99.8	100.3	102.0	104.2
70°	81.5	82.4	82.8	82.0	82.8	83.7	84.6	85.0	86.8	87.6	88.9
72.5°	68.0	68.9	67.6	68.0	68.5	69.3	69.8	70.6	71.5	74.1	75.0
75°	54.5	54.1	53.6	55.4	54.5	56.2	56.7	56.7	57.6	59.7	60.6
77.5°	41.9	41.9	42.3	41.4	42.7	42.3	42.7	44.0	45.3	45.3	48.8
80°	29.2	30.1	30.1	30.1	30.5	31.0	30.1	32.3	32.7	32.7	34.0
82.5°	18.7	19.2	18.7	19.6	19.6	20.5	20.1	20.5	21.4	22.2	22.7
85°	10.0	10.0	10.9	10.9	10.5	10.9	10.5	10.9	11.8	11.8	12.2
87.5°	3.5	3.5	3.5	3.5	3.9	3.5	3.9	3.9	3.5	3.5	4.8
90°	9.4	10.5	11.9	14.6	17.3	20.1	22.8	23.6	24.5	25.3	26.2
92.5°	33.6	34.2	34.8	36.1	37.4	38.6	39.9	40.5	41.2	41.8	42.5
95°	62.0	62.7	63.5	65.2	66.9	68.6	70.3	71.1	72.0	72.8	73.7
97.5°	96.4	96.9	97.5	98.8	100.1	101.3	102.6	103.7	104.7	105.8	106.9
100°	134.3	134.9	135.4	136.5	137.6	138.6	139.7	140.3	140.9	141.6	142.2
102.5°	174.5	174.8	175.5	177.0	178.5	180.0	181.5	182.1	182.7	183.4	184.0
105°	215.5	215.7	216.6	218.5	220.4	222.3	224.2	224.2	224.2	224.2	224.2
107.5°	264.0	264.1	264.5	265.4	266.2	267.1	267.9	268.5	269.2	269.8	270.5
110°	310.5	310.7	310.9	311.3	311.8	312.2	312.6	313.4	314.3	315.1	316.0

TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	357.2	357.3	357.3	357.3	357.3	357.3	357.3	358.3	359.4	360.4	361.5
115°	406.4	406.7	406.5	406.1	405.6	405.2	404.8	405.0	405.2	405.4	405.6
117.5°	453.1	453.2	453.0	452.6	452.1	451.7	451.3	451.3	451.3	451.3	451.3
120°	502.0	502.6	502.1	501.0	500.0	498.9	497.9	497.7	497.5	497.2	497.0
122.5°	546.9	547.3	547.1	546.7	546.2	545.8	545.4	544.8	544.1	543.5	542.8
125°	593.5	593.8	593.6	593.2	592.7	592.3	591.9	591.1	590.2	589.4	588.5
127.5°	639.8	640.4	640.2	639.8	639.3	638.9	638.5	637.2	636.0	634.7	633.4
130°	685.2	686.0	685.7	685.1	684.4	683.8	683.2	682.4	681.5	680.7	679.8
132.5°	728.9	729.7	729.5	729.1	728.6	728.2	727.8	726.8	725.7	724.7	723.6
135°	771.9	772.5	772.4	772.2	771.9	771.7	771.5	770.7	769.8	769.0	768.1
137.5°	811.9	812.4	812.7	813.3	814.0	814.6	815.2	814.2	813.1	812.1	811.0
140°	854.6	855.1	855.2	855.4	855.7	855.9	856.1	855.9	855.7	855.4	855.2
142.5°	893.6	894.1	894.3	894.7	895.2	895.6	896.0	895.8	895.6	895.3	895.1
145°	931.9	932.1	932.4	933.1	933.7	934.4	935.0	934.8	934.6	934.3	934.1
147.5°	968.8	969.2	969.5	970.1	970.8	971.4	972.0	972.0	972.0	972.0	972.0
150°	1004.1	1004.3	1004.5	1004.9	1005.4	1005.8	1006.2	1006.2	1006.2	1006.2	1006.2
152.5°	1035.4	1035.7	1035.8	1036.0	1036.2	1036.4	1036.6	1037.0	1037.4	1037.9	1038.3
155°	1065.1	1065.1	1065.2	1065.4	1065.7	1065.9	1066.1	1066.9	1067.8	1068.6	1069.5
157.5°	1091.8	1091.7	1091.8	1092.0	1092.3	1092.5	1092.7	1093.5	1094.4	1095.2	1096.1
160°	1116.6	1116.4	1116.4	1116.4	1116.4	1116.4	1116.4	1117.5	1118.5	1119.6	1120.7
162.5°	1138.6	1138.3	1138.4	1138.6	1138.8	1139.0	1139.2	1140.3	1141.3	1142.4	1143.5
165°	1157.6	1157.3	1157.3	1157.3	1157.3	1157.3	1157.3	1158.6	1159.8	1161.1	1162.4
167.5°	1172.9	1172.5	1172.6	1172.8	1173.0	1173.2	1173.4	1174.7	1175.9	1177.2	1178.5
170°	1186.2	1185.8	1185.8	1185.8	1185.8	1185.8	1185.8	1187.3	1188.7	1190.2	1191.7
172.5°	1196.6	1196.2	1196.2	1196.2	1196.2	1196.2	1196.2	1197.5	1198.7	1200.0	1201.3
175°	1203.3	1202.9	1202.9	1202.9	1202.9	1202.9	1202.9	1204.2	1205.4	1206.7	1208.0
177.5°	1207.1	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1208.0	1209.2	1210.5	1211.8
180°	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5

TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	426.8	427.3	425.5	424.2	427.7	425.5	425.5	426.0	425.1	426.4	426.0
5°	402.9	403.3	400.2	401.1	399.4	398.9	398.5	401.1	400.7	400.2	401.1
7.5°	379.3	379.3	378.0	377.1	377.1	375.8	377.6	377.1	378.0	378.0	379.3
10°	359.7	360.6	358.4	356.2	355.8	356.2	356.2	356.6	357.1	360.1	359.7
12.5°	343.6	342.3	341.8	340.5	338.3	337.5	336.6	341.4	340.1	340.1	340.1
15°	325.7	328.7	328.3	324.4	323.5	325.2	324.4	324.4	328.7	328.3	327.9
17.5°	316.1	315.2	314.3	312.2	312.6	312.2	312.6	312.6	315.2	315.2	315.2
20°	305.2	303.4	303.4	302.6	302.6	301.3	303.0	303.4	305.2	305.2	305.6
22.5°	295.6	294.3	294.3	293.9	294.7	293.0	294.7	295.2	295.2	296.5	296.5
25°	287.3	286.4	286.4	287.3	287.3	287.3	287.3	289.1	287.8	288.2	287.8
27.5°	279.9	280.3	280.8	281.2	280.8	281.2	281.7	282.5	283.0	282.5	281.7
30°	272.9	274.2	274.7	274.7	275.5	276.0	276.4	276.4	276.9	275.5	276.4
32.5°	267.7	267.7	268.6	269.0	269.9	270.3	270.3	271.2	270.8	269.4	269.9
35°	260.3	260.3	262.0	262.9	264.2	263.8	264.2	264.2	264.6	263.8	262.5
37.5°	252.9	253.7	253.7	255.5	255.9	256.4	255.9	256.8	256.4	255.5	255.1
40°	244.2	243.7	244.2	245.5	245.9	245.9	245.9	246.8	246.8	246.8	246.3
42.5°	233.3	234.6	234.1	235.4	235.0	235.0	235.9	236.7	237.2	235.9	236.3
45°	222.8	222.8	223.7	223.7	224.1	224.1	225.8	225.0	225.8	225.0	225.4
47.5°	211.5	211.9	211.9	212.3	213.2	214.1	213.2	213.6	213.6	214.1	213.2
50°	198.8	198.8	199.7	201.0	202.7	201.9	201.4	203.2	201.9	201.9	201.0
52.5°	185.7	187.0	187.5	188.8	190.1	190.5	191.0	190.1	190.5	189.2	189.7
55°	173.1	173.5	175.3	176.6	177.9	177.9	177.4	177.9	178.3	176.6	176.6
57.5°	160.4	161.8	163.5	163.5	165.2	165.2	164.8	164.8	165.2	163.9	163.5
60°	146.9	148.2	150.4	150.4	153.0	153.5	152.6	151.7	151.7	150.4	150.9
62.5°	132.5	133.8	135.2	137.3	139.1	138.2	140.0	138.2	138.6	136.0	136.0
65°	119.9	120.3	122.5	124.7	124.7	125.6	124.7	125.1	123.8	123.8	122.1
67.5°	105.1	105.1	107.3	109.4	111.6	111.6	111.6	110.3	110.3	109.0	109.0
70°	92.0	91.6	93.7	95.0	96.4	96.8	95.9	95.5	94.6	93.3	92.9
72.5°	75.9	76.7	78.9	79.8	82.0	81.5	83.7	81.1	81.1	78.9	78.5
75°	61.5	62.3	64.5	65.8	67.1	67.1	68.5	67.1	65.4	64.5	64.1
77.5°	48.8	48.4	50.1	52.3	52.8	52.3	53.2	52.8	51.0	51.0	50.1
80°	34.9	36.2	37.9	37.5	39.2	38.8	38.8	37.9	37.9	36.6	37.5
82.5°	23.1	24.4	24.9	24.4	24.9	25.7	26.2	25.7	25.7	24.9	25.3
85°	12.2	12.2	13.1	13.5	13.1	13.1	13.5	14.8	14.0	13.1	14.0
87.5°	3.9	3.5	3.5	3.9	3.5	3.5	3.9	3.9	4.4	4.4	4.4
90°	26.6	26.8	27.2	27.7	28.1	28.5	28.1	27.7	27.2	26.8	26.6
92.5°	42.8	42.6	42.2	41.7	41.3	40.9	41.3	41.7	42.2	42.6	42.8
95°	74.1	74.1	74.1	74.1	74.1	74.1	74.1	74.1	74.1	74.1	74.1
97.5°	107.4	107.3	107.1	106.8	106.6	106.4	106.6	106.8	107.1	107.3	107.4
100°	142.5	142.7	143.1	143.6	144.0	144.4	144.0	143.6	143.1	142.7	142.5
102.5°	184.3	184.2	184.0	183.8	183.6	183.4	183.6	183.8	184.0	184.2	184.3
105°	224.2	224.4	224.8	225.3	225.7	226.1	225.7	225.3	224.8	224.4	224.2
107.5°	270.8	270.7	270.5	270.2	270.0	269.8	270.0	270.2	270.5	270.7	270.8
110°	316.4	316.2	315.8	315.3	314.9	314.5	314.9	315.3	315.8	316.2	316.4

TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	362.0	362.0	362.0	362.0	362.0	362.0	362.0	362.0	362.0	362.0	362.0
115°	405.7	405.6	405.4	405.2	405.0	404.8	405.0	405.2	405.4	405.6	405.7
117.5°	451.3	451.0	450.4	449.7	449.1	448.5	449.1	449.7	450.4	451.0	451.3
120°	496.9	496.7	496.3	495.8	495.4	495.0	495.4	495.8	496.3	496.7	496.9
122.5°	542.5	542.2	541.6	540.9	540.3	539.7	540.3	540.9	541.6	542.2	542.5
125°	588.1	587.7	586.8	586.0	585.1	584.3	585.1	586.0	586.8	587.7	588.1
127.5°	632.8	632.4	631.5	630.7	629.8	629.0	629.8	630.7	631.5	632.4	632.8
130°	679.4	678.7	677.2	675.7	674.2	672.7	674.2	675.7	677.2	678.7	679.4
132.5°	723.1	722.6	721.5	720.4	719.4	718.3	719.4	720.4	721.5	722.6	723.1
135°	767.7	767.5	767.1	766.6	766.2	765.8	766.2	766.6	767.1	767.5	767.7
137.5°	810.5	810.2	809.5	808.9	808.2	807.6	808.2	808.9	809.5	810.2	810.5
140°	855.1	854.4	852.9	851.4	850.0	848.5	850.0	851.4	852.9	854.4	855.1
142.5°	895.0	894.5	893.4	892.4	891.3	890.3	891.3	892.4	893.4	894.5	895.0
145°	934.0	933.6	932.7	931.9	931.0	930.2	931.0	931.9	932.7	933.6	934.0
147.5°	972.0	971.4	970.1	968.8	967.6	966.3	967.6	968.8	970.1	971.4	972.0
150°	1006.2	1005.6	1004.3	1003.0	1001.8	1000.5	1001.8	1003.0	1004.3	1005.6	1006.2
152.5°	1038.5	1038.0	1036.9	1035.9	1034.8	1033.8	1034.8	1035.9	1036.9	1038.0	1038.5
155°	1069.9	1069.2	1067.7	1066.2	1064.7	1063.2	1064.7	1066.2	1067.7	1069.2	1069.9
157.5°	1096.5	1095.9	1094.6	1093.3	1092.1	1090.8	1092.1	1093.3	1094.6	1095.9	1096.5
160°	1121.2	1120.8	1119.9	1119.1	1118.2	1117.4	1118.2	1119.1	1119.9	1120.8	1121.2
162.5°	1144.0	1143.3	1141.8	1140.3	1138.8	1137.3	1138.8	1140.3	1141.8	1143.3	1144.0
165°	1163.0	1162.3	1160.8	1159.3	1157.8	1156.3	1157.8	1159.3	1160.8	1162.3	1163.0
167.5°	1179.1	1178.5	1177.2	1175.9	1174.7	1173.4	1174.7	1175.9	1177.2	1178.5	1179.1
170°	1192.4	1191.7	1190.2	1188.7	1187.3	1185.8	1187.3	1188.7	1190.2	1191.7	1192.4
172.5°	1201.9	1201.2	1199.7	1198.2	1196.8	1195.3	1196.8	1198.2	1199.7	1201.2	1201.9
175°	1208.6	1207.9	1206.4	1204.9	1203.4	1201.9	1203.4	1204.9	1206.4	1207.9	1208.6
177.5°	1212.4	1211.7	1210.2	1208.7	1207.2	1205.7	1207.2	1208.7	1210.2	1211.7	1212.4
180°	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5

TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	427.3	428.1	428.6	426.8	425.5	427.7	430.8	432.9	434.7	436.9	438.2
5°	402.0	405.0	405.0	405.9	407.2	409.4	415.1	419.0	422.5	425.1	427.3
7.5°	380.6	382.8	384.1	386.3	388.5	391.5	398.1	403.7	409.0	412.0	415.5
10°	361.4	363.2	365.4	366.7	370.6	375.0	383.2	388.0	394.1	398.9	403.3
12.5°	343.1	349.2	350.5	350.1	353.6	358.4	366.7	374.1	380.6	385.4	390.2
15°	330.0	332.2	334.8	334.4	341.8	343.1	350.1	358.8	367.5	370.6	375.0
17.5°	315.7	319.1	321.8	323.1	325.2	330.0	336.6	343.1	354.5	354.9	366.2
20°	304.3	307.8	309.6	311.3	312.6	318.3	323.9	331.4	340.5	345.3	351.4
22.5°	296.9	298.7	300.0	301.3	303.0	306.1	313.0	321.3	327.4	332.7	336.6
25°	288.2	289.9	291.7	292.6	293.9	295.6	300.8	307.4	316.1	319.6	323.5
27.5°	282.1	282.1	283.0	283.0	284.7	286.4	290.4	296.5	303.4	307.8	313.0
30°	275.5	275.1	275.5	275.1	274.7	277.3	280.8	286.0	290.8	296.0	299.5
32.5°	269.0	268.6	268.6	269.0	267.3	268.6	270.3	275.1	280.3	283.0	286.9
35°	262.0	261.2	261.2	261.2	260.3	259.4	261.2	265.5	269.0	272.5	275.5
37.5°	255.1	253.7	253.7	252.9	252.0	250.7	250.7	254.2	259.0	260.3	264.2
40°	245.5	245.5	244.6	244.2	243.3	242.4	241.1	244.2	248.5	249.8	252.9
42.5°	235.9	234.6	234.1	234.1	234.1	232.8	231.9	234.1	236.7	238.9	240.7
45°	225.0	224.1	224.5	224.1	223.2	222.8	222.4	223.2	226.3	227.2	229.3
47.5°	213.2	212.8	212.8	212.3	211.9	212.3	210.6	212.8	213.6	214.5	216.3
50°	201.0	200.6	200.1	199.7	199.7	200.1	199.7	199.7	201.4	202.3	204.0
52.5°	188.8	187.5	187.5	187.0	187.0	186.2	187.0	187.5	188.3	189.2	190.1
55°	175.7	175.7	174.4	174.4	173.5	173.5	174.0	173.5	175.3	176.1	176.1
57.5°	163.1	161.3	161.8	160.9	160.0	159.6	159.6	160.4	161.3	161.3	162.2
60°	149.5	147.8	147.4	145.6	146.5	145.2	145.6	145.6	147.4	146.5	147.4
62.5°	136.0	133.8	132.5	131.7	131.7	132.1	131.2	130.8	131.7	132.5	134.3
65°	121.6	120.3	119.0	117.7	117.7	117.3	118.2	116.8	116.4	116.8	117.7
67.5°	106.8	105.5	104.2	102.9	103.3	102.0	101.1	102.5	101.6	102.0	102.9
70°	92.4	91.6	88.9	88.1	87.6	88.1	87.6	86.8	88.1	87.6	88.1
72.5°	78.0	77.2	75.9	73.7	73.7	73.2	72.8	72.8	72.4	72.4	72.4
75°	64.1	62.3	61.0	60.6	59.7	59.3	58.9	58.0	58.4	58.9	58.0
77.5°	49.7	47.5	47.1	47.1	45.8	45.8	46.2	45.8	45.3	45.3	45.3
80°	36.6	34.9	34.9	34.0	33.1	33.1	33.1	33.1	32.7	32.3	32.7
82.5°	23.5	23.1	22.7	22.7	23.5	21.8	22.7	22.2	21.8	21.8	21.4
85°	13.1	13.5	13.1	13.5	12.6	13.1	13.1	13.1	12.6	13.1	12.2
87.5°	4.8	4.8	4.8	5.2	5.2	5.2	5.2	5.2	5.7	5.2	5.2
90°	26.2	25.3	24.5	23.6	22.8	20.1	17.3	14.6	11.9	10.5	9.4
92.5°	42.5	41.8	41.2	40.5	39.9	38.6	37.4	36.1	34.8	34.2	33.6
95°	73.7	72.8	72.0	71.1	70.3	68.6	66.9	65.2	63.5	62.7	62.0
97.5°	106.9	105.8	104.7	103.7	102.6	101.3	100.1	98.8	97.5	96.9	96.4
100°	142.2	141.6	140.9	140.3	139.7	138.6	137.6	136.5	135.4	134.9	134.3
102.5°	184.0	183.4	182.7	182.1	181.5	180.0	178.5	177.0	175.5	174.8	174.5
105°	224.2	224.2	224.2	224.2	224.2	222.3	220.4	218.5	216.6	215.7	215.5
107.5°	270.5	269.8	269.2	268.5	267.9	267.1	266.2	265.4	264.5	264.1	264.0
110°	316.0	315.1	314.3	313.4	312.6	312.2	311.8	311.3	310.9	310.7	310.5

TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	361.5	360.4	359.4	358.3	357.3	357.3	357.3	357.3	357.3	357.3	357.2
115°	405.6	405.4	405.2	405.0	404.8	405.2	405.6	406.1	406.5	406.7	406.4
117.5°	451.3	451.3	451.3	451.3	451.3	451.7	452.1	452.6	453.0	453.2	453.1
120°	497.0	497.2	497.5	497.7	497.9	498.9	500.0	501.0	502.1	502.6	502.0
122.5°	542.8	543.5	544.1	544.8	545.4	545.8	546.2	546.7	547.1	547.3	546.9
125°	588.5	589.4	590.2	591.1	591.9	592.3	592.7	593.2	593.6	593.8	593.5
127.5°	633.4	634.7	636.0	637.2	638.5	638.9	639.3	639.8	640.2	640.4	639.8
130°	679.8	680.7	681.5	682.4	683.2	683.8	684.4	685.1	685.7	686.0	685.2
132.5°	723.6	724.7	725.7	726.8	727.8	728.2	728.6	729.1	729.5	729.7	728.9
135°	768.1	769.0	769.8	770.7	771.5	771.7	771.9	772.2	772.4	772.5	771.9
137.5°	811.0	812.1	813.1	814.2	815.2	814.6	814.0	813.3	812.7	812.4	811.9
140°	855.2	855.4	855.7	855.9	856.1	855.9	855.7	855.4	855.2	855.1	854.6
142.5°	895.1	895.3	895.6	895.8	896.0	895.6	895.2	894.7	894.3	894.1	893.6
145°	934.1	934.3	934.6	934.8	935.0	934.4	933.7	933.1	932.4	932.1	931.9
147.5°	972.0	972.0	972.0	972.0	972.0	971.4	970.8	970.1	969.5	969.2	968.8
150°	1006.2	1006.2	1006.2	1006.2	1006.2	1005.8	1005.4	1004.9	1004.5	1004.3	1004.1
152.5°	1038.3	1037.9	1037.4	1037.0	1036.6	1036.4	1036.2	1036.0	1035.8	1035.7	1035.4
155°	1069.5	1068.6	1067.8	1066.9	1066.1	1065.9	1065.7	1065.4	1065.2	1065.1	1065.1
157.5°	1096.1	1095.2	1094.4	1093.5	1092.7	1092.5	1092.3	1092.0	1091.8	1091.7	1091.8
160°	1120.7	1119.6	1118.5	1117.5	1116.4	1116.4	1116.4	1116.4	1116.4	1116.4	1116.6
162.5°	1143.5	1142.4	1141.3	1140.3	1139.2	1139.0	1138.8	1138.6	1138.4	1138.3	1138.6
165°	1162.4	1161.1	1159.8	1158.6	1157.3	1157.3	1157.3	1157.3	1157.3	1157.3	1157.6
167.5°	1178.5	1177.2	1175.9	1174.7	1173.4	1173.2	1173.0	1172.8	1172.6	1172.5	1172.9
170°	1191.7	1190.2	1188.7	1187.3	1185.8	1185.8	1185.8	1185.8	1185.8	1185.8	1186.2
172.5°	1201.3	1200.0	1198.7	1197.5	1196.2	1196.2	1196.2	1196.2	1196.2	1196.2	1196.6
175°	1208.0	1206.7	1205.4	1204.2	1202.9	1202.9	1202.9	1202.9	1202.9	1202.9	1203.3
177.5°	1211.8	1210.5	1209.2	1208.0	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1207.1
180°	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5	1209.5

TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	449.9	449.9	449.9	449.9
2.5°	440.4	441.7	446.0	451.3
5°	431.6	435.1	441.2	449.5
7.5°	422.0	427.3	436.0	446.5
10°	411.1	418.6	429.5	442.5
12.5°	399.4	409.0	422.9	436.4
15°	392.0	401.5	414.2	429.0
17.5°	377.6	388.9	402.0	422.9
20°	362.7	375.4	392.4	413.3
22.5°	351.4	364.9	381.1	403.3
25°	337.9	351.8	369.3	392.4
27.5°	323.5	337.5	357.1	381.5
30°	312.6	326.1	344.9	371.0
32.5°	299.5	312.6	332.2	359.7
35°	284.7	299.5	318.3	346.2
37.5°	273.4	286.9	306.5	333.1
40°	261.2	272.9	292.1	318.3
42.5°	248.1	261.2	277.7	303.9
45°	235.9	245.5	262.5	287.3
47.5°	222.8	233.7	246.8	266.0
50°	208.8	218.0	232.4	245.5
52.5°	195.3	202.7	214.9	225.0
55°	180.9	188.3	197.5	203.6
57.5°	167.4	172.7	178.8	182.7
60°	150.9	156.1	160.0	163.9
62.5°	136.0	140.0	142.1	144.3
65°	120.8	122.9	124.3	126.0
67.5°	104.2	106.4	106.8	109.4
70°	88.9	89.4	90.3	91.6
72.5°	74.6	75.4	75.0	75.9
75°	59.7	60.6	59.7	60.6
77.5°	45.3	46.2	46.2	47.5
80°	32.7	33.1	33.6	33.6
82.5°	21.4	22.7	21.8	22.2
85°	12.2	12.6	12.6	13.1
87.5°	5.7	6.1	5.7	6.5
90°	7.3	5.2	3.1	1.0
92.5°	32.3	31.0	29.8	28.5
95°	60.5	59.0	57.6	56.1
97.5°	95.3	94.3	93.2	92.2
100°	133.0	131.7	130.5	129.2
102.5°	173.9	173.2	172.6	172.0
105°	215.1	214.6	214.2	213.8
107.5°	263.8	263.6	263.4	263.2
110°	310.1	309.6	309.2	308.8

TEST NUMBER: P1011494

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	357.0	356.7	356.5	356.3
115°	405.7	405.1	404.4	403.8
117.5°	452.9	452.7	452.5	452.3
120°	500.7	499.4	498.2	496.9
122.5°	546.0	545.2	544.3	543.5
125°	592.9	592.2	591.6	591.0
127.5°	638.5	637.2	636.0	634.7
130°	683.5	681.8	680.1	678.4
132.5°	727.2	725.5	723.8	722.1
135°	770.6	769.3	768.1	766.8
137.5°	810.8	809.7	808.7	807.6
140°	853.5	852.5	851.4	850.4
142.5°	892.5	891.4	890.4	889.3
145°	931.5	931.0	930.6	930.2
147.5°	967.9	967.1	966.2	965.4
150°	1003.7	1003.2	1002.8	1002.4
152.5°	1034.7	1034.1	1033.4	1032.8
155°	1065.1	1065.1	1065.1	1065.1
157.5°	1092.0	1092.3	1092.5	1092.7
160°	1117.0	1117.5	1117.9	1118.3
162.5°	1139.2	1139.9	1140.5	1141.1
165°	1158.2	1158.9	1159.5	1160.1
167.5°	1173.8	1174.6	1175.5	1176.3
170°	1187.1	1187.9	1188.8	1189.6
172.5°	1197.5	1198.3	1199.2	1200.0
175°	1204.2	1205.0	1205.9	1206.7
177.5°	1208.0	1208.8	1209.7	1210.5
180°	1209.5	1209.5	1209.5	1209.5

(END OF REPORT)