

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011211

Luminaire Tested: S123DIP-B1000D805UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011211
REPORT IS A COMBINATION OF REPORTS P989289 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D805UB30-4F0-XX-W2A-F
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7230.0 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011211

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1011211

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	99	95	91	87	92	88	85	82	76	74	71	65	63	62	55	54	52
2	90	83	77	71	84	77	72	67	67	63	59	57	54	51	48	46	44
3	82	73	65	59	76	68	61	56	59	54	50	51	47	43	43	40	38
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32
5	69	57	49	43	64	54	46	41	47	41	37	40	36	32	34	31	28
6	64	52	43	37	59	48	41	36	42	36	32	37	32	28	31	28	25
7	59	47	38	33	55	44	36	31	38	32	28	33	29	25	29	25	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	23	20
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	21	18
10	48	35	28	23	44	33	27	22	30	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16937	16937	16937
5°	16979	16352	16328
10°	16828	15798	15636
15°	16593	15222	14883
20°	16326	14585	14137
25°	15978	13910	13339
30°	15598	13212	12499
35°	15200	12498	11666
40°	14784	11751	10845
45°	14325	11021	9988
50°	13859	10209	9129
55°	13262	9362	8257
60°	12647	8428	7329
65°	12067	7417	6363
70°	11235	6297	5234
75°	10035	4987	4062
80°	8665	3505	2873
85°	6762	1882	1438

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14325 cd/sqm

TEST NUMBER: P1011211

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.3	2.1
10°-20°	418.8	5.8
20°-30°	618.6	8.6
30°-40°	722.5	10.0
40°-50°	726.3	10.0
50°-60°	638.0	8.8
60°-70°	475.2	6.6
70°-80°	270.4	3.7
80°-90°	78.9	1.1
90°-100°	36.2	0.5
100°-110°	175.2	2.4
110°-120°	429.3	5.9
120°-130°	545.1	7.5
130°-140°	582.3	8.1
140°-150°	544.5	7.5
150°-160°	439.2	6.1
160°-170°	283.4	3.9
170°-180°	97.7	1.4
0°-30°	1185.8	16.4
0°-40°	1908.2	26.4
0°-60°	3272.5	45.3
0°-90°	4097.0	56.7
90°-120°	640.8	8.9
90°-150°	2312.6	32.0
90°-180°	3133.0	43.3
0°-180°	7230.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1574	1574	1574	1574	1574	
5°	1575	1568	1553	1567	1564	149
15°	1499	1494	1476	1487	1479	423
25°	1361	1353	1335	1337	1333	627
35°	1177	1169	1151	1143	1136	736
45°	965	959	942	925	919	745
55°	732	731	713	698	691	656
65°	499	492	479	468	464	493
75°	264	258	254	248	244	282
85°	70	68	68	65	65	75
90°	1	8	18	21	23	7
95°	47	15	24	29	29	56
105°	228	236	167	32	34	241
115°	427	431	438	446	449	422
125°	602	608	611	612	614	538
135°	749	754	757	759	757	577
145°	864	870	871	873	873	541
155°	952	951	951	955	951	439
165°	1004	1002	1001	1007	1002	284
175°	1028	1024	1025	1030	1024	98
180°	1028	1028	1028	1028	1028	

TEST NUMBER: P1011211

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1573.5	1573.5	1573.5	1573.5	1573.5
2.5°	1580.2	1574.8	1559.9	1573.5	1572.1
5°	1574.8	1568.0	1553.2	1566.7	1564.0
7.5°	1562.6	1555.9	1541.0	1553.2	1551.8
10°	1546.4	1539.6	1522.0	1534.2	1531.5
12.5°	1524.7	1519.3	1503.1	1511.2	1509.9
15°	1499.0	1493.6	1476.0	1486.9	1478.7
17.5°	1470.6	1463.9	1446.3	1454.4	1451.7
20°	1438.2	1430.0	1412.5	1417.9	1413.8
22.5°	1401.6	1393.5	1375.9	1380.0	1374.6
25°	1361.0	1352.9	1335.3	1336.7	1332.6
27.5°	1319.1	1311.0	1292.0	1293.4	1289.3
30°	1273.1	1266.3	1247.4	1247.4	1237.9
32.5°	1227.1	1217.6	1204.1	1194.6	1190.6
35°	1177.0	1168.9	1151.3	1143.2	1136.5
37.5°	1127.0	1116.2	1098.6	1089.1	1085.0
40°	1074.2	1066.1	1047.2	1036.3	1030.9
42.5°	1021.5	1012.0	993.0	982.2	976.8
45°	964.6	959.2	941.6	925.4	918.6
47.5°	909.2	901.0	884.8	868.6	863.2
50°	852.3	845.6	828.0	813.1	805.0
52.5°	792.8	788.8	769.8	757.6	749.5
55°	731.9	730.6	713.0	698.1	691.3
57.5°	675.1	669.7	656.2	642.6	634.5
60°	612.9	611.5	595.3	583.1	576.3
62.5°	557.4	553.3	537.1	524.9	520.9
65°	499.2	492.5	478.9	468.1	464.1
67.5°	437.0	431.6	420.8	411.3	405.9
70°	381.5	373.4	365.3	355.8	349.1
72.5°	323.3	317.9	308.5	300.3	297.6
75°	263.8	258.4	254.4	247.6	243.5
77.5°	211.1	208.4	202.9	197.5	197.5
80°	159.6	155.6	152.9	151.5	151.5
82.5°	109.6	109.6	109.6	106.9	105.5
85°	70.4	67.6	67.6	64.9	64.9
87.5°	35.2	31.1	29.8	28.4	28.4
90°	0.8	8.4	18.3	21.4	22.9
92.5°	17.6	13.0	19.9	25.2	26.0
95°	46.6	15.3	23.7	29.0	29.0
97.5°	84.7	63.4	24.4	30.5	31.3
100°	129.0	144.3	25.2	31.3	32.1
102.5°	179.4	189.3	56.5	31.3	32.8
105°	227.5	235.9	167.2	32.1	33.6
107.5°	278.7	285.5	297.0	179.4	79.4
110°	329.8	335.9	344.3	319.1	210.0



TEST NUMBER: P1011211

CATALOG NUMBER: S123DIP-B1000D805UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	378.7	384.0	392.4	399.3	397.8
115°	426.8	431.4	438.2	445.9	448.9
117.5°	474.1	479.5	483.3	489.4	490.2
120°	517.7	524.5	526.8	532.9	532.9
122.5°	561.9	567.3	570.3	574.2	574.9
125°	601.6	607.7	610.8	612.3	613.9
127.5°	641.3	647.4	651.3	653.6	652.0
130°	678.0	684.1	687.2	690.2	688.7
132.5°	713.1	719.2	721.5	724.6	722.3
135°	749.0	753.6	756.6	758.9	756.6
137.5°	779.5	785.6	787.2	791.0	789.5
140°	810.1	814.7	816.9	820.0	818.5
142.5°	838.3	842.9	845.2	847.5	845.2
145°	864.3	869.6	871.2	872.7	872.7
147.5°	889.5	893.3	894.8	896.4	892.5
150°	912.4	914.7	916.2	917.7	915.4
152.5°	933.0	933.8	934.5	937.6	933.8
155°	952.1	950.6	951.3	955.1	950.6
157.5°	967.4	967.4	966.6	971.2	965.1
160°	981.1	980.3	979.6	984.2	978.8
162.5°	994.1	991.8	991.0	996.4	991.8
165°	1004.0	1001.7	1001.0	1007.1	1001.7
167.5°	1012.4	1009.3	1009.3	1015.5	1009.3
170°	1019.3	1016.2	1016.2	1022.3	1016.2
172.5°	1023.9	1020.0	1020.8	1026.9	1020.0
175°	1027.7	1023.9	1024.6	1030.0	1023.9
177.5°	1029.2	1025.4	1026.1	1032.3	1024.6
180°	1027.7	1027.7	1027.7	1027.7	1027.7

(END OF REPORT)