

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011499

Luminaire Tested: S123DIP-B340D1025UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011499
REPORT IS A COMBINATION OF REPORTS P989676 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1025UB50-4F0-XX-W2A-F
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5221.0 lumens
Efficiency: N/A
Efficacy: 125.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011499

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1011499

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33
1	92	88	84	81	82	79	75	73	61	59	57	44	43	42	29	29	28
2	84	77	71	66	75	69	64	59	53	50	47	39	37	35	26	25	24
3	76	67	60	55	68	60	54	50	47	43	39	34	32	30	23	21	20
4	70	60	52	46	62	53	47	42	42	37	33	31	28	25	20	19	17
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15
6	59	47	39	34	52	42	36	31	33	28	25	25	21	19	17	15	13
7	54	42	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10
9	47	35	28	23	41	31	25	21	25	20	17	19	15	13	13	11	9
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5459	5459	5459
5°	5473	5271	5263
10°	5425	5092	5041
15°	5349	4907	4798
20°	5263	4701	4557
25°	5150	4483	4300
30°	5028	4259	4029
35°	4900	4029	3760
40°	4766	3787	3496
45°	4617	3552	3220
50°	4467	3291	2943
55°	4274	3017	2662
60°	4077	2717	2363
65°	3890	2391	2051
70°	3622	2029	1687
75°	3233	1607	1310
80°	2796	1130	925
85°	2180	607	463

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4617 cd/sqm

TEST NUMBER: P1011499

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.8	0.9
10°-20°	135.0	2.6
20°-30°	199.4	3.8
30°-40°	232.9	4.5
40°-50°	234.1	4.5
50°-60°	205.7	3.9
60°-70°	153.2	2.9
70°-80°	87.2	1.7
80°-90°	27.3	0.5
90°-100°	45.1	0.9
100°-110°	218.0	4.2
110°-120°	534.3	10.2
120°-130°	678.2	13.0
130°-140°	724.6	13.9
140°-150°	677.5	13.0
150°-160°	546.5	10.5
160°-170°	352.7	6.8
170°-180°	121.5	2.3
0°-30°	382.2	7.3
0°-40°	615.1	11.8
0°-60°	1054.9	20.2
0°-90°	1322.5	25.3
90°-120°	797.4	15.3
90°-150°	2877.8	55.1
90°-180°	3898.0	74.7
0°-180°	5221.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	507	507	507	507	507	
5°	508	505	501	505	504	48
15°	483	482	476	479	477	136
25°	439	436	430	431	430	202
35°	379	377	371	368	366	237
45°	311	309	304	298	296	240
55°	236	236	230	225	223	211
65°	161	159	154	151	150	159
75°	85	83	82	80	78	91
85°	23	22	22	21	21	24
90°	1	10	23	27	28	5
95°	58	19	30	36	36	69
105°	283	294	208	40	42	300
115°	531	537	545	555	559	524
125°	749	756	760	762	764	669
135°	932	938	942	944	942	718
145°	1076	1082	1084	1086	1086	673
155°	1185	1183	1184	1188	1183	546
165°	1249	1246	1246	1253	1246	353
175°	1279	1274	1275	1282	1274	122
180°	1279	1279	1279	1279	1279	

TEST NUMBER: P1011499

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	507.2	507.2	507.2	507.2	507.2
2.5°	509.4	507.6	502.8	507.2	506.8
5°	507.6	505.4	500.7	505.0	504.1
7.5°	503.7	501.5	496.7	500.7	500.2
10°	498.5	496.3	490.6	494.5	493.7
12.5°	491.5	489.7	484.5	487.1	486.7
15°	483.2	481.5	475.8	479.3	476.7
17.5°	474.0	471.9	466.2	468.8	467.9
20°	463.6	461.0	455.3	457.0	455.7
22.5°	451.8	449.2	443.5	444.8	443.1
25°	438.7	436.1	430.4	430.9	429.6
27.5°	425.2	422.6	416.5	416.9	415.6
30°	410.4	408.2	402.1	402.1	399.0
32.5°	395.5	392.5	388.1	385.1	383.8
35°	379.4	376.8	371.1	368.5	366.3
37.5°	363.3	359.8	354.1	351.1	349.8
40°	346.3	343.7	337.5	334.1	332.3
42.5°	329.3	326.2	320.1	316.6	314.9
45°	310.9	309.2	303.5	298.3	296.1
47.5°	293.1	290.4	285.2	280.0	278.2
50°	274.7	272.6	266.9	262.1	259.5
52.5°	255.6	254.3	248.1	244.2	241.6
55°	235.9	235.5	229.8	225.0	222.9
57.5°	217.6	215.9	211.5	207.2	204.5
60°	197.6	197.1	191.9	188.0	185.8
62.5°	179.7	178.4	173.1	169.2	167.9
65°	160.9	158.7	154.4	150.9	149.6
67.5°	140.9	139.1	135.6	132.6	130.8
70°	123.0	120.4	117.7	114.7	112.5
72.5°	104.2	102.5	99.4	96.8	95.9
75°	85.0	83.3	82.0	79.8	78.5
77.5°	68.0	67.2	65.4	63.7	63.7
80°	51.5	50.2	49.3	48.8	48.8
82.5°	35.3	35.3	35.3	34.5	34.0
85°	22.7	21.8	21.8	20.9	20.9
87.5°	11.3	10.0	9.6	9.2	9.2
90°	1.0	10.5	22.8	26.6	28.5
92.5°	21.9	16.2	24.7	31.4	32.3
95°	58.0	19.0	29.5	36.1	36.1
97.5°	105.5	78.9	30.4	38.0	39.0
100°	160.6	179.6	31.4	39.0	39.9
102.5°	223.3	235.6	70.3	39.0	40.9
105°	283.1	293.6	208.1	39.9	41.8
107.5°	346.8	355.3	369.6	223.3	98.8
110°	410.4	418.0	428.5	397.1	261.3

TEST NUMBER: P1011499

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	471.2	477.9	488.3	496.9	495.0
115°	531.1	536.8	545.3	554.8	558.6
117.5°	590.0	596.6	601.4	609.0	609.9
120°	644.1	652.7	655.5	663.1	663.1
122.5°	699.2	705.9	709.7	714.4	715.4
125°	748.6	756.2	760.0	761.9	763.8
127.5°	798.0	805.6	810.4	813.2	811.3
130°	843.6	851.2	855.0	858.8	856.9
132.5°	887.4	895.0	897.8	901.6	898.8
135°	932.0	937.7	941.5	944.4	941.5
137.5°	970.0	977.6	979.5	984.3	982.4
140°	1008.0	1013.7	1016.6	1020.4	1018.5
142.5°	1043.2	1048.9	1051.7	1054.6	1051.7
145°	1075.5	1082.1	1084.0	1085.9	1085.9
147.5°	1106.8	1111.6	1113.5	1115.4	1110.6
150°	1135.3	1138.2	1140.1	1142.0	1139.1
152.5°	1161.0	1161.9	1162.9	1166.7	1161.9
155°	1184.7	1182.8	1183.8	1188.5	1182.8
157.5°	1203.7	1203.7	1202.8	1208.5	1200.9
160°	1220.8	1219.9	1218.9	1224.6	1218.0
162.5°	1237.0	1234.1	1233.2	1239.8	1234.1
165°	1249.3	1246.5	1245.5	1253.1	1246.5
167.5°	1259.8	1256.0	1256.0	1263.6	1256.0
170°	1268.3	1264.5	1264.5	1272.1	1264.5
172.5°	1274.0	1269.3	1270.2	1277.8	1269.3
175°	1278.8	1274.0	1275.0	1281.6	1274.0
177.5°	1280.7	1275.9	1276.9	1284.5	1275.0
180°	1278.8	1278.8	1278.8	1278.8	1278.8

(END OF REPORT)