

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011509

Luminaire Tested: S123DIP-B340D1195UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011509
REPORT IS A COMBINATION OF REPORTS P989686 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1195UB27-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5425.0 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011509

CATALOG NUMBER: S123DIP-B340D1195UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011509

CATALOG NUMBER: S123DIP-B340D1195UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	29	28
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	25	24
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	23	21	20
4	70	59	52	46	62	53	47	42	41	37	33	31	28	25	20	19	17
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15
6	59	47	39	34	52	42	36	31	33	28	25	25	21	19	17	15	13
7	54	42	35	29	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	38	31	26	45	35	28	24	27	22	19	20	17	15	14	12	10
9	47	35	28	23	41	31	25	21	25	20	17	19	15	13	13	11	9
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5628	5628	5628
5°	5643	5435	5427
10°	5593	5251	5197
15°	5515	5060	4947
20°	5426	4847	4699
25°	5311	4623	4433
30°	5184	4391	4154
35°	5052	4155	3877
40°	4913	3905	3604
45°	4761	3664	3320
50°	4607	3393	3033
55°	4408	3112	2745
60°	4203	2800	2437
65°	4010	2466	2114
70°	3734	2093	1739
75°	3336	1656	1350
80°	2883	1164	956
85°	2248	627	479

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4761 cd/sqm

TEST NUMBER: P1011509

CATALOG NUMBER: S123DIP-B340D1195UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.3	0.9
10°-20°	139.2	2.6
20°-30°	205.6	3.8
30°-40°	240.1	4.4
40°-50°	241.4	4.4
50°-60°	212.1	3.9
60°-70°	157.9	2.9
70°-80°	89.9	1.7
80°-90°	28.6	0.5
90°-100°	94.3	1.7
100°-110°	285.6	5.3
110°-120°	486.1	9.0
120°-130°	639.5	11.8
130°-140°	718.9	13.3
140°-150°	706.7	13.0
150°-160°	595.0	11.0
160°-170°	396.1	7.3
170°-180°	138.7	2.6
0°-30°	394.1	7.3
0°-40°	634.2	11.7
0°-60°	1087.7	20.0
0°-90°	1364.1	25.1
90°-120°	866.0	16.0
90°-150°	2931.1	54.0
90°-180°	4061.0	74.9
0°-180°	5425.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	523	523	523	523	523	
5°	523	521	516	521	520	50
15°	498	496	491	494	492	140
25°	452	450	444	444	443	208
35°	391	388	383	380	378	245
45°	321	319	313	308	305	248
55°	243	243	237	232	230	218
65°	166	164	159	156	154	164
75°	88	86	84	82	81	94
85°	23	22	22	22	22	25
90°	1	13	28	32	34	7
95°	68	76	85	90	90	75
105°	259	261	272	272	274	277
115°	489	493	490	492	490	484
125°	716	720	717	713	708	639
135°	929	936	935	930	928	716
145°	1127	1129	1133	1132	1127	704
155°	1291	1291	1292	1296	1288	594
165°	1406	1402	1402	1409	1401	396
175°	1462	1458	1458	1464	1456	139
180°	1466	1466	1466	1466	1466	

TEST NUMBER: P1011509

CATALOG NUMBER: S123DIP-B340D1195UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	522.9	522.9	522.9	522.9	522.9
2.5°	525.2	523.4	518.5	522.9	522.5
5°	523.4	521.1	516.2	520.7	519.8
7.5°	519.4	517.1	512.2	516.2	515.8
10°	514.0	511.7	505.9	509.9	509.0
12.5°	506.8	505.0	499.6	502.3	501.8
15°	498.2	496.4	490.6	494.2	491.5
17.5°	488.8	486.5	480.7	483.4	482.5
20°	478.0	475.3	469.4	471.2	469.9
22.5°	465.8	463.1	457.3	458.6	456.8
25°	452.4	449.7	443.8	444.3	442.9
27.5°	438.4	435.7	429.4	429.9	428.5
30°	423.1	420.9	414.6	414.6	411.4
32.5°	407.8	404.7	400.2	397.0	395.7
35°	391.2	388.5	382.7	380.0	377.7
37.5°	374.6	371.0	365.1	362.0	360.6
40°	357.0	354.3	348.0	344.4	342.6
42.5°	339.5	336.3	330.0	326.4	324.6
45°	320.6	318.8	313.0	307.6	305.3
47.5°	302.2	299.5	294.1	288.7	286.9
50°	283.3	281.0	275.2	270.2	267.5
52.5°	263.5	262.1	255.9	251.8	249.1
55°	243.3	242.8	237.0	232.0	229.8
57.5°	224.4	222.6	218.1	213.6	210.9
60°	203.7	203.2	197.8	193.8	191.6
62.5°	185.3	183.9	178.5	174.5	173.1
65°	165.9	163.7	159.2	155.6	154.2
67.5°	145.2	143.4	139.8	136.7	134.9
70°	126.8	124.1	121.4	118.3	116.0
72.5°	107.5	105.7	102.5	99.8	98.9
75°	87.7	85.9	84.5	82.3	80.9
77.5°	70.1	69.2	67.4	65.6	65.6
80°	53.1	51.7	50.8	50.4	50.4
82.5°	36.4	36.4	36.4	35.5	35.1
85°	23.4	22.5	22.5	21.6	21.6
87.5°	11.7	10.3	9.9	9.4	9.4
90°	1.2	12.7	27.6	32.2	34.5
92.5°	34.5	41.4	48.4	51.8	49.5
95°	67.9	76.0	85.2	89.8	89.8
97.5°	111.7	117.4	124.3	130.1	128.9
100°	156.6	163.5	169.2	172.7	175.0
102.5°	208.4	211.8	219.9	223.4	222.2
105°	259.0	261.3	271.7	271.7	274.0
107.5°	318.9	320.1	324.7	328.1	327.0
110°	374.2	376.5	378.8	383.4	381.1

TEST NUMBER: P1011509

CATALOG NUMBER: S123DIP-B340D1195UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	431.7	432.9	432.9	438.6	438.6
115°	489.3	492.8	490.5	491.6	490.5
117.5°	548.0	549.2	546.9	546.9	543.4
120°	602.1	609.0	603.3	602.1	599.8
122.5°	658.5	663.1	660.8	657.4	653.9
125°	716.1	719.6	717.3	712.7	708.0
127.5°	769.1	776.0	773.7	766.8	762.2
130°	822.0	831.2	827.8	823.2	815.1
132.5°	875.0	884.2	881.9	876.1	870.4
135°	929.1	936.0	934.9	930.2	927.9
137.5°	978.6	984.4	987.8	982.1	978.6
140°	1030.4	1036.2	1037.3	1036.2	1028.1
142.5°	1077.6	1083.4	1085.7	1084.5	1078.8
145°	1127.1	1129.4	1132.9	1131.7	1127.1
147.5°	1169.7	1174.3	1177.8	1177.8	1170.9
150°	1214.6	1216.9	1219.2	1219.2	1212.3
152.5°	1251.5	1254.9	1256.1	1258.4	1252.6
155°	1290.6	1290.6	1291.8	1296.4	1288.3
157.5°	1324.0	1322.8	1324.0	1328.6	1321.7
160°	1355.1	1352.8	1352.8	1358.5	1353.9
162.5°	1382.7	1379.2	1380.4	1386.2	1378.1
165°	1405.7	1402.3	1402.3	1409.2	1401.1
167.5°	1425.3	1420.7	1421.8	1428.8	1421.8
170°	1441.4	1436.8	1436.8	1444.9	1436.8
172.5°	1454.1	1449.5	1449.5	1456.4	1448.3
175°	1462.1	1457.5	1457.5	1464.4	1456.4
177.5°	1466.7	1462.1	1462.1	1469.1	1461.0
180°	1465.6	1465.6	1465.6	1465.6	1465.6

(END OF REPORT)