

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011227

Luminaire Tested: S123DIP-B1000D805UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011227
REPORT IS A COMBINATION OF REPORTS P989308 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D805UB40-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6752.0 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 67.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011227

CATALOG NUMBER: S123DIP-B1000D805UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011227

CATALOG NUMBER: S123DIP-B1000D805UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66
1	100	96	92	88	93	90	86	83	78	75	73	68	66	64	58	57	55
2	91	83	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34
5	70	58	50	43	65	54	47	41	48	42	37	42	37	34	36	33	30
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	29	52	40	33	28	36	30	26	32	27	23	28	24	21
9	52	39	31	26	48	37	30	25	33	27	23	29	24	21	26	22	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16841	16841	16841
5°	16884	16260	16236
10°	16733	15710	15549
15°	16500	15138	14799
20°	16234	14502	14058
25°	15889	13832	13264
30°	15511	13138	12430
35°	15115	12429	11601
40°	14701	11685	10784
45°	14245	10959	9933
50°	13783	10151	9078
55°	13187	9310	8211
60°	12575	8380	7288
65°	12000	7375	6326
70°	11173	6261	5204
75°	9978	4958	4041
80°	8616	3484	2858
85°	6724	1874	1432

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14245 cd/sqm

TEST NUMBER: P1011227

CATALOG NUMBER: S123DIP-B1000D805UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.5	2.2
10°-20°	416.5	6.2
20°-30°	615.1	9.1
30°-40°	718.4	10.6
40°-50°	722.2	10.7
50°-60°	634.4	9.4
60°-70°	472.5	7.0
70°-80°	268.9	4.0
80°-90°	78.5	1.2
90°-100°	62.2	0.9
100°-110°	188.3	2.8
110°-120°	320.6	4.7
120°-130°	421.7	6.2
130°-140°	474.0	7.0
140°-150°	466.0	6.9
150°-160°	392.4	5.8
160°-170°	261.2	3.9
170°-180°	91.5	1.4
0°-30°	1179.1	17.5
0°-40°	1897.5	28.1
0°-60°	3254.2	48.2
0°-90°	4074.0	60.3
90°-120°	571.1	8.5
90°-150°	1932.9	28.6
90°-180°	2678.0	39.7
0°-180°	6752.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1565	1565	1565	1565	1565	
5°	1566	1559	1544	1558	1555	149
15°	1491	1485	1468	1478	1470	420
25°	1353	1345	1328	1329	1325	623
35°	1170	1162	1145	1137	1130	732
45°	959	954	936	920	914	741
55°	728	726	709	694	688	652
65°	496	490	476	466	461	490
75°	262	257	253	246	242	280
85°	70	67	67	65	65	75
90°	1	8	18	21	23	8
95°	45	50	56	59	59	49
105°	171	172	179	179	181	183
115°	323	325	323	324	323	319
125°	472	474	473	470	467	421
135°	613	617	616	613	612	472
145°	743	745	747	746	743	464
155°	851	851	852	855	850	392
165°	927	925	925	929	924	261
175°	964	961	961	966	960	92
180°	966	966	966	966	966	

TEST NUMBER: P1011227

CATALOG NUMBER: S123DIP-B1000D805UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1564.6	1564.6	1564.6	1564.6	1564.6
2.5°	1571.3	1566.0	1551.2	1564.6	1563.3
5°	1566.0	1559.2	1544.4	1557.9	1555.2
7.5°	1553.9	1547.1	1532.3	1544.4	1543.1
10°	1537.7	1531.0	1513.5	1525.6	1522.9
12.5°	1516.2	1510.8	1494.7	1502.7	1501.4
15°	1490.6	1485.2	1467.8	1478.5	1470.4
17.5°	1462.4	1455.6	1438.2	1446.2	1443.5
20°	1430.1	1422.0	1404.5	1409.9	1405.9
22.5°	1393.8	1385.7	1368.2	1372.2	1366.9
25°	1353.4	1345.3	1327.8	1329.2	1325.1
27.5°	1311.7	1303.6	1284.8	1286.1	1282.1
30°	1266.0	1259.2	1240.4	1240.4	1231.0
32.5°	1220.2	1210.8	1197.3	1187.9	1183.9
35°	1170.4	1162.4	1144.9	1136.8	1130.1
37.5°	1120.7	1109.9	1092.4	1083.0	1079.0
40°	1068.2	1060.1	1041.3	1030.5	1025.1
42.5°	1015.7	1006.3	987.5	976.7	971.3
45°	959.2	953.8	936.3	920.2	913.5
47.5°	904.1	896.0	879.8	863.7	858.3
50°	847.6	840.8	823.3	808.5	800.5
52.5°	788.4	784.3	765.5	753.4	745.3
55°	727.8	726.5	709.0	694.2	687.5
57.5°	671.3	665.9	652.5	639.0	631.0
60°	609.4	608.1	591.9	579.8	573.1
62.5°	554.3	550.2	534.1	522.0	518.0
65°	496.4	489.7	476.2	465.5	461.4
67.5°	434.5	429.2	418.4	409.0	403.6
70°	379.4	371.3	363.2	353.8	347.1
72.5°	321.5	316.2	306.7	298.7	296.0
75°	262.3	257.0	252.9	246.2	242.2
77.5°	209.9	207.2	201.8	196.4	196.4
80°	158.7	154.7	152.0	150.7	150.7
82.5°	109.0	109.0	109.0	106.3	104.9
85°	70.0	67.3	67.3	64.6	64.6
87.5°	35.0	30.9	29.6	28.3	28.3
90°	0.8	8.4	18.2	21.3	22.8
92.5°	22.8	27.3	31.9	34.2	32.6
95°	44.8	50.1	56.2	59.2	59.2
97.5°	73.6	77.4	82.0	85.8	85.0
100°	103.3	107.8	111.6	113.9	115.4
102.5°	137.4	139.7	145.0	147.3	146.5
105°	170.8	172.3	179.2	179.2	180.7
107.5°	210.3	211.1	214.1	216.4	215.6
110°	246.7	248.3	249.8	252.8	251.3



TEST NUMBER: P1011227

CATALOG NUMBER: S123DIP-B1000D805UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	284.7	285.5	285.5	289.3	289.3
115°	322.7	324.9	323.4	324.2	323.4
117.5°	361.4	362.1	360.6	360.6	358.4
120°	397.1	401.6	397.8	397.1	395.6
122.5°	434.3	437.3	435.8	433.5	431.2
125°	472.2	474.5	473.0	470.0	466.9
127.5°	507.2	511.7	510.2	505.6	502.6
130°	542.1	548.2	545.9	542.8	537.5
132.5°	577.0	583.1	581.6	577.8	574.0
135°	612.7	617.2	616.5	613.4	611.9
137.5°	645.3	649.1	651.4	647.6	645.3
140°	679.5	683.3	684.1	683.3	678.0
142.5°	710.6	714.4	715.9	715.2	711.4
145°	743.3	744.8	747.1	746.3	743.3
147.5°	771.4	774.4	776.7	776.7	772.1
150°	801.0	802.5	804.0	804.0	799.5
152.5°	825.3	827.5	828.3	829.8	826.0
155°	851.1	851.1	851.8	854.9	849.6
157.5°	873.1	872.3	873.1	876.1	871.6
160°	893.6	892.1	892.1	895.9	892.8
162.5°	911.8	909.5	910.3	914.1	908.8
165°	927.0	924.7	924.7	929.3	924.0
167.5°	939.9	936.9	937.6	942.2	937.6
170°	950.5	947.5	947.5	952.8	947.5
172.5°	958.9	955.9	955.9	960.4	955.1
175°	964.2	961.2	961.2	965.7	960.4
177.5°	967.2	964.2	964.2	968.8	963.4
180°	966.5	966.5	966.5	966.5	966.5

(END OF REPORT)