

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011521

Luminaire Tested: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011521
REPORT IS A COMBINATION OF REPORTS P989713 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1195UB35-4F0-XX-W2A-A1
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5535.0 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29
2	84	77	71	67	75	69	64	60	54	50	48	40	38	36	27	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	33	30	24	22	21
4	70	60	53	47	62	54	47	43	42	38	34	31	28	26	21	19	18
5	64	53	46	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	17	15	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	14	12	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10
10	44	32	25	21	39	29	23	19	23	19	16	18	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5061	5061	5061	5061
5°	5064	5831	5079	4352
10°	5032	7056	5037	3800
15°	4962	8368	5002	3421
20°	4903	9634	4913	3148
25°	4813	9878	4824	3005
30°	4750	8161	4750	2912
35°	4671	5458	4641	2829
40°	4577	3940	4521	2703
45°	4458	3121	4331	2547
50°	4171	2650	4023	2392
55°	3856	2329	3698	2220
60°	3535	2028	3347	2040
65°	3184	1736	3029	1799
70°	2818	1441	2630	1516
75°	2408	1086	2252	1171
80°	1906	726	1754	768
85°	1316	332	1047	304

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 8162 cd/sqm

TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.2	0.8
10°-20°	148.5	2.7
20°-30°	249.9	4.5
30°-40°	282.4	5.1
40°-50°	252.9	4.6
50°-60°	204.2	3.7
60°-70°	142.3	2.6
70°-80°	74.7	1.3
80°-90°	21.0	0.4
90°-100°	95.6	1.7
100°-110°	289.2	5.2
110°-120°	492.4	8.9
120°-130°	647.7	11.7
130°-140°	728.0	13.2
140°-150°	715.8	12.9
150°-160°	602.6	10.9
160°-170°	401.2	7.2
170°-180°	140.5	2.5
0°-30°	444.6	8.0
0°-40°	727.0	13.1
0°-60°	1184.1	21.4
0°-90°	1422.1	25.7
90°-120°	877.1	15.8
90°-150°	2968.6	53.6
90°-180°	4113.0	74.3
0°-180°	5535.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	470	470	470	470	470	
5°	470	558	471	417	470	45
15°	448	831	452	340	448	127
25°	410	987	411	300	410	189
35°	362	532	359	276	362	226
45°	300	287	292	234	300	230
55°	213	195	204	186	213	191
65°	132	127	125	131	132	131
75°	63	65	59	70	63	68
85°	14	15	11	14	14	16
90°	1	35	1	35	1	6
95°	69	91	69	91	69	76
105°	262	278	262	278	262	281
115°	496	497	496	497	496	490
125°	725	717	725	717	725	647
135°	941	940	941	940	941	725
145°	1142	1142	1142	1142	1142	713
155°	1307	1305	1307	1305	1307	602
165°	1424	1419	1424	1419	1424	402
175°	1481	1475	1481	1475	1481	141
180°	1484	1484	1484	1484	1484	

TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	471.5	475.2	477.0	479.7	482.5	486.6	487.9	490.2	489.3	491.1	492.0
5°	469.7	476.1	481.5	488.4	494.8	499.3	503.9	511.2	516.6	517.5	521.6
7.5°	466.5	475.6	485.2	494.8	507.1	514.3	522.5	532.6	540.8	554.0	559.0
10°	462.4	475.2	488.8	502.0	518.9	530.3	540.3	557.2	574.0	587.7	600.4
12.5°	456.0	472.0	489.7	509.3	531.2	544.4	558.1	580.4	605.9	626.9	640.5
15°	448.3	468.3	491.1	512.1	536.2	560.8	575.4	600.4	636.9	656.5	691.6
17.5°	441.9	462.4	485.2	518.0	550.8	575.4	585.9	631.9	656.9	689.7	729.4
20°	431.9	457.9	487.0	519.8	562.2	577.2	598.6	645.1	676.1	718.9	767.6
22.5°	421.4	449.2	484.3	518.4	565.8	581.8	610.9	647.8	697.0	739.4	793.2
25°	410.0	440.1	475.6	516.2	562.6	585.9	613.2	658.8	712.1	765.4	815.0
27.5°	398.6	431.4	468.3	508.9	554.0	581.3	608.6	656.0	724.4	782.2	845.5
30°	387.7	420.5	457.4	498.9	546.2	572.7	598.6	657.9	733.9	799.1	862.9
32.5°	375.8	409.6	448.3	482.9	530.7	559.0	588.1	657.9	739.9	809.1	867.4
35°	361.7	396.4	429.6	464.2	511.6	543.0	575.8	653.3	745.3	812.3	848.3
37.5°	348.1	378.6	407.3	441.0	490.7	524.4	562.2	647.8	742.6	798.6	808.6
40°	332.6	363.1	386.3	417.8	470.2	509.3	547.6	640.5	730.7	766.3	737.1
42.5°	317.5	341.7	361.7	392.3	449.2	487.5	528.9	627.3	707.5	714.8	649.2
45°	300.2	317.5	335.3	369.9	426.4	465.6	511.6	608.2	670.2	649.2	566.3
47.5°	277.9	293.4	313.0	344.9	402.3	442.8	486.6	583.6	615.9	572.2	481.5
50°	256.5	269.7	287.9	318.9	376.8	416.4	462.9	544.9	560.8	492.0	415.0
52.5°	235.1	245.1	262.9	293.8	351.7	390.0	432.3	505.2	496.1	422.3	354.0
55°	212.8	221.4	238.3	268.8	322.5	359.0	399.5	456.5	432.8	362.6	308.0
57.5°	190.9	200.0	217.3	242.8	293.4	328.9	361.3	405.9	370.4	314.3	266.1
60°	171.3	179.0	192.3	217.3	263.3	292.0	321.6	352.2	322.5	268.3	231.4
62.5°	150.8	158.1	170.4	193.2	232.8	258.3	282.0	307.1	274.3	234.6	201.8
65°	131.7	137.6	149.0	169.9	202.3	223.2	242.4	259.7	233.3	196.8	172.2
67.5°	114.3	119.4	128.9	147.6	174.9	190.0	205.5	220.0	197.7	168.6	147.6
70°	95.7	99.8	108.4	122.1	144.0	159.5	170.8	181.8	161.7	138.5	124.4
72.5°	79.3	83.4	88.8	103.0	118.0	127.6	139.9	145.8	134.4	115.3	101.1
75°	63.3	66.5	71.5	80.6	94.8	101.1	108.9	113.4	103.0	90.2	81.5
77.5°	49.7	51.0	54.7	61.0	70.6	77.9	83.8	86.6	79.3	71.1	63.8
80°	35.1	36.9	39.6	45.1	52.4	54.7	58.3	61.5	56.9	49.7	45.1
82.5°	23.2	25.5	26.9	29.2	33.7	36.4	37.4	40.1	36.0	33.3	31.4
85°	13.7	14.6	15.0	16.4	18.7	20.0	21.4	21.9	21.0	20.5	18.7
87.5°	6.8	6.8	6.8	7.7	8.2	9.1	9.6	9.6	9.6	9.1	8.7
90°	1.2	3.8	6.4	8.9	11.5	12.8	14.5	17.9	21.2	24.6	28.0
92.5°	35.0	36.6	38.1	39.7	41.2	42.0	42.8	44.3	45.9	47.4	49.0
95°	68.8	70.6	72.4	74.3	76.1	77.0	78.0	80.1	82.2	84.2	86.3
97.5°	113.1	114.4	115.7	117.0	118.3	118.9	119.7	121.2	122.8	124.3	125.9
100°	158.6	160.2	161.7	163.3	164.8	165.6	166.2	167.5	168.8	170.1	171.4
102.5°	211.1	211.9	212.6	213.4	214.1	214.5	215.4	217.2	219.1	220.9	222.7
105°	262.4	262.9	263.4	263.9	264.4	264.7	265.9	268.2	270.5	272.9	275.2
107.5°	323.0	323.3	323.5	323.8	324.1	324.2	324.7	325.7	326.8	327.8	328.8
110°	379.0	379.5	380.0	380.5	381.0	381.3	381.6	382.1	382.6	383.1	383.6

TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	437.3	437.5	437.8	438.0	438.3	438.4	438.4	438.4	438.4	438.4	438.4
115°	495.6	496.4	497.2	497.9	498.7	499.1	498.8	498.3	497.8	497.2	496.7
117.5°	555.0	555.3	555.5	555.8	556.1	556.2	555.9	555.4	554.9	554.4	553.9
120°	609.8	611.4	612.9	614.5	616.0	616.8	616.2	614.9	613.6	612.3	611.0
122.5°	667.0	668.0	669.0	670.1	671.1	671.6	671.3	670.8	670.3	669.8	669.3
125°	725.3	726.1	726.9	727.6	728.4	728.8	728.5	728.0	727.5	726.9	726.4
127.5°	778.9	780.5	782.0	783.6	785.1	785.9	785.6	785.1	784.6	784.1	783.6
130°	832.5	834.6	836.7	838.8	840.9	841.9	841.5	840.7	840.0	839.2	838.4
132.5°	886.2	888.3	890.3	892.4	894.5	895.5	895.2	894.7	894.2	893.7	893.2
135°	941.0	942.6	944.1	945.7	947.2	948.0	947.9	947.6	947.3	947.1	946.8
137.5°	991.1	992.4	993.7	995.0	996.3	997.0	997.4	998.1	998.9	999.6	1000.4
140°	1043.6	1044.9	1046.2	1047.5	1048.8	1049.4	1049.5	1049.8	1050.1	1050.3	1050.6
142.5°	1091.4	1092.7	1094.0	1095.3	1096.6	1097.2	1097.5	1098.0	1098.5	1099.1	1099.6
145°	1141.5	1142.0	1142.6	1143.1	1143.6	1143.9	1144.3	1145.1	1145.8	1146.6	1147.4
147.5°	1184.7	1185.7	1186.7	1187.8	1188.8	1189.3	1189.7	1190.5	1191.2	1192.0	1192.8
150°	1230.2	1230.7	1231.2	1231.7	1232.2	1232.5	1232.8	1233.3	1233.8	1234.3	1234.8
152.5°	1267.5	1268.3	1269.1	1269.8	1270.6	1271.0	1271.1	1271.4	1271.6	1271.9	1272.1
155°	1307.1	1307.1	1307.1	1307.1	1307.1	1307.1	1307.2	1307.5	1307.8	1308.0	1308.3
157.5°	1340.9	1340.7	1340.4	1340.2	1339.9	1339.8	1339.9	1340.2	1340.4	1340.7	1340.9
160°	1372.4	1371.9	1371.4	1370.9	1370.4	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1
162.5°	1400.4	1399.6	1398.8	1398.1	1397.3	1396.9	1397.0	1397.3	1397.6	1397.8	1398.1
165°	1423.7	1422.9	1422.1	1421.4	1420.6	1420.2	1420.2	1420.2	1420.2	1420.2	1420.2
167.5°	1443.5	1442.5	1441.5	1440.4	1439.4	1438.9	1439.0	1439.3	1439.5	1439.8	1440.0
170°	1459.9	1458.9	1457.8	1456.8	1455.7	1455.2	1455.2	1455.2	1455.2	1455.2	1455.2
172.5°	1472.7	1471.7	1470.6	1469.6	1468.5	1468.0	1468.0	1468.0	1468.0	1468.0	1468.0
175°	1480.9	1479.9	1478.8	1477.8	1476.7	1476.2	1476.2	1476.2	1476.2	1476.2	1476.2
177.5°	1485.5	1484.5	1483.5	1482.4	1481.4	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9
180°	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3

TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	495.2	496.1	499.3	501.6	506.1	505.7	505.7	505.2	503.9	506.1	507.5
5°	529.8	537.6	538.5	548.5	549.0	553.1	555.8	553.5	559.0	558.5	554.4
7.5°	572.7	583.1	588.1	597.7	608.6	605.9	616.4	618.2	617.3	621.9	625.0
10°	619.6	637.8	650.6	668.3	672.9	675.6	682.5	688.4	700.2	691.1	697.0
12.5°	673.3	686.6	703.4	731.7	745.8	754.9	758.1	762.2	770.4	765.4	765.8
15°	718.4	736.2	764.9	800.0	804.1	815.5	812.7	837.3	849.2	831.4	841.4
17.5°	765.4	789.1	823.2	853.7	871.1	878.8	886.1	909.8	908.9	906.1	908.4
20°	795.4	834.2	876.5	917.1	922.1	928.0	947.6	957.6	955.8	963.5	968.6
22.5°	837.8	878.8	923.9	950.8	962.2	969.0	984.5	990.9	993.6	995.4	992.2
25°	873.3	917.1	950.3	974.0	980.9	984.5	989.5	991.3	990.0	986.8	989.5
27.5°	897.5	932.6	955.3	966.3	962.6	956.7	947.1	940.8	926.6	919.8	928.0
30°	907.5	923.0	929.8	911.6	893.4	878.8	860.6	826.9	800.4	808.2	797.7
32.5°	891.6	881.5	848.7	801.8	787.7	764.0	712.5	672.9	674.3	653.3	662.0
35°	844.6	799.1	737.1	666.1	647.4	634.6	578.1	569.5	551.2	531.7	537.1
37.5°	761.7	695.2	620.0	567.6	539.9	512.1	480.2	461.0	450.1	441.9	448.3
40°	660.6	579.5	517.5	470.6	446.9	429.2	407.3	388.2	375.8	374.5	376.8
42.5°	561.3	492.9	436.0	391.3	383.6	362.6	348.5	333.5	329.8	323.9	327.1
45°	475.2	419.6	372.7	336.2	327.1	321.6	304.3	294.8	290.7	287.0	292.5
47.5°	412.8	354.4	320.3	298.4	289.3	280.2	270.6	264.2	261.0	261.5	261.0
50°	352.6	309.8	279.7	262.9	257.4	251.0	243.3	239.2	237.8	233.7	236.9
52.5°	303.4	272.4	251.5	235.5	231.4	226.9	220.5	218.2	215.0	214.1	214.1
55°	263.8	239.6	222.8	212.3	207.3	203.6	200.0	197.3	195.0	195.0	195.0
57.5°	232.8	211.8	199.5	190.4	188.6	185.0	180.9	180.9	177.7	177.2	178.6
60°	206.4	187.7	178.1	170.4	167.7	166.7	162.6	162.6	161.7	159.5	161.3
62.5°	179.5	165.8	157.6	151.7	149.0	149.0	145.8	143.5	143.5	144.0	143.1
65°	154.9	144.9	137.6	133.0	131.7	129.8	129.4	127.6	126.2	126.6	126.2
67.5°	133.0	125.3	120.3	116.6	114.3	113.4	112.1	112.1	111.2	111.6	109.3
70°	113.4	105.7	101.6	97.9	97.0	97.0	95.2	95.7	94.8	96.1	95.2
72.5°	93.4	87.5	84.3	82.9	82.0	81.5	80.6	79.7	79.3	80.2	79.7
75°	75.6	70.6	68.3	67.4	66.5	66.5	66.1	65.6	65.1	65.1	65.1
77.5°	58.8	55.6	52.8	53.8	52.4	52.8	51.5	51.5	51.9	51.5	51.5
80°	43.3	41.0	41.0	40.1	38.3	39.2	39.2	37.8	37.4	38.3	36.9
82.5°	28.7	28.2	27.3	26.9	26.0	26.4	26.0	25.5	25.1	26.0	25.1
85°	16.9	16.9	16.4	15.5	16.4	15.9	15.5	15.5	15.0	15.0	15.0
87.5°	8.7	7.7	7.7	7.3	7.7	6.8	7.3	6.8	6.4	6.8	6.4
90°	29.0	30.0	31.1	32.1	32.6	32.9	33.4	33.9	34.5	35.0	34.5
92.5°	49.8	50.6	51.3	52.1	52.5	52.2	51.7	51.2	50.6	50.1	50.6
95°	87.3	88.3	89.4	90.4	90.9	90.9	90.9	90.9	90.9	90.9	90.9
97.5°	127.2	128.5	129.8	131.1	131.8	131.7	131.4	131.1	130.9	130.6	130.9
100°	172.2	173.0	173.7	174.5	174.9	175.2	175.7	176.2	176.7	177.2	176.7
102.5°	223.5	224.3	225.0	225.8	226.2	226.1	225.8	225.5	225.3	225.0	225.3
105°	275.2	275.2	275.2	275.2	275.2	275.5	276.0	276.5	277.0	277.5	277.0
107.5°	329.6	330.4	331.1	331.9	332.3	332.2	331.9	331.7	331.4	331.2	331.4
110°	384.6	385.7	386.7	387.8	388.3	388.0	387.5	387.0	386.5	386.0	386.5

TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	439.7	441.0	442.3	443.6	444.3	444.3	444.3	444.3	444.3	444.3	444.3
115°	497.0	497.2	497.5	497.8	497.9	497.8	497.5	497.2	497.0	496.7	497.0
117.5°	553.9	553.9	553.9	553.9	553.9	553.5	552.7	552.0	551.2	550.4	551.2
120°	610.7	610.5	610.2	609.9	609.8	609.5	609.0	608.5	608.0	607.5	608.0
122.5°	668.5	667.7	667.0	666.2	665.8	665.4	664.6	663.9	663.1	662.3	663.1
125°	725.4	724.4	723.3	722.3	721.8	721.3	720.2	719.2	718.1	717.1	718.1
127.5°	782.0	780.5	778.9	777.4	776.6	776.1	775.0	774.0	772.9	771.9	772.9
130°	837.4	836.3	835.3	834.2	833.7	832.8	831.0	829.1	827.3	825.5	827.3
132.5°	891.9	890.6	889.3	888.0	887.3	886.7	885.4	884.1	882.8	881.5	882.8
135°	945.8	944.7	943.7	942.6	942.1	941.8	941.3	940.8	940.3	939.8	940.3
137.5°	999.1	997.8	996.5	995.2	994.6	994.2	993.4	992.7	991.9	991.1	991.9
140°	1050.3	1050.1	1049.8	1049.5	1049.4	1048.5	1046.7	1044.9	1043.1	1041.3	1043.1
142.5°	1099.3	1099.1	1098.8	1098.5	1098.4	1097.8	1096.5	1095.2	1093.9	1092.6	1093.9
145°	1147.1	1146.9	1146.6	1146.3	1146.2	1145.7	1144.6	1143.6	1142.5	1141.5	1142.5
147.5°	1192.8	1192.8	1192.8	1192.8	1192.8	1192.0	1190.5	1188.9	1187.4	1185.8	1187.4
150°	1234.8	1234.8	1234.8	1234.8	1234.8	1234.0	1232.5	1230.9	1229.4	1227.8	1229.4
152.5°	1272.6	1273.2	1273.7	1274.2	1274.5	1273.8	1272.5	1271.2	1269.9	1268.6	1269.9
155°	1309.3	1310.3	1311.4	1312.4	1312.9	1312.0	1310.2	1308.4	1306.6	1304.8	1306.6
157.5°	1341.9	1343.0	1344.0	1345.1	1345.6	1344.8	1343.3	1341.7	1340.2	1338.6	1340.2
160°	1371.4	1372.7	1374.0	1375.3	1375.9	1375.4	1374.3	1373.3	1372.2	1371.2	1372.2
162.5°	1399.4	1400.7	1402.0	1403.3	1403.9	1403.0	1401.2	1399.3	1397.5	1395.7	1397.5
165°	1421.8	1423.3	1424.9	1426.4	1427.2	1426.3	1424.5	1422.7	1420.9	1419.1	1420.9
167.5°	1441.6	1443.1	1444.7	1446.2	1447.0	1446.2	1444.7	1443.1	1441.6	1440.0	1441.6
170°	1457.0	1458.8	1460.7	1462.5	1463.4	1462.5	1460.7	1458.8	1457.0	1455.2	1457.0
172.5°	1469.6	1471.1	1472.7	1474.2	1475.0	1474.1	1472.3	1470.5	1468.7	1466.9	1468.7
175°	1477.8	1479.3	1480.9	1482.4	1483.2	1482.3	1480.5	1478.6	1476.8	1475.0	1476.8
177.5°	1482.4	1484.0	1485.5	1487.0	1487.8	1486.9	1485.1	1483.3	1481.5	1479.7	1481.5
180°	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3

TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	503.9	505.2	501.6	500.7	500.7	502.5	501.1	488.8	491.1	488.4	487.5
5°	559.4	556.7	553.1	551.2	549.0	542.6	542.1	528.0	525.3	516.2	512.1
7.5°	620.5	618.2	607.3	605.9	605.0	599.1	584.0	569.0	558.1	547.6	537.6
10°	690.2	683.4	678.4	668.3	663.3	655.1	635.5	621.4	602.7	586.8	565.8
12.5°	774.0	766.3	749.4	742.1	735.8	713.0	693.4	677.4	641.0	630.1	604.1
15°	835.5	819.1	817.3	801.4	800.4	775.4	738.0	720.7	692.5	652.4	625.5
17.5°	902.0	887.5	876.1	856.9	854.2	830.5	803.2	760.8	729.8	691.6	657.4
20°	950.8	943.0	923.5	915.7	899.8	879.7	851.5	799.1	761.3	723.0	681.1
22.5°	989.5	981.8	966.3	955.8	946.7	920.7	887.0	842.4	790.4	740.3	697.0
25°	989.1	986.8	980.4	975.4	968.6	949.4	921.2	878.3	820.5	765.4	705.2
27.5°	933.0	939.4	950.3	955.8	954.4	951.7	935.8	899.8	847.8	782.2	714.8
30°	816.4	839.6	860.1	887.5	895.7	915.7	924.8	904.3	862.9	801.8	727.1
32.5°	677.0	710.7	755.3	770.4	796.3	835.1	878.3	886.1	860.1	813.2	734.8
35°	555.3	583.1	617.8	641.5	664.7	727.6	782.2	829.6	838.3	807.3	733.0
37.5°	459.7	479.3	509.8	529.8	551.2	605.0	681.5	743.0	786.3	787.2	728.0
40°	390.4	399.1	425.5	440.1	460.6	507.1	575.4	655.6	718.9	748.1	714.8
42.5°	330.7	342.1	364.0	374.9	388.2	428.7	473.8	549.9	628.2	690.7	690.2
45°	295.2	303.4	313.4	322.5	337.6	361.7	413.2	470.2	545.3	615.9	643.7
47.5°	263.8	271.5	281.5	284.3	294.3	317.1	348.5	398.2	468.3	538.5	590.9
50°	237.4	243.7	250.6	255.6	260.1	278.8	302.5	344.4	400.5	468.3	533.5
52.5°	216.9	221.4	227.3	230.1	234.2	247.8	266.1	297.0	343.0	405.0	468.3
55°	197.7	200.9	204.6	209.1	210.9	221.0	235.1	261.5	295.7	351.2	411.4
57.5°	180.0	181.3	183.6	186.3	188.6	197.3	209.6	227.3	257.4	300.2	357.2
60°	159.9	163.6	164.9	167.7	169.0	175.9	185.4	200.5	223.7	260.6	303.4
62.5°	143.1	145.3	147.6	149.0	152.2	154.4	162.2	175.9	195.0	222.3	261.0
65°	128.0	128.9	130.3	131.7	132.6	135.3	142.6	151.7	166.3	190.4	220.5
67.5°	110.7	111.6	113.4	113.9	114.8	118.4	122.5	130.3	142.6	160.8	185.4
70°	93.8	95.2	96.1	97.0	98.4	99.8	104.3	110.7	120.3	133.0	152.2
72.5°	79.3	80.6	80.6	81.5	81.1	82.9	87.5	92.0	98.4	108.9	125.7
75°	64.7	64.7	65.6	66.1	66.5	68.3	70.2	73.8	78.8	87.0	97.5
77.5°	51.0	50.6	51.5	51.5	51.5	52.8	54.7	56.5	59.7	65.6	73.8
80°	37.4	37.4	38.3	38.7	37.8	38.3	39.2	41.0	43.3	47.4	51.9
82.5°	24.6	26.4	26.0	26.4	26.0	26.9	27.3	27.8	28.7	30.5	33.7
85°	15.0	15.0	15.0	15.5	15.0	15.5	15.5	15.5	15.9	16.9	18.2
87.5°	6.4	6.4	6.4	6.8	6.4	6.4	6.8	6.4	6.8	6.8	7.3
90°	33.9	33.4	32.9	32.6	32.1	31.1	30.0	29.0	28.0	24.6	21.2
92.5°	51.2	51.7	52.2	52.5	52.1	51.3	50.6	49.8	49.0	47.4	45.9
95°	90.9	90.9	90.9	90.9	90.4	89.4	88.3	87.3	86.3	84.2	82.2
97.5°	131.1	131.4	131.7	131.8	131.1	129.8	128.5	127.2	125.9	124.3	122.8
100°	176.2	175.7	175.2	174.9	174.5	173.7	173.0	172.2	171.4	170.1	168.8
102.5°	225.5	225.8	226.1	226.2	225.8	225.0	224.3	223.5	222.7	220.9	219.1
105°	276.5	276.0	275.5	275.2	275.2	275.2	275.2	275.2	275.2	272.9	270.5
107.5°	331.7	331.9	332.2	332.3	331.9	331.1	330.4	329.6	328.8	327.8	326.8
110°	387.0	387.5	388.0	388.3	387.8	386.7	385.7	384.6	383.6	383.1	382.6

TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	444.3	444.3	444.3	444.3	443.6	442.3	441.0	439.7	438.4	438.4	438.4
115°	497.2	497.5	497.8	497.9	497.8	497.5	497.2	497.0	496.7	497.2	497.8
117.5°	552.0	552.7	553.5	553.9	553.9	553.9	553.9	553.9	553.9	554.4	554.9
120°	608.5	609.0	609.5	609.8	609.9	610.2	610.5	610.7	611.0	612.3	613.6
122.5°	663.9	664.6	665.4	665.8	666.2	667.0	667.7	668.5	669.3	669.8	670.3
125°	719.2	720.2	721.3	721.8	722.3	723.3	724.4	725.4	726.4	726.9	727.5
127.5°	774.0	775.0	776.1	776.6	777.4	778.9	780.5	782.0	783.6	784.1	784.6
130°	829.1	831.0	832.8	833.7	834.2	835.3	836.3	837.4	838.4	839.2	840.0
132.5°	884.1	885.4	886.7	887.3	888.0	889.3	890.6	891.9	893.2	893.7	894.2
135°	940.8	941.3	941.8	942.1	942.6	943.7	944.7	945.8	946.8	947.1	947.3
137.5°	992.7	993.4	994.2	994.6	995.2	996.5	997.8	999.1	1000.4	999.6	998.9
140°	1044.9	1046.7	1048.5	1049.4	1049.5	1049.8	1050.1	1050.3	1050.6	1050.3	1050.1
142.5°	1095.2	1096.5	1097.8	1098.4	1098.5	1098.8	1099.1	1099.3	1099.6	1099.1	1098.5
145°	1143.6	1144.6	1145.7	1146.2	1146.3	1146.6	1146.9	1147.1	1147.4	1146.6	1145.8
147.5°	1188.9	1190.5	1192.0	1192.8	1192.8	1192.8	1192.8	1192.8	1192.8	1192.0	1191.2
150°	1230.9	1232.5	1234.0	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.3	1233.8
152.5°	1271.2	1272.5	1273.8	1274.5	1274.2	1273.7	1273.2	1272.6	1272.1	1271.9	1271.6
155°	1308.4	1310.2	1312.0	1312.9	1312.4	1311.4	1310.3	1309.3	1308.3	1308.0	1307.8
157.5°	1341.7	1343.3	1344.8	1345.6	1345.1	1344.0	1343.0	1341.9	1340.9	1340.7	1340.4
160°	1373.3	1374.3	1375.4	1375.9	1375.3	1374.0	1372.7	1371.4	1370.1	1370.1	1370.1
162.5°	1399.3	1401.2	1403.0	1403.9	1403.3	1402.0	1400.7	1399.4	1398.1	1397.8	1397.6
165°	1422.7	1424.5	1426.3	1427.2	1426.4	1424.9	1423.3	1421.8	1420.2	1420.2	1420.2
167.5°	1443.1	1444.7	1446.2	1447.0	1446.2	1444.7	1443.1	1441.6	1440.0	1439.8	1439.5
170°	1458.8	1460.7	1462.5	1463.4	1462.5	1460.7	1458.8	1457.0	1455.2	1455.2	1455.2
172.5°	1470.5	1472.3	1474.1	1475.0	1474.2	1472.7	1471.1	1469.6	1468.0	1468.0	1468.0
175°	1478.6	1480.5	1482.3	1483.2	1482.4	1480.9	1479.3	1477.8	1476.2	1476.2	1476.2
177.5°	1483.3	1485.1	1486.9	1487.8	1487.0	1485.5	1484.0	1482.4	1480.9	1480.9	1480.9
180°	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3

TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	482.9	481.5	481.5	480.6	477.9	472.9	472.4	473.3	470.6	467.9	463.8
5°	506.6	497.9	495.2	492.5	487.0	477.9	474.3	471.1	466.1	460.1	453.8
7.5°	526.6	514.3	510.7	505.7	494.8	482.0	473.8	467.0	460.1	451.9	444.2
10°	551.7	533.9	525.3	518.0	503.0	485.2	472.9	462.9	451.9	441.9	431.9
12.5°	579.9	551.2	548.5	530.7	513.4	487.0	472.0	457.4	442.8	430.5	420.0
15°	603.6	572.2	560.8	549.0	515.7	482.9	468.3	451.9	435.1	421.9	406.4
17.5°	618.7	592.7	568.6	552.6	518.0	488.8	460.6	441.9	424.1	405.9	393.2
20°	636.9	599.1	578.1	556.7	522.5	484.3	456.0	432.8	410.9	394.5	379.0
22.5°	655.1	604.1	586.8	563.5	523.5	479.7	447.8	424.6	399.5	383.1	366.3
25°	653.3	611.4	582.7	563.1	514.3	475.6	438.3	410.9	387.7	366.7	349.9
27.5°	654.7	603.2	574.0	551.2	508.0	469.7	428.2	399.5	375.4	353.5	335.8
30°	655.1	590.9	565.4	538.0	496.1	455.6	416.9	387.7	362.2	338.5	322.5
32.5°	653.8	580.9	549.0	524.4	477.4	441.9	403.6	372.7	346.7	324.8	309.8
35°	650.6	569.0	532.1	501.1	458.3	422.3	391.3	359.4	331.7	311.6	294.3
37.5°	641.9	556.3	514.3	483.8	436.0	399.5	372.2	345.8	318.9	295.2	280.6
40°	635.5	538.9	496.6	463.3	411.8	376.3	353.5	328.5	302.0	280.6	266.5
42.5°	620.9	522.5	478.4	438.7	388.2	351.7	330.3	310.2	287.5	266.5	253.8
45°	597.3	504.8	456.0	415.9	362.2	327.6	308.0	291.6	271.5	251.5	238.7
47.5°	564.0	479.3	432.3	392.3	336.7	301.6	282.0	269.7	253.8	236.9	226.0
50°	528.0	451.5	408.2	368.6	312.1	277.9	258.8	247.4	236.9	221.4	210.9
52.5°	481.1	421.9	380.4	342.6	285.6	252.8	236.0	227.8	216.9	205.9	196.8
55°	435.5	383.6	349.4	313.4	259.7	229.2	212.8	204.1	197.7	188.6	181.3
57.5°	382.7	348.1	316.6	283.8	235.5	207.7	192.3	181.8	177.7	173.6	166.7
60°	333.9	307.5	282.0	254.7	210.5	185.4	170.4	162.2	158.1	155.4	150.8
62.5°	289.3	268.8	246.9	225.1	185.0	162.2	150.8	142.6	139.0	138.5	134.4
65°	246.5	231.9	214.1	192.7	161.3	141.2	130.3	125.3	121.2	121.2	118.0
67.5°	203.6	193.6	179.5	164.5	139.9	121.2	111.2	106.6	104.3	104.3	102.0
70°	169.5	162.6	149.9	136.7	115.3	101.1	93.4	89.3	87.9	88.4	86.6
72.5°	137.6	130.3	119.8	110.2	94.3	83.8	78.4	73.8	71.5	72.0	71.5
75°	106.6	103.0	93.8	86.6	73.8	66.5	61.5	59.2	57.4	57.9	56.9
77.5°	80.2	74.7	69.7	64.7	56.9	51.0	46.9	44.6	43.3	43.3	43.3
80°	54.7	53.8	49.7	46.9	40.5	36.0	32.8	32.3	31.0	31.0	31.0
82.5°	35.5	33.3	31.0	29.2	25.5	22.8	21.4	20.5	20.0	19.6	20.5
85°	19.6	18.2	17.3	15.5	14.1	12.8	11.4	10.9	10.5	10.9	10.5
87.5°	7.7	6.4	6.4	5.9	5.5	5.0	5.0	4.1	4.1	3.6	3.6
90°	17.9	14.5	12.8	11.5	8.9	6.4	3.8	1.2	3.8	6.4	8.9
92.5°	44.3	42.8	42.0	41.2	39.7	38.1	36.6	35.0	36.6	38.1	39.7
95°	80.1	78.0	77.0	76.1	74.3	72.4	70.6	68.8	70.6	72.4	74.3
97.5°	121.2	119.7	118.9	118.3	117.0	115.7	114.4	113.1	114.4	115.7	117.0
100°	167.5	166.2	165.6	164.8	163.3	161.7	160.2	158.6	160.2	161.7	163.3
102.5°	217.2	215.4	214.5	214.1	213.4	212.6	211.9	211.1	211.9	212.6	213.4
105°	268.2	265.9	264.7	264.4	263.9	263.4	262.9	262.4	262.9	263.4	263.9
107.5°	325.7	324.7	324.2	324.1	323.8	323.5	323.3	323.0	323.3	323.5	323.8
110°	382.1	381.6	381.3	381.0	380.5	380.0	379.5	379.0	379.5	380.0	380.5

TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	438.4	438.4	438.4	438.3	438.0	437.8	437.5	437.3	437.5	437.8	438.0
115°	498.3	498.8	499.1	498.7	497.9	497.2	496.4	495.6	496.4	497.2	497.9
117.5°	555.4	555.9	556.2	556.1	555.8	555.5	555.3	555.0	555.3	555.5	555.8
120°	614.9	616.2	616.8	616.0	614.5	612.9	611.4	609.8	611.4	612.9	614.5
122.5°	670.8	671.3	671.6	671.1	670.1	669.0	668.0	667.0	668.0	669.0	670.1
125°	728.0	728.5	728.8	728.4	727.6	726.9	726.1	725.3	726.1	726.9	727.6
127.5°	785.1	785.6	785.9	785.1	783.6	782.0	780.5	778.9	780.5	782.0	783.6
130°	840.7	841.5	841.9	840.9	838.8	836.7	834.6	832.5	834.6	836.7	838.8
132.5°	894.7	895.2	895.5	894.5	892.4	890.3	888.3	886.2	888.3	890.3	892.4
135°	947.6	947.9	948.0	947.2	945.7	944.1	942.6	941.0	942.6	944.1	945.7
137.5°	998.1	997.4	997.0	996.3	995.0	993.7	992.4	991.1	992.4	993.7	995.0
140°	1049.8	1049.5	1049.4	1048.8	1047.5	1046.2	1044.9	1043.6	1044.9	1046.2	1047.5
142.5°	1098.0	1097.5	1097.2	1096.6	1095.3	1094.0	1092.7	1091.4	1092.7	1094.0	1095.3
145°	1145.1	1144.3	1143.9	1143.6	1143.1	1142.6	1142.0	1141.5	1142.0	1142.6	1143.1
147.5°	1190.5	1189.7	1189.3	1188.8	1187.8	1186.7	1185.7	1184.7	1185.7	1186.7	1187.8
150°	1233.3	1232.8	1232.5	1232.2	1231.7	1231.2	1230.7	1230.2	1230.7	1231.2	1231.7
152.5°	1271.4	1271.1	1271.0	1270.6	1269.8	1269.1	1268.3	1267.5	1268.3	1269.1	1269.8
155°	1307.5	1307.2	1307.1	1307.1	1307.1	1307.1	1307.1	1307.1	1307.1	1307.1	1307.1
157.5°	1340.2	1339.9	1339.8	1339.9	1340.2	1340.4	1340.7	1340.9	1340.7	1340.4	1340.2
160°	1370.1	1370.1	1370.1	1370.4	1370.9	1371.4	1371.9	1372.4	1371.9	1371.4	1370.9
162.5°	1397.3	1397.0	1396.9	1397.3	1398.1	1398.8	1399.6	1400.4	1399.6	1398.8	1398.1
165°	1420.2	1420.2	1420.2	1420.6	1421.4	1422.1	1422.9	1423.7	1422.9	1422.1	1421.4
167.5°	1439.3	1439.0	1438.9	1439.4	1440.4	1441.5	1442.5	1443.5	1442.5	1441.5	1440.4
170°	1455.2	1455.2	1455.2	1455.7	1456.8	1457.8	1458.9	1459.9	1458.9	1457.8	1456.8
172.5°	1468.0	1468.0	1468.0	1468.5	1469.6	1470.6	1471.7	1472.7	1471.7	1470.6	1469.6
175°	1476.2	1476.2	1476.2	1476.7	1477.8	1478.8	1479.9	1480.9	1479.9	1478.8	1477.8
177.5°	1480.9	1480.9	1480.9	1481.4	1482.4	1483.5	1484.5	1485.5	1484.5	1483.5	1482.4
180°	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3

TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	462.9	462.4	463.3	460.6	456.0	453.8	447.4	446.0	445.6	446.0	446.5
5°	450.1	449.7	448.3	443.7	438.3	434.2	426.4	426.0	423.2	420.5	421.9
7.5°	437.8	436.0	433.3	427.3	420.0	415.5	409.1	404.6	400.9	398.6	396.8
10°	425.5	422.8	420.0	412.3	403.2	396.4	388.6	385.0	380.9	379.0	377.2
12.5°	409.6	406.8	401.8	392.7	387.2	378.6	370.8	367.2	364.9	361.3	359.0
15°	396.8	391.3	388.6	379.0	367.6	366.7	352.6	351.7	347.1	347.1	343.5
17.5°	382.2	378.1	373.1	363.5	355.3	347.1	339.9	337.1	333.0	332.1	330.3
20°	368.1	362.6	360.8	351.2	342.6	332.6	324.8	322.1	320.3	318.4	319.8
22.5°	353.5	349.0	344.4	335.8	329.4	319.4	314.8	312.1	309.3	308.4	308.9
25°	339.4	335.3	330.7	322.1	315.3	307.1	303.0	301.6	300.2	300.2	299.8
27.5°	325.7	321.6	317.5	309.8	303.0	297.0	293.8	292.5	291.1	292.0	292.9
30°	311.6	308.0	304.3	297.5	292.0	286.6	284.7	283.8	283.4	285.6	285.6
32.5°	298.9	295.7	292.9	286.6	281.1	276.5	275.2	275.6	276.1	277.4	278.4
35°	285.6	283.4	280.6	275.2	270.6	266.5	267.0	267.0	267.9	270.2	272.0
37.5°	273.8	270.6	268.3	263.8	260.1	256.5	257.9	259.2	260.1	262.9	263.8
40°	259.7	258.3	256.5	251.9	248.7	248.3	248.7	249.7	251.5	252.8	254.2
42.5°	248.3	246.5	244.2	240.5	237.8	238.3	238.7	239.6	240.5	242.8	244.2
45°	235.5	234.2	232.3	229.2	226.9	227.3	227.8	227.8	228.7	231.4	232.3
47.5°	221.4	221.9	219.6	216.4	215.0	215.0	215.0	215.9	218.2	219.1	219.6
50°	207.7	206.8	206.4	203.2	202.3	201.8	202.3	202.7	205.9	205.5	206.8
52.5°	193.2	193.2	192.7	190.9	189.5	189.5	188.6	190.9	191.8	192.7	194.1
55°	179.0	177.7	177.2	176.3	174.5	174.0	174.9	177.7	178.6	179.5	180.9
57.5°	163.6	163.6	162.6	161.3	161.3	161.3	161.3	163.1	164.5	165.4	168.1
60°	149.4	147.6	146.2	146.2	146.2	145.8	148.5	148.5	151.3	151.7	152.6
62.5°	132.6	131.7	130.8	131.2	130.8	131.7	132.6	134.4	134.9	136.2	137.6
65°	116.6	116.6	115.7	118.4	116.6	116.6	118.9	118.9	119.8	121.2	123.0
67.5°	101.1	101.6	100.7	100.7	101.6	102.0	102.5	104.3	104.8	106.6	108.9
70°	85.2	86.1	86.6	85.6	86.6	87.5	88.4	88.8	90.7	91.6	92.9
72.5°	71.1	72.0	70.6	71.1	71.5	72.4	72.9	73.8	74.7	77.4	78.4
75°	56.9	56.5	56.0	57.9	56.9	58.8	59.2	59.2	60.1	62.4	63.3
77.5°	43.7	43.7	44.2	43.3	44.6	44.2	44.6	46.0	47.4	47.4	51.0
80°	30.5	31.4	31.4	31.4	31.9	32.3	31.4	33.7	34.2	34.2	35.5
82.5°	19.6	20.0	19.6	20.5	20.5	21.4	21.0	21.4	22.3	23.2	23.7
85°	10.5	10.5	11.4	11.4	10.9	11.4	10.9	11.4	12.3	12.3	12.8
87.5°	3.6	3.6	3.6	3.6	4.1	3.6	4.1	4.1	3.6	3.6	5.0
90°	11.5	12.8	14.5	17.9	21.2	24.6	28.0	29.0	30.0	31.1	32.1
92.5°	41.2	42.0	42.8	44.3	45.9	47.4	49.0	49.8	50.6	51.3	52.1
95°	76.1	77.0	78.0	80.1	82.2	84.2	86.3	87.3	88.3	89.4	90.4
97.5°	118.3	118.9	119.7	121.2	122.8	124.3	125.9	127.2	128.5	129.8	131.1
100°	164.8	165.6	166.2	167.5	168.8	170.1	171.4	172.2	173.0	173.7	174.5
102.5°	214.1	214.5	215.4	217.2	219.1	220.9	222.7	223.5	224.3	225.0	225.8
105°	264.4	264.7	265.9	268.2	270.5	272.9	275.2	275.2	275.2	275.2	275.2
107.5°	324.1	324.2	324.7	325.7	326.8	327.8	328.8	329.6	330.4	331.1	331.9
110°	381.0	381.3	381.6	382.1	382.6	383.1	383.6	384.6	385.7	386.7	387.8

TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	438.3	438.4	438.4	438.4	438.4	438.4	438.4	439.7	441.0	442.3	443.6
115°	498.7	499.1	498.8	498.3	497.8	497.2	496.7	497.0	497.2	497.5	497.8
117.5°	556.1	556.2	555.9	555.4	554.9	554.4	553.9	553.9	553.9	553.9	553.9
120°	616.0	616.8	616.2	614.9	613.6	612.3	611.0	610.7	610.5	610.2	609.9
122.5°	671.1	671.6	671.3	670.8	670.3	669.8	669.3	668.5	667.7	667.0	666.2
125°	728.4	728.8	728.5	728.0	727.5	726.9	726.4	725.4	724.4	723.3	722.3
127.5°	785.1	785.9	785.6	785.1	784.6	784.1	783.6	782.0	780.5	778.9	777.4
130°	840.9	841.9	841.5	840.7	840.0	839.2	838.4	837.4	836.3	835.3	834.2
132.5°	894.5	895.5	895.2	894.7	894.2	893.7	893.2	891.9	890.6	889.3	888.0
135°	947.2	948.0	947.9	947.6	947.3	947.1	946.8	945.8	944.7	943.7	942.6
137.5°	996.3	997.0	997.4	998.1	998.9	999.6	1000.4	999.1	997.8	996.5	995.2
140°	1048.8	1049.4	1049.5	1049.8	1050.1	1050.3	1050.6	1050.3	1050.1	1049.8	1049.5
142.5°	1096.6	1097.2	1097.5	1098.0	1098.5	1099.1	1099.6	1099.3	1099.1	1098.8	1098.5
145°	1143.6	1143.9	1144.3	1145.1	1145.8	1146.6	1147.4	1147.1	1146.9	1146.6	1146.3
147.5°	1188.8	1189.3	1189.7	1190.5	1191.2	1192.0	1192.8	1192.8	1192.8	1192.8	1192.8
150°	1232.2	1232.5	1232.8	1233.3	1233.8	1234.3	1234.8	1234.8	1234.8	1234.8	1234.8
152.5°	1270.6	1271.0	1271.1	1271.4	1271.6	1271.9	1272.1	1272.6	1273.2	1273.7	1274.2
155°	1307.1	1307.1	1307.2	1307.5	1307.8	1308.0	1308.3	1309.3	1310.3	1311.4	1312.4
157.5°	1339.9	1339.8	1339.9	1340.2	1340.4	1340.7	1340.9	1341.9	1343.0	1344.0	1345.1
160°	1370.4	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1371.4	1372.7	1374.0	1375.3
162.5°	1397.3	1396.9	1397.0	1397.3	1397.6	1397.8	1398.1	1399.4	1400.7	1402.0	1403.3
165°	1420.6	1420.2	1420.2	1420.2	1420.2	1420.2	1420.2	1421.8	1423.3	1424.9	1426.4
167.5°	1439.4	1438.9	1439.0	1439.3	1439.5	1439.8	1440.0	1441.6	1443.1	1444.7	1446.2
170°	1455.7	1455.2	1455.2	1455.2	1455.2	1455.2	1455.2	1457.0	1458.8	1460.7	1462.5
172.5°	1468.5	1468.0	1468.0	1468.0	1468.0	1468.0	1468.0	1469.6	1471.1	1472.7	1474.2
175°	1476.7	1476.2	1476.2	1476.2	1476.2	1476.2	1476.2	1477.8	1479.3	1480.9	1482.4
177.5°	1481.4	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1482.4	1484.0	1485.5	1487.0
180°	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3

TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	446.0	446.5	444.6	443.3	446.9	444.6	444.6	445.1	444.2	445.6	445.1
5°	421.0	421.4	418.2	419.1	417.3	416.9	416.4	419.1	418.7	418.2	419.1
7.5°	396.4	396.4	395.0	394.1	394.1	392.7	394.5	394.1	395.0	395.0	396.4
10°	375.8	376.8	374.5	372.2	371.7	372.2	372.2	372.7	373.1	376.3	375.8
12.5°	359.0	357.6	357.2	355.8	353.5	352.6	351.7	356.7	355.3	355.3	355.3
15°	340.3	343.5	343.0	338.9	338.0	339.9	338.9	338.9	343.5	343.0	342.6
17.5°	330.3	329.4	328.5	326.2	326.6	326.2	326.6	326.6	329.4	329.4	329.4
20°	318.9	317.1	317.1	316.2	316.2	314.8	316.6	317.1	318.9	318.9	319.4
22.5°	308.9	307.5	307.5	307.1	308.0	306.1	308.0	308.4	308.4	309.8	309.8
25°	300.2	299.3	299.3	300.2	300.2	300.2	300.2	302.0	300.7	301.1	300.7
27.5°	292.5	292.9	293.4	293.8	293.4	293.8	294.3	295.2	295.7	295.2	294.3
30°	285.2	286.6	287.0	287.0	287.9	288.4	288.8	288.8	289.3	287.9	288.8
32.5°	279.7	279.7	280.6	281.1	282.0	282.5	282.5	283.4	282.9	281.5	282.0
35°	272.0	272.0	273.8	274.7	276.1	275.6	276.1	276.1	276.5	275.6	274.3
37.5°	264.2	265.1	265.1	267.0	267.4	267.9	267.4	268.3	267.9	267.0	266.5
40°	255.1	254.7	255.1	256.5	256.9	256.9	256.9	257.9	257.9	257.9	257.4
42.5°	243.7	245.1	244.6	246.0	245.6	245.6	246.5	247.4	247.8	246.5	246.9
45°	232.8	232.8	233.7	233.7	234.2	234.2	236.0	235.1	236.0	235.1	235.5
47.5°	221.0	221.4	221.4	221.9	222.8	223.7	222.8	223.2	223.2	223.7	222.8
50°	207.7	207.7	208.7	210.0	211.8	210.9	210.5	212.3	210.9	210.9	210.0
52.5°	194.1	195.4	195.9	197.3	198.6	199.1	199.5	198.6	199.1	197.7	198.2
55°	180.9	181.3	183.1	184.5	185.9	185.9	185.4	185.9	186.3	184.5	184.5
57.5°	167.7	169.0	170.8	170.8	172.7	172.7	172.2	172.2	172.7	171.3	170.8
60°	153.5	154.9	157.2	157.2	159.9	160.4	159.5	158.5	158.5	157.2	157.6
62.5°	138.5	139.9	141.2	143.5	145.3	144.4	146.2	144.4	144.9	142.1	142.1
65°	125.3	125.7	128.0	130.3	130.3	131.2	130.3	130.8	129.4	129.4	127.6
67.5°	109.8	109.8	112.1	114.3	116.6	116.6	116.6	115.3	115.3	113.9	113.9
70°	96.1	95.7	97.9	99.3	100.7	101.1	100.2	99.8	98.9	97.5	97.0
72.5°	79.3	80.2	82.5	83.4	85.6	85.2	87.5	84.7	84.7	82.5	82.0
75°	64.2	65.1	67.4	68.8	70.2	70.2	71.5	70.2	68.3	67.4	67.0
77.5°	51.0	50.6	52.4	54.7	55.1	54.7	55.6	55.1	53.3	53.3	52.4
80°	36.4	37.8	39.6	39.2	41.0	40.5	40.5	39.6	39.6	38.3	39.2
82.5°	24.1	25.5	26.0	25.5	26.0	26.9	27.3	26.9	26.9	26.0	26.4
85°	12.8	12.8	13.7	14.1	13.7	13.7	14.1	15.5	14.6	13.7	14.6
87.5°	4.1	3.6	3.6	4.1	3.6	3.6	4.1	4.1	4.6	4.6	4.6
90°	32.6	32.9	33.4	33.9	34.5	35.0	34.5	33.9	33.4	32.9	32.6
92.5°	52.5	52.2	51.7	51.2	50.6	50.1	50.6	51.2	51.7	52.2	52.5
95°	90.9	90.9	90.9	90.9	90.9	90.9	90.9	90.9	90.9	90.9	90.9
97.5°	131.8	131.7	131.4	131.1	130.9	130.6	130.9	131.1	131.4	131.7	131.8
100°	174.9	175.2	175.7	176.2	176.7	177.2	176.7	176.2	175.7	175.2	174.9
102.5°	226.2	226.1	225.8	225.5	225.3	225.0	225.3	225.5	225.8	226.1	226.2
105°	275.2	275.5	276.0	276.5	277.0	277.5	277.0	276.5	276.0	275.5	275.2
107.5°	332.3	332.2	331.9	331.7	331.4	331.2	331.4	331.7	331.9	332.2	332.3
110°	388.3	388.0	387.5	387.0	386.5	386.0	386.5	387.0	387.5	388.0	388.3

TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	444.3	444.3	444.3	444.3	444.3	444.3	444.3	444.3	444.3	444.3	444.3
115°	497.9	497.8	497.5	497.2	497.0	496.7	497.0	497.2	497.5	497.8	497.9
117.5°	553.9	553.5	552.7	552.0	551.2	550.4	551.2	552.0	552.7	553.5	553.9
120°	609.8	609.5	609.0	608.5	608.0	607.5	608.0	608.5	609.0	609.5	609.8
122.5°	665.8	665.4	664.6	663.9	663.1	662.3	663.1	663.9	664.6	665.4	665.8
125°	721.8	721.3	720.2	719.2	718.1	717.1	718.1	719.2	720.2	721.3	721.8
127.5°	776.6	776.1	775.0	774.0	772.9	771.9	772.9	774.0	775.0	776.1	776.6
130°	833.7	832.8	831.0	829.1	827.3	825.5	827.3	829.1	831.0	832.8	833.7
132.5°	887.3	886.7	885.4	884.1	882.8	881.5	882.8	884.1	885.4	886.7	887.3
135°	942.1	941.8	941.3	940.8	940.3	939.8	940.3	940.8	941.3	941.8	942.1
137.5°	994.6	994.2	993.4	992.7	991.9	991.1	991.9	992.7	993.4	994.2	994.6
140°	1049.4	1048.5	1046.7	1044.9	1043.1	1041.3	1043.1	1044.9	1046.7	1048.5	1049.4
142.5°	1098.4	1097.8	1096.5	1095.2	1093.9	1092.6	1093.9	1095.2	1096.5	1097.8	1098.4
145°	1146.2	1145.7	1144.6	1143.6	1142.5	1141.5	1142.5	1143.6	1144.6	1145.7	1146.2
147.5°	1192.8	1192.0	1190.5	1188.9	1187.4	1185.8	1187.4	1188.9	1190.5	1192.0	1192.8
150°	1234.8	1234.0	1232.5	1230.9	1229.4	1227.8	1229.4	1230.9	1232.5	1234.0	1234.8
152.5°	1274.5	1273.8	1272.5	1271.2	1269.9	1268.6	1269.9	1271.2	1272.5	1273.8	1274.5
155°	1312.9	1312.0	1310.2	1308.4	1306.6	1304.8	1306.6	1308.4	1310.2	1312.0	1312.9
157.5°	1345.6	1344.8	1343.3	1341.7	1340.2	1338.6	1340.2	1341.7	1343.3	1344.8	1345.6
160°	1375.9	1375.4	1374.3	1373.3	1372.2	1371.2	1372.2	1373.3	1374.3	1375.4	1375.9
162.5°	1403.9	1403.0	1401.2	1399.3	1397.5	1395.7	1397.5	1399.3	1401.2	1403.0	1403.9
165°	1427.2	1426.3	1424.5	1422.7	1420.9	1419.1	1420.9	1422.7	1424.5	1426.3	1427.2
167.5°	1447.0	1446.2	1444.7	1443.1	1441.6	1440.0	1441.6	1443.1	1444.7	1446.2	1447.0
170°	1463.4	1462.5	1460.7	1458.8	1457.0	1455.2	1457.0	1458.8	1460.7	1462.5	1463.4
172.5°	1475.0	1474.1	1472.3	1470.5	1468.7	1466.9	1468.7	1470.5	1472.3	1474.1	1475.0
175°	1483.2	1482.3	1480.5	1478.6	1476.8	1475.0	1476.8	1478.6	1480.5	1482.3	1483.2
177.5°	1487.8	1486.9	1485.1	1483.3	1481.5	1479.7	1481.5	1483.3	1485.1	1486.9	1487.8
180°	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3

TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	446.5	447.4	447.8	446.0	444.6	446.9	450.1	452.4	454.2	456.5	457.9
5°	420.0	423.2	423.2	424.1	425.5	427.8	433.7	437.8	441.5	444.2	446.5
7.5°	397.7	400.0	401.4	403.6	405.9	409.1	415.9	421.9	427.3	430.5	434.2
10°	377.7	379.5	381.8	383.1	387.2	391.8	400.5	405.5	411.8	416.9	421.4
12.5°	358.5	364.9	366.3	365.8	369.5	374.5	383.1	390.9	397.7	402.7	407.7
15°	344.9	347.1	349.9	349.4	357.2	358.5	365.8	374.9	384.1	387.2	391.8
17.5°	329.8	333.5	336.2	337.6	339.9	344.9	351.7	358.5	370.4	370.8	382.7
20°	318.0	321.6	323.5	325.3	326.6	332.6	338.5	346.2	355.8	360.8	367.2
22.5°	310.2	312.1	313.4	314.8	316.6	319.8	327.1	335.8	342.1	347.6	351.7
25°	301.1	303.0	304.8	305.7	307.1	308.9	314.3	321.2	330.3	333.9	338.0
27.5°	294.8	294.8	295.7	295.7	297.5	299.3	303.4	309.8	317.1	321.6	327.1
30°	287.9	287.5	287.9	287.5	287.0	289.7	293.4	298.9	303.9	309.3	313.0
32.5°	281.1	280.6	280.6	281.1	279.3	280.6	282.5	287.5	292.9	295.7	299.8
35°	273.8	272.9	272.9	272.9	272.0	271.1	272.9	277.4	281.1	284.7	287.9
37.5°	266.5	265.1	265.1	264.2	263.3	262.0	262.0	265.6	270.6	272.0	276.1
40°	256.5	256.5	255.6	255.1	254.2	253.3	251.9	255.1	259.7	261.0	264.2
42.5°	246.5	245.1	244.6	244.6	244.6	243.3	242.4	244.6	247.4	249.7	251.5
45°	235.1	234.2	234.6	234.2	233.3	232.8	232.3	233.3	236.4	237.4	239.6
47.5°	222.8	222.3	222.3	221.9	221.4	221.9	220.0	222.3	223.2	224.1	226.0
50°	210.0	209.6	209.1	208.7	208.7	209.1	208.7	208.7	210.5	211.4	213.2
52.5°	197.3	195.9	195.9	195.4	195.4	194.5	195.4	195.9	196.8	197.7	198.6
55°	183.6	183.6	182.2	182.2	181.3	181.3	181.8	181.3	183.1	184.1	184.1
57.5°	170.4	168.6	169.0	168.1	167.2	166.7	166.7	167.7	168.6	168.6	169.5
60°	156.3	154.4	154.0	152.2	153.1	151.7	152.2	152.2	154.0	153.1	154.0
62.5°	142.1	139.9	138.5	137.6	137.6	138.0	137.1	136.7	137.6	138.5	140.3
65°	127.1	125.7	124.4	123.0	123.0	122.5	123.5	122.1	121.6	122.1	123.0
67.5°	111.6	110.2	108.9	107.5	108.0	106.6	105.7	107.1	106.1	106.6	107.5
70°	96.6	95.7	92.9	92.0	91.6	92.0	91.6	90.7	92.0	91.6	92.0
72.5°	81.5	80.6	79.3	77.0	77.0	76.5	76.1	76.1	75.6	75.6	75.6
75°	67.0	65.1	63.8	63.3	62.4	62.0	61.5	60.6	61.0	61.5	60.6
77.5°	51.9	49.7	49.2	49.2	47.8	47.8	48.3	47.8	47.4	47.4	47.4
80°	38.3	36.4	36.4	35.5	34.6	34.6	34.6	34.6	34.2	33.7	34.2
82.5°	24.6	24.1	23.7	23.7	24.6	22.8	23.7	23.2	22.8	22.8	22.3
85°	13.7	14.1	13.7	14.1	13.2	13.7	13.7	13.7	13.2	13.7	12.8
87.5°	5.0	5.0	5.0	5.5	5.5	5.5	5.5	5.5	5.9	5.5	5.5
90°	32.1	31.1	30.0	29.0	28.0	24.6	21.2	17.9	14.5	12.8	11.5
92.5°	52.1	51.3	50.6	49.8	49.0	47.4	45.9	44.3	42.8	42.0	41.2
95°	90.4	89.4	88.3	87.3	86.3	84.2	82.2	80.1	78.0	77.0	76.1
97.5°	131.1	129.8	128.5	127.2	125.9	124.3	122.8	121.2	119.7	118.9	118.3
100°	174.5	173.7	173.0	172.2	171.4	170.1	168.8	167.5	166.2	165.6	164.8
102.5°	225.8	225.0	224.3	223.5	222.7	220.9	219.1	217.2	215.4	214.5	214.1
105°	275.2	275.2	275.2	275.2	275.2	272.9	270.5	268.2	265.9	264.7	264.4
107.5°	331.9	331.1	330.4	329.6	328.8	327.8	326.8	325.7	324.7	324.2	324.1
110°	387.8	386.7	385.7	384.6	383.6	383.1	382.6	382.1	381.6	381.3	381.0

TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	443.6	442.3	441.0	439.7	438.4	438.4	438.4	438.4	438.4	438.4	438.3
115°	497.8	497.5	497.2	497.0	496.7	497.2	497.8	498.3	498.8	499.1	498.7
117.5°	553.9	553.9	553.9	553.9	553.9	554.4	554.9	555.4	555.9	556.2	556.1
120°	609.9	610.2	610.5	610.7	611.0	612.3	613.6	614.9	616.2	616.8	616.0
122.5°	666.2	667.0	667.7	668.5	669.3	669.8	670.3	670.8	671.3	671.6	671.1
125°	722.3	723.3	724.4	725.4	726.4	726.9	727.5	728.0	728.5	728.8	728.4
127.5°	777.4	778.9	780.5	782.0	783.6	784.1	784.6	785.1	785.6	785.9	785.1
130°	834.2	835.3	836.3	837.4	838.4	839.2	840.0	840.7	841.5	841.9	840.9
132.5°	888.0	889.3	890.6	891.9	893.2	893.7	894.2	894.7	895.2	895.5	894.5
135°	942.6	943.7	944.7	945.8	946.8	947.1	947.3	947.6	947.9	948.0	947.2
137.5°	995.2	996.5	997.8	999.1	1000.4	999.6	998.9	998.1	997.4	997.0	996.3
140°	1049.5	1049.8	1050.1	1050.3	1050.6	1050.3	1050.1	1049.8	1049.5	1049.4	1048.8
142.5°	1098.5	1098.8	1099.1	1099.3	1099.6	1099.1	1098.5	1098.0	1097.5	1097.2	1096.6
145°	1146.3	1146.6	1146.9	1147.1	1147.4	1146.6	1145.8	1145.1	1144.3	1143.9	1143.6
147.5°	1192.8	1192.8	1192.8	1192.8	1192.8	1192.0	1191.2	1190.5	1189.7	1189.3	1188.8
150°	1234.8	1234.8	1234.8	1234.8	1234.8	1234.3	1233.8	1233.3	1232.8	1232.5	1232.2
152.5°	1274.2	1273.7	1273.2	1272.6	1272.1	1271.9	1271.6	1271.4	1271.1	1271.0	1270.6
155°	1312.4	1311.4	1310.3	1309.3	1308.3	1308.0	1307.8	1307.5	1307.2	1307.1	1307.1
157.5°	1345.1	1344.0	1343.0	1341.9	1340.9	1340.7	1340.4	1340.2	1339.9	1339.8	1339.9
160°	1375.3	1374.0	1372.7	1371.4	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.4
162.5°	1403.3	1402.0	1400.7	1399.4	1398.1	1397.8	1397.6	1397.3	1397.0	1396.9	1397.3
165°	1426.4	1424.9	1423.3	1421.8	1420.2	1420.2	1420.2	1420.2	1420.2	1420.2	1420.6
167.5°	1446.2	1444.7	1443.1	1441.6	1440.0	1439.8	1439.5	1439.3	1439.0	1438.9	1439.4
170°	1462.5	1460.7	1458.8	1457.0	1455.2	1455.2	1455.2	1455.2	1455.2	1455.2	1455.7
172.5°	1474.2	1472.7	1471.1	1469.6	1468.0	1468.0	1468.0	1468.0	1468.0	1468.0	1468.5
175°	1482.4	1480.9	1479.3	1477.8	1476.2	1476.2	1476.2	1476.2	1476.2	1476.2	1476.7
177.5°	1487.0	1485.5	1484.0	1482.4	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1481.4
180°	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3

TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	470.2	470.2	470.2	470.2
2.5°	460.1	461.5	466.1	471.5
5°	451.0	454.7	461.0	469.7
7.5°	441.0	446.5	455.6	466.5
10°	429.6	437.4	448.7	462.4
12.5°	417.3	427.3	441.9	456.0
15°	409.6	419.6	432.8	448.3
17.5°	394.5	406.4	420.0	441.9
20°	379.0	392.3	410.0	431.9
22.5°	367.2	381.3	398.2	421.4
25°	353.1	367.6	385.9	410.0
27.5°	338.0	352.6	373.1	398.6
30°	326.6	340.8	360.4	387.7
32.5°	313.0	326.6	347.1	375.8
35°	297.5	313.0	332.6	361.7
37.5°	285.6	299.8	320.3	348.1
40°	272.9	285.2	305.2	332.6
42.5°	259.2	272.9	290.2	317.5
45°	246.5	256.5	274.3	300.2
47.5°	232.8	244.2	257.9	277.9
50°	218.2	227.8	242.8	256.5
52.5°	204.1	211.8	224.6	235.1
55°	189.1	196.8	206.4	212.8
57.5°	174.9	180.4	186.8	190.9
60°	157.6	163.1	167.2	171.3
62.5°	142.1	146.2	148.5	150.8
65°	126.2	128.5	129.8	131.7
67.5°	108.9	111.2	111.6	114.3
70°	92.9	93.4	94.3	95.7
72.5°	77.9	78.8	78.4	79.3
75°	62.4	63.3	62.4	63.3
77.5°	47.4	48.3	48.3	49.7
80°	34.2	34.6	35.1	35.1
82.5°	22.3	23.7	22.8	23.2
85°	12.8	13.2	13.2	13.7
87.5°	5.9	6.4	5.9	6.8
90°	8.9	6.4	3.8	1.2
92.5°	39.7	38.1	36.6	35.0
95°	74.3	72.4	70.6	68.8
97.5°	117.0	115.7	114.4	113.1
100°	163.3	161.7	160.2	158.6
102.5°	213.4	212.6	211.9	211.1
105°	263.9	263.4	262.9	262.4
107.5°	323.8	323.5	323.3	323.0
110°	380.5	380.0	379.5	379.0

TEST NUMBER: P1011521

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	438.0	437.8	437.5	437.3
115°	497.9	497.2	496.4	495.6
117.5°	555.8	555.5	555.3	555.0
120°	614.5	612.9	611.4	609.8
122.5°	670.1	669.0	668.0	667.0
125°	727.6	726.9	726.1	725.3
127.5°	783.6	782.0	780.5	778.9
130°	838.8	836.7	834.6	832.5
132.5°	892.4	890.3	888.3	886.2
135°	945.7	944.1	942.6	941.0
137.5°	995.0	993.7	992.4	991.1
140°	1047.5	1046.2	1044.9	1043.6
142.5°	1095.3	1094.0	1092.7	1091.4
145°	1143.1	1142.6	1142.0	1141.5
147.5°	1187.8	1186.7	1185.7	1184.7
150°	1231.7	1231.2	1230.7	1230.2
152.5°	1269.8	1269.1	1268.3	1267.5
155°	1307.1	1307.1	1307.1	1307.1
157.5°	1340.2	1340.4	1340.7	1340.9
160°	1370.9	1371.4	1371.9	1372.4
162.5°	1398.1	1398.8	1399.6	1400.4
165°	1421.4	1422.1	1422.9	1423.7
167.5°	1440.4	1441.5	1442.5	1443.5
170°	1456.8	1457.8	1458.9	1459.9
172.5°	1469.6	1470.6	1471.7	1472.7
175°	1477.8	1478.8	1479.9	1480.9
177.5°	1482.4	1483.5	1484.5	1485.5
180°	1484.3	1484.3	1484.3	1484.3

(END OF REPORT)