

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011236

Luminaire Tested: S123DIP-B1000D805UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011236
REPORT IS A COMBINATION OF REPORTS P989317 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1000D805UB50-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6529.0 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011236

CATALOG NUMBER: S123DIP-B1000D805UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011236

CATALOG NUMBER: S123DIP-B1000D805UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66
1	100	96	92	88	93	89	86	83	78	75	73	68	66	64	58	57	55
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	51	49	47
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34
5	70	58	50	43	65	54	47	41	48	42	37	42	37	34	36	33	30
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	29	52	40	33	28	36	30	26	32	27	23	28	24	21
9	52	39	31	26	48	37	30	25	33	27	23	29	24	21	26	22	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16283	16283	16283
5°	16323	15721	15697
10°	16178	15189	15033
15°	15953	14635	14309
20°	15696	14022	13592
25°	15362	13373	12824
30°	14997	12702	12018
35°	14614	12016	11216
40°	14214	11298	10428
45°	13773	10596	9603
50°	13326	9815	8776
55°	12751	9001	7939
60°	12158	8103	7047
65°	11603	7132	6116
70°	10802	6054	5032
75°	9647	4793	3906
80°	8333	3369	2763
85°	6493	1810	1383

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13773 cd/sqm

TEST NUMBER: P1011236

CATALOG NUMBER: S123DIP-B1000D805UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.6	2.2
10°-20°	402.7	6.2
20°-30°	594.7	9.1
30°-40°	694.6	10.6
40°-50°	698.3	10.7
50°-60°	613.4	9.4
60°-70°	456.8	7.0
70°-80°	260.0	4.0
80°-90°	75.9	1.2
90°-100°	60.2	0.9
100°-110°	182.1	2.8
110°-120°	310.1	4.7
120°-130°	407.9	6.2
130°-140°	458.5	7.0
140°-150°	450.7	6.9
150°-160°	379.5	5.8
160°-170°	252.6	3.9
170°-180°	88.5	1.4
0°-30°	1140.0	17.5
0°-40°	1834.6	28.1
0°-60°	3146.3	48.2
0°-90°	3939.0	60.3
90°-120°	552.3	8.5
90°-150°	1869.5	28.6
90°-180°	2590.0	39.7
0°-180°	6529.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1513	1513	1513	1513	1513	
5°	1514	1508	1493	1506	1504	144
15°	1441	1436	1419	1430	1422	406
25°	1308	1301	1284	1285	1281	603
35°	1132	1124	1107	1099	1093	708
45°	927	922	905	890	883	716
55°	704	702	686	671	665	630
65°	480	474	460	450	446	474
75°	254	248	244	238	234	271
85°	68	65	65	62	62	73
90°	1	8	18	21	22	8
95°	43	48	54	57	57	48
105°	165	167	173	173	175	177
115°	312	314	313	314	313	309
125°	457	459	458	454	452	407
135°	593	597	596	593	592	457
145°	719	720	722	722	719	449
155°	823	823	824	827	822	379
165°	897	894	894	899	894	253
175°	932	930	930	934	929	89
180°	935	935	935	935	935	

TEST NUMBER: P1011236

CATALOG NUMBER: S123DIP-B1000D805UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1512.7	1512.7	1512.7	1512.7	1512.7
2.5°	1519.2	1514.0	1499.7	1512.7	1511.4
5°	1514.0	1507.5	1493.2	1506.2	1503.6
7.5°	1502.3	1495.8	1481.5	1493.2	1491.9
10°	1486.7	1480.2	1463.3	1475.0	1472.4
12.5°	1465.9	1460.7	1445.1	1452.9	1451.6
15°	1441.2	1436.0	1419.1	1429.5	1421.7
17.5°	1413.9	1407.4	1390.5	1398.3	1395.7
20°	1382.7	1374.9	1358.0	1363.2	1359.3
22.5°	1347.6	1339.7	1322.8	1326.7	1321.5
25°	1308.5	1300.7	1283.8	1285.1	1281.2
27.5°	1268.2	1260.4	1242.2	1243.5	1239.6
30°	1224.0	1217.5	1199.3	1199.3	1190.2
32.5°	1179.8	1170.7	1157.6	1148.5	1144.6
35°	1131.6	1123.8	1106.9	1099.1	1092.6
37.5°	1083.5	1073.1	1056.2	1047.1	1043.2
40°	1032.8	1025.0	1006.8	996.4	991.2
42.5°	982.0	972.9	954.7	944.3	939.1
45°	927.4	922.2	905.3	889.7	883.2
47.5°	874.1	866.3	850.7	835.1	829.9
50°	819.5	813.0	796.0	781.7	773.9
52.5°	762.2	758.3	740.1	728.4	720.6
55°	703.7	702.4	685.5	671.2	664.7
57.5°	649.1	643.9	630.9	617.8	610.0
60°	589.2	587.9	572.3	560.6	554.1
62.5°	535.9	532.0	516.4	504.7	500.8
65°	480.0	473.5	460.5	450.1	446.1
67.5°	420.1	414.9	404.5	395.4	390.2
70°	366.8	359.0	351.2	342.1	335.6
72.5°	310.9	305.7	296.6	288.8	286.2
75°	253.6	248.4	244.5	238.0	234.1
77.5°	202.9	200.3	195.1	189.9	189.9
80°	153.5	149.6	147.0	145.7	145.7
82.5°	105.4	105.4	105.4	102.8	101.5
85°	67.6	65.0	65.0	62.4	62.4
87.5°	33.8	29.9	28.6	27.3	27.3
90°	0.7	8.1	17.6	20.6	22.0
92.5°	22.0	26.4	30.8	33.0	31.6
95°	43.3	48.5	54.3	57.3	57.3
97.5°	71.2	74.9	79.3	83.0	82.2
100°	99.9	104.3	107.9	110.1	111.6
102.5°	132.9	135.1	140.2	142.5	141.7
105°	165.2	166.7	173.3	173.3	174.8
107.5°	203.4	204.1	207.1	209.3	208.5
110°	238.6	240.1	241.6	244.5	243.0



TEST NUMBER: P1011236

CATALOG NUMBER: S123DIP-B1000D805UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	275.4	276.1	276.1	279.8	279.8
115°	312.1	314.3	312.8	313.5	312.8
117.5°	349.5	350.3	348.8	348.8	346.6
120°	384.0	388.4	384.8	384.0	382.6
122.5°	420.0	423.0	421.5	419.3	417.1
125°	456.7	458.9	457.5	454.5	451.6
127.5°	490.5	494.9	493.4	489.0	486.1
130°	524.3	530.2	528.0	525.0	519.9
132.5°	558.1	563.9	562.5	558.8	555.1
135°	592.6	597.0	596.2	593.3	591.8
137.5°	624.1	627.8	630.0	626.3	624.1
140°	657.2	660.9	661.6	660.9	655.7
142.5°	687.3	691.0	692.4	691.7	688.0
145°	718.9	720.3	722.5	721.8	718.9
147.5°	746.0	749.0	751.2	751.2	746.8
150°	774.7	776.1	777.6	777.6	773.2
152.5°	798.2	800.4	801.1	802.6	798.9
155°	823.1	823.1	823.9	826.8	821.7
157.5°	844.4	843.7	844.4	847.4	843.0
160°	864.3	862.8	862.8	866.5	863.5
162.5°	881.9	879.7	880.4	884.1	878.9
165°	896.6	894.4	894.4	898.8	893.6
167.5°	909.1	906.1	906.8	911.3	906.8
170°	919.3	916.4	916.4	921.5	916.4
172.5°	927.4	924.5	924.5	928.9	923.7
175°	932.5	929.6	929.6	934.0	928.9
177.5°	935.5	932.5	932.5	937.0	931.8
180°	934.8	934.8	934.8	934.8	934.8

(END OF REPORT)