

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011527

Luminaire Tested: S123DIP-B340D1195UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011527
REPORT IS A COMBINATION OF REPORTS P989719 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1195UB35-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5495.0 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011527

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011527

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70		51	51	51		33
1	92	88	84	81	82	78	75	73	61	59	57		44	43	42		29
2	84	77	71	66	74	69	64	59	53	50	47		39	37	35		26
3	76	67	60	55	68	60	54	50	47	43	39		34	32	29		23
4	70	59	52	46	62	53	47	42	41	37	33		31	28	25		20
5	64	53	45	39	57	47	41	36	37	32	29		27	24	22		18
6	59	47	39	34	52	42	36	31	33	28	25		25	21	19		17
7	54	42	35	29	48	38	32	27	30	25	22		22	19	17		15
8	50	38	31	26	45	35	28	24	27	22	19		20	17	15		14
9	47	35	28	23	41	31	25	21	25	20	17		19	15	13		13
10	43	32	25	20	39	29	23	19	23	18	15		17	14	12		12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5704	5704	5704
5°	5717	5506	5499
10°	5667	5321	5265
15°	5588	5127	5012
20°	5497	4911	4761
25°	5380	4684	4492
30°	5253	4449	4210
35°	5119	4209	3928
40°	4978	3957	3653
45°	4824	3712	3364
50°	4667	3438	3074
55°	4466	3153	2780
60°	4259	2839	2468
65°	4064	2498	2143
70°	3784	2120	1762
75°	3378	1680	1368
80°	2921	1180	967
85°	2276	635	485

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4824 cd/sqm

TEST NUMBER: P1011527

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	0.9
10°-20°	141.0	2.6
20°-30°	208.3	3.8
30°-40°	243.3	4.4
40°-50°	244.6	4.5
50°-60°	214.8	3.9
60°-70°	160.0	2.9
70°-80°	91.1	1.7
80°-90°	29.0	0.5
90°-100°	95.6	1.7
100°-110°	289.2	5.3
110°-120°	492.4	9.0
120°-130°	647.7	11.8
130°-140°	728.0	13.2
140°-150°	715.8	13.0
150°-160°	602.6	11.0
160°-170°	401.2	7.3
170°-180°	140.5	2.6
0°-30°	399.3	7.3
0°-40°	642.6	11.7
0°-60°	1102.0	20.1
0°-90°	1382.1	25.2
90°-120°	877.1	16.0
90°-150°	2968.6	54.0
90°-180°	4113.0	74.8
0°-180°	5495.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	530	530	530	530	530	
5°	530	528	523	528	527	50
15°	505	503	497	501	498	142
25°	458	456	450	450	449	211
35°	396	394	388	385	383	248
45°	325	323	317	312	309	251
55°	246	246	240	235	233	221
65°	168	166	161	158	156	166
75°	89	87	86	83	82	95
85°	24	23	23	22	22	25
90°	1	13	28	33	35	7
95°	69	77	86	91	91	76
105°	262	265	275	275	278	281
115°	496	499	497	498	497	490
125°	725	729	726	722	717	647
135°	941	948	947	942	940	725
145°	1142	1144	1147	1146	1142	713
155°	1307	1307	1308	1313	1305	602
165°	1424	1420	1420	1427	1419	402
175°	1481	1476	1476	1483	1475	141
180°	1484	1484	1484	1484	1484	

TEST NUMBER: P1011527

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	529.9	529.9	529.9	529.9	529.9
2.5°	532.1	530.3	525.3	529.9	529.4
5°	530.3	528.0	523.0	527.6	526.7
7.5°	526.2	523.9	518.9	523.0	522.6
10°	520.8	518.5	512.6	516.7	515.7
12.5°	513.5	511.6	506.2	508.9	508.5
15°	504.8	503.0	497.1	500.7	498.0
17.5°	495.2	493.0	487.0	489.8	488.9
20°	484.3	481.6	475.6	477.5	476.1
22.5°	472.0	469.3	463.3	464.7	462.9
25°	458.3	455.6	449.7	450.1	448.8
27.5°	444.2	441.5	435.1	435.6	434.2
30°	428.7	426.4	420.1	420.1	416.9
32.5°	413.2	410.0	405.5	402.3	400.9
35°	396.4	393.6	387.7	385.0	382.7
37.5°	379.5	375.9	369.9	366.8	365.4
40°	361.7	359.0	352.6	349.0	347.2
42.5°	344.0	340.8	334.4	330.8	328.9
45°	324.8	323.0	317.1	311.6	309.4
47.5°	306.2	303.4	298.0	292.5	290.7
50°	287.0	284.8	278.8	273.8	271.1
52.5°	267.0	265.6	259.2	255.1	252.4
55°	246.5	246.0	240.1	235.1	232.8
57.5°	227.3	225.5	221.0	216.4	213.7
60°	206.4	205.9	200.5	196.4	194.1
62.5°	187.7	186.3	180.9	176.8	175.4
65°	168.1	165.8	161.3	157.6	156.3
67.5°	147.2	145.3	141.7	138.5	136.7
70°	128.5	125.7	123.0	119.8	117.5
72.5°	108.9	107.1	103.9	101.1	100.2
75°	88.8	87.0	85.7	83.4	82.0
77.5°	71.1	70.2	68.3	66.5	66.5
80°	53.8	52.4	51.5	51.0	51.0
82.5°	36.9	36.9	36.9	36.0	35.5
85°	23.7	22.8	22.8	21.9	21.9
87.5°	11.8	10.5	10.0	9.6	9.6
90°	1.2	12.8	28.0	32.6	35.0
92.5°	35.0	42.0	49.0	52.5	50.1
95°	68.8	77.0	86.3	90.9	90.9
97.5°	113.1	118.9	125.9	131.8	130.6
100°	158.6	165.6	171.4	174.9	177.2
102.5°	211.1	214.5	222.7	226.2	225.0
105°	262.4	264.7	275.2	275.2	277.5
107.5°	323.0	324.2	328.8	332.3	331.2
110°	379.0	381.3	383.6	388.3	386.0

TEST NUMBER: P1011527

CATALOG NUMBER: S123DIP-B340D1195UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	437.3	438.4	438.4	444.3	444.3
115°	495.6	499.1	496.7	497.9	496.7
117.5°	555.0	556.2	553.9	553.9	550.4
120°	609.8	616.8	611.0	609.8	607.5
122.5°	667.0	671.6	669.3	665.8	662.3
125°	725.3	728.8	726.4	721.8	717.1
127.5°	778.9	785.9	783.6	776.6	771.9
130°	832.5	841.9	838.4	833.7	825.5
132.5°	886.2	895.5	893.2	887.3	881.5
135°	941.0	948.0	946.8	942.1	939.8
137.5°	991.1	997.0	1000.4	994.6	991.1
140°	1043.6	1049.4	1050.6	1049.4	1041.3
142.5°	1091.4	1097.2	1099.6	1098.4	1092.6
145°	1141.5	1143.9	1147.4	1146.2	1141.5
147.5°	1184.7	1189.3	1192.8	1192.8	1185.8
150°	1230.2	1232.5	1234.8	1234.8	1227.8
152.5°	1267.5	1271.0	1272.1	1274.5	1268.6
155°	1307.1	1307.1	1308.3	1312.9	1304.8
157.5°	1340.9	1339.8	1340.9	1345.6	1338.6
160°	1372.4	1370.1	1370.1	1375.9	1371.2
162.5°	1400.4	1396.9	1398.1	1403.9	1395.7
165°	1423.7	1420.2	1420.2	1427.2	1419.1
167.5°	1443.5	1438.9	1440.0	1447.0	1440.0
170°	1459.9	1455.2	1455.2	1463.4	1455.2
172.5°	1472.7	1468.0	1468.0	1475.0	1466.9
175°	1480.9	1476.2	1476.2	1483.2	1475.0
177.5°	1485.5	1480.9	1480.9	1487.8	1479.7
180°	1484.3	1484.3	1484.3	1484.3	1484.3

(END OF REPORT)