

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011545

Luminaire Tested: S123DIP-B340D1195UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011545
REPORT IS A COMBINATION OF REPORTS P989737 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1195UB50-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5261.0 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011545

CATALOG NUMBER: S123DIP-B340D1195UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011545

CATALOG NUMBER: S123DIP-B340D1195UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	29	28
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	25	24
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	23	21	20
4	70	59	52	46	62	53	47	42	41	37	33	31	28	25	20	19	17
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15
6	59	47	39	34	52	42	36	31	33	28	25	25	21	19	17	15	13
7	54	42	35	29	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	38	31	26	45	35	28	24	27	22	19	20	17	15	14	12	10
9	47	35	28	23	41	31	25	21	25	20	17	19	15	13	13	11	9
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5459	5459	5459
5°	5473	5271	5263
10°	5425	5092	5041
15°	5349	4907	4798
20°	5263	4701	4557
25°	5150	4483	4300
30°	5028	4259	4029
35°	4900	4029	3760
40°	4766	3787	3496
45°	4617	3552	3220
50°	4467	3291	2943
55°	4274	3017	2662
60°	4077	2717	2363
65°	3890	2391	2051
70°	3622	2029	1687
75°	3233	1607	1310
80°	2796	1130	925
85°	2180	607	463

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4617 cd/sqm

TEST NUMBER: P1011545

CATALOG NUMBER: S123DIP-B340D1195UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.8	0.9
10°-20°	135.0	2.6
20°-30°	199.4	3.8
30°-40°	232.9	4.4
40°-50°	234.1	4.4
50°-60°	205.7	3.9
60°-70°	153.2	2.9
70°-80°	87.2	1.7
80°-90°	27.8	0.5
90°-100°	91.5	1.7
100°-110°	276.9	5.3
110°-120°	471.4	9.0
120°-130°	620.2	11.8
130°-140°	697.1	13.3
140°-150°	685.3	13.0
150°-160°	577.0	11.0
160°-170°	384.1	7.3
170°-180°	134.5	2.6
0°-30°	382.2	7.3
0°-40°	615.1	11.7
0°-60°	1054.9	20.1
0°-90°	1323.0	25.1
90°-120°	839.8	16.0
90°-150°	2842.4	54.0
90°-180°	3938.0	74.9
0°-180°	5261.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	507	507	507	507	507	
5°	508	505	501	505	504	48
15°	483	482	476	479	477	136
25°	439	436	430	431	430	202
35°	379	377	371	368	366	237
45°	311	309	304	298	296	240
55°	236	236	230	225	223	211
65°	161	159	154	151	150	159
75°	85	83	82	80	78	91
85°	23	22	22	21	21	24
90°	1	12	27	31	34	6
95°	66	74	83	87	87	73
105°	251	253	264	264	266	269
115°	474	478	476	477	476	470
125°	694	698	696	691	687	619
135°	901	908	907	902	900	694
145°	1093	1095	1099	1098	1093	683
155°	1252	1252	1253	1257	1249	576
165°	1363	1360	1360	1366	1359	384
175°	1418	1413	1413	1420	1412	135
180°	1421	1421	1421	1421	1421	

TEST NUMBER: P1011545

CATALOG NUMBER: S123DIP-B340D1195UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	507.2	507.2	507.2	507.2	507.2
2.5°	509.4	507.6	502.8	507.2	506.8
5°	507.6	505.4	500.7	505.0	504.1
7.5°	503.7	501.5	496.7	500.7	500.2
10°	498.5	496.3	490.6	494.5	493.7
12.5°	491.5	489.7	484.5	487.1	486.7
15°	483.2	481.5	475.8	479.3	476.7
17.5°	474.0	471.9	466.2	468.8	467.9
20°	463.6	461.0	455.3	457.0	455.7
22.5°	451.8	449.2	443.5	444.8	443.1
25°	438.7	436.1	430.4	430.9	429.6
27.5°	425.2	422.6	416.5	416.9	415.6
30°	410.4	408.2	402.1	402.1	399.0
32.5°	395.5	392.5	388.1	385.1	383.8
35°	379.4	376.8	371.1	368.5	366.3
37.5°	363.3	359.8	354.1	351.1	349.8
40°	346.3	343.7	337.5	334.1	332.3
42.5°	329.3	326.2	320.1	316.6	314.9
45°	310.9	309.2	303.5	298.3	296.1
47.5°	293.1	290.4	285.2	280.0	278.2
50°	274.7	272.6	266.9	262.1	259.5
52.5°	255.6	254.3	248.1	244.2	241.6
55°	235.9	235.5	229.8	225.0	222.9
57.5°	217.6	215.9	211.5	207.2	204.5
60°	197.6	197.1	191.9	188.0	185.8
62.5°	179.7	178.4	173.1	169.2	167.9
65°	160.9	158.7	154.4	150.9	149.6
67.5°	140.9	139.1	135.6	132.6	130.8
70°	123.0	120.4	117.7	114.7	112.5
72.5°	104.2	102.5	99.4	96.8	95.9
75°	85.0	83.3	82.0	79.8	78.5
77.5°	68.0	67.2	65.4	63.7	63.7
80°	51.5	50.2	49.3	48.8	48.8
82.5°	35.3	35.3	35.3	34.5	34.0
85°	22.7	21.8	21.8	20.9	20.9
87.5°	11.3	10.0	9.6	9.2	9.2
90°	1.1	12.3	26.8	31.3	33.5
92.5°	33.5	40.2	46.9	50.2	48.0
95°	65.9	73.7	82.6	87.1	87.1
97.5°	108.3	113.9	120.6	126.2	125.0
100°	151.8	158.5	164.1	167.5	169.7
102.5°	202.1	205.4	213.2	216.6	215.5
105°	251.2	253.4	263.5	263.5	265.7
107.5°	309.3	310.4	314.8	318.2	317.1
110°	362.8	365.1	367.3	371.8	369.5

TEST NUMBER: P1011545

CATALOG NUMBER: S123DIP-B340D1195UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	418.7	419.8	419.8	425.4	425.4
115°	474.5	477.8	475.6	476.7	475.6
117.5°	531.4	532.5	530.3	530.3	527.0
120°	583.9	590.6	585.0	583.9	581.7
122.5°	638.6	643.1	640.8	637.5	634.1
125°	694.4	697.8	695.5	691.1	686.6
127.5°	745.8	752.5	750.3	743.6	739.1
130°	797.1	806.1	802.7	798.3	790.4
132.5°	848.5	857.4	855.2	849.6	844.0
135°	901.0	907.7	906.6	902.1	899.9
137.5°	949.0	954.6	957.9	952.3	949.0
140°	999.2	1004.8	1005.9	1004.8	997.0
142.5°	1045.0	1050.6	1052.8	1051.7	1046.1
145°	1093.0	1095.2	1098.6	1097.5	1093.0
147.5°	1134.3	1138.8	1142.1	1142.1	1135.4
150°	1177.9	1180.1	1182.3	1182.3	1175.6
152.5°	1213.6	1216.9	1218.0	1220.3	1214.7
155°	1251.5	1251.5	1252.7	1257.1	1249.3
157.5°	1283.9	1282.8	1283.9	1288.4	1281.7
160°	1314.1	1311.8	1311.8	1317.4	1312.9
162.5°	1340.9	1337.5	1338.6	1344.2	1336.4
165°	1363.2	1359.8	1359.8	1366.5	1358.7
167.5°	1382.2	1377.7	1378.8	1385.5	1378.8
170°	1397.8	1393.3	1393.3	1401.1	1393.3
172.5°	1410.1	1405.6	1405.6	1412.3	1404.5
175°	1417.9	1413.4	1413.4	1420.1	1412.3
177.5°	1422.4	1417.9	1417.9	1424.6	1416.8
180°	1421.2	1421.2	1421.2	1421.2	1421.2

(END OF REPORT)