

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011322

Luminaire Tested: S123DIP-B1165D1195UB50-4F0-XX-W2A-D

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011322
REPORT IS A COMBINATION OF REPORTS P989433 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D1195UB50-4F0-XX-W2A-D
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9257.0 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011322

CATALOG NUMBER: S123DIP-B1165D1195UB50-4F0-XX-W2A-D

Luminous Intensity Polar Plot



TEST NUMBER: P1011322

CATALOG NUMBER: S123DIP-B1165D1195UB50-4F0-XX-W2A-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	96	91	87	83	88	84	80	77	70	67	65	57	55	53	45	44	43
2	87	79	73	67	79	73	67	62	61	56	53	49	46	44	39	37	35
3	79	69	62	55	72	64	57	52	53	48	44	43	40	37	34	32	29
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	28	25
5	66	54	46	40	60	50	43	37	42	36	32	34	30	27	27	24	22
6	61	49	40	34	56	45	37	32	38	32	28	31	27	23	25	22	19
7	56	44	36	30	51	40	33	28	34	28	24	28	24	20	23	19	17
8	52	40	32	26	48	37	30	25	31	25	21	26	21	18	21	17	15
9	48	36	28	23	44	33	27	22	28	23	19	24	19	16	19	16	13
10	45	33	26	21	41	31	24	20	26	21	17	22	18	15	18	15	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14966	14966	14966
5°	15008	14527	14515
10°	14867	14134	14026
15°	14670	13699	13507
20°	14391	13215	12949
25°	14048	12670	12372
30°	13696	12176	11792
35°	13302	11658	11319
40°	12924	11183	10819
45°	12506	10726	10409
50°	12093	10272	9962
55°	11636	9805	9551
60°	11188	9329	9130
65°	10728	8820	8638
70°	10036	8250	8130
75°	9160	7602	7606
80°	8143	6943	7009
85°	7127	6410	6581

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12506 cd/sqm

TEST NUMBER: P1011322

CATALOG NUMBER: S123DIP-B1165D1195UB50-4F0-XX-W2A-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.9	1.4
10°-20°	376.0	4.1
20°-30°	562.3	6.1
30°-40°	671.4	7.3
40°-50°	702.4	7.6
50°-60°	659.2	7.1
60°-70°	550.6	5.9
70°-80°	393.7	4.3
80°-90°	237.3	2.6
90°-100°	200.2	2.2
100°-110°	364.4	3.9
110°-120°	700.1	7.6
120°-130°	838.2	9.1
130°-140°	869.9	9.4
140°-150°	800.0	8.6
150°-160°	642.2	6.9
160°-170°	414.4	4.5
170°-180°	142.8	1.5
0°-30°	1070.2	11.6
0°-40°	1741.6	18.8
0°-60°	3103.2	33.5
0°-90°	4284.7	46.3
90°-120°	1264.7	13.7
90°-150°	3772.8	40.8
90°-180°	4972.0	53.7
0°-180°	9257.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1390	1390	1390	1390	1390	
5°	1392	1389	1380	1392	1390	132
15°	1325	1330	1328	1344	1342	373
25°	1197	1212	1216	1236	1236	552
35°	1030	1054	1074	1097	1103	644
45°	842	878	916	945	957	649
55°	642	692	747	788	800	575
65°	444	503	570	615	630	439
75°	241	312	388	438	456	257
85°	74	150	230	282	297	76
90°	21	106	198	254	271	18
95°	85	98	185	239	254	94
105°	345	394	358	203	219	365
115°	632	656	721	769	785	624
125°	884	893	942	976	988	791
135°	1098	1103	1124	1155	1159	846
145°	1265	1272	1274	1288	1294	792
155°	1392	1390	1391	1397	1390	641
165°	1468	1465	1464	1472	1465	415
175°	1503	1497	1498	1506	1497	143
180°	1503	1503	1503	1503	1503	

TEST NUMBER: P1011322

CATALOG NUMBER: S123DIP-B1165D1195UB50-4F0-XX-W2A-D

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1390.4	1390.4	1390.4	1390.4	1390.4
2.5°	1398.0	1393.5	1381.4	1393.5	1392.0
5°	1392.0	1388.9	1379.8	1392.0	1390.4
7.5°	1381.4	1381.4	1372.3	1387.4	1385.9
10°	1366.2	1369.2	1361.7	1376.8	1373.8
12.5°	1348.0	1352.6	1348.0	1361.7	1358.6
15°	1325.3	1329.9	1328.3	1343.5	1342.0
17.5°	1298.1	1307.1	1305.6	1319.3	1316.2
20°	1267.8	1276.9	1279.9	1293.5	1295.0
22.5°	1236.0	1245.0	1249.6	1267.8	1266.2
25°	1196.6	1211.7	1216.3	1236.0	1236.0
27.5°	1158.7	1175.4	1184.5	1201.1	1202.6
30°	1117.8	1137.5	1149.6	1167.8	1167.8
32.5°	1072.4	1095.1	1111.8	1131.4	1136.0
35°	1030.0	1054.2	1073.9	1096.6	1102.7
37.5°	984.5	1011.8	1034.5	1060.3	1064.8
40°	939.1	966.3	996.6	1022.4	1028.4
42.5°	889.1	923.9	955.7	984.5	993.6
45°	842.1	878.5	916.4	945.1	957.3
47.5°	792.2	833.1	875.5	907.3	916.4
50°	743.7	786.1	833.1	867.9	878.5
52.5°	692.2	737.6	790.6	827.0	840.6
55°	642.2	692.2	746.7	787.6	799.7
57.5°	593.7	645.2	704.3	745.2	758.8
60°	542.2	596.8	658.9	701.3	717.9
62.5°	493.8	549.8	616.5	658.9	674.0
65°	443.8	502.9	569.5	614.9	630.1
67.5°	393.8	455.9	522.6	572.5	584.7
70°	340.8	405.9	478.6	527.1	542.2
72.5°	292.3	357.5	433.2	483.2	498.3
75°	240.8	312.0	387.8	437.7	455.9
77.5°	196.9	268.1	343.8	396.8	410.5
80°	150.0	224.2	302.9	354.4	369.6
82.5°	109.1	184.8	265.1	316.6	331.7
85°	74.2	150.0	230.2	281.7	296.9
87.5°	45.4	121.2	198.4	249.9	265.1
90°	20.8	106.2	198.0	254.0	271.3
92.5°	43.9	102.3	188.0	245.8	260.7
95°	84.8	98.0	184.6	239.3	254.5
97.5°	139.0	162.4	176.6	231.0	247.2
100°	202.3	273.1	168.6	221.5	237.7
102.5°	274.5	331.4	205.3	210.9	228.2
105°	344.8	393.5	358.1	202.9	218.7
107.5°	418.1	459.9	538.8	407.8	275.1
110°	491.4	527.6	600.4	603.0	455.4

TEST NUMBER: P1011322

CATALOG NUMBER: S123DIP-B1165D1195UB50-4F0-XX-W2A-D

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	562.8	591.8	661.6	709.6	720.9
115°	631.7	656.5	721.1	768.6	785.1
117.5°	700.9	720.8	777.9	823.1	836.4
120°	763.0	780.6	833.9	877.7	888.3
122.5°	827.8	838.6	889.9	928.9	940.6
125°	884.2	893.1	941.6	975.6	988.5
127.5°	942.3	949.7	993.2	1026.8	1035.2
130°	995.9	1003.3	1038.1	1071.3	1078.2
132.5°	1045.7	1054.6	1080.7	1112.5	1119.7
135°	1098.2	1103.4	1124.5	1155.1	1159.3
137.5°	1142.8	1150.3	1163.1	1193.0	1198.2
140°	1186.0	1192.7	1200.6	1227.8	1233.2
142.5°	1227.3	1232.5	1235.8	1258.9	1263.1
145°	1265.3	1271.6	1273.8	1288.1	1294.2
147.5°	1300.6	1306.2	1308.4	1315.1	1315.7
150°	1334.1	1337.4	1339.7	1341.9	1341.6
152.5°	1364.2	1365.3	1366.5	1370.9	1365.3
155°	1392.1	1389.9	1391.0	1396.6	1389.9
157.5°	1414.5	1414.5	1413.4	1420.1	1411.1
160°	1434.6	1433.4	1432.3	1439.0	1431.2
162.5°	1453.5	1450.2	1449.1	1456.9	1450.2
165°	1468.1	1464.7	1463.6	1472.5	1464.7
167.5°	1480.3	1475.9	1475.9	1484.8	1475.9
170°	1490.4	1485.9	1485.9	1494.8	1485.9
172.5°	1497.1	1491.5	1492.6	1501.5	1491.5
175°	1502.7	1497.1	1498.2	1506.0	1497.1
177.5°	1504.9	1499.3	1500.4	1509.4	1498.2
180°	1502.7	1502.7	1502.7	1502.7	1502.7

(END OF REPORT)