

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011609

Luminaire Tested: S123DIP-B340D585UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011609
REPORT IS A COMBINATION OF REPORTS P989834 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D585UB35-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3553.0 lumens
Efficiency: N/A
Efficacy: 125.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	92	88	84	87	84	80	77	68	66	64	55	53	52	42	41	40
2	87	80	74	69	79	73	68	64	60	57	53	48	46	44	37	35	34
3	80	71	64	58	72	65	58	54	53	49	45	43	40	37	33	31	29
4	73	63	55	49	66	57	51	45	47	42	39	38	35	32	30	27	25
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	19
7	57	45	37	32	52	41	35	30	35	29	26	28	24	21	22	19	17
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	18	15
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	22	18	22	18	15	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5061	5061	5061	5061
5°	5064	5831	5079	4352
10°	5032	7056	5037	3800
15°	4962	8368	5002	3421
20°	4903	9634	4913	3148
25°	4813	9878	4824	3005
30°	4750	8161	4750	2912
35°	4671	5458	4641	2829
40°	4577	3940	4521	2703
45°	4458	3121	4331	2547
50°	4171	2650	4023	2392
55°	3856	2329	3698	2220
60°	3535	2028	3347	2040
65°	3184	1736	3029	1799
70°	2818	1441	2630	1516
75°	2408	1086	2252	1171
80°	1906	726	1754	768
85°	1316	332	1047	304

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 8162 cd/sqm

TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.2	1.3
10°-20°	148.5	4.2
20°-30°	249.9	7.0
30°-40°	282.4	7.9
40°-50°	252.9	7.1
50°-60°	204.2	5.7
60°-70°	142.3	4.0
70°-80°	74.7	2.1
80°-90°	19.5	0.5
90°-100°	153.8	4.3
100°-110°	450.4	12.7
110°-120°	439.8	12.4
120°-130°	350.3	9.9
130°-140°	276.4	7.8
140°-150°	206.2	5.8
150°-160°	143.7	4.0
160°-170°	84.4	2.4
170°-180°	27.5	0.8
0°-30°	444.6	12.5
0°-40°	727.0	20.5
0°-60°	1184.1	33.3
0°-90°	1420.6	40.0
90°-120°	1044.0	29.4
90°-150°	1876.8	52.8
90°-180°	2132.0	60.0
0°-180°	3553.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	470	470	470	470	470	
5°	470	558	471	417	470	45
15°	448	831	452	340	448	127
25°	410	987	411	300	410	189
35°	362	532	359	276	362	226
45°	300	287	292	234	300	230
55°	213	195	204	186	213	191
65°	132	127	125	131	132	131
75°	63	65	59	70	63	68
85°	14	15	11	14	14	16
90°	1	17	1	17	1	2
95°	20	67	20	67	20	21
105°	67	730	67	730	67	71
115°	118	888	118	888	118	116
125°	164	700	164	700	164	145
135°	192	568	192	568	192	148
145°	219	444	219	444	219	137
155°	248	368	248	368	248	114
165°	271	321	271	321	271	77
175°	283	289	283	289	283	27
180°	284	284	284	284	284	

TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	471.5	475.2	477.0	479.7	482.5	486.6	487.9	490.2	489.3	491.1	492.0
5°	469.7	476.1	481.5	488.4	494.8	499.3	503.9	511.2	516.6	517.5	521.6
7.5°	466.5	475.6	485.2	494.8	507.1	514.3	522.5	532.6	540.8	554.0	559.0
10°	462.4	475.2	488.8	502.0	518.9	530.3	540.3	557.2	574.0	587.7	600.4
12.5°	456.0	472.0	489.7	509.3	531.2	544.4	558.1	580.4	605.9	626.9	640.5
15°	448.3	468.3	491.1	512.1	536.2	560.8	575.4	600.4	636.9	656.5	691.6
17.5°	441.9	462.4	485.2	518.0	550.8	575.4	585.9	631.9	656.9	689.7	729.4
20°	431.9	457.9	487.0	519.8	562.2	577.2	598.6	645.1	676.1	718.9	767.6
22.5°	421.4	449.2	484.3	518.4	565.8	581.8	610.9	647.8	697.0	739.4	793.2
25°	410.0	440.1	475.6	516.2	562.6	585.9	613.2	658.8	712.1	765.4	815.0
27.5°	398.6	431.4	468.3	508.9	554.0	581.3	608.6	656.0	724.4	782.2	845.5
30°	387.7	420.5	457.4	498.9	546.2	572.7	598.6	657.9	733.9	799.1	862.9
32.5°	375.8	409.6	448.3	482.9	530.7	559.0	588.1	657.9	739.9	809.1	867.4
35°	361.7	396.4	429.6	464.2	511.6	543.0	575.8	653.3	745.3	812.3	848.3
37.5°	348.1	378.6	407.3	441.0	490.7	524.4	562.2	647.8	742.6	798.6	808.6
40°	332.6	363.1	386.3	417.8	470.2	509.3	547.6	640.5	730.7	766.3	737.1
42.5°	317.5	341.7	361.7	392.3	449.2	487.5	528.9	627.3	707.5	714.8	649.2
45°	300.2	317.5	335.3	369.9	426.4	465.6	511.6	608.2	670.2	649.2	566.3
47.5°	277.9	293.4	313.0	344.9	402.3	442.8	486.6	583.6	615.9	572.2	481.5
50°	256.5	269.7	287.9	318.9	376.8	416.4	462.9	544.9	560.8	492.0	415.0
52.5°	235.1	245.1	262.9	293.8	351.7	390.0	432.3	505.2	496.1	422.3	354.0
55°	212.8	221.4	238.3	268.8	322.5	359.0	399.5	456.5	432.8	362.6	308.0
57.5°	190.9	200.0	217.3	242.8	293.4	328.9	361.3	405.9	370.4	314.3	266.1
60°	171.3	179.0	192.3	217.3	263.3	292.0	321.6	352.2	322.5	268.3	231.4
62.5°	150.8	158.1	170.4	193.2	232.8	258.3	282.0	307.1	274.3	234.6	201.8
65°	131.7	137.6	149.0	169.9	202.3	223.2	242.4	259.7	233.3	196.8	172.2
67.5°	114.3	119.4	128.9	147.6	174.9	190.0	205.5	220.0	197.7	168.6	147.6
70°	95.7	99.8	108.4	122.1	144.0	159.5	170.8	181.8	161.7	138.5	124.4
72.5°	79.3	83.4	88.8	103.0	118.0	127.6	139.9	145.8	134.4	115.3	101.1
75°	63.3	66.5	71.5	80.6	94.8	101.1	108.9	113.4	103.0	90.2	81.5
77.5°	49.7	51.0	54.7	61.0	70.6	77.9	83.8	86.6	79.3	71.1	63.8
80°	35.1	36.9	39.6	45.1	52.4	54.7	58.3	61.5	56.9	49.7	45.1
82.5°	23.2	25.5	26.9	29.2	33.7	36.4	37.4	40.1	36.0	33.3	31.4
85°	13.7	14.6	15.0	16.4	18.7	20.0	21.4	21.9	21.0	20.5	18.7
87.5°	6.8	6.8	6.8	7.7	8.2	9.1	9.6	9.6	9.6	9.1	8.7
90°	1.1	2.3	3.4	5.2	6.3	6.9	7.5	9.2	10.9	12.6	14.3
92.5°	8.6	12.6	18.4	23.5	29.3	34.4	39.6	58.0	88.4	118.2	106.7
95°	19.5	21.2	27.5	37.3	52.2	63.4	74.6	123.4	208.9	303.0	340.3
97.5°	31.0	31.6	36.7	45.3	60.3	72.6	84.9	133.1	232.4	390.8	523.4
100°	42.5	43.0	47.1	55.1	68.9	80.1	91.2	131.4	216.3	367.3	543.4
102.5°	54.5	55.7	59.1	66.6	78.6	88.6	98.7	133.7	202.6	332.8	506.1
105°	66.6	68.3	71.7	78.6	89.5	98.4	107.3	138.3	197.4	305.9	461.4
107.5°	79.2	80.9	84.4	91.2	101.6	109.9	118.2	145.8	196.3	286.4	421.8
110°	93.0	94.7	97.6	103.9	113.6	121.6	129.7	155.5	199.1	276.0	389.1

TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	105.6	107.3	110.2	116.5	126.3	134.0	141.7	165.3	204.9	270.3	367.3
115°	117.6	119.9	123.4	129.1	138.9	146.6	154.4	176.2	211.2	269.7	352.9
117.5°	129.7	132.6	135.4	140.6	151.5	158.6	165.8	187.7	219.2	270.3	343.2
120°	142.3	144.0	146.9	152.6	163.6	170.8	177.9	198.6	228.4	272.6	336.9
122.5°	153.2	154.9	157.8	164.1	174.5	182.2	189.9	210.0	237.0	276.6	332.8
125°	163.6	164.7	168.1	174.5	185.4	193.2	200.9	220.9	246.2	280.6	329.4
127.5°	171.6	173.3	177.3	183.6	195.7	203.4	211.2	230.7	253.6	285.2	327.7
130°	179.0	180.8	185.9	192.8	204.9	212.6	220.4	239.3	261.1	289.8	326.0
132.5°	184.8	187.1	192.8	201.4	213.5	221.0	228.4	246.8	268.0	293.2	325.4
135°	191.7	194.0	200.3	208.9	220.9	228.6	236.4	254.2	273.7	296.7	324.8
137.5°	198.0	200.3	206.6	215.8	227.8	235.0	242.2	259.4	278.3	299.0	323.7
140°	204.3	207.2	212.9	222.1	233.6	240.8	247.9	264.6	281.8	301.3	323.1
142.5°	211.2	213.5	219.8	227.8	239.3	245.9	252.5	268.6	285.2	303.0	321.9
145°	218.6	220.4	225.5	234.1	243.9	250.5	257.1	272.0	287.5	303.6	320.8
147.5°	226.1	227.3	232.4	239.9	249.6	255.4	261.1	274.9	289.2	303.6	319.1
150°	233.6	234.1	238.7	246.2	254.2	259.4	264.6	277.8	289.8	303.6	316.8
152.5°	241.0	241.0	245.6	251.9	258.8	263.7	268.6	279.5	290.9	301.9	313.9
155°	248.5	248.5	251.9	257.7	264.0	268.0	272.0	281.8	290.9	300.7	310.5
157.5°	254.2	254.8	257.7	262.8	268.6	271.8	274.9	282.9	291.5	299.0	307.6
160°	261.1	261.1	263.4	268.0	272.0	274.9	277.8	284.6	291.5	297.8	304.1
162.5°	266.3	266.3	268.0	271.4	274.9	277.2	279.5	285.2	290.9	295.5	300.7
165°	271.4	270.9	272.0	274.9	277.2	279.2	281.2	285.8	289.8	293.2	297.3
167.5°	275.5	274.9	275.5	277.8	279.5	280.9	282.3	285.8	289.2	290.9	293.8
170°	278.9	277.8	278.3	280.0	281.2	281.8	282.3	285.2	287.5	288.7	290.4
172.5°	281.2	280.6	280.6	281.8	282.3	282.6	282.9	285.2	286.9	286.9	287.5
175°	282.9	282.3	281.8	282.9	282.9	283.2	283.5	284.6	285.8	285.2	285.2
177.5°	284.1	283.5	282.9	283.5	283.5	283.5	283.5	284.1	285.2	284.1	283.5
180°	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5

TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	495.2	496.1	499.3	501.6	506.1	505.7	505.7	505.2	503.9	506.1	507.5
5°	529.8	537.6	538.5	548.5	549.0	553.1	555.8	553.5	559.0	558.5	554.4
7.5°	572.7	583.1	588.1	597.7	608.6	605.9	616.4	618.2	617.3	621.9	625.0
10°	619.6	637.8	650.6	668.3	672.9	675.6	682.5	688.4	700.2	691.1	697.0
12.5°	673.3	686.6	703.4	731.7	745.8	754.9	758.1	762.2	770.4	765.4	765.8
15°	718.4	736.2	764.9	800.0	804.1	815.5	812.7	837.3	849.2	831.4	841.4
17.5°	765.4	789.1	823.2	853.7	871.1	878.8	886.1	909.8	908.9	906.1	908.4
20°	795.4	834.2	876.5	917.1	922.1	928.0	947.6	957.6	955.8	963.5	968.6
22.5°	837.8	878.8	923.9	950.8	962.2	969.0	984.5	990.9	993.6	995.4	992.2
25°	873.3	917.1	950.3	974.0	980.9	984.5	989.5	991.3	990.0	986.8	989.5
27.5°	897.5	932.6	955.3	966.3	962.6	956.7	947.1	940.8	926.6	919.8	928.0
30°	907.5	923.0	929.8	911.6	893.4	878.8	860.6	826.9	800.4	808.2	797.7
32.5°	891.6	881.5	848.7	801.8	787.7	764.0	712.5	672.9	674.3	653.3	662.0
35°	844.6	799.1	737.1	666.1	647.4	634.6	578.1	569.5	551.2	531.7	537.1
37.5°	761.7	695.2	620.0	567.6	539.9	512.1	480.2	461.0	450.1	441.9	448.3
40°	660.6	579.5	517.5	470.6	446.9	429.2	407.3	388.2	375.8	374.5	376.8
42.5°	561.3	492.9	436.0	391.3	383.6	362.6	348.5	333.5	329.8	323.9	327.1
45°	475.2	419.6	372.7	336.2	327.1	321.6	304.3	294.8	290.7	287.0	292.5
47.5°	412.8	354.4	320.3	298.4	289.3	280.2	270.6	264.2	261.0	261.5	261.0
50°	352.6	309.8	279.7	262.9	257.4	251.0	243.3	239.2	237.8	233.7	236.9
52.5°	303.4	272.4	251.5	235.5	231.4	226.9	220.5	218.2	215.0	214.1	214.1
55°	263.8	239.6	222.8	212.3	207.3	203.6	200.0	197.3	195.0	195.0	195.0
57.5°	232.8	211.8	199.5	190.4	188.6	185.0	180.9	180.9	177.7	177.2	178.6
60°	206.4	187.7	178.1	170.4	167.7	166.7	162.6	162.6	161.7	159.5	161.3
62.5°	179.5	165.8	157.6	151.7	149.0	149.0	145.8	143.5	143.5	144.0	143.1
65°	154.9	144.9	137.6	133.0	131.7	129.8	129.4	127.6	126.2	126.6	126.2
67.5°	133.0	125.3	120.3	116.6	114.3	113.4	112.1	112.1	111.2	111.6	109.3
70°	113.4	105.7	101.6	97.9	97.0	97.0	95.2	95.7	94.8	96.1	95.2
72.5°	93.4	87.5	84.3	82.9	82.0	81.5	80.6	79.7	79.3	80.2	79.7
75°	75.6	70.6	68.3	67.4	66.5	66.5	66.1	65.6	65.1	65.1	65.1
77.5°	58.8	55.6	52.8	53.8	52.4	52.8	51.5	51.5	51.9	51.5	51.5
80°	43.3	41.0	41.0	40.1	38.3	39.2	39.2	37.8	37.4	38.3	36.9
82.5°	28.7	28.2	27.3	26.9	26.0	26.4	26.0	25.5	25.1	26.0	25.1
85°	16.9	16.9	16.4	15.5	16.4	15.9	15.5	15.5	15.0	15.0	15.0
87.5°	8.7	7.7	7.7	7.3	7.7	6.8	7.3	6.8	6.4	6.8	6.4
90°	13.8	14.3	14.9	15.5	16.0	16.6	16.1	16.6	17.2	16.6	17.2
92.5°	79.8	56.8	44.2	38.4	36.4	34.4	33.3	31.0	31.6	30.4	31.6
95°	276.0	206.6	140.0	109.6	99.2	88.9	78.0	72.9	68.9	66.6	68.9
97.5°	541.2	474.6	358.1	282.3	249.6	216.9	178.5	156.7	142.9	136.6	142.9
100°	656.5	676.6	630.1	563.0	522.2	481.5	423.5	381.6	359.2	359.8	359.2
102.5°	662.2	743.7	753.5	721.3	699.2	677.2	635.3	604.3	586.5	569.8	586.5
105°	626.1	746.0	803.4	814.3	806.8	799.4	773.0	751.2	732.8	730.0	732.8
107.5°	574.4	711.6	801.7	846.4	854.2	861.9	858.5	848.2	840.7	834.4	840.7
110°	526.2	657.6	763.2	835.5	855.6	875.7	891.8	896.4	895.2	894.1	895.2

TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	484.3	604.3	712.7	795.9	823.2	850.5	883.2	899.8	905.6	906.1	905.6
115°	452.2	558.4	658.2	742.6	773.8	805.1	848.2	873.4	884.9	887.8	884.9
117.5°	431.0	522.8	611.2	688.6	721.0	753.5	798.2	826.4	843.6	847.6	843.6
120°	414.9	495.8	573.3	642.2	671.2	700.1	745.4	777.6	791.4	794.8	791.4
122.5°	401.7	474.6	542.9	605.4	631.8	658.2	697.2	725.4	740.9	745.4	740.9
125°	390.8	456.2	518.8	573.9	596.8	619.8	656.5	681.8	696.1	700.1	696.1
127.5°	380.5	439.6	496.4	546.9	568.2	589.4	622.6	644.4	657.6	661.1	657.6
130°	372.4	424.1	475.7	522.2	541.7	561.2	591.7	612.3	624.4	629.0	624.4
132.5°	365.0	409.7	456.2	498.7	517.0	535.4	563.5	584.2	594.5	597.4	594.5
135°	358.7	397.1	437.9	475.2	491.6	507.9	536.0	553.2	563.5	567.6	563.5
137.5°	352.9	385.1	419.5	452.8	467.4	482.0	506.1	523.9	532.5	536.0	532.5
140°	347.8	374.7	404.0	431.5	443.8	456.2	478.0	494.1	503.3	502.7	503.3
142.5°	343.2	365.0	389.1	412.0	422.4	432.7	450.5	464.3	472.3	471.7	472.3
145°	339.2	357.5	376.5	394.8	403.2	411.5	425.8	437.9	442.4	443.6	442.4
147.5°	335.1	351.2	366.7	382.2	388.2	394.2	405.7	414.3	418.9	419.5	418.9
150°	331.1	344.3	357.5	369.6	375.0	380.5	389.1	395.4	398.8	398.8	398.8
152.5°	326.5	338.0	348.9	359.2	363.5	367.8	374.2	379.9	381.6	381.6	381.6
155°	321.9	331.7	340.9	349.5	353.0	356.4	361.5	366.1	367.3	367.8	367.3
157.5°	316.8	324.8	332.8	339.7	342.6	345.5	350.1	353.5	354.6	354.6	354.6
160°	311.6	319.1	325.4	331.1	333.1	335.1	339.2	342.6	342.6	342.0	342.6
162.5°	306.4	312.2	317.3	322.5	324.2	326.0	328.3	331.1	331.1	330.5	331.1
165°	301.9	306.4	309.9	313.9	315.4	316.8	319.1	321.4	320.8	320.8	320.8
167.5°	297.3	301.3	304.1	306.4	307.5	308.7	309.9	311.6	311.0	311.0	311.0
170°	293.2	296.1	297.8	300.1	300.7	301.3	301.9	303.0	302.4	302.4	302.4
172.5°	289.2	291.5	292.7	294.4	294.7	295.0	295.0	296.1	295.0	294.4	295.0
175°	286.4	287.5	288.1	289.2	289.2	289.2	289.2	289.8	289.2	288.7	289.2
177.5°	284.1	284.6	285.2	285.8	285.8	285.8	285.2	285.8	284.6	284.6	284.6
180°	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5

TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	503.9	505.2	501.6	500.7	500.7	502.5	501.1	488.8	491.1	488.4	487.5
5°	559.4	556.7	553.1	551.2	549.0	542.6	542.1	528.0	525.3	516.2	512.1
7.5°	620.5	618.2	607.3	605.9	605.0	599.1	584.0	569.0	558.1	547.6	537.6
10°	690.2	683.4	678.4	668.3	663.3	655.1	635.5	621.4	602.7	586.8	565.8
12.5°	774.0	766.3	749.4	742.1	735.8	713.0	693.4	677.4	641.0	630.1	604.1
15°	835.5	819.1	817.3	801.4	800.4	775.4	738.0	720.7	692.5	652.4	625.5
17.5°	902.0	887.5	876.1	856.9	854.2	830.5	803.2	760.8	729.8	691.6	657.4
20°	950.8	943.0	923.5	915.7	899.8	879.7	851.5	799.1	761.3	723.0	681.1
22.5°	989.5	981.8	966.3	955.8	946.7	920.7	887.0	842.4	790.4	740.3	697.0
25°	989.1	986.8	980.4	975.4	968.6	949.4	921.2	878.3	820.5	765.4	705.2
27.5°	933.0	939.4	950.3	955.8	954.4	951.7	935.8	899.8	847.8	782.2	714.8
30°	816.4	839.6	860.1	887.5	895.7	915.7	924.8	904.3	862.9	801.8	727.1
32.5°	677.0	710.7	755.3	770.4	796.3	835.1	878.3	886.1	860.1	813.2	734.8
35°	555.3	583.1	617.8	641.5	664.7	727.6	782.2	829.6	838.3	807.3	733.0
37.5°	459.7	479.3	509.8	529.8	551.2	605.0	681.5	743.0	786.3	787.2	728.0
40°	390.4	399.1	425.5	440.1	460.6	507.1	575.4	655.6	718.9	748.1	714.8
42.5°	330.7	342.1	364.0	374.9	388.2	428.7	473.8	549.9	628.2	690.7	690.2
45°	295.2	303.4	313.4	322.5	337.6	361.7	413.2	470.2	545.3	615.9	643.7
47.5°	263.8	271.5	281.5	284.3	294.3	317.1	348.5	398.2	468.3	538.5	590.9
50°	237.4	243.7	250.6	255.6	260.1	278.8	302.5	344.4	400.5	468.3	533.5
52.5°	216.9	221.4	227.3	230.1	234.2	247.8	266.1	297.0	343.0	405.0	468.3
55°	197.7	200.9	204.6	209.1	210.9	221.0	235.1	261.5	295.7	351.2	411.4
57.5°	180.0	181.3	183.6	186.3	188.6	197.3	209.6	227.3	257.4	300.2	357.2
60°	159.9	163.6	164.9	167.7	169.0	175.9	185.4	200.5	223.7	260.6	303.4
62.5°	143.1	145.3	147.6	149.0	152.2	154.4	162.2	175.9	195.0	222.3	261.0
65°	128.0	128.9	130.3	131.7	132.6	135.3	142.6	151.7	166.3	190.4	220.5
67.5°	110.7	111.6	113.4	113.9	114.8	118.4	122.5	130.3	142.6	160.8	185.4
70°	93.8	95.2	96.1	97.0	98.4	99.8	104.3	110.7	120.3	133.0	152.2
72.5°	79.3	80.6	80.6	81.5	81.1	82.9	87.5	92.0	98.4	108.9	125.7
75°	64.7	64.7	65.6	66.1	66.5	68.3	70.2	73.8	78.8	87.0	97.5
77.5°	51.0	50.6	51.5	51.5	51.5	52.8	54.7	56.5	59.7	65.6	73.8
80°	37.4	37.4	38.3	38.7	37.8	38.3	39.2	41.0	43.3	47.4	51.9
82.5°	24.6	26.4	26.0	26.4	26.0	26.9	27.3	27.8	28.7	30.5	33.7
85°	15.0	15.0	15.0	15.5	15.0	15.5	15.5	15.5	15.9	16.9	18.2
87.5°	6.4	6.4	6.4	6.8	6.4	6.4	6.8	6.4	6.8	6.8	7.3
90°	16.6	16.1	16.6	16.0	15.5	14.9	14.3	13.8	14.3	12.6	10.9
92.5°	31.0	33.3	34.4	36.4	38.4	44.2	56.8	79.8	106.7	118.2	88.4
95°	72.9	78.0	88.9	99.2	109.6	140.0	206.6	276.0	340.3	303.0	208.9
97.5°	156.7	178.5	216.9	249.6	282.3	358.1	474.6	541.2	523.4	390.8	232.4
100°	381.6	423.5	481.5	522.2	563.0	630.1	676.6	656.5	543.4	367.3	216.3
102.5°	604.3	635.3	677.2	699.2	721.3	753.5	743.7	662.2	506.1	332.8	202.6
105°	751.2	773.0	799.4	806.8	814.3	803.4	746.0	626.1	461.4	305.9	197.4
107.5°	848.2	858.5	861.9	854.2	846.4	801.7	711.6	574.4	421.8	286.4	196.3
110°	896.4	891.8	875.7	855.6	835.5	763.2	657.6	526.2	389.1	276.0	199.1

TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	899.8	883.2	850.5	823.2	795.9	712.7	604.3	484.3	367.3	270.3	204.9
115°	873.4	848.2	805.1	773.8	742.6	658.2	558.4	452.2	352.9	269.7	211.2
117.5°	826.4	798.2	753.5	721.0	688.6	611.2	522.8	431.0	343.2	270.3	219.2
120°	777.6	745.4	700.1	671.2	642.2	573.3	495.8	414.9	336.9	272.6	228.4
122.5°	725.4	697.2	658.2	631.8	605.4	542.9	474.6	401.7	332.8	276.6	237.0
125°	681.8	656.5	619.8	596.8	573.9	518.8	456.2	390.8	329.4	280.6	246.2
127.5°	644.4	622.6	589.4	568.2	546.9	496.4	439.6	380.5	327.7	285.2	253.6
130°	612.3	591.7	561.2	541.7	522.2	475.7	424.1	372.4	326.0	289.8	261.1
132.5°	584.2	563.5	535.4	517.0	498.7	456.2	409.7	365.0	325.4	293.2	268.0
135°	553.2	536.0	507.9	491.6	475.2	437.9	397.1	358.7	324.8	296.7	273.7
137.5°	523.9	506.1	482.0	467.4	452.8	419.5	385.1	352.9	323.7	299.0	278.3
140°	494.1	478.0	456.2	443.8	431.5	404.0	374.7	347.8	323.1	301.3	281.8
142.5°	464.3	450.5	432.7	422.4	412.0	389.1	365.0	343.2	321.9	303.0	285.2
145°	437.9	425.8	411.5	403.2	394.8	376.5	357.5	339.2	320.8	303.6	287.5
147.5°	414.3	405.7	394.2	388.2	382.2	366.7	351.2	335.1	319.1	303.6	289.2
150°	395.4	389.1	380.5	375.0	369.6	357.5	344.3	331.1	316.8	303.6	289.8
152.5°	379.9	374.2	367.8	363.5	359.2	348.9	338.0	326.5	313.9	301.9	290.9
155°	366.1	361.5	356.4	353.0	349.5	340.9	331.7	321.9	310.5	300.7	290.9
157.5°	353.5	350.1	345.5	342.6	339.7	332.8	324.8	316.8	307.6	299.0	291.5
160°	342.6	339.2	335.1	333.1	331.1	325.4	319.1	311.6	304.1	297.8	291.5
162.5°	331.1	328.3	326.0	324.2	322.5	317.3	312.2	306.4	300.7	295.5	290.9
165°	321.4	319.1	316.8	315.4	313.9	309.9	306.4	301.9	297.3	293.2	289.8
167.5°	311.6	309.9	308.7	307.5	306.4	304.1	301.3	297.3	293.8	290.9	289.2
170°	303.0	301.9	301.3	300.7	300.1	297.8	296.1	293.2	290.4	288.7	287.5
172.5°	296.1	295.0	295.0	294.7	294.4	292.7	291.5	289.2	287.5	286.9	286.9
175°	289.8	289.2	289.2	289.2	289.2	288.1	287.5	286.4	285.2	285.2	285.8
177.5°	285.8	285.2	285.8	285.8	285.8	285.2	284.6	284.1	283.5	284.1	285.2
180°	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5

TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	482.9	481.5	481.5	480.6	477.9	472.9	472.4	473.3	470.6	467.9	463.8
5°	506.6	497.9	495.2	492.5	487.0	477.9	474.3	471.1	466.1	460.1	453.8
7.5°	526.6	514.3	510.7	505.7	494.8	482.0	473.8	467.0	460.1	451.9	444.2
10°	551.7	533.9	525.3	518.0	503.0	485.2	472.9	462.9	451.9	441.9	431.9
12.5°	579.9	551.2	548.5	530.7	513.4	487.0	472.0	457.4	442.8	430.5	420.0
15°	603.6	572.2	560.8	549.0	515.7	482.9	468.3	451.9	435.1	421.9	406.4
17.5°	618.7	592.7	568.6	552.6	518.0	488.8	460.6	441.9	424.1	405.9	393.2
20°	636.9	599.1	578.1	556.7	522.5	484.3	456.0	432.8	410.9	394.5	379.0
22.5°	655.1	604.1	586.8	563.5	523.5	479.7	447.8	424.6	399.5	383.1	366.3
25°	653.3	611.4	582.7	563.1	514.3	475.6	438.3	410.9	387.7	366.7	349.9
27.5°	654.7	603.2	574.0	551.2	508.0	469.7	428.2	399.5	375.4	353.5	335.8
30°	655.1	590.9	565.4	538.0	496.1	455.6	416.9	387.7	362.2	338.5	322.5
32.5°	653.8	580.9	549.0	524.4	477.4	441.9	403.6	372.7	346.7	324.8	309.8
35°	650.6	569.0	532.1	501.1	458.3	422.3	391.3	359.4	331.7	311.6	294.3
37.5°	641.9	556.3	514.3	483.8	436.0	399.5	372.2	345.8	318.9	295.2	280.6
40°	635.5	538.9	496.6	463.3	411.8	376.3	353.5	328.5	302.0	280.6	266.5
42.5°	620.9	522.5	478.4	438.7	388.2	351.7	330.3	310.2	287.5	266.5	253.8
45°	597.3	504.8	456.0	415.9	362.2	327.6	308.0	291.6	271.5	251.5	238.7
47.5°	564.0	479.3	432.3	392.3	336.7	301.6	282.0	269.7	253.8	236.9	226.0
50°	528.0	451.5	408.2	368.6	312.1	277.9	258.8	247.4	236.9	221.4	210.9
52.5°	481.1	421.9	380.4	342.6	285.6	252.8	236.0	227.8	216.9	205.9	196.8
55°	435.5	383.6	349.4	313.4	259.7	229.2	212.8	204.1	197.7	188.6	181.3
57.5°	382.7	348.1	316.6	283.8	235.5	207.7	192.3	181.8	177.7	173.6	166.7
60°	333.9	307.5	282.0	254.7	210.5	185.4	170.4	162.2	158.1	155.4	150.8
62.5°	289.3	268.8	246.9	225.1	185.0	162.2	150.8	142.6	139.0	138.5	134.4
65°	246.5	231.9	214.1	192.7	161.3	141.2	130.3	125.3	121.2	121.2	118.0
67.5°	203.6	193.6	179.5	164.5	139.9	121.2	111.2	106.6	104.3	104.3	102.0
70°	169.5	162.6	149.9	136.7	115.3	101.1	93.4	89.3	87.9	88.4	86.6
72.5°	137.6	130.3	119.8	110.2	94.3	83.8	78.4	73.8	71.5	72.0	71.5
75°	106.6	103.0	93.8	86.6	73.8	66.5	61.5	59.2	57.4	57.9	56.9
77.5°	80.2	74.7	69.7	64.7	56.9	51.0	46.9	44.6	43.3	43.3	43.3
80°	54.7	53.8	49.7	46.9	40.5	36.0	32.8	32.3	31.0	31.0	31.0
82.5°	35.5	33.3	31.0	29.2	25.5	22.8	21.4	20.5	20.0	19.6	20.5
85°	19.6	18.2	17.3	15.5	14.1	12.8	11.4	10.9	10.5	10.9	10.5
87.5°	7.7	6.4	6.4	5.9	5.5	5.0	5.0	4.1	4.1	3.6	3.6
90°	9.2	7.5	6.9	6.3	5.2	3.4	2.3	1.1	2.3	3.4	5.2
92.5°	58.0	39.6	34.4	29.3	23.5	18.4	12.6	8.6	12.6	18.4	23.5
95°	123.4	74.6	63.4	52.2	37.3	27.5	21.2	19.5	21.2	27.5	37.3
97.5°	133.1	84.9	72.6	60.3	45.3	36.7	31.6	31.0	31.6	36.7	45.3
100°	131.4	91.2	80.1	68.9	55.1	47.1	43.0	42.5	43.0	47.1	55.1
102.5°	133.7	98.7	88.6	78.6	66.6	59.1	55.7	54.5	55.7	59.1	66.6
105°	138.3	107.3	98.4	89.5	78.6	71.7	68.3	66.6	68.3	71.7	78.6
107.5°	145.8	118.2	109.9	101.6	91.2	84.4	80.9	79.2	80.9	84.4	91.2
110°	155.5	129.7	121.6	113.6	103.9	97.6	94.7	93.0	94.7	97.6	103.9

TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	165.3	141.7	134.0	126.3	116.5	110.2	107.3	105.6	107.3	110.2	116.5
115°	176.2	154.4	146.6	138.9	129.1	123.4	119.9	117.6	119.9	123.4	129.1
117.5°	187.7	165.8	158.6	151.5	140.6	135.4	132.6	129.7	132.6	135.4	140.6
120°	198.6	177.9	170.8	163.6	152.6	146.9	144.0	142.3	144.0	146.9	152.6
122.5°	210.0	189.9	182.2	174.5	164.1	157.8	154.9	153.2	154.9	157.8	164.1
125°	220.9	200.9	193.2	185.4	174.5	168.1	164.7	163.6	164.7	168.1	174.5
127.5°	230.7	211.2	203.4	195.7	183.6	177.3	173.3	171.6	173.3	177.3	183.6
130°	239.3	220.4	212.6	204.9	192.8	185.9	180.8	179.0	180.8	185.9	192.8
132.5°	246.8	228.4	221.0	213.5	201.4	192.8	187.1	184.8	187.1	192.8	201.4
135°	254.2	236.4	228.6	220.9	208.9	200.3	194.0	191.7	194.0	200.3	208.9
137.5°	259.4	242.2	235.0	227.8	215.8	206.6	200.3	198.0	200.3	206.6	215.8
140°	264.6	247.9	240.8	233.6	222.1	212.9	207.2	204.3	207.2	212.9	222.1
142.5°	268.6	252.5	245.9	239.3	227.8	219.8	213.5	211.2	213.5	219.8	227.8
145°	272.0	257.1	250.5	243.9	234.1	225.5	220.4	218.6	220.4	225.5	234.1
147.5°	274.9	261.1	255.4	249.6	239.9	232.4	227.3	226.1	227.3	232.4	239.9
150°	277.8	264.6	259.4	254.2	246.2	238.7	234.1	233.6	234.1	238.7	246.2
152.5°	279.5	268.6	263.7	258.8	251.9	245.6	241.0	241.0	241.0	245.6	251.9
155°	281.8	272.0	268.0	264.0	257.7	251.9	248.5	248.5	248.5	251.9	257.7
157.5°	282.9	274.9	271.8	268.6	262.8	257.7	254.8	254.2	254.8	257.7	262.8
160°	284.6	277.8	274.9	272.0	268.0	263.4	261.1	261.1	261.1	263.4	268.0
162.5°	285.2	279.5	277.2	274.9	271.4	268.0	266.3	266.3	266.3	268.0	271.4
165°	285.8	281.2	279.2	277.2	274.9	272.0	270.9	271.4	270.9	272.0	274.9
167.5°	285.8	282.3	280.9	279.5	277.8	275.5	274.9	275.5	274.9	275.5	277.8
170°	285.2	282.3	281.8	281.2	280.0	278.3	277.8	278.9	277.8	278.3	280.0
172.5°	285.2	282.9	282.6	282.3	281.8	280.6	280.6	281.2	280.6	280.6	281.8
175°	284.6	283.5	283.2	282.9	282.9	281.8	282.3	282.9	282.3	281.8	282.9
177.5°	284.1	283.5	283.5	283.5	283.5	282.9	283.5	284.1	283.5	282.9	283.5
180°	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5

TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	462.9	462.4	463.3	460.6	456.0	453.8	447.4	446.0	445.6	446.0	446.5
5°	450.1	449.7	448.3	443.7	438.3	434.2	426.4	426.0	423.2	420.5	421.9
7.5°	437.8	436.0	433.3	427.3	420.0	415.5	409.1	404.6	400.9	398.6	396.8
10°	425.5	422.8	420.0	412.3	403.2	396.4	388.6	385.0	380.9	379.0	377.2
12.5°	409.6	406.8	401.8	392.7	387.2	378.6	370.8	367.2	364.9	361.3	359.0
15°	396.8	391.3	388.6	379.0	367.6	366.7	352.6	351.7	347.1	347.1	343.5
17.5°	382.2	378.1	373.1	363.5	355.3	347.1	339.9	337.1	333.0	332.1	330.3
20°	368.1	362.6	360.8	351.2	342.6	332.6	324.8	322.1	320.3	318.4	319.8
22.5°	353.5	349.0	344.4	335.8	329.4	319.4	314.8	312.1	309.3	308.4	308.9
25°	339.4	335.3	330.7	322.1	315.3	307.1	303.0	301.6	300.2	300.2	299.8
27.5°	325.7	321.6	317.5	309.8	303.0	297.0	293.8	292.5	291.1	292.0	292.9
30°	311.6	308.0	304.3	297.5	292.0	286.6	284.7	283.8	283.4	285.6	285.6
32.5°	298.9	295.7	292.9	286.6	281.1	276.5	275.2	275.6	276.1	277.4	278.4
35°	285.6	283.4	280.6	275.2	270.6	266.5	267.0	267.0	267.9	270.2	272.0
37.5°	273.8	270.6	268.3	263.8	260.1	256.5	257.9	259.2	260.1	262.9	263.8
40°	259.7	258.3	256.5	251.9	248.7	248.3	248.7	249.7	251.5	252.8	254.2
42.5°	248.3	246.5	244.2	240.5	237.8	238.3	238.7	239.6	240.5	242.8	244.2
45°	235.5	234.2	232.3	229.2	226.9	227.3	227.8	227.8	228.7	231.4	232.3
47.5°	221.4	221.9	219.6	216.4	215.0	215.0	215.0	215.9	218.2	219.1	219.6
50°	207.7	206.8	206.4	203.2	202.3	201.8	202.3	202.7	205.9	205.5	206.8
52.5°	193.2	193.2	192.7	190.9	189.5	189.5	188.6	190.9	191.8	192.7	194.1
55°	179.0	177.7	177.2	176.3	174.5	174.0	174.9	177.7	178.6	179.5	180.9
57.5°	163.6	163.6	162.6	161.3	161.3	161.3	161.3	163.1	164.5	165.4	168.1
60°	149.4	147.6	146.2	146.2	146.2	145.8	148.5	148.5	151.3	151.7	152.6
62.5°	132.6	131.7	130.8	131.2	130.8	131.7	132.6	134.4	134.9	136.2	137.6
65°	116.6	116.6	115.7	118.4	116.6	116.6	118.9	118.9	119.8	121.2	123.0
67.5°	101.1	101.6	100.7	100.7	101.6	102.0	102.5	104.3	104.8	106.6	108.9
70°	85.2	86.1	86.6	85.6	86.6	87.5	88.4	88.8	90.7	91.6	92.9
72.5°	71.1	72.0	70.6	71.1	71.5	72.4	72.9	73.8	74.7	77.4	78.4
75°	56.9	56.5	56.0	57.9	56.9	58.8	59.2	59.2	60.1	62.4	63.3
77.5°	43.7	43.7	44.2	43.3	44.6	44.2	44.6	46.0	47.4	47.4	51.0
80°	30.5	31.4	31.4	31.4	31.9	32.3	31.4	33.7	34.2	34.2	35.5
82.5°	19.6	20.0	19.6	20.5	20.5	21.4	21.0	21.4	22.3	23.2	23.7
85°	10.5	10.5	11.4	11.4	10.9	11.4	10.9	11.4	12.3	12.3	12.8
87.5°	3.6	3.6	3.6	3.6	4.1	3.6	4.1	4.1	3.6	3.6	5.0
90°	6.3	6.9	7.5	9.2	10.9	12.6	14.3	13.8	14.3	14.9	15.5
92.5°	29.3	34.4	39.6	58.0	88.4	118.2	106.7	79.8	56.8	44.2	38.4
95°	52.2	63.4	74.6	123.4	208.9	303.0	340.3	276.0	206.6	140.0	109.6
97.5°	60.3	72.6	84.9	133.1	232.4	390.8	523.4	541.2	474.6	358.1	282.3
100°	68.9	80.1	91.2	131.4	216.3	367.3	543.4	656.5	676.6	630.1	563.0
102.5°	78.6	88.6	98.7	133.7	202.6	332.8	506.1	662.2	743.7	753.5	721.3
105°	89.5	98.4	107.3	138.3	197.4	305.9	461.4	626.1	746.0	803.4	814.3
107.5°	101.6	109.9	118.2	145.8	196.3	286.4	421.8	574.4	711.6	801.7	846.4
110°	113.6	121.6	129.7	155.5	199.1	276.0	389.1	526.2	657.6	763.2	835.5

TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	126.3	134.0	141.7	165.3	204.9	270.3	367.3	484.3	604.3	712.7	795.9
115°	138.9	146.6	154.4	176.2	211.2	269.7	352.9	452.2	558.4	658.2	742.6
117.5°	151.5	158.6	165.8	187.7	219.2	270.3	343.2	431.0	522.8	611.2	688.6
120°	163.6	170.8	177.9	198.6	228.4	272.6	336.9	414.9	495.8	573.3	642.2
122.5°	174.5	182.2	189.9	210.0	237.0	276.6	332.8	401.7	474.6	542.9	605.4
125°	185.4	193.2	200.9	220.9	246.2	280.6	329.4	390.8	456.2	518.8	573.9
127.5°	195.7	203.4	211.2	230.7	253.6	285.2	327.7	380.5	439.6	496.4	546.9
130°	204.9	212.6	220.4	239.3	261.1	289.8	326.0	372.4	424.1	475.7	522.2
132.5°	213.5	221.0	228.4	246.8	268.0	293.2	325.4	365.0	409.7	456.2	498.7
135°	220.9	228.6	236.4	254.2	273.7	296.7	324.8	358.7	397.1	437.9	475.2
137.5°	227.8	235.0	242.2	259.4	278.3	299.0	323.7	352.9	385.1	419.5	452.8
140°	233.6	240.8	247.9	264.6	281.8	301.3	323.1	347.8	374.7	404.0	431.5
142.5°	239.3	245.9	252.5	268.6	285.2	303.0	321.9	343.2	365.0	389.1	412.0
145°	243.9	250.5	257.1	272.0	287.5	303.6	320.8	339.2	357.5	376.5	394.8
147.5°	249.6	255.4	261.1	274.9	289.2	303.6	319.1	335.1	351.2	366.7	382.2
150°	254.2	259.4	264.6	277.8	289.8	303.6	316.8	331.1	344.3	357.5	369.6
152.5°	258.8	263.7	268.6	279.5	290.9	301.9	313.9	326.5	338.0	348.9	359.2
155°	264.0	268.0	272.0	281.8	290.9	300.7	310.5	321.9	331.7	340.9	349.5
157.5°	268.6	271.8	274.9	282.9	291.5	299.0	307.6	316.8	324.8	332.8	339.7
160°	272.0	274.9	277.8	284.6	291.5	297.8	304.1	311.6	319.1	325.4	331.1
162.5°	274.9	277.2	279.5	285.2	290.9	295.5	300.7	306.4	312.2	317.3	322.5
165°	277.2	279.2	281.2	285.8	289.8	293.2	297.3	301.9	306.4	309.9	313.9
167.5°	279.5	280.9	282.3	285.8	289.2	290.9	293.8	297.3	301.3	304.1	306.4
170°	281.2	281.8	282.3	285.2	287.5	288.7	290.4	293.2	296.1	297.8	300.1
172.5°	282.3	282.6	282.9	285.2	286.9	286.9	287.5	289.2	291.5	292.7	294.4
175°	282.9	283.2	283.5	284.6	285.8	285.2	285.2	286.4	287.5	288.1	289.2
177.5°	283.5	283.5	283.5	284.1	285.2	284.1	283.5	284.1	284.6	285.2	285.8
180°	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5

TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	446.0	446.5	444.6	443.3	446.9	444.6	444.6	445.1	444.2	445.6	445.1
5°	421.0	421.4	418.2	419.1	417.3	416.9	416.4	419.1	418.7	418.2	419.1
7.5°	396.4	396.4	395.0	394.1	394.1	392.7	394.5	394.1	395.0	395.0	396.4
10°	375.8	376.8	374.5	372.2	371.7	372.2	372.2	372.7	373.1	376.3	375.8
12.5°	359.0	357.6	357.2	355.8	353.5	352.6	351.7	356.7	355.3	355.3	355.3
15°	340.3	343.5	343.0	338.9	338.0	339.9	338.9	338.9	343.5	343.0	342.6
17.5°	330.3	329.4	328.5	326.2	326.6	326.2	326.6	326.6	329.4	329.4	329.4
20°	318.9	317.1	317.1	316.2	316.2	314.8	316.6	317.1	318.9	318.9	319.4
22.5°	308.9	307.5	307.5	307.1	308.0	306.1	308.0	308.4	308.4	309.8	309.8
25°	300.2	299.3	299.3	300.2	300.2	300.2	300.2	302.0	300.7	301.1	300.7
27.5°	292.5	292.9	293.4	293.8	293.4	293.8	294.3	295.2	295.7	295.2	294.3
30°	285.2	286.6	287.0	287.0	287.9	288.4	288.8	288.8	289.3	287.9	288.8
32.5°	279.7	279.7	280.6	281.1	282.0	282.5	282.5	283.4	282.9	281.5	282.0
35°	272.0	272.0	273.8	274.7	276.1	275.6	276.1	276.1	276.5	275.6	274.3
37.5°	264.2	265.1	265.1	267.0	267.4	267.9	267.4	268.3	267.9	267.0	266.5
40°	255.1	254.7	255.1	256.5	256.9	256.9	256.9	257.9	257.9	257.9	257.4
42.5°	243.7	245.1	244.6	246.0	245.6	245.6	246.5	247.4	247.8	246.5	246.9
45°	232.8	232.8	233.7	233.7	234.2	234.2	236.0	235.1	236.0	235.1	235.5
47.5°	221.0	221.4	221.4	221.9	222.8	223.7	222.8	223.2	223.2	223.7	222.8
50°	207.7	207.7	208.7	210.0	211.8	210.9	210.5	212.3	210.9	210.9	210.0
52.5°	194.1	195.4	195.9	197.3	198.6	199.1	199.5	198.6	199.1	197.7	198.2
55°	180.9	181.3	183.1	184.5	185.9	185.9	185.4	185.9	186.3	184.5	184.5
57.5°	167.7	169.0	170.8	170.8	172.7	172.7	172.2	172.2	172.7	171.3	170.8
60°	153.5	154.9	157.2	157.2	159.9	160.4	159.5	158.5	158.5	157.2	157.6
62.5°	138.5	139.9	141.2	143.5	145.3	144.4	146.2	144.4	144.9	142.1	142.1
65°	125.3	125.7	128.0	130.3	130.3	131.2	130.3	130.8	129.4	129.4	127.6
67.5°	109.8	109.8	112.1	114.3	116.6	116.6	116.6	115.3	115.3	113.9	113.9
70°	96.1	95.7	97.9	99.3	100.7	101.1	100.2	99.8	98.9	97.5	97.0
72.5°	79.3	80.2	82.5	83.4	85.6	85.2	87.5	84.7	84.7	82.5	82.0
75°	64.2	65.1	67.4	68.8	70.2	70.2	71.5	70.2	68.3	67.4	67.0
77.5°	51.0	50.6	52.4	54.7	55.1	54.7	55.6	55.1	53.3	53.3	52.4
80°	36.4	37.8	39.6	39.2	41.0	40.5	40.5	39.6	39.6	38.3	39.2
82.5°	24.1	25.5	26.0	25.5	26.0	26.9	27.3	26.9	26.9	26.0	26.4
85°	12.8	12.8	13.7	14.1	13.7	13.7	14.1	15.5	14.6	13.7	14.6
87.5°	4.1	3.6	3.6	4.1	3.6	3.6	4.1	4.1	4.6	4.6	4.6
90°	16.0	16.6	16.1	16.6	17.2	16.6	17.2	16.6	16.1	16.6	16.0
92.5°	36.4	34.4	33.3	31.0	31.6	30.4	31.6	31.0	33.3	34.4	36.4
95°	99.2	88.9	78.0	72.9	68.9	66.6	68.9	72.9	78.0	88.9	99.2
97.5°	249.6	216.9	178.5	156.7	142.9	136.6	142.9	156.7	178.5	216.9	249.6
100°	522.2	481.5	423.5	381.6	359.2	359.8	359.2	381.6	423.5	481.5	522.2
102.5°	699.2	677.2	635.3	604.3	586.5	569.8	586.5	604.3	635.3	677.2	699.2
105°	806.8	799.4	773.0	751.2	732.8	730.0	732.8	751.2	773.0	799.4	806.8
107.5°	854.2	861.9	858.5	848.2	840.7	834.4	840.7	848.2	858.5	861.9	854.2
110°	855.6	875.7	891.8	896.4	895.2	894.1	895.2	896.4	891.8	875.7	855.6

TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	823.2	850.5	883.2	899.8	905.6	906.1	905.6	899.8	883.2	850.5	823.2
115°	773.8	805.1	848.2	873.4	884.9	887.8	884.9	873.4	848.2	805.1	773.8
117.5°	721.0	753.5	798.2	826.4	843.6	847.6	843.6	826.4	798.2	753.5	721.0
120°	671.2	700.1	745.4	777.6	791.4	794.8	791.4	777.6	745.4	700.1	671.2
122.5°	631.8	658.2	697.2	725.4	740.9	745.4	740.9	725.4	697.2	658.2	631.8
125°	596.8	619.8	656.5	681.8	696.1	700.1	696.1	681.8	656.5	619.8	596.8
127.5°	568.2	589.4	622.6	644.4	657.6	661.1	657.6	644.4	622.6	589.4	568.2
130°	541.7	561.2	591.7	612.3	624.4	629.0	624.4	612.3	591.7	561.2	541.7
132.5°	517.0	535.4	563.5	584.2	594.5	597.4	594.5	584.2	563.5	535.4	517.0
135°	491.6	507.9	536.0	553.2	563.5	567.6	563.5	553.2	536.0	507.9	491.6
137.5°	467.4	482.0	506.1	523.9	532.5	536.0	532.5	523.9	506.1	482.0	467.4
140°	443.8	456.2	478.0	494.1	503.3	502.7	503.3	494.1	478.0	456.2	443.8
142.5°	422.4	432.7	450.5	464.3	472.3	471.7	472.3	464.3	450.5	432.7	422.4
145°	403.2	411.5	425.8	437.9	442.4	443.6	442.4	437.9	425.8	411.5	403.2
147.5°	388.2	394.2	405.7	414.3	418.9	419.5	418.9	414.3	405.7	394.2	388.2
150°	375.0	380.5	389.1	395.4	398.8	398.8	398.8	395.4	389.1	380.5	375.0
152.5°	363.5	367.8	374.2	379.9	381.6	381.6	381.6	379.9	374.2	367.8	363.5
155°	353.0	356.4	361.5	366.1	367.3	367.8	367.3	366.1	361.5	356.4	353.0
157.5°	342.6	345.5	350.1	353.5	354.6	354.6	354.6	353.5	350.1	345.5	342.6
160°	333.1	335.1	339.2	342.6	342.6	342.0	342.6	342.6	339.2	335.1	333.1
162.5°	324.2	326.0	328.3	331.1	331.1	330.5	331.1	331.1	328.3	326.0	324.2
165°	315.4	316.8	319.1	321.4	320.8	320.8	320.8	321.4	319.1	316.8	315.4
167.5°	307.5	308.7	309.9	311.6	311.0	311.0	311.0	311.6	309.9	308.7	307.5
170°	300.7	301.3	301.9	303.0	302.4	302.4	302.4	303.0	301.9	301.3	300.7
172.5°	294.7	295.0	295.0	296.1	295.0	294.4	295.0	296.1	295.0	295.0	294.7
175°	289.2	289.2	289.2	289.8	289.2	288.7	289.2	289.8	289.2	289.2	289.2
177.5°	285.8	285.8	285.2	285.8	284.6	284.6	284.6	285.8	285.2	285.8	285.8
180°	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5

TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	446.5	447.4	447.8	446.0	444.6	446.9	450.1	452.4	454.2	456.5	457.9
5°	420.0	423.2	423.2	424.1	425.5	427.8	433.7	437.8	441.5	444.2	446.5
7.5°	397.7	400.0	401.4	403.6	405.9	409.1	415.9	421.9	427.3	430.5	434.2
10°	377.7	379.5	381.8	383.1	387.2	391.8	400.5	405.5	411.8	416.9	421.4
12.5°	358.5	364.9	366.3	365.8	369.5	374.5	383.1	390.9	397.7	402.7	407.7
15°	344.9	347.1	349.9	349.4	357.2	358.5	365.8	374.9	384.1	387.2	391.8
17.5°	329.8	333.5	336.2	337.6	339.9	344.9	351.7	358.5	370.4	370.8	382.7
20°	318.0	321.6	323.5	325.3	326.6	332.6	338.5	346.2	355.8	360.8	367.2
22.5°	310.2	312.1	313.4	314.8	316.6	319.8	327.1	335.8	342.1	347.6	351.7
25°	301.1	303.0	304.8	305.7	307.1	308.9	314.3	321.2	330.3	333.9	338.0
27.5°	294.8	294.8	295.7	295.7	297.5	299.3	303.4	309.8	317.1	321.6	327.1
30°	287.9	287.5	287.9	287.5	287.0	289.7	293.4	298.9	303.9	309.3	313.0
32.5°	281.1	280.6	280.6	281.1	279.3	280.6	282.5	287.5	292.9	295.7	299.8
35°	273.8	272.9	272.9	272.9	272.0	271.1	272.9	277.4	281.1	284.7	287.9
37.5°	266.5	265.1	265.1	264.2	263.3	262.0	262.0	265.6	270.6	272.0	276.1
40°	256.5	256.5	255.6	255.1	254.2	253.3	251.9	255.1	259.7	261.0	264.2
42.5°	246.5	245.1	244.6	244.6	244.6	243.3	242.4	244.6	247.4	249.7	251.5
45°	235.1	234.2	234.6	234.2	233.3	232.8	232.3	233.3	236.4	237.4	239.6
47.5°	222.8	222.3	222.3	221.9	221.4	221.9	220.0	222.3	223.2	224.1	226.0
50°	210.0	209.6	209.1	208.7	208.7	209.1	208.7	208.7	210.5	211.4	213.2
52.5°	197.3	195.9	195.9	195.4	195.4	194.5	195.4	195.9	196.8	197.7	198.6
55°	183.6	183.6	182.2	182.2	181.3	181.3	181.8	181.3	183.1	184.1	184.1
57.5°	170.4	168.6	169.0	168.1	167.2	166.7	166.7	167.7	168.6	168.6	169.5
60°	156.3	154.4	154.0	152.2	153.1	151.7	152.2	152.2	154.0	153.1	154.0
62.5°	142.1	139.9	138.5	137.6	137.6	138.0	137.1	136.7	137.6	138.5	140.3
65°	127.1	125.7	124.4	123.0	123.0	122.5	123.5	122.1	121.6	122.1	123.0
67.5°	111.6	110.2	108.9	107.5	108.0	106.6	105.7	107.1	106.1	106.6	107.5
70°	96.6	95.7	92.9	92.0	91.6	92.0	91.6	90.7	92.0	91.6	92.0
72.5°	81.5	80.6	79.3	77.0	77.0	76.5	76.1	76.1	75.6	75.6	75.6
75°	67.0	65.1	63.8	63.3	62.4	62.0	61.5	60.6	61.0	61.5	60.6
77.5°	51.9	49.7	49.2	49.2	47.8	47.8	48.3	47.8	47.4	47.4	47.4
80°	38.3	36.4	36.4	35.5	34.6	34.6	34.6	34.6	34.2	33.7	34.2
82.5°	24.6	24.1	23.7	23.7	24.6	22.8	23.7	23.2	22.8	22.8	22.3
85°	13.7	14.1	13.7	14.1	13.2	13.7	13.7	13.7	13.2	13.7	12.8
87.5°	5.0	5.0	5.0	5.5	5.5	5.5	5.5	5.5	5.9	5.5	5.5
90°	15.5	14.9	14.3	13.8	14.3	12.6	10.9	9.2	7.5	6.9	6.3
92.5°	38.4	44.2	56.8	79.8	106.7	118.2	88.4	58.0	39.6	34.4	29.3
95°	109.6	140.0	206.6	276.0	340.3	303.0	208.9	123.4	74.6	63.4	52.2
97.5°	282.3	358.1	474.6	541.2	523.4	390.8	232.4	133.1	84.9	72.6	60.3
100°	563.0	630.1	676.6	656.5	543.4	367.3	216.3	131.4	91.2	80.1	68.9
102.5°	721.3	753.5	743.7	662.2	506.1	332.8	202.6	133.7	98.7	88.6	78.6
105°	814.3	803.4	746.0	626.1	461.4	305.9	197.4	138.3	107.3	98.4	89.5
107.5°	846.4	801.7	711.6	574.4	421.8	286.4	196.3	145.8	118.2	109.9	101.6
110°	835.5	763.2	657.6	526.2	389.1	276.0	199.1	155.5	129.7	121.6	113.6

TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	795.9	712.7	604.3	484.3	367.3	270.3	204.9	165.3	141.7	134.0	126.3
115°	742.6	658.2	558.4	452.2	352.9	269.7	211.2	176.2	154.4	146.6	138.9
117.5°	688.6	611.2	522.8	431.0	343.2	270.3	219.2	187.7	165.8	158.6	151.5
120°	642.2	573.3	495.8	414.9	336.9	272.6	228.4	198.6	177.9	170.8	163.6
122.5°	605.4	542.9	474.6	401.7	332.8	276.6	237.0	210.0	189.9	182.2	174.5
125°	573.9	518.8	456.2	390.8	329.4	280.6	246.2	220.9	200.9	193.2	185.4
127.5°	546.9	496.4	439.6	380.5	327.7	285.2	253.6	230.7	211.2	203.4	195.7
130°	522.2	475.7	424.1	372.4	326.0	289.8	261.1	239.3	220.4	212.6	204.9
132.5°	498.7	456.2	409.7	365.0	325.4	293.2	268.0	246.8	228.4	221.0	213.5
135°	475.2	437.9	397.1	358.7	324.8	296.7	273.7	254.2	236.4	228.6	220.9
137.5°	452.8	419.5	385.1	352.9	323.7	299.0	278.3	259.4	242.2	235.0	227.8
140°	431.5	404.0	374.7	347.8	323.1	301.3	281.8	264.6	247.9	240.8	233.6
142.5°	412.0	389.1	365.0	343.2	321.9	303.0	285.2	268.6	252.5	245.9	239.3
145°	394.8	376.5	357.5	339.2	320.8	303.6	287.5	272.0	257.1	250.5	243.9
147.5°	382.2	366.7	351.2	335.1	319.1	303.6	289.2	274.9	261.1	255.4	249.6
150°	369.6	357.5	344.3	331.1	316.8	303.6	289.8	277.8	264.6	259.4	254.2
152.5°	359.2	348.9	338.0	326.5	313.9	301.9	290.9	279.5	268.6	263.7	258.8
155°	349.5	340.9	331.7	321.9	310.5	300.7	290.9	281.8	272.0	268.0	264.0
157.5°	339.7	332.8	324.8	316.8	307.6	299.0	291.5	282.9	274.9	271.8	268.6
160°	331.1	325.4	319.1	311.6	304.1	297.8	291.5	284.6	277.8	274.9	272.0
162.5°	322.5	317.3	312.2	306.4	300.7	295.5	290.9	285.2	279.5	277.2	274.9
165°	313.9	309.9	306.4	301.9	297.3	293.2	289.8	285.8	281.2	279.2	277.2
167.5°	306.4	304.1	301.3	297.3	293.8	290.9	289.2	285.8	282.3	280.9	279.5
170°	300.1	297.8	296.1	293.2	290.4	288.7	287.5	285.2	282.3	281.8	281.2
172.5°	294.4	292.7	291.5	289.2	287.5	286.9	286.9	285.2	282.9	282.6	282.3
175°	289.2	288.1	287.5	286.4	285.2	285.2	285.8	284.6	283.5	283.2	282.9
177.5°	285.8	285.2	284.6	284.1	283.5	284.1	285.2	284.1	283.5	283.5	283.5
180°	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5	283.5

TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	470.2	470.2	470.2	470.2
2.5°	460.1	461.5	466.1	471.5
5°	451.0	454.7	461.0	469.7
7.5°	441.0	446.5	455.6	466.5
10°	429.6	437.4	448.7	462.4
12.5°	417.3	427.3	441.9	456.0
15°	409.6	419.6	432.8	448.3
17.5°	394.5	406.4	420.0	441.9
20°	379.0	392.3	410.0	431.9
22.5°	367.2	381.3	398.2	421.4
25°	353.1	367.6	385.9	410.0
27.5°	338.0	352.6	373.1	398.6
30°	326.6	340.8	360.4	387.7
32.5°	313.0	326.6	347.1	375.8
35°	297.5	313.0	332.6	361.7
37.5°	285.6	299.8	320.3	348.1
40°	272.9	285.2	305.2	332.6
42.5°	259.2	272.9	290.2	317.5
45°	246.5	256.5	274.3	300.2
47.5°	232.8	244.2	257.9	277.9
50°	218.2	227.8	242.8	256.5
52.5°	204.1	211.8	224.6	235.1
55°	189.1	196.8	206.4	212.8
57.5°	174.9	180.4	186.8	190.9
60°	157.6	163.1	167.2	171.3
62.5°	142.1	146.2	148.5	150.8
65°	126.2	128.5	129.8	131.7
67.5°	108.9	111.2	111.6	114.3
70°	92.9	93.4	94.3	95.7
72.5°	77.9	78.8	78.4	79.3
75°	62.4	63.3	62.4	63.3
77.5°	47.4	48.3	48.3	49.7
80°	34.2	34.6	35.1	35.1
82.5°	22.3	23.7	22.8	23.2
85°	12.8	13.2	13.2	13.7
87.5°	5.9	6.4	5.9	6.8
90°	5.2	3.4	2.3	1.1
92.5°	23.5	18.4	12.6	8.6
95°	37.3	27.5	21.2	19.5
97.5°	45.3	36.7	31.6	31.0
100°	55.1	47.1	43.0	42.5
102.5°	66.6	59.1	55.7	54.5
105°	78.6	71.7	68.3	66.6
107.5°	91.2	84.4	80.9	79.2
110°	103.9	97.6	94.7	93.0

TEST NUMBER: P1011609

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	116.5	110.2	107.3	105.6
115°	129.1	123.4	119.9	117.6
117.5°	140.6	135.4	132.6	129.7
120°	152.6	146.9	144.0	142.3
122.5°	164.1	157.8	154.9	153.2
125°	174.5	168.1	164.7	163.6
127.5°	183.6	177.3	173.3	171.6
130°	192.8	185.9	180.8	179.0
132.5°	201.4	192.8	187.1	184.8
135°	208.9	200.3	194.0	191.7
137.5°	215.8	206.6	200.3	198.0
140°	222.1	212.9	207.2	204.3
142.5°	227.8	219.8	213.5	211.2
145°	234.1	225.5	220.4	218.6
147.5°	239.9	232.4	227.3	226.1
150°	246.2	238.7	234.1	233.6
152.5°	251.9	245.6	241.0	241.0
155°	257.7	251.9	248.5	248.5
157.5°	262.8	257.7	254.8	254.2
160°	268.0	263.4	261.1	261.1
162.5°	271.4	268.0	266.3	266.3
165°	274.9	272.0	270.9	271.4
167.5°	277.8	275.5	274.9	275.5
170°	280.0	278.3	277.8	278.9
172.5°	281.8	280.6	280.6	281.2
175°	282.9	281.8	282.3	282.9
177.5°	283.5	282.9	283.5	284.1
180°	283.5	283.5	283.5	283.5

(END OF REPORT)