

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011614

Luminaire Tested: S123DIP-B340D585UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011614
REPORT IS A COMBINATION OF REPORTS P989839 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D585UB35-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3405.0 lumens
Efficiency: N/A
Efficacy: 119.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011614

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011614

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47
1	96	91	87	84	87	83	80	77	68	66	64	55	53	52	42	41	40
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	34
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	33	30	29
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25
5	67	55	47	41	60	50	43	38	42	37	32	34	30	27	26	24	21
6	61	49	41	36	56	45	38	33	38	32	28	30	26	23	24	21	19
7	57	44	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	16	13
10	46	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5704	5704	5704
5°	5717	5506	5499
10°	5667	5321	5265
15°	5588	5127	5012
20°	5497	4911	4761
25°	5380	4684	4492
30°	5253	4449	4210
35°	5119	4209	3928
40°	4978	3957	3653
45°	4824	3712	3364
50°	4667	3438	3074
55°	4466	3153	2780
60°	4259	2839	2468
65°	4064	2498	2143
70°	3784	2120	1762
75°	3378	1680	1368
80°	2921	1180	967
85°	2276	635	485

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4824 cd/sqm

TEST NUMBER: P1011614

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	1.5
10°-20°	141.0	4.1
20°-30°	208.3	6.1
30°-40°	243.3	7.1
40°-50°	244.6	7.2
50°-60°	214.8	6.3
60°-70°	160.0	4.7
70°-80°	91.1	2.7
80°-90°	27.4	0.8
90°-100°	47.0	1.4
100°-110°	142.4	4.2
110°-120°	242.3	7.1
120°-130°	318.8	9.4
130°-140°	358.4	10.5
140°-150°	352.3	10.3
150°-160°	296.6	8.7
160°-170°	197.5	5.8
170°-180°	69.1	2.0
0°-30°	399.3	11.7
0°-40°	642.6	18.9
0°-60°	1102.0	32.4
0°-90°	1380.5	40.5
90°-120°	431.8	12.7
90°-150°	1461.2	42.9
90°-180°	2024.0	59.4
0°-180°	3405.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	530	530	530	530	530	
5°	530	528	523	528	527	50
15°	505	503	497	501	498	142
25°	458	456	450	450	449	211
35°	396	394	388	385	383	248
45°	325	323	317	312	309	251
55°	246	246	240	235	233	221
65°	168	166	161	158	156	166
75°	89	87	86	83	82	95
85°	24	23	23	22	22	25
90°	1	6	14	16	17	4
95°	34	38	42	45	45	37
105°	129	130	136	136	137	138
115°	244	246	244	245	244	241
125°	357	359	358	355	353	318
135°	463	467	466	464	463	357
145°	562	563	565	564	562	351
155°	643	643	644	646	642	296
165°	701	699	699	702	698	198
175°	729	727	727	730	726	69
180°	731	731	731	731	731	

TEST NUMBER: P1011614

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	529.9	529.9	529.9	529.9	529.9
2.5°	532.1	530.3	525.3	529.9	529.4
5°	530.3	528.0	523.0	527.6	526.7
7.5°	526.2	523.9	518.9	523.0	522.6
10°	520.8	518.5	512.6	516.7	515.7
12.5°	513.5	511.6	506.2	508.9	508.5
15°	504.8	503.0	497.1	500.7	498.0
17.5°	495.2	493.0	487.0	489.8	488.9
20°	484.3	481.6	475.6	477.5	476.1
22.5°	472.0	469.3	463.3	464.7	462.9
25°	458.3	455.6	449.7	450.1	448.8
27.5°	444.2	441.5	435.1	435.6	434.2
30°	428.7	426.4	420.1	420.1	416.9
32.5°	413.2	410.0	405.5	402.3	400.9
35°	396.4	393.6	387.7	385.0	382.7
37.5°	379.5	375.9	369.9	366.8	365.4
40°	361.7	359.0	352.6	349.0	347.2
42.5°	344.0	340.8	334.4	330.8	328.9
45°	324.8	323.0	317.1	311.6	309.4
47.5°	306.2	303.4	298.0	292.5	290.7
50°	287.0	284.8	278.8	273.8	271.1
52.5°	267.0	265.6	259.2	255.1	252.4
55°	246.5	246.0	240.1	235.1	232.8
57.5°	227.3	225.5	221.0	216.4	213.7
60°	206.4	205.9	200.5	196.4	194.1
62.5°	187.7	186.3	180.9	176.8	175.4
65°	168.1	165.8	161.3	157.6	156.3
67.5°	147.2	145.3	141.7	138.5	136.7
70°	128.5	125.7	123.0	119.8	117.5
72.5°	108.9	107.1	103.9	101.1	100.2
75°	88.8	87.0	85.7	83.4	82.0
77.5°	71.1	70.2	68.3	66.5	66.5
80°	53.8	52.4	51.5	51.0	51.0
82.5°	36.9	36.9	36.9	36.0	35.5
85°	23.7	22.8	22.8	21.9	21.9
87.5°	11.8	10.5	10.0	9.6	9.6
90°	0.6	6.3	13.8	16.1	17.2
92.5°	17.2	20.7	24.1	25.8	24.7
95°	33.9	37.9	42.5	44.8	44.8
97.5°	55.7	58.5	62.0	64.9	64.3
100°	78.1	81.5	84.4	86.1	87.2
102.5°	103.9	105.6	109.6	111.3	110.8
105°	129.1	130.3	135.5	135.5	136.6
107.5°	159.0	159.6	161.9	163.6	163.0
110°	186.5	187.7	188.8	191.1	190.0

TEST NUMBER: P1011614

CATALOG NUMBER: S123DIP-B340D585UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	215.2	215.8	215.8	218.7	218.7
115°	243.9	245.6	244.5	245.1	244.5
117.5°	273.2	273.8	272.6	272.6	270.9
120°	300.2	303.6	300.7	300.2	299.0
122.5°	328.3	330.6	329.4	327.7	326.0
125°	357.0	358.7	357.6	355.3	353.0
127.5°	383.4	386.8	385.7	382.2	380.0
130°	409.8	414.4	412.7	410.4	406.4
132.5°	436.2	440.8	439.6	436.8	433.9
135°	463.2	466.6	466.0	463.7	462.6
137.5°	487.9	490.7	492.4	489.6	487.9
140°	513.7	516.6	517.1	516.6	512.5
142.5°	537.2	540.1	541.2	540.7	537.8
145°	561.9	563.0	564.8	564.2	561.9
147.5°	583.1	585.4	587.1	587.1	583.7
150°	605.5	606.7	607.8	607.8	604.4
152.5°	623.9	625.6	626.2	627.3	624.5
155°	643.4	643.4	644.0	646.3	642.2
157.5°	660.0	659.5	660.0	662.3	658.9
160°	675.5	674.4	674.4	677.3	675.0
162.5°	689.3	687.6	688.2	691.0	687.0
165°	700.8	699.1	699.1	702.5	698.5
167.5°	710.5	708.3	708.8	712.3	708.8
170°	718.6	716.3	716.3	720.3	716.3
172.5°	724.9	722.6	722.6	726.0	722.0
175°	728.9	726.6	726.6	730.1	726.0
177.5°	731.2	728.9	728.9	732.4	728.3
180°	730.6	730.6	730.6	730.6	730.6

(END OF REPORT)