

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011618

Luminaire Tested: S123DIP-B340D585UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011618
REPORT IS A COMBINATION OF REPORTS P989843 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D585UB40-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3518.0 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	92	88	84	87	84	80	77	68	66	64	55	53	52	42	41	40
2	87	80	74	69	79	73	68	64	60	57	53	48	46	44	37	35	34
3	80	71	64	58	72	65	58	54	53	49	45	43	40	37	33	31	29
4	73	63	55	49	66	57	51	45	47	42	39	38	35	32	30	27	25
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	19
7	57	45	37	32	52	41	35	30	35	29	26	28	24	21	22	19	17
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	18	15
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	22	18	22	18	15	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5011	5011	5011	5011
5°	5014	5773	5028	4308
10°	4982	6987	4987	3762
15°	4914	8285	4954	3387
20°	4854	9539	4864	3117
25°	4766	9779	4777	2976
30°	4704	8080	4704	2883
35°	4626	5404	4596	2801
40°	4532	3901	4476	2676
45°	4415	3090	4288	2521
50°	4130	2624	3982	2369
55°	3818	2306	3662	2198
60°	3500	2008	3314	2019
65°	3152	1719	2998	1781
70°	2789	1427	2603	1501
75°	2385	1076	2229	1159
80°	1884	719	1737	760
85°	1297	330	1037	299

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 8081 cd/sqm

TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.8	1.3
10°-20°	147.0	4.2
20°-30°	247.4	7.0
30°-40°	279.6	7.9
40°-50°	250.4	7.1
50°-60°	202.2	5.7
60°-70°	140.9	4.0
70°-80°	73.9	2.1
80°-90°	19.3	0.5
90°-100°	152.3	4.3
100°-110°	445.9	12.7
110°-120°	435.5	12.4
120°-130°	346.8	9.9
130°-140°	273.6	7.8
140°-150°	204.1	5.8
150°-160°	142.3	4.0
160°-170°	83.6	2.4
170°-180°	27.2	0.8
0°-30°	440.3	12.5
0°-40°	719.9	20.5
0°-60°	1172.5	33.3
0°-90°	1406.6	40.0
90°-120°	1033.7	29.4
90°-150°	1858.3	52.8
90°-180°	2111.0	60.0
0°-180°	3518.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	466	466	466	466	466	
5°	465	553	466	413	465	44
15°	444	823	448	336	444	125
25°	406	977	407	297	406	187
35°	358	526	356	273	358	224
45°	297	284	289	232	297	227
55°	211	193	202	184	211	189
65°	130	125	124	130	130	130
75°	63	64	59	70	63	67
85°	14	15	11	14	14	16
90°	1	16	1	16	1	2
95°	19	66	19	66	19	20
105°	66	723	66	723	66	70
115°	116	879	116	879	116	115
125°	162	693	162	693	162	144
135°	190	562	190	562	190	147
145°	216	439	216	439	216	136
155°	246	364	246	364	246	113
165°	269	318	269	318	269	76
175°	280	286	280	286	280	27
180°	281	281	281	281	281	

TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5
2.5°	466.9	470.5	472.3	475.0	477.7	481.8	483.1	485.4	484.5	486.3	487.2
5°	465.1	471.4	476.8	483.6	489.9	494.4	498.9	506.1	511.5	512.4	516.5
7.5°	461.9	470.9	480.4	489.9	502.1	509.3	517.4	527.3	535.4	548.5	553.5
10°	457.8	470.5	484.0	497.1	513.8	525.1	535.0	551.7	568.4	581.9	594.5
12.5°	451.5	467.3	484.9	504.3	526.0	539.0	552.6	574.7	599.9	620.7	634.2
15°	443.9	463.7	486.3	507.0	530.9	555.3	569.7	594.5	630.6	650.0	684.7
17.5°	437.5	457.8	480.4	512.9	545.4	569.7	580.1	625.6	650.5	682.9	722.2
20°	427.6	453.3	482.2	514.7	556.6	571.5	592.7	638.7	669.4	711.8	760.1
22.5°	417.2	444.8	479.5	513.3	560.2	576.0	604.9	641.4	690.2	732.1	785.3
25°	406.0	435.7	470.9	511.1	557.1	580.1	607.2	652.3	705.0	757.8	807.0
27.5°	394.7	427.2	463.7	503.9	548.5	575.6	602.6	649.6	717.2	774.5	837.2
30°	383.9	416.3	452.9	493.9	540.8	567.0	592.7	651.4	726.7	791.2	854.3
32.5°	372.1	405.5	443.9	478.1	525.5	553.5	582.3	651.4	732.6	801.1	858.9
35°	358.2	392.4	425.4	459.7	506.6	537.7	570.2	646.8	738.0	804.3	839.9
37.5°	344.6	374.8	403.3	436.6	485.8	519.2	556.6	641.4	735.3	790.7	800.7
40°	329.3	359.5	382.5	413.6	465.5	504.3	542.2	634.2	723.5	758.7	729.8
42.5°	314.4	338.3	358.2	388.4	444.8	482.7	523.7	621.1	700.5	707.7	642.8
45°	297.3	314.4	332.0	366.3	422.2	461.0	506.6	602.2	663.5	642.8	560.7
47.5°	275.2	290.5	309.9	341.5	398.3	438.5	481.8	577.8	609.9	566.6	476.8
50°	254.0	267.0	285.1	315.8	373.0	412.3	458.3	539.5	555.3	487.2	410.9
52.5°	232.8	242.7	260.3	290.9	348.2	386.1	428.1	500.2	491.2	418.2	350.5
55°	210.7	219.2	235.9	266.1	319.4	355.5	395.6	452.0	428.5	359.1	304.9
57.5°	189.0	198.0	215.2	240.4	290.5	325.7	357.7	401.9	366.7	311.2	263.4
60°	169.6	177.3	190.4	215.2	260.7	289.1	318.5	348.7	319.4	265.7	229.1
62.5°	149.3	156.5	168.7	191.3	230.5	255.8	279.2	304.0	271.6	232.3	199.8
65°	130.4	136.2	147.5	168.3	200.3	221.0	240.0	257.1	231.0	194.9	170.5
67.5°	113.2	118.2	127.7	146.2	173.2	188.1	203.4	217.9	195.8	166.9	146.2
70°	94.7	98.8	107.4	120.9	142.5	157.9	169.2	180.0	160.1	137.1	123.1
72.5°	78.5	82.5	88.0	101.9	116.8	126.3	138.5	144.3	133.1	114.1	100.1
75°	62.7	65.9	70.8	79.8	93.8	100.1	107.8	112.3	101.9	89.3	80.7
77.5°	49.2	50.5	54.1	60.4	69.9	77.1	83.0	85.7	78.5	70.4	63.2
80°	34.7	36.5	39.2	44.7	51.9	54.1	57.7	60.9	56.4	49.2	44.7
82.5°	23.0	25.3	26.6	28.9	33.4	36.1	37.0	39.7	35.6	32.9	31.1
85°	13.5	14.4	14.9	16.2	18.5	19.8	21.2	21.7	20.7	20.3	18.5
87.5°	6.8	6.8	6.8	7.7	8.1	9.0	9.5	9.5	9.5	9.0	8.6
90°	1.1	2.3	3.4	5.1	6.3	6.8	7.4	9.1	10.8	12.5	14.2
92.5°	8.5	12.5	18.2	23.3	29.0	34.1	39.2	57.4	87.5	117.1	105.7
95°	19.3	21.0	27.3	36.9	51.7	62.8	73.9	122.2	206.8	300.0	337.0
97.5°	30.7	31.3	36.4	44.9	59.7	71.9	84.1	131.8	230.1	387.0	518.2
100°	42.0	42.6	46.6	54.5	68.2	79.2	90.3	130.1	214.2	363.7	538.1
102.5°	54.0	55.1	58.5	65.9	77.8	87.8	97.7	132.4	200.6	329.6	501.2
105°	65.9	67.6	71.0	77.8	88.6	97.4	106.3	136.9	195.5	302.9	456.8
107.5°	78.4	80.1	83.5	90.3	100.6	108.8	117.1	144.3	194.3	283.5	417.6
110°	92.1	93.8	96.6	102.8	112.5	120.4	128.4	154.0	197.2	273.3	385.3

TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	104.6	106.3	109.1	115.3	125.0	132.6	140.3	163.6	202.9	267.6	363.7
115°	116.5	118.8	122.2	127.8	137.5	145.2	152.9	174.4	209.1	267.1	349.5
117.5°	128.4	131.3	134.1	139.2	150.0	157.1	164.2	185.8	217.1	267.6	339.8
120°	140.9	142.6	145.5	151.1	161.9	169.0	176.1	196.6	226.2	269.9	333.5
122.5°	151.7	153.4	156.3	162.5	172.7	180.4	188.1	208.0	234.7	273.9	329.6
125°	161.9	163.1	166.5	172.7	183.5	191.2	198.9	218.8	243.8	277.9	326.2
127.5°	169.9	171.6	175.6	181.8	193.8	201.4	209.1	228.4	251.2	282.4	324.5
130°	177.3	179.0	184.1	190.9	202.9	210.6	218.2	236.9	258.5	286.9	322.7
132.5°	183.0	185.2	190.9	199.4	211.4	218.8	226.2	244.3	265.4	290.4	322.2
135°	189.8	192.1	198.3	206.8	218.8	226.4	234.1	251.7	271.0	293.8	321.6
137.5°	196.0	198.3	204.6	213.6	225.6	232.7	239.8	256.8	275.6	296.0	320.5
140°	202.3	205.1	210.8	219.9	231.3	238.4	245.5	261.9	279.0	298.3	319.9
142.5°	209.1	211.4	217.6	225.6	236.9	243.4	250.0	265.9	282.4	300.0	318.8
145°	216.5	218.2	223.3	231.8	241.5	248.0	254.6	269.3	284.7	300.6	317.6
147.5°	223.9	225.0	230.1	237.5	247.2	252.8	258.5	272.2	286.4	300.6	315.9
150°	231.3	231.8	236.4	243.8	251.7	256.8	261.9	275.0	286.9	300.6	313.7
152.5°	238.7	238.7	243.2	249.4	256.3	261.1	265.9	276.7	288.1	298.9	310.8
155°	246.0	246.0	249.4	255.1	261.4	265.4	269.3	279.0	288.1	297.7	307.4
157.5°	251.7	252.3	255.1	260.2	265.9	269.0	272.2	280.1	288.7	296.0	304.6
160°	258.5	258.5	260.8	265.4	269.3	272.2	275.0	281.8	288.7	294.9	301.2
162.5°	263.7	263.7	265.4	268.8	272.2	274.4	276.7	282.4	288.1	292.6	297.7
165°	268.8	268.2	269.3	272.2	274.4	276.4	278.4	283.0	286.9	290.4	294.3
167.5°	272.7	272.2	272.7	275.0	276.7	278.2	279.6	283.0	286.4	288.1	290.9
170°	276.2	275.0	275.6	277.3	278.4	279.0	279.6	282.4	284.7	285.8	287.5
172.5°	278.4	277.9	277.9	279.0	279.6	279.8	280.1	282.4	284.1	284.1	284.7
175°	280.1	279.6	279.0	280.1	280.1	280.4	280.7	281.8	283.0	282.4	282.4
177.5°	281.3	280.7	280.1	280.7	280.7	280.7	280.7	281.3	282.4	281.3	280.7
180°	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7

TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5
2.5°	490.3	491.2	494.4	496.6	501.2	500.7	500.7	500.2	498.9	501.2	502.5
5°	524.6	532.3	533.2	543.1	543.6	547.6	550.3	548.1	553.5	553.0	549.0
7.5°	567.0	577.4	582.3	591.8	602.6	599.9	610.3	612.1	611.2	615.7	618.9
10°	613.5	631.5	644.1	661.7	666.2	669.0	675.7	681.6	693.3	684.3	690.2
12.5°	666.7	679.8	696.5	724.4	738.4	747.4	750.6	754.7	762.8	757.8	758.3
15°	711.4	728.9	757.4	792.1	796.2	807.4	804.7	829.1	840.8	823.2	833.1
17.5°	757.8	781.3	815.1	845.3	862.5	870.1	877.4	900.8	899.9	897.2	899.5
20°	787.6	825.9	867.9	908.0	913.0	918.9	938.2	948.2	946.4	954.0	959.0
22.5°	829.5	870.1	914.8	941.4	952.7	959.4	974.8	981.1	983.8	985.6	982.5
25°	864.7	908.0	941.0	964.4	971.2	974.8	979.7	981.6	980.2	977.0	979.7
27.5°	888.6	923.4	945.9	956.7	953.1	947.3	937.8	931.5	917.5	910.7	918.9
30°	898.6	913.9	920.7	902.6	884.6	870.1	852.1	818.7	792.5	800.2	789.8
32.5°	882.8	872.8	840.4	793.9	779.9	756.5	705.5	666.2	667.6	646.8	655.4
35°	836.3	791.2	729.8	659.5	641.0	628.4	572.4	563.9	545.8	526.4	531.8
37.5°	754.2	688.3	613.9	562.0	534.5	507.0	475.4	456.5	445.7	437.5	443.9
40°	654.1	573.8	512.4	466.0	442.5	424.9	403.3	384.3	372.1	370.8	373.0
42.5°	555.7	488.1	431.7	387.5	379.8	359.1	345.1	330.2	326.6	320.7	323.9
45°	470.5	415.4	369.0	332.9	323.9	318.5	301.3	291.8	287.8	284.2	289.6
47.5°	408.7	350.9	317.1	295.5	286.4	277.4	267.9	261.6	258.5	258.9	258.5
50°	349.1	306.7	277.0	260.3	254.9	248.5	240.9	236.8	235.5	231.4	234.6
52.5°	300.4	269.7	249.0	233.2	229.1	224.6	218.3	216.1	212.9	212.0	212.0
55°	261.2	237.3	220.6	210.2	205.2	201.6	198.0	195.3	193.1	193.1	193.1
57.5°	230.5	209.8	197.6	188.6	186.7	183.1	179.1	179.1	175.9	175.5	176.8
60°	204.3	185.8	176.4	168.7	166.0	165.1	161.0	161.0	160.1	157.9	159.7
62.5°	177.7	164.2	156.1	150.2	147.5	147.5	144.3	142.1	142.1	142.5	141.6
65°	153.4	143.4	136.2	131.7	130.4	128.6	128.1	126.3	124.9	125.4	124.9
67.5°	131.7	124.0	119.1	115.5	113.2	112.3	111.0	111.0	110.1	110.5	108.3
70°	112.3	104.7	100.6	97.0	96.1	96.1	94.3	94.7	93.8	95.2	94.3
72.5°	92.5	86.6	83.4	82.1	81.2	80.7	79.8	78.9	78.5	79.4	78.9
75°	74.9	69.9	67.7	66.8	65.9	65.9	65.4	65.0	64.5	64.5	64.5
77.5°	58.2	55.0	52.3	53.2	51.9	52.3	51.0	51.0	51.4	51.0	51.0
80°	42.9	40.6	40.6	39.7	37.9	38.8	38.8	37.4	37.0	37.9	36.5
82.5°	28.4	28.0	27.1	26.6	25.7	26.2	25.7	25.3	24.8	25.7	24.8
85°	16.7	16.7	16.2	15.3	16.2	15.8	15.3	15.3	14.9	14.9	14.9
87.5°	8.6	7.7	7.7	7.2	7.7	6.8	7.2	6.8	6.3	6.8	6.3
90°	13.6	14.2	14.8	15.3	15.9	16.5	15.9	16.5	17.0	16.5	17.0
92.5°	79.0	56.3	43.8	38.1	36.1	34.1	33.0	30.7	31.3	30.1	31.3
95°	273.3	204.6	138.6	108.5	98.3	88.1	77.3	72.2	68.2	65.9	68.2
97.5°	535.8	469.9	354.6	279.6	247.2	214.8	176.7	155.1	141.5	135.2	141.5
100°	650.0	669.9	623.9	557.4	517.0	476.7	419.3	377.9	355.7	356.3	355.7
102.5°	655.7	736.4	746.1	714.2	692.4	670.5	629.0	598.3	580.7	564.2	580.7
105°	619.9	738.7	795.5	806.3	798.9	791.5	765.4	743.8	725.6	722.8	725.6
107.5°	568.8	704.6	793.8	838.1	845.8	853.5	850.1	839.8	832.4	826.2	832.4
110°	521.1	651.2	755.7	827.3	847.2	867.1	883.0	887.6	886.4	885.3	886.4

TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	479.6	598.3	705.7	788.1	815.1	842.1	874.5	891.0	896.6	897.2	896.6
115°	447.8	552.9	651.7	735.3	766.2	797.2	839.8	864.8	876.2	879.0	876.2
117.5°	426.7	517.6	605.2	681.9	714.0	746.1	790.4	818.2	835.3	839.3	835.3
120°	410.8	490.9	567.6	635.8	664.5	693.2	738.1	769.9	783.6	787.0	783.6
122.5°	397.8	469.9	537.5	599.5	625.6	651.7	690.4	718.2	733.6	738.1	733.6
125°	387.0	451.7	513.7	568.2	591.0	613.7	650.0	675.0	689.2	693.2	689.2
127.5°	376.7	435.3	491.5	541.5	562.6	583.6	616.5	638.1	651.2	654.6	651.2
130°	368.8	419.9	471.1	517.1	536.4	555.7	585.8	606.3	618.2	622.8	618.2
132.5°	361.4	405.7	451.7	493.8	512.0	530.1	558.0	578.4	588.7	591.5	588.7
135°	355.1	393.2	433.5	470.5	486.7	502.9	530.7	547.8	558.0	562.0	558.0
137.5°	349.5	381.3	415.4	448.3	462.8	477.3	501.2	518.8	527.3	530.7	527.3
140°	344.3	371.0	400.0	427.3	439.5	451.7	473.3	489.2	498.3	497.8	498.3
142.5°	339.8	361.4	385.3	408.0	418.2	428.4	446.0	459.7	467.6	467.1	467.6
145°	335.8	354.0	372.7	390.9	399.2	407.4	421.6	433.5	438.1	439.2	438.1
147.5°	331.8	347.7	363.1	378.4	384.4	390.4	401.7	410.3	414.8	415.4	414.8
150°	327.9	340.9	354.0	365.9	371.3	376.7	385.3	391.5	394.9	394.9	394.9
152.5°	323.3	334.7	345.5	355.7	360.0	364.2	370.5	376.2	377.9	377.9	377.9
155°	318.8	328.4	337.5	346.0	349.4	352.9	358.0	362.5	363.7	364.2	363.7
157.5°	313.7	321.6	329.6	336.4	339.2	342.1	346.6	350.0	351.2	351.2	351.2
160°	308.5	315.9	322.2	327.9	329.8	331.8	335.8	339.2	339.2	338.7	339.2
162.5°	303.4	309.1	314.2	319.3	321.0	322.7	325.0	327.9	327.9	327.3	327.9
165°	298.9	303.4	306.8	310.8	312.2	313.7	315.9	318.2	317.6	317.6	317.6
167.5°	294.3	298.3	301.2	303.4	304.5	305.7	306.8	308.5	308.0	308.0	308.0
170°	290.4	293.2	294.9	297.2	297.8	298.3	298.9	300.0	299.5	299.5	299.5
172.5°	286.4	288.7	289.8	291.5	291.8	292.1	292.1	293.2	292.1	291.5	292.1
175°	283.5	284.7	285.2	286.4	286.4	286.4	286.4	286.9	286.4	285.8	286.4
177.5°	281.3	281.8	282.4	283.0	283.0	283.0	282.4	283.0	281.8	281.8	281.8
180°	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7

TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5
2.5°	498.9	500.2	496.6	495.7	495.7	497.5	496.2	484.0	486.3	483.6	482.7
5°	553.9	551.2	547.6	545.8	543.6	537.2	536.8	522.8	520.1	511.1	507.0
7.5°	614.4	612.1	601.3	599.9	599.0	593.2	578.3	563.4	552.6	542.2	532.3
10°	683.4	676.6	671.7	661.7	656.8	648.7	629.3	615.3	596.8	581.0	560.2
12.5°	766.4	758.7	742.0	734.8	728.5	705.9	686.5	670.8	634.7	623.8	598.1
15°	827.3	811.0	809.2	793.5	792.5	767.7	730.8	713.6	685.6	645.9	619.3
17.5°	893.1	878.7	867.4	848.5	845.8	822.3	795.3	753.3	722.6	684.7	650.9
20°	941.4	933.7	914.3	906.7	890.9	871.0	843.1	791.2	753.8	715.9	674.4
22.5°	979.7	972.1	956.7	946.4	937.3	911.6	878.3	834.0	782.6	733.0	690.2
25°	979.3	977.0	970.7	965.8	959.0	940.1	912.1	869.7	812.4	757.8	698.3
27.5°	923.8	930.1	941.0	946.4	945.0	942.3	926.5	890.9	839.5	774.5	707.7
30°	808.3	831.3	851.6	878.7	886.8	906.7	915.7	895.4	854.3	793.9	719.9
32.5°	670.3	703.7	747.9	762.8	788.5	826.8	869.7	877.4	851.6	805.2	727.6
35°	549.9	577.4	611.7	635.1	658.1	720.4	774.5	821.4	830.0	799.3	725.8
37.5°	455.1	474.5	504.8	524.6	545.8	599.0	674.8	735.7	778.6	779.5	720.8
40°	386.6	395.1	421.3	435.7	456.0	502.1	569.7	649.1	711.8	740.7	707.7
42.5°	327.5	338.8	360.4	371.2	384.3	424.5	469.1	544.5	622.0	683.8	683.4
45°	292.3	300.4	310.3	319.4	334.3	358.2	409.1	465.5	539.9	609.9	637.4
47.5°	261.2	268.8	278.8	281.5	291.4	314.0	345.1	394.2	463.7	533.2	585.1
50°	235.0	241.3	248.1	253.1	257.6	276.1	299.5	341.0	396.5	463.7	528.2
52.5°	214.7	219.2	225.1	227.8	231.9	245.4	263.4	294.1	339.7	401.0	463.7
55°	195.8	198.9	202.5	207.0	208.9	218.8	232.8	258.9	292.8	347.8	407.3
57.5°	178.2	179.5	181.8	184.5	186.7	195.3	207.5	225.1	254.9	297.3	353.6
60°	158.3	161.9	163.3	166.0	167.4	174.1	183.6	198.5	221.5	258.0	300.4
62.5°	141.6	143.9	146.2	147.5	150.7	152.9	160.6	174.1	193.1	220.1	258.5
65°	126.8	127.7	129.0	130.4	131.3	134.0	141.2	150.2	164.6	188.6	218.3
67.5°	109.6	110.5	112.3	112.8	113.7	117.3	121.3	129.0	141.2	159.2	183.6
70°	92.9	94.3	95.2	96.1	97.4	98.8	103.3	109.6	119.1	131.7	150.7
72.5°	78.5	79.8	79.8	80.7	80.3	82.1	86.6	91.1	97.4	107.8	124.5
75°	64.1	64.1	65.0	65.4	65.9	67.7	69.5	73.1	78.0	86.2	96.5
77.5°	50.5	50.1	51.0	51.0	51.0	52.3	54.1	55.9	59.1	65.0	73.1
80°	37.0	37.0	37.9	38.3	37.4	37.9	38.8	40.6	42.9	46.9	51.4
82.5°	24.4	26.2	25.7	26.2	25.7	26.6	27.1	27.5	28.4	30.2	33.4
85°	14.9	14.9	14.9	15.3	14.9	15.3	15.3	15.3	15.8	16.7	18.0
87.5°	6.3	6.3	6.3	6.8	6.3	6.3	6.8	6.3	6.8	6.8	7.2
90°	16.5	15.9	16.5	15.9	15.3	14.8	14.2	13.6	14.2	12.5	10.8
92.5°	30.7	33.0	34.1	36.1	38.1	43.8	56.3	79.0	105.7	117.1	87.5
95°	72.2	77.3	88.1	98.3	108.5	138.6	204.6	273.3	337.0	300.0	206.8
97.5°	155.1	176.7	214.8	247.2	279.6	354.6	469.9	535.8	518.2	387.0	230.1
100°	377.9	419.3	476.7	517.0	557.4	623.9	669.9	650.0	538.1	363.7	214.2
102.5°	598.3	629.0	670.5	692.4	714.2	746.1	736.4	655.7	501.2	329.6	200.6
105°	743.8	765.4	791.5	798.9	806.3	795.5	738.7	619.9	456.8	302.9	195.5
107.5°	839.8	850.1	853.5	845.8	838.1	793.8	704.6	568.8	417.6	283.5	194.3
110°	887.6	883.0	867.1	847.2	827.3	755.7	651.2	521.1	385.3	273.3	197.2

TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	891.0	874.5	842.1	815.1	788.1	705.7	598.3	479.6	363.7	267.6	202.9
115°	864.8	839.8	797.2	766.2	735.3	651.7	552.9	447.8	349.5	267.1	209.1
117.5°	818.2	790.4	746.1	714.0	681.9	605.2	517.6	426.7	339.8	267.6	217.1
120°	769.9	738.1	693.2	664.5	635.8	567.6	490.9	410.8	333.5	269.9	226.2
122.5°	718.2	690.4	651.7	625.6	599.5	537.5	469.9	397.8	329.6	273.9	234.7
125°	675.0	650.0	613.7	591.0	568.2	513.7	451.7	387.0	326.2	277.9	243.8
127.5°	638.1	616.5	583.6	562.6	541.5	491.5	435.3	376.7	324.5	282.4	251.2
130°	606.3	585.8	555.7	536.4	517.1	471.1	419.9	368.8	322.7	286.9	258.5
132.5°	578.4	558.0	530.1	512.0	493.8	451.7	405.7	361.4	322.2	290.4	265.4
135°	547.8	530.7	502.9	486.7	470.5	433.5	393.2	355.1	321.6	293.8	271.0
137.5°	518.8	501.2	477.3	462.8	448.3	415.4	381.3	349.5	320.5	296.0	275.6
140°	489.2	473.3	451.7	439.5	427.3	400.0	371.0	344.3	319.9	298.3	279.0
142.5°	459.7	446.0	428.4	418.2	408.0	385.3	361.4	339.8	318.8	300.0	282.4
145°	433.5	421.6	407.4	399.2	390.9	372.7	354.0	335.8	317.6	300.6	284.7
147.5°	410.3	401.7	390.4	384.4	378.4	363.1	347.7	331.8	315.9	300.6	286.4
150°	391.5	385.3	376.7	371.3	365.9	354.0	340.9	327.9	313.7	300.6	286.9
152.5°	376.2	370.5	364.2	360.0	355.7	345.5	334.7	323.3	310.8	298.9	288.1
155°	362.5	358.0	352.9	349.4	346.0	337.5	328.4	318.8	307.4	297.7	288.1
157.5°	350.0	346.6	342.1	339.2	336.4	329.6	321.6	313.7	304.6	296.0	288.7
160°	339.2	335.8	331.8	329.8	327.9	322.2	315.9	308.5	301.2	294.9	288.7
162.5°	327.9	325.0	322.7	321.0	319.3	314.2	309.1	303.4	297.7	292.6	288.1
165°	318.2	315.9	313.7	312.2	310.8	306.8	303.4	298.9	294.3	290.4	286.9
167.5°	308.5	306.8	305.7	304.5	303.4	301.2	298.3	294.3	290.9	288.1	286.4
170°	300.0	298.9	298.3	297.8	297.2	294.9	293.2	290.4	287.5	285.8	284.7
172.5°	293.2	292.1	292.1	291.8	291.5	289.8	288.7	286.4	284.7	284.1	284.1
175°	286.9	286.4	286.4	286.4	286.4	285.2	284.7	283.5	282.4	282.4	283.0
177.5°	283.0	282.4	283.0	283.0	283.0	282.4	281.8	281.3	280.7	281.3	282.4
180°	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7

TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5
2.5°	478.1	476.8	476.8	475.9	473.2	468.2	467.8	468.7	466.0	463.3	459.2
5°	501.6	493.0	490.3	487.6	482.2	473.2	469.6	466.4	461.5	455.6	449.3
7.5°	521.4	509.3	505.7	500.7	489.9	477.2	469.1	462.4	455.6	447.5	439.8
10°	546.3	528.7	520.1	512.9	498.0	480.4	468.2	458.3	447.5	437.5	427.6
12.5°	574.2	545.8	543.1	525.5	508.4	482.2	467.3	452.9	438.5	426.3	415.9
15°	597.7	566.6	555.3	543.6	510.6	478.1	463.7	447.5	430.8	417.7	402.4
17.5°	612.6	586.9	562.9	547.2	512.9	484.0	456.0	437.5	420.0	401.9	389.3
20°	630.6	593.2	572.4	551.2	517.4	479.5	451.5	428.5	406.9	390.6	375.3
22.5°	648.7	598.1	581.0	558.0	518.3	475.0	443.4	420.4	395.6	379.4	362.7
25°	646.8	605.4	576.9	557.5	509.3	470.9	433.9	406.9	383.9	363.1	346.4
27.5°	648.2	597.2	568.4	545.8	503.0	465.1	424.0	395.6	371.7	350.0	332.4
30°	648.7	585.1	559.8	532.7	491.2	451.1	412.7	383.9	358.6	335.2	319.4
32.5°	647.3	575.1	543.6	519.2	472.7	437.5	399.7	369.0	343.3	321.6	306.7
35°	644.1	563.4	526.9	496.2	453.8	418.2	387.5	355.9	328.4	308.5	291.4
37.5°	635.6	550.8	509.3	479.0	431.7	395.6	368.5	342.4	315.8	292.3	277.9
40°	629.3	533.6	491.7	458.7	407.8	372.6	350.0	325.2	299.1	277.9	263.9
42.5°	614.8	517.4	473.6	434.4	384.3	348.2	327.0	307.2	284.6	263.9	251.3
45°	591.4	499.8	451.5	411.8	358.6	324.3	304.9	288.7	268.8	249.0	236.4
47.5°	558.4	474.5	428.1	388.4	333.3	298.6	279.2	267.0	251.3	234.6	223.7
50°	522.8	447.0	404.2	364.9	309.0	275.2	256.2	244.9	234.6	219.2	208.9
52.5°	476.3	417.7	376.7	339.2	282.8	250.3	233.7	225.5	214.7	203.9	194.9
55°	431.2	379.8	346.0	310.3	257.1	226.9	210.7	202.1	195.8	186.7	179.5
57.5°	378.9	344.6	313.5	281.0	233.2	205.7	190.4	180.0	175.9	171.9	165.1
60°	330.6	304.5	279.2	252.2	208.4	183.6	168.7	160.6	156.5	153.8	149.3
62.5°	286.4	266.1	244.5	222.8	183.1	160.6	149.3	141.2	137.6	137.1	133.1
65°	244.0	229.6	212.0	190.8	159.7	139.8	129.0	124.0	120.0	120.0	116.8
67.5°	201.6	191.7	177.7	162.8	138.5	120.0	110.1	105.6	103.3	103.3	101.0
70°	167.8	161.0	148.4	135.3	114.1	100.1	92.5	88.4	87.1	87.5	85.7
72.5°	136.2	129.0	118.6	109.2	93.4	83.0	77.6	73.1	70.8	71.3	70.8
75°	105.6	101.9	92.9	85.7	73.1	65.9	60.9	58.6	56.8	57.3	56.4
77.5°	79.4	74.0	69.0	64.1	56.4	50.5	46.5	44.2	42.9	42.9	42.9
80°	54.1	53.2	49.2	46.5	40.1	35.6	32.5	32.0	30.7	30.7	30.7
82.5°	35.2	32.9	30.7	28.9	25.3	22.6	21.2	20.3	19.8	19.4	20.3
85°	19.4	18.0	17.1	15.3	14.0	12.6	11.3	10.8	10.4	10.8	10.4
87.5°	7.7	6.3	6.3	5.9	5.4	5.0	5.0	4.1	4.1	3.6	3.6
90°	9.1	7.4	6.8	6.3	5.1	3.4	2.3	1.1	2.3	3.4	5.1
92.5°	57.4	39.2	34.1	29.0	23.3	18.2	12.5	8.5	12.5	18.2	23.3
95°	122.2	73.9	62.8	51.7	36.9	27.3	21.0	19.3	21.0	27.3	36.9
97.5°	131.8	84.1	71.9	59.7	44.9	36.4	31.3	30.7	31.3	36.4	44.9
100°	130.1	90.3	79.2	68.2	54.5	46.6	42.6	42.0	42.6	46.6	54.5
102.5°	132.4	97.7	87.8	77.8	65.9	58.5	55.1	54.0	55.1	58.5	65.9
105°	136.9	106.3	97.4	88.6	77.8	71.0	67.6	65.9	67.6	71.0	77.8
107.5°	144.3	117.1	108.8	100.6	90.3	83.5	80.1	78.4	80.1	83.5	90.3
110°	154.0	128.4	120.4	112.5	102.8	96.6	93.8	92.1	93.8	96.6	102.8

TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	163.6	140.3	132.6	125.0	115.3	109.1	106.3	104.6	106.3	109.1	115.3
115°	174.4	152.9	145.2	137.5	127.8	122.2	118.8	116.5	118.8	122.2	127.8
117.5°	185.8	164.2	157.1	150.0	139.2	134.1	131.3	128.4	131.3	134.1	139.2
120°	196.6	176.1	169.0	161.9	151.1	145.5	142.6	140.9	142.6	145.5	151.1
122.5°	208.0	188.1	180.4	172.7	162.5	156.3	153.4	151.7	153.4	156.3	162.5
125°	218.8	198.9	191.2	183.5	172.7	166.5	163.1	161.9	163.1	166.5	172.7
127.5°	228.4	209.1	201.4	193.8	181.8	175.6	171.6	169.9	171.6	175.6	181.8
130°	236.9	218.2	210.6	202.9	190.9	184.1	179.0	177.3	179.0	184.1	190.9
132.5°	244.3	226.2	218.8	211.4	199.4	190.9	185.2	183.0	185.2	190.9	199.4
135°	251.7	234.1	226.4	218.8	206.8	198.3	192.1	189.8	192.1	198.3	206.8
137.5°	256.8	239.8	232.7	225.6	213.6	204.6	198.3	196.0	198.3	204.6	213.6
140°	261.9	245.5	238.4	231.3	219.9	210.8	205.1	202.3	205.1	210.8	219.9
142.5°	265.9	250.0	243.4	236.9	225.6	217.6	211.4	209.1	211.4	217.6	225.6
145°	269.3	254.6	248.0	241.5	231.8	223.3	218.2	216.5	218.2	223.3	231.8
147.5°	272.2	258.5	252.8	247.2	237.5	230.1	225.0	223.9	225.0	230.1	237.5
150°	275.0	261.9	256.8	251.7	243.8	236.4	231.8	231.3	231.8	236.4	243.8
152.5°	276.7	265.9	261.1	256.3	249.4	243.2	238.7	238.7	238.7	243.2	249.4
155°	279.0	269.3	265.4	261.4	255.1	249.4	246.0	246.0	246.0	249.4	255.1
157.5°	280.1	272.2	269.0	265.9	260.2	255.1	252.3	251.7	252.3	255.1	260.2
160°	281.8	275.0	272.2	269.3	265.4	260.8	258.5	258.5	258.5	260.8	265.4
162.5°	282.4	276.7	274.4	272.2	268.8	265.4	263.7	263.7	263.7	265.4	268.8
165°	283.0	278.4	276.4	274.4	272.2	269.3	268.2	268.8	268.2	269.3	272.2
167.5°	283.0	279.6	278.2	276.7	275.0	272.7	272.2	272.7	272.2	272.7	275.0
170°	282.4	279.6	279.0	278.4	277.3	275.6	275.0	276.2	275.0	275.6	277.3
172.5°	282.4	280.1	279.8	279.6	279.0	277.9	277.9	278.4	277.9	277.9	279.0
175°	281.8	280.7	280.4	280.1	280.1	279.0	279.6	280.1	279.6	279.0	280.1
177.5°	281.3	280.7	280.7	280.7	280.7	280.1	280.7	281.3	280.7	280.1	280.7
180°	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7

TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5
2.5°	458.3	457.8	458.7	456.0	451.5	449.3	443.0	441.6	441.2	441.6	442.1
5°	445.7	445.2	443.9	439.4	433.9	429.9	422.2	421.8	419.1	416.3	417.7
7.5°	433.5	431.7	429.0	423.1	415.9	411.4	405.1	400.6	397.0	394.7	392.9
10°	421.3	418.6	415.9	408.2	399.2	392.4	384.8	381.2	377.1	375.3	373.5
12.5°	405.5	402.8	397.9	388.8	383.4	374.8	367.2	363.6	361.3	357.7	355.5
15°	392.9	387.5	384.8	375.3	364.0	363.1	349.1	348.2	343.7	343.7	340.1
17.5°	378.5	374.4	369.4	360.0	351.8	343.7	336.5	333.8	329.7	328.8	327.0
20°	364.5	359.1	357.3	347.8	339.2	329.3	321.6	318.9	317.1	315.3	316.7
22.5°	350.0	345.5	341.0	332.4	326.1	316.2	311.7	309.0	306.3	305.4	305.8
25°	336.1	332.0	327.5	318.9	312.1	304.0	300.0	298.6	297.3	297.3	296.8
27.5°	322.5	318.5	314.4	306.7	300.0	294.1	290.9	289.6	288.2	289.1	290.0
30°	308.5	304.9	301.3	294.6	289.1	283.7	281.9	281.0	280.6	282.8	282.8
32.5°	295.9	292.8	290.0	283.7	278.3	273.8	272.5	272.9	273.4	274.7	275.6
35°	282.8	280.6	277.9	272.5	267.9	263.9	264.3	264.3	265.2	267.5	269.3
37.5°	271.1	267.9	265.7	261.2	257.6	254.0	255.3	256.7	257.6	260.3	261.2
40°	257.1	255.8	254.0	249.4	246.3	245.8	246.3	247.2	249.0	250.3	251.7
42.5°	245.8	244.0	241.8	238.2	235.5	235.9	236.4	237.3	238.2	240.4	241.8
45°	233.2	231.9	230.1	226.9	224.6	225.1	225.5	225.5	226.4	229.1	230.1
47.5°	219.2	219.7	217.4	214.3	212.9	212.9	212.9	213.8	216.1	217.0	217.4
50°	205.7	204.8	204.3	201.2	200.3	199.8	200.3	200.7	203.9	203.4	204.8
52.5°	191.3	191.3	190.8	189.0	187.6	187.6	186.7	189.0	189.9	190.8	192.2
55°	177.3	175.9	175.5	174.6	172.8	172.3	173.2	175.9	176.8	177.7	179.1
57.5°	161.9	161.9	161.0	159.7	159.7	159.7	159.7	161.5	162.8	163.7	166.4
60°	148.0	146.2	144.8	144.8	144.8	144.3	147.1	147.1	149.8	150.2	151.1
62.5°	131.3	130.4	129.5	129.9	129.5	130.4	131.3	133.1	133.5	134.9	136.2
65°	115.5	115.5	114.6	117.3	115.5	115.5	117.7	117.7	118.6	120.0	121.8
67.5°	100.1	100.6	99.7	99.7	100.6	101.0	101.5	103.3	103.7	105.6	107.8
70°	84.4	85.3	85.7	84.8	85.7	86.6	87.5	88.0	89.8	90.7	92.0
72.5°	70.4	71.3	69.9	70.4	70.8	71.7	72.2	73.1	74.0	76.7	77.6
75°	56.4	55.9	55.5	57.3	56.4	58.2	58.6	58.6	59.5	61.8	62.7
77.5°	43.3	43.3	43.8	42.9	44.2	43.8	44.2	45.6	46.9	46.9	50.5
80°	30.2	31.1	31.1	31.1	31.6	32.0	31.1	33.4	33.8	33.8	35.2
82.5°	19.4	19.8	19.4	20.3	20.3	21.2	20.7	21.2	22.1	23.0	23.5
85°	10.4	10.4	11.3	11.3	10.8	11.3	10.8	11.3	12.2	12.2	12.6
87.5°	3.6	3.6	3.6	3.6	4.1	3.6	4.1	4.1	3.6	3.6	5.0
90°	6.3	6.8	7.4	9.1	10.8	12.5	14.2	13.6	14.2	14.8	15.3
92.5°	29.0	34.1	39.2	57.4	87.5	117.1	105.7	79.0	56.3	43.8	38.1
95°	51.7	62.8	73.9	122.2	206.8	300.0	337.0	273.3	204.6	138.6	108.5
97.5°	59.7	71.9	84.1	131.8	230.1	387.0	518.2	535.8	469.9	354.6	279.6
100°	68.2	79.2	90.3	130.1	214.2	363.7	538.1	650.0	669.9	623.9	557.4
102.5°	77.8	87.8	97.7	132.4	200.6	329.6	501.2	655.7	736.4	746.1	714.2
105°	88.6	97.4	106.3	136.9	195.5	302.9	456.8	619.9	738.7	795.5	806.3
107.5°	100.6	108.8	117.1	144.3	194.3	283.5	417.6	568.8	704.6	793.8	838.1
110°	112.5	120.4	128.4	154.0	197.2	273.3	385.3	521.1	651.2	755.7	827.3

TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	125.0	132.6	140.3	163.6	202.9	267.6	363.7	479.6	598.3	705.7	788.1
115°	137.5	145.2	152.9	174.4	209.1	267.1	349.5	447.8	552.9	651.7	735.3
117.5°	150.0	157.1	164.2	185.8	217.1	267.6	339.8	426.7	517.6	605.2	681.9
120°	161.9	169.0	176.1	196.6	226.2	269.9	333.5	410.8	490.9	567.6	635.8
122.5°	172.7	180.4	188.1	208.0	234.7	273.9	329.6	397.8	469.9	537.5	599.5
125°	183.5	191.2	198.9	218.8	243.8	277.9	326.2	387.0	451.7	513.7	568.2
127.5°	193.8	201.4	209.1	228.4	251.2	282.4	324.5	376.7	435.3	491.5	541.5
130°	202.9	210.6	218.2	236.9	258.5	286.9	322.7	368.8	419.9	471.1	517.1
132.5°	211.4	218.8	226.2	244.3	265.4	290.4	322.2	361.4	405.7	451.7	493.8
135°	218.8	226.4	234.1	251.7	271.0	293.8	321.6	355.1	393.2	433.5	470.5
137.5°	225.6	232.7	239.8	256.8	275.6	296.0	320.5	349.5	381.3	415.4	448.3
140°	231.3	238.4	245.5	261.9	279.0	298.3	319.9	344.3	371.0	400.0	427.3
142.5°	236.9	243.4	250.0	265.9	282.4	300.0	318.8	339.8	361.4	385.3	408.0
145°	241.5	248.0	254.6	269.3	284.7	300.6	317.6	335.8	354.0	372.7	390.9
147.5°	247.2	252.8	258.5	272.2	286.4	300.6	315.9	331.8	347.7	363.1	378.4
150°	251.7	256.8	261.9	275.0	286.9	300.6	313.7	327.9	340.9	354.0	365.9
152.5°	256.3	261.1	265.9	276.7	288.1	298.9	310.8	323.3	334.7	345.5	355.7
155°	261.4	265.4	269.3	279.0	288.1	297.7	307.4	318.8	328.4	337.5	346.0
157.5°	265.9	269.0	272.2	280.1	288.7	296.0	304.6	313.7	321.6	329.6	336.4
160°	269.3	272.2	275.0	281.8	288.7	294.9	301.2	308.5	315.9	322.2	327.9
162.5°	272.2	274.4	276.7	282.4	288.1	292.6	297.7	303.4	309.1	314.2	319.3
165°	274.4	276.4	278.4	283.0	286.9	290.4	294.3	298.9	303.4	306.8	310.8
167.5°	276.7	278.2	279.6	283.0	286.4	288.1	290.9	294.3	298.3	301.2	303.4
170°	278.4	279.0	279.6	282.4	284.7	285.8	287.5	290.4	293.2	294.9	297.2
172.5°	279.6	279.8	280.1	282.4	284.1	284.1	284.7	286.4	288.7	289.8	291.5
175°	280.1	280.4	280.7	281.8	283.0	282.4	282.4	283.5	284.7	285.2	286.4
177.5°	280.7	280.7	280.7	281.3	282.4	281.3	280.7	281.3	281.8	282.4	283.0
180°	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7

TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5
2.5°	441.6	442.1	440.3	438.9	442.5	440.3	440.3	440.7	439.8	441.2	440.7
5°	416.8	417.2	414.1	415.0	413.2	412.7	412.3	415.0	414.5	414.1	415.0
7.5°	392.4	392.4	391.1	390.2	390.2	388.8	390.6	390.2	391.1	391.1	392.4
10°	372.1	373.0	370.8	368.5	368.1	368.5	368.5	369.0	369.4	372.6	372.1
12.5°	355.5	354.1	353.6	352.3	350.0	349.1	348.2	353.2	351.8	351.8	351.8
15°	337.0	340.1	339.7	335.6	334.7	336.5	335.6	335.6	340.1	339.7	339.2
17.5°	327.0	326.1	325.2	323.0	323.4	323.0	323.4	323.4	326.1	326.1	326.1
20°	315.8	314.0	314.0	313.1	313.1	311.7	313.5	314.0	315.8	315.8	316.2
22.5°	305.8	304.5	304.5	304.0	304.9	303.1	304.9	305.4	305.4	306.7	306.7
25°	297.3	296.4	296.4	297.3	297.3	297.3	297.3	299.1	297.7	298.2	297.7
27.5°	289.6	290.0	290.5	290.9	290.5	290.9	291.4	292.3	292.8	292.3	291.4
30°	282.4	283.7	284.2	284.2	285.1	285.5	286.0	286.0	286.4	285.1	286.0
32.5°	277.0	277.0	277.9	278.3	279.2	279.7	279.7	280.6	280.1	278.8	279.2
35°	269.3	269.3	271.1	272.0	273.4	272.9	273.4	273.4	273.8	272.9	271.6
37.5°	261.6	262.5	262.5	264.3	264.8	265.2	264.8	265.7	265.2	264.3	263.9
40°	252.6	252.2	252.6	254.0	254.4	254.4	254.4	255.3	255.3	255.3	254.9
42.5°	241.3	242.7	242.2	243.6	243.1	243.1	244.0	244.9	245.4	244.0	244.5
45°	230.5	230.5	231.4	231.4	231.9	231.9	233.7	232.8	233.7	232.8	233.2
47.5°	218.8	219.2	219.2	219.7	220.6	221.5	220.6	221.0	221.0	221.5	220.6
50°	205.7	205.7	206.6	207.9	209.8	208.9	208.4	210.2	208.9	208.9	207.9
52.5°	192.2	193.5	194.0	195.3	196.7	197.1	197.6	196.7	197.1	195.8	196.2
55°	179.1	179.5	181.3	182.7	184.0	184.0	183.6	184.0	184.5	182.7	182.7
57.5°	166.0	167.4	169.2	169.2	171.0	171.0	170.5	170.5	171.0	169.6	169.2
60°	152.0	153.4	155.6	155.6	158.3	158.8	157.9	157.0	157.0	155.6	156.1
62.5°	137.1	138.5	139.8	142.1	143.9	143.0	144.8	143.0	143.4	140.7	140.7
65°	124.0	124.5	126.8	129.0	129.0	129.9	129.0	129.5	128.1	128.1	126.3
67.5°	108.7	108.7	111.0	113.2	115.5	115.5	115.5	114.1	114.1	112.8	112.8
70°	95.2	94.7	97.0	98.3	99.7	100.1	99.2	98.8	97.9	96.5	96.1
72.5°	78.5	79.4	81.6	82.5	84.8	84.4	86.6	83.9	83.9	81.6	81.2
75°	63.6	64.5	66.8	68.1	69.5	69.5	70.8	69.5	67.7	66.8	66.3
77.5°	50.5	50.1	51.9	54.1	54.6	54.1	55.0	54.6	52.8	52.8	51.9
80°	36.1	37.4	39.2	38.8	40.6	40.1	40.1	39.2	39.2	37.9	38.8
82.5°	23.9	25.3	25.7	25.3	25.7	26.6	27.1	26.6	26.6	25.7	26.2
85°	12.6	12.6	13.5	14.0	13.5	13.5	14.0	15.3	14.4	13.5	14.4
87.5°	4.1	3.6	3.6	4.1	3.6	3.6	4.1	4.1	4.5	4.5	4.5
90°	15.9	16.5	15.9	16.5	17.0	16.5	17.0	16.5	15.9	16.5	15.9
92.5°	36.1	34.1	33.0	30.7	31.3	30.1	31.3	30.7	33.0	34.1	36.1
95°	98.3	88.1	77.3	72.2	68.2	65.9	68.2	72.2	77.3	88.1	98.3
97.5°	247.2	214.8	176.7	155.1	141.5	135.2	141.5	155.1	176.7	214.8	247.2
100°	517.0	476.7	419.3	377.9	355.7	356.3	355.7	377.9	419.3	476.7	517.0
102.5°	692.4	670.5	629.0	598.3	580.7	564.2	580.7	598.3	629.0	670.5	692.4
105°	798.9	791.5	765.4	743.8	725.6	722.8	725.6	743.8	765.4	791.5	798.9
107.5°	845.8	853.5	850.1	839.8	832.4	826.2	832.4	839.8	850.1	853.5	845.8
110°	847.2	867.1	883.0	887.6	886.4	885.3	886.4	887.6	883.0	867.1	847.2



TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	815.1	842.1	874.5	891.0	896.6	897.2	896.6	891.0	874.5	842.1	815.1
115°	766.2	797.2	839.8	864.8	876.2	879.0	876.2	864.8	839.8	797.2	766.2
117.5°	714.0	746.1	790.4	818.2	835.3	839.3	835.3	818.2	790.4	746.1	714.0
120°	664.5	693.2	738.1	769.9	783.6	787.0	783.6	769.9	738.1	693.2	664.5
122.5°	625.6	651.7	690.4	718.2	733.6	738.1	733.6	718.2	690.4	651.7	625.6
125°	591.0	613.7	650.0	675.0	689.2	693.2	689.2	675.0	650.0	613.7	591.0
127.5°	562.6	583.6	616.5	638.1	651.2	654.6	651.2	638.1	616.5	583.6	562.6
130°	536.4	555.7	585.8	606.3	618.2	622.8	618.2	606.3	585.8	555.7	536.4
132.5°	512.0	530.1	558.0	578.4	588.7	591.5	588.7	578.4	558.0	530.1	512.0
135°	486.7	502.9	530.7	547.8	558.0	562.0	558.0	547.8	530.7	502.9	486.7
137.5°	462.8	477.3	501.2	518.8	527.3	530.7	527.3	518.8	501.2	477.3	462.8
140°	439.5	451.7	473.3	489.2	498.3	497.8	498.3	489.2	473.3	451.7	439.5
142.5°	418.2	428.4	446.0	459.7	467.6	467.1	467.6	459.7	446.0	428.4	418.2
145°	399.2	407.4	421.6	433.5	438.1	439.2	438.1	433.5	421.6	407.4	399.2
147.5°	384.4	390.4	401.7	410.3	414.8	415.4	414.8	410.3	401.7	390.4	384.4
150°	371.3	376.7	385.3	391.5	394.9	394.9	394.9	391.5	385.3	376.7	371.3
152.5°	360.0	364.2	370.5	376.2	377.9	377.9	377.9	376.2	370.5	364.2	360.0
155°	349.4	352.9	358.0	362.5	363.7	364.2	363.7	362.5	358.0	352.9	349.4
157.5°	339.2	342.1	346.6	350.0	351.2	351.2	351.2	350.0	346.6	342.1	339.2
160°	329.8	331.8	335.8	339.2	339.2	338.7	339.2	339.2	335.8	331.8	329.8
162.5°	321.0	322.7	325.0	327.9	327.9	327.3	327.9	327.9	325.0	322.7	321.0
165°	312.2	313.7	315.9	318.2	317.6	317.6	317.6	318.2	315.9	313.7	312.2
167.5°	304.5	305.7	306.8	308.5	308.0	308.0	308.0	308.5	306.8	305.7	304.5
170°	297.8	298.3	298.9	300.0	299.5	299.5	299.5	300.0	298.9	298.3	297.8
172.5°	291.8	292.1	292.1	293.2	292.1	291.5	292.1	293.2	292.1	292.1	291.8
175°	286.4	286.4	286.4	286.9	286.4	285.8	286.4	286.9	286.4	286.4	286.4
177.5°	283.0	283.0	282.4	283.0	281.8	281.8	281.8	283.0	282.4	283.0	283.0
180°	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7

TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5	465.5
2.5°	442.1	443.0	443.4	441.6	440.3	442.5	445.7	447.9	449.7	452.0	453.3
5°	415.9	419.1	419.1	420.0	421.3	423.6	429.4	433.5	437.1	439.8	442.1
7.5°	393.8	396.0	397.4	399.7	401.9	405.1	411.8	417.7	423.1	426.3	429.9
10°	373.9	375.8	378.0	379.4	383.4	387.9	396.5	401.5	407.8	412.7	417.2
12.5°	355.0	361.3	362.7	362.2	365.8	370.8	379.4	387.0	393.8	398.8	403.7
15°	341.5	343.7	346.4	346.0	353.6	355.0	362.2	371.2	380.3	383.4	387.9
17.5°	326.6	330.2	332.9	334.3	336.5	341.5	348.2	355.0	366.7	367.2	378.9
20°	314.9	318.5	320.3	322.1	323.4	329.3	335.2	342.8	352.3	357.3	363.6
22.5°	307.2	309.0	310.3	311.7	313.5	316.7	323.9	332.4	338.8	344.2	348.2
25°	298.2	300.0	301.8	302.7	304.0	305.8	311.2	318.0	327.0	330.6	334.7
27.5°	291.8	291.8	292.8	292.8	294.6	296.4	300.4	306.7	314.0	318.5	323.9
30°	285.1	284.6	285.1	284.6	284.2	286.9	290.5	295.9	300.9	306.3	309.9
32.5°	278.3	277.9	277.9	278.3	276.5	277.9	279.7	284.6	290.0	292.8	296.8
35°	271.1	270.2	270.2	270.2	269.3	268.4	270.2	274.7	278.3	281.9	285.1
37.5°	263.9	262.5	262.5	261.6	260.7	259.4	259.4	263.0	267.9	269.3	273.4
40°	254.0	254.0	253.1	252.6	251.7	250.8	249.4	252.6	257.1	258.5	261.6
42.5°	244.0	242.7	242.2	242.2	242.2	240.9	240.0	242.2	244.9	247.2	249.0
45°	232.8	231.9	232.3	231.9	231.0	230.5	230.1	231.0	234.1	235.0	237.3
47.5°	220.6	220.1	220.1	219.7	219.2	219.7	217.9	220.1	221.0	221.9	223.7
50°	207.9	207.5	207.0	206.6	206.6	207.0	206.6	206.6	208.4	209.3	211.1
52.5°	195.3	194.0	194.0	193.5	193.5	192.6	193.5	194.0	194.9	195.8	196.7
55°	181.8	181.8	180.4	180.4	179.5	179.5	180.0	179.5	181.3	182.2	182.2
57.5°	168.7	166.9	167.4	166.4	165.5	165.1	165.1	166.0	166.9	166.9	167.8
60°	154.7	152.9	152.5	150.7	151.6	150.2	150.7	150.7	152.5	151.6	152.5
62.5°	140.7	138.5	137.1	136.2	136.2	136.7	135.8	135.3	136.2	137.1	138.9
65°	125.9	124.5	123.1	121.8	121.8	121.3	122.2	120.9	120.4	120.9	121.8
67.5°	110.5	109.2	107.8	106.5	106.9	105.6	104.7	106.0	105.1	105.6	106.5
70°	95.6	94.7	92.0	91.1	90.7	91.1	90.7	89.8	91.1	90.7	91.1
72.5°	80.7	79.8	78.5	76.2	76.2	75.8	75.3	75.3	74.9	74.9	74.9
75°	66.3	64.5	63.2	62.7	61.8	61.3	60.9	60.0	60.4	60.9	60.0
77.5°	51.4	49.2	48.7	48.7	47.4	47.4	47.8	47.4	46.9	46.9	46.9
80°	37.9	36.1	36.1	35.2	34.3	34.3	34.3	34.3	33.8	33.4	33.8
82.5°	24.4	23.9	23.5	23.5	24.4	22.6	23.5	23.0	22.6	22.6	22.1
85°	13.5	14.0	13.5	14.0	13.1	13.5	13.5	13.5	13.1	13.5	12.6
87.5°	5.0	5.0	5.0	5.4	5.4	5.4	5.4	5.4	5.9	5.4	5.4
90°	15.3	14.8	14.2	13.6	14.2	12.5	10.8	9.1	7.4	6.8	6.3
92.5°	38.1	43.8	56.3	79.0	105.7	117.1	87.5	57.4	39.2	34.1	29.0
95°	108.5	138.6	204.6	273.3	337.0	300.0	206.8	122.2	73.9	62.8	51.7
97.5°	279.6	354.6	469.9	535.8	518.2	387.0	230.1	131.8	84.1	71.9	59.7
100°	557.4	623.9	669.9	650.0	538.1	363.7	214.2	130.1	90.3	79.2	68.2
102.5°	714.2	746.1	736.4	655.7	501.2	329.6	200.6	132.4	97.7	87.8	77.8
105°	806.3	795.5	738.7	619.9	456.8	302.9	195.5	136.9	106.3	97.4	88.6
107.5°	838.1	793.8	704.6	568.8	417.6	283.5	194.3	144.3	117.1	108.8	100.6
110°	827.3	755.7	651.2	521.1	385.3	273.3	197.2	154.0	128.4	120.4	112.5

TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	788.1	705.7	598.3	479.6	363.7	267.6	202.9	163.6	140.3	132.6	125.0
115°	735.3	651.7	552.9	447.8	349.5	267.1	209.1	174.4	152.9	145.2	137.5
117.5°	681.9	605.2	517.6	426.7	339.8	267.6	217.1	185.8	164.2	157.1	150.0
120°	635.8	567.6	490.9	410.8	333.5	269.9	226.2	196.6	176.1	169.0	161.9
122.5°	599.5	537.5	469.9	397.8	329.6	273.9	234.7	208.0	188.1	180.4	172.7
125°	568.2	513.7	451.7	387.0	326.2	277.9	243.8	218.8	198.9	191.2	183.5
127.5°	541.5	491.5	435.3	376.7	324.5	282.4	251.2	228.4	209.1	201.4	193.8
130°	517.1	471.1	419.9	368.8	322.7	286.9	258.5	236.9	218.2	210.6	202.9
132.5°	493.8	451.7	405.7	361.4	322.2	290.4	265.4	244.3	226.2	218.8	211.4
135°	470.5	433.5	393.2	355.1	321.6	293.8	271.0	251.7	234.1	226.4	218.8
137.5°	448.3	415.4	381.3	349.5	320.5	296.0	275.6	256.8	239.8	232.7	225.6
140°	427.3	400.0	371.0	344.3	319.9	298.3	279.0	261.9	245.5	238.4	231.3
142.5°	408.0	385.3	361.4	339.8	318.8	300.0	282.4	265.9	250.0	243.4	236.9
145°	390.9	372.7	354.0	335.8	317.6	300.6	284.7	269.3	254.6	248.0	241.5
147.5°	378.4	363.1	347.7	331.8	315.9	300.6	286.4	272.2	258.5	252.8	247.2
150°	365.9	354.0	340.9	327.9	313.7	300.6	286.9	275.0	261.9	256.8	251.7
152.5°	355.7	345.5	334.7	323.3	310.8	298.9	288.1	276.7	265.9	261.1	256.3
155°	346.0	337.5	328.4	318.8	307.4	297.7	288.1	279.0	269.3	265.4	261.4
157.5°	336.4	329.6	321.6	313.7	304.6	296.0	288.7	280.1	272.2	269.0	265.9
160°	327.9	322.2	315.9	308.5	301.2	294.9	288.7	281.8	275.0	272.2	269.3
162.5°	319.3	314.2	309.1	303.4	297.7	292.6	288.1	282.4	276.7	274.4	272.2
165°	310.8	306.8	303.4	298.9	294.3	290.4	286.9	283.0	278.4	276.4	274.4
167.5°	303.4	301.2	298.3	294.3	290.9	288.1	286.4	283.0	279.6	278.2	276.7
170°	297.2	294.9	293.2	290.4	287.5	285.8	284.7	282.4	279.6	279.0	278.4
172.5°	291.5	289.8	288.7	286.4	284.7	284.1	284.1	282.4	280.1	279.8	279.6
175°	286.4	285.2	284.7	283.5	282.4	282.4	283.0	281.8	280.7	280.4	280.1
177.5°	283.0	282.4	281.8	281.3	280.7	281.3	282.4	281.3	280.7	280.7	280.7
180°	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7	280.7

TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	465.5	465.5	465.5	465.5
2.5°	455.6	456.9	461.5	466.9
5°	446.6	450.2	456.5	465.1
7.5°	436.6	442.1	451.1	461.9
10°	425.4	433.0	444.3	457.8
12.5°	413.2	423.1	437.5	451.5
15°	405.5	415.4	428.5	443.9
17.5°	390.6	402.4	415.9	437.5
20°	375.3	388.4	406.0	427.6
22.5°	363.6	377.6	394.2	417.2
25°	349.6	364.0	382.1	406.0
27.5°	334.7	349.1	369.4	394.7
30°	323.4	337.4	356.8	383.9
32.5°	309.9	323.4	343.7	372.1
35°	294.6	309.9	329.3	358.2
37.5°	282.8	296.8	317.1	344.6
40°	270.2	282.4	302.2	329.3
42.5°	256.7	270.2	287.3	314.4
45°	244.0	254.0	271.6	297.3
47.5°	230.5	241.8	255.3	275.2
50°	216.1	225.5	240.4	254.0
52.5°	202.1	209.8	222.4	232.8
55°	187.2	194.9	204.3	210.7
57.5°	173.2	178.6	184.9	189.0
60°	156.1	161.5	165.5	169.6
62.5°	140.7	144.8	147.1	149.3
65°	124.9	127.2	128.6	130.4
67.5°	107.8	110.1	110.5	113.2
70°	92.0	92.5	93.4	94.7
72.5°	77.1	78.0	77.6	78.5
75°	61.8	62.7	61.8	62.7
77.5°	46.9	47.8	47.8	49.2
80°	33.8	34.3	34.7	34.7
82.5°	22.1	23.5	22.6	23.0
85°	12.6	13.1	13.1	13.5
87.5°	5.9	6.3	5.9	6.8
90°	5.1	3.4	2.3	1.1
92.5°	23.3	18.2	12.5	8.5
95°	36.9	27.3	21.0	19.3
97.5°	44.9	36.4	31.3	30.7
100°	54.5	46.6	42.6	42.0
102.5°	65.9	58.5	55.1	54.0
105°	77.8	71.0	67.6	65.9
107.5°	90.3	83.5	80.1	78.4
110°	102.8	96.6	93.8	92.1

TEST NUMBER: P1011618

CATALOG NUMBER: S123DIP-B340D585UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	115.3	109.1	106.3	104.6
115°	127.8	122.2	118.8	116.5
117.5°	139.2	134.1	131.3	128.4
120°	151.1	145.5	142.6	140.9
122.5°	162.5	156.3	153.4	151.7
125°	172.7	166.5	163.1	161.9
127.5°	181.8	175.6	171.6	169.9
130°	190.9	184.1	179.0	177.3
132.5°	199.4	190.9	185.2	183.0
135°	206.8	198.3	192.1	189.8
137.5°	213.6	204.6	198.3	196.0
140°	219.9	210.8	205.1	202.3
142.5°	225.6	217.6	211.4	209.1
145°	231.8	223.3	218.2	216.5
147.5°	237.5	230.1	225.0	223.9
150°	243.8	236.4	231.8	231.3
152.5°	249.4	243.2	238.7	238.7
155°	255.1	249.4	246.0	246.0
157.5°	260.2	255.1	252.3	251.7
160°	265.4	260.8	258.5	258.5
162.5°	268.8	265.4	263.7	263.7
165°	272.2	269.3	268.2	268.8
167.5°	275.0	272.7	272.2	272.7
170°	277.3	275.6	275.0	276.2
172.5°	279.0	277.9	277.9	278.4
175°	280.1	279.0	279.6	280.1
177.5°	280.7	280.1	280.7	281.3
180°	280.7	280.7	280.7	280.7

(END OF REPORT)