

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011356

Luminaire Tested: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011356
REPORT IS A COMBINATION OF REPORTS P989482 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D365UB40-4F0-XX-W2A-A1
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6127.0 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	83	83	83	80
1	105	101	97	93	100	96	93	90	88	86	83	81	79	77	74	73	71	71	71	71	68
2	96	88	82	77	91	85	79	74	78	74	70	72	68	65	66	63	61	61	61	61	58
3	88	78	71	65	84	75	68	63	69	64	59	64	59	56	59	55	52	52	52	52	49
4	81	69	61	55	77	67	59	54	62	56	51	57	52	48	53	49	45	45	45	45	43
5	74	62	54	48	71	60	52	46	56	49	44	52	46	42	48	43	40	40	40	40	37
6	69	56	48	42	65	54	46	41	50	44	39	47	41	37	43	39	35	35	35	35	33
7	64	51	43	37	61	49	41	36	46	39	34	43	37	33	40	35	31	31	31	31	29
8	59	46	38	33	56	45	37	32	42	35	31	39	34	29	37	32	28	28	28	28	26
9	55	43	35	29	53	41	34	29	39	32	28	36	31	27	34	29	25	25	25	25	23
10	52	39	32	27	49	38	31	26	36	29	25	33	28	24	31	27	23	23	23	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17400	17400	17400	17400
5°	17412	20048	17463	14963
10°	17301	24262	17319	13067
15°	17062	28772	17201	11762
20°	16857	33127	16892	10823
25°	16551	33962	16587	10333
30°	16332	28058	16332	10011
35°	16061	18765	15961	9728
40°	15738	13546	15543	9295
45°	15331	10730	14888	8754
50°	14341	9113	13832	8225
55°	13254	8007	12716	7633
60°	12154	6972	11506	7012
65°	10943	5970	10414	6184
70°	9686	4955	9041	5213
75°	8281	3737	7745	4024
80°	6547	2496	6037	2644
85°	4515	1146	3612	1042

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 28063 cd/sqm

TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.0	2.6
10°-20°	510.6	8.3
20°-30°	859.2	14.0
30°-40°	971.0	15.8
40°-50°	869.7	14.2
50°-60°	702.0	11.5
60°-70°	489.2	8.0
70°-80°	256.8	4.2
80°-90°	62.5	1.0
90°-100°	29.0	0.5
100°-110°	87.7	1.4
110°-120°	149.3	2.4
120°-130°	196.4	3.2
130°-140°	220.7	3.6
140°-150°	217.0	3.5
150°-160°	182.7	3.0
160°-170°	121.6	2.0
170°-180°	42.6	0.7
0°-30°	1528.8	25.0
0°-40°	2499.8	40.8
0°-60°	4071.5	66.5
0°-90°	4880.0	79.6
90°-120°	265.9	4.3
90°-150°	900.1	14.7
90°-180°	1247.0	20.4
0°-180°	6127.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1616	1616	1616	1616	1616	
5°	1615	1920	1620	1433	1615	153
15°	1541	2859	1554	1169	1541	436
25°	1410	3393	1413	1032	1410	650
35°	1244	1828	1236	948	1244	778
45°	1032	987	1002	805	1032	790
55°	732	670	702	639	732	655
65°	453	436	431	451	453	451
75°	218	224	204	241	218	233
85°	47	52	38	47	47	54
90°	0	11	0	11	0	5
95°	21	28	21	28	21	23
105°	80	84	80	84	80	85
115°	150	151	150	151	150	149
125°	220	217	220	217	220	196
135°	285	285	285	285	285	220
145°	346	346	346	346	346	216
155°	396	396	396	396	396	182
165°	432	430	432	430	432	122
175°	449	447	449	447	449	43
180°	450	450	450	450	450	

TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1621.2	1633.8	1640.0	1649.4	1658.8	1672.9	1677.6	1685.5	1682.3	1688.6	1691.7
5°	1615.0	1636.9	1655.7	1679.2	1701.1	1716.8	1732.5	1757.5	1776.3	1779.5	1793.6
7.5°	1604.0	1635.3	1668.2	1701.1	1743.4	1768.5	1796.7	1831.1	1859.3	1904.8	1922.0
10°	1589.9	1633.8	1680.8	1726.2	1784.2	1823.3	1857.8	1915.7	1973.7	2020.7	2064.5
12.5°	1568.0	1622.8	1683.9	1751.3	1826.4	1871.9	1918.9	1995.6	2083.3	2155.4	2202.4
15°	1541.4	1610.3	1688.6	1760.7	1843.7	1928.3	1978.4	2064.5	2189.9	2257.2	2377.8
17.5°	1519.4	1589.9	1668.2	1781.0	1893.8	1978.4	2014.4	2172.6	2258.8	2371.6	2507.8
20°	1485.0	1574.3	1674.5	1787.3	1933.0	1984.7	2058.3	2218.1	2324.6	2471.8	2639.4
22.5°	1448.9	1544.5	1665.1	1782.6	1945.5	2000.3	2100.6	2227.5	2396.6	2542.3	2727.1
25°	1409.8	1513.2	1635.3	1774.8	1934.5	2014.4	2108.4	2265.0	2448.3	2631.6	2802.3
27.5°	1370.6	1483.4	1610.3	1749.7	1904.8	1998.8	2092.7	2255.6	2490.6	2689.5	2907.3
30°	1333.0	1445.8	1572.7	1715.2	1878.1	1969.0	2058.3	2261.9	2523.5	2747.5	2966.8
32.5°	1292.3	1408.2	1541.4	1660.4	1824.9	1922.0	2022.3	2261.9	2543.9	2782.0	2982.5
35°	1243.7	1362.8	1477.1	1596.2	1759.1	1867.2	1980.0	2246.2	2562.7	2792.9	2916.7
37.5°	1196.7	1301.7	1400.4	1516.3	1687.0	1803.0	1933.0	2227.5	2553.3	2745.9	2780.4
40°	1143.5	1248.4	1328.3	1436.4	1616.5	1751.3	1882.8	2202.4	2512.5	2634.7	2534.5
42.5°	1091.8	1174.8	1243.7	1348.7	1544.5	1676.1	1818.6	2157.0	2432.7	2457.7	2232.2
45°	1032.3	1091.8	1152.9	1271.9	1466.2	1600.9	1759.1	2091.2	2304.2	2232.2	1947.1
47.5°	955.5	1008.8	1076.1	1185.8	1383.2	1522.6	1672.9	2006.6	2117.8	1967.4	1655.7
50°	881.9	927.3	990.0	1096.5	1295.4	1431.7	1591.5	1873.4	1928.3	1691.7	1427.0
52.5°	808.3	842.7	903.8	1010.3	1209.3	1340.9	1486.5	1737.2	1705.8	1452.1	1217.1
55°	731.5	761.3	819.2	924.2	1109.0	1234.3	1373.8	1569.6	1488.1	1246.9	1058.9
57.5°	656.3	687.7	747.2	834.9	1008.8	1131.0	1242.2	1395.7	1273.5	1080.8	914.8
60°	589.0	615.6	661.0	747.2	905.4	1004.1	1105.9	1210.8	1109.0	922.6	795.7
62.5°	518.5	543.5	585.8	664.2	800.4	888.2	969.6	1055.8	943.0	806.7	693.9
65°	452.7	473.1	512.2	584.3	695.5	767.5	833.3	892.9	802.0	676.7	592.1
67.5°	393.2	410.4	443.3	507.5	601.5	653.2	706.5	756.6	679.8	579.6	507.5
70°	328.9	343.0	372.8	419.8	495.0	548.2	587.4	625.0	556.1	476.2	427.6
72.5°	272.6	286.7	305.5	354.0	405.7	438.6	480.9	501.3	462.1	396.3	347.7
75°	217.7	228.7	245.9	277.3	325.8	347.7	374.4	390.0	354.0	310.2	280.4
77.5°	170.7	175.4	188.0	209.9	242.8	267.9	288.2	297.6	272.6	244.4	219.3
80°	120.6	126.9	136.3	155.1	180.1	188.0	200.5	211.5	195.8	170.7	155.1
82.5°	79.9	87.7	92.4	100.3	115.9	125.3	128.4	137.8	123.7	114.3	108.1
85°	47.0	50.1	51.7	56.4	64.2	68.9	73.6	75.2	72.1	70.5	64.2
87.5°	23.5	23.5	23.5	26.6	28.2	31.3	32.9	32.9	32.9	31.3	29.8
90°	0.4	1.2	2.0	2.7	3.5	3.9	4.4	5.4	6.5	7.5	8.5
92.5°	10.6	11.1	11.5	12.0	12.5	12.7	12.9	13.4	13.9	14.3	14.8
95°	20.9	21.4	22.0	22.5	23.0	23.3	23.6	24.3	24.9	25.6	26.2
97.5°	34.3	34.7	35.1	35.5	35.9	36.1	36.3	36.8	37.3	37.7	38.2
100°	48.1	48.6	49.0	49.5	50.0	50.2	50.4	50.8	51.2	51.6	52.0
102.5°	64.0	64.2	64.5	64.7	65.0	65.1	65.4	65.9	66.4	67.0	67.5
105°	79.5	79.7	79.9	80.0	80.2	80.3	80.6	81.3	82.0	82.7	83.4
107.5°	97.9	98.0	98.1	98.2	98.3	98.3	98.5	98.8	99.1	99.4	99.7
110°	114.9	115.1	115.2	115.4	115.5	115.6	115.7	115.8	116.0	116.1	116.3

TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	132.6	132.7	132.7	132.8	132.9	132.9	132.9	132.9	132.9	132.9	132.9
115°	150.3	150.5	150.7	151.0	151.2	151.3	151.2	151.1	150.9	150.8	150.6
117.5°	168.3	168.4	168.4	168.5	168.6	168.6	168.5	168.4	168.2	168.1	167.9
120°	184.9	185.4	185.8	186.3	186.8	187.0	186.8	186.4	186.1	185.7	185.3
122.5°	202.2	202.5	202.8	203.1	203.4	203.6	203.5	203.4	203.2	203.1	202.9
125°	219.9	220.1	220.4	220.6	220.9	221.0	220.9	220.8	220.6	220.5	220.3
127.5°	236.2	236.7	237.1	237.6	238.1	238.3	238.2	238.1	237.9	237.8	237.6
130°	252.4	253.0	253.7	254.3	255.0	255.3	255.2	254.9	254.7	254.4	254.2
132.5°	268.7	269.3	269.9	270.6	271.2	271.5	271.4	271.3	271.1	271.0	270.8
135°	285.3	285.8	286.2	286.7	287.2	287.4	287.4	287.3	287.2	287.2	287.1
137.5°	300.5	300.9	301.3	301.7	302.1	302.3	302.4	302.6	302.9	303.1	303.3
140°	316.4	316.8	317.2	317.6	318.0	318.2	318.2	318.3	318.4	318.4	318.5
142.5°	330.9	331.3	331.7	332.1	332.5	332.7	332.8	332.9	333.1	333.2	333.4
145°	346.1	346.3	346.4	346.6	346.7	346.8	346.9	347.2	347.4	347.7	347.9
147.5°	359.2	359.5	359.8	360.1	360.4	360.6	360.7	361.0	361.2	361.5	361.7
150°	373.0	373.2	373.3	373.5	373.6	373.7	373.8	373.9	374.1	374.2	374.4
152.5°	384.3	384.5	384.8	385.0	385.3	385.4	385.4	385.5	385.6	385.6	385.7
155°	396.3	396.3	396.3	396.3	396.3	396.3	396.3	396.4	396.5	396.6	396.7
157.5°	406.6	406.5	406.4	406.3	406.2	406.2	406.2	406.3	406.4	406.5	406.6
160°	416.1	415.9	415.8	415.6	415.5	415.4	415.4	415.4	415.4	415.4	415.4
162.5°	424.6	424.4	424.1	423.9	423.6	423.5	423.5	423.6	423.7	423.8	423.9
165°	431.7	431.5	431.2	431.0	430.7	430.6	430.6	430.6	430.6	430.6	430.6
167.5°	437.7	437.4	437.1	436.8	436.5	436.3	436.3	436.4	436.5	436.5	436.6
170°	442.6	442.3	442.0	441.7	441.4	441.2	441.2	441.2	441.2	441.2	441.2
172.5°	446.5	446.2	445.9	445.6	445.3	445.1	445.1	445.1	445.1	445.1	445.1
175°	449.0	448.7	448.4	448.1	447.8	447.6	447.6	447.6	447.6	447.6	447.6
177.5°	450.4	450.1	449.8	449.5	449.2	449.0	449.0	449.0	449.0	449.0	449.0
180°	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1

TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1702.7	1705.8	1716.8	1724.6	1740.3	1738.7	1738.7	1737.2	1732.5	1740.3	1745.0
5°	1821.7	1848.4	1851.5	1886.0	1887.5	1901.6	1911.0	1903.2	1922.0	1920.4	1906.3
7.5°	1969.0	2005.0	2022.3	2055.1	2092.7	2083.3	2119.4	2125.6	2122.5	2138.2	2149.1
10°	2130.3	2193.0	2236.9	2297.9	2313.6	2323.0	2346.5	2366.9	2407.6	2376.3	2396.6
12.5°	2315.2	2360.6	2418.6	2515.7	2564.2	2595.6	2606.5	2620.6	2648.8	2631.6	2633.2
15°	2470.2	2531.3	2630.0	2750.6	2764.7	2803.9	2794.5	2879.1	2919.8	2858.7	2893.2
17.5°	2631.6	2713.0	2830.5	2935.5	2995.0	3021.6	3046.7	3128.1	3125.0	3115.6	3123.4
20°	2735.0	2868.1	3013.8	3153.2	3170.4	3190.8	3258.2	3292.6	3286.4	3313.0	3330.2
22.5°	2880.7	3021.6	3176.7	3269.1	3308.3	3331.8	3385.0	3407.0	3416.4	3422.6	3411.7
25°	3002.8	3153.2	3267.6	3349.0	3372.5	3385.0	3402.3	3408.5	3403.8	3392.9	3402.3
27.5°	3085.9	3206.5	3284.8	3322.4	3309.8	3289.5	3256.6	3234.7	3186.1	3162.6	3190.8
30°	3120.3	3173.6	3197.1	3134.4	3071.8	3021.6	2959.0	2843.1	2752.2	2778.8	2742.8
32.5°	3065.5	3031.0	2918.2	2756.9	2708.3	2626.9	2449.9	2313.6	2318.3	2246.2	2276.0
35°	2904.1	2747.5	2534.5	2290.1	2225.9	2182.0	1987.8	1958.0	1895.4	1828.0	1846.8
37.5°	2619.1	2390.4	2131.9	1951.8	1856.2	1760.7	1651.0	1585.2	1547.6	1519.4	1541.4
40°	2271.3	1992.5	1779.5	1618.1	1536.7	1475.6	1400.4	1334.6	1292.3	1287.6	1295.4
42.5°	1929.8	1694.9	1499.1	1345.6	1318.9	1246.9	1198.3	1146.6	1134.1	1113.7	1124.7
45°	1633.8	1442.7	1281.3	1156.0	1124.7	1105.9	1046.4	1013.5	999.4	986.8	1005.6
47.5°	1419.2	1218.7	1101.2	1026.0	994.7	963.3	930.5	908.5	897.6	899.1	897.6
50°	1212.4	1065.2	961.8	903.8	885.0	863.1	836.5	822.4	817.7	803.6	814.5
52.5°	1043.2	936.7	864.7	809.8	795.7	780.1	758.1	750.3	739.4	736.2	736.2
55°	907.0	823.9	766.0	730.0	712.7	700.2	687.7	678.3	670.4	670.4	670.4
57.5°	800.4	728.4	686.1	654.8	648.5	636.0	621.9	621.9	610.9	609.3	614.0
60°	709.6	645.4	612.5	585.8	576.4	573.3	559.2	559.2	556.1	548.2	554.5
62.5°	617.2	570.2	542.0	521.6	512.2	512.2	501.3	493.4	493.4	495.0	491.9
65°	532.6	498.1	473.1	457.4	452.7	446.4	444.9	438.6	433.9	435.5	433.9
67.5°	457.4	430.8	413.5	401.0	393.2	390.0	385.3	385.3	382.2	383.8	375.9
70°	390.0	363.4	349.3	336.8	333.6	333.6	327.4	328.9	325.8	330.5	327.4
72.5°	321.1	300.8	289.8	285.1	282.0	280.4	277.3	274.1	272.6	275.7	274.1
75°	260.0	242.8	235.0	231.8	228.7	228.7	227.1	225.6	224.0	224.0	224.0
77.5°	202.1	191.1	181.7	184.8	180.1	181.7	177.0	177.0	178.6	177.0	177.0
80°	148.8	141.0	141.0	137.8	131.6	134.7	134.7	130.0	128.4	131.6	126.9
82.5°	98.7	97.1	94.0	92.4	89.3	90.9	89.3	87.7	86.2	89.3	86.2
85°	58.0	58.0	56.4	53.3	56.4	54.8	53.3	53.3	51.7	51.7	51.7
87.5°	29.8	26.6	26.6	25.1	26.6	23.5	25.1	23.5	21.9	23.5	21.9
90°	8.8	9.1	9.4	9.7	9.9	10.0	10.1	10.3	10.4	10.6	10.4
92.5°	15.0	15.3	15.5	15.8	15.9	15.8	15.7	15.5	15.4	15.2	15.4
95°	26.5	26.8	27.1	27.4	27.6	27.6	27.6	27.6	27.6	27.6	27.6
97.5°	38.6	39.0	39.4	39.8	40.0	40.0	39.9	39.8	39.7	39.6	39.7
100°	52.2	52.4	52.7	52.9	53.0	53.1	53.2	53.4	53.5	53.7	53.5
102.5°	67.7	68.0	68.2	68.5	68.6	68.6	68.5	68.4	68.3	68.2	68.3
105°	83.4	83.4	83.4	83.4	83.4	83.5	83.6	83.8	83.9	84.1	83.9
107.5°	99.9	100.2	100.4	100.7	100.8	100.8	100.7	100.6	100.5	100.4	100.5
110°	116.6	116.9	117.2	117.5	117.7	117.6	117.5	117.3	117.2	117.0	117.2

TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	133.3	133.7	134.1	134.5	134.7	134.7	134.7	134.7	134.7	134.7	134.7
115°	150.7	150.8	150.9	151.0	151.0	151.0	150.9	150.8	150.7	150.6	150.7
117.5°	167.9	167.9	167.9	167.9	167.9	167.8	167.6	167.3	167.1	166.9	167.1
120°	185.2	185.1	185.0	184.9	184.9	184.8	184.7	184.5	184.4	184.2	184.4
122.5°	202.7	202.5	202.2	202.0	201.9	201.8	201.5	201.3	201.0	200.8	201.0
125°	220.0	219.6	219.3	219.0	218.8	218.6	218.3	218.0	217.7	217.4	217.7
127.5°	237.1	236.7	236.2	235.7	235.5	235.3	235.0	234.7	234.3	234.0	234.3
130°	253.9	253.6	253.3	253.0	252.8	252.5	252.0	251.4	250.9	250.3	250.9
132.5°	270.4	270.0	269.6	269.2	269.0	268.8	268.4	268.1	267.7	267.3	267.7
135°	286.8	286.5	286.2	285.9	285.7	285.6	285.5	285.3	285.2	285.0	285.2
137.5°	302.9	302.5	302.2	301.8	301.6	301.5	301.2	301.0	300.7	300.5	300.7
140°	318.4	318.4	318.3	318.2	318.2	317.9	317.4	316.8	316.3	315.7	316.3
142.5°	333.3	333.2	333.1	333.0	333.0	332.8	332.4	332.1	331.7	331.3	331.7
145°	347.8	347.7	347.6	347.5	347.5	347.3	347.0	346.7	346.4	346.1	346.4
147.5°	361.7	361.7	361.7	361.7	361.7	361.5	361.0	360.5	360.1	359.6	360.1
150°	374.4	374.4	374.4	374.4	374.4	374.2	373.7	373.2	372.8	372.3	372.8
152.5°	385.9	386.0	386.2	386.3	386.4	386.2	385.8	385.5	385.1	384.7	385.1
155°	397.0	397.3	397.6	397.9	398.1	397.8	397.3	396.7	396.2	395.6	396.2
157.5°	406.9	407.2	407.5	407.8	408.0	407.8	407.3	406.8	406.4	405.9	406.4
160°	415.8	416.2	416.6	417.0	417.2	417.0	416.7	416.4	416.1	415.8	416.1
162.5°	424.3	424.7	425.1	425.5	425.7	425.4	424.9	424.3	423.8	423.2	423.8
165°	431.1	431.5	432.0	432.5	432.7	432.4	431.9	431.4	430.8	430.3	430.8
167.5°	437.1	437.6	438.1	438.6	438.8	438.6	438.1	437.6	437.1	436.6	437.1
170°	441.8	442.3	442.9	443.4	443.7	443.4	442.9	442.3	441.8	441.2	441.8
172.5°	445.6	446.0	446.5	447.0	447.2	446.9	446.4	445.9	445.3	444.8	445.3
175°	448.1	448.5	449.0	449.5	449.7	449.4	448.9	448.3	447.8	447.2	447.8
177.5°	449.5	449.9	450.4	450.9	451.1	450.8	450.3	449.8	449.2	448.7	449.2
180°	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1

TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1732.5	1737.2	1724.6	1721.5	1721.5	1727.8	1723.1	1680.8	1688.6	1679.2	1676.1
5°	1923.6	1914.2	1901.6	1895.4	1887.5	1865.6	1864.0	1815.5	1806.1	1774.8	1760.7
7.5°	2133.5	2125.6	2088.0	2083.3	2080.2	2059.8	2008.2	1956.5	1918.9	1882.8	1848.4
10°	2373.1	2349.6	2332.4	2297.9	2280.7	2252.5	2185.2	2136.6	2072.4	2017.6	1945.5
12.5°	2661.4	2634.7	2576.8	2551.7	2529.8	2451.5	2384.1	2329.3	2204.0	2166.4	2077.1
15°	2872.8	2816.4	2810.2	2755.3	2752.2	2666.1	2537.6	2478.1	2381.0	2243.1	2150.7
17.5°	3101.5	3051.4	3012.2	2946.4	2937.0	2855.6	2761.6	2615.9	2509.4	2377.8	2260.3
20°	3269.1	3242.5	3175.1	3148.5	3093.7	3024.8	2927.6	2747.5	2617.5	2485.9	2341.8
22.5°	3402.3	3375.6	3322.4	3286.4	3255.0	3165.7	3049.8	2896.3	2717.7	2545.4	2396.6
25°	3400.7	3392.9	3370.9	3353.7	3330.2	3264.4	3167.3	3020.1	2821.1	2631.6	2424.8
27.5°	3208.0	3230.0	3267.6	3286.4	3281.7	3272.3	3217.4	3093.7	2915.1	2689.5	2457.7
30°	2807.0	2886.9	2957.4	3051.4	3079.6	3148.5	3179.8	3109.3	2966.8	2756.9	2500.0
32.5°	2327.7	2443.6	2597.1	2648.8	2738.1	2871.3	3020.1	3046.7	2957.4	2796.1	2526.6
35°	1909.5	2005.0	2124.1	2205.5	2285.4	2501.6	2689.5	2852.5	2882.2	2775.7	2520.4
37.5°	1580.5	1647.9	1752.8	1821.7	1895.4	2080.2	2343.4	2554.8	2703.6	2706.8	2503.1
40°	1342.4	1372.2	1463.0	1513.2	1583.7	1743.4	1978.4	2254.1	2471.8	2572.1	2457.7
42.5°	1137.2	1176.4	1251.6	1289.2	1334.6	1474.0	1629.1	1890.7	2160.1	2374.7	2373.1
45°	1015.0	1043.2	1077.7	1109.0	1160.7	1243.7	1420.7	1616.5	1875.0	2117.8	2213.4
47.5°	907.0	933.6	968.0	977.4	1011.9	1090.2	1198.3	1369.1	1610.3	1851.5	2031.6
50°	816.1	838.0	861.5	878.8	894.4	958.7	1040.1	1184.2	1376.9	1610.3	1834.3
52.5°	745.6	761.3	781.6	791.0	805.1	852.1	914.8	1021.3	1179.5	1392.5	1610.3
55°	679.8	690.8	703.3	719.0	725.3	759.7	808.3	899.1	1016.6	1207.7	1414.5
57.5°	618.7	623.4	631.3	640.7	648.5	678.3	720.6	781.6	885.0	1032.3	1228.1
60°	549.8	562.3	567.0	576.4	581.1	604.6	637.5	689.2	769.1	896.0	1043.2
62.5°	491.9	499.7	507.5	512.2	523.2	531.0	557.6	604.6	670.4	764.4	897.6
65°	440.2	443.3	448.0	452.7	455.8	465.2	490.3	521.6	571.7	654.8	758.1
67.5°	380.6	383.8	390.0	391.6	394.7	407.3	421.4	448.0	490.3	552.9	637.5
70°	322.7	327.4	330.5	333.6	338.3	343.0	358.7	380.6	413.5	457.4	523.2
72.5°	272.6	277.3	277.3	280.4	278.8	285.1	300.8	316.4	338.3	374.4	432.3
75°	222.4	222.4	225.6	227.1	228.7	235.0	241.2	253.8	271.0	299.2	335.2
77.5°	175.4	173.9	177.0	177.0	177.0	181.7	188.0	194.2	205.2	225.6	253.8
80°	128.4	128.4	131.6	133.1	130.0	131.6	134.7	141.0	148.8	162.9	178.6
82.5°	84.6	90.9	89.3	90.9	89.3	92.4	94.0	95.6	98.7	105.0	115.9
85°	51.7	51.7	51.7	53.3	51.7	53.3	53.3	53.3	54.8	58.0	62.7
87.5°	21.9	21.9	21.9	23.5	21.9	21.9	23.5	21.9	23.5	23.5	25.1
90°	10.3	10.1	10.0	9.9	9.7	9.4	9.1	8.8	8.5	7.5	6.5
92.5°	15.5	15.7	15.8	15.9	15.8	15.5	15.3	15.0	14.8	14.3	13.9
95°	27.6	27.6	27.6	27.6	27.4	27.1	26.8	26.5	26.2	25.6	24.9
97.5°	39.8	39.9	40.0	40.0	39.8	39.4	39.0	38.6	38.2	37.7	37.3
100°	53.4	53.2	53.1	53.0	52.9	52.7	52.4	52.2	52.0	51.6	51.2
102.5°	68.4	68.5	68.6	68.6	68.5	68.2	68.0	67.7	67.5	67.0	66.4
105°	83.8	83.6	83.5	83.4	83.4	83.4	83.4	83.4	83.4	82.7	82.0
107.5°	100.6	100.7	100.8	100.8	100.7	100.4	100.2	99.9	99.7	99.4	99.1
110°	117.3	117.5	117.6	117.7	117.5	117.2	116.9	116.6	116.3	116.1	116.0

TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	134.7	134.7	134.7	134.7	134.5	134.1	133.7	133.3	132.9	132.9	132.9
115°	150.8	150.9	151.0	151.0	151.0	150.9	150.8	150.7	150.6	150.8	150.9
117.5°	167.3	167.6	167.8	167.9	167.9	167.9	167.9	167.9	167.9	168.1	168.2
120°	184.5	184.7	184.8	184.9	184.9	185.0	185.1	185.2	185.3	185.7	186.1
122.5°	201.3	201.5	201.8	201.9	202.0	202.2	202.5	202.7	202.9	203.1	203.2
125°	218.0	218.3	218.6	218.8	219.0	219.3	219.6	220.0	220.3	220.5	220.6
127.5°	234.7	235.0	235.3	235.5	235.7	236.2	236.7	237.1	237.6	237.8	237.9
130°	251.4	252.0	252.5	252.8	253.0	253.3	253.6	253.9	254.2	254.4	254.7
132.5°	268.1	268.4	268.8	269.0	269.2	269.6	270.0	270.4	270.8	271.0	271.1
135°	285.3	285.5	285.6	285.7	285.9	286.2	286.5	286.8	287.1	287.2	287.2
137.5°	301.0	301.2	301.5	301.6	301.8	302.2	302.5	302.9	303.3	303.1	302.9
140°	316.8	317.4	317.9	318.2	318.2	318.3	318.4	318.4	318.5	318.4	318.4
142.5°	332.1	332.4	332.8	333.0	333.0	333.1	333.2	333.3	333.4	333.2	333.1
145°	346.7	347.0	347.3	347.5	347.5	347.6	347.7	347.8	347.9	347.7	347.4
147.5°	360.5	361.0	361.5	361.7	361.7	361.7	361.7	361.7	361.7	361.5	361.2
150°	373.2	373.7	374.2	374.4	374.4	374.4	374.4	374.4	374.4	374.2	374.1
152.5°	385.5	385.8	386.2	386.4	386.3	386.2	386.0	385.9	385.7	385.6	385.6
155°	396.7	397.3	397.8	398.1	397.9	397.6	397.3	397.0	396.7	396.6	396.5
157.5°	406.8	407.3	407.8	408.0	407.8	407.5	407.2	406.9	406.6	406.5	406.4
160°	416.4	416.7	417.0	417.2	417.0	416.6	416.2	415.8	415.4	415.4	415.4
162.5°	424.3	424.9	425.4	425.7	425.5	425.1	424.7	424.3	423.9	423.8	423.7
165°	431.4	431.9	432.4	432.7	432.5	432.0	431.5	431.1	430.6	430.6	430.6
167.5°	437.6	438.1	438.6	438.8	438.6	438.1	437.6	437.1	436.6	436.5	436.5
170°	442.3	442.9	443.4	443.7	443.4	442.9	442.3	441.8	441.2	441.2	441.2
172.5°	445.9	446.4	446.9	447.2	447.0	446.5	446.0	445.6	445.1	445.1	445.1
175°	448.3	448.9	449.4	449.7	449.5	449.0	448.5	448.1	447.6	447.6	447.6
177.5°	449.8	450.3	450.8	451.1	450.9	450.4	449.9	449.5	449.0	449.0	449.0
180°	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1

TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1660.4	1655.7	1655.7	1652.6	1643.2	1625.9	1624.4	1627.5	1618.1	1608.7	1594.6
5°	1741.9	1712.1	1702.7	1693.3	1674.5	1643.2	1630.6	1619.7	1602.4	1582.1	1560.2
7.5°	1810.8	1768.5	1756.0	1738.7	1701.1	1657.3	1629.1	1605.6	1582.1	1553.9	1527.3
10°	1896.9	1835.8	1806.1	1781.0	1729.3	1668.2	1625.9	1591.5	1553.9	1519.4	1485.0
12.5°	1994.1	1895.4	1886.0	1824.9	1765.4	1674.5	1622.8	1572.7	1522.6	1480.3	1444.2
15°	2075.5	1967.4	1928.3	1887.5	1773.2	1660.4	1610.3	1553.9	1495.9	1450.5	1397.2
17.5°	2127.2	2037.9	1954.9	1900.1	1781.0	1680.8	1583.7	1519.4	1458.3	1395.7	1351.8
20°	2189.9	2059.8	1987.8	1914.2	1796.7	1665.1	1568.0	1488.1	1412.9	1356.5	1303.3
22.5°	2252.5	2077.1	2017.6	1937.7	1799.8	1649.4	1539.8	1459.9	1373.8	1317.4	1259.4
25°	2246.2	2102.1	2003.5	1936.1	1768.5	1635.3	1506.9	1412.9	1333.0	1261.0	1203.0
27.5°	2250.9	2073.9	1973.7	1895.4	1746.6	1615.0	1472.4	1373.8	1290.7	1215.5	1154.5
30°	2252.5	2031.6	1943.9	1849.9	1705.8	1566.4	1433.3	1333.0	1245.3	1163.9	1109.0
32.5°	2247.8	1997.2	1887.5	1803.0	1641.6	1519.4	1387.8	1281.3	1192.0	1116.9	1065.2
35°	2236.9	1956.5	1829.6	1723.1	1575.8	1452.1	1345.6	1235.9	1140.4	1071.4	1011.9
37.5°	2207.1	1912.6	1768.5	1663.5	1499.1	1373.8	1279.8	1188.9	1096.5	1015.0	964.9
40°	2185.2	1853.1	1707.4	1593.1	1416.0	1293.9	1215.5	1129.4	1038.5	964.9	916.4
42.5°	2135.0	1796.7	1644.7	1508.5	1334.6	1209.3	1135.7	1066.7	988.4	916.4	872.5
45°	2053.6	1735.6	1568.0	1430.1	1245.3	1126.3	1058.9	1002.5	933.6	864.7	820.8
47.5°	1939.2	1647.9	1486.5	1348.7	1157.6	1037.0	969.6	927.3	872.5	814.5	776.9
50°	1815.5	1552.3	1403.5	1267.2	1073.0	955.5	889.7	850.6	814.5	761.3	725.3
52.5°	1654.1	1450.5	1308.0	1177.9	982.1	869.4	811.4	783.2	745.6	708.0	676.7
55°	1497.5	1318.9	1201.4	1077.7	892.9	787.9	731.5	701.8	679.8	648.5	623.4
57.5°	1315.8	1196.7	1088.7	975.9	809.8	714.3	661.0	625.0	610.9	596.8	573.3
60°	1148.2	1057.3	969.6	875.6	723.7	637.5	585.8	557.6	543.5	534.1	518.5
62.5°	994.7	924.2	849.0	773.8	636.0	557.6	518.5	490.3	477.8	476.2	462.1
65°	847.4	797.3	736.2	662.6	554.5	485.6	448.0	430.8	416.7	416.7	405.7
67.5°	700.2	665.7	617.2	565.5	480.9	416.7	382.2	366.5	358.7	358.7	350.9
70°	582.7	559.2	515.4	469.9	396.3	347.7	321.1	307.0	302.3	303.9	297.6
72.5°	473.1	448.0	412.0	379.1	324.2	288.2	269.4	253.8	245.9	247.5	245.9
75°	366.5	354.0	322.7	297.6	253.8	228.7	211.5	203.6	197.4	198.9	195.8
77.5°	275.7	256.9	239.7	222.4	195.8	175.4	161.3	153.5	148.8	148.8	148.8
80°	188.0	184.8	170.7	161.3	139.4	123.7	112.8	111.2	106.5	106.5	106.5
82.5°	122.2	114.3	106.5	100.3	87.7	78.3	73.6	70.5	68.9	67.4	70.5
85°	67.4	62.7	59.5	53.3	48.6	43.9	39.2	37.6	36.0	37.6	36.0
87.5°	26.6	21.9	21.9	20.4	18.8	17.2	17.2	14.1	14.1	12.5	12.5
90°	5.4	4.4	3.9	3.5	2.7	2.0	1.2	0.4	1.2	2.0	2.7
92.5°	13.4	12.9	12.7	12.5	12.0	11.5	11.1	10.6	11.1	11.5	12.0
95°	24.3	23.6	23.3	23.0	22.5	22.0	21.4	20.9	21.4	22.0	22.5
97.5°	36.8	36.3	36.1	35.9	35.5	35.1	34.7	34.3	34.7	35.1	35.5
100°	50.8	50.4	50.2	50.0	49.5	49.0	48.6	48.1	48.6	49.0	49.5
102.5°	65.9	65.4	65.1	65.0	64.7	64.5	64.2	64.0	64.2	64.5	64.7
105°	81.3	80.6	80.3	80.2	80.0	79.9	79.7	79.5	79.7	79.9	80.0
107.5°	98.8	98.5	98.3	98.3	98.2	98.1	98.0	97.9	98.0	98.1	98.2
110°	115.8	115.7	115.6	115.5	115.4	115.2	115.1	114.9	115.1	115.2	115.4

TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	132.9	132.9	132.9	132.9	132.8	132.7	132.7	132.6	132.7	132.7	132.8
115°	151.1	151.2	151.3	151.2	151.0	150.7	150.5	150.3	150.5	150.7	151.0
117.5°	168.4	168.5	168.6	168.6	168.5	168.4	168.4	168.3	168.4	168.4	168.5
120°	186.4	186.8	187.0	186.8	186.3	185.8	185.4	184.9	185.4	185.8	186.3
122.5°	203.4	203.5	203.6	203.4	203.1	202.8	202.5	202.2	202.5	202.8	203.1
125°	220.8	220.9	221.0	220.9	220.6	220.4	220.1	219.9	220.1	220.4	220.6
127.5°	238.1	238.2	238.3	238.1	237.6	237.1	236.7	236.2	236.7	237.1	237.6
130°	254.9	255.2	255.3	255.0	254.3	253.7	253.0	252.4	253.0	253.7	254.3
132.5°	271.3	271.4	271.5	271.2	270.6	269.9	269.3	268.7	269.3	269.9	270.6
135°	287.3	287.4	287.4	287.2	286.7	286.2	285.8	285.3	285.8	286.2	286.7
137.5°	302.6	302.4	302.3	302.1	301.7	301.3	300.9	300.5	300.9	301.3	301.7
140°	318.3	318.2	318.2	318.0	317.6	317.2	316.8	316.4	316.8	317.2	317.6
142.5°	332.9	332.8	332.7	332.5	332.1	331.7	331.3	330.9	331.3	331.7	332.1
145°	347.2	346.9	346.8	346.7	346.6	346.4	346.3	346.1	346.3	346.4	346.6
147.5°	361.0	360.7	360.6	360.4	360.1	359.8	359.5	359.2	359.5	359.8	360.1
150°	373.9	373.8	373.7	373.6	373.5	373.3	373.2	373.0	373.2	373.3	373.5
152.5°	385.5	385.4	385.4	385.3	385.0	384.8	384.5	384.3	384.5	384.8	385.0
155°	396.4	396.3	396.3	396.3	396.3	396.3	396.3	396.3	396.3	396.3	396.3
157.5°	406.3	406.2	406.2	406.2	406.3	406.4	406.5	406.6	406.5	406.4	406.3
160°	415.4	415.4	415.4	415.5	415.6	415.8	415.9	416.1	415.9	415.8	415.6
162.5°	423.6	423.5	423.5	423.6	423.9	424.1	424.4	424.6	424.4	424.1	423.9
165°	430.6	430.6	430.6	430.7	431.0	431.2	431.5	431.7	431.5	431.2	431.0
167.5°	436.4	436.3	436.3	436.5	436.8	437.1	437.4	437.7	437.4	437.1	436.8
170°	441.2	441.2	441.2	441.4	441.7	442.0	442.3	442.6	442.3	442.0	441.7
172.5°	445.1	445.1	445.1	445.3	445.6	445.9	446.2	446.5	446.2	445.9	445.6
175°	447.6	447.6	447.6	447.8	448.1	448.4	448.7	449.0	448.7	448.4	448.1
177.5°	449.0	449.0	449.0	449.2	449.5	449.8	450.1	450.4	450.1	449.8	449.5
180°	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1

TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1591.5	1589.9	1593.1	1583.7	1568.0	1560.2	1538.2	1533.5	1532.0	1533.5	1535.1
5°	1547.6	1546.1	1541.4	1525.7	1506.9	1492.8	1466.2	1464.6	1455.2	1445.8	1450.5
7.5°	1505.3	1499.1	1489.7	1469.3	1444.2	1428.6	1406.6	1391.0	1378.5	1370.6	1364.4
10°	1463.0	1453.6	1444.2	1417.6	1386.3	1362.8	1336.2	1323.6	1309.5	1303.3	1297.0
12.5°	1408.2	1398.8	1381.6	1350.3	1331.5	1301.7	1275.1	1262.5	1254.7	1242.2	1234.3
15°	1364.4	1345.6	1336.2	1303.3	1264.1	1261.0	1212.4	1209.3	1193.6	1193.6	1181.1
17.5°	1314.2	1300.1	1282.9	1250.0	1221.8	1193.6	1168.6	1159.2	1145.1	1141.9	1135.7
20°	1265.7	1246.9	1240.6	1207.7	1177.9	1143.5	1116.9	1107.5	1101.2	1094.9	1099.6
22.5°	1215.5	1199.9	1184.2	1154.5	1132.5	1098.1	1082.4	1073.0	1063.6	1060.5	1062.0
25°	1167.0	1152.9	1137.2	1107.5	1084.0	1055.8	1041.7	1037.0	1032.3	1032.3	1030.7
27.5°	1120.0	1105.9	1091.8	1065.2	1041.7	1021.3	1010.3	1005.6	1000.9	1004.1	1007.2
30°	1071.4	1058.9	1046.4	1022.9	1004.1	985.3	979.0	975.9	974.3	982.1	982.1
32.5°	1027.6	1016.6	1007.2	985.3	966.5	950.8	946.1	947.7	949.3	954.0	957.1
35°	982.1	974.3	964.9	946.1	930.5	916.4	917.9	917.9	921.1	928.9	935.2
37.5°	941.4	930.5	922.6	907.0	894.4	881.9	886.6	891.3	894.4	903.8	907.0
40°	892.9	888.2	881.9	866.2	855.3	853.7	855.3	858.4	864.7	869.4	874.1
42.5°	853.7	847.4	839.6	827.1	817.7	819.2	820.8	823.9	827.1	834.9	839.6
45°	809.8	805.1	798.9	787.9	780.1	781.6	783.2	783.2	786.3	795.7	798.9
47.5°	761.3	762.8	755.0	744.1	739.4	739.4	739.4	742.5	750.3	753.4	755.0
50°	714.3	711.2	709.6	698.6	695.5	693.9	695.5	697.1	708.0	706.5	711.2
52.5°	664.2	664.2	662.6	656.3	651.6	651.6	648.5	656.3	659.5	662.6	667.3
55°	615.6	610.9	609.3	606.2	599.9	598.4	601.5	610.9	614.0	617.2	621.9
57.5°	562.3	562.3	559.2	554.5	554.5	554.5	554.5	560.8	565.5	568.6	578.0
60°	513.8	507.5	502.8	502.8	502.8	501.3	510.7	510.7	520.1	521.6	524.8
62.5°	455.8	452.7	449.6	451.1	449.6	452.7	455.8	462.1	463.7	468.4	473.1
65°	401.0	401.0	397.9	407.3	401.0	401.0	408.8	408.8	412.0	416.7	422.9
67.5°	347.7	349.3	346.2	346.2	349.3	350.9	352.4	358.7	360.3	366.5	374.4
70°	292.9	296.1	297.6	294.5	297.6	300.8	303.9	305.5	311.7	314.9	319.6
72.5°	244.4	247.5	242.8	244.4	245.9	249.1	250.6	253.8	256.9	266.3	269.4
75°	195.8	194.2	192.7	198.9	195.8	202.1	203.6	203.6	206.8	214.6	217.7
77.5°	150.4	150.4	151.9	148.8	153.5	151.9	153.5	158.2	162.9	162.9	175.4
80°	105.0	108.1	108.1	108.1	109.6	111.2	108.1	115.9	117.5	117.5	122.2
82.5°	67.4	68.9	67.4	70.5	70.5	73.6	72.1	73.6	76.8	79.9	81.5
85°	36.0	36.0	39.2	39.2	37.6	39.2	37.6	39.2	42.3	42.3	43.9
87.5°	12.5	12.5	12.5	12.5	14.1	12.5	14.1	14.1	12.5	12.5	17.2
90°	3.5	3.9	4.4	5.4	6.5	7.5	8.5	8.8	9.1	9.4	9.7
92.5°	12.5	12.7	12.9	13.4	13.9	14.3	14.8	15.0	15.3	15.5	15.8
95°	23.0	23.3	23.6	24.3	24.9	25.6	26.2	26.5	26.8	27.1	27.4
97.5°	35.9	36.1	36.3	36.8	37.3	37.7	38.2	38.6	39.0	39.4	39.8
100°	50.0	50.2	50.4	50.8	51.2	51.6	52.0	52.2	52.4	52.7	52.9
102.5°	65.0	65.1	65.4	65.9	66.4	67.0	67.5	67.7	68.0	68.2	68.5
105°	80.2	80.3	80.6	81.3	82.0	82.7	83.4	83.4	83.4	83.4	83.4
107.5°	98.3	98.3	98.5	98.8	99.1	99.4	99.7	99.9	100.2	100.4	100.7
110°	115.5	115.6	115.7	115.8	116.0	116.1	116.3	116.6	116.9	117.2	117.5

TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	132.9	132.9	132.9	132.9	132.9	132.9	132.9	133.3	133.7	134.1	134.5
115°	151.2	151.3	151.2	151.1	150.9	150.8	150.6	150.7	150.8	150.9	151.0
117.5°	168.6	168.6	168.5	168.4	168.2	168.1	167.9	167.9	167.9	167.9	167.9
120°	186.8	187.0	186.8	186.4	186.1	185.7	185.3	185.2	185.1	185.0	184.9
122.5°	203.4	203.6	203.5	203.4	203.2	203.1	202.9	202.7	202.5	202.2	202.0
125°	220.9	221.0	220.9	220.8	220.6	220.5	220.3	220.0	219.6	219.3	219.0
127.5°	238.1	238.3	238.2	238.1	237.9	237.8	237.6	237.1	236.7	236.2	235.7
130°	255.0	255.3	255.2	254.9	254.7	254.4	254.2	253.9	253.6	253.3	253.0
132.5°	271.2	271.5	271.4	271.3	271.1	271.0	270.8	270.4	270.0	269.6	269.2
135°	287.2	287.4	287.4	287.3	287.2	287.2	287.1	286.8	286.5	286.2	285.9
137.5°	302.1	302.3	302.4	302.6	302.9	303.1	303.3	302.9	302.5	302.2	301.8
140°	318.0	318.2	318.2	318.3	318.4	318.4	318.5	318.4	318.4	318.3	318.2
142.5°	332.5	332.7	332.8	332.9	333.1	333.2	333.4	333.3	333.2	333.1	333.0
145°	346.7	346.8	346.9	347.2	347.4	347.7	347.9	347.8	347.7	347.6	347.5
147.5°	360.4	360.6	360.7	361.0	361.2	361.5	361.7	361.7	361.7	361.7	361.7
150°	373.6	373.7	373.8	373.9	374.1	374.2	374.4	374.4	374.4	374.4	374.4
152.5°	385.3	385.4	385.4	385.5	385.6	385.6	385.7	385.9	386.0	386.2	386.3
155°	396.3	396.3	396.3	396.4	396.5	396.6	396.7	397.0	397.3	397.6	397.9
157.5°	406.2	406.2	406.2	406.3	406.4	406.5	406.6	406.9	407.2	407.5	407.8
160°	415.5	415.4	415.4	415.4	415.4	415.4	415.4	415.8	416.2	416.6	417.0
162.5°	423.6	423.5	423.5	423.6	423.7	423.8	423.9	424.3	424.7	425.1	425.5
165°	430.7	430.6	430.6	430.6	430.6	430.6	430.6	431.1	431.5	432.0	432.5
167.5°	436.5	436.3	436.3	436.4	436.5	436.5	436.6	437.1	437.6	438.1	438.6
170°	441.4	441.2	441.2	441.2	441.2	441.2	441.2	441.8	442.3	442.9	443.4
172.5°	445.3	445.1	445.1	445.1	445.1	445.1	445.1	445.6	446.0	446.5	447.0
175°	447.8	447.6	447.6	447.6	447.6	447.6	447.6	448.1	448.5	449.0	449.5
177.5°	449.2	449.0	449.0	449.0	449.0	449.0	449.0	449.5	449.9	450.4	450.9
180°	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1

TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1533.5	1535.1	1528.8	1524.1	1536.7	1528.8	1528.8	1530.4	1527.3	1532.0	1530.4
5°	1447.4	1448.9	1438.0	1441.1	1434.8	1433.3	1431.7	1441.1	1439.5	1438.0	1441.1
7.5°	1362.8	1362.8	1358.1	1355.0	1355.0	1350.3	1356.5	1355.0	1358.1	1358.1	1362.8
10°	1292.3	1295.4	1287.6	1279.8	1278.2	1279.8	1279.8	1281.3	1282.9	1293.9	1292.3
12.5°	1234.3	1229.6	1228.1	1223.4	1215.5	1212.4	1209.3	1226.5	1221.8	1221.8	1221.8
15°	1170.1	1181.1	1179.5	1165.4	1162.3	1168.6	1165.4	1165.4	1181.1	1179.5	1177.9
17.5°	1135.7	1132.5	1129.4	1121.6	1123.1	1121.6	1123.1	1123.1	1132.5	1132.5	1132.5
20°	1096.5	1090.2	1090.2	1087.1	1087.1	1082.4	1088.7	1090.2	1096.5	1096.5	1098.1
22.5°	1062.0	1057.3	1057.3	1055.8	1058.9	1052.6	1058.9	1060.5	1060.5	1065.2	1065.2
25°	1032.3	1029.1	1029.1	1032.3	1032.3	1032.3	1032.3	1038.5	1033.8	1035.4	1033.8
27.5°	1005.6	1007.2	1008.8	1010.3	1008.8	1010.3	1011.9	1015.0	1016.6	1015.0	1011.9
30°	980.6	985.3	986.8	986.8	990.0	991.5	993.1	993.1	994.7	990.0	993.1
32.5°	961.8	961.8	964.9	966.5	969.6	971.2	971.2	974.3	972.7	968.0	969.6
35°	935.2	935.2	941.4	944.6	949.3	947.7	949.3	949.3	950.8	947.7	943.0
37.5°	908.5	911.7	911.7	917.9	919.5	921.1	919.5	922.6	921.1	917.9	916.4
40°	877.2	875.6	877.2	881.9	883.5	883.5	883.5	886.6	886.6	886.6	885.0
42.5°	838.0	842.7	841.2	845.9	844.3	844.3	847.4	850.6	852.1	847.4	849.0
45°	800.4	800.4	803.6	803.6	805.1	805.1	811.4	808.3	811.4	808.3	809.8
47.5°	759.7	761.3	761.3	762.8	766.0	769.1	766.0	767.5	767.5	769.1	766.0
50°	714.3	714.3	717.4	722.1	728.4	725.3	723.7	730.0	725.3	725.3	722.1
52.5°	667.3	672.0	673.6	678.3	683.0	684.5	686.1	683.0	684.5	679.8	681.4
55°	621.9	623.4	629.7	634.4	639.1	639.1	637.5	639.1	640.7	634.4	634.4
57.5°	576.4	581.1	587.4	587.4	593.7	593.7	592.1	592.1	593.7	589.0	587.4
60°	527.9	532.6	540.4	540.4	549.8	551.4	548.2	545.1	545.1	540.4	542.0
62.5°	476.2	480.9	485.6	493.4	499.7	496.6	502.8	496.6	498.1	488.7	488.7
65°	430.8	432.3	440.2	448.0	448.0	451.1	448.0	449.6	444.9	444.9	438.6
67.5°	377.5	377.5	385.3	393.2	401.0	401.0	401.0	396.3	396.3	391.6	391.6
70°	330.5	328.9	336.8	341.5	346.2	347.7	344.6	343.0	339.9	335.2	333.6
72.5°	272.6	275.7	283.5	286.7	294.5	292.9	300.8	291.4	291.4	283.5	282.0
75°	220.9	224.0	231.8	236.5	241.2	241.2	245.9	241.2	235.0	231.8	230.3
77.5°	175.4	173.9	180.1	188.0	189.5	188.0	191.1	189.5	183.3	183.3	180.1
80°	125.3	130.0	136.3	134.7	141.0	139.4	139.4	136.3	136.3	131.6	134.7
82.5°	83.0	87.7	89.3	87.7	89.3	92.4	94.0	92.4	92.4	89.3	90.9
85°	43.9	43.9	47.0	48.6	47.0	47.0	48.6	53.3	50.1	47.0	50.1
87.5°	14.1	12.5	12.5	14.1	12.5	12.5	14.1	14.1	15.7	15.7	15.7
90°	9.9	10.0	10.1	10.3	10.4	10.6	10.4	10.3	10.1	10.0	9.9
92.5°	15.9	15.8	15.7	15.5	15.4	15.2	15.4	15.5	15.7	15.8	15.9
95°	27.6	27.6	27.6	27.6	27.6	27.6	27.6	27.6	27.6	27.6	27.6
97.5°	40.0	40.0	39.9	39.8	39.7	39.6	39.7	39.8	39.9	40.0	40.0
100°	53.0	53.1	53.2	53.4	53.5	53.7	53.5	53.4	53.2	53.1	53.0
102.5°	68.6	68.6	68.5	68.4	68.3	68.2	68.3	68.4	68.5	68.6	68.6
105°	83.4	83.5	83.6	83.8	83.9	84.1	83.9	83.8	83.6	83.5	83.4
107.5°	100.8	100.8	100.7	100.6	100.5	100.4	100.5	100.6	100.7	100.8	100.8
110°	117.7	117.6	117.5	117.3	117.2	117.0	117.2	117.3	117.5	117.6	117.7

TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	134.7	134.7	134.7	134.7	134.7	134.7	134.7	134.7	134.7	134.7	134.7
115°	151.0	151.0	150.9	150.8	150.7	150.6	150.7	150.8	150.9	151.0	151.0
117.5°	167.9	167.8	167.6	167.3	167.1	166.9	167.1	167.3	167.6	167.8	167.9
120°	184.9	184.8	184.7	184.5	184.4	184.2	184.4	184.5	184.7	184.8	184.9
122.5°	201.9	201.8	201.5	201.3	201.0	200.8	201.0	201.3	201.5	201.8	201.9
125°	218.8	218.6	218.3	218.0	217.7	217.4	217.7	218.0	218.3	218.6	218.8
127.5°	235.5	235.3	235.0	234.7	234.3	234.0	234.3	234.7	235.0	235.3	235.5
130°	252.8	252.5	252.0	251.4	250.9	250.3	250.9	251.4	252.0	252.5	252.8
132.5°	269.0	268.8	268.4	268.1	267.7	267.3	267.7	268.1	268.4	268.8	269.0
135°	285.7	285.6	285.5	285.3	285.2	285.0	285.2	285.3	285.5	285.6	285.7
137.5°	301.6	301.5	301.2	301.0	300.7	300.5	300.7	301.0	301.2	301.5	301.6
140°	318.2	317.9	317.4	316.8	316.3	315.7	316.3	316.8	317.4	317.9	318.2
142.5°	333.0	332.8	332.4	332.1	331.7	331.3	331.7	332.1	332.4	332.8	333.0
145°	347.5	347.3	347.0	346.7	346.4	346.1	346.4	346.7	347.0	347.3	347.5
147.5°	361.7	361.5	361.0	360.5	360.1	359.6	360.1	360.5	361.0	361.5	361.7
150°	374.4	374.2	373.7	373.2	372.8	372.3	372.8	373.2	373.7	374.2	374.4
152.5°	386.4	386.2	385.8	385.5	385.1	384.7	385.1	385.5	385.8	386.2	386.4
155°	398.1	397.8	397.3	396.7	396.2	395.6	396.2	396.7	397.3	397.8	398.1
157.5°	408.0	407.8	407.3	406.8	406.4	405.9	406.4	406.8	407.3	407.8	408.0
160°	417.2	417.0	416.7	416.4	416.1	415.8	416.1	416.4	416.7	417.0	417.2
162.5°	425.7	425.4	424.9	424.3	423.8	423.2	423.8	424.3	424.9	425.4	425.7
165°	432.7	432.4	431.9	431.4	430.8	430.3	430.8	431.4	431.9	432.4	432.7
167.5°	438.8	438.6	438.1	437.6	437.1	436.6	437.1	437.6	438.1	438.6	438.8
170°	443.7	443.4	442.9	442.3	441.8	441.2	441.8	442.3	442.9	443.4	443.7
172.5°	447.2	446.9	446.4	445.9	445.3	444.8	445.3	445.9	446.4	446.9	447.2
175°	449.7	449.4	448.9	448.3	447.8	447.2	447.8	448.3	448.9	449.4	449.7
177.5°	451.1	450.8	450.3	449.8	449.2	448.7	449.2	449.8	450.3	450.8	451.1
180°	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1

TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1535.1	1538.2	1539.8	1533.5	1528.8	1536.7	1547.6	1555.5	1561.7	1569.6	1574.3
5°	1444.2	1455.2	1455.2	1458.3	1463.0	1470.9	1491.2	1505.3	1517.9	1527.3	1535.1
7.5°	1367.5	1375.3	1380.0	1387.8	1395.7	1406.6	1430.1	1450.5	1469.3	1480.3	1492.8
10°	1298.6	1304.8	1312.7	1317.4	1331.5	1347.1	1376.9	1394.1	1416.0	1433.3	1448.9
12.5°	1232.8	1254.7	1259.4	1257.8	1270.4	1287.6	1317.4	1344.0	1367.5	1384.7	1401.9
15°	1185.8	1193.6	1203.0	1201.4	1228.1	1232.8	1257.8	1289.2	1320.5	1331.5	1347.1
17.5°	1134.1	1146.6	1156.0	1160.7	1168.6	1185.8	1209.3	1232.8	1273.5	1275.1	1315.8
20°	1093.4	1105.9	1112.2	1118.4	1123.1	1143.5	1163.9	1190.5	1223.4	1240.6	1262.5
22.5°	1066.7	1073.0	1077.7	1082.4	1088.7	1099.6	1124.7	1154.5	1176.4	1195.2	1209.3
25°	1035.4	1041.7	1047.9	1051.1	1055.8	1062.0	1080.8	1104.3	1135.7	1148.2	1162.3
27.5°	1013.5	1013.5	1016.6	1016.6	1022.9	1029.1	1043.2	1065.2	1090.2	1105.9	1124.7
30°	990.0	988.4	990.0	988.4	986.8	996.2	1008.8	1027.6	1044.8	1063.6	1076.1
32.5°	966.5	964.9	964.9	966.5	960.2	964.9	971.2	988.4	1007.2	1016.6	1030.7
35°	941.4	938.3	938.3	938.3	935.2	932.0	938.3	954.0	966.5	979.0	990.0
37.5°	916.4	911.7	911.7	908.5	905.4	900.7	900.7	913.2	930.5	935.2	949.3
40°	881.9	881.9	878.8	877.2	874.1	870.9	866.2	877.2	892.9	897.6	908.5
42.5°	847.4	842.7	841.2	841.2	841.2	836.5	833.3	841.2	850.6	858.4	864.7
45°	808.3	805.1	806.7	805.1	802.0	800.4	798.9	802.0	813.0	816.1	823.9
47.5°	766.0	764.4	764.4	762.8	761.3	762.8	756.6	764.4	767.5	770.7	776.9
50°	722.1	720.6	719.0	717.4	717.4	719.0	717.4	717.4	723.7	726.8	733.1
52.5°	678.3	673.6	673.6	672.0	672.0	668.9	672.0	673.6	676.7	679.8	683.0
55°	631.3	631.3	626.6	626.6	623.4	623.4	625.0	623.4	629.7	632.8	632.8
57.5°	585.8	579.6	581.1	578.0	574.9	573.3	573.3	576.4	579.6	579.6	582.7
60°	537.3	531.0	529.5	523.2	526.3	521.6	523.2	523.2	529.5	526.3	529.5
62.5°	488.7	480.9	476.2	473.1	473.1	474.6	471.5	469.9	473.1	476.2	482.5
65°	437.0	432.3	427.6	422.9	422.9	421.4	424.5	419.8	418.2	419.8	422.9
67.5°	383.8	379.1	374.4	369.7	371.2	366.5	363.4	368.1	365.0	366.5	369.7
70°	332.1	328.9	319.6	316.4	314.9	316.4	314.9	311.7	316.4	314.9	316.4
72.5°	280.4	277.3	272.6	264.7	264.7	263.2	261.6	261.6	260.0	260.0	260.0
75°	230.3	224.0	219.3	217.7	214.6	213.0	211.5	208.3	209.9	211.5	208.3
77.5°	178.6	170.7	169.2	169.2	164.5	164.5	166.0	164.5	162.9	162.9	162.9
80°	131.6	125.3	125.3	122.2	119.0	119.0	119.0	119.0	117.5	115.9	117.5
82.5°	84.6	83.0	81.5	81.5	84.6	78.3	81.5	79.9	78.3	78.3	76.8
85°	47.0	48.6	47.0	48.6	45.4	47.0	47.0	47.0	45.4	47.0	43.9
87.5°	17.2	17.2	17.2	18.8	18.8	18.8	18.8	18.8	20.4	18.8	18.8
90°	9.7	9.4	9.1	8.8	8.5	7.5	6.5	5.4	4.4	3.9	3.5
92.5°	15.8	15.5	15.3	15.0	14.8	14.3	13.9	13.4	12.9	12.7	12.5
95°	27.4	27.1	26.8	26.5	26.2	25.6	24.9	24.3	23.6	23.3	23.0
97.5°	39.8	39.4	39.0	38.6	38.2	37.7	37.3	36.8	36.3	36.1	35.9
100°	52.9	52.7	52.4	52.2	52.0	51.6	51.2	50.8	50.4	50.2	50.0
102.5°	68.5	68.2	68.0	67.7	67.5	67.0	66.4	65.9	65.4	65.1	65.0
105°	83.4	83.4	83.4	83.4	83.4	82.7	82.0	81.3	80.6	80.3	80.2
107.5°	100.7	100.4	100.2	99.9	99.7	99.4	99.1	98.8	98.5	98.3	98.3
110°	117.5	117.2	116.9	116.6	116.3	116.1	116.0	115.8	115.7	115.6	115.5



TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	134.5	134.1	133.7	133.3	132.9	132.9	132.9	132.9	132.9	132.9	132.9
115°	151.0	150.9	150.8	150.7	150.6	150.8	150.9	151.1	151.2	151.3	151.2
117.5°	167.9	167.9	167.9	167.9	167.9	168.1	168.2	168.4	168.5	168.6	168.6
120°	184.9	185.0	185.1	185.2	185.3	185.7	186.1	186.4	186.8	187.0	186.8
122.5°	202.0	202.2	202.5	202.7	202.9	203.1	203.2	203.4	203.5	203.6	203.4
125°	219.0	219.3	219.6	220.0	220.3	220.5	220.6	220.8	220.9	221.0	220.9
127.5°	235.7	236.2	236.7	237.1	237.6	237.8	237.9	238.1	238.2	238.3	238.1
130°	253.0	253.3	253.6	253.9	254.2	254.4	254.7	254.9	255.2	255.3	255.0
132.5°	269.2	269.6	270.0	270.4	270.8	271.0	271.1	271.3	271.4	271.5	271.2
135°	285.9	286.2	286.5	286.8	287.1	287.2	287.2	287.3	287.4	287.4	287.2
137.5°	301.8	302.2	302.5	302.9	303.3	303.1	302.9	302.6	302.4	302.3	302.1
140°	318.2	318.3	318.4	318.4	318.5	318.4	318.4	318.3	318.2	318.2	318.0
142.5°	333.0	333.1	333.2	333.3	333.4	333.2	333.1	332.9	332.8	332.7	332.5
145°	347.5	347.6	347.7	347.8	347.9	347.7	347.4	347.2	346.9	346.8	346.7
147.5°	361.7	361.7	361.7	361.7	361.7	361.5	361.2	361.0	360.7	360.6	360.4
150°	374.4	374.4	374.4	374.4	374.4	374.2	374.1	373.9	373.8	373.7	373.6
152.5°	386.3	386.2	386.0	385.9	385.7	385.6	385.6	385.5	385.4	385.4	385.3
155°	397.9	397.6	397.3	397.0	396.7	396.6	396.5	396.4	396.3	396.3	396.3
157.5°	407.8	407.5	407.2	406.9	406.6	406.5	406.4	406.3	406.2	406.2	406.2
160°	417.0	416.6	416.2	415.8	415.4	415.4	415.4	415.4	415.4	415.4	415.5
162.5°	425.5	425.1	424.7	424.3	423.9	423.8	423.7	423.6	423.5	423.5	423.6
165°	432.5	432.0	431.5	431.1	430.6	430.6	430.6	430.6	430.6	430.6	430.7
167.5°	438.6	438.1	437.6	437.1	436.6	436.5	436.5	436.4	436.3	436.3	436.5
170°	443.4	442.9	442.3	441.8	441.2	441.2	441.2	441.2	441.2	441.2	441.4
172.5°	447.0	446.5	446.0	445.6	445.1	445.1	445.1	445.1	445.1	445.1	445.3
175°	449.5	449.0	448.5	448.1	447.6	447.6	447.6	447.6	447.6	447.6	447.8
177.5°	450.9	450.4	449.9	449.5	449.0	449.0	449.0	449.0	449.0	449.0	449.2
180°	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1	450.1

TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1616.5	1616.5	1616.5	1616.5
2.5°	1582.1	1586.8	1602.4	1621.2
5°	1550.8	1563.3	1585.2	1615.0
7.5°	1516.3	1535.1	1566.4	1604.0
10°	1477.1	1503.8	1542.9	1589.9
12.5°	1434.8	1469.3	1519.4	1568.0
15°	1408.2	1442.7	1488.1	1541.4
17.5°	1356.5	1397.2	1444.2	1519.4
20°	1303.3	1348.7	1409.8	1485.0
22.5°	1262.5	1311.1	1369.1	1448.9
25°	1214.0	1264.1	1326.8	1409.8
27.5°	1162.3	1212.4	1282.9	1370.6
30°	1123.1	1171.7	1239.0	1333.0
32.5°	1076.1	1123.1	1193.6	1292.3
35°	1022.9	1076.1	1143.5	1243.7
37.5°	982.1	1030.7	1101.2	1196.7
40°	938.3	980.6	1049.5	1143.5
42.5°	891.3	938.3	997.8	1091.8
45°	847.4	881.9	943.0	1032.3
47.5°	800.4	839.6	886.6	955.5
50°	750.3	783.2	834.9	881.9
52.5°	701.8	728.4	772.2	808.3
55°	650.1	676.7	709.6	731.5
57.5°	601.5	620.3	642.2	656.3
60°	542.0	560.8	574.9	589.0
62.5°	488.7	502.8	510.7	518.5
65°	433.9	441.7	446.4	452.7
67.5°	374.4	382.2	383.8	393.2
70°	319.6	321.1	324.2	328.9
72.5°	267.9	271.0	269.4	272.6
75°	214.6	217.7	214.6	217.7
77.5°	162.9	166.0	166.0	170.7
80°	117.5	119.0	120.6	120.6
82.5°	76.8	81.5	78.3	79.9
85°	43.9	45.4	45.4	47.0
87.5°	20.4	21.9	20.4	23.5
90°	2.7	2.0	1.2	0.4
92.5°	12.0	11.5	11.1	10.6
95°	22.5	22.0	21.4	20.9
97.5°	35.5	35.1	34.7	34.3
100°	49.5	49.0	48.6	48.1
102.5°	64.7	64.5	64.2	64.0
105°	80.0	79.9	79.7	79.5
107.5°	98.2	98.1	98.0	97.9
110°	115.4	115.2	115.1	114.9

TEST NUMBER: P1011356

CATALOG NUMBER: S123DIP-B1165D365UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	132.8	132.7	132.7	132.6
115°	151.0	150.7	150.5	150.3
117.5°	168.5	168.4	168.4	168.3
120°	186.3	185.8	185.4	184.9
122.5°	203.1	202.8	202.5	202.2
125°	220.6	220.4	220.1	219.9
127.5°	237.6	237.1	236.7	236.2
130°	254.3	253.7	253.0	252.4
132.5°	270.6	269.9	269.3	268.7
135°	286.7	286.2	285.8	285.3
137.5°	301.7	301.3	300.9	300.5
140°	317.6	317.2	316.8	316.4
142.5°	332.1	331.7	331.3	330.9
145°	346.6	346.4	346.3	346.1
147.5°	360.1	359.8	359.5	359.2
150°	373.5	373.3	373.2	373.0
152.5°	385.0	384.8	384.5	384.3
155°	396.3	396.3	396.3	396.3
157.5°	406.3	406.4	406.5	406.6
160°	415.6	415.8	415.9	416.1
162.5°	423.9	424.1	424.4	424.6
165°	431.0	431.2	431.5	431.7
167.5°	436.8	437.1	437.4	437.7
170°	441.7	442.0	442.3	442.6
172.5°	445.6	445.9	446.2	446.5
175°	448.1	448.4	448.7	449.0
177.5°	449.5	449.8	450.1	450.4
180°	450.1	450.1	450.1	450.1

(END OF REPORT)