

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011631

Luminaire Tested: S123DIP-B340D585UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011631
REPORT IS A COMBINATION OF REPORTS P989856 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D585UB50-4F0-XX-W2A-F
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3576.0 lumens
Efficiency: N/A
Efficacy: 125.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011631

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1011631

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	83	86	82	79	76	67	64	62	52	51	49	39	38	37
2	86	79	73	68	78	72	67	62	58	55	51	46	43	41	34	33	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	35	30	28	27
4	72	61	54	48	65	56	49	44	46	41	37	36	32	30	27	25	23
5	66	55	47	41	59	50	43	38	41	36	32	32	29	26	24	22	20
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	18	18	16	14
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5459	5459	5459
5°	5473	5271	5263
10°	5425	5092	5041
15°	5349	4907	4798
20°	5263	4701	4557
25°	5150	4483	4300
30°	5028	4259	4029
35°	4900	4029	3760
40°	4766	3787	3496
45°	4617	3552	3220
50°	4467	3291	2943
55°	4274	3017	2662
60°	4077	2717	2363
65°	3890	2391	2051
70°	3622	2029	1687
75°	3233	1607	1310
80°	2796	1130	925
85°	2180	607	463

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4617 cd/sqm

TEST NUMBER: P1011631

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.8	1.3
10°-20°	135.0	3.8
20°-30°	199.4	5.6
30°-40°	232.9	6.5
40°-50°	234.1	6.5
50°-60°	205.7	5.8
60°-70°	153.2	4.3
70°-80°	87.2	2.4
80°-90°	26.3	0.7
90°-100°	26.1	0.7
100°-110°	126.1	3.5
110°-120°	309.0	8.6
120°-130°	392.2	11.0
130°-140°	419.0	11.7
140°-150°	391.8	11.0
150°-160°	316.0	8.8
160°-170°	204.0	5.7
170°-180°	70.3	2.0
0°-30°	382.2	10.7
0°-40°	615.1	17.2
0°-60°	1054.9	29.5
0°-90°	1321.5	37.0
90°-120°	461.1	12.9
90°-150°	1664.2	46.5
90°-180°	2255.0	63.1
0°-180°	3576.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	507	507	507	507	507	
5°	508	505	501	505	504	48
15°	483	482	476	479	477	136
25°	439	436	430	431	430	202
35°	379	377	371	368	366	237
45°	311	309	304	298	296	240
55°	236	236	230	225	223	211
65°	161	159	154	151	150	159
75°	85	83	82	80	78	91
85°	23	22	22	21	21	24
90°	0	6	13	15	16	3
95°	34	11	17	21	21	40
105°	164	170	120	23	24	174
115°	307	310	315	321	323	303
125°	433	437	440	441	442	387
135°	539	542	544	546	544	415
145°	622	626	627	628	628	389
155°	685	684	685	687	684	316
165°	722	721	720	725	721	204
175°	740	737	737	741	737	70
180°	740	740	740	740	740	

TEST NUMBER: P1011631

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	507.2	507.2	507.2	507.2	507.2
2.5°	509.4	507.6	502.8	507.2	506.8
5°	507.6	505.4	500.7	505.0	504.1
7.5°	503.7	501.5	496.7	500.7	500.2
10°	498.5	496.3	490.6	494.5	493.7
12.5°	491.5	489.7	484.5	487.1	486.7
15°	483.2	481.5	475.8	479.3	476.7
17.5°	474.0	471.9	466.2	468.8	467.9
20°	463.6	461.0	455.3	457.0	455.7
22.5°	451.8	449.2	443.5	444.8	443.1
25°	438.7	436.1	430.4	430.9	429.6
27.5°	425.2	422.6	416.5	416.9	415.6
30°	410.4	408.2	402.1	402.1	399.0
32.5°	395.5	392.5	388.1	385.1	383.8
35°	379.4	376.8	371.1	368.5	366.3
37.5°	363.3	359.8	354.1	351.1	349.8
40°	346.3	343.7	337.5	334.1	332.3
42.5°	329.3	326.2	320.1	316.6	314.9
45°	310.9	309.2	303.5	298.3	296.1
47.5°	293.1	290.4	285.2	280.0	278.2
50°	274.7	272.6	266.9	262.1	259.5
52.5°	255.6	254.3	248.1	244.2	241.6
55°	235.9	235.5	229.8	225.0	222.9
57.5°	217.6	215.9	211.5	207.2	204.5
60°	197.6	197.1	191.9	188.0	185.8
62.5°	179.7	178.4	173.1	169.2	167.9
65°	160.9	158.7	154.4	150.9	149.6
67.5°	140.9	139.1	135.6	132.6	130.8
70°	123.0	120.4	117.7	114.7	112.5
72.5°	104.2	102.5	99.4	96.8	95.9
75°	85.0	83.3	82.0	79.8	78.5
77.5°	68.0	67.2	65.4	63.7	63.7
80°	51.5	50.2	49.3	48.8	48.8
82.5°	35.3	35.3	35.3	34.5	34.0
85°	22.7	21.8	21.8	20.9	20.9
87.5°	11.3	10.0	9.6	9.2	9.2
90°	0.5	6.0	13.2	15.4	16.5
92.5°	12.6	9.3	14.3	18.1	18.7
95°	33.5	11.0	17.0	20.9	20.9
97.5°	61.0	45.6	17.6	22.0	22.5
100°	92.9	103.8	18.1	22.5	23.1
102.5°	129.1	136.3	40.7	22.5	23.6
105°	163.7	169.8	120.3	23.1	24.2
107.5°	200.5	205.5	213.7	129.1	57.1
110°	237.4	241.7	247.8	229.7	151.1

TEST NUMBER: P1011631

CATALOG NUMBER: S123DIP-B340D585UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	272.5	276.4	282.4	287.4	286.3
115°	307.1	310.4	315.4	320.9	323.1
117.5°	341.2	345.0	347.8	352.2	352.7
120°	372.5	377.5	379.1	383.5	383.5
122.5°	404.4	408.2	410.4	413.2	413.7
125°	432.9	437.3	439.5	440.6	441.7
127.5°	461.5	465.9	468.7	470.3	469.2
130°	487.9	492.3	494.5	496.7	495.6
132.5°	513.2	517.6	519.2	521.4	519.8
135°	539.0	542.3	544.5	546.1	544.5
137.5°	561.0	565.4	566.5	569.2	568.1
140°	582.9	586.2	587.9	590.1	589.0
142.5°	603.3	606.6	608.2	609.9	608.2
145°	622.0	625.8	626.9	628.0	628.0
147.5°	640.1	642.8	643.9	645.0	642.3
150°	656.6	658.2	659.3	660.4	658.8
152.5°	671.4	672.0	672.5	674.7	672.0
155°	685.1	684.0	684.6	687.3	684.0
157.5°	696.1	696.1	695.6	698.9	694.5
160°	706.0	705.5	704.9	708.2	704.4
162.5°	715.4	713.7	713.2	717.0	713.7
165°	722.5	720.9	720.3	724.7	720.9
167.5°	728.5	726.3	726.3	730.7	726.3
170°	733.5	731.3	731.3	735.7	731.3
172.5°	736.8	734.0	734.6	739.0	734.0
175°	739.5	736.8	737.3	741.2	736.8
177.5°	740.6	737.9	738.4	742.8	737.3
180°	739.5	739.5	739.5	739.5	739.5

(END OF REPORT)