

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011366

Luminaire Tested: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011366
REPORT IS A COMBINATION OF REPORTS P989492 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D365UB50-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5989.0 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83
1	105	100	96	93	100	96	93	89	88	85	83	81	79	77	74	72	71
2	96	88	82	77	91	85	79	74	78	73	69	71	68	65	65	63	60
3	88	78	70	64	83	75	68	62	69	63	59	63	59	55	58	55	52
4	80	69	61	55	77	67	59	53	61	55	50	57	52	48	52	48	45
5	74	62	54	48	71	60	52	46	55	49	44	51	46	42	47	43	39
6	68	56	48	42	65	54	46	41	50	43	39	46	41	37	43	38	35
7	63	51	42	37	60	49	41	36	46	39	34	42	37	33	39	35	31
8	59	46	38	33	56	45	37	32	42	35	31	39	33	29	36	31	28
9	55	42	35	29	53	41	34	29	38	32	28	36	30	26	33	29	25
10	52	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16826	16826	16826	16826
5°	16837	19388	16886	14469
10°	16731	23460	16747	12635
15°	16499	27823	16633	11373
20°	16301	32034	16335	10466
25°	16005	32841	16040	9992
30°	15793	27132	15793	9681
35°	15532	18146	15434	9407
40°	15219	13099	15030	8987
45°	14824	10376	14397	8466
50°	13868	8812	13375	7953
55°	12818	7743	12296	7381
60°	11751	6743	11126	6781
65°	10583	5773	10071	5980
70°	9368	4792	8743	5042
75°	8007	3614	7490	3892
80°	6330	2412	5836	2556
85°	4361	1108	3496	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 27137 cd/sqm

TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.7	2.6
10°-20°	493.8	8.2
20°-30°	830.9	13.9
30°-40°	938.9	15.7
40°-50°	841.0	14.0
50°-60°	678.9	11.3
60°-70°	473.1	7.9
70°-80°	248.3	4.1
80°-90°	60.5	1.0
90°-100°	91.6	1.5
100°-110°	268.2	4.5
110°-120°	261.9	4.4
120°-130°	208.6	3.5
130°-140°	164.6	2.7
140°-150°	122.8	2.1
150°-160°	85.6	1.4
160°-170°	50.3	0.8
170°-180°	16.4	0.3
0°-30°	1478.4	24.7
0°-40°	2417.3	40.4
0°-60°	3937.1	65.7
0°-90°	4718.9	78.8
90°-120°	621.8	10.4
90°-150°	1117.8	18.7
90°-180°	1270.0	21.2
0°-180°	5989.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1563	1563	1563	1563	1563	
5°	1562	1857	1566	1386	1562	148
15°	1490	2764	1503	1130	1490	421
25°	1363	3281	1366	998	1363	629
35°	1203	1768	1195	916	1203	753
45°	998	954	969	779	998	763
55°	707	648	679	618	707	633
65°	438	421	417	436	438	436
75°	210	217	197	233	210	226
85°	45	50	36	45	45	52
90°	1	10	1	10	1	4
95°	12	40	12	40	12	12
105°	40	435	40	435	40	42
115°	70	529	70	529	70	69
125°	97	417	97	417	97	87
135°	114	338	114	338	114	88
145°	130	264	130	264	130	82
155°	148	219	148	219	148	68
165°	162	191	162	191	162	46
175°	168	172	168	172	168	16
180°	169	169	169	169	169	



TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1567.7	1579.9	1585.9	1595.0	1604.1	1617.7	1622.3	1629.9	1626.8	1632.9	1635.9
5°	1561.7	1582.9	1601.1	1623.8	1645.0	1660.1	1675.3	1699.5	1717.7	1720.7	1734.4
7.5°	1551.1	1581.4	1613.2	1645.0	1685.9	1710.1	1737.4	1770.7	1798.0	1841.9	1858.6
10°	1537.5	1579.9	1625.3	1669.2	1725.3	1763.1	1796.5	1852.5	1908.6	1954.0	1996.4
12.5°	1516.2	1569.3	1628.3	1693.5	1766.2	1810.1	1855.5	1929.8	2014.6	2084.3	2129.7
15°	1490.5	1557.1	1632.9	1702.6	1782.8	1864.6	1913.1	1996.4	2117.6	2182.7	2299.4
17.5°	1469.3	1537.5	1613.2	1722.3	1831.3	1913.1	1947.9	2100.9	2184.2	2293.3	2425.1
20°	1436.0	1522.3	1619.2	1728.3	1869.2	1919.2	1990.4	2144.9	2247.9	2390.2	2552.3
22.5°	1401.1	1493.5	1610.2	1723.8	1881.3	1934.3	2031.3	2153.9	2317.5	2458.4	2637.1
25°	1363.3	1463.2	1581.4	1716.2	1870.7	1947.9	2038.8	2190.3	2367.5	2544.8	2709.9
27.5°	1325.4	1434.5	1557.1	1692.0	1841.9	1932.8	2023.7	2181.2	2408.4	2600.8	2811.3
30°	1289.0	1398.1	1520.8	1658.6	1816.2	1904.0	1990.4	2187.3	2440.2	2656.8	2868.9
32.5°	1249.7	1361.7	1490.5	1605.6	1764.7	1858.6	1955.5	2187.3	2459.9	2690.2	2884.1
35°	1202.7	1317.8	1428.4	1543.5	1701.0	1805.6	1914.6	2172.1	2478.1	2700.8	2820.4
37.5°	1157.3	1258.7	1354.2	1466.3	1631.4	1743.5	1869.2	2153.9	2469.0	2655.3	2688.6
40°	1105.8	1207.2	1284.5	1389.0	1563.2	1693.5	1820.7	2129.7	2429.6	2547.8	2450.8
42.5°	1055.8	1136.0	1202.7	1304.2	1493.5	1620.8	1758.6	2085.8	2352.4	2376.6	2158.5
45°	998.2	1055.8	1114.8	1230.0	1417.8	1548.1	1701.0	2022.2	2228.2	2158.5	1882.8
47.5°	924.0	975.5	1040.6	1146.7	1337.5	1472.3	1617.7	1940.4	2047.9	1902.5	1601.1
50°	852.8	896.7	957.3	1060.3	1252.7	1384.5	1539.0	1811.6	1864.6	1635.9	1379.9
52.5°	781.6	814.9	874.0	977.0	1169.4	1296.6	1437.5	1679.8	1649.5	1404.2	1176.9
55°	707.4	736.2	792.2	893.7	1072.4	1193.6	1328.4	1517.8	1439.0	1205.7	1024.0
57.5°	634.7	665.0	722.5	807.4	975.5	1093.6	1201.2	1349.6	1231.5	1045.2	884.6
60°	569.5	595.3	639.2	722.5	875.5	970.9	1069.4	1170.9	1072.4	892.2	769.5
62.5°	501.4	525.6	566.5	642.2	774.0	858.9	937.6	1020.9	911.9	780.1	671.0
65°	437.8	457.4	495.3	565.0	672.5	742.2	805.8	863.4	775.5	654.4	572.6
67.5°	380.2	396.9	428.7	490.8	581.7	631.6	683.1	731.6	657.4	560.5	490.8
70°	318.1	331.7	360.5	405.9	478.7	530.2	568.0	604.4	537.7	460.5	413.5
72.5°	263.6	277.2	295.4	342.3	392.3	424.1	465.0	484.7	446.8	383.2	336.3
75°	210.5	221.2	237.8	268.1	315.1	336.3	362.0	377.2	342.3	299.9	271.1
77.5°	165.1	169.7	181.8	203.0	234.8	259.0	278.7	287.8	263.6	236.3	212.1
80°	116.6	122.7	131.8	150.0	174.2	181.8	193.9	204.5	189.3	165.1	150.0
82.5°	77.3	84.8	89.4	96.9	112.1	121.2	124.2	133.3	119.7	110.6	104.5
85°	45.4	48.5	50.0	54.5	62.1	66.6	71.2	72.7	69.7	68.2	62.1
87.5°	22.7	22.7	22.7	25.8	27.3	30.3	31.8	31.8	31.8	30.3	28.8
90°	0.7	1.4	2.1	3.1	3.8	4.1	4.4	5.5	6.5	7.5	8.5
92.5°	5.1	7.5	10.9	14.0	17.4	20.5	23.6	34.5	52.6	70.4	63.6
95°	11.6	12.6	16.4	22.2	31.1	37.8	44.4	73.5	124.4	180.5	202.7
97.5°	18.5	18.8	21.9	27.0	35.9	43.2	50.6	79.3	138.4	232.8	311.7
100°	25.3	25.6	28.0	32.8	41.0	47.6	54.3	78.3	128.9	218.7	323.7
102.5°	32.5	33.2	35.2	39.6	46.8	52.8	58.8	79.6	120.7	198.2	301.5
105°	39.6	40.7	42.7	46.8	53.3	58.6	63.9	82.4	117.6	182.2	274.8
107.5°	47.2	48.2	50.2	54.3	60.5	65.4	70.4	86.8	116.9	170.6	251.2
110°	55.4	56.4	58.1	61.9	67.7	72.4	77.2	92.6	118.6	164.4	231.7

TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	62.9	63.9	65.6	69.4	75.2	79.8	84.4	98.4	122.0	161.0	218.7
115°	70.1	71.4	73.5	76.9	82.7	87.3	91.9	104.9	125.8	160.6	210.2
117.5°	77.2	79.0	80.7	83.7	90.2	94.5	98.8	111.8	130.6	161.0	204.4
120°	84.8	85.8	87.5	90.9	97.4	101.7	106.0	118.3	136.0	162.4	200.6
122.5°	91.3	92.3	94.0	97.8	103.9	108.5	113.1	125.1	141.2	164.7	198.2
125°	97.4	98.1	100.1	103.9	110.4	115.0	119.6	131.6	146.6	167.1	196.2
127.5°	102.2	103.2	105.6	109.4	116.6	121.2	125.8	137.4	151.1	169.9	195.2
130°	106.6	107.7	110.7	114.8	122.0	126.6	131.2	142.5	155.5	172.6	194.1
132.5°	110.1	111.4	114.8	120.0	127.1	131.6	136.0	147.0	159.6	174.7	193.8
135°	114.2	115.5	119.3	124.4	131.6	136.2	140.8	151.4	163.0	176.7	193.5
137.5°	117.9	119.3	123.0	128.5	135.7	140.0	144.2	154.5	165.8	178.1	192.8
140°	121.7	123.4	126.8	132.3	139.1	143.4	147.7	157.6	167.8	179.4	192.4
142.5°	125.8	127.1	130.9	135.7	142.5	146.4	150.4	160.0	169.9	180.5	191.7
145°	130.2	131.2	134.3	139.5	145.3	149.2	153.1	162.0	171.2	180.8	191.1
147.5°	134.7	135.3	138.4	142.9	148.7	152.1	155.5	163.7	172.3	180.8	190.0
150°	139.1	139.5	142.2	146.6	151.4	154.5	157.6	165.4	172.6	180.8	188.7
152.5°	143.6	143.6	146.3	150.0	154.1	157.0	160.0	166.5	173.3	179.8	187.0
155°	148.0	148.0	150.0	153.5	157.2	159.6	162.0	167.8	173.3	179.1	184.9
157.5°	151.4	151.8	153.5	156.5	160.0	161.8	163.7	168.5	173.6	178.1	183.2
160°	155.5	155.5	156.9	159.6	162.0	163.7	165.4	169.5	173.6	177.4	181.1
162.5°	158.6	158.6	159.6	161.7	163.7	165.1	166.5	169.9	173.3	176.0	179.1
165°	161.7	161.3	162.0	163.7	165.1	166.3	167.5	170.2	172.6	174.7	177.0
167.5°	164.1	163.7	164.1	165.4	166.5	167.4	168.2	170.2	172.3	173.3	175.0
170°	166.1	165.4	165.8	166.8	167.5	167.8	168.2	169.9	171.2	171.9	172.9
172.5°	167.5	167.1	167.1	167.8	168.2	168.4	168.5	169.9	170.9	170.9	171.2
175°	168.5	168.2	167.8	168.5	168.5	168.6	168.8	169.5	170.2	169.9	169.9
177.5°	169.2	168.8	168.5	168.8	168.8	168.8	168.8	169.2	169.9	169.2	168.8
180°	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8

TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1646.5	1649.5	1660.1	1667.7	1682.9	1681.4	1681.4	1679.8	1675.3	1682.9	1687.4
5°	1761.6	1787.4	1790.4	1823.7	1825.3	1838.9	1848.0	1840.4	1858.6	1857.1	1843.4
7.5°	1904.0	1938.9	1955.5	1987.3	2023.7	2014.6	2049.4	2055.5	2052.5	2067.6	2078.2
10°	2060.0	2120.6	2163.0	2222.1	2237.3	2246.3	2269.1	2288.8	2328.1	2297.8	2317.5
12.5°	2238.8	2282.7	2338.7	2432.7	2479.6	2509.9	2520.5	2534.1	2561.4	2544.8	2546.3
15°	2388.7	2447.8	2543.2	2659.9	2673.5	2711.4	2702.3	2784.1	2823.5	2764.4	2797.7
17.5°	2544.8	2623.5	2737.1	2838.6	2896.2	2921.9	2946.2	3024.9	3021.9	3012.8	3020.4
20°	2644.7	2773.5	2914.3	3049.2	3065.8	3085.5	3150.6	3184.0	3177.9	3203.7	3220.3
22.5°	2785.6	2921.9	3071.9	3161.2	3199.1	3221.8	3273.3	3294.5	3303.6	3309.7	3299.1
25°	2903.7	3049.2	3159.7	3238.5	3261.2	3273.3	3290.0	3296.1	3291.5	3280.9	3290.0
27.5°	2984.0	3100.7	3176.4	3212.7	3200.6	3180.9	3149.1	3127.9	3081.0	3058.2	3085.5
30°	3017.3	3068.8	3091.6	3031.0	2970.4	2921.9	2861.3	2749.2	2661.4	2687.1	2652.3
32.5°	2964.3	2931.0	2821.9	2665.9	2619.0	2540.2	2369.0	2237.3	2241.8	2172.1	2200.9
35°	2808.3	2656.8	2450.8	2214.5	2152.4	2110.0	1922.2	1893.4	1832.8	1767.7	1785.9
37.5°	2532.6	2311.5	2061.6	1887.4	1795.0	1702.6	1596.5	1532.9	1496.6	1469.3	1490.5
40°	2196.4	1926.7	1720.7	1564.7	1486.0	1426.9	1354.2	1290.6	1249.7	1245.1	1252.7
42.5°	1866.2	1638.9	1449.6	1301.2	1275.4	1205.7	1158.8	1108.8	1096.7	1077.0	1087.6
45°	1579.9	1395.1	1239.1	1117.9	1087.6	1069.4	1011.8	980.0	966.4	954.3	972.5
47.5°	1372.3	1178.5	1064.9	992.1	961.9	931.6	899.8	878.5	867.9	869.5	867.9
50°	1172.4	1030.0	930.0	874.0	855.8	834.6	808.9	795.2	790.7	777.1	787.7
52.5°	1008.8	905.8	836.1	783.1	769.5	754.3	733.1	725.6	715.0	711.9	711.9
55°	877.0	796.7	740.7	705.9	689.2	677.1	665.0	655.9	648.3	648.3	648.3
57.5°	774.0	704.4	663.5	633.2	627.1	615.0	601.3	601.3	590.7	589.2	593.8
60°	686.2	624.1	592.3	566.5	557.4	554.4	540.8	540.8	537.7	530.2	536.2
62.5°	596.8	551.4	524.1	504.4	495.3	495.3	484.7	477.1	477.1	478.7	475.6
65°	515.0	481.7	457.4	442.3	437.8	431.7	430.2	424.1	419.6	421.1	419.6
67.5°	442.3	416.6	399.9	387.8	380.2	377.2	372.6	372.6	369.6	371.1	363.5
70°	377.2	351.4	337.8	325.7	322.6	322.6	316.6	318.1	315.1	319.6	316.6
72.5°	310.5	290.8	280.2	275.7	272.7	271.1	268.1	265.1	263.6	266.6	265.1
75°	251.4	234.8	227.2	224.2	221.2	221.2	219.6	218.1	216.6	216.6	216.6
77.5°	195.4	184.8	175.7	178.7	174.2	175.7	171.2	171.2	172.7	171.2	171.2
80°	143.9	136.3	136.3	133.3	127.2	130.3	130.3	125.7	124.2	127.2	122.7
82.5°	95.4	93.9	90.9	89.4	86.3	87.9	86.3	84.8	83.3	86.3	83.3
85°	56.0	56.0	54.5	51.5	54.5	53.0	51.5	51.5	50.0	50.0	50.0
87.5°	28.8	25.8	25.8	24.2	25.8	22.7	24.2	22.7	21.2	22.7	21.2
90°	8.2	8.5	8.9	9.2	9.6	9.9	9.6	9.9	10.3	9.9	10.3
92.5°	47.5	33.8	26.3	22.9	21.7	20.5	19.8	18.5	18.8	18.1	18.8
95°	164.4	123.0	83.4	65.3	59.2	53.0	46.5	43.4	41.0	39.6	41.0
97.5°	322.3	282.7	213.3	168.2	148.7	129.2	106.3	93.3	85.1	81.3	85.1
100°	391.0	403.0	375.3	335.3	311.0	286.8	252.2	227.3	214.0	214.3	214.0
102.5°	394.4	443.0	448.8	429.6	416.4	403.3	378.4	359.9	349.3	339.4	349.3
105°	372.9	444.3	478.5	485.0	480.6	476.1	460.4	447.4	436.5	434.8	436.5
107.5°	342.1	423.8	477.5	504.1	508.8	513.4	511.3	505.2	500.7	497.0	500.7
110°	313.4	391.7	454.6	497.6	509.6	521.6	531.1	533.9	533.2	532.5	533.2

TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	288.5	359.9	424.5	474.1	490.3	506.5	526.0	535.9	539.3	539.7	539.3
115°	269.3	332.6	392.0	442.3	460.9	479.5	505.2	520.2	527.0	528.7	527.0
117.5°	256.7	311.4	364.0	410.1	429.4	448.8	475.4	492.2	502.4	504.8	502.4
120°	247.1	295.3	341.4	382.5	399.8	417.0	444.0	463.1	471.3	473.4	471.3
122.5°	239.3	282.7	323.3	360.6	376.3	392.0	415.3	432.0	441.3	444.0	441.3
125°	232.8	271.7	309.0	341.8	355.5	369.1	391.0	406.0	414.6	417.0	414.6
127.5°	226.6	261.8	295.6	325.7	338.4	351.0	370.8	383.8	391.7	393.7	391.7
130°	221.8	252.6	283.3	311.0	322.6	334.3	352.4	364.7	371.9	374.6	371.9
132.5°	217.4	244.0	271.7	297.0	308.0	318.9	335.6	347.9	354.1	355.8	354.1
135°	213.6	236.5	260.8	283.0	292.8	302.5	319.2	329.5	335.6	338.0	335.6
137.5°	210.2	229.3	249.8	269.7	278.4	287.1	301.5	312.1	317.2	319.2	317.2
140°	207.1	223.2	240.6	257.0	264.4	271.7	284.7	294.3	299.8	299.4	299.8
142.5°	204.4	217.4	231.7	245.4	251.6	257.7	268.3	276.5	281.3	281.0	281.3
145°	202.0	212.9	224.2	235.2	240.2	245.1	253.6	260.8	263.5	264.2	263.5
147.5°	199.6	209.2	218.4	227.6	231.2	234.8	241.6	246.8	249.5	249.8	249.5
150°	197.2	205.1	212.9	220.1	223.4	226.6	231.7	235.5	237.5	237.5	237.5
152.5°	194.5	201.3	207.8	214.0	216.6	219.1	222.8	226.3	227.3	227.3	227.3
155°	191.7	197.6	203.0	208.2	210.2	212.3	215.3	218.1	218.7	219.1	218.7
157.5°	188.7	193.5	198.2	202.3	204.0	205.8	208.5	210.5	211.2	211.2	211.2
160°	185.6	190.0	193.8	197.2	198.4	199.6	202.0	204.0	204.0	203.7	204.0
162.5°	182.5	185.9	189.0	192.1	193.1	194.1	195.5	197.2	197.2	196.9	197.2
165°	179.8	182.5	184.6	187.0	187.8	188.7	190.0	191.4	191.1	191.1	191.1
167.5°	177.0	179.4	181.1	182.5	183.2	183.9	184.6	185.6	185.3	185.3	185.3
170°	174.7	176.4	177.4	178.8	179.1	179.4	179.8	180.5	180.1	180.1	180.1
172.5°	172.3	173.6	174.3	175.3	175.5	175.7	175.7	176.4	175.7	175.3	175.7
175°	170.6	171.2	171.6	172.3	172.3	172.3	172.3	172.6	172.3	171.9	172.3
177.5°	169.2	169.5	169.9	170.2	170.2	170.2	169.9	170.2	169.5	169.5	169.5
180°	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8

TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1675.3	1679.8	1667.7	1664.7	1664.7	1670.7	1666.2	1625.3	1632.9	1623.8	1620.8
5°	1860.1	1851.0	1838.9	1832.8	1825.3	1804.0	1802.5	1755.6	1746.5	1716.2	1702.6
7.5°	2063.1	2055.5	2019.1	2014.6	2011.6	1991.9	1941.9	1891.9	1855.5	1820.7	1787.4
10°	2294.8	2272.1	2255.4	2222.1	2205.5	2178.2	2113.1	2066.1	2004.0	1951.0	1881.3
12.5°	2573.5	2547.8	2491.7	2467.5	2446.3	2370.6	2305.4	2252.4	2131.2	2094.9	2008.5
15°	2778.0	2723.5	2717.4	2664.4	2661.4	2578.1	2453.9	2396.3	2302.4	2169.1	2079.7
17.5°	2999.2	2950.7	2912.8	2849.2	2840.1	2761.4	2670.5	2529.6	2426.6	2299.4	2185.8
20°	3161.2	3135.5	3070.4	3044.6	2991.6	2924.9	2831.0	2656.8	2531.1	2403.9	2264.5
22.5°	3290.0	3264.2	3212.7	3177.9	3147.6	3061.3	2949.2	2800.7	2628.1	2461.4	2317.5
25°	3288.5	3280.9	3259.7	3243.0	3220.3	3156.7	3062.8	2920.4	2728.0	2544.8	2344.8
27.5°	3102.2	3123.4	3159.7	3177.9	3173.4	3164.3	3111.3	2991.6	2818.9	2600.8	2376.6
30°	2714.4	2791.7	2859.8	2950.7	2978.0	3044.6	3074.9	3006.7	2868.9	2665.9	2417.5
32.5°	2250.9	2363.0	2511.4	2561.4	2647.8	2776.5	2920.4	2946.2	2859.8	2703.8	2443.3
35°	1846.5	1938.9	2054.0	2132.7	2210.0	2419.0	2600.8	2758.3	2787.1	2684.1	2437.2
37.5°	1528.4	1593.5	1695.0	1761.6	1832.8	2011.6	2266.0	2470.5	2614.4	2617.5	2420.5
40°	1298.1	1326.9	1414.8	1463.2	1531.4	1685.9	1913.1	2179.7	2390.2	2487.2	2376.6
42.5°	1099.7	1137.6	1210.3	1246.6	1290.6	1425.4	1575.3	1828.3	2088.8	2296.3	2294.8
45°	981.5	1008.8	1042.1	1072.4	1122.4	1202.7	1373.9	1563.2	1813.1	2047.9	2140.3
47.5°	877.0	902.8	936.1	945.2	978.5	1054.3	1158.8	1323.9	1557.1	1790.4	1964.6
50°	789.2	810.4	833.1	849.8	864.9	927.0	1005.8	1145.1	1331.4	1557.1	1773.8
52.5°	721.0	736.2	755.9	764.9	778.6	824.0	884.6	987.6	1140.6	1346.6	1557.1
55°	657.4	668.0	680.1	695.3	701.3	734.6	781.6	869.5	983.1	1167.9	1367.8
57.5°	598.3	602.9	610.4	619.5	627.1	655.9	696.8	755.9	855.8	998.2	1187.6
60°	531.7	543.8	548.3	557.4	562.0	584.7	616.5	666.5	743.7	866.4	1008.8
62.5°	475.6	483.2	490.8	495.3	505.9	513.5	539.2	584.7	648.3	739.2	867.9
65°	425.6	428.7	433.2	437.8	440.8	449.9	474.1	504.4	552.9	633.2	733.1
67.5°	368.1	371.1	377.2	378.7	381.7	393.8	407.5	433.2	474.1	534.7	616.5
70°	312.0	316.6	319.6	322.6	327.2	331.7	346.9	368.1	399.9	442.3	505.9
72.5°	263.6	268.1	268.1	271.1	269.6	275.7	290.8	306.0	327.2	362.0	418.1
75°	215.1	215.1	218.1	219.6	221.2	227.2	233.3	245.4	262.0	289.3	324.2
77.5°	169.7	168.1	171.2	171.2	171.2	175.7	181.8	187.8	198.4	218.1	245.4
80°	124.2	124.2	127.2	128.8	125.7	127.2	130.3	136.3	143.9	157.5	172.7
82.5°	81.8	87.9	86.3	87.9	86.3	89.4	90.9	92.4	95.4	101.5	112.1
85°	50.0	50.0	50.0	51.5	50.0	51.5	51.5	51.5	53.0	56.0	60.6
87.5°	21.2	21.2	21.2	22.7	21.2	21.2	22.7	21.2	22.7	22.7	24.2
90°	9.9	9.6	9.9	9.6	9.2	8.9	8.5	8.2	8.5	7.5	6.5
92.5°	18.5	19.8	20.5	21.7	22.9	26.3	33.8	47.5	63.6	70.4	52.6
95°	43.4	46.5	53.0	59.2	65.3	83.4	123.0	164.4	202.7	180.5	124.4
97.5°	93.3	106.3	129.2	148.7	168.2	213.3	282.7	322.3	311.7	232.8	138.4
100°	227.3	252.2	286.8	311.0	335.3	375.3	403.0	391.0	323.7	218.7	128.9
102.5°	359.9	378.4	403.3	416.4	429.6	448.8	443.0	394.4	301.5	198.2	120.7
105°	447.4	460.4	476.1	480.6	485.0	478.5	444.3	372.9	274.8	182.2	117.6
107.5°	505.2	511.3	513.4	508.8	504.1	477.5	423.8	342.1	251.2	170.6	116.9
110°	533.9	531.1	521.6	509.6	497.6	454.6	391.7	313.4	231.7	164.4	118.6

TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	535.9	526.0	506.5	490.3	474.1	424.5	359.9	288.5	218.7	161.0	122.0
115°	520.2	505.2	479.5	460.9	442.3	392.0	332.6	269.3	210.2	160.6	125.8
117.5°	492.2	475.4	448.8	429.4	410.1	364.0	311.4	256.7	204.4	161.0	130.6
120°	463.1	444.0	417.0	399.8	382.5	341.4	295.3	247.1	200.6	162.4	136.0
122.5°	432.0	415.3	392.0	376.3	360.6	323.3	282.7	239.3	198.2	164.7	141.2
125°	406.0	391.0	369.1	355.5	341.8	309.0	271.7	232.8	196.2	167.1	146.6
127.5°	383.8	370.8	351.0	338.4	325.7	295.6	261.8	226.6	195.2	169.9	151.1
130°	364.7	352.4	334.3	322.6	311.0	283.3	252.6	221.8	194.1	172.6	155.5
132.5°	347.9	335.6	318.9	308.0	297.0	271.7	244.0	217.4	193.8	174.7	159.6
135°	329.5	319.2	302.5	292.8	283.0	260.8	236.5	213.6	193.5	176.7	163.0
137.5°	312.1	301.5	287.1	278.4	269.7	249.8	229.3	210.2	192.8	178.1	165.8
140°	294.3	284.7	271.7	264.4	257.0	240.6	223.2	207.1	192.4	179.4	167.8
142.5°	276.5	268.3	257.7	251.6	245.4	231.7	217.4	204.4	191.7	180.5	169.9
145°	260.8	253.6	245.1	240.2	235.2	224.2	212.9	202.0	191.1	180.8	171.2
147.5°	246.8	241.6	234.8	231.2	227.6	218.4	209.2	199.6	190.0	180.8	172.3
150°	235.5	231.7	226.6	223.4	220.1	212.9	205.1	197.2	188.7	180.8	172.6
152.5°	226.3	222.8	219.1	216.6	214.0	207.8	201.3	194.5	187.0	179.8	173.3
155°	218.1	215.3	212.3	210.2	208.2	203.0	197.6	191.7	184.9	179.1	173.3
157.5°	210.5	208.5	205.8	204.0	202.3	198.2	193.5	188.7	183.2	178.1	173.6
160°	204.0	202.0	199.6	198.4	197.2	193.8	190.0	185.6	181.1	177.4	173.6
162.5°	197.2	195.5	194.1	193.1	192.1	189.0	185.9	182.5	179.1	176.0	173.3
165°	191.4	190.0	188.7	187.8	187.0	184.6	182.5	179.8	177.0	174.7	172.6
167.5°	185.6	184.6	183.9	183.2	182.5	181.1	179.4	177.0	175.0	173.3	172.3
170°	180.5	179.8	179.4	179.1	178.8	177.4	176.4	174.7	172.9	171.9	171.2
172.5°	176.4	175.7	175.7	175.5	175.3	174.3	173.6	172.3	171.2	170.9	170.9
175°	172.6	172.3	172.3	172.3	172.3	171.6	171.2	170.6	169.9	169.9	170.2
177.5°	170.2	169.9	170.2	170.2	170.2	169.9	169.5	169.2	168.8	169.2	169.9
180°	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8

TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1605.6	1601.1	1601.1	1598.0	1589.0	1572.3	1570.8	1573.8	1564.7	1555.6	1542.0
5°	1684.4	1655.6	1646.5	1637.4	1619.2	1589.0	1576.8	1566.2	1549.6	1529.9	1508.7
7.5°	1751.0	1710.1	1698.0	1681.4	1645.0	1602.6	1575.3	1552.6	1529.9	1502.6	1476.9
10°	1834.3	1775.3	1746.5	1722.3	1672.3	1613.2	1572.3	1539.0	1502.6	1469.3	1436.0
12.5°	1928.3	1832.8	1823.7	1764.7	1707.1	1619.2	1569.3	1520.8	1472.3	1431.4	1396.6
15°	2007.0	1902.5	1864.6	1825.3	1714.7	1605.6	1557.1	1502.6	1446.6	1402.6	1351.1
17.5°	2057.0	1970.7	1890.4	1837.4	1722.3	1625.3	1531.4	1469.3	1410.2	1349.6	1307.2
20°	2117.6	1991.9	1922.2	1851.0	1737.4	1610.2	1516.2	1439.0	1366.3	1311.8	1260.3
22.5°	2178.2	2008.5	1951.0	1873.7	1740.4	1595.0	1489.0	1411.7	1328.4	1273.9	1217.8
25°	2172.1	2032.8	1937.3	1872.2	1710.1	1581.4	1457.2	1366.3	1289.0	1219.4	1163.3
27.5°	2176.7	2005.5	1908.6	1832.8	1688.9	1561.7	1423.8	1328.4	1248.1	1175.4	1116.4
30°	2178.2	1964.6	1879.8	1788.9	1649.5	1514.7	1386.0	1289.0	1204.2	1125.4	1072.4
32.5°	2173.6	1931.3	1825.3	1743.5	1587.4	1469.3	1342.1	1239.1	1152.7	1080.0	1030.0
35°	2163.0	1891.9	1769.2	1666.2	1523.8	1404.2	1301.2	1195.1	1102.7	1036.1	978.5
37.5°	2134.3	1849.5	1710.1	1608.6	1449.6	1328.4	1237.5	1149.7	1060.3	981.5	933.1
40°	2113.1	1791.9	1651.1	1540.5	1369.3	1251.2	1175.4	1092.1	1004.3	933.1	886.1
42.5°	2064.6	1737.4	1590.5	1458.7	1290.6	1169.4	1098.2	1031.5	955.8	886.1	843.7
45°	1985.8	1678.3	1516.2	1383.0	1204.2	1089.1	1024.0	969.4	902.8	836.1	793.7
47.5°	1875.2	1593.5	1437.5	1304.2	1119.4	1002.8	937.6	896.7	843.7	787.7	751.3
50°	1755.6	1501.1	1357.2	1225.4	1037.6	924.0	860.4	822.5	787.7	736.2	701.3
52.5°	1599.6	1402.6	1264.8	1139.1	949.7	840.7	784.6	757.4	721.0	684.7	654.4
55°	1448.1	1275.4	1161.8	1042.1	863.4	761.9	707.4	678.6	657.4	627.1	602.9
57.5°	1272.4	1157.3	1052.7	943.7	783.1	690.7	639.2	604.4	590.7	577.1	554.4
60°	1110.3	1022.4	937.6	846.7	699.8	616.5	566.5	539.2	525.6	516.5	501.4
62.5°	961.9	893.7	821.0	748.3	615.0	539.2	501.4	474.1	462.0	460.5	446.8
65°	819.5	771.0	711.9	640.7	536.2	469.6	433.2	416.6	402.9	402.9	392.3
67.5°	677.1	643.8	596.8	546.8	465.0	402.9	369.6	354.4	346.9	346.9	339.3
70°	563.5	540.8	498.3	454.4	383.2	336.3	310.5	296.9	292.3	293.9	287.8
72.5°	457.4	433.2	398.4	366.6	313.5	278.7	260.5	245.4	237.8	239.3	237.8
75°	354.4	342.3	312.0	287.8	245.4	221.2	204.5	196.9	190.9	192.4	189.3
77.5°	266.6	248.4	231.8	215.1	189.3	169.7	156.0	148.4	143.9	143.9	143.9
80°	181.8	178.7	165.1	156.0	134.8	119.7	109.1	107.5	103.0	103.0	103.0
82.5°	118.1	110.6	103.0	96.9	84.8	75.7	71.2	68.2	66.6	65.1	68.2
85°	65.1	60.6	57.6	51.5	47.0	42.4	37.9	36.4	34.8	36.4	34.8
87.5°	25.8	21.2	21.2	19.7	18.2	16.7	16.7	13.6	13.6	12.1	12.1
90°	5.5	4.4	4.1	3.8	3.1	2.1	1.4	0.7	1.4	2.1	3.1
92.5°	34.5	23.6	20.5	17.4	14.0	10.9	7.5	5.1	7.5	10.9	14.0
95°	73.5	44.4	37.8	31.1	22.2	16.4	12.6	11.6	12.6	16.4	22.2
97.5°	79.3	50.6	43.2	35.9	27.0	21.9	18.8	18.5	18.8	21.9	27.0
100°	78.3	54.3	47.6	41.0	32.8	28.0	25.6	25.3	25.6	28.0	32.8
102.5°	79.6	58.8	52.8	46.8	39.6	35.2	33.2	32.5	33.2	35.2	39.6
105°	82.4	63.9	58.6	53.3	46.8	42.7	40.7	39.6	40.7	42.7	46.8
107.5°	86.8	70.4	65.4	60.5	54.3	50.2	48.2	47.2	48.2	50.2	54.3
110°	92.6	77.2	72.4	67.7	61.9	58.1	56.4	55.4	56.4	58.1	61.9

TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	98.4	84.4	79.8	75.2	69.4	65.6	63.9	62.9	63.9	65.6	69.4
115°	104.9	91.9	87.3	82.7	76.9	73.5	71.4	70.1	71.4	73.5	76.9
117.5°	111.8	98.8	94.5	90.2	83.7	80.7	79.0	77.2	79.0	80.7	83.7
120°	118.3	106.0	101.7	97.4	90.9	87.5	85.8	84.8	85.8	87.5	90.9
122.5°	125.1	113.1	108.5	103.9	97.8	94.0	92.3	91.3	92.3	94.0	97.8
125°	131.6	119.6	115.0	110.4	103.9	100.1	98.1	97.4	98.1	100.1	103.9
127.5°	137.4	125.8	121.2	116.6	109.4	105.6	103.2	102.2	103.2	105.6	109.4
130°	142.5	131.2	126.6	122.0	114.8	110.7	107.7	106.6	107.7	110.7	114.8
132.5°	147.0	136.0	131.6	127.1	120.0	114.8	111.4	110.1	111.4	114.8	120.0
135°	151.4	140.8	136.2	131.6	124.4	119.3	115.5	114.2	115.5	119.3	124.4
137.5°	154.5	144.2	140.0	135.7	128.5	123.0	119.3	117.9	119.3	123.0	128.5
140°	157.6	147.7	143.4	139.1	132.3	126.8	123.4	121.7	123.4	126.8	132.3
142.5°	160.0	150.4	146.4	142.5	135.7	130.9	127.1	125.8	127.1	130.9	135.7
145°	162.0	153.1	149.2	145.3	139.5	134.3	131.2	130.2	131.2	134.3	139.5
147.5°	163.7	155.5	152.1	148.7	142.9	138.4	135.3	134.7	135.3	138.4	142.9
150°	165.4	157.6	154.5	151.4	146.6	142.2	139.5	139.1	139.5	142.2	146.6
152.5°	166.5	160.0	157.0	154.1	150.0	146.3	143.6	143.6	143.6	146.3	150.0
155°	167.8	162.0	159.6	157.2	153.5	150.0	148.0	148.0	148.0	150.0	153.5
157.5°	168.5	163.7	161.8	160.0	156.5	153.5	151.8	151.4	151.8	153.5	156.5
160°	169.5	165.4	163.7	162.0	159.6	156.9	155.5	155.5	155.5	156.9	159.6
162.5°	169.9	166.5	165.1	163.7	161.7	159.6	158.6	158.6	158.6	159.6	161.7
165°	170.2	167.5	166.3	165.1	163.7	162.0	161.3	161.7	161.3	162.0	163.7
167.5°	170.2	168.2	167.4	166.5	165.4	164.1	163.7	164.1	163.7	164.1	165.4
170°	169.9	168.2	167.8	167.5	166.8	165.8	165.4	166.1	165.4	165.8	166.8
172.5°	169.9	168.5	168.4	168.2	167.8	167.1	167.1	167.5	167.1	167.1	167.8
175°	169.5	168.8	168.6	168.5	168.5	167.8	168.2	168.5	168.2	167.8	168.5
177.5°	169.2	168.8	168.8	168.8	168.8	168.5	168.8	169.2	168.8	168.5	168.8
180°	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8

TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1539.0	1537.5	1540.5	1531.4	1516.2	1508.7	1487.5	1482.9	1481.4	1482.9	1484.4
5°	1496.6	1495.0	1490.5	1475.3	1457.2	1443.5	1417.8	1416.3	1407.2	1398.1	1402.6
7.5°	1455.7	1449.6	1440.5	1420.8	1396.6	1381.4	1360.2	1345.1	1333.0	1325.4	1319.3
10°	1414.8	1405.7	1396.6	1370.8	1340.5	1317.8	1292.1	1279.9	1266.3	1260.3	1254.2
12.5°	1361.7	1352.7	1336.0	1305.7	1287.5	1258.7	1233.0	1220.9	1213.3	1201.2	1193.6
15°	1319.3	1301.2	1292.1	1260.3	1222.4	1219.4	1172.4	1169.4	1154.2	1154.2	1142.1
17.5°	1270.9	1257.2	1240.6	1208.8	1181.5	1154.2	1130.0	1120.9	1107.3	1104.2	1098.2
20°	1223.9	1205.7	1199.7	1167.9	1139.1	1105.8	1080.0	1070.9	1064.9	1058.8	1063.3
22.5°	1175.4	1160.3	1145.1	1116.4	1095.2	1061.8	1046.7	1037.6	1028.5	1025.5	1027.0
25°	1128.5	1114.8	1099.7	1070.9	1048.2	1020.9	1007.3	1002.8	998.2	998.2	996.7
27.5°	1083.0	1069.4	1055.8	1030.0	1007.3	987.6	977.0	972.5	967.9	970.9	974.0
30°	1036.1	1024.0	1011.8	989.1	970.9	952.8	946.7	943.7	942.2	949.7	949.7
32.5°	993.7	983.1	974.0	952.8	934.6	919.4	914.9	916.4	917.9	922.5	925.5
35°	949.7	942.2	933.1	914.9	899.8	886.1	887.6	887.6	890.7	898.2	904.3
37.5°	910.4	899.8	892.2	877.0	864.9	852.8	857.3	861.9	864.9	874.0	877.0
40°	863.4	858.9	852.8	837.6	827.0	825.5	827.0	830.1	836.1	840.7	845.2
42.5°	825.5	819.5	811.9	799.8	790.7	792.2	793.7	796.7	799.8	807.4	811.9
45°	783.1	778.6	772.5	761.9	754.3	755.9	757.4	757.4	760.4	769.5	772.5
47.5°	736.2	737.7	730.1	719.5	715.0	715.0	715.0	718.0	725.6	728.6	730.1
50°	690.7	687.7	686.2	675.6	672.5	671.0	672.5	674.1	684.7	683.1	687.7
52.5°	642.2	642.2	640.7	634.7	630.1	630.1	627.1	634.7	637.7	640.7	645.3
55°	595.3	590.7	589.2	586.2	580.1	578.6	581.7	590.7	593.8	596.8	601.3
57.5°	543.8	543.8	540.8	536.2	536.2	536.2	536.2	542.3	546.8	549.8	558.9
60°	496.8	490.8	486.2	486.2	486.2	484.7	493.8	493.8	502.9	504.4	507.4
62.5°	440.8	437.8	434.7	436.2	434.7	437.8	440.8	446.8	448.4	452.9	457.4
65°	387.8	387.8	384.7	393.8	387.8	387.8	395.3	395.3	398.4	402.9	409.0
67.5°	336.3	337.8	334.8	334.8	337.8	339.3	340.8	346.9	348.4	354.4	362.0
70°	283.3	286.3	287.8	284.8	287.8	290.8	293.9	295.4	301.4	304.5	309.0
72.5°	236.3	239.3	234.8	236.3	237.8	240.8	242.4	245.4	248.4	257.5	260.5
75°	189.3	187.8	186.3	192.4	189.3	195.4	196.9	196.9	199.9	207.5	210.5
77.5°	145.4	145.4	146.9	143.9	148.4	146.9	148.4	153.0	157.5	157.5	169.7
80°	101.5	104.5	104.5	104.5	106.0	107.5	104.5	112.1	113.6	113.6	118.1
82.5°	65.1	66.6	65.1	68.2	68.2	71.2	69.7	71.2	74.2	77.3	78.8
85°	34.8	34.8	37.9	37.9	36.4	37.9	36.4	37.9	40.9	40.9	42.4
87.5°	12.1	12.1	12.1	12.1	13.6	12.1	13.6	13.6	12.1	12.1	16.7
90°	3.8	4.1	4.4	5.5	6.5	7.5	8.5	8.2	8.5	8.9	9.2
92.5°	17.4	20.5	23.6	34.5	52.6	70.4	63.6	47.5	33.8	26.3	22.9
95°	31.1	37.8	44.4	73.5	124.4	180.5	202.7	164.4	123.0	83.4	65.3
97.5°	35.9	43.2	50.6	79.3	138.4	232.8	311.7	322.3	282.7	213.3	168.2
100°	41.0	47.6	54.3	78.3	128.9	218.7	323.7	391.0	403.0	375.3	335.3
102.5°	46.8	52.8	58.8	79.6	120.7	198.2	301.5	394.4	443.0	448.8	429.6
105°	53.3	58.6	63.9	82.4	117.6	182.2	274.8	372.9	444.3	478.5	485.0
107.5°	60.5	65.4	70.4	86.8	116.9	170.6	251.2	342.1	423.8	477.5	504.1
110°	67.7	72.4	77.2	92.6	118.6	164.4	231.7	313.4	391.7	454.6	497.6

TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	75.2	79.8	84.4	98.4	122.0	161.0	218.7	288.5	359.9	424.5	474.1
115°	82.7	87.3	91.9	104.9	125.8	160.6	210.2	269.3	332.6	392.0	442.3
117.5°	90.2	94.5	98.8	111.8	130.6	161.0	204.4	256.7	311.4	364.0	410.1
120°	97.4	101.7	106.0	118.3	136.0	162.4	200.6	247.1	295.3	341.4	382.5
122.5°	103.9	108.5	113.1	125.1	141.2	164.7	198.2	239.3	282.7	323.3	360.6
125°	110.4	115.0	119.6	131.6	146.6	167.1	196.2	232.8	271.7	309.0	341.8
127.5°	116.6	121.2	125.8	137.4	151.1	169.9	195.2	226.6	261.8	295.6	325.7
130°	122.0	126.6	131.2	142.5	155.5	172.6	194.1	221.8	252.6	283.3	311.0
132.5°	127.1	131.6	136.0	147.0	159.6	174.7	193.8	217.4	244.0	271.7	297.0
135°	131.6	136.2	140.8	151.4	163.0	176.7	193.5	213.6	236.5	260.8	283.0
137.5°	135.7	140.0	144.2	154.5	165.8	178.1	192.8	210.2	229.3	249.8	269.7
140°	139.1	143.4	147.7	157.6	167.8	179.4	192.4	207.1	223.2	240.6	257.0
142.5°	142.5	146.4	150.4	160.0	169.9	180.5	191.7	204.4	217.4	231.7	245.4
145°	145.3	149.2	153.1	162.0	171.2	180.8	191.1	202.0	212.9	224.2	235.2
147.5°	148.7	152.1	155.5	163.7	172.3	180.8	190.0	199.6	209.2	218.4	227.6
150°	151.4	154.5	157.6	165.4	172.6	180.8	188.7	197.2	205.1	212.9	220.1
152.5°	154.1	157.0	160.0	166.5	173.3	179.8	187.0	194.5	201.3	207.8	214.0
155°	157.2	159.6	162.0	167.8	173.3	179.1	184.9	191.7	197.6	203.0	208.2
157.5°	160.0	161.8	163.7	168.5	173.6	178.1	183.2	188.7	193.5	198.2	202.3
160°	162.0	163.7	165.4	169.5	173.6	177.4	181.1	185.6	190.0	193.8	197.2
162.5°	163.7	165.1	166.5	169.9	173.3	176.0	179.1	182.5	185.9	189.0	192.1
165°	165.1	166.3	167.5	170.2	172.6	174.7	177.0	179.8	182.5	184.6	187.0
167.5°	166.5	167.4	168.2	170.2	172.3	173.3	175.0	177.0	179.4	181.1	182.5
170°	167.5	167.8	168.2	169.9	171.2	171.9	172.9	174.7	176.4	177.4	178.8
172.5°	168.2	168.4	168.5	169.9	170.9	170.9	171.2	172.3	173.6	174.3	175.3
175°	168.5	168.6	168.8	169.5	170.2	169.9	169.9	170.6	171.2	171.6	172.3
177.5°	168.8	168.8	168.8	169.2	169.9	169.2	168.8	169.2	169.5	169.9	170.2
180°	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8

TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1482.9	1484.4	1478.4	1473.8	1486.0	1478.4	1478.4	1479.9	1476.9	1481.4	1479.9
5°	1399.6	1401.1	1390.5	1393.6	1387.5	1386.0	1384.5	1393.6	1392.0	1390.5	1393.6
7.5°	1317.8	1317.8	1313.3	1310.2	1310.2	1305.7	1311.8	1310.2	1313.3	1313.3	1317.8
10°	1249.7	1252.7	1245.1	1237.5	1236.0	1237.5	1237.5	1239.1	1240.6	1251.2	1249.7
12.5°	1193.6	1189.1	1187.6	1183.0	1175.4	1172.4	1169.4	1186.0	1181.5	1181.5	1181.5
15°	1131.5	1142.1	1140.6	1127.0	1123.9	1130.0	1127.0	1127.0	1142.1	1140.6	1139.1
17.5°	1098.2	1095.2	1092.1	1084.5	1086.1	1084.5	1086.1	1086.1	1095.2	1095.2	1095.2
20°	1060.3	1054.3	1054.3	1051.2	1051.2	1046.7	1052.7	1054.3	1060.3	1060.3	1061.8
22.5°	1027.0	1022.4	1022.4	1020.9	1024.0	1017.9	1024.0	1025.5	1025.5	1030.0	1030.0
25°	998.2	995.2	995.2	998.2	998.2	998.2	998.2	1004.3	999.7	1001.2	999.7
27.5°	972.5	974.0	975.5	977.0	975.5	977.0	978.5	981.5	983.1	981.5	978.5
30°	948.2	952.8	954.3	954.3	957.3	958.8	960.3	960.3	961.9	957.3	960.3
32.5°	930.0	930.0	933.1	934.6	937.6	939.1	939.1	942.2	940.6	936.1	937.6
35°	904.3	904.3	910.4	913.4	917.9	916.4	917.9	917.9	919.4	916.4	911.9
37.5°	878.5	881.6	881.6	887.6	889.1	890.7	889.1	892.2	890.7	887.6	886.1
40°	848.3	846.7	848.3	852.8	854.3	854.3	854.3	857.3	857.3	857.3	855.8
42.5°	810.4	814.9	813.4	818.0	816.4	816.4	819.5	822.5	824.0	819.5	821.0
45°	774.0	774.0	777.1	777.1	778.6	778.6	784.6	781.6	784.6	781.6	783.1
47.5°	734.6	736.2	736.2	737.7	740.7	743.7	740.7	742.2	742.2	743.7	740.7
50°	690.7	690.7	693.7	698.3	704.4	701.3	699.8	705.9	701.3	701.3	698.3
52.5°	645.3	649.8	651.3	655.9	660.4	661.9	663.5	660.4	661.9	657.4	658.9
55°	601.3	602.9	608.9	613.5	618.0	618.0	616.5	618.0	619.5	613.5	613.5
57.5°	557.4	562.0	568.0	568.0	574.1	574.1	572.6	572.6	574.1	569.5	568.0
60°	510.5	515.0	522.6	522.6	531.7	533.2	530.2	527.1	527.1	522.6	524.1
62.5°	460.5	465.0	469.6	477.1	483.2	480.2	486.2	480.2	481.7	472.6	472.6
65°	416.6	418.1	425.6	433.2	433.2	436.2	433.2	434.7	430.2	430.2	424.1
67.5°	365.1	365.1	372.6	380.2	387.8	387.8	387.8	383.2	383.2	378.7	378.7
70°	319.6	318.1	325.7	330.2	334.8	336.3	333.2	331.7	328.7	324.2	322.6
72.5°	263.6	266.6	274.2	277.2	284.8	283.3	290.8	281.7	281.7	274.2	272.7
75°	213.6	216.6	224.2	228.7	233.3	233.3	237.8	233.3	227.2	224.2	222.7
77.5°	169.7	168.1	174.2	181.8	183.3	181.8	184.8	183.3	177.2	177.2	174.2
80°	121.2	125.7	131.8	130.3	136.3	134.8	134.8	131.8	131.8	127.2	130.3
82.5°	80.3	84.8	86.3	84.8	86.3	89.4	90.9	89.4	89.4	86.3	87.9
85°	42.4	42.4	45.4	47.0	45.4	45.4	47.0	51.5	48.5	45.4	48.5
87.5°	13.6	12.1	12.1	13.6	12.1	12.1	13.6	13.6	15.1	15.1	15.1
90°	9.6	9.9	9.6	9.9	10.3	9.9	10.3	9.9	9.6	9.9	9.6
92.5°	21.7	20.5	19.8	18.5	18.8	18.1	18.8	18.5	19.8	20.5	21.7
95°	59.2	53.0	46.5	43.4	41.0	39.6	41.0	43.4	46.5	53.0	59.2
97.5°	148.7	129.2	106.3	93.3	85.1	81.3	85.1	93.3	106.3	129.2	148.7
100°	311.0	286.8	252.2	227.3	214.0	214.3	214.0	227.3	252.2	286.8	311.0
102.5°	416.4	403.3	378.4	359.9	349.3	339.4	349.3	359.9	378.4	403.3	416.4
105°	480.6	476.1	460.4	447.4	436.5	434.8	436.5	447.4	460.4	476.1	480.6
107.5°	508.8	513.4	511.3	505.2	500.7	497.0	500.7	505.2	511.3	513.4	508.8
110°	509.6	521.6	531.1	533.9	533.2	532.5	533.2	533.9	531.1	521.6	509.6

TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	490.3	506.5	526.0	535.9	539.3	539.7	539.3	535.9	526.0	506.5	490.3
115°	460.9	479.5	505.2	520.2	527.0	528.7	527.0	520.2	505.2	479.5	460.9
117.5°	429.4	448.8	475.4	492.2	502.4	504.8	502.4	492.2	475.4	448.8	429.4
120°	399.8	417.0	444.0	463.1	471.3	473.4	471.3	463.1	444.0	417.0	399.8
122.5°	376.3	392.0	415.3	432.0	441.3	444.0	441.3	432.0	415.3	392.0	376.3
125°	355.5	369.1	391.0	406.0	414.6	417.0	414.6	406.0	391.0	369.1	355.5
127.5°	338.4	351.0	370.8	383.8	391.7	393.7	391.7	383.8	370.8	351.0	338.4
130°	322.6	334.3	352.4	364.7	371.9	374.6	371.9	364.7	352.4	334.3	322.6
132.5°	308.0	318.9	335.6	347.9	354.1	355.8	354.1	347.9	335.6	318.9	308.0
135°	292.8	302.5	319.2	329.5	335.6	338.0	335.6	329.5	319.2	302.5	292.8
137.5°	278.4	287.1	301.5	312.1	317.2	319.2	317.2	312.1	301.5	287.1	278.4
140°	264.4	271.7	284.7	294.3	299.8	299.4	299.8	294.3	284.7	271.7	264.4
142.5°	251.6	257.7	268.3	276.5	281.3	281.0	281.3	276.5	268.3	257.7	251.6
145°	240.2	245.1	253.6	260.8	263.5	264.2	263.5	260.8	253.6	245.1	240.2
147.5°	231.2	234.8	241.6	246.8	249.5	249.8	249.5	246.8	241.6	234.8	231.2
150°	223.4	226.6	231.7	235.5	237.5	237.5	237.5	235.5	231.7	226.6	223.4
152.5°	216.6	219.1	222.8	226.3	227.3	227.3	227.3	226.3	222.8	219.1	216.6
155°	210.2	212.3	215.3	218.1	218.7	219.1	218.7	218.1	215.3	212.3	210.2
157.5°	204.0	205.8	208.5	210.5	211.2	211.2	211.2	210.5	208.5	205.8	204.0
160°	198.4	199.6	202.0	204.0	204.0	203.7	204.0	204.0	202.0	199.6	198.4
162.5°	193.1	194.1	195.5	197.2	197.2	196.9	197.2	197.2	195.5	194.1	193.1
165°	187.8	188.7	190.0	191.4	191.1	191.1	191.1	191.4	190.0	188.7	187.8
167.5°	183.2	183.9	184.6	185.6	185.3	185.3	185.3	185.6	184.6	183.9	183.2
170°	179.1	179.4	179.8	180.5	180.1	180.1	180.1	180.5	179.8	179.4	179.1
172.5°	175.5	175.7	175.7	176.4	175.7	175.3	175.7	176.4	175.7	175.7	175.5
175°	172.3	172.3	172.3	172.6	172.3	171.9	172.3	172.6	172.3	172.3	172.3
177.5°	170.2	170.2	169.9	170.2	169.5	169.5	169.5	170.2	169.9	170.2	170.2
180°	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8

TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1484.4	1487.5	1489.0	1482.9	1478.4	1486.0	1496.6	1504.1	1510.2	1517.8	1522.3
5°	1396.6	1407.2	1407.2	1410.2	1414.8	1422.3	1442.0	1455.7	1467.8	1476.9	1484.4
7.5°	1322.4	1329.9	1334.5	1342.1	1349.6	1360.2	1383.0	1402.6	1420.8	1431.4	1443.5
10°	1255.7	1261.8	1269.3	1273.9	1287.5	1302.7	1331.4	1348.1	1369.3	1386.0	1401.1
12.5°	1192.1	1213.3	1217.8	1216.3	1228.4	1245.1	1273.9	1299.6	1322.4	1339.0	1355.7
15°	1146.7	1154.2	1163.3	1161.8	1187.6	1192.1	1216.3	1246.6	1276.9	1287.5	1302.7
17.5°	1096.7	1108.8	1117.9	1122.4	1130.0	1146.7	1169.4	1192.1	1231.5	1233.0	1272.4
20°	1057.3	1069.4	1075.5	1081.5	1086.1	1105.8	1125.4	1151.2	1183.0	1199.7	1220.9
22.5°	1031.5	1037.6	1042.1	1046.7	1052.7	1063.3	1087.6	1116.4	1137.6	1155.7	1169.4
25°	1001.2	1007.3	1013.4	1016.4	1020.9	1027.0	1045.2	1067.9	1098.2	1110.3	1123.9
27.5°	980.0	980.0	983.1	983.1	989.1	995.2	1008.8	1030.0	1054.3	1069.4	1087.6
30°	957.3	955.8	957.3	955.8	954.3	963.4	975.5	993.7	1010.3	1028.5	1040.6
32.5°	934.6	933.1	933.1	934.6	928.5	933.1	939.1	955.8	974.0	983.1	996.7
35°	910.4	907.3	907.3	907.3	904.3	901.3	907.3	922.5	934.6	946.7	957.3
37.5°	886.1	881.6	881.6	878.5	875.5	871.0	871.0	883.1	899.8	904.3	917.9
40°	852.8	852.8	849.8	848.3	845.2	842.2	837.6	848.3	863.4	867.9	878.5
42.5°	819.5	814.9	813.4	813.4	813.4	808.9	805.8	813.4	822.5	830.1	836.1
45°	781.6	778.6	780.1	778.6	775.5	774.0	772.5	775.5	786.1	789.2	796.7
47.5°	740.7	739.2	739.2	737.7	736.2	737.7	731.6	739.2	742.2	745.2	751.3
50°	698.3	696.8	695.3	693.7	693.7	695.3	693.7	693.7	699.8	702.8	708.9
52.5°	655.9	651.3	651.3	649.8	649.8	646.8	649.8	651.3	654.4	657.4	660.4
55°	610.4	610.4	605.9	605.9	602.9	602.9	604.4	602.9	608.9	612.0	612.0
57.5°	566.5	560.5	562.0	558.9	555.9	554.4	554.4	557.4	560.5	560.5	563.5
60°	519.6	513.5	512.0	505.9	509.0	504.4	505.9	505.9	512.0	509.0	512.0
62.5°	472.6	465.0	460.5	457.4	457.4	459.0	455.9	454.4	457.4	460.5	466.5
65°	422.6	418.1	413.5	409.0	409.0	407.5	410.5	405.9	404.4	405.9	409.0
67.5°	371.1	366.6	362.0	357.5	359.0	354.4	351.4	356.0	352.9	354.4	357.5
70°	321.1	318.1	309.0	306.0	304.5	306.0	304.5	301.4	306.0	304.5	306.0
72.5°	271.1	268.1	263.6	256.0	256.0	254.5	253.0	253.0	251.4	251.4	251.4
75°	222.7	216.6	212.1	210.5	207.5	206.0	204.5	201.5	203.0	204.5	201.5
77.5°	172.7	165.1	163.6	163.6	159.0	159.0	160.6	159.0	157.5	157.5	157.5
80°	127.2	121.2	121.2	118.1	115.1	115.1	115.1	115.1	113.6	112.1	113.6
82.5°	81.8	80.3	78.8	78.8	81.8	75.7	78.8	77.3	75.7	75.7	74.2
85°	45.4	47.0	45.4	47.0	43.9	45.4	45.4	45.4	43.9	45.4	42.4
87.5°	16.7	16.7	16.7	18.2	18.2	18.2	18.2	18.2	19.7	18.2	18.2
90°	9.2	8.9	8.5	8.2	8.5	7.5	6.5	5.5	4.4	4.1	3.8
92.5°	22.9	26.3	33.8	47.5	63.6	70.4	52.6	34.5	23.6	20.5	17.4
95°	65.3	83.4	123.0	164.4	202.7	180.5	124.4	73.5	44.4	37.8	31.1
97.5°	168.2	213.3	282.7	322.3	311.7	232.8	138.4	79.3	50.6	43.2	35.9
100°	335.3	375.3	403.0	391.0	323.7	218.7	128.9	78.3	54.3	47.6	41.0
102.5°	429.6	448.8	443.0	394.4	301.5	198.2	120.7	79.6	58.8	52.8	46.8
105°	485.0	478.5	444.3	372.9	274.8	182.2	117.6	82.4	63.9	58.6	53.3
107.5°	504.1	477.5	423.8	342.1	251.2	170.6	116.9	86.8	70.4	65.4	60.5
110°	497.6	454.6	391.7	313.4	231.7	164.4	118.6	92.6	77.2	72.4	67.7

TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	474.1	424.5	359.9	288.5	218.7	161.0	122.0	98.4	84.4	79.8	75.2
115°	442.3	392.0	332.6	269.3	210.2	160.6	125.8	104.9	91.9	87.3	82.7
117.5°	410.1	364.0	311.4	256.7	204.4	161.0	130.6	111.8	98.8	94.5	90.2
120°	382.5	341.4	295.3	247.1	200.6	162.4	136.0	118.3	106.0	101.7	97.4
122.5°	360.6	323.3	282.7	239.3	198.2	164.7	141.2	125.1	113.1	108.5	103.9
125°	341.8	309.0	271.7	232.8	196.2	167.1	146.6	131.6	119.6	115.0	110.4
127.5°	325.7	295.6	261.8	226.6	195.2	169.9	151.1	137.4	125.8	121.2	116.6
130°	311.0	283.3	252.6	221.8	194.1	172.6	155.5	142.5	131.2	126.6	122.0
132.5°	297.0	271.7	244.0	217.4	193.8	174.7	159.6	147.0	136.0	131.6	127.1
135°	283.0	260.8	236.5	213.6	193.5	176.7	163.0	151.4	140.8	136.2	131.6
137.5°	269.7	249.8	229.3	210.2	192.8	178.1	165.8	154.5	144.2	140.0	135.7
140°	257.0	240.6	223.2	207.1	192.4	179.4	167.8	157.6	147.7	143.4	139.1
142.5°	245.4	231.7	217.4	204.4	191.7	180.5	169.9	160.0	150.4	146.4	142.5
145°	235.2	224.2	212.9	202.0	191.1	180.8	171.2	162.0	153.1	149.2	145.3
147.5°	227.6	218.4	209.2	199.6	190.0	180.8	172.3	163.7	155.5	152.1	148.7
150°	220.1	212.9	205.1	197.2	188.7	180.8	172.6	165.4	157.6	154.5	151.4
152.5°	214.0	207.8	201.3	194.5	187.0	179.8	173.3	166.5	160.0	157.0	154.1
155°	208.2	203.0	197.6	191.7	184.9	179.1	173.3	167.8	162.0	159.6	157.2
157.5°	202.3	198.2	193.5	188.7	183.2	178.1	173.6	168.5	163.7	161.8	160.0
160°	197.2	193.8	190.0	185.6	181.1	177.4	173.6	169.5	165.4	163.7	162.0
162.5°	192.1	189.0	185.9	182.5	179.1	176.0	173.3	169.9	166.5	165.1	163.7
165°	187.0	184.6	182.5	179.8	177.0	174.7	172.6	170.2	167.5	166.3	165.1
167.5°	182.5	181.1	179.4	177.0	175.0	173.3	172.3	170.2	168.2	167.4	166.5
170°	178.8	177.4	176.4	174.7	172.9	171.9	171.2	169.9	168.2	167.8	167.5
172.5°	175.3	174.3	173.6	172.3	171.2	170.9	170.9	169.9	168.5	168.4	168.2
175°	172.3	171.6	171.2	170.6	169.9	169.9	170.2	169.5	168.8	168.6	168.5
177.5°	170.2	169.9	169.5	169.2	168.8	169.2	169.9	169.2	168.8	168.8	168.8
180°	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8	168.8

TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1563.2	1563.2	1563.2	1563.2
2.5°	1529.9	1534.4	1549.6	1567.7
5°	1499.6	1511.7	1532.9	1561.7
7.5°	1466.3	1484.4	1514.7	1551.1
10°	1428.4	1454.1	1492.0	1537.5
12.5°	1387.5	1420.8	1469.3	1516.2
15°	1361.7	1395.1	1439.0	1490.5
17.5°	1311.8	1351.1	1396.6	1469.3
20°	1260.3	1304.2	1363.3	1436.0
22.5°	1220.9	1267.8	1323.9	1401.1
25°	1173.9	1222.4	1283.0	1363.3
27.5°	1123.9	1172.4	1240.6	1325.4
30°	1086.1	1133.0	1198.2	1289.0
32.5°	1040.6	1086.1	1154.2	1249.7
35°	989.1	1040.6	1105.8	1202.7
37.5°	949.7	996.7	1064.9	1157.3
40°	907.3	948.2	1014.9	1105.8
42.5°	861.9	907.3	964.9	1055.8
45°	819.5	852.8	911.9	998.2
47.5°	774.0	811.9	857.3	924.0
50°	725.6	757.4	807.4	852.8
52.5°	678.6	704.4	746.8	781.6
55°	628.6	654.4	686.2	707.4
57.5°	581.7	599.8	621.0	634.7
60°	524.1	542.3	555.9	569.5
62.5°	472.6	486.2	493.8	501.4
65°	419.6	427.2	431.7	437.8
67.5°	362.0	369.6	371.1	380.2
70°	309.0	310.5	313.5	318.1
72.5°	259.0	262.0	260.5	263.6
75°	207.5	210.5	207.5	210.5
77.5°	157.5	160.6	160.6	165.1
80°	113.6	115.1	116.6	116.6
82.5°	74.2	78.8	75.7	77.3
85°	42.4	43.9	43.9	45.4
87.5°	19.7	21.2	19.7	22.7
90°	3.1	2.1	1.4	0.7
92.5°	14.0	10.9	7.5	5.1
95°	22.2	16.4	12.6	11.6
97.5°	27.0	21.9	18.8	18.5
100°	32.8	28.0	25.6	25.3
102.5°	39.6	35.2	33.2	32.5
105°	46.8	42.7	40.7	39.6
107.5°	54.3	50.2	48.2	47.2
110°	61.9	58.1	56.4	55.4

TEST NUMBER: P1011366

CATALOG NUMBER: S123DIP-B1165D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	69.4	65.6	63.9	62.9
115°	76.9	73.5	71.4	70.1
117.5°	83.7	80.7	79.0	77.2
120°	90.9	87.5	85.8	84.8
122.5°	97.8	94.0	92.3	91.3
125°	103.9	100.1	98.1	97.4
127.5°	109.4	105.6	103.2	102.2
130°	114.8	110.7	107.7	106.6
132.5°	120.0	114.8	111.4	110.1
135°	124.4	119.3	115.5	114.2
137.5°	128.5	123.0	119.3	117.9
140°	132.3	126.8	123.4	121.7
142.5°	135.7	130.9	127.1	125.8
145°	139.5	134.3	131.2	130.2
147.5°	142.9	138.4	135.3	134.7
150°	146.6	142.2	139.5	139.1
152.5°	150.0	146.3	143.6	143.6
155°	153.5	150.0	148.0	148.0
157.5°	156.5	153.5	151.8	151.4
160°	159.6	156.9	155.5	155.5
162.5°	161.7	159.6	158.6	158.6
165°	163.7	162.0	161.3	161.7
167.5°	165.4	164.1	163.7	164.1
170°	166.8	165.8	165.4	166.1
172.5°	167.8	167.1	167.1	167.5
175°	168.5	167.8	168.2	168.5
177.5°	168.8	168.5	168.8	169.2
180°	168.8	168.8	168.8	168.8

(END OF REPORT)