

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011664

Luminaire Tested: S123DIP-B340D805UB40-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011664
REPORT IS A COMBINATION OF REPORTS P989907 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D805UB40-4F0-XX-W2A-F
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4482.0 lumens
Efficiency: N/A
Efficacy: 131.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011664

CATALOG NUMBER: S123DIP-B340D805UB40-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1011664

CATALOG NUMBER: S123DIP-B340D805UB40-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38
1	93	89	85	82	84	80	77	74	63	61	59	48	47	45	34	33	32
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	30	28	27
3	77	68	61	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	60	53	47	63	54	48	43	43	39	35	33	30	27	23	21	20
5	65	54	46	40	58	48	42	37	39	34	30	30	26	23	21	19	17
6	60	48	40	34	53	43	37	32	35	30	26	27	23	20	19	17	15
7	55	43	35	30	49	39	32	28	31	26	23	24	21	18	17	15	13
8	51	39	32	26	46	35	29	24	29	24	20	22	19	16	16	14	12
9	47	36	28	23	42	32	26	22	26	21	18	20	17	14	15	12	11
10	44	32	25	21	40	30	23	19	24	19	16	19	15	13	14	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5646	5646	5646
5°	5659	5450	5442
10°	5610	5266	5212
15°	5531	5074	4961
20°	5442	4861	4713
25°	5326	4637	4446
30°	5200	4404	4166
35°	5066	4167	3888
40°	4928	3917	3615
45°	4775	3674	3329
50°	4620	3403	3043
55°	4421	3121	2752
60°	4216	2809	2443
65°	4022	2472	2121
70°	3746	2100	1745
75°	3344	1662	1355
80°	2888	1169	958
85°	2257	627	479

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4775 cd/sqm

TEST NUMBER: P1011664

CATALOG NUMBER: S123DIP-B340D805UB40-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.4	1.1
10°-20°	139.6	3.1
20°-30°	206.2	4.6
30°-40°	240.8	5.4
40°-50°	242.1	5.4
50°-60°	212.7	4.7
60°-70°	158.4	3.5
70°-80°	90.1	2.0
80°-90°	27.7	0.6
90°-100°	36.0	0.8
100°-110°	174.2	3.9
110°-120°	426.9	9.5
120°-130°	541.9	12.1
130°-140°	578.9	12.9
140°-150°	541.4	12.1
150°-160°	436.7	9.7
160°-170°	281.8	6.3
170°-180°	97.1	2.2
0°-30°	395.3	8.8
0°-40°	636.1	14.2
0°-60°	1090.8	24.3
0°-90°	1367.0	30.5
90°-120°	637.1	14.2
90°-150°	2299.4	51.3
90°-180°	3115.0	69.5
0°-180°	4482.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	524	524	524	524	524	
5°	525	523	518	522	521	50
15°	500	498	492	496	493	141
25°	454	451	445	446	444	209
35°	392	390	384	381	379	245
45°	322	320	314	308	306	248
55°	244	244	238	233	230	219
65°	166	164	160	156	155	164
75°	88	86	85	82	81	94
85°	24	22	22	22	22	25
90°	1	8	18	21	23	4
95°	46	15	24	29	29	55
105°	226	235	166	32	33	240
115°	424	429	436	443	446	419
125°	598	604	607	609	610	534
135°	745	749	752	755	752	573
145°	859	865	866	868	868	538
155°	947	945	946	950	945	436
165°	998	996	995	1001	996	282
175°	1022	1018	1019	1024	1018	97
180°	1022	1022	1022	1022	1022	

TEST NUMBER: P1011664

CATALOG NUMBER: S123DIP-B340D805UB40-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	524.5	524.5	524.5	524.5	524.5
2.5°	526.7	524.9	520.0	524.5	524.0
5°	524.9	522.7	517.7	522.2	521.3
7.5°	520.9	518.6	513.7	517.7	517.3
10°	515.5	513.2	507.3	511.4	510.5
12.5°	508.2	506.4	501.0	503.7	503.3
15°	499.7	497.9	492.0	495.6	492.9
17.5°	490.2	488.0	482.1	484.8	483.9
20°	479.4	476.7	470.8	472.6	471.3
22.5°	467.2	464.5	458.6	460.0	458.2
25°	453.7	451.0	445.1	445.6	444.2
27.5°	439.7	437.0	430.7	431.1	429.8
30°	424.4	422.1	415.8	415.8	412.6
32.5°	409.0	405.9	401.4	398.2	396.9
35°	392.3	389.6	383.8	381.1	378.8
37.5°	375.7	372.1	366.2	363.0	361.7
40°	358.1	355.4	349.1	345.4	343.6
42.5°	340.5	337.3	331.0	327.4	325.6
45°	321.5	319.7	313.9	308.5	306.2
47.5°	303.1	300.3	294.9	289.5	287.7
50°	284.1	281.9	276.0	271.0	268.3
52.5°	264.3	262.9	256.6	252.5	249.8
55°	244.0	243.5	237.7	232.7	230.4
57.5°	225.0	223.2	218.7	214.2	211.5
60°	204.3	203.8	198.4	194.4	192.1
62.5°	185.8	184.4	179.0	175.0	173.6
65°	166.4	164.2	159.6	156.0	154.7
67.5°	145.7	143.9	140.3	137.1	135.3
70°	127.2	124.5	121.8	118.6	116.4
72.5°	107.8	106.0	102.8	100.1	99.2
75°	87.9	86.1	84.8	82.5	81.2
77.5°	70.4	69.5	67.6	65.8	65.8
80°	53.2	51.9	51.0	50.5	50.5
82.5°	36.5	36.5	36.5	35.6	35.2
85°	23.5	22.5	22.5	21.6	21.6
87.5°	11.7	10.4	9.9	9.5	9.5
90°	0.8	8.4	18.2	21.3	22.8
92.5°	17.5	12.9	19.7	25.1	25.8
95°	46.3	15.2	23.5	28.8	28.8
97.5°	84.3	63.0	24.3	30.4	31.1
100°	128.3	143.5	25.1	31.1	31.9
102.5°	178.4	188.3	56.2	31.1	32.6
105°	226.2	234.6	166.2	31.9	33.4
107.5°	277.1	283.9	295.3	178.4	78.9
110°	327.9	334.0	342.4	317.3	208.8

TEST NUMBER: P1011664

CATALOG NUMBER: S123DIP-B340D805UB40-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.5	381.8	390.2	397.0	395.5
115°	424.3	428.9	435.7	443.3	446.4
117.5°	471.4	476.7	480.5	486.6	487.4
120°	514.7	521.5	523.8	529.9	529.9
122.5°	558.7	564.0	567.1	570.9	571.6
125°	598.2	604.3	607.3	608.8	610.3
127.5°	637.7	643.7	647.5	649.8	648.3
130°	674.1	680.2	683.2	686.2	684.7
132.5°	709.0	715.1	717.4	720.4	718.1
135°	744.7	749.2	752.3	754.6	752.3
137.5°	775.1	781.1	782.7	786.4	784.9
140°	805.4	810.0	812.3	815.3	813.8
142.5°	833.5	838.1	840.3	842.6	840.3
145°	859.3	864.6	866.2	867.7	867.7
147.5°	884.4	888.2	889.7	891.2	887.4
150°	907.1	909.4	910.9	912.5	910.2
152.5°	927.6	928.4	929.2	932.2	928.4
155°	946.6	945.1	945.9	949.7	945.1
157.5°	961.8	961.8	961.0	965.6	959.5
160°	975.5	974.7	973.9	978.5	973.2
162.5°	988.4	986.1	985.3	990.6	986.1
165°	998.2	996.0	995.2	1001.3	996.0
167.5°	1006.6	1003.6	1003.6	1009.6	1003.6
170°	1013.4	1010.4	1010.4	1016.5	1010.4
172.5°	1018.0	1014.2	1014.9	1021.0	1014.2
175°	1021.8	1018.0	1018.7	1024.0	1018.0
177.5°	1023.3	1019.5	1020.3	1026.3	1018.7
180°	1021.8	1021.8	1021.8	1021.8	1021.8

(END OF REPORT)