

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011666

Luminaire Tested: S123DIP-B340D805UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011666
REPORT IS A COMBINATION OF REPORTS P989909 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D805UB40-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4194.6 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011666

CATALOG NUMBER: S123DIP-B340D805UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011666

CATALOG NUMBER: S123DIP-B340D805UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	82	84	81	78	75	64	62	60	49	48	47	35	35	34
2	85	78	72	67	77	71	66	61	56	53	50	43	41	39	31	30	28
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	28	26	24
4	71	61	53	47	64	55	48	43	44	39	35	34	31	28	25	22	21
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13
9	48	36	28	24	43	33	26	22	27	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5646	5646	5646
5°	5659	5450	5442
10°	5610	5266	5212
15°	5531	5074	4961
20°	5442	4861	4713
25°	5326	4637	4446
30°	5200	4404	4166
35°	5066	4167	3888
40°	4928	3917	3615
45°	4775	3674	3329
50°	4620	3403	3043
55°	4421	3121	2752
60°	4216	2809	2443
65°	4022	2472	2121
70°	3746	2100	1745
75°	3344	1662	1355
80°	2888	1169	958
85°	2257	627	479

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4775 cd/sqm

TEST NUMBER: P1011666

CATALOG NUMBER: S123DIP-B340D805UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.4	1.2
10°-20°	139.6	3.3
20°-30°	206.2	4.9
30°-40°	240.8	5.7
40°-50°	242.1	5.8
50°-60°	212.7	5.1
60°-70°	158.4	3.8
70°-80°	90.1	2.1
80°-90°	27.7	0.7
90°-100°	213.1	5.1
100°-110°	595.7	14.2
110°-120°	580.8	13.8
120°-130°	462.5	11.0
130°-140°	365.1	8.7
140°-150°	272.4	6.5
150°-160°	190.0	4.5
160°-170°	111.6	2.7
170°-180°	36.3	0.9
0°-30°	395.3	9.4
0°-40°	636.1	15.2
0°-60°	1090.8	26.0
0°-90°	1367.1	32.6
90°-120°	1389.6	33.1
90°-150°	2489.6	59.4
90°-180°	2828.0	67.4
0°-180°	4194.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	524	524	524	524	524	
5°	525	523	518	522	521	50
15°	500	498	492	496	493	141
25°	454	451	445	446	444	209
35°	392	390	384	381	379	245
45°	322	320	314	308	306	248
55°	244	244	238	233	230	219
65°	166	164	160	156	155	164
75°	88	86	85	82	81	94
85°	24	22	22	22	22	25
90°	2	9	19	21	22	4
95°	26	84	450	131	88	27
105°	88	130	610	1067	966	94
115°	156	194	467	1024	1174	154
125°	216	255	436	790	926	192
135°	254	303	430	650	751	196
145°	289	331	424	533	587	181
155°	329	354	411	467	487	151
165°	359	369	393	417	424	101
175°	374	375	377	383	382	36
180°	375	375	375	375	375	

TEST NUMBER: P1011666

CATALOG NUMBER: S123DIP-B340D805UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	524.5	524.5	524.5	524.5	524.5
2.5°	526.7	524.9	520.0	524.5	524.0
5°	524.9	522.7	517.7	522.2	521.3
7.5°	520.9	518.6	513.7	517.7	517.3
10°	515.5	513.2	507.3	511.4	510.5
12.5°	508.2	506.4	501.0	503.7	503.3
15°	499.7	497.9	492.0	495.6	492.9
17.5°	490.2	488.0	482.1	484.8	483.9
20°	479.4	476.7	470.8	472.6	471.3
22.5°	467.2	464.5	458.6	460.0	458.2
25°	453.7	451.0	445.1	445.6	444.2
27.5°	439.7	437.0	430.7	431.1	429.8
30°	424.4	422.1	415.8	415.8	412.6
32.5°	409.0	405.9	401.4	398.2	396.9
35°	392.3	389.6	383.8	381.1	378.8
37.5°	375.7	372.1	366.2	363.0	361.7
40°	358.1	355.4	349.1	345.4	343.6
42.5°	340.5	337.3	331.0	327.4	325.6
45°	321.5	319.7	313.9	308.5	306.2
47.5°	303.1	300.3	294.9	289.5	287.7
50°	284.1	281.9	276.0	271.0	268.3
52.5°	264.3	262.9	256.6	252.5	249.8
55°	244.0	243.5	237.7	232.7	230.4
57.5°	225.0	223.2	218.7	214.2	211.5
60°	204.3	203.8	198.4	194.4	192.1
62.5°	185.8	184.4	179.0	175.0	173.6
65°	166.4	164.2	159.6	156.0	154.7
67.5°	145.7	143.9	140.3	137.1	135.3
70°	127.2	124.5	121.8	118.6	116.4
72.5°	107.8	106.0	102.8	100.1	99.2
75°	87.9	86.1	84.8	82.5	81.2
77.5°	70.4	69.5	67.6	65.8	65.8
80°	53.2	51.9	51.0	50.5	50.5
82.5°	36.5	36.5	36.5	35.6	35.2
85°	23.5	22.5	22.5	21.6	21.6
87.5°	11.7	10.4	9.9	9.5	9.5
90°	1.5	9.2	19.0	21.2	22.0
92.5°	11.4	45.6	141.2	48.2	40.2
95°	25.8	83.9	450.2	131.4	88.1
97.5°	41.0	96.1	692.3	330.2	180.7
100°	56.2	105.9	718.9	690.8	476.0
102.5°	72.1	117.3	669.6	925.0	753.8
105°	88.1	130.2	610.4	1067.4	965.6
107.5°	104.8	145.4	558.0	1130.0	1103.8
110°	123.0	161.0	514.7	1131.9	1182.7

TEST NUMBER: P1011666

CATALOG NUMBER: S123DIP-B340D805UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	139.7	177.2	485.9	1089.0	1198.7
115°	155.6	194.0	466.9	1023.7	1174.4
117.5°	171.6	209.9	454.0	953.9	1121.3
120°	188.3	225.8	445.6	887.8	1051.4
122.5°	202.7	241.0	440.3	835.8	986.1
125°	216.4	255.4	435.7	789.5	926.2
127.5°	227.0	269.2	433.5	751.6	874.5
130°	236.9	281.2	431.2	716.6	832.0
132.5°	244.4	292.2	430.4	684.0	790.3
135°	253.6	302.6	429.7	650.2	750.8
137.5°	261.9	310.9	428.2	618.4	709.0
140°	270.3	318.5	427.4	587.2	665.0
142.5°	279.4	325.3	425.9	558.8	624.0
145°	289.2	331.4	424.4	533.3	586.8
147.5°	299.1	337.8	422.1	513.6	554.9
150°	309.0	343.2	419.0	496.1	527.6
152.5°	318.8	348.8	415.3	480.9	504.8
155°	328.7	354.5	410.7	466.8	486.6
157.5°	336.3	359.5	406.9	453.2	469.2
160°	345.4	363.6	402.3	440.6	452.5
162.5°	352.2	366.6	397.8	428.9	437.3
165°	359.1	369.4	393.2	417.2	424.4
167.5°	364.4	371.6	388.7	406.9	411.5
170°	368.9	372.8	384.1	397.8	400.1
172.5°	372.0	373.9	380.3	389.8	389.4
175°	374.3	374.6	377.3	382.6	381.9
177.5°	375.8	375.0	375.0	378.1	376.5
180°	375.0	375.0	375.0	375.0	375.0

(END OF REPORT)