

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011677

Luminaire Tested: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011677
REPORT IS A COMBINATION OF REPORTS P989920 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1025UB27-4F0-XX-W2A-A1
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5814.0 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47
1	96	92	88	85	87	84	81	78	69	67	64	55	53	52	42	41	40
2	87	80	74	69	79	73	68	64	60	57	54	49	46	44	37	36	34
3	80	71	64	58	73	65	59	54	53	49	45	43	40	37	33	31	29
4	73	63	55	49	66	57	51	46	48	43	39	38	35	32	30	28	26
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	27	24	22
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	20
7	57	45	37	32	52	42	35	30	35	29	26	28	24	22	22	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8402	8402	8402	8402
5°	8408	9682	8432	7225
10°	8354	11716	8363	6310
15°	8239	13894	8307	5680
20°	8140	15996	8157	5226
25°	7992	16400	8010	4990
30°	7887	13549	7887	4835
35°	7756	9061	7707	4697
40°	7600	6542	7506	4488
45°	7403	5181	7189	4227
50°	6926	4400	6678	3971
55°	6400	3866	6141	3686
60°	5868	3366	5557	3387
65°	5284	2883	5028	2986
70°	4676	2393	4367	2517
75°	3998	1805	3739	1944
80°	3160	1204	2915	1276
85°	2180	554	1748	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13551 cd/sqm

TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.8	1.3
10°-20°	246.6	4.2
20°-30°	414.9	7.1
30°-40°	468.9	8.1
40°-50°	419.9	7.2
50°-60°	339.0	5.8
60°-70°	236.2	4.1
70°-80°	124.0	2.1
80°-90°	32.4	0.6
90°-100°	80.3	1.4
100°-110°	243.0	4.2
110°-120°	413.6	7.1
120°-130°	544.2	9.4
130°-140°	611.7	10.5
140°-150°	601.3	10.3
150°-160°	506.3	8.7
160°-170°	337.0	5.8
170°-180°	118.0	2.0
0°-30°	738.2	12.7
0°-40°	1207.1	20.8
0°-60°	1966.1	33.8
0°-90°	2358.6	40.6
90°-120°	736.9	12.7
90°-150°	2494.0	42.9
90°-180°	3455.0	59.4
0°-180°	5814.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	781	781	781	781	781	
5°	780	927	782	692	780	74
15°	744	1380	750	564	744	210
25°	681	1638	682	498	681	314
35°	601	883	597	458	601	376
45°	498	476	484	389	498	381
55°	353	324	339	309	353	316
65°	219	210	208	218	219	218
75°	105	108	98	116	105	113
85°	23	25	18	23	23	26
90°	1	29	1	29	1	6
95°	58	76	58	76	58	64
105°	220	233	220	233	220	236
115°	416	417	416	417	416	412
125°	609	602	609	602	609	543
135°	791	790	791	790	791	609
145°	959	959	959	959	959	599
155°	1098	1096	1098	1096	1098	506
165°	1196	1192	1196	1192	1196	337
175°	1244	1239	1244	1239	1244	118
180°	1247	1247	1247	1247	1247	

TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	782.9	788.9	792.0	796.5	801.0	807.8	810.1	813.9	812.4	815.4	816.9
5°	779.9	790.4	799.5	810.9	821.5	829.0	836.6	848.7	857.8	859.3	866.1
7.5°	774.6	789.7	805.6	821.5	841.9	854.0	867.6	884.2	897.9	919.8	928.1
10°	767.7	788.9	811.6	833.6	861.5	880.5	897.1	925.1	953.1	975.8	996.9
12.5°	757.2	783.6	813.1	845.7	882.0	903.9	926.6	963.7	1006.0	1040.8	1063.5
15°	744.3	777.6	815.4	850.2	890.3	931.1	955.3	996.9	1057.5	1090.0	1148.2
17.5°	733.7	767.7	805.6	860.0	914.5	955.3	972.7	1049.1	1090.7	1145.2	1211.0
20°	717.1	760.2	808.6	863.1	933.4	958.4	993.9	1071.1	1122.5	1193.6	1274.5
22.5°	699.7	745.8	804.1	860.8	939.5	965.9	1014.3	1075.6	1157.3	1227.6	1316.9
25°	680.8	730.7	789.7	857.0	934.2	972.7	1018.1	1093.8	1182.3	1270.8	1353.2
27.5°	661.9	716.3	777.6	844.9	919.8	965.2	1010.6	1089.2	1202.7	1298.7	1403.9
30°	643.7	698.2	759.4	828.3	906.9	950.8	993.9	1092.2	1218.6	1326.7	1432.6
32.5°	624.0	680.0	744.3	801.8	881.2	928.1	976.5	1092.2	1228.4	1343.4	1440.2
35°	600.6	658.1	713.3	770.8	849.4	901.6	956.1	1084.7	1237.5	1348.7	1408.4
37.5°	577.9	628.6	676.2	732.2	814.6	870.6	933.4	1075.6	1232.9	1326.0	1342.6
40°	552.2	602.9	641.4	693.6	780.6	845.7	909.2	1063.5	1213.3	1272.3	1223.9
42.5°	527.2	567.3	600.6	651.3	745.8	809.4	878.2	1041.6	1174.7	1186.8	1077.9
45°	498.5	527.2	556.7	614.2	708.0	773.0	849.4	1009.8	1112.7	1077.9	940.2
47.5°	461.4	487.1	519.6	572.6	667.9	735.2	807.8	969.0	1022.7	950.0	799.5
50°	425.9	447.8	478.0	529.5	625.5	691.4	768.5	904.7	931.1	816.9	689.1
52.5°	390.3	406.9	436.4	487.9	583.9	647.5	717.8	838.9	823.7	701.2	587.7
55°	353.2	367.6	395.6	446.3	535.5	596.0	663.4	757.9	718.6	602.1	511.3
57.5°	316.9	332.1	360.8	403.2	487.1	546.1	599.8	674.0	615.0	521.9	441.7
60°	284.4	297.3	319.2	360.8	437.2	484.9	534.0	584.7	535.5	445.5	384.3
62.5°	250.4	262.5	282.9	320.7	386.5	428.9	468.2	509.8	455.4	389.5	335.1
65°	218.6	228.4	247.3	282.1	335.8	370.6	402.4	431.1	387.3	326.8	285.9
67.5°	189.9	198.2	214.1	245.1	290.5	315.4	341.1	365.3	328.3	279.9	245.1
70°	158.8	165.7	180.0	202.7	239.0	264.7	283.7	301.8	268.5	229.9	206.5
72.5°	131.6	138.4	147.5	170.9	195.9	211.8	232.2	242.0	223.1	191.4	167.9
75°	105.1	110.4	118.8	133.9	157.3	167.9	180.8	188.3	170.9	149.8	135.4
77.5°	82.4	84.7	90.8	101.4	117.2	129.3	139.2	143.7	131.6	118.0	105.9
80°	58.2	61.3	65.8	74.9	87.0	90.8	96.8	102.1	94.6	82.4	74.9
82.5°	38.6	42.4	44.6	48.4	56.0	60.5	62.0	66.6	59.8	55.2	52.2
85°	22.7	24.2	25.0	27.2	31.0	33.3	35.6	36.3	34.8	34.0	31.0
87.5°	11.3	11.3	11.3	12.9	13.6	15.1	15.9	15.9	15.9	15.1	14.4
90°	1.0	3.2	5.4	7.5	9.7	10.8	12.2	15.0	17.9	20.7	23.5
92.5°	29.4	30.7	32.0	33.3	34.6	35.3	35.9	37.2	38.5	39.8	41.1
95°	57.8	59.3	60.9	62.4	63.9	64.7	65.6	67.3	69.0	70.8	72.5
97.5°	95.0	96.1	97.2	98.3	99.4	99.9	100.6	101.9	103.2	104.5	105.8
100°	133.2	134.5	135.8	137.1	138.4	139.1	139.6	140.7	141.8	142.9	144.0
102.5°	177.3	177.9	178.6	179.2	179.9	180.2	181.0	182.5	184.0	185.6	187.1
105°	220.4	220.8	221.3	221.7	222.2	222.4	223.4	225.3	227.3	229.2	231.2
107.5°	271.4	271.6	271.8	272.0	272.2	272.3	272.7	273.6	274.5	275.4	276.3
110°	318.4	318.8	319.2	319.7	320.1	320.3	320.5	321.0	321.4	321.9	322.3

TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	367.4	367.6	367.8	368.0	368.2	368.3	368.3	368.3	368.3	368.3	368.3
115°	416.3	417.0	417.6	418.3	419.0	419.3	419.1	418.6	418.2	417.7	417.3
117.5°	466.3	466.5	466.7	467.0	467.2	467.3	467.1	466.6	466.2	465.7	465.3
120°	512.3	513.6	514.9	516.2	517.5	518.2	517.7	516.6	515.5	514.4	513.3
122.5°	560.3	561.2	562.1	563.0	563.9	564.3	564.1	563.6	563.2	562.7	562.3
125°	609.3	610.0	610.6	611.3	612.0	612.3	612.1	611.6	611.2	610.7	610.3
127.5°	654.4	655.7	657.0	658.3	659.6	660.3	660.1	659.6	659.2	658.7	658.3
130°	699.4	701.2	702.9	704.7	706.4	707.3	707.0	706.3	705.6	705.0	704.3
132.5°	744.5	746.2	748.0	749.7	751.4	752.3	752.1	751.7	751.2	750.8	750.4
135°	790.6	791.9	793.2	794.5	795.8	796.4	796.3	796.1	795.9	795.7	795.5
137.5°	832.7	833.8	834.9	836.0	837.1	837.6	837.9	838.6	839.2	839.9	840.5
140°	876.8	877.9	879.0	880.1	881.2	881.7	881.8	882.0	882.2	882.4	882.6
142.5°	916.9	918.0	919.1	920.2	921.3	921.8	922.0	922.5	922.9	923.4	923.8
145°	959.0	959.4	959.9	960.3	960.8	961.0	961.3	962.0	962.6	963.3	963.9
147.5°	995.3	996.2	997.0	997.9	998.8	999.2	999.5	1000.2	1000.9	1001.5	1002.2
150°	1033.5	1033.9	1034.4	1034.8	1035.3	1035.5	1035.7	1036.1	1036.6	1037.0	1037.4
152.5°	1064.8	1065.5	1066.1	1066.8	1067.5	1067.8	1067.9	1068.1	1068.4	1068.6	1068.8
155°	1098.2	1098.2	1098.2	1098.2	1098.2	1098.2	1098.3	1098.5	1098.7	1098.9	1099.1
157.5°	1126.6	1126.4	1126.2	1125.9	1125.7	1125.6	1125.7	1125.9	1126.2	1126.4	1126.6
160°	1153.0	1152.6	1152.2	1151.7	1151.3	1151.1	1151.1	1151.1	1151.1	1151.1	1151.1
162.5°	1176.5	1175.9	1175.2	1174.6	1173.9	1173.6	1173.7	1173.9	1174.2	1174.4	1174.6
165°	1196.1	1195.5	1194.8	1194.2	1193.5	1193.2	1193.2	1193.2	1193.2	1193.2	1193.2
167.5°	1212.8	1211.9	1211.1	1210.2	1209.3	1208.9	1209.0	1209.2	1209.4	1209.6	1209.8
170°	1226.5	1225.6	1224.8	1223.9	1223.0	1222.6	1222.6	1222.6	1222.6	1222.6	1222.6
172.5°	1237.3	1236.4	1235.5	1234.6	1233.7	1233.3	1233.3	1233.3	1233.3	1233.3	1233.3
175°	1244.1	1243.2	1242.4	1241.5	1240.6	1240.2	1240.2	1240.2	1240.2	1240.2	1240.2
177.5°	1248.0	1247.1	1246.3	1245.4	1244.5	1244.1	1244.1	1244.1	1244.1	1244.1	1244.1
180°	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1

TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	822.2	823.7	829.0	832.8	840.4	839.6	839.6	838.9	836.6	840.4	842.6
5°	879.7	892.6	894.1	910.7	911.5	918.3	922.8	919.0	928.1	927.4	920.5
7.5°	950.8	968.2	976.5	992.4	1010.6	1006.0	1023.4	1026.4	1024.9	1032.5	1037.8
10°	1028.7	1059.0	1080.1	1109.6	1117.2	1121.7	1133.1	1142.9	1162.6	1147.5	1157.3
12.5°	1118.0	1139.9	1167.9	1214.8	1238.2	1253.4	1258.7	1265.5	1279.1	1270.8	1271.5
15°	1192.8	1222.3	1270.0	1328.2	1335.1	1354.0	1349.4	1390.3	1409.9	1380.4	1397.1
17.5°	1270.8	1310.1	1366.8	1417.5	1446.2	1459.1	1471.2	1510.5	1509.0	1504.5	1508.3
20°	1320.7	1385.0	1455.3	1522.6	1531.0	1540.8	1573.3	1590.0	1586.9	1599.8	1608.1
22.5°	1391.0	1459.1	1534.0	1578.6	1597.5	1608.9	1634.6	1645.2	1649.7	1652.7	1647.4
25°	1450.0	1522.6	1577.9	1617.2	1628.5	1634.6	1642.9	1645.9	1643.7	1638.4	1642.9
27.5°	1490.1	1548.4	1586.2	1604.3	1598.3	1588.4	1572.6	1562.0	1538.5	1527.2	1540.8
30°	1506.8	1532.5	1543.8	1513.6	1483.3	1459.1	1428.8	1372.9	1329.0	1341.9	1324.5
32.5°	1480.3	1463.6	1409.2	1331.3	1307.8	1268.5	1183.0	1117.2	1119.5	1084.7	1099.1
35°	1402.4	1326.7	1223.9	1105.9	1074.8	1053.7	959.9	945.5	915.2	882.7	891.8
37.5°	1264.7	1154.3	1029.5	942.5	896.3	850.2	797.2	765.5	747.3	733.7	744.3
40°	1096.8	962.1	859.3	781.4	742.0	712.5	676.2	644.5	624.0	621.8	625.5
42.5°	931.9	818.4	723.9	649.8	636.9	602.1	578.6	553.7	547.6	537.8	543.1
45°	788.9	696.6	618.7	558.2	543.1	534.0	505.3	489.4	482.6	476.5	485.6
47.5°	685.3	588.5	531.8	495.4	480.3	465.2	449.3	438.7	433.4	434.2	433.4
50°	585.5	514.4	464.4	436.4	427.4	416.8	403.9	397.1	394.8	388.0	393.3
52.5°	503.8	452.3	417.5	391.1	384.3	376.7	366.1	362.3	357.0	355.5	355.5
55°	438.0	397.9	369.9	352.5	344.2	338.1	332.1	327.5	323.7	323.7	323.7
57.5°	386.5	351.7	331.3	316.2	313.2	307.1	300.3	300.3	295.0	294.2	296.5
60°	342.7	311.6	295.8	282.9	278.4	276.8	270.0	270.0	268.5	264.7	267.8
62.5°	298.0	275.3	261.7	251.9	247.3	247.3	242.0	238.3	238.3	239.0	237.5
65°	257.2	240.5	228.4	220.9	218.6	215.6	214.8	211.8	209.5	210.3	209.5
67.5°	220.9	208.0	199.7	193.6	189.9	188.3	186.1	186.1	184.6	185.3	181.5
70°	188.3	175.5	168.7	162.6	161.1	161.1	158.1	158.8	157.3	159.6	158.1
72.5°	155.1	145.2	139.9	137.7	136.2	135.4	133.9	132.4	131.6	133.1	132.4
75°	125.6	117.2	113.5	111.9	110.4	110.4	109.7	108.9	108.2	108.2	108.2
77.5°	97.6	92.3	87.7	89.3	87.0	87.7	85.5	85.5	86.2	85.5	85.5
80°	71.9	68.1	68.1	66.6	63.5	65.1	65.1	62.8	62.0	63.5	61.3
82.5°	47.7	46.9	45.4	44.6	43.1	43.9	43.1	42.4	41.6	43.1	41.6
85°	28.0	28.0	27.2	25.7	27.2	26.5	25.7	25.7	25.0	25.0	25.0
87.5°	14.4	12.9	12.9	12.1	12.9	11.3	12.1	11.3	10.6	11.3	10.6
90°	24.4	25.2	26.1	27.0	27.4	27.6	28.1	28.5	29.0	29.4	29.0
92.5°	41.8	42.4	43.1	43.8	44.1	43.9	43.4	43.0	42.5	42.1	42.5
95°	73.4	74.2	75.1	76.0	76.4	76.4	76.4	76.4	76.4	76.4	76.4
97.5°	106.9	108.0	109.1	110.2	110.7	110.6	110.4	110.1	109.9	109.7	109.9
100°	144.6	145.3	145.9	146.6	146.9	147.1	147.6	148.0	148.5	148.9	148.5
102.5°	187.7	188.4	189.0	189.7	190.0	189.9	189.7	189.5	189.3	189.1	189.3
105°	231.2	231.2	231.2	231.2	231.2	231.4	231.8	232.3	232.7	233.1	232.7
107.5°	276.9	277.6	278.2	278.9	279.2	279.1	278.9	278.6	278.4	278.2	278.4
110°	323.2	324.0	324.9	325.8	326.2	326.0	325.6	325.1	324.7	324.3	324.7

TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	369.4	370.5	371.6	372.7	373.2	373.2	373.2	373.2	373.2	373.2	373.2
115°	417.5	417.7	418.0	418.2	418.3	418.2	418.0	417.7	417.5	417.3	417.5
117.5°	465.3	465.3	465.3	465.3	465.3	465.0	464.3	463.7	463.0	462.4	463.0
120°	513.1	512.9	512.6	512.4	512.3	512.1	511.7	511.2	510.8	510.4	510.8
122.5°	561.7	561.0	560.4	559.7	559.4	559.1	558.4	557.7	557.1	556.4	557.1
125°	609.4	608.6	607.7	606.8	606.4	606.0	605.1	604.2	603.4	602.5	603.4
127.5°	657.0	655.7	654.4	653.1	652.4	652.0	651.1	650.2	649.4	648.5	649.4
130°	703.4	702.6	701.7	700.8	700.4	699.6	698.1	696.6	695.1	693.6	695.1
132.5°	749.3	748.2	747.1	746.0	745.5	745.0	743.9	742.8	741.7	740.6	741.7
135°	794.6	793.7	792.8	791.9	791.5	791.3	790.9	790.4	790.0	789.6	790.0
137.5°	839.4	838.3	837.2	836.1	835.6	835.3	834.6	834.0	833.3	832.7	833.3
140°	882.4	882.2	882.0	881.8	881.7	880.9	879.4	877.9	876.3	874.8	876.3
142.5°	923.6	923.4	923.1	922.9	922.8	922.3	921.2	920.1	919.0	917.9	919.0
145°	963.7	963.5	963.3	963.1	963.0	962.6	961.7	960.8	959.9	959.0	959.9
147.5°	1002.2	1002.2	1002.2	1002.2	1002.2	1001.5	1000.2	998.9	997.6	996.3	997.6
150°	1037.4	1037.4	1037.4	1037.4	1037.4	1036.7	1035.4	1034.1	1032.8	1031.5	1032.8
152.5°	1069.2	1069.6	1070.1	1070.5	1070.7	1070.2	1069.1	1068.0	1066.9	1065.8	1066.9
155°	1100.0	1100.9	1101.8	1102.7	1103.1	1102.3	1100.8	1099.3	1097.7	1096.2	1097.7
157.5°	1127.5	1128.3	1129.2	1130.1	1130.5	1129.8	1128.5	1127.2	1125.9	1124.6	1125.9
160°	1152.2	1153.3	1154.4	1155.5	1156.0	1155.6	1154.7	1153.8	1152.9	1152.0	1152.9
162.5°	1175.7	1176.8	1177.9	1179.0	1179.5	1178.7	1177.2	1175.7	1174.1	1172.6	1174.1
165°	1194.5	1195.8	1197.1	1198.4	1199.1	1198.3	1196.8	1195.3	1193.7	1192.2	1193.7
167.5°	1211.1	1212.4	1213.7	1215.0	1215.7	1215.0	1213.7	1212.4	1211.1	1209.8	1211.1
170°	1224.1	1225.6	1227.1	1228.6	1229.4	1228.6	1227.1	1225.6	1224.1	1222.6	1224.1
172.5°	1234.6	1235.9	1237.2	1238.5	1239.2	1238.4	1236.9	1235.4	1233.9	1232.4	1233.9
175°	1241.5	1242.8	1244.1	1245.4	1246.1	1245.3	1243.8	1242.3	1240.7	1239.2	1240.7
177.5°	1245.4	1246.7	1248.0	1249.3	1250.0	1249.2	1247.7	1246.2	1244.6	1243.1	1244.6
180°	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1

TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	836.6	838.9	832.8	831.3	831.3	834.3	832.0	811.6	815.4	810.9	809.4
5°	928.9	924.3	918.3	915.2	911.5	900.9	900.1	876.7	872.1	857.0	850.2
7.5°	1030.2	1026.4	1008.3	1006.0	1004.5	994.7	969.7	944.7	926.6	909.2	892.6
10°	1146.0	1134.6	1126.3	1109.6	1101.3	1087.7	1055.2	1031.7	1000.7	974.2	939.5
12.5°	1285.1	1272.3	1244.3	1232.2	1221.6	1183.8	1151.2	1124.8	1064.3	1046.1	1003.0
15°	1387.2	1360.0	1357.0	1330.5	1329.0	1287.4	1225.4	1196.6	1149.7	1083.2	1038.5
17.5°	1497.7	1473.5	1454.6	1422.8	1418.3	1378.9	1333.5	1263.2	1211.8	1148.2	1091.5
20°	1578.6	1565.8	1533.2	1520.4	1493.9	1460.6	1413.7	1326.7	1263.9	1200.4	1130.8
22.5°	1642.9	1630.0	1604.3	1586.9	1571.8	1528.7	1472.7	1398.6	1312.4	1229.2	1157.3
25°	1642.2	1638.4	1627.8	1619.5	1608.1	1576.3	1529.4	1458.3	1362.3	1270.8	1170.9
27.5°	1549.1	1559.7	1577.9	1586.9	1584.7	1580.1	1553.7	1493.9	1407.7	1298.7	1186.8
30°	1355.5	1394.1	1428.1	1473.5	1487.1	1520.4	1535.5	1501.5	1432.6	1331.3	1207.2
32.5°	1124.0	1180.0	1254.1	1279.1	1322.2	1386.5	1458.3	1471.2	1428.1	1350.2	1220.1
35°	922.1	968.2	1025.7	1065.0	1103.6	1208.0	1298.7	1377.4	1391.8	1340.3	1217.1
37.5°	763.2	795.7	846.4	879.7	915.2	1004.5	1131.6	1233.7	1305.6	1307.1	1208.7
40°	648.2	662.6	706.5	730.7	764.7	841.9	955.3	1088.5	1193.6	1242.0	1186.8
42.5°	549.1	568.1	604.4	622.5	644.5	711.8	786.7	913.0	1043.1	1146.7	1146.0
45°	490.1	503.8	520.4	535.5	560.5	600.6	686.1	780.6	905.4	1022.7	1068.8
47.5°	438.0	450.8	467.5	472.0	488.6	526.5	578.6	661.1	777.6	894.1	981.1
50°	394.1	404.7	416.0	424.3	431.9	462.9	502.3	571.8	664.9	777.6	885.7
52.5°	360.0	367.6	377.4	382.0	388.8	411.5	441.7	493.2	569.6	672.4	777.6
55°	328.3	333.6	339.6	347.2	350.2	366.9	390.3	434.2	490.9	583.2	683.0
57.5°	298.8	301.0	304.8	309.4	313.2	327.5	347.9	377.4	427.4	498.5	593.0
60°	265.5	271.5	273.8	278.4	280.6	292.0	307.9	332.8	371.4	432.7	503.8
62.5°	237.5	241.3	245.1	247.3	252.6	256.4	269.3	292.0	323.7	369.1	433.4
65°	212.5	214.1	216.3	218.6	220.1	224.7	236.8	251.9	276.1	316.2	366.1
67.5°	183.8	185.3	188.3	189.1	190.6	196.7	203.5	216.3	236.8	267.0	307.9
70°	155.8	158.1	159.6	161.1	163.4	165.7	173.2	183.8	199.7	220.9	252.6
72.5°	131.6	133.9	133.9	135.4	134.6	137.7	145.2	152.8	163.4	180.8	208.8
75°	107.4	107.4	108.9	109.7	110.4	113.5	116.5	122.5	130.9	144.5	161.9
77.5°	84.7	84.0	85.5	85.5	85.5	87.7	90.8	93.8	99.1	108.9	122.5
80°	62.0	62.0	63.5	64.3	62.8	63.5	65.1	68.1	71.9	78.7	86.2
82.5°	40.8	43.9	43.1	43.9	43.1	44.6	45.4	46.1	47.7	50.7	56.0
85°	25.0	25.0	25.0	25.7	25.0	25.7	25.7	25.7	26.5	28.0	30.3
87.5°	10.6	10.6	10.6	11.3	10.6	10.6	11.3	10.6	11.3	11.3	12.1
90°	28.5	28.1	27.6	27.4	27.0	26.1	25.2	24.4	23.5	20.7	17.9
92.5°	43.0	43.4	43.9	44.1	43.8	43.1	42.4	41.8	41.1	39.8	38.5
95°	76.4	76.4	76.4	76.4	76.0	75.1	74.2	73.4	72.5	70.8	69.0
97.5°	110.1	110.4	110.6	110.7	110.2	109.1	108.0	106.9	105.8	104.5	103.2
100°	148.0	147.6	147.1	146.9	146.6	145.9	145.3	144.6	144.0	142.9	141.8
102.5°	189.5	189.7	189.9	190.0	189.7	189.0	188.4	187.7	187.1	185.6	184.0
105°	232.3	231.8	231.4	231.2	231.2	231.2	231.2	231.2	231.2	229.2	227.3
107.5°	278.6	278.9	279.1	279.2	278.9	278.2	277.6	276.9	276.3	275.4	274.5
110°	325.1	325.6	326.0	326.2	325.8	324.9	324.0	323.2	322.3	321.9	321.4

TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	373.2	373.2	373.2	373.2	372.7	371.6	370.5	369.4	368.3	368.3	368.3
115°	417.7	418.0	418.2	418.3	418.2	418.0	417.7	417.5	417.3	417.7	418.2
117.5°	463.7	464.3	465.0	465.3	465.3	465.3	465.3	465.3	465.3	465.7	466.2
120°	511.2	511.7	512.1	512.3	512.4	512.6	512.9	513.1	513.3	514.4	515.5
122.5°	557.7	558.4	559.1	559.4	559.7	560.4	561.0	561.7	562.3	562.7	563.2
125°	604.2	605.1	606.0	606.4	606.8	607.7	608.6	609.4	610.3	610.7	611.2
127.5°	650.2	651.1	652.0	652.4	653.1	654.4	655.7	657.0	658.3	658.7	659.2
130°	696.6	698.1	699.6	700.4	700.8	701.7	702.6	703.4	704.3	705.0	705.6
132.5°	742.8	743.9	745.0	745.5	746.0	747.1	748.2	749.3	750.4	750.8	751.2
135°	790.4	790.9	791.3	791.5	791.9	792.8	793.7	794.6	795.5	795.7	795.9
137.5°	834.0	834.6	835.3	835.6	836.1	837.2	838.3	839.4	840.5	839.9	839.2
140°	877.9	879.4	880.9	881.7	881.8	882.0	882.2	882.4	882.6	882.4	882.2
142.5°	920.1	921.2	922.3	922.8	922.9	923.1	923.4	923.6	923.8	923.4	922.9
145°	960.8	961.7	962.6	963.0	963.1	963.3	963.5	963.7	963.9	963.3	962.6
147.5°	998.9	1000.2	1001.5	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1001.5	1000.9
150°	1034.1	1035.4	1036.7	1037.4	1037.4	1037.4	1037.4	1037.4	1037.4	1037.0	1036.6
152.5°	1068.0	1069.1	1070.2	1070.7	1070.5	1070.1	1069.6	1069.2	1068.8	1068.6	1068.4
155°	1099.3	1100.8	1102.3	1103.1	1102.7	1101.8	1100.9	1100.0	1099.1	1098.9	1098.7
157.5°	1127.2	1128.5	1129.8	1130.5	1130.1	1129.2	1128.3	1127.5	1126.6	1126.4	1126.2
160°	1153.8	1154.7	1155.6	1156.0	1155.5	1154.4	1153.3	1152.2	1151.1	1151.1	1151.1
162.5°	1175.7	1177.2	1178.7	1179.5	1179.0	1177.9	1176.8	1175.7	1174.6	1174.4	1174.2
165°	1195.3	1196.8	1198.3	1199.1	1198.4	1197.1	1195.8	1194.5	1193.2	1193.2	1193.2
167.5°	1212.4	1213.7	1215.0	1215.7	1215.0	1213.7	1212.4	1211.1	1209.8	1209.6	1209.4
170°	1225.6	1227.1	1228.6	1229.4	1228.6	1227.1	1225.6	1224.1	1222.6	1222.6	1222.6
172.5°	1235.4	1236.9	1238.4	1239.2	1238.5	1237.2	1235.9	1234.6	1233.3	1233.3	1233.3
175°	1242.3	1243.8	1245.3	1246.1	1245.4	1244.1	1242.8	1241.5	1240.2	1240.2	1240.2
177.5°	1246.2	1247.7	1249.2	1250.0	1249.3	1248.0	1246.7	1245.4	1244.1	1244.1	1244.1
180°	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1

TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	801.8	799.5	799.5	798.0	793.5	785.1	784.4	785.9	781.4	776.8	770.0
5°	841.1	826.7	822.2	817.7	808.6	793.5	787.4	782.1	773.8	764.0	753.4
7.5°	874.4	854.0	847.9	839.6	821.5	800.3	786.7	775.3	764.0	750.4	737.5
10°	916.0	886.5	872.1	860.0	835.1	805.6	785.1	768.5	750.4	733.7	717.1
12.5°	962.9	915.2	910.7	881.2	852.5	808.6	783.6	759.4	735.2	714.8	697.4
15°	1002.2	950.0	931.1	911.5	856.2	801.8	777.6	750.4	722.4	700.4	674.7
17.5°	1027.2	984.1	944.0	917.5	860.0	811.6	764.7	733.7	704.2	674.0	652.8
20°	1057.5	994.7	959.9	924.3	867.6	804.1	757.2	718.6	682.3	655.0	629.3
22.5°	1087.7	1003.0	974.2	935.7	869.1	796.5	743.5	705.0	663.4	636.1	608.1
25°	1084.7	1015.1	967.4	934.9	854.0	789.7	727.7	682.3	643.7	608.9	580.9
27.5°	1087.0	1001.5	953.1	915.2	843.4	779.9	711.0	663.4	623.3	587.0	557.5
30°	1087.7	981.1	938.7	893.3	823.7	756.4	692.1	643.7	601.3	562.0	535.5
32.5°	1085.4	964.4	911.5	870.6	792.7	733.7	670.2	618.7	575.6	539.3	514.4
35°	1080.1	944.7	883.5	832.0	760.9	701.2	649.8	596.8	550.7	517.4	488.6
37.5°	1065.8	923.6	854.0	803.3	723.9	663.4	618.0	574.1	529.5	490.1	465.9
40°	1055.2	894.8	824.5	769.3	683.8	624.8	587.0	545.4	501.5	465.9	442.5
42.5°	1031.0	867.6	794.2	728.4	644.5	583.9	548.4	515.1	477.3	442.5	421.3
45°	991.6	838.1	757.2	690.6	601.3	543.9	511.3	484.1	450.8	417.5	396.4
47.5°	936.4	795.7	717.8	651.3	559.0	500.7	468.2	447.8	421.3	393.3	375.2
50°	876.7	749.6	677.7	611.9	518.1	461.4	429.6	410.7	393.3	367.6	350.2
52.5°	798.8	700.4	631.6	568.8	474.3	419.8	391.8	378.2	360.0	341.9	326.8
55°	723.1	636.9	580.2	520.4	431.1	380.5	353.2	338.9	328.3	313.2	301.0
57.5°	635.4	577.9	525.7	471.2	391.1	344.9	319.2	301.8	295.0	288.2	276.8
60°	554.4	510.6	468.2	422.8	349.5	307.9	282.9	269.3	262.5	257.9	250.4
62.5°	480.3	446.3	410.0	373.7	307.1	269.3	250.4	236.8	230.7	229.9	223.1
65°	409.2	385.0	355.5	320.0	267.8	234.5	216.3	208.0	201.2	201.2	195.9
67.5°	338.1	321.5	298.0	273.1	232.2	201.2	184.6	177.0	173.2	173.2	169.4
70°	281.4	270.0	248.9	226.9	191.4	167.9	155.1	148.3	146.0	146.7	143.7
72.5°	228.4	216.3	198.9	183.0	156.6	139.2	130.1	122.5	118.8	119.5	118.8
75°	177.0	170.9	155.8	143.7	122.5	110.4	102.1	98.3	95.3	96.1	94.6
77.5°	133.1	124.1	115.7	107.4	94.6	84.7	77.9	74.1	71.9	71.9	71.9
80°	90.8	89.3	82.4	77.9	67.3	59.8	54.5	53.7	51.4	51.4	51.4
82.5°	59.0	55.2	51.4	48.4	42.4	37.8	35.6	34.0	33.3	32.5	34.0
85°	32.5	30.3	28.7	25.7	23.4	21.2	18.9	18.2	17.4	18.2	17.4
87.5°	12.9	10.6	10.6	9.8	9.1	8.3	8.3	6.8	6.8	6.1	6.1
90°	15.0	12.2	10.8	9.7	7.5	5.4	3.2	1.0	3.2	5.4	7.5
92.5°	37.2	35.9	35.3	34.6	33.3	32.0	30.7	29.4	30.7	32.0	33.3
95°	67.3	65.6	64.7	63.9	62.4	60.9	59.3	57.8	59.3	60.9	62.4
97.5°	101.9	100.6	99.9	99.4	98.3	97.2	96.1	95.0	96.1	97.2	98.3
100°	140.7	139.6	139.1	138.4	137.1	135.8	134.5	133.2	134.5	135.8	137.1
102.5°	182.5	181.0	180.2	179.9	179.2	178.6	177.9	177.3	177.9	178.6	179.2
105°	225.3	223.4	222.4	222.2	221.7	221.3	220.8	220.4	220.8	221.3	221.7
107.5°	273.6	272.7	272.3	272.2	272.0	271.8	271.6	271.4	271.6	271.8	272.0
110°	321.0	320.5	320.3	320.1	319.7	319.2	318.8	318.4	318.8	319.2	319.7

TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	368.3	368.3	368.3	368.2	368.0	367.8	367.6	367.4	367.6	367.8	368.0
115°	418.6	419.1	419.3	419.0	418.3	417.6	417.0	416.3	417.0	417.6	418.3
117.5°	466.6	467.1	467.3	467.2	467.0	466.7	466.5	466.3	466.5	466.7	467.0
120°	516.6	517.7	518.2	517.5	516.2	514.9	513.6	512.3	513.6	514.9	516.2
122.5°	563.6	564.1	564.3	563.9	563.0	562.1	561.2	560.3	561.2	562.1	563.0
125°	611.6	612.1	612.3	612.0	611.3	610.6	610.0	609.3	610.0	610.6	611.3
127.5°	659.6	660.1	660.3	659.6	658.3	657.0	655.7	654.4	655.7	657.0	658.3
130°	706.3	707.0	707.3	706.4	704.7	702.9	701.2	699.4	701.2	702.9	704.7
132.5°	751.7	752.1	752.3	751.4	749.7	748.0	746.2	744.5	746.2	748.0	749.7
135°	796.1	796.3	796.4	795.8	794.5	793.2	791.9	790.6	791.9	793.2	794.5
137.5°	838.6	837.9	837.6	837.1	836.0	834.9	833.8	832.7	833.8	834.9	836.0
140°	882.0	881.8	881.7	881.2	880.1	879.0	877.9	876.8	877.9	879.0	880.1
142.5°	922.5	922.0	921.8	921.3	920.2	919.1	918.0	916.9	918.0	919.1	920.2
145°	962.0	961.3	961.0	960.8	960.3	959.9	959.4	959.0	959.4	959.9	960.3
147.5°	1000.2	999.5	999.2	998.8	997.9	997.0	996.2	995.3	996.2	997.0	997.9
150°	1036.1	1035.7	1035.5	1035.3	1034.8	1034.4	1033.9	1033.5	1033.9	1034.4	1034.8
152.5°	1068.1	1067.9	1067.8	1067.5	1066.8	1066.1	1065.5	1064.8	1065.5	1066.1	1066.8
155°	1098.5	1098.3	1098.2	1098.2	1098.2	1098.2	1098.2	1098.2	1098.2	1098.2	1098.2
157.5°	1125.9	1125.7	1125.6	1125.7	1125.9	1126.2	1126.4	1126.6	1126.4	1126.2	1125.9
160°	1151.1	1151.1	1151.1	1151.3	1151.7	1152.2	1152.6	1153.0	1152.6	1152.2	1151.7
162.5°	1173.9	1173.7	1173.6	1173.9	1174.6	1175.2	1175.9	1176.5	1175.9	1175.2	1174.6
165°	1193.2	1193.2	1193.2	1193.5	1194.2	1194.8	1195.5	1196.1	1195.5	1194.8	1194.2
167.5°	1209.2	1209.0	1208.9	1209.3	1210.2	1211.1	1211.9	1212.8	1211.9	1211.1	1210.2
170°	1222.6	1222.6	1222.6	1223.0	1223.9	1224.8	1225.6	1226.5	1225.6	1224.8	1223.9
172.5°	1233.3	1233.3	1233.3	1233.7	1234.6	1235.5	1236.4	1237.3	1236.4	1235.5	1234.6
175°	1240.2	1240.2	1240.2	1240.6	1241.5	1242.4	1243.2	1244.1	1243.2	1242.4	1241.5
177.5°	1244.1	1244.1	1244.1	1244.5	1245.4	1246.3	1247.1	1248.0	1247.1	1246.3	1245.4
180°	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1

TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	768.5	767.7	769.3	764.7	757.2	753.4	742.8	740.5	739.8	740.5	741.3
5°	747.3	746.6	744.3	736.7	727.7	720.9	708.0	707.2	702.7	698.2	700.4
7.5°	726.9	723.9	719.3	709.5	697.4	689.8	679.2	671.7	665.6	661.9	658.8
10°	706.5	701.9	697.4	684.5	669.4	658.1	645.2	639.2	632.4	629.3	626.3
12.5°	680.0	675.5	667.1	652.0	642.9	628.6	615.7	609.7	605.9	599.8	596.0
15°	658.8	649.8	645.2	629.3	610.4	608.9	585.5	583.9	576.4	576.4	570.3
17.5°	634.6	627.8	619.5	603.6	590.0	576.4	564.3	559.7	552.9	551.4	548.4
20°	611.2	602.1	599.1	583.2	568.8	552.2	539.3	534.8	531.8	528.7	531.0
22.5°	587.0	579.4	571.8	557.5	546.9	530.2	522.7	518.1	513.6	512.1	512.8
25°	563.5	556.7	549.1	534.8	523.4	509.8	503.0	500.7	498.5	498.5	497.7
27.5°	540.8	534.0	527.2	514.4	503.0	493.2	487.9	485.6	483.3	484.9	486.4
30°	517.4	511.3	505.3	493.9	484.9	475.8	472.8	471.2	470.5	474.3	474.3
32.5°	496.2	490.9	486.4	475.8	466.7	459.1	456.9	457.6	458.4	460.6	462.2
35°	474.3	470.5	465.9	456.9	449.3	442.5	443.3	443.3	444.8	448.5	451.6
37.5°	454.6	449.3	445.5	438.0	431.9	425.9	428.1	430.4	431.9	436.4	438.0
40°	431.1	428.9	425.9	418.3	413.0	412.2	413.0	414.5	417.5	419.8	422.1
42.5°	412.2	409.2	405.4	399.4	394.8	395.6	396.4	397.9	399.4	403.2	405.4
45°	391.1	388.8	385.8	380.5	376.7	377.4	378.2	378.2	379.7	384.3	385.8
47.5°	367.6	368.4	364.6	359.3	357.0	357.0	357.0	358.5	362.3	363.8	364.6
50°	344.9	343.4	342.7	337.4	335.8	335.1	335.8	336.6	341.9	341.1	343.4
52.5°	320.7	320.7	320.0	316.9	314.7	314.7	313.2	316.9	318.4	320.0	322.2
55°	297.3	295.0	294.2	292.7	289.7	288.9	290.5	295.0	296.5	298.0	300.3
57.5°	271.5	271.5	270.0	267.8	267.8	267.8	267.8	270.8	273.1	274.6	279.1
60°	248.1	245.1	242.8	242.8	242.8	242.0	246.6	246.6	251.1	251.9	253.4
62.5°	220.1	218.6	217.1	217.8	217.1	218.6	220.1	223.1	223.9	226.2	228.4
65°	193.6	193.6	192.1	196.7	193.6	193.6	197.4	197.4	198.9	201.2	204.2
67.5°	167.9	168.7	167.2	167.2	168.7	169.4	170.2	173.2	174.0	177.0	180.8
70°	141.4	143.0	143.7	142.2	143.7	145.2	146.7	147.5	150.5	152.0	154.3
72.5°	118.0	119.5	117.2	118.0	118.8	120.3	121.0	122.5	124.1	128.6	130.1
75°	94.6	93.8	93.0	96.1	94.6	97.6	98.3	98.3	99.8	103.6	105.1
77.5°	72.6	72.6	73.4	71.9	74.1	73.4	74.1	76.4	78.7	78.7	84.7
80°	50.7	52.2	52.2	52.2	52.9	53.7	52.2	56.0	56.7	56.7	59.0
82.5°	32.5	33.3	32.5	34.0	34.0	35.6	34.8	35.6	37.1	38.6	39.3
85°	17.4	17.4	18.9	18.9	18.2	18.9	18.2	18.9	20.4	20.4	21.2
87.5°	6.1	6.1	6.1	6.1	6.8	6.1	6.8	6.8	6.1	6.1	8.3
90°	9.7	10.8	12.2	15.0	17.9	20.7	23.5	24.4	25.2	26.1	27.0
92.5°	34.6	35.3	35.9	37.2	38.5	39.8	41.1	41.8	42.4	43.1	43.8
95°	63.9	64.7	65.6	67.3	69.0	70.8	72.5	73.4	74.2	75.1	76.0
97.5°	99.4	99.9	100.6	101.9	103.2	104.5	105.8	106.9	108.0	109.1	110.2
100°	138.4	139.1	139.6	140.7	141.8	142.9	144.0	144.6	145.3	145.9	146.6
102.5°	179.9	180.2	181.0	182.5	184.0	185.6	187.1	187.7	188.4	189.0	189.7
105°	222.2	222.4	223.4	225.3	227.3	229.2	231.2	231.2	231.2	231.2	231.2
107.5°	272.2	272.3	272.7	273.6	274.5	275.4	276.3	276.9	277.6	278.2	278.9
110°	320.1	320.3	320.5	321.0	321.4	321.9	322.3	323.2	324.0	324.9	325.8

TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	368.2	368.3	368.3	368.3	368.3	368.3	368.3	369.4	370.5	371.6	372.7
115°	419.0	419.3	419.1	418.6	418.2	417.7	417.3	417.5	417.7	418.0	418.2
117.5°	467.2	467.3	467.1	466.6	466.2	465.7	465.3	465.3	465.3	465.3	465.3
120°	517.5	518.2	517.7	516.6	515.5	514.4	513.3	513.1	512.9	512.6	512.4
122.5°	563.9	564.3	564.1	563.6	563.2	562.7	562.3	561.7	561.0	560.4	559.7
125°	612.0	612.3	612.1	611.6	611.2	610.7	610.3	609.4	608.6	607.7	606.8
127.5°	659.6	660.3	660.1	659.6	659.2	658.7	658.3	657.0	655.7	654.4	653.1
130°	706.4	707.3	707.0	706.3	705.6	705.0	704.3	703.4	702.6	701.7	700.8
132.5°	751.4	752.3	752.1	751.7	751.2	750.8	750.4	749.3	748.2	747.1	746.0
135°	795.8	796.4	796.3	796.1	795.9	795.7	795.5	794.6	793.7	792.8	791.9
137.5°	837.1	837.6	837.9	838.6	839.2	839.9	840.5	839.4	838.3	837.2	836.1
140°	881.2	881.7	881.8	882.0	882.2	882.4	882.6	882.4	882.2	882.0	881.8
142.5°	921.3	921.8	922.0	922.5	922.9	923.4	923.8	923.6	923.4	923.1	922.9
145°	960.8	961.0	961.3	962.0	962.6	963.3	963.9	963.7	963.5	963.3	963.1
147.5°	998.8	999.2	999.5	1000.2	1000.9	1001.5	1002.2	1002.2	1002.2	1002.2	1002.2
150°	1035.3	1035.5	1035.7	1036.1	1036.6	1037.0	1037.4	1037.4	1037.4	1037.4	1037.4
152.5°	1067.5	1067.8	1067.9	1068.1	1068.4	1068.6	1068.8	1069.2	1069.6	1070.1	1070.5
155°	1098.2	1098.2	1098.3	1098.5	1098.7	1098.9	1099.1	1100.0	1100.9	1101.8	1102.7
157.5°	1125.7	1125.6	1125.7	1125.9	1126.2	1126.4	1126.6	1127.5	1128.3	1129.2	1130.1
160°	1151.3	1151.1	1151.1	1151.1	1151.1	1151.1	1151.1	1152.2	1153.3	1154.4	1155.5
162.5°	1173.9	1173.6	1173.7	1173.9	1174.2	1174.4	1174.6	1175.7	1176.8	1177.9	1179.0
165°	1193.5	1193.2	1193.2	1193.2	1193.2	1193.2	1193.2	1194.5	1195.8	1197.1	1198.4
167.5°	1209.3	1208.9	1209.0	1209.2	1209.4	1209.6	1209.8	1211.1	1212.4	1213.7	1215.0
170°	1223.0	1222.6	1222.6	1222.6	1222.6	1222.6	1222.6	1224.1	1225.6	1227.1	1228.6
172.5°	1233.7	1233.3	1233.3	1233.3	1233.3	1233.3	1233.3	1234.6	1235.9	1237.2	1238.5
175°	1240.6	1240.2	1240.2	1240.2	1240.2	1240.2	1240.2	1241.5	1242.8	1244.1	1245.4
177.5°	1244.5	1244.1	1244.1	1244.1	1244.1	1244.1	1244.1	1245.4	1246.7	1248.0	1249.3
180°	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1

TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	740.5	741.3	738.2	736.0	742.0	738.2	738.2	739.0	737.5	739.8	739.0
5°	698.9	699.7	694.4	695.9	692.9	692.1	691.4	695.9	695.1	694.4	695.9
7.5°	658.1	658.1	655.8	654.3	654.3	652.0	655.0	654.3	655.8	655.8	658.1
10°	624.0	625.5	621.8	618.0	617.2	618.0	618.0	618.7	619.5	624.8	624.0
12.5°	596.0	593.8	593.0	590.8	587.0	585.5	583.9	592.3	590.0	590.0	590.0
15°	565.0	570.3	569.6	562.8	561.3	564.3	562.8	562.8	570.3	569.6	568.8
17.5°	548.4	546.9	545.4	541.6	542.3	541.6	542.3	542.3	546.9	546.9	546.9
20°	529.5	526.5	526.5	524.9	524.9	522.7	525.7	526.5	529.5	529.5	530.2
22.5°	512.8	510.6	510.6	509.8	511.3	508.3	511.3	512.1	512.1	514.4	514.4
25°	498.5	497.0	497.0	498.5	498.5	498.5	498.5	501.5	499.2	500.0	499.2
27.5°	485.6	486.4	487.1	487.9	487.1	487.9	488.6	490.1	490.9	490.1	488.6
30°	473.5	475.8	476.5	476.5	478.0	478.8	479.6	479.6	480.3	478.0	479.6
32.5°	464.4	464.4	465.9	466.7	468.2	469.0	469.0	470.5	469.7	467.5	468.2
35°	451.6	451.6	454.6	456.1	458.4	457.6	458.4	458.4	459.1	457.6	455.4
37.5°	438.7	440.2	440.2	443.3	444.0	444.8	444.0	445.5	444.8	443.3	442.5
40°	423.6	422.8	423.6	425.9	426.6	426.6	426.6	428.1	428.1	428.1	427.4
42.5°	404.7	406.9	406.2	408.5	407.7	407.7	409.2	410.7	411.5	409.2	410.0
45°	386.5	386.5	388.0	388.0	388.8	388.8	391.8	390.3	391.8	390.3	391.1
47.5°	366.9	367.6	367.6	368.4	369.9	371.4	369.9	370.6	370.6	371.4	369.9
50°	344.9	344.9	346.4	348.7	351.7	350.2	349.5	352.5	350.2	350.2	348.7
52.5°	322.2	324.5	325.3	327.5	329.8	330.5	331.3	329.8	330.5	328.3	329.0
55°	300.3	301.0	304.1	306.3	308.6	308.6	307.9	308.6	309.4	306.3	306.3
57.5°	278.4	280.6	283.7	283.7	286.7	286.7	285.9	285.9	286.7	284.4	283.7
60°	254.9	257.2	261.0	261.0	265.5	266.3	264.7	263.2	263.2	261.0	261.7
62.5°	229.9	232.2	234.5	238.3	241.3	239.8	242.8	239.8	240.5	236.0	236.0
65°	208.0	208.8	212.5	216.3	216.3	217.8	216.3	217.1	214.8	214.8	211.8
67.5°	182.3	182.3	186.1	189.9	193.6	193.6	193.6	191.4	191.4	189.1	189.1
70°	159.6	158.8	162.6	164.9	167.2	167.9	166.4	165.7	164.1	161.9	161.1
72.5°	131.6	133.1	136.9	138.4	142.2	141.4	145.2	140.7	140.7	136.9	136.2
75°	106.7	108.2	111.9	114.2	116.5	116.5	118.8	116.5	113.5	111.9	111.2
77.5°	84.7	84.0	87.0	90.8	91.5	90.8	92.3	91.5	88.5	88.5	87.0
80°	60.5	62.8	65.8	65.1	68.1	67.3	67.3	65.8	65.8	63.5	65.1
82.5°	40.1	42.4	43.1	42.4	43.1	44.6	45.4	44.6	44.6	43.1	43.9
85°	21.2	21.2	22.7	23.4	22.7	22.7	23.4	25.7	24.2	22.7	24.2
87.5°	6.8	6.1	6.1	6.8	6.1	6.1	6.8	6.8	7.6	7.6	7.6
90°	27.4	27.6	28.1	28.5	29.0	29.4	29.0	28.5	28.1	27.6	27.4
92.5°	44.1	43.9	43.4	43.0	42.5	42.1	42.5	43.0	43.4	43.9	44.1
95°	76.4	76.4	76.4	76.4	76.4	76.4	76.4	76.4	76.4	76.4	76.4
97.5°	110.7	110.6	110.4	110.1	109.9	109.7	109.9	110.1	110.4	110.6	110.7
100°	146.9	147.1	147.6	148.0	148.5	148.9	148.5	148.0	147.6	147.1	146.9
102.5°	190.0	189.9	189.7	189.5	189.3	189.1	189.3	189.5	189.7	189.9	190.0
105°	231.2	231.4	231.8	232.3	232.7	233.1	232.7	232.3	231.8	231.4	231.2
107.5°	279.2	279.1	278.9	278.6	278.4	278.2	278.4	278.6	278.9	279.1	279.2
110°	326.2	326.0	325.6	325.1	324.7	324.3	324.7	325.1	325.6	326.0	326.2

TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	373.2	373.2	373.2	373.2	373.2	373.2	373.2	373.2	373.2	373.2	373.2
115°	418.3	418.2	418.0	417.7	417.5	417.3	417.5	417.7	418.0	418.2	418.3
117.5°	465.3	465.0	464.3	463.7	463.0	462.4	463.0	463.7	464.3	465.0	465.3
120°	512.3	512.1	511.7	511.2	510.8	510.4	510.8	511.2	511.7	512.1	512.3
122.5°	559.4	559.1	558.4	557.7	557.1	556.4	557.1	557.7	558.4	559.1	559.4
125°	606.4	606.0	605.1	604.2	603.4	602.5	603.4	604.2	605.1	606.0	606.4
127.5°	652.4	652.0	651.1	650.2	649.4	648.5	649.4	650.2	651.1	652.0	652.4
130°	700.4	699.6	698.1	696.6	695.1	693.6	695.1	696.6	698.1	699.6	700.4
132.5°	745.5	745.0	743.9	742.8	741.7	740.6	741.7	742.8	743.9	745.0	745.5
135°	791.5	791.3	790.9	790.4	790.0	789.6	790.0	790.4	790.9	791.3	791.5
137.5°	835.6	835.3	834.6	834.0	833.3	832.7	833.3	834.0	834.6	835.3	835.6
140°	881.7	880.9	879.4	877.9	876.3	874.8	876.3	877.9	879.4	880.9	881.7
142.5°	922.8	922.3	921.2	920.1	919.0	917.9	919.0	920.1	921.2	922.3	922.8
145°	963.0	962.6	961.7	960.8	959.9	959.0	959.9	960.8	961.7	962.6	963.0
147.5°	1002.2	1001.5	1000.2	998.9	997.6	996.3	997.6	998.9	1000.2	1001.5	1002.2
150°	1037.4	1036.7	1035.4	1034.1	1032.8	1031.5	1032.8	1034.1	1035.4	1036.7	1037.4
152.5°	1070.7	1070.2	1069.1	1068.0	1066.9	1065.8	1066.9	1068.0	1069.1	1070.2	1070.7
155°	1103.1	1102.3	1100.8	1099.3	1097.7	1096.2	1097.7	1099.3	1100.8	1102.3	1103.1
157.5°	1130.5	1129.8	1128.5	1127.2	1125.9	1124.6	1125.9	1127.2	1128.5	1129.8	1130.5
160°	1156.0	1155.6	1154.7	1153.8	1152.9	1152.0	1152.9	1153.8	1154.7	1155.6	1156.0
162.5°	1179.5	1178.7	1177.2	1175.7	1174.1	1172.6	1174.1	1175.7	1177.2	1178.7	1179.5
165°	1199.1	1198.3	1196.8	1195.3	1193.7	1192.2	1193.7	1195.3	1196.8	1198.3	1199.1
167.5°	1215.7	1215.0	1213.7	1212.4	1211.1	1209.8	1211.1	1212.4	1213.7	1215.0	1215.7
170°	1229.4	1228.6	1227.1	1225.6	1224.1	1222.6	1224.1	1225.6	1227.1	1228.6	1229.4
172.5°	1239.2	1238.4	1236.9	1235.4	1233.9	1232.4	1233.9	1235.4	1236.9	1238.4	1239.2
175°	1246.1	1245.3	1243.8	1242.3	1240.7	1239.2	1240.7	1242.3	1243.8	1245.3	1246.1
177.5°	1250.0	1249.2	1247.7	1246.2	1244.6	1243.1	1244.6	1246.2	1247.7	1249.2	1250.0
180°	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1

TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	741.3	742.8	743.5	740.5	738.2	742.0	747.3	751.1	754.1	757.9	760.2
5°	697.4	702.7	702.7	704.2	706.5	710.3	720.1	726.9	733.0	737.5	741.3
7.5°	660.3	664.1	666.4	670.2	674.0	679.2	690.6	700.4	709.5	714.8	720.9
10°	627.1	630.1	633.9	636.1	642.9	650.5	664.9	673.2	683.8	692.1	699.7
12.5°	595.3	605.9	608.1	607.4	613.4	621.8	636.1	649.0	660.3	668.7	677.0
15°	572.6	576.4	580.9	580.2	593.0	595.3	607.4	622.5	637.6	642.9	650.5
17.5°	547.6	553.7	558.2	560.5	564.3	572.6	583.9	595.3	615.0	615.7	635.4
20°	528.0	534.0	537.0	540.1	542.3	552.2	562.0	574.9	590.8	599.1	609.7
22.5°	515.1	518.1	520.4	522.7	525.7	531.0	543.1	557.5	568.1	577.1	583.9
25°	500.0	503.0	506.0	507.5	509.8	512.8	521.9	533.3	548.4	554.4	561.3
27.5°	489.4	489.4	490.9	490.9	493.9	497.0	503.8	514.4	526.5	534.0	543.1
30°	478.0	477.3	478.0	477.3	476.5	481.1	487.1	496.2	504.5	513.6	519.6
32.5°	466.7	465.9	465.9	466.7	463.7	465.9	469.0	477.3	486.4	490.9	497.7
35°	454.6	453.1	453.1	453.1	451.6	450.1	453.1	460.6	466.7	472.8	478.0
37.5°	442.5	440.2	440.2	438.7	437.2	434.9	434.9	441.0	449.3	451.6	458.4
40°	425.9	425.9	424.3	423.6	422.1	420.6	418.3	423.6	431.1	433.4	438.7
42.5°	409.2	406.9	406.2	406.2	406.2	403.9	402.4	406.2	410.7	414.5	417.5
45°	390.3	388.8	389.5	388.8	387.3	386.5	385.8	387.3	392.6	394.1	397.9
47.5°	369.9	369.1	369.1	368.4	367.6	368.4	365.3	369.1	370.6	372.2	375.2
50°	348.7	347.9	347.2	346.4	346.4	347.2	346.4	346.4	349.5	351.0	354.0
52.5°	327.5	325.3	325.3	324.5	324.5	323.0	324.5	325.3	326.8	328.3	329.8
55°	304.8	304.8	302.6	302.6	301.0	301.0	301.8	301.0	304.1	305.6	305.6
57.5°	282.9	279.9	280.6	279.1	277.6	276.8	276.8	278.4	279.9	279.9	281.4
60°	259.4	256.4	255.7	252.6	254.2	251.9	252.6	252.6	255.7	254.2	255.7
62.5°	236.0	232.2	229.9	228.4	228.4	229.2	227.7	226.9	228.4	229.9	233.0
65°	211.0	208.8	206.5	204.2	204.2	203.5	205.0	202.7	202.0	202.7	204.2
67.5°	185.3	183.0	180.8	178.5	179.3	177.0	175.5	177.8	176.2	177.0	178.5
70°	160.4	158.8	154.3	152.8	152.0	152.8	152.0	150.5	152.8	152.0	152.8
72.5°	135.4	133.9	131.6	127.8	127.8	127.1	126.3	126.3	125.6	125.6	125.6
75°	111.2	108.2	105.9	105.1	103.6	102.9	102.1	100.6	101.4	102.1	100.6
77.5°	86.2	82.4	81.7	81.7	79.4	79.4	80.2	79.4	78.7	78.7	78.7
80°	63.5	60.5	60.5	59.0	57.5	57.5	57.5	57.5	56.7	56.0	56.7
82.5°	40.8	40.1	39.3	39.3	40.8	37.8	39.3	38.6	37.8	37.8	37.1
85°	22.7	23.4	22.7	23.4	21.9	22.7	22.7	22.7	21.9	22.7	21.2
87.5°	8.3	8.3	8.3	9.1	9.1	9.1	9.1	9.1	9.8	9.1	9.1
90°	27.0	26.1	25.2	24.4	23.5	20.7	17.9	15.0	12.2	10.8	9.7
92.5°	43.8	43.1	42.4	41.8	41.1	39.8	38.5	37.2	35.9	35.3	34.6
95°	76.0	75.1	74.2	73.4	72.5	70.8	69.0	67.3	65.6	64.7	63.9
97.5°	110.2	109.1	108.0	106.9	105.8	104.5	103.2	101.9	100.6	99.9	99.4
100°	146.6	145.9	145.3	144.6	144.0	142.9	141.8	140.7	139.6	139.1	138.4
102.5°	189.7	189.0	188.4	187.7	187.1	185.6	184.0	182.5	181.0	180.2	179.9
105°	231.2	231.2	231.2	231.2	231.2	229.2	227.3	225.3	223.4	222.4	222.2
107.5°	278.9	278.2	277.6	276.9	276.3	275.4	274.5	273.6	272.7	272.3	272.2
110°	325.8	324.9	324.0	323.2	322.3	321.9	321.4	321.0	320.5	320.3	320.1

TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	372.7	371.6	370.5	369.4	368.3	368.3	368.3	368.3	368.3	368.3	368.2
115°	418.2	418.0	417.7	417.5	417.3	417.7	418.2	418.6	419.1	419.3	419.0
117.5°	465.3	465.3	465.3	465.3	465.3	465.7	466.2	466.6	467.1	467.3	467.2
120°	512.4	512.6	512.9	513.1	513.3	514.4	515.5	516.6	517.7	518.2	517.5
122.5°	559.7	560.4	561.0	561.7	562.3	562.7	563.2	563.6	564.1	564.3	563.9
125°	606.8	607.7	608.6	609.4	610.3	610.7	611.2	611.6	612.1	612.3	612.0
127.5°	653.1	654.4	655.7	657.0	658.3	658.7	659.2	659.6	660.1	660.3	659.6
130°	700.8	701.7	702.6	703.4	704.3	705.0	705.6	706.3	707.0	707.3	706.4
132.5°	746.0	747.1	748.2	749.3	750.4	750.8	751.2	751.7	752.1	752.3	751.4
135°	791.9	792.8	793.7	794.6	795.5	795.7	795.9	796.1	796.3	796.4	795.8
137.5°	836.1	837.2	838.3	839.4	840.5	839.9	839.2	838.6	837.9	837.6	837.1
140°	881.8	882.0	882.2	882.4	882.6	882.4	882.2	882.0	881.8	881.7	881.2
142.5°	922.9	923.1	923.4	923.6	923.8	923.4	922.9	922.5	922.0	921.8	921.3
145°	963.1	963.3	963.5	963.7	963.9	963.3	962.6	962.0	961.3	961.0	960.8
147.5°	1002.2	1002.2	1002.2	1002.2	1002.2	1001.5	1000.9	1000.2	999.5	999.2	998.8
150°	1037.4	1037.4	1037.4	1037.4	1037.4	1037.0	1036.6	1036.1	1035.7	1035.5	1035.3
152.5°	1070.5	1070.1	1069.6	1069.2	1068.8	1068.6	1068.4	1068.1	1067.9	1067.8	1067.5
155°	1102.7	1101.8	1100.9	1100.0	1099.1	1098.9	1098.7	1098.5	1098.3	1098.2	1098.2
157.5°	1130.1	1129.2	1128.3	1127.5	1126.6	1126.4	1126.2	1125.9	1125.7	1125.6	1125.7
160°	1155.5	1154.4	1153.3	1152.2	1151.1	1151.1	1151.1	1151.1	1151.1	1151.1	1151.3
162.5°	1179.0	1177.9	1176.8	1175.7	1174.6	1174.4	1174.2	1173.9	1173.7	1173.6	1173.9
165°	1198.4	1197.1	1195.8	1194.5	1193.2	1193.2	1193.2	1193.2	1193.2	1193.2	1193.5
167.5°	1215.0	1213.7	1212.4	1211.1	1209.8	1209.6	1209.4	1209.2	1209.0	1208.9	1209.3
170°	1228.6	1227.1	1225.6	1224.1	1222.6	1222.6	1222.6	1222.6	1222.6	1222.6	1223.0
172.5°	1238.5	1237.2	1235.9	1234.6	1233.3	1233.3	1233.3	1233.3	1233.3	1233.3	1233.7
175°	1245.4	1244.1	1242.8	1241.5	1240.2	1240.2	1240.2	1240.2	1240.2	1240.2	1240.6
177.5°	1249.3	1248.0	1246.7	1245.4	1244.1	1244.1	1244.1	1244.1	1244.1	1244.1	1244.5
180°	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1

TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	780.6	780.6	780.6	780.6
2.5°	764.0	766.2	773.8	782.9
5°	748.8	754.9	765.5	779.9
7.5°	732.2	741.3	756.4	774.6
10°	713.3	726.1	745.1	767.7
12.5°	692.9	709.5	733.7	757.2
15°	680.0	696.6	718.6	744.3
17.5°	655.0	674.7	697.4	733.7
20°	629.3	651.3	680.8	717.1
22.5°	609.7	633.1	661.1	699.7
25°	586.2	610.4	640.7	680.8
27.5°	561.3	585.5	619.5	661.9
30°	542.3	565.8	598.3	643.7
32.5°	519.6	542.3	576.4	624.0
35°	493.9	519.6	552.2	600.6
37.5°	474.3	497.7	531.8	577.9
40°	453.1	473.5	506.8	552.2
42.5°	430.4	453.1	481.8	527.2
45°	409.2	425.9	455.4	498.5
47.5°	386.5	405.4	428.1	461.4
50°	362.3	378.2	403.2	425.9
52.5°	338.9	351.7	372.9	390.3
55°	313.9	326.8	342.7	353.2
57.5°	290.5	299.5	310.1	316.9
60°	261.7	270.8	277.6	284.4
62.5°	236.0	242.8	246.6	250.4
65°	209.5	213.3	215.6	218.6
67.5°	180.8	184.6	185.3	189.9
70°	154.3	155.1	156.6	158.8
72.5°	129.3	130.9	130.1	131.6
75°	103.6	105.1	103.6	105.1
77.5°	78.7	80.2	80.2	82.4
80°	56.7	57.5	58.2	58.2
82.5°	37.1	39.3	37.8	38.6
85°	21.2	21.9	21.9	22.7
87.5°	9.8	10.6	9.8	11.3
90°	7.5	5.4	3.2	1.0
92.5°	33.3	32.0	30.7	29.4
95°	62.4	60.9	59.3	57.8
97.5°	98.3	97.2	96.1	95.0
100°	137.1	135.8	134.5	133.2
102.5°	179.2	178.6	177.9	177.3
105°	221.7	221.3	220.8	220.4
107.5°	272.0	271.8	271.6	271.4
110°	319.7	319.2	318.8	318.4

TEST NUMBER: P1011677

CATALOG NUMBER: S123DIP-B560D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	368.0	367.8	367.6	367.4
115°	418.3	417.6	417.0	416.3
117.5°	467.0	466.7	466.5	466.3
120°	516.2	514.9	513.6	512.3
122.5°	563.0	562.1	561.2	560.3
125°	611.3	610.6	610.0	609.3
127.5°	658.3	657.0	655.7	654.4
130°	704.7	702.9	701.2	699.4
132.5°	749.7	748.0	746.2	744.5
135°	794.5	793.2	791.9	790.6
137.5°	836.0	834.9	833.8	832.7
140°	880.1	879.0	877.9	876.8
142.5°	920.2	919.1	918.0	916.9
145°	960.3	959.9	959.4	959.0
147.5°	997.9	997.0	996.2	995.3
150°	1034.8	1034.4	1033.9	1033.5
152.5°	1066.8	1066.1	1065.5	1064.8
155°	1098.2	1098.2	1098.2	1098.2
157.5°	1125.9	1126.2	1126.4	1126.6
160°	1151.7	1152.2	1152.6	1153.0
162.5°	1174.6	1175.2	1175.9	1176.5
165°	1194.2	1194.8	1195.5	1196.1
167.5°	1210.2	1211.1	1211.9	1212.8
170°	1223.9	1224.8	1225.6	1226.5
172.5°	1234.6	1235.5	1236.4	1237.3
175°	1241.5	1242.4	1243.2	1244.1
177.5°	1245.4	1246.3	1247.1	1248.0
180°	1247.1	1247.1	1247.1	1247.1

(END OF REPORT)