

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011406

Luminaire Tested: S123DIP-B1165D585UB50-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011406
REPORT IS A COMBINATION OF REPORTS P989550 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B1165D585UB50-4F0-XX-W2A-A
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6974.0 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68		
1	102	98	94	91	96	92	89	86	82	80	77	73	71	69	65	63	62	58		
2	93	86	80	75	88	81	76	71	73	68	65	65	61	59	57	55	53	49		
3	85	76	68	63	80	72	65	60	64	59	55	57	53	50	51	48	45	42		
4	78	67	59	53	74	64	57	51	57	52	47	51	47	43	46	42	39	36		
5	72	60	52	46	68	57	50	44	52	46	41	46	41	38	41	37	34	32		
6	66	54	46	40	63	52	44	39	47	40	36	42	37	33	38	34	30	28		
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	25		
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	32	27	24	22		
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20		
10	50	38	30	25	47	36	29	25	33	27	23	30	25	21	27	23	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16826	16826	16826	16826
5°	16837	19388	16886	14469
10°	16731	23460	16747	12635
15°	16499	27823	16633	11373
20°	16301	32034	16335	10466
25°	16005	32841	16040	9992
30°	15793	27132	15793	9681
35°	15532	18146	15434	9407
40°	15219	13099	15030	8987
45°	14824	10376	14397	8466
50°	13868	8812	13375	7953
55°	12818	7743	12296	7381
60°	11751	6743	11126	6781
65°	10583	5773	10071	5980
70°	9368	4792	8743	5042
75°	8007	3614	7490	3892
80°	6330	2412	5836	2556
85°	4361	1108	3496	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 27137 cd/sqm

TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.7	2.2
10°-20°	493.8	7.1
20°-30°	830.9	11.9
30°-40°	938.9	13.5
40°-50°	841.0	12.1
50°-60°	678.9	9.7
60°-70°	473.1	6.8
70°-80°	248.3	3.6
80°-90°	61.0	0.9
90°-100°	26.1	0.4
100°-110°	126.1	1.8
110°-120°	309.0	4.4
120°-130°	392.2	5.6
130°-140°	419.0	6.0
140°-150°	391.8	5.6
150°-160°	316.0	4.5
160°-170°	204.0	2.9
170°-180°	70.3	1.0
0°-30°	1478.4	21.2
0°-40°	2417.3	34.7
0°-60°	3937.1	56.5
0°-90°	4719.5	67.7
90°-120°	461.2	6.6
90°-150°	1664.2	23.9
90°-180°	2255.0	32.3
0°-180°	6974.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1563	1563	1563	1563	1563	
5°	1562	1857	1566	1386	1562	148
15°	1490	2764	1503	1130	1490	421
25°	1363	3281	1366	998	1363	629
35°	1203	1768	1195	916	1203	753
45°	998	954	969	779	998	763
55°	707	648	679	618	707	633
65°	438	421	417	436	438	436
75°	210	217	197	233	210	226
85°	45	50	36	45	45	52
90°	0	16	0	16	0	5
95°	34	21	34	21	34	40
105°	164	24	164	24	164	174
115°	307	323	307	323	307	303
125°	433	442	433	442	433	387
135°	539	544	539	544	539	415
145°	622	628	622	628	622	389
155°	685	684	685	684	685	316
165°	722	721	722	721	722	204
175°	740	737	740	737	740	70
180°	740	740	740	740	740	

TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1567.7	1579.9	1585.9	1595.0	1604.1	1617.7	1622.3	1629.9	1626.8	1632.9	1635.9
5°	1561.7	1582.9	1601.1	1623.8	1645.0	1660.1	1675.3	1699.5	1717.7	1720.7	1734.4
7.5°	1551.1	1581.4	1613.2	1645.0	1685.9	1710.1	1737.4	1770.7	1798.0	1841.9	1858.6
10°	1537.5	1579.9	1625.3	1669.2	1725.3	1763.1	1796.5	1852.5	1908.6	1954.0	1996.4
12.5°	1516.2	1569.3	1628.3	1693.5	1766.2	1810.1	1855.5	1929.8	2014.6	2084.3	2129.7
15°	1490.5	1557.1	1632.9	1702.6	1782.8	1864.6	1913.1	1996.4	2117.6	2182.7	2299.4
17.5°	1469.3	1537.5	1613.2	1722.3	1831.3	1913.1	1947.9	2100.9	2184.2	2293.3	2425.1
20°	1436.0	1522.3	1619.2	1728.3	1869.2	1919.2	1990.4	2144.9	2247.9	2390.2	2552.3
22.5°	1401.1	1493.5	1610.2	1723.8	1881.3	1934.3	2031.3	2153.9	2317.5	2458.4	2637.1
25°	1363.3	1463.2	1581.4	1716.2	1870.7	1947.9	2038.8	2190.3	2367.5	2544.8	2709.9
27.5°	1325.4	1434.5	1557.1	1692.0	1841.9	1932.8	2023.7	2181.2	2408.4	2600.8	2811.3
30°	1289.0	1398.1	1520.8	1658.6	1816.2	1904.0	1990.4	2187.3	2440.2	2656.8	2868.9
32.5°	1249.7	1361.7	1490.5	1605.6	1764.7	1858.6	1955.5	2187.3	2459.9	2690.2	2884.1
35°	1202.7	1317.8	1428.4	1543.5	1701.0	1805.6	1914.6	2172.1	2478.1	2700.8	2820.4
37.5°	1157.3	1258.7	1354.2	1466.3	1631.4	1743.5	1869.2	2153.9	2469.0	2655.3	2688.6
40°	1105.8	1207.2	1284.5	1389.0	1563.2	1693.5	1820.7	2129.7	2429.6	2547.8	2450.8
42.5°	1055.8	1136.0	1202.7	1304.2	1493.5	1620.8	1758.6	2085.8	2352.4	2376.6	2158.5
45°	998.2	1055.8	1114.8	1230.0	1417.8	1548.1	1701.0	2022.2	2228.2	2158.5	1882.8
47.5°	924.0	975.5	1040.6	1146.7	1337.5	1472.3	1617.7	1940.4	2047.9	1902.5	1601.1
50°	852.8	896.7	957.3	1060.3	1252.7	1384.5	1539.0	1811.6	1864.6	1635.9	1379.9
52.5°	781.6	814.9	874.0	977.0	1169.4	1296.6	1437.5	1679.8	1649.5	1404.2	1176.9
55°	707.4	736.2	792.2	893.7	1072.4	1193.6	1328.4	1517.8	1439.0	1205.7	1024.0
57.5°	634.7	665.0	722.5	807.4	975.5	1093.6	1201.2	1349.6	1231.5	1045.2	884.6
60°	569.5	595.3	639.2	722.5	875.5	970.9	1069.4	1170.9	1072.4	892.2	769.5
62.5°	501.4	525.6	566.5	642.2	774.0	858.9	937.6	1020.9	911.9	780.1	671.0
65°	437.8	457.4	495.3	565.0	672.5	742.2	805.8	863.4	775.5	654.4	572.6
67.5°	380.2	396.9	428.7	490.8	581.7	631.6	683.1	731.6	657.4	560.5	490.8
70°	318.1	331.7	360.5	405.9	478.7	530.2	568.0	604.4	537.7	460.5	413.5
72.5°	263.6	277.2	295.4	342.3	392.3	424.1	465.0	484.7	446.8	383.2	336.3
75°	210.5	221.2	237.8	268.1	315.1	336.3	362.0	377.2	342.3	299.9	271.1
77.5°	165.1	169.7	181.8	203.0	234.8	259.0	278.7	287.8	263.6	236.3	212.1
80°	116.6	122.7	131.8	150.0	174.2	181.8	193.9	204.5	189.3	165.1	150.0
82.5°	77.3	84.8	89.4	96.9	112.1	121.2	124.2	133.3	119.7	110.6	104.5
85°	45.4	48.5	50.0	54.5	62.1	66.6	71.2	72.7	69.7	68.2	62.1
87.5°	22.7	22.7	22.7	25.8	27.3	30.3	31.8	31.8	31.8	30.3	28.8
90°	0.5	1.7	2.9	4.2	5.4	6.0	6.8	8.4	10.0	11.6	13.2
92.5°	12.6	11.9	11.1	10.4	9.7	9.3	9.9	11.0	12.1	13.2	14.3
95°	33.5	28.5	23.5	18.5	13.5	11.0	11.7	13.0	14.3	15.7	17.0
97.5°	61.0	57.6	54.2	50.7	47.3	45.6	42.5	36.3	30.0	23.8	17.6
100°	92.9	95.3	97.7	100.2	102.6	103.8	94.3	75.2	56.2	37.1	18.1
102.5°	129.1	130.7	132.3	133.9	135.5	136.3	125.7	104.4	83.2	61.9	40.7
105°	163.7	165.1	166.4	167.8	169.1	169.8	164.3	153.3	142.3	131.3	120.3
107.5°	200.5	201.6	202.7	203.8	204.9	205.5	206.4	208.2	210.1	211.9	213.7
110°	237.4	238.4	239.3	240.3	241.2	241.7	242.4	243.7	245.1	246.4	247.8

TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	272.5	273.4	274.2	275.1	276.0	276.4	277.1	278.4	279.7	281.1	282.4
115°	307.1	307.8	308.6	309.3	310.0	310.4	311.0	312.1	313.2	314.3	315.4
117.5°	341.2	342.0	342.9	343.7	344.6	345.0	345.3	345.9	346.6	347.2	347.8
120°	372.5	373.6	374.7	375.8	376.9	377.5	377.7	378.0	378.4	378.7	379.1
122.5°	404.4	405.2	406.1	406.9	407.8	408.2	408.4	408.9	409.4	409.9	410.4
125°	432.9	433.9	434.9	435.8	436.8	437.3	437.5	438.0	438.5	439.0	439.5
127.5°	461.5	462.5	463.5	464.4	465.4	465.9	466.2	466.8	467.5	468.1	468.7
130°	487.9	488.9	489.9	490.8	491.8	492.3	492.5	493.0	493.5	494.0	494.5
132.5°	513.2	514.2	515.2	516.1	517.1	517.6	517.8	518.1	518.5	518.8	519.2
135°	539.0	539.7	540.5	541.2	541.9	542.3	542.5	543.0	543.5	544.0	544.5
137.5°	561.0	562.0	563.0	563.9	564.9	565.4	565.5	565.8	566.0	566.3	566.5
140°	582.9	583.6	584.4	585.1	585.8	586.2	586.4	586.8	587.1	587.5	587.9
142.5°	603.3	604.0	604.8	605.5	606.2	606.6	606.8	607.1	607.5	607.8	608.2
145°	622.0	622.8	623.7	624.5	625.4	625.8	625.9	626.2	626.4	626.7	626.9
147.5°	640.1	640.7	641.3	641.9	642.5	642.8	642.9	643.2	643.4	643.7	643.9
150°	656.6	657.0	657.3	657.7	658.0	658.2	658.3	658.6	658.8	659.1	659.3
152.5°	671.4	671.5	671.7	671.8	671.9	672.0	672.1	672.2	672.3	672.4	672.5
155°	685.1	684.9	684.6	684.4	684.1	684.0	684.1	684.2	684.3	684.5	684.6
157.5°	696.1	696.1	696.1	696.1	696.1	696.1	696.0	695.9	695.8	695.7	695.6
160°	706.0	705.9	705.8	705.7	705.6	705.5	705.4	705.3	705.2	705.0	704.9
162.5°	715.4	715.0	714.6	714.3	713.9	713.7	713.6	713.5	713.4	713.3	713.2
165°	722.5	722.1	721.8	721.4	721.1	720.9	720.8	720.7	720.6	720.4	720.3
167.5°	728.5	728.0	727.5	727.0	726.5	726.3	726.3	726.3	726.3	726.3	726.3
170°	733.5	733.0	732.5	732.0	731.5	731.3	731.3	731.3	731.3	731.3	731.3
172.5°	736.8	736.2	735.6	734.9	734.3	734.0	734.1	734.2	734.3	734.5	734.6
175°	739.5	738.9	738.3	737.7	737.1	736.8	736.9	737.0	737.1	737.2	737.3
177.5°	740.6	740.0	739.4	738.8	738.2	737.9	738.0	738.1	738.2	738.3	738.4
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1646.5	1649.5	1660.1	1667.7	1682.9	1681.4	1681.4	1679.8	1675.3	1682.9	1687.4
5°	1761.6	1787.4	1790.4	1823.7	1825.3	1838.9	1848.0	1840.4	1858.6	1857.1	1843.4
7.5°	1904.0	1938.9	1955.5	1987.3	2023.7	2014.6	2049.4	2055.5	2052.5	2067.6	2078.2
10°	2060.0	2120.6	2163.0	2222.1	2237.3	2246.3	2269.1	2288.8	2328.1	2297.8	2317.5
12.5°	2238.8	2282.7	2338.7	2432.7	2479.6	2509.9	2520.5	2534.1	2561.4	2544.8	2546.3
15°	2388.7	2447.8	2543.2	2659.9	2673.5	2711.4	2702.3	2784.1	2823.5	2764.4	2797.7
17.5°	2544.8	2623.5	2737.1	2838.6	2896.2	2921.9	2946.2	3024.9	3021.9	3012.8	3020.4
20°	2644.7	2773.5	2914.3	3049.2	3065.8	3085.5	3150.6	3184.0	3177.9	3203.7	3220.3
22.5°	2785.6	2921.9	3071.9	3161.2	3199.1	3221.8	3273.3	3294.5	3303.6	3309.7	3299.1
25°	2903.7	3049.2	3159.7	3238.5	3261.2	3273.3	3290.0	3296.1	3291.5	3280.9	3290.0
27.5°	2984.0	3100.7	3176.4	3212.7	3200.6	3180.9	3149.1	3127.9	3081.0	3058.2	3085.5
30°	3017.3	3068.8	3091.6	3031.0	2970.4	2921.9	2861.3	2749.2	2661.4	2687.1	2652.3
32.5°	2964.3	2931.0	2821.9	2665.9	2619.0	2540.2	2369.0	2237.3	2241.8	2172.1	2200.9
35°	2808.3	2656.8	2450.8	2214.5	2152.4	2110.0	1922.2	1893.4	1832.8	1767.7	1785.9
37.5°	2532.6	2311.5	2061.6	1887.4	1795.0	1702.6	1596.5	1532.9	1496.6	1469.3	1490.5
40°	2196.4	1926.7	1720.7	1564.7	1486.0	1426.9	1354.2	1290.6	1249.7	1245.1	1252.7
42.5°	1866.2	1638.9	1449.6	1301.2	1275.4	1205.7	1158.8	1108.8	1096.7	1077.0	1087.6
45°	1579.9	1395.1	1239.1	1117.9	1087.6	1069.4	1011.8	980.0	966.4	954.3	972.5
47.5°	1372.3	1178.5	1064.9	992.1	961.9	931.6	899.8	878.5	867.9	869.5	867.9
50°	1172.4	1030.0	930.0	874.0	855.8	834.6	808.9	795.2	790.7	777.1	787.7
52.5°	1008.8	905.8	836.1	783.1	769.5	754.3	733.1	725.6	715.0	711.9	711.9
55°	877.0	796.7	740.7	705.9	689.2	677.1	665.0	655.9	648.3	648.3	648.3
57.5°	774.0	704.4	663.5	633.2	627.1	615.0	601.3	601.3	590.7	589.2	593.8
60°	686.2	624.1	592.3	566.5	557.4	554.4	540.8	540.8	537.7	530.2	536.2
62.5°	596.8	551.4	524.1	504.4	495.3	495.3	484.7	477.1	477.1	478.7	475.6
65°	515.0	481.7	457.4	442.3	437.8	431.7	430.2	424.1	419.6	421.1	419.6
67.5°	442.3	416.6	399.9	387.8	380.2	377.2	372.6	372.6	369.6	371.1	363.5
70°	377.2	351.4	337.8	325.7	322.6	322.6	316.6	318.1	315.1	319.6	316.6
72.5°	310.5	290.8	280.2	275.7	272.7	271.1	268.1	265.1	263.6	266.6	265.1
75°	251.4	234.8	227.2	224.2	221.2	221.2	219.6	218.1	216.6	216.6	216.6
77.5°	195.4	184.8	175.7	178.7	174.2	175.7	171.2	171.2	172.7	171.2	171.2
80°	143.9	136.3	136.3	133.3	127.2	130.3	130.3	125.7	124.2	127.2	122.7
82.5°	95.4	93.9	90.9	89.4	86.3	87.9	86.3	84.8	83.3	86.3	83.3
85°	56.0	56.0	54.5	51.5	54.5	53.0	51.5	51.5	50.0	50.0	50.0
87.5°	28.8	25.8	25.8	24.2	25.8	22.7	24.2	22.7	21.2	22.7	21.2
90°	13.7	14.2	14.7	15.2	15.4	15.5	15.8	16.0	16.3	16.5	16.3
92.5°	15.1	16.0	16.8	17.7	18.1	18.2	18.3	18.4	18.6	18.7	18.6
95°	17.9	18.7	19.6	20.5	20.9	20.9	20.9	20.9	20.9	20.9	20.9
97.5°	18.6	19.6	20.5	21.5	22.0	22.1	22.2	22.3	22.4	22.5	22.4
100°	19.1	20.1	21.0	22.0	22.5	22.6	22.7	22.8	23.0	23.1	23.0
102.5°	36.7	32.6	28.6	24.5	22.5	22.6	22.9	23.1	23.4	23.6	23.4
105°	98.7	77.1	55.5	33.9	23.1	23.2	23.5	23.7	24.0	24.2	24.0
107.5°	194.9	176.1	157.3	138.5	129.1	121.1	105.1	89.1	73.1	57.1	73.1
110°	243.8	239.8	235.7	231.7	229.7	221.0	203.5	186.0	168.6	151.1	168.6

TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	283.5	284.6	285.7	286.8	287.4	287.3	287.0	286.8	286.5	286.3	286.5
115°	316.6	317.8	319.1	320.3	320.9	321.1	321.6	322.1	322.6	323.1	322.6
117.5°	348.8	349.8	350.7	351.7	352.2	352.3	352.4	352.5	352.6	352.7	352.6
120°	380.1	381.1	382.0	383.0	383.5	383.5	383.5	383.5	383.5	383.5	383.5
122.5°	411.0	411.6	412.3	412.9	413.2	413.3	413.4	413.5	413.6	413.7	413.6
125°	439.7	440.0	440.2	440.5	440.6	440.7	441.0	441.2	441.5	441.7	441.5
127.5°	469.1	469.4	469.8	470.1	470.3	470.2	469.9	469.7	469.4	469.2	469.4
130°	495.0	495.5	496.0	496.5	496.7	496.6	496.3	496.1	495.8	495.6	495.8
132.5°	519.7	520.2	520.7	521.2	521.4	521.2	520.9	520.5	520.2	519.8	520.2
135°	544.9	545.2	545.6	545.9	546.1	545.9	545.6	545.2	544.9	544.5	544.9
137.5°	567.1	567.7	568.3	568.9	569.2	569.1	568.8	568.6	568.3	568.1	568.3
140°	588.4	588.9	589.4	589.9	590.1	590.0	589.7	589.5	589.2	589.0	589.2
142.5°	608.6	609.0	609.3	609.7	609.9	609.7	609.3	609.0	608.6	608.2	608.6
145°	627.1	627.4	627.6	627.9	628.0	628.0	628.0	628.0	628.0	628.0	628.0
147.5°	644.1	644.4	644.6	644.9	645.0	644.7	644.1	643.5	642.9	642.3	642.9
150°	659.5	659.8	660.0	660.3	660.4	660.2	659.9	659.5	659.2	658.8	659.2
152.5°	673.0	673.5	674.0	674.5	674.7	674.4	673.8	673.2	672.6	672.0	672.6
155°	685.2	685.8	686.4	687.0	687.3	686.9	686.2	685.5	684.7	684.0	684.7
157.5°	696.3	697.1	697.8	698.5	698.9	698.4	697.4	696.5	695.5	694.5	695.5
160°	705.6	706.4	707.1	707.8	708.2	707.8	706.9	706.1	705.2	704.4	705.2
162.5°	714.0	714.9	715.7	716.6	717.0	716.6	715.9	715.2	714.4	713.7	714.4
165°	721.3	722.3	723.2	724.2	724.7	724.3	723.4	722.6	721.7	720.9	721.7
167.5°	727.3	728.3	729.2	730.2	730.7	730.2	729.2	728.3	727.3	726.3	727.3
170°	732.3	733.3	734.2	735.2	735.7	735.2	734.2	733.3	732.3	731.3	732.3
172.5°	735.6	736.6	737.5	738.5	739.0	738.4	737.3	736.2	735.1	734.0	735.1
175°	738.2	739.0	739.9	740.8	741.2	740.7	739.7	738.8	737.8	736.8	737.8
177.5°	739.4	740.4	741.3	742.3	742.8	742.2	741.0	739.7	738.5	737.3	738.5
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1675.3	1679.8	1667.7	1664.7	1664.7	1670.7	1666.2	1625.3	1632.9	1623.8	1620.8
5°	1860.1	1851.0	1838.9	1832.8	1825.3	1804.0	1802.5	1755.6	1746.5	1716.2	1702.6
7.5°	2063.1	2055.5	2019.1	2014.6	2011.6	1991.9	1941.9	1891.9	1855.5	1820.7	1787.4
10°	2294.8	2272.1	2255.4	2222.1	2205.5	2178.2	2113.1	2066.1	2004.0	1951.0	1881.3
12.5°	2573.5	2547.8	2491.7	2467.5	2446.3	2370.6	2305.4	2252.4	2131.2	2094.9	2008.5
15°	2778.0	2723.5	2717.4	2664.4	2661.4	2578.1	2453.9	2396.3	2302.4	2169.1	2079.7
17.5°	2999.2	2950.7	2912.8	2849.2	2840.1	2761.4	2670.5	2529.6	2426.6	2299.4	2185.8
20°	3161.2	3135.5	3070.4	3044.6	2991.6	2924.9	2831.0	2656.8	2531.1	2403.9	2264.5
22.5°	3290.0	3264.2	3212.7	3177.9	3147.6	3061.3	2949.2	2800.7	2628.1	2461.4	2317.5
25°	3288.5	3280.9	3259.7	3243.0	3220.3	3156.7	3062.8	2920.4	2728.0	2544.8	2344.8
27.5°	3102.2	3123.4	3159.7	3177.9	3173.4	3164.3	3111.3	2991.6	2818.9	2600.8	2376.6
30°	2714.4	2791.7	2859.8	2950.7	2978.0	3044.6	3074.9	3006.7	2868.9	2665.9	2417.5
32.5°	2250.9	2363.0	2511.4	2561.4	2647.8	2776.5	2920.4	2946.2	2859.8	2703.8	2443.3
35°	1846.5	1938.9	2054.0	2132.7	2210.0	2419.0	2600.8	2758.3	2787.1	2684.1	2437.2
37.5°	1528.4	1593.5	1695.0	1761.6	1832.8	2011.6	2266.0	2470.5	2614.4	2617.5	2420.5
40°	1298.1	1326.9	1414.8	1463.2	1531.4	1685.9	1913.1	2179.7	2390.2	2487.2	2376.6
42.5°	1099.7	1137.6	1210.3	1246.6	1290.6	1425.4	1575.3	1828.3	2088.8	2296.3	2294.8
45°	981.5	1008.8	1042.1	1072.4	1122.4	1202.7	1373.9	1563.2	1813.1	2047.9	2140.3
47.5°	877.0	902.8	936.1	945.2	978.5	1054.3	1158.8	1323.9	1557.1	1790.4	1964.6
50°	789.2	810.4	833.1	849.8	864.9	927.0	1005.8	1145.1	1331.4	1557.1	1773.8
52.5°	721.0	736.2	755.9	764.9	778.6	824.0	884.6	987.6	1140.6	1346.6	1557.1
55°	657.4	668.0	680.1	695.3	701.3	734.6	781.6	869.5	983.1	1167.9	1367.8
57.5°	598.3	602.9	610.4	619.5	627.1	655.9	696.8	755.9	855.8	998.2	1187.6
60°	531.7	543.8	548.3	557.4	562.0	584.7	616.5	666.5	743.7	866.4	1008.8
62.5°	475.6	483.2	490.8	495.3	505.9	513.5	539.2	584.7	648.3	739.2	867.9
65°	425.6	428.7	433.2	437.8	440.8	449.9	474.1	504.4	552.9	633.2	733.1
67.5°	368.1	371.1	377.2	378.7	381.7	393.8	407.5	433.2	474.1	534.7	616.5
70°	312.0	316.6	319.6	322.6	327.2	331.7	346.9	368.1	399.9	442.3	505.9
72.5°	263.6	268.1	268.1	271.1	269.6	275.7	290.8	306.0	327.2	362.0	418.1
75°	215.1	215.1	218.1	219.6	221.2	227.2	233.3	245.4	262.0	289.3	324.2
77.5°	169.7	168.1	171.2	171.2	171.2	175.7	181.8	187.8	198.4	218.1	245.4
80°	124.2	124.2	127.2	128.8	125.7	127.2	130.3	136.3	143.9	157.5	172.7
82.5°	81.8	87.9	86.3	87.9	86.3	89.4	90.9	92.4	95.4	101.5	112.1
85°	50.0	50.0	50.0	51.5	50.0	51.5	51.5	51.5	53.0	56.0	60.6
87.5°	21.2	21.2	21.2	22.7	21.2	21.2	22.7	21.2	22.7	22.7	24.2
90°	16.0	15.8	15.5	15.4	15.2	14.7	14.2	13.7	13.2	11.6	10.0
92.5°	18.4	18.3	18.2	18.1	17.7	16.8	16.0	15.1	14.3	13.2	12.1
95°	20.9	20.9	20.9	20.9	20.5	19.6	18.7	17.9	17.0	15.7	14.3
97.5°	22.3	22.2	22.1	22.0	21.5	20.5	19.6	18.6	17.6	23.8	30.0
100°	22.8	22.7	22.6	22.5	22.0	21.0	20.1	19.1	18.1	37.1	56.2
102.5°	23.1	22.9	22.6	22.5	24.5	28.6	32.6	36.7	40.7	61.9	83.2
105°	23.7	23.5	23.2	23.1	33.9	55.5	77.1	98.7	120.3	131.3	142.3
107.5°	89.1	105.1	121.1	129.1	138.5	157.3	176.1	194.9	213.7	211.9	210.1
110°	186.0	203.5	221.0	229.7	231.7	235.7	239.8	243.8	247.8	246.4	245.1

TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	286.8	287.0	287.3	287.4	286.8	285.7	284.6	283.5	282.4	281.1	279.7
115°	322.1	321.6	321.1	320.9	320.3	319.1	317.8	316.6	315.4	314.3	313.2
117.5°	352.5	352.4	352.3	352.2	351.7	350.7	349.8	348.8	347.8	347.2	346.6
120°	383.5	383.5	383.5	383.5	383.0	382.0	381.1	380.1	379.1	378.7	378.4
122.5°	413.5	413.4	413.3	413.2	412.9	412.3	411.6	411.0	410.4	409.9	409.4
125°	441.2	441.0	440.7	440.6	440.5	440.2	440.0	439.7	439.5	439.0	438.5
127.5°	469.7	469.9	470.2	470.3	470.1	469.8	469.4	469.1	468.7	468.1	467.5
130°	496.1	496.3	496.6	496.7	496.5	496.0	495.5	495.0	494.5	494.0	493.5
132.5°	520.5	520.9	521.2	521.4	521.2	520.7	520.2	519.7	519.2	518.8	518.5
135°	545.2	545.6	545.9	546.1	545.9	545.6	545.2	544.9	544.5	544.0	543.5
137.5°	568.6	568.8	569.1	569.2	568.9	568.3	567.7	567.1	566.5	566.3	566.0
140°	589.5	589.7	590.0	590.1	589.9	589.4	588.9	588.4	587.9	587.5	587.1
142.5°	609.0	609.3	609.7	609.9	609.7	609.3	609.0	608.6	608.2	607.8	607.5
145°	628.0	628.0	628.0	628.0	627.9	627.6	627.4	627.1	626.9	626.7	626.4
147.5°	643.5	644.1	644.7	645.0	644.9	644.6	644.4	644.1	643.9	643.7	643.4
150°	659.5	659.9	660.2	660.4	660.3	660.0	659.8	659.5	659.3	659.1	658.8
152.5°	673.2	673.8	674.4	674.7	674.5	674.0	673.5	673.0	672.5	672.4	672.3
155°	685.5	686.2	686.9	687.3	687.0	686.4	685.8	685.2	684.6	684.5	684.3
157.5°	696.5	697.4	698.4	698.9	698.5	697.8	697.1	696.3	695.6	695.7	695.8
160°	706.1	706.9	707.8	708.2	707.8	707.1	706.4	705.6	704.9	705.0	705.2
162.5°	715.2	715.9	716.6	717.0	716.6	715.7	714.9	714.0	713.2	713.3	713.4
165°	722.6	723.4	724.3	724.7	724.2	723.2	722.3	721.3	720.3	720.4	720.6
167.5°	728.3	729.2	730.2	730.7	730.2	729.2	728.3	727.3	726.3	726.3	726.3
170°	733.3	734.2	735.2	735.7	735.2	734.2	733.3	732.3	731.3	731.3	731.3
172.5°	736.2	737.3	738.4	739.0	738.5	737.5	736.6	735.6	734.6	734.5	734.3
175°	738.8	739.7	740.7	741.2	740.8	739.9	739.0	738.2	737.3	737.2	737.1
177.5°	739.7	741.0	742.2	742.8	742.3	741.3	740.4	739.4	738.4	738.3	738.2
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1605.6	1601.1	1601.1	1598.0	1589.0	1572.3	1570.8	1573.8	1564.7	1555.6	1542.0
5°	1684.4	1655.6	1646.5	1637.4	1619.2	1589.0	1576.8	1566.2	1549.6	1529.9	1508.7
7.5°	1751.0	1710.1	1698.0	1681.4	1645.0	1602.6	1575.3	1552.6	1529.9	1502.6	1476.9
10°	1834.3	1775.3	1746.5	1722.3	1672.3	1613.2	1572.3	1539.0	1502.6	1469.3	1436.0
12.5°	1928.3	1832.8	1823.7	1764.7	1707.1	1619.2	1569.3	1520.8	1472.3	1431.4	1396.6
15°	2007.0	1902.5	1864.6	1825.3	1714.7	1605.6	1557.1	1502.6	1446.6	1402.6	1351.1
17.5°	2057.0	1970.7	1890.4	1837.4	1722.3	1625.3	1531.4	1469.3	1410.2	1349.6	1307.2
20°	2117.6	1991.9	1922.2	1851.0	1737.4	1610.2	1516.2	1439.0	1366.3	1311.8	1260.3
22.5°	2178.2	2008.5	1951.0	1873.7	1740.4	1595.0	1489.0	1411.7	1328.4	1273.9	1217.8
25°	2172.1	2032.8	1937.3	1872.2	1710.1	1581.4	1457.2	1366.3	1289.0	1219.4	1163.3
27.5°	2176.7	2005.5	1908.6	1832.8	1688.9	1561.7	1423.8	1328.4	1248.1	1175.4	1116.4
30°	2178.2	1964.6	1879.8	1788.9	1649.5	1514.7	1386.0	1289.0	1204.2	1125.4	1072.4
32.5°	2173.6	1931.3	1825.3	1743.5	1587.4	1469.3	1342.1	1239.1	1152.7	1080.0	1030.0
35°	2163.0	1891.9	1769.2	1666.2	1523.8	1404.2	1301.2	1195.1	1102.7	1036.1	978.5
37.5°	2134.3	1849.5	1710.1	1608.6	1449.6	1328.4	1237.5	1149.7	1060.3	981.5	933.1
40°	2113.1	1791.9	1651.1	1540.5	1369.3	1251.2	1175.4	1092.1	1004.3	933.1	886.1
42.5°	2064.6	1737.4	1590.5	1458.7	1290.6	1169.4	1098.2	1031.5	955.8	886.1	843.7
45°	1985.8	1678.3	1516.2	1383.0	1204.2	1089.1	1024.0	969.4	902.8	836.1	793.7
47.5°	1875.2	1593.5	1437.5	1304.2	1119.4	1002.8	937.6	896.7	843.7	787.7	751.3
50°	1755.6	1501.1	1357.2	1225.4	1037.6	924.0	860.4	822.5	787.7	736.2	701.3
52.5°	1599.6	1402.6	1264.8	1139.1	949.7	840.7	784.6	757.4	721.0	684.7	654.4
55°	1448.1	1275.4	1161.8	1042.1	863.4	761.9	707.4	678.6	657.4	627.1	602.9
57.5°	1272.4	1157.3	1052.7	943.7	783.1	690.7	639.2	604.4	590.7	577.1	554.4
60°	1110.3	1022.4	937.6	846.7	699.8	616.5	566.5	539.2	525.6	516.5	501.4
62.5°	961.9	893.7	821.0	748.3	615.0	539.2	501.4	474.1	462.0	460.5	446.8
65°	819.5	771.0	711.9	640.7	536.2	469.6	433.2	416.6	402.9	402.9	392.3
67.5°	677.1	643.8	596.8	546.8	465.0	402.9	369.6	354.4	346.9	346.9	339.3
70°	563.5	540.8	498.3	454.4	383.2	336.3	310.5	296.9	292.3	293.9	287.8
72.5°	457.4	433.2	398.4	366.6	313.5	278.7	260.5	245.4	237.8	239.3	237.8
75°	354.4	342.3	312.0	287.8	245.4	221.2	204.5	196.9	190.9	192.4	189.3
77.5°	266.6	248.4	231.8	215.1	189.3	169.7	156.0	148.4	143.9	143.9	143.9
80°	181.8	178.7	165.1	156.0	134.8	119.7	109.1	107.5	103.0	103.0	103.0
82.5°	118.1	110.6	103.0	96.9	84.8	75.7	71.2	68.2	66.6	65.1	68.2
85°	65.1	60.6	57.6	51.5	47.0	42.4	37.9	36.4	34.8	36.4	34.8
87.5°	25.8	21.2	21.2	19.7	18.2	16.7	16.7	13.6	13.6	12.1	12.1
90°	8.4	6.8	6.0	5.4	4.2	2.9	1.7	0.5	1.7	2.9	4.2
92.5°	11.0	9.9	9.3	9.7	10.4	11.1	11.9	12.6	11.9	11.1	10.4
95°	13.0	11.7	11.0	13.5	18.5	23.5	28.5	33.5	28.5	23.5	18.5
97.5°	36.3	42.5	45.6	47.3	50.7	54.2	57.6	61.0	57.6	54.2	50.7
100°	75.2	94.3	103.8	102.6	100.2	97.7	95.3	92.9	95.3	97.7	100.2
102.5°	104.4	125.7	136.3	135.5	133.9	132.3	130.7	129.1	130.7	132.3	133.9
105°	153.3	164.3	169.8	169.1	167.8	166.4	165.1	163.7	165.1	166.4	167.8
107.5°	208.2	206.4	205.5	204.9	203.8	202.7	201.6	200.5	201.6	202.7	203.8
110°	243.7	242.4	241.7	241.2	240.3	239.3	238.4	237.4	238.4	239.3	240.3

TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	278.4	277.1	276.4	276.0	275.1	274.2	273.4	272.5	273.4	274.2	275.1
115°	312.1	311.0	310.4	310.0	309.3	308.6	307.8	307.1	307.8	308.6	309.3
117.5°	345.9	345.3	345.0	344.6	343.7	342.9	342.0	341.2	342.0	342.9	343.7
120°	378.0	377.7	377.5	376.9	375.8	374.7	373.6	372.5	373.6	374.7	375.8
122.5°	408.9	408.4	408.2	407.8	406.9	406.1	405.2	404.4	405.2	406.1	406.9
125°	438.0	437.5	437.3	436.8	435.8	434.9	433.9	432.9	433.9	434.9	435.8
127.5°	466.8	466.2	465.9	465.4	464.4	463.5	462.5	461.5	462.5	463.5	464.4
130°	493.0	492.5	492.3	491.8	490.8	489.9	488.9	487.9	488.9	489.9	490.8
132.5°	518.1	517.8	517.6	517.1	516.1	515.2	514.2	513.2	514.2	515.2	516.1
135°	543.0	542.5	542.3	541.9	541.2	540.5	539.7	539.0	539.7	540.5	541.2
137.5°	565.8	565.5	565.4	564.9	563.9	563.0	562.0	561.0	562.0	563.0	563.9
140°	586.8	586.4	586.2	585.8	585.1	584.4	583.6	582.9	583.6	584.4	585.1
142.5°	607.1	606.8	606.6	606.2	605.5	604.8	604.0	603.3	604.0	604.8	605.5
145°	626.2	625.9	625.8	625.4	624.5	623.7	622.8	622.0	622.8	623.7	624.5
147.5°	643.2	642.9	642.8	642.5	641.9	641.3	640.7	640.1	640.7	641.3	641.9
150°	658.6	658.3	658.2	658.0	657.7	657.3	657.0	656.6	657.0	657.3	657.7
152.5°	672.2	672.1	672.0	671.9	671.8	671.7	671.5	671.4	671.5	671.7	671.8
155°	684.2	684.1	684.0	684.1	684.4	684.6	684.9	685.1	684.9	684.6	684.4
157.5°	695.9	696.0	696.1	696.1	696.1	696.1	696.1	696.1	696.1	696.1	696.1
160°	705.3	705.4	705.5	705.6	705.7	705.8	705.9	706.0	705.9	705.8	705.7
162.5°	713.5	713.6	713.7	713.9	714.3	714.6	715.0	715.4	715.0	714.6	714.3
165°	720.7	720.8	720.9	721.1	721.4	721.8	722.1	722.5	722.1	721.8	721.4
167.5°	726.3	726.3	726.3	726.5	727.0	727.5	728.0	728.5	728.0	727.5	727.0
170°	731.3	731.3	731.3	731.5	732.0	732.5	733.0	733.5	733.0	732.5	732.0
172.5°	734.2	734.1	734.0	734.3	734.9	735.6	736.2	736.8	736.2	735.6	734.9
175°	737.0	736.9	736.8	737.1	737.7	738.3	738.9	739.5	738.9	738.3	737.7
177.5°	738.1	738.0	737.9	738.2	738.8	739.4	740.0	740.6	740.0	739.4	738.8
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1539.0	1537.5	1540.5	1531.4	1516.2	1508.7	1487.5	1482.9	1481.4	1482.9	1484.4
5°	1496.6	1495.0	1490.5	1475.3	1457.2	1443.5	1417.8	1416.3	1407.2	1398.1	1402.6
7.5°	1455.7	1449.6	1440.5	1420.8	1396.6	1381.4	1360.2	1345.1	1333.0	1325.4	1319.3
10°	1414.8	1405.7	1396.6	1370.8	1340.5	1317.8	1292.1	1279.9	1266.3	1260.3	1254.2
12.5°	1361.7	1352.7	1336.0	1305.7	1287.5	1258.7	1233.0	1220.9	1213.3	1201.2	1193.6
15°	1319.3	1301.2	1292.1	1260.3	1222.4	1219.4	1172.4	1169.4	1154.2	1154.2	1142.1
17.5°	1270.9	1257.2	1240.6	1208.8	1181.5	1154.2	1130.0	1120.9	1107.3	1104.2	1098.2
20°	1223.9	1205.7	1199.7	1167.9	1139.1	1105.8	1080.0	1070.9	1064.9	1058.8	1063.3
22.5°	1175.4	1160.3	1145.1	1116.4	1095.2	1061.8	1046.7	1037.6	1028.5	1025.5	1027.0
25°	1128.5	1114.8	1099.7	1070.9	1048.2	1020.9	1007.3	1002.8	998.2	998.2	996.7
27.5°	1083.0	1069.4	1055.8	1030.0	1007.3	987.6	977.0	972.5	967.9	970.9	974.0
30°	1036.1	1024.0	1011.8	989.1	970.9	952.8	946.7	943.7	942.2	949.7	949.7
32.5°	993.7	983.1	974.0	952.8	934.6	919.4	914.9	916.4	917.9	922.5	925.5
35°	949.7	942.2	933.1	914.9	899.8	886.1	887.6	887.6	890.7	898.2	904.3
37.5°	910.4	899.8	892.2	877.0	864.9	852.8	857.3	861.9	864.9	874.0	877.0
40°	863.4	858.9	852.8	837.6	827.0	825.5	827.0	830.1	836.1	840.7	845.2
42.5°	825.5	819.5	811.9	799.8	790.7	792.2	793.7	796.7	799.8	807.4	811.9
45°	783.1	778.6	772.5	761.9	754.3	755.9	757.4	757.4	760.4	769.5	772.5
47.5°	736.2	737.7	730.1	719.5	715.0	715.0	715.0	718.0	725.6	728.6	730.1
50°	690.7	687.7	686.2	675.6	672.5	671.0	672.5	674.1	684.7	683.1	687.7
52.5°	642.2	642.2	640.7	634.7	630.1	630.1	627.1	634.7	637.7	640.7	645.3
55°	595.3	590.7	589.2	586.2	580.1	578.6	581.7	590.7	593.8	596.8	601.3
57.5°	543.8	543.8	540.8	536.2	536.2	536.2	536.2	542.3	546.8	549.8	558.9
60°	496.8	490.8	486.2	486.2	486.2	484.7	493.8	493.8	502.9	504.4	507.4
62.5°	440.8	437.8	434.7	436.2	434.7	437.8	440.8	446.8	448.4	452.9	457.4
65°	387.8	387.8	384.7	393.8	387.8	387.8	395.3	395.3	398.4	402.9	409.0
67.5°	336.3	337.8	334.8	334.8	337.8	339.3	340.8	346.9	348.4	354.4	362.0
70°	283.3	286.3	287.8	284.8	287.8	290.8	293.9	295.4	301.4	304.5	309.0
72.5°	236.3	239.3	234.8	236.3	237.8	240.8	242.4	245.4	248.4	257.5	260.5
75°	189.3	187.8	186.3	192.4	189.3	195.4	196.9	196.9	199.9	207.5	210.5
77.5°	145.4	145.4	146.9	143.9	148.4	146.9	148.4	153.0	157.5	157.5	169.7
80°	101.5	104.5	104.5	104.5	106.0	107.5	104.5	112.1	113.6	113.6	118.1
82.5°	65.1	66.6	65.1	68.2	68.2	71.2	69.7	71.2	74.2	77.3	78.8
85°	34.8	34.8	37.9	37.9	36.4	37.9	36.4	37.9	40.9	40.9	42.4
87.5°	12.1	12.1	12.1	12.1	13.6	12.1	13.6	13.6	12.1	12.1	16.7
90°	5.4	6.0	6.8	8.4	10.0	11.6	13.2	13.7	14.2	14.7	15.2
92.5°	9.7	9.3	9.9	11.0	12.1	13.2	14.3	15.1	16.0	16.8	17.7
95°	13.5	11.0	11.7	13.0	14.3	15.7	17.0	17.9	18.7	19.6	20.5
97.5°	47.3	45.6	42.5	36.3	30.0	23.8	17.6	18.6	19.6	20.5	21.5
100°	102.6	103.8	94.3	75.2	56.2	37.1	18.1	19.1	20.1	21.0	22.0
102.5°	135.5	136.3	125.7	104.4	83.2	61.9	40.7	36.7	32.6	28.6	24.5
105°	169.1	169.8	164.3	153.3	142.3	131.3	120.3	98.7	77.1	55.5	33.9
107.5°	204.9	205.5	206.4	208.2	210.1	211.9	213.7	194.9	176.1	157.3	138.5
110°	241.2	241.7	242.4	243.7	245.1	246.4	247.8	243.8	239.8	235.7	231.7

TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	276.0	276.4	277.1	278.4	279.7	281.1	282.4	283.5	284.6	285.7	286.8
115°	310.0	310.4	311.0	312.1	313.2	314.3	315.4	316.6	317.8	319.1	320.3
117.5°	344.6	345.0	345.3	345.9	346.6	347.2	347.8	348.8	349.8	350.7	351.7
120°	376.9	377.5	377.7	378.0	378.4	378.7	379.1	380.1	381.1	382.0	383.0
122.5°	407.8	408.2	408.4	408.9	409.4	409.9	410.4	411.0	411.6	412.3	412.9
125°	436.8	437.3	437.5	438.0	438.5	439.0	439.5	439.7	440.0	440.2	440.5
127.5°	465.4	465.9	466.2	466.8	467.5	468.1	468.7	469.1	469.4	469.8	470.1
130°	491.8	492.3	492.5	493.0	493.5	494.0	494.5	495.0	495.5	496.0	496.5
132.5°	517.1	517.6	517.8	518.1	518.5	518.8	519.2	519.7	520.2	520.7	521.2
135°	541.9	542.3	542.5	543.0	543.5	544.0	544.5	544.9	545.2	545.6	545.9
137.5°	564.9	565.4	565.5	565.8	566.0	566.3	566.5	567.1	567.7	568.3	568.9
140°	585.8	586.2	586.4	586.8	587.1	587.5	587.9	588.4	588.9	589.4	589.9
142.5°	606.2	606.6	606.8	607.1	607.5	607.8	608.2	608.6	609.0	609.3	609.7
145°	625.4	625.8	625.9	626.2	626.4	626.7	626.9	627.1	627.4	627.6	627.9
147.5°	642.5	642.8	642.9	643.2	643.4	643.7	643.9	644.1	644.4	644.6	644.9
150°	658.0	658.2	658.3	658.6	658.8	659.1	659.3	659.5	659.8	660.0	660.3
152.5°	671.9	672.0	672.1	672.2	672.3	672.4	672.5	673.0	673.5	674.0	674.5
155°	684.1	684.0	684.1	684.2	684.3	684.5	684.6	685.2	685.8	686.4	687.0
157.5°	696.1	696.1	696.0	695.9	695.8	695.7	695.6	696.3	697.1	697.8	698.5
160°	705.6	705.5	705.4	705.3	705.2	705.0	704.9	705.6	706.4	707.1	707.8
162.5°	713.9	713.7	713.6	713.5	713.4	713.3	713.2	714.0	714.9	715.7	716.6
165°	721.1	720.9	720.8	720.7	720.6	720.4	720.3	721.3	722.3	723.2	724.2
167.5°	726.5	726.3	726.3	726.3	726.3	726.3	726.3	727.3	728.3	729.2	730.2
170°	731.5	731.3	731.3	731.3	731.3	731.3	731.3	732.3	733.3	734.2	735.2
172.5°	734.3	734.0	734.1	734.2	734.3	734.5	734.6	735.6	736.6	737.5	738.5
175°	737.1	736.8	736.9	737.0	737.1	737.2	737.3	738.2	739.0	739.9	740.8
177.5°	738.2	737.9	738.0	738.1	738.2	738.3	738.4	739.4	740.4	741.3	742.3
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1482.9	1484.4	1478.4	1473.8	1486.0	1478.4	1478.4	1479.9	1476.9	1481.4	1479.9
5°	1399.6	1401.1	1390.5	1393.6	1387.5	1386.0	1384.5	1393.6	1392.0	1390.5	1393.6
7.5°	1317.8	1317.8	1313.3	1310.2	1310.2	1305.7	1311.8	1310.2	1313.3	1313.3	1317.8
10°	1249.7	1252.7	1245.1	1237.5	1236.0	1237.5	1237.5	1239.1	1240.6	1251.2	1249.7
12.5°	1193.6	1189.1	1187.6	1183.0	1175.4	1172.4	1169.4	1186.0	1181.5	1181.5	1181.5
15°	1131.5	1142.1	1140.6	1127.0	1123.9	1130.0	1127.0	1127.0	1142.1	1140.6	1139.1
17.5°	1098.2	1095.2	1092.1	1084.5	1086.1	1084.5	1086.1	1086.1	1095.2	1095.2	1095.2
20°	1060.3	1054.3	1054.3	1051.2	1051.2	1046.7	1052.7	1054.3	1060.3	1060.3	1061.8
22.5°	1027.0	1022.4	1022.4	1020.9	1024.0	1017.9	1024.0	1025.5	1025.5	1030.0	1030.0
25°	998.2	995.2	995.2	998.2	998.2	998.2	998.2	1004.3	999.7	1001.2	999.7
27.5°	972.5	974.0	975.5	977.0	975.5	977.0	978.5	981.5	983.1	981.5	978.5
30°	948.2	952.8	954.3	954.3	957.3	958.8	960.3	960.3	961.9	957.3	960.3
32.5°	930.0	930.0	933.1	934.6	937.6	939.1	939.1	942.2	940.6	936.1	937.6
35°	904.3	904.3	910.4	913.4	917.9	916.4	917.9	917.9	919.4	916.4	911.9
37.5°	878.5	881.6	881.6	887.6	889.1	890.7	889.1	892.2	890.7	887.6	886.1
40°	848.3	846.7	848.3	852.8	854.3	854.3	854.3	857.3	857.3	857.3	855.8
42.5°	810.4	814.9	813.4	818.0	816.4	816.4	819.5	822.5	824.0	819.5	821.0
45°	774.0	774.0	777.1	777.1	778.6	778.6	784.6	781.6	784.6	781.6	783.1
47.5°	734.6	736.2	736.2	737.7	740.7	743.7	740.7	742.2	742.2	743.7	740.7
50°	690.7	690.7	693.7	698.3	704.4	701.3	699.8	705.9	701.3	701.3	698.3
52.5°	645.3	649.8	651.3	655.9	660.4	661.9	663.5	660.4	661.9	657.4	658.9
55°	601.3	602.9	608.9	613.5	618.0	618.0	616.5	618.0	619.5	613.5	613.5
57.5°	557.4	562.0	568.0	568.0	574.1	574.1	572.6	572.6	574.1	569.5	568.0
60°	510.5	515.0	522.6	522.6	531.7	533.2	530.2	527.1	527.1	522.6	524.1
62.5°	460.5	465.0	469.6	477.1	483.2	480.2	486.2	480.2	481.7	472.6	472.6
65°	416.6	418.1	425.6	433.2	433.2	436.2	433.2	434.7	430.2	430.2	424.1
67.5°	365.1	365.1	372.6	380.2	387.8	387.8	387.8	383.2	383.2	378.7	378.7
70°	319.6	318.1	325.7	330.2	334.8	336.3	333.2	331.7	328.7	324.2	322.6
72.5°	263.6	266.6	274.2	277.2	284.8	283.3	290.8	281.7	281.7	274.2	272.7
75°	213.6	216.6	224.2	228.7	233.3	233.3	237.8	233.3	227.2	224.2	222.7
77.5°	169.7	168.1	174.2	181.8	183.3	181.8	184.8	183.3	177.2	177.2	174.2
80°	121.2	125.7	131.8	130.3	136.3	134.8	134.8	131.8	131.8	127.2	130.3
82.5°	80.3	84.8	86.3	84.8	86.3	89.4	90.9	89.4	89.4	86.3	87.9
85°	42.4	42.4	45.4	47.0	45.4	45.4	47.0	51.5	48.5	45.4	48.5
87.5°	13.6	12.1	12.1	13.6	12.1	12.1	13.6	13.6	15.1	15.1	15.1
90°	15.4	15.5	15.8	16.0	16.3	16.5	16.3	16.0	15.8	15.5	15.4
92.5°	18.1	18.2	18.3	18.4	18.6	18.7	18.6	18.4	18.3	18.2	18.1
95°	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9	20.9
97.5°	22.0	22.1	22.2	22.3	22.4	22.5	22.4	22.3	22.2	22.1	22.0
100°	22.5	22.6	22.7	22.8	23.0	23.1	23.0	22.8	22.7	22.6	22.5
102.5°	22.5	22.6	22.9	23.1	23.4	23.6	23.4	23.1	22.9	22.6	22.5
105°	23.1	23.2	23.5	23.7	24.0	24.2	24.0	23.7	23.5	23.2	23.1
107.5°	129.1	121.1	105.1	89.1	73.1	57.1	73.1	89.1	105.1	121.1	129.1
110°	229.7	221.0	203.5	186.0	168.6	151.1	168.6	186.0	203.5	221.0	229.7

TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	287.4	287.3	287.0	286.8	286.5	286.3	286.5	286.8	287.0	287.3	287.4
115°	320.9	321.1	321.6	322.1	322.6	323.1	322.6	322.1	321.6	321.1	320.9
117.5°	352.2	352.3	352.4	352.5	352.6	352.7	352.6	352.5	352.4	352.3	352.2
120°	383.5	383.5	383.5	383.5	383.5	383.5	383.5	383.5	383.5	383.5	383.5
122.5°	413.2	413.3	413.4	413.5	413.6	413.7	413.6	413.5	413.4	413.3	413.2
125°	440.6	440.7	441.0	441.2	441.5	441.7	441.5	441.2	441.0	440.7	440.6
127.5°	470.3	470.2	469.9	469.7	469.4	469.2	469.4	469.7	469.9	470.2	470.3
130°	496.7	496.6	496.3	496.1	495.8	495.6	495.8	496.1	496.3	496.6	496.7
132.5°	521.4	521.2	520.9	520.5	520.2	519.8	520.2	520.5	520.9	521.2	521.4
135°	546.1	545.9	545.6	545.2	544.9	544.5	544.9	545.2	545.6	545.9	546.1
137.5°	569.2	569.1	568.8	568.6	568.3	568.1	568.3	568.6	568.8	569.1	569.2
140°	590.1	590.0	589.7	589.5	589.2	589.0	589.2	589.5	589.7	590.0	590.1
142.5°	609.9	609.7	609.3	609.0	608.6	608.2	608.6	609.0	609.3	609.7	609.9
145°	628.0	628.0	628.0	628.0	628.0	628.0	628.0	628.0	628.0	628.0	628.0
147.5°	645.0	644.7	644.1	643.5	642.9	642.3	642.9	643.5	644.1	644.7	645.0
150°	660.4	660.2	659.9	659.5	659.2	658.8	659.2	659.5	659.9	660.2	660.4
152.5°	674.7	674.4	673.8	673.2	672.6	672.0	672.6	673.2	673.8	674.4	674.7
155°	687.3	686.9	686.2	685.5	684.7	684.0	684.7	685.5	686.2	686.9	687.3
157.5°	698.9	698.4	697.4	696.5	695.5	694.5	695.5	696.5	697.4	698.4	698.9
160°	708.2	707.8	706.9	706.1	705.2	704.4	705.2	706.1	706.9	707.8	708.2
162.5°	717.0	716.6	715.9	715.2	714.4	713.7	714.4	715.2	715.9	716.6	717.0
165°	724.7	724.3	723.4	722.6	721.7	720.9	721.7	722.6	723.4	724.3	724.7
167.5°	730.7	730.2	729.2	728.3	727.3	726.3	727.3	728.3	729.2	730.2	730.7
170°	735.7	735.2	734.2	733.3	732.3	731.3	732.3	733.3	734.2	735.2	735.7
172.5°	739.0	738.4	737.3	736.2	735.1	734.0	735.1	736.2	737.3	738.4	739.0
175°	741.2	740.7	739.7	738.8	737.8	736.8	737.8	738.8	739.7	740.7	741.2
177.5°	742.8	742.2	741.0	739.7	738.5	737.3	738.5	739.7	741.0	742.2	742.8
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1484.4	1487.5	1489.0	1482.9	1478.4	1486.0	1496.6	1504.1	1510.2	1517.8	1522.3
5°	1396.6	1407.2	1407.2	1410.2	1414.8	1422.3	1442.0	1455.7	1467.8	1476.9	1484.4
7.5°	1322.4	1329.9	1334.5	1342.1	1349.6	1360.2	1383.0	1402.6	1420.8	1431.4	1443.5
10°	1255.7	1261.8	1269.3	1273.9	1287.5	1302.7	1331.4	1348.1	1369.3	1386.0	1401.1
12.5°	1192.1	1213.3	1217.8	1216.3	1228.4	1245.1	1273.9	1299.6	1322.4	1339.0	1355.7
15°	1146.7	1154.2	1163.3	1161.8	1187.6	1192.1	1216.3	1246.6	1276.9	1287.5	1302.7
17.5°	1096.7	1108.8	1117.9	1122.4	1130.0	1146.7	1169.4	1192.1	1231.5	1233.0	1272.4
20°	1057.3	1069.4	1075.5	1081.5	1086.1	1105.8	1125.4	1151.2	1183.0	1199.7	1220.9
22.5°	1031.5	1037.6	1042.1	1046.7	1052.7	1063.3	1087.6	1116.4	1137.6	1155.7	1169.4
25°	1001.2	1007.3	1013.4	1016.4	1020.9	1027.0	1045.2	1067.9	1098.2	1110.3	1123.9
27.5°	980.0	980.0	983.1	983.1	989.1	995.2	1008.8	1030.0	1054.3	1069.4	1087.6
30°	957.3	955.8	957.3	955.8	954.3	963.4	975.5	993.7	1010.3	1028.5	1040.6
32.5°	934.6	933.1	933.1	934.6	928.5	933.1	939.1	955.8	974.0	983.1	996.7
35°	910.4	907.3	907.3	907.3	904.3	901.3	907.3	922.5	934.6	946.7	957.3
37.5°	886.1	881.6	881.6	878.5	875.5	871.0	871.0	883.1	899.8	904.3	917.9
40°	852.8	852.8	849.8	848.3	845.2	842.2	837.6	848.3	863.4	867.9	878.5
42.5°	819.5	814.9	813.4	813.4	813.4	808.9	805.8	813.4	822.5	830.1	836.1
45°	781.6	778.6	780.1	778.6	775.5	774.0	772.5	775.5	786.1	789.2	796.7
47.5°	740.7	739.2	739.2	737.7	736.2	737.7	731.6	739.2	742.2	745.2	751.3
50°	698.3	696.8	695.3	693.7	693.7	695.3	693.7	693.7	699.8	702.8	708.9
52.5°	655.9	651.3	651.3	649.8	649.8	646.8	649.8	651.3	654.4	657.4	660.4
55°	610.4	610.4	605.9	605.9	602.9	602.9	604.4	602.9	608.9	612.0	612.0
57.5°	566.5	560.5	562.0	558.9	555.9	554.4	554.4	557.4	560.5	560.5	563.5
60°	519.6	513.5	512.0	505.9	509.0	504.4	505.9	505.9	512.0	509.0	512.0
62.5°	472.6	465.0	460.5	457.4	457.4	459.0	455.9	454.4	457.4	460.5	466.5
65°	422.6	418.1	413.5	409.0	409.0	407.5	410.5	405.9	404.4	405.9	409.0
67.5°	371.1	366.6	362.0	357.5	359.0	354.4	351.4	356.0	352.9	354.4	357.5
70°	321.1	318.1	309.0	306.0	304.5	306.0	304.5	301.4	306.0	304.5	306.0
72.5°	271.1	268.1	263.6	256.0	256.0	254.5	253.0	253.0	251.4	251.4	251.4
75°	222.7	216.6	212.1	210.5	207.5	206.0	204.5	201.5	203.0	204.5	201.5
77.5°	172.7	165.1	163.6	163.6	159.0	159.0	160.6	159.0	157.5	157.5	157.5
80°	127.2	121.2	121.2	118.1	115.1	115.1	115.1	115.1	113.6	112.1	113.6
82.5°	81.8	80.3	78.8	78.8	81.8	75.7	78.8	77.3	75.7	75.7	74.2
85°	45.4	47.0	45.4	47.0	43.9	45.4	45.4	45.4	43.9	45.4	42.4
87.5°	16.7	16.7	16.7	18.2	18.2	18.2	18.2	18.2	19.7	18.2	18.2
90°	15.2	14.7	14.2	13.7	13.2	11.6	10.0	8.4	6.8	6.0	5.4
92.5°	17.7	16.8	16.0	15.1	14.3	13.2	12.1	11.0	9.9	9.3	9.7
95°	20.5	19.6	18.7	17.9	17.0	15.7	14.3	13.0	11.7	11.0	13.5
97.5°	21.5	20.5	19.6	18.6	17.6	23.8	30.0	36.3	42.5	45.6	47.3
100°	22.0	21.0	20.1	19.1	18.1	37.1	56.2	75.2	94.3	103.8	102.6
102.5°	24.5	28.6	32.6	36.7	40.7	61.9	83.2	104.4	125.7	136.3	135.5
105°	33.9	55.5	77.1	98.7	120.3	131.3	142.3	153.3	164.3	169.8	169.1
107.5°	138.5	157.3	176.1	194.9	213.7	211.9	210.1	208.2	206.4	205.5	204.9
110°	231.7	235.7	239.8	243.8	247.8	246.4	245.1	243.7	242.4	241.7	241.2

TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	286.8	285.7	284.6	283.5	282.4	281.1	279.7	278.4	277.1	276.4	276.0
115°	320.3	319.1	317.8	316.6	315.4	314.3	313.2	312.1	311.0	310.4	310.0
117.5°	351.7	350.7	349.8	348.8	347.8	347.2	346.6	345.9	345.3	345.0	344.6
120°	383.0	382.0	381.1	380.1	379.1	378.7	378.4	378.0	377.7	377.5	376.9
122.5°	412.9	412.3	411.6	411.0	410.4	409.9	409.4	408.9	408.4	408.2	407.8
125°	440.5	440.2	440.0	439.7	439.5	439.0	438.5	438.0	437.5	437.3	436.8
127.5°	470.1	469.8	469.4	469.1	468.7	468.1	467.5	466.8	466.2	465.9	465.4
130°	496.5	496.0	495.5	495.0	494.5	494.0	493.5	493.0	492.5	492.3	491.8
132.5°	521.2	520.7	520.2	519.7	519.2	518.8	518.5	518.1	517.8	517.6	517.1
135°	545.9	545.6	545.2	544.9	544.5	544.0	543.5	543.0	542.5	542.3	541.9
137.5°	568.9	568.3	567.7	567.1	566.5	566.3	566.0	565.8	565.5	565.4	564.9
140°	589.9	589.4	588.9	588.4	587.9	587.5	587.1	586.8	586.4	586.2	585.8
142.5°	609.7	609.3	609.0	608.6	608.2	607.8	607.5	607.1	606.8	606.6	606.2
145°	627.9	627.6	627.4	627.1	626.9	626.7	626.4	626.2	625.9	625.8	625.4
147.5°	644.9	644.6	644.4	644.1	643.9	643.7	643.4	643.2	642.9	642.8	642.5
150°	660.3	660.0	659.8	659.5	659.3	659.1	658.8	658.6	658.3	658.2	658.0
152.5°	674.5	674.0	673.5	673.0	672.5	672.4	672.3	672.2	672.1	672.0	671.9
155°	687.0	686.4	685.8	685.2	684.6	684.5	684.3	684.2	684.1	684.0	684.1
157.5°	698.5	697.8	697.1	696.3	695.6	695.7	695.8	695.9	696.0	696.1	696.1
160°	707.8	707.1	706.4	705.6	704.9	705.0	705.2	705.3	705.4	705.5	705.6
162.5°	716.6	715.7	714.9	714.0	713.2	713.3	713.4	713.5	713.6	713.7	713.9
165°	724.2	723.2	722.3	721.3	720.3	720.4	720.6	720.7	720.8	720.9	721.1
167.5°	730.2	729.2	728.3	727.3	726.3	726.3	726.3	726.3	726.3	726.3	726.5
170°	735.2	734.2	733.3	732.3	731.3	731.3	731.3	731.3	731.3	731.3	731.5
172.5°	738.5	737.5	736.6	735.6	734.6	734.5	734.3	734.2	734.1	734.0	734.3
175°	740.8	739.9	739.0	738.2	737.3	737.2	737.1	737.0	736.9	736.8	737.1
177.5°	742.3	741.3	740.4	739.4	738.4	738.3	738.2	738.1	738.0	737.9	738.2
180°	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5	739.5

TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1563.2	1563.2	1563.2	1563.2
2.5°	1529.9	1534.4	1549.6	1567.7
5°	1499.6	1511.7	1532.9	1561.7
7.5°	1466.3	1484.4	1514.7	1551.1
10°	1428.4	1454.1	1492.0	1537.5
12.5°	1387.5	1420.8	1469.3	1516.2
15°	1361.7	1395.1	1439.0	1490.5
17.5°	1311.8	1351.1	1396.6	1469.3
20°	1260.3	1304.2	1363.3	1436.0
22.5°	1220.9	1267.8	1323.9	1401.1
25°	1173.9	1222.4	1283.0	1363.3
27.5°	1123.9	1172.4	1240.6	1325.4
30°	1086.1	1133.0	1198.2	1289.0
32.5°	1040.6	1086.1	1154.2	1249.7
35°	989.1	1040.6	1105.8	1202.7
37.5°	949.7	996.7	1064.9	1157.3
40°	907.3	948.2	1014.9	1105.8
42.5°	861.9	907.3	964.9	1055.8
45°	819.5	852.8	911.9	998.2
47.5°	774.0	811.9	857.3	924.0
50°	725.6	757.4	807.4	852.8
52.5°	678.6	704.4	746.8	781.6
55°	628.6	654.4	686.2	707.4
57.5°	581.7	599.8	621.0	634.7
60°	524.1	542.3	555.9	569.5
62.5°	472.6	486.2	493.8	501.4
65°	419.6	427.2	431.7	437.8
67.5°	362.0	369.6	371.1	380.2
70°	309.0	310.5	313.5	318.1
72.5°	259.0	262.0	260.5	263.6
75°	207.5	210.5	207.5	210.5
77.5°	157.5	160.6	160.6	165.1
80°	113.6	115.1	116.6	116.6
82.5°	74.2	78.8	75.7	77.3
85°	42.4	43.9	43.9	45.4
87.5°	19.7	21.2	19.7	22.7
90°	4.2	2.9	1.7	0.5
92.5°	10.4	11.1	11.9	12.6
95°	18.5	23.5	28.5	33.5
97.5°	50.7	54.2	57.6	61.0
100°	100.2	97.7	95.3	92.9
102.5°	133.9	132.3	130.7	129.1
105°	167.8	166.4	165.1	163.7
107.5°	203.8	202.7	201.6	200.5
110°	240.3	239.3	238.4	237.4

TEST NUMBER: P1011406

CATALOG NUMBER: S123DIP-B1165D585UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	275.1	274.2	273.4	272.5
115°	309.3	308.6	307.8	307.1
117.5°	343.7	342.9	342.0	341.2
120°	375.8	374.7	373.6	372.5
122.5°	406.9	406.1	405.2	404.4
125°	435.8	434.9	433.9	432.9
127.5°	464.4	463.5	462.5	461.5
130°	490.8	489.9	488.9	487.9
132.5°	516.1	515.2	514.2	513.2
135°	541.2	540.5	539.7	539.0
137.5°	563.9	563.0	562.0	561.0
140°	585.1	584.4	583.6	582.9
142.5°	605.5	604.8	604.0	603.3
145°	624.5	623.7	622.8	622.0
147.5°	641.9	641.3	640.7	640.1
150°	657.7	657.3	657.0	656.6
152.5°	671.8	671.7	671.5	671.4
155°	684.4	684.6	684.9	685.1
157.5°	696.1	696.1	696.1	696.1
160°	705.7	705.8	705.9	706.0
162.5°	714.3	714.6	715.0	715.4
165°	721.4	721.8	722.1	722.5
167.5°	727.0	727.5	728.0	728.5
170°	732.0	732.5	733.0	733.5
172.5°	734.9	735.6	736.2	736.8
175°	737.7	738.3	738.9	739.5
177.5°	738.8	739.4	740.0	740.6
180°	739.5	739.5	739.5	739.5

(END OF REPORT)