

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011702

Luminaire Tested: S123DIP-B560D1025UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011702
REPORT IS A COMBINATION OF REPORTS P989960 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1025UB35-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6018.6 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011702

CATALOG NUMBER: S123DIP-B560D1025UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011702

CATALOG NUMBER: S123DIP-B560D1025UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	86	83	79	77	67	65	63	53	52	50	40	39	38
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32
3	79	70	62	57	71	64	57	52	52	47	44	41	38	35	31	29	27
4	72	62	54	48	65	56	49	44	46	41	37	37	33	30	28	26	24
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	36	31	51	41	34	29	34	28	24	27	23	20	21	18	16
8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	19	16	14
9	48	36	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9591	9591	9591
5°	9615	9261	9246
10°	9529	8946	8855
15°	9397	8621	8428
20°	9245	8259	8005
25°	9049	7877	7554
30°	8834	7482	7078
35°	8609	7078	6607
40°	8372	6654	6142
45°	8113	6241	5656
50°	7849	5781	5170
55°	7510	5302	4676
60°	7162	4773	4151
65°	6834	4200	3603
70°	6364	3567	2964
75°	5683	2823	2301
80°	4908	1985	1627
85°	3823	1067	816

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8113 cd/sqm

TEST NUMBER: P1011702

CATALOG NUMBER: S123DIP-B560D1025UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.0	1.4
10°-20°	237.2	3.9
20°-30°	350.3	5.8
30°-40°	409.1	6.8
40°-50°	411.3	6.8
50°-60°	361.3	6.0
60°-70°	269.1	4.5
70°-80°	153.1	2.5
80°-90°	46.3	0.8
90°-100°	278.6	4.6
100°-110°	778.8	12.9
110°-120°	759.4	12.6
120°-130°	604.7	10.0
130°-140°	477.3	7.9
140°-150°	356.1	5.9
150°-160°	248.4	4.1
160°-170°	145.9	2.4
170°-180°	47.5	0.8
0°-30°	671.5	11.2
0°-40°	1080.6	18.0
0°-60°	1853.3	30.8
0°-90°	2321.8	38.6
90°-120°	1816.8	30.2
90°-150°	3255.0	54.1
90°-180°	3697.0	61.4
0°-180°	6018.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	880	887	886	85
15°	849	846	836	842	837	239
25°	771	766	756	757	755	355
35°	667	662	652	647	644	417
45°	546	543	533	524	520	422
55°	414	414	404	395	392	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	43
90°	2	12	25	28	29	5
95°	34	110	589	172	115	36
105°	115	170	798	1396	1262	122
115°	204	254	610	1338	1536	201
125°	283	334	570	1032	1211	251
135°	332	396	562	850	982	256
145°	378	433	555	697	767	237
155°	430	464	537	610	636	198
165°	470	483	514	545	555	132
175°	489	490	493	500	499	46
180°	490	490	490	490	490	

TEST NUMBER: P1011702

CATALOG NUMBER: S123DIP-B560D1025UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	891.0	891.0	891.0	891.0	891.0
2.5°	894.9	891.8	883.4	891.0	890.3
5°	891.8	888.0	879.6	887.2	885.7
7.5°	884.9	881.1	872.7	879.6	878.8
10°	875.7	871.9	861.9	868.8	867.3
12.5°	863.5	860.4	851.2	855.8	855.0
15°	848.9	845.8	835.9	842.0	837.4
17.5°	832.8	829.0	819.0	823.6	822.1
20°	814.4	809.8	799.9	802.9	800.6
22.5°	793.7	789.1	779.2	781.5	778.4
25°	770.8	766.2	756.2	757.0	754.7
27.5°	747.0	742.4	731.7	732.5	730.2
30°	721.0	717.1	706.4	706.4	701.0
32.5°	694.9	689.5	681.9	676.5	674.2
35°	666.6	662.0	652.0	647.4	643.6
37.5°	638.2	632.1	622.1	616.8	614.5
40°	608.3	603.7	593.0	586.9	583.8
42.5°	578.5	573.1	562.4	556.2	553.2
45°	546.3	543.2	533.2	524.1	520.2
47.5°	514.9	510.3	501.1	491.9	488.8
50°	482.7	478.9	468.9	460.5	455.9
52.5°	449.0	446.7	435.9	429.1	424.5
55°	414.5	413.7	403.8	395.3	391.5
57.5°	382.3	379.3	371.6	363.9	359.3
60°	347.1	346.3	337.1	330.2	326.4
62.5°	315.7	313.4	304.2	297.3	295.0
65°	282.7	278.9	271.2	265.1	262.8
67.5°	247.5	244.4	238.3	232.9	229.8
70°	216.1	211.5	206.9	201.5	197.7
72.5°	183.1	180.0	174.7	170.1	168.6
75°	149.4	146.3	144.0	140.2	137.9
77.5°	119.5	118.0	114.9	111.9	111.9
80°	90.4	88.1	86.6	85.8	85.8
82.5°	62.1	62.1	62.1	60.5	59.8
85°	39.8	38.3	38.3	36.8	36.8
87.5°	19.9	17.6	16.9	16.1	16.1
90°	2.0	11.9	24.8	27.8	28.8
92.5°	14.9	59.6	184.6	63.0	52.6
95°	33.7	109.6	588.6	171.7	115.1
97.5°	53.6	125.6	905.2	431.8	236.2
100°	73.4	138.4	940.0	903.2	622.3
102.5°	94.3	153.4	875.4	1209.4	985.6
105°	115.1	170.2	798.0	1395.5	1262.5
107.5°	137.0	190.1	729.5	1477.4	1443.2
110°	160.8	210.4	673.0	1480.0	1546.4



TEST NUMBER: P1011702

CATALOG NUMBER: S123DIP-B560D1025UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	182.6	231.8	635.2	1423.8	1567.3
115°	203.5	253.6	610.4	1338.5	1535.5
117.5°	224.3	274.4	593.6	1247.2	1466.0
120°	246.2	295.3	582.6	1160.8	1374.7
122.5°	265.0	315.1	575.7	1092.8	1289.3
125°	282.9	334.0	569.7	1032.3	1210.9
127.5°	296.8	351.9	566.8	982.6	1143.4
130°	309.7	367.7	563.8	937.0	1087.8
132.5°	319.6	382.1	562.8	894.3	1033.3
135°	331.5	395.5	561.8	850.1	981.6
137.5°	342.4	406.4	559.8	808.4	927.1
140°	353.4	416.4	558.8	767.8	869.5
142.5°	365.3	425.3	556.8	730.6	815.9
145°	378.2	433.2	554.8	697.3	767.3
147.5°	391.1	441.7	551.9	671.4	725.6
150°	404.0	448.6	547.9	648.7	689.8
152.5°	416.9	456.0	542.9	628.8	660.1
155°	429.8	463.6	537.0	610.4	636.2
157.5°	439.7	470.0	532.0	592.6	613.4
160°	451.6	475.4	526.1	576.2	591.6
162.5°	460.5	479.4	520.1	560.8	571.7
165°	469.5	482.9	514.1	545.4	554.8
167.5°	476.4	485.8	508.2	532.0	538.0
170°	482.4	487.4	502.2	520.1	523.1
172.5°	486.4	488.8	497.3	509.7	509.2
175°	489.3	489.8	493.3	500.3	499.3
177.5°	491.3	490.3	490.3	494.3	492.3
180°	490.3	490.3	490.3	490.3	490.3

(END OF REPORT)