

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011732

Luminaire Tested: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011732
REPORT IS A COMBINATION OF REPORTS P990005 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1195UB30-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6694.0 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	32	31
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	30	28	27
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18
7	56	44	37	31	51	41	34	29	33	28	25	27	23	20	20	18	16
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	18	16	14
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	15	13
10	45	33	26	22	41	31	25	20	25	21	17	20	17	14	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8473	8473	8473	8473
5°	8480	9763	8504	7287
10°	8426	11815	8434	6363
15°	8309	14012	8376	5728
20°	8209	16132	8226	5270
25°	8059	16539	8078	5032
30°	7954	13664	7954	4876
35°	7822	9138	7773	4737
40°	7664	6596	7569	4526
45°	7466	5226	7250	4263
50°	6984	4437	6735	4005
55°	6454	3900	6191	3717
60°	5918	3395	5604	3415
65°	5330	2908	5072	3012
70°	4718	2414	4403	2538
75°	4032	1820	3774	1960
80°	3187	1216	2942	1288
85°	2200	559	1758	508

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13666 cd/sqm

TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.4	1.2
10°-20°	248.7	3.7
20°-30°	418.4	6.3
30°-40°	472.9	7.1
40°-50°	423.5	6.3
50°-60°	341.9	5.1
60°-70°	238.2	3.6
70°-80°	125.0	1.9
80°-90°	33.2	0.5
90°-100°	311.3	4.7
100°-110°	911.3	13.6
110°-120°	889.9	13.3
120°-130°	708.7	10.6
130°-140°	559.2	8.4
140°-150°	417.1	6.2
150°-160°	290.9	4.3
160°-170°	170.9	2.6
170°-180°	55.6	0.8
0°-30°	744.5	11.1
0°-40°	1217.4	18.2
0°-60°	1982.7	29.6
0°-90°	2379.2	35.5
90°-120°	2112.5	31.6
90°-150°	3797.6	56.7
90°-180°	4315.0	64.5
0°-180°	6694.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	787	787	787	787	787	
5°	786	935	789	698	786	75
15°	751	1392	757	569	751	212
25°	686	1652	688	503	686	317
35°	606	890	602	462	606	379
45°	503	481	488	392	503	384
55°	356	326	342	311	356	319
65°	220	212	210	220	220	220
75°	106	109	99	118	106	114
85°	23	25	18	23	23	26
90°	2	34	2	34	2	5
95°	40	135	40	135	40	42
105°	135	1477	135	1477	135	143
115°	238	1796	238	1796	238	236
125°	331	1417	331	1417	331	294
135°	388	1148	388	1148	388	300
145°	442	898	442	898	442	277
155°	503	744	503	744	503	231
165°	549	649	549	649	549	155
175°	572	584	572	584	572	54
180°	574	574	574	574	574	

TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2
2.5°	789.5	795.6	798.7	803.3	807.8	814.7	817.0	820.8	819.3	822.3	823.9
5°	786.5	797.2	806.3	817.7	828.4	836.1	843.7	855.9	865.0	866.6	873.4
7.5°	781.1	796.4	812.4	828.4	849.0	861.2	875.0	891.7	905.5	927.6	936.0
10°	774.3	795.6	818.5	840.6	868.9	887.9	904.7	932.9	961.2	984.0	1005.4
12.5°	763.6	790.3	820.0	852.8	889.5	911.6	934.5	971.8	1014.6	1049.6	1072.5
15°	750.6	784.2	822.3	857.4	897.8	939.0	963.4	1005.4	1066.4	1099.2	1158.0
17.5°	739.9	774.3	812.4	867.3	922.3	963.4	981.0	1058.0	1100.0	1154.9	1221.3
20°	723.2	766.6	815.5	870.4	941.3	966.5	1002.4	1080.2	1132.0	1203.7	1285.4
22.5°	705.6	752.1	810.9	868.1	947.4	974.1	1022.9	1084.7	1167.1	1238.1	1328.1
25°	686.5	736.9	796.4	864.3	942.1	981.0	1026.8	1103.0	1192.3	1281.5	1364.7
27.5°	667.5	722.4	784.2	852.1	927.6	973.4	1019.1	1098.5	1212.9	1309.8	1415.8
30°	649.2	704.1	765.9	835.3	914.6	958.9	1002.4	1101.5	1228.9	1338.0	1444.8
32.5°	629.3	685.8	750.6	808.6	888.7	936.0	984.8	1101.5	1238.8	1354.8	1452.4
35°	605.7	663.7	719.3	777.3	856.7	909.3	964.2	1093.9	1248.0	1360.1	1420.4
37.5°	582.8	633.9	682.0	738.4	821.6	878.0	941.3	1084.7	1243.4	1337.2	1354.0
40°	556.9	608.0	646.9	699.5	787.2	852.8	916.9	1072.5	1223.6	1283.1	1234.2
42.5°	531.7	572.1	605.7	656.8	752.1	816.2	885.6	1050.4	1184.7	1196.9	1087.0
45°	502.7	531.7	561.4	619.4	714.0	779.6	856.7	1018.4	1122.1	1087.0	948.2
47.5°	465.3	491.3	524.1	577.5	673.6	741.5	814.7	977.2	1031.3	958.1	806.3
50°	429.5	451.6	482.1	534.0	630.9	697.2	775.0	912.3	939.0	823.9	694.9
52.5°	393.6	410.4	440.1	492.0	588.9	653.0	723.9	846.0	830.7	707.1	592.7
55°	356.2	370.7	399.0	450.1	540.1	601.1	669.0	764.3	724.7	607.2	515.7
57.5°	319.6	334.9	363.9	406.6	491.3	550.8	604.9	679.7	620.2	526.3	445.5
60°	286.8	299.8	321.9	363.9	440.9	489.0	538.6	589.7	540.1	449.3	387.5
62.5°	252.5	264.7	285.3	323.4	389.8	432.5	472.2	514.1	459.2	392.9	337.9
65°	220.5	230.4	249.4	284.5	338.7	373.8	405.8	434.8	390.6	329.5	288.3
67.5°	191.5	199.9	215.9	247.2	292.9	318.1	344.0	368.4	331.1	282.2	247.2
70°	160.2	167.1	181.6	204.4	241.1	267.0	286.1	304.4	270.8	231.9	208.3
72.5°	132.7	139.6	148.8	172.4	197.6	213.6	234.2	244.1	225.0	193.0	169.3
75°	106.0	111.4	119.8	135.0	158.7	169.3	182.3	189.9	172.4	151.0	136.5
77.5°	83.1	85.4	91.5	102.2	118.2	130.4	140.4	144.9	132.7	119.0	106.8
80°	58.7	61.8	66.4	75.5	87.7	91.5	97.6	103.0	95.4	83.1	75.5
82.5°	38.9	42.7	45.0	48.8	56.4	61.0	62.6	67.1	60.3	55.7	52.6
85°	22.9	24.4	25.2	27.5	31.3	33.6	35.9	36.6	35.1	34.3	31.3
87.5°	11.4	11.4	11.4	13.0	13.7	15.3	16.0	16.0	16.0	15.3	14.5
90°	2.3	4.6	7.0	10.5	12.8	14.0	15.1	18.6	22.1	25.5	29.0
92.5°	17.4	25.5	37.2	47.6	59.2	69.6	80.1	117.3	178.8	239.2	216.0
95°	39.5	43.0	55.7	75.5	105.7	128.4	151.0	249.7	422.7	613.1	688.6
97.5°	62.7	63.9	74.3	91.7	121.9	146.9	171.9	269.4	470.3	790.8	1059.0
100°	85.9	87.1	95.2	111.5	139.3	162.0	184.6	265.9	437.8	743.2	1099.6
102.5°	110.3	112.6	119.6	134.7	159.1	179.4	199.7	270.6	409.9	673.5	1024.2
105°	134.7	138.2	145.1	159.1	181.1	199.1	217.1	279.8	399.4	618.9	933.6
107.5°	160.2	163.7	170.7	184.6	205.5	222.4	239.2	294.9	397.1	579.4	853.5
110°	188.1	191.6	197.4	210.2	229.9	246.2	262.4	314.7	402.9	558.5	787.3

TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	213.7	217.1	222.9	235.7	255.5	271.2	286.8	334.4	414.5	546.9	743.2
115°	238.0	242.7	249.7	261.3	281.0	296.7	312.4	356.5	427.3	545.8	714.1
117.5°	262.4	268.2	274.0	284.5	306.5	321.0	335.6	379.7	443.6	546.9	694.4
120°	288.0	291.5	297.3	308.9	330.9	345.4	360.0	401.8	462.1	551.6	681.6
122.5°	310.0	313.5	319.3	332.1	353.0	368.6	384.3	425.0	479.6	559.7	673.5
125°	330.9	333.3	340.2	353.0	375.1	390.8	406.4	447.1	498.1	567.8	666.5
127.5°	347.2	350.7	358.8	371.6	396.0	411.6	427.3	466.8	513.2	577.1	663.0
130°	362.3	365.8	376.2	390.2	414.5	430.2	445.9	484.2	528.3	586.4	659.5
132.5°	373.9	378.5	390.2	407.6	432.0	447.0	462.1	499.3	542.3	593.4	658.4
135°	387.8	392.5	405.2	422.7	447.1	462.8	478.4	514.4	553.9	600.3	657.2
137.5°	400.6	405.2	418.0	436.6	461.0	475.5	490.0	524.9	563.2	605.0	654.9
140°	413.4	419.2	430.8	449.4	472.6	487.1	501.6	535.3	570.1	609.6	653.7
142.5°	427.3	432.0	444.7	461.0	484.2	497.6	510.9	543.4	577.1	613.1	651.4
145°	442.4	445.9	456.3	473.8	493.5	506.8	520.2	550.4	581.7	614.3	649.1
147.5°	457.5	459.8	470.3	485.4	505.1	516.7	528.3	556.2	585.2	614.3	645.6
150°	472.6	473.8	483.0	498.1	514.4	524.8	535.3	562.0	586.4	614.3	641.0
152.5°	487.7	487.7	497.0	509.8	523.7	533.6	543.4	565.5	588.7	610.8	635.2
155°	502.8	502.8	509.8	521.4	534.1	542.2	550.4	570.1	588.7	608.5	628.2
157.5°	514.4	515.6	521.4	531.8	543.4	549.8	556.2	572.5	589.9	605.0	622.4
160°	528.3	528.3	533.0	542.3	550.4	556.2	562.0	575.9	589.9	602.6	615.4
162.5°	538.8	538.8	542.3	549.2	556.2	560.8	565.5	577.1	588.7	598.0	608.5
165°	549.2	548.1	550.4	556.2	560.8	564.9	569.0	578.3	586.4	593.4	601.5
167.5°	557.4	556.2	557.4	562.0	565.5	568.4	571.3	578.3	585.2	588.7	594.5
170°	564.3	562.0	563.2	566.7	569.0	570.2	571.3	577.1	581.7	584.1	587.6
172.5°	569.0	567.8	567.8	570.1	571.3	571.9	572.5	577.1	580.6	580.6	581.7
175°	572.5	571.3	570.1	572.5	572.5	573.0	573.6	575.9	578.3	577.1	577.1
177.5°	574.8	573.6	572.5	573.6	573.6	573.6	573.6	574.8	577.1	574.8	573.6
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2
2.5°	829.2	830.7	836.1	839.9	847.5	846.7	846.7	846.0	843.7	847.5	849.8
5°	887.2	900.1	901.7	918.4	919.2	926.1	930.6	926.8	936.0	935.2	928.4
7.5°	958.9	976.4	984.8	1000.8	1019.1	1014.6	1032.1	1035.2	1033.6	1041.3	1046.6
10°	1037.4	1068.0	1089.3	1119.1	1126.7	1131.3	1142.7	1152.6	1172.5	1157.2	1167.1
12.5°	1127.5	1149.6	1177.8	1225.1	1248.7	1264.0	1269.3	1276.2	1289.9	1281.5	1282.3
15°	1203.0	1232.7	1280.8	1339.5	1346.4	1365.5	1360.9	1402.1	1421.9	1392.2	1408.9
17.5°	1281.5	1321.2	1378.4	1429.5	1458.5	1471.5	1483.7	1523.4	1521.8	1517.3	1521.1
20°	1331.9	1396.7	1467.7	1535.6	1544.0	1553.9	1586.7	1603.5	1600.4	1613.4	1621.8
22.5°	1402.8	1471.5	1547.0	1592.0	1611.1	1622.5	1648.5	1659.1	1663.7	1666.8	1661.4
25°	1462.3	1535.6	1591.3	1630.9	1642.4	1648.5	1656.9	1659.9	1657.6	1652.3	1656.9
27.5°	1502.8	1561.5	1599.6	1617.9	1611.8	1601.9	1585.9	1575.2	1551.6	1540.1	1553.9
30°	1519.5	1545.5	1556.9	1526.4	1495.9	1471.5	1441.0	1384.5	1340.3	1353.2	1335.7
32.5°	1492.8	1476.1	1421.1	1342.6	1318.9	1279.3	1193.1	1126.7	1129.0	1093.9	1108.4
35°	1414.3	1338.0	1234.2	1115.2	1084.0	1062.6	968.0	953.5	923.0	890.2	899.4
37.5°	1275.4	1164.1	1038.2	950.5	903.9	857.4	804.0	772.0	753.7	739.9	750.6
40°	1106.1	970.3	866.6	788.0	748.3	718.6	682.0	649.9	629.3	627.0	630.9
42.5°	939.8	825.4	730.0	655.3	642.3	607.2	583.6	558.4	552.3	542.4	547.7
45°	795.6	702.6	624.0	563.0	547.7	538.6	509.6	493.5	486.7	480.6	489.7
47.5°	691.1	593.5	536.3	499.6	484.4	469.1	453.1	442.4	437.1	437.9	437.1
50°	590.4	518.7	468.4	440.1	431.0	420.3	407.3	400.5	398.2	391.3	396.7
52.5°	508.0	456.2	421.1	394.4	387.5	379.9	369.2	365.4	360.1	358.5	358.5
55°	441.7	401.2	373.0	355.5	347.1	341.0	334.9	330.3	326.5	326.5	326.5
57.5°	389.8	354.7	334.1	318.9	315.8	309.7	302.8	302.8	297.5	296.7	299.0
60°	345.6	314.3	298.3	285.3	280.7	279.2	272.3	272.3	270.8	267.0	270.0
62.5°	300.6	277.7	263.9	254.0	249.4	249.4	244.1	240.3	240.3	241.1	239.5
65°	259.4	242.6	230.4	222.7	220.5	217.4	216.6	213.6	211.3	212.1	211.3
67.5°	222.7	209.8	201.4	195.3	191.5	189.9	187.7	187.7	186.1	186.9	183.1
70°	189.9	177.0	170.1	164.0	162.5	162.5	159.4	160.2	158.7	161.0	159.4
72.5°	156.4	146.5	141.1	138.8	137.3	136.5	135.0	133.5	132.7	134.3	133.5
75°	126.6	118.2	114.4	112.9	111.4	111.4	110.6	109.8	109.1	109.1	109.1
77.5°	98.4	93.1	88.5	90.0	87.7	88.5	86.2	86.2	87.0	86.2	86.2
80°	72.5	68.7	68.7	67.1	64.1	65.6	65.6	63.3	62.6	64.1	61.8
82.5°	48.1	47.3	45.8	45.0	43.5	44.2	43.5	42.7	42.0	43.5	42.0
85°	28.2	28.2	27.5	25.9	27.5	26.7	25.9	25.9	25.2	25.2	25.2
87.5°	14.5	13.0	13.0	12.2	13.0	11.4	12.2	11.4	10.7	11.4	10.7
90°	27.9	29.0	30.2	31.4	32.6	33.7	32.5	33.7	34.8	33.7	34.8
92.5°	161.4	115.0	89.4	77.8	73.8	69.7	67.3	62.7	63.9	61.5	63.9
95°	558.5	418.0	283.3	221.8	200.9	180.0	157.9	147.5	139.3	134.7	139.3
97.5°	1095.0	960.3	724.6	571.3	505.1	438.9	361.1	317.0	289.1	276.4	289.1
100°	1328.4	1369.0	1275.0	1139.1	1056.6	974.2	856.9	772.2	726.9	728.1	726.9
102.5°	1340.0	1504.9	1524.6	1459.6	1414.9	1370.2	1285.4	1222.7	1186.7	1153.0	1186.7
105°	1266.8	1509.5	1625.6	1647.7	1632.6	1617.5	1564.1	1520.0	1482.8	1477.0	1482.8
107.5°	1162.3	1439.9	1622.2	1712.7	1728.4	1744.1	1737.1	1716.2	1701.1	1688.3	1701.1
110°	1064.8	1330.7	1544.4	1690.7	1731.4	1772.0	1804.5	1813.8	1811.4	1809.1	1811.4

TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	980.0	1222.7	1442.2	1610.5	1665.7	1720.9	1787.0	1820.7	1832.3	1833.5	1832.3
115°	915.0	1129.8	1331.9	1502.6	1565.8	1629.1	1716.2	1767.3	1790.5	1796.3	1790.5
117.5°	872.0	1057.8	1236.6	1393.4	1459.0	1524.6	1615.2	1672.1	1706.9	1715.1	1706.9
120°	839.5	1003.3	1160.0	1299.4	1358.0	1416.6	1508.4	1573.4	1601.3	1608.2	1601.3
122.5°	812.8	960.3	1098.5	1225.0	1278.4	1331.9	1410.8	1467.7	1499.1	1508.4	1499.1
125°	790.8	923.1	1049.7	1161.2	1207.6	1254.1	1328.4	1379.5	1408.5	1416.6	1408.5
127.5°	769.9	889.5	1004.4	1106.6	1149.6	1192.5	1259.9	1304.0	1330.7	1337.7	1330.7
130°	753.6	858.1	962.6	1056.7	1096.2	1135.6	1197.2	1239.0	1263.4	1272.6	1263.4
132.5°	738.5	829.1	923.1	1009.1	1046.2	1083.4	1140.3	1182.1	1203.0	1208.8	1203.0
135°	725.7	803.5	886.0	961.5	994.6	1027.6	1084.5	1119.4	1140.3	1148.4	1140.3
137.5°	714.1	779.1	848.8	916.2	945.8	975.4	1024.2	1060.2	1077.6	1084.5	1077.6
140°	703.7	758.2	817.5	873.2	898.2	923.1	967.3	999.8	1018.3	1017.2	1018.3
142.5°	694.4	738.5	787.3	833.7	854.6	875.5	911.5	939.4	955.6	954.5	955.6
145°	686.3	723.4	761.7	798.9	815.8	832.6	861.6	886.0	895.3	897.6	895.3
147.5°	678.1	710.6	742.0	773.3	785.5	797.7	820.9	838.4	847.7	848.8	847.7
150°	670.0	696.7	723.4	747.8	758.8	769.9	787.3	800.0	807.0	807.0	807.0
152.5°	660.7	683.9	706.0	726.9	735.6	744.3	757.1	768.7	772.2	772.2	772.2
155°	651.4	671.2	689.7	707.2	714.2	721.1	731.5	740.8	743.2	744.3	743.2
157.5°	641.0	657.2	673.5	687.4	693.2	699.0	708.3	715.3	717.6	717.6	717.6
160°	630.5	645.6	658.4	670.0	674.0	678.1	686.3	693.2	693.2	692.1	693.2
162.5°	620.1	631.7	642.1	652.6	656.0	659.5	664.2	670.0	670.0	668.8	670.0
165°	610.8	620.1	627.0	635.2	638.1	641.0	645.6	650.3	649.1	649.1	649.1
167.5°	601.5	609.6	615.4	620.1	622.4	624.7	627.0	630.5	629.4	629.4	629.4
170°	593.4	599.2	602.6	607.3	608.4	609.6	610.8	613.1	611.9	611.9	611.9
172.5°	585.2	589.9	592.2	595.7	596.2	596.8	596.8	599.2	596.8	595.7	596.8
175°	579.4	581.7	582.9	585.2	585.2	585.2	585.2	586.4	585.2	584.1	585.2
177.5°	574.8	575.9	577.1	578.3	578.3	578.3	577.1	578.3	575.9	575.9	575.9
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2
2.5°	843.7	846.0	839.9	838.3	838.3	841.4	839.1	818.5	822.3	817.7	816.2
5°	936.7	932.2	926.1	923.0	919.2	908.5	907.8	884.1	879.5	864.3	857.4
7.5°	1039.0	1035.2	1016.8	1014.6	1013.0	1003.1	977.9	952.8	934.5	916.9	900.1
10°	1155.7	1144.2	1135.8	1119.1	1110.7	1096.9	1064.1	1040.5	1009.2	982.5	947.4
12.5°	1296.0	1283.1	1254.8	1242.6	1232.0	1193.8	1161.0	1134.3	1073.3	1055.0	1011.5
15°	1399.0	1371.6	1368.5	1341.8	1340.3	1298.3	1235.8	1206.8	1159.5	1092.4	1047.4
17.5°	1510.4	1486.0	1466.9	1434.9	1430.3	1390.6	1344.9	1273.9	1222.0	1158.0	1100.8
20°	1592.0	1579.0	1546.2	1533.3	1506.6	1473.0	1425.7	1338.0	1274.7	1210.6	1140.4
22.5°	1656.9	1643.9	1617.9	1600.4	1585.1	1541.7	1485.2	1410.5	1323.5	1239.6	1167.1
25°	1656.1	1652.3	1641.6	1633.2	1621.8	1589.7	1542.4	1470.7	1373.8	1281.5	1180.9
27.5°	1562.3	1572.9	1591.3	1600.4	1598.1	1593.5	1566.8	1506.6	1419.6	1309.8	1196.9
30°	1367.0	1405.9	1440.2	1486.0	1499.7	1533.3	1548.5	1514.2	1444.8	1342.6	1217.5
32.5°	1133.6	1190.0	1264.8	1289.9	1333.4	1398.3	1470.7	1483.7	1440.2	1361.6	1230.4
35°	929.9	976.4	1034.4	1074.1	1113.0	1218.2	1309.8	1389.1	1403.6	1351.7	1227.4
37.5°	769.7	802.5	853.6	887.2	923.0	1013.0	1141.2	1244.2	1316.6	1318.2	1219.0
40°	653.7	668.2	712.5	736.9	771.2	849.0	963.4	1097.7	1203.7	1252.6	1196.9
42.5°	553.8	572.9	609.5	627.8	649.9	717.8	793.3	920.7	1051.9	1156.4	1155.7
45°	494.3	508.0	524.8	540.1	565.3	605.7	691.9	787.2	913.1	1031.3	1077.9
47.5°	441.7	454.6	471.4	476.0	492.8	530.9	583.6	666.7	784.2	901.7	989.4
50°	397.4	408.1	419.6	427.9	435.6	466.8	506.5	576.7	670.5	784.2	893.3
52.5°	363.1	370.7	380.6	385.2	392.1	415.0	445.5	497.4	574.4	678.2	784.2
55°	331.1	336.4	342.5	350.1	353.2	370.0	393.6	437.9	495.1	588.1	688.8
57.5°	301.3	303.6	307.4	312.0	315.8	330.3	350.9	380.6	431.0	502.7	598.1
60°	267.8	273.9	276.1	280.7	283.0	294.5	310.5	335.6	374.5	436.3	508.0
62.5°	239.5	243.3	247.2	249.4	254.8	258.6	271.6	294.5	326.5	372.3	437.1
65°	214.4	215.9	218.2	220.5	222.0	226.6	238.8	254.0	278.4	318.9	369.2
67.5°	185.4	186.9	189.9	190.7	192.2	198.3	205.2	218.2	238.8	269.3	310.5
70°	157.1	159.4	161.0	162.5	164.8	167.1	174.7	185.4	201.4	222.7	254.8
72.5°	132.7	135.0	135.0	136.5	135.8	138.8	146.5	154.1	164.8	182.3	210.5
75°	108.3	108.3	109.8	110.6	111.4	114.4	117.5	123.6	132.0	145.7	163.2
77.5°	85.4	84.7	86.2	86.2	86.2	88.5	91.5	94.6	99.9	109.8	123.6
80°	62.6	62.6	64.1	64.8	63.3	64.1	65.6	68.7	72.5	79.3	87.0
82.5°	41.2	44.2	43.5	44.2	43.5	45.0	45.8	46.5	48.1	51.1	56.4
85°	25.2	25.2	25.2	25.9	25.2	25.9	25.9	25.9	26.7	28.2	30.5
87.5°	10.7	10.7	10.7	11.4	10.7	10.7	11.4	10.7	11.4	11.4	12.2
90°	33.7	32.5	33.7	32.6	31.4	30.2	29.0	27.9	29.0	25.5	22.1
92.5°	62.7	67.3	69.7	73.8	77.8	89.4	115.0	161.4	216.0	239.2	178.8
95°	147.5	157.9	180.0	200.9	221.8	283.3	418.0	558.5	688.6	613.1	422.7
97.5°	317.0	361.1	438.9	505.1	571.3	724.6	960.3	1095.0	1059.0	790.8	470.3
100°	772.2	856.9	974.2	1056.6	1139.1	1275.0	1369.0	1328.4	1099.6	743.2	437.8
102.5°	1222.7	1285.4	1370.2	1414.9	1459.6	1524.6	1504.9	1340.0	1024.2	673.5	409.9
105°	1520.0	1564.1	1617.5	1632.6	1647.7	1625.6	1509.5	1266.8	933.6	618.9	399.4
107.5°	1716.2	1737.1	1744.1	1728.4	1712.7	1622.2	1439.9	1162.3	853.5	579.4	397.1
110°	1813.8	1804.5	1772.0	1731.4	1690.7	1544.4	1330.7	1064.8	787.3	558.5	402.9

TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1820.7	1787.0	1720.9	1665.7	1610.5	1442.2	1222.7	980.0	743.2	546.9	414.5
115°	1767.3	1716.2	1629.1	1565.8	1502.6	1331.9	1129.8	915.0	714.1	545.8	427.3
117.5°	1672.1	1615.2	1524.6	1459.0	1393.4	1236.6	1057.8	872.0	694.4	546.9	443.6
120°	1573.4	1508.4	1416.6	1358.0	1299.4	1160.0	1003.3	839.5	681.6	551.6	462.1
122.5°	1467.7	1410.8	1331.9	1278.4	1225.0	1098.5	960.3	812.8	673.5	559.7	479.6
125°	1379.5	1328.4	1254.1	1207.6	1161.2	1049.7	923.1	790.8	666.5	567.8	498.1
127.5°	1304.0	1259.9	1192.5	1149.6	1106.6	1004.4	889.5	769.9	663.0	577.1	513.2
130°	1239.0	1197.2	1135.6	1096.2	1056.7	962.6	858.1	753.6	659.5	586.4	528.3
132.5°	1182.1	1140.3	1083.4	1046.2	1009.1	923.1	829.1	738.5	658.4	593.4	542.3
135°	1119.4	1084.5	1027.6	994.6	961.5	886.0	803.5	725.7	657.2	600.3	553.9
137.5°	1060.2	1024.2	975.4	945.8	916.2	848.8	779.1	714.1	654.9	605.0	563.2
140°	999.8	967.3	923.1	898.2	873.2	817.5	758.2	703.7	653.7	609.6	570.1
142.5°	939.4	911.5	875.5	854.6	833.7	787.3	738.5	694.4	651.4	613.1	577.1
145°	886.0	861.6	832.6	815.8	798.9	761.7	723.4	686.3	649.1	614.3	581.7
147.5°	838.4	820.9	797.7	785.5	773.3	742.0	710.6	678.1	645.6	614.3	585.2
150°	800.0	787.3	769.9	758.8	747.8	723.4	696.7	670.0	641.0	614.3	586.4
152.5°	768.7	757.1	744.3	735.6	726.9	706.0	683.9	660.7	635.2	610.8	588.7
155°	740.8	731.5	721.1	714.2	707.2	689.7	671.2	651.4	628.2	608.5	588.7
157.5°	715.3	708.3	699.0	693.2	687.4	673.5	657.2	641.0	622.4	605.0	589.9
160°	693.2	686.3	678.1	674.0	670.0	658.4	645.6	630.5	615.4	602.6	589.9
162.5°	670.0	664.2	659.5	656.0	652.6	642.1	631.7	620.1	608.5	598.0	588.7
165°	650.3	645.6	641.0	638.1	635.2	627.0	620.1	610.8	601.5	593.4	586.4
167.5°	630.5	627.0	624.7	622.4	620.1	615.4	609.6	601.5	594.5	588.7	585.2
170°	613.1	610.8	609.6	608.4	607.3	602.6	599.2	593.4	587.6	584.1	581.7
172.5°	599.2	596.8	596.8	596.2	595.7	592.2	589.9	585.2	581.7	580.6	580.6
175°	586.4	585.2	585.2	585.2	585.2	582.9	581.7	579.4	577.1	577.1	578.3
177.5°	578.3	577.1	578.3	578.3	578.3	577.1	575.9	574.8	573.6	574.8	577.1
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2
2.5°	808.6	806.3	806.3	804.8	800.2	791.8	791.0	792.6	788.0	783.4	776.6
5°	848.3	833.8	829.2	824.6	815.5	800.2	794.1	788.8	780.4	770.5	759.8
7.5°	881.8	861.2	855.1	846.7	828.4	807.1	793.3	781.9	770.5	756.7	743.8
10°	923.8	894.0	879.5	867.3	842.2	812.4	791.8	775.0	756.7	739.9	723.2
12.5°	971.1	923.0	918.4	888.7	859.7	815.5	790.3	765.9	741.5	720.9	703.3
15°	1010.7	958.1	939.0	919.2	863.5	808.6	784.2	756.7	728.5	706.4	680.4
17.5°	1035.9	992.4	952.0	925.3	867.3	818.5	771.2	739.9	710.2	679.7	658.3
20°	1066.4	1003.1	968.0	932.2	875.0	810.9	763.6	724.7	688.1	660.6	634.7
22.5°	1096.9	1011.5	982.5	943.6	876.5	803.3	749.9	711.0	669.0	641.5	613.3
25°	1093.9	1023.7	975.7	942.9	861.2	796.4	733.8	688.1	649.2	614.1	585.8
27.5°	1096.2	1010.0	961.2	923.0	850.5	786.5	717.1	669.0	628.6	592.0	562.2
30°	1096.9	989.4	946.7	900.9	830.7	762.8	698.0	649.2	606.4	566.8	540.1
32.5°	1094.7	972.6	919.2	878.0	799.4	739.9	675.9	624.0	580.5	543.9	518.7
35°	1089.3	952.8	891.0	839.1	767.4	707.1	655.3	601.9	555.3	521.8	492.8
37.5°	1074.8	931.4	861.2	810.1	730.0	669.0	623.2	579.0	534.0	494.3	469.9
40°	1064.1	902.4	831.5	775.8	689.6	630.1	592.0	550.0	505.8	469.9	446.3
42.5°	1039.7	875.0	801.0	734.6	649.9	588.9	553.0	519.5	481.3	446.3	424.9
45°	1000.1	845.2	763.6	696.5	606.4	548.5	515.7	488.2	454.6	421.1	399.7
47.5°	944.4	802.5	723.9	656.8	563.7	505.0	472.2	451.6	424.9	396.7	378.4
50°	884.1	756.0	683.5	617.1	522.5	465.3	433.3	414.2	396.7	370.7	353.2
52.5°	805.5	706.4	637.0	573.6	478.3	423.4	395.1	381.4	363.1	344.8	329.5
55°	729.3	642.3	585.1	524.8	434.8	383.7	356.2	341.7	331.1	315.8	303.6
57.5°	640.8	582.8	530.2	475.2	394.4	347.8	321.9	304.4	297.5	290.6	279.2
60°	559.2	514.9	472.2	426.4	352.4	310.5	285.3	271.6	264.7	260.1	252.5
62.5°	484.4	450.1	413.5	376.8	309.7	271.6	252.5	238.8	232.7	231.9	225.0
65°	412.7	388.3	358.5	322.7	270.0	236.5	218.2	209.8	202.9	202.9	197.6
67.5°	341.0	324.2	300.6	275.4	234.2	202.9	186.1	178.5	174.7	174.7	170.9
70°	283.8	272.3	251.0	228.8	193.0	169.3	156.4	149.5	147.2	148.0	144.9
72.5°	230.4	218.2	200.6	184.6	157.9	140.4	131.2	123.6	119.8	120.5	119.8
75°	178.5	172.4	157.1	144.9	123.6	111.4	103.0	99.2	96.1	96.9	95.4
77.5°	134.3	125.1	116.7	108.3	95.4	85.4	78.6	74.8	72.5	72.5	72.5
80°	91.5	90.0	83.1	78.6	67.9	60.3	54.9	54.2	51.9	51.9	51.9
82.5°	59.5	55.7	51.9	48.8	42.7	38.1	35.9	34.3	33.6	32.8	34.3
85°	32.8	30.5	29.0	25.9	23.6	21.4	19.1	18.3	17.5	18.3	17.5
87.5°	13.0	10.7	10.7	9.9	9.2	8.4	8.4	6.9	6.9	6.1	6.1
90°	18.6	15.1	14.0	12.8	10.5	7.0	4.6	2.3	4.6	7.0	10.5
92.5°	117.3	80.1	69.6	59.2	47.6	37.2	25.5	17.4	25.5	37.2	47.6
95°	249.7	151.0	128.4	105.7	75.5	55.7	43.0	39.5	43.0	55.7	75.5
97.5°	269.4	171.9	146.9	121.9	91.7	74.3	63.9	62.7	63.9	74.3	91.7
100°	265.9	184.6	162.0	139.3	111.5	95.2	87.1	85.9	87.1	95.2	111.5
102.5°	270.6	199.7	179.4	159.1	134.7	119.6	112.6	110.3	112.6	119.6	134.7
105°	279.8	217.1	199.1	181.1	159.1	145.1	138.2	134.7	138.2	145.1	159.1
107.5°	294.9	239.2	222.4	205.5	184.6	170.7	163.7	160.2	163.7	170.7	184.6
110°	314.7	262.4	246.2	229.9	210.2	197.4	191.6	188.1	191.6	197.4	210.2

TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	334.4	286.8	271.2	255.5	235.7	222.9	217.1	213.7	217.1	222.9	235.7
115°	356.5	312.4	296.7	281.0	261.3	249.7	242.7	238.0	242.7	249.7	261.3
117.5°	379.7	335.6	321.0	306.5	284.5	274.0	268.2	262.4	268.2	274.0	284.5
120°	401.8	360.0	345.4	330.9	308.9	297.3	291.5	288.0	291.5	297.3	308.9
122.5°	425.0	384.3	368.6	353.0	332.1	319.3	313.5	310.0	313.5	319.3	332.1
125°	447.1	406.4	390.8	375.1	353.0	340.2	333.3	330.9	333.3	340.2	353.0
127.5°	466.8	427.3	411.6	396.0	371.6	358.8	350.7	347.2	350.7	358.8	371.6
130°	484.2	445.9	430.2	414.5	390.2	376.2	365.8	362.3	365.8	376.2	390.2
132.5°	499.3	462.1	447.0	432.0	407.6	390.2	378.5	373.9	378.5	390.2	407.6
135°	514.4	478.4	462.8	447.1	422.7	405.2	392.5	387.8	392.5	405.2	422.7
137.5°	524.9	490.0	475.5	461.0	436.6	418.0	405.2	400.6	405.2	418.0	436.6
140°	535.3	501.6	487.1	472.6	449.4	430.8	419.2	413.4	419.2	430.8	449.4
142.5°	543.4	510.9	497.6	484.2	461.0	444.7	432.0	427.3	432.0	444.7	461.0
145°	550.4	520.2	506.8	493.5	473.8	456.3	445.9	442.4	445.9	456.3	473.8
147.5°	556.2	528.3	516.7	505.1	485.4	470.3	459.8	457.5	459.8	470.3	485.4
150°	562.0	535.3	524.8	514.4	498.1	483.0	473.8	472.6	473.8	483.0	498.1
152.5°	565.5	543.4	533.6	523.7	509.8	497.0	487.7	487.7	487.7	497.0	509.8
155°	570.1	550.4	542.2	534.1	521.4	509.8	502.8	502.8	502.8	509.8	521.4
157.5°	572.5	556.2	549.8	543.4	531.8	521.4	515.6	514.4	515.6	521.4	531.8
160°	575.9	562.0	556.2	550.4	542.3	533.0	528.3	528.3	528.3	533.0	542.3
162.5°	577.1	565.5	560.8	556.2	549.2	542.3	538.8	538.8	538.8	542.3	549.2
165°	578.3	569.0	564.9	560.8	556.2	550.4	548.1	549.2	548.1	550.4	556.2
167.5°	578.3	571.3	568.4	565.5	562.0	557.4	556.2	557.4	556.2	557.4	562.0
170°	577.1	571.3	570.2	569.0	566.7	563.2	562.0	564.3	562.0	563.2	566.7
172.5°	577.1	572.5	571.9	571.3	570.1	567.8	567.8	569.0	567.8	567.8	570.1
175°	575.9	573.6	573.0	572.5	572.5	570.1	571.3	572.5	571.3	570.1	572.5
177.5°	574.8	573.6	573.6	573.6	573.6	572.5	573.6	574.8	573.6	572.5	573.6
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2
2.5°	775.0	774.3	775.8	771.2	763.6	759.8	749.1	746.8	746.0	746.8	747.6
5°	753.7	752.9	750.6	743.0	733.8	727.0	714.0	713.2	708.7	704.1	706.4
7.5°	733.1	730.0	725.4	715.5	703.3	695.7	685.0	677.4	671.3	667.5	664.4
10°	712.5	707.9	703.3	690.4	675.1	663.7	650.7	644.6	637.7	634.7	631.6
12.5°	685.8	681.2	672.8	657.6	648.4	633.9	620.9	614.8	611.0	604.9	601.1
15°	664.4	655.3	650.7	634.7	615.6	614.1	590.4	588.9	581.3	581.3	575.2
17.5°	640.0	633.1	624.8	608.7	595.0	581.3	569.1	564.5	557.6	556.1	553.0
20°	616.4	607.2	604.2	588.1	573.6	556.9	543.9	539.3	536.3	533.2	535.5
22.5°	592.0	584.3	576.7	562.2	551.5	534.7	527.1	522.5	518.0	516.4	517.2
25°	568.3	561.4	553.8	539.3	527.9	514.1	507.3	505.0	502.7	502.7	501.9
27.5°	545.4	538.6	531.7	518.7	507.3	497.4	492.0	489.7	487.4	489.0	490.5
30°	521.8	515.7	509.6	498.1	489.0	479.8	476.8	475.2	474.5	478.3	478.3
32.5°	500.4	495.1	490.5	479.8	470.7	463.0	460.7	461.5	462.3	464.6	466.1
35°	478.3	474.5	469.9	460.7	453.1	446.3	447.0	447.0	448.5	452.4	455.4
37.5°	458.5	453.1	449.3	441.7	435.6	429.5	431.8	434.0	435.6	440.1	441.7
40°	434.8	432.5	429.5	421.8	416.5	415.7	416.5	418.0	421.1	423.4	425.7
42.5°	415.7	412.7	408.9	402.8	398.2	399.0	399.7	401.2	402.8	406.6	408.9
45°	394.4	392.1	389.0	383.7	379.9	380.6	381.4	381.4	382.9	387.5	389.0
47.5°	370.7	371.5	367.7	362.3	360.1	360.1	360.1	361.6	365.4	366.9	367.7
50°	347.8	346.3	345.6	340.2	338.7	337.9	338.7	339.5	344.8	344.0	346.3
52.5°	323.4	323.4	322.7	319.6	317.3	317.3	315.8	319.6	321.1	322.7	325.0
55°	299.8	297.5	296.7	295.2	292.2	291.4	292.9	297.5	299.0	300.6	302.8
57.5°	273.9	273.9	272.3	270.0	270.0	270.0	270.0	273.1	275.4	276.9	281.5
60°	250.2	247.2	244.9	244.9	244.9	244.1	248.7	248.7	253.3	254.0	255.5
62.5°	222.0	220.5	218.9	219.7	218.9	220.5	222.0	225.0	225.8	228.1	230.4
65°	195.3	195.3	193.8	198.3	195.3	195.3	199.1	199.1	200.6	202.9	206.0
67.5°	169.3	170.1	168.6	168.6	170.1	170.9	171.6	174.7	175.4	178.5	182.3
70°	142.6	144.2	144.9	143.4	144.9	146.5	148.0	148.8	151.8	153.3	155.6
72.5°	119.0	120.5	118.2	119.0	119.8	121.3	122.1	123.6	125.1	129.7	131.2
75°	95.4	94.6	93.8	96.9	95.4	98.4	99.2	99.2	100.7	104.5	106.0
77.5°	73.2	73.2	74.0	72.5	74.8	74.0	74.8	77.0	79.3	79.3	85.4
80°	51.1	52.6	52.6	52.6	53.4	54.2	52.6	56.4	57.2	57.2	59.5
82.5°	32.8	33.6	32.8	34.3	34.3	35.9	35.1	35.9	37.4	38.9	39.7
85°	17.5	17.5	19.1	19.1	18.3	19.1	18.3	19.1	20.6	20.6	21.4
87.5°	6.1	6.1	6.1	6.1	6.9	6.1	6.9	6.9	6.1	6.1	8.4
90°	12.8	14.0	15.1	18.6	22.1	25.5	29.0	27.9	29.0	30.2	31.4
92.5°	59.2	69.6	80.1	117.3	178.8	239.2	216.0	161.4	115.0	89.4	77.8
95°	105.7	128.4	151.0	249.7	422.7	613.1	688.6	558.5	418.0	283.3	221.8
97.5°	121.9	146.9	171.9	269.4	470.3	790.8	1059.0	1095.0	960.3	724.6	571.3
100°	139.3	162.0	184.6	265.9	437.8	743.2	1099.6	1328.4	1369.0	1275.0	1139.1
102.5°	159.1	179.4	199.7	270.6	409.9	673.5	1024.2	1340.0	1504.9	1524.6	1459.6
105°	181.1	199.1	217.1	279.8	399.4	618.9	933.6	1266.8	1509.5	1625.6	1647.7
107.5°	205.5	222.4	239.2	294.9	397.1	579.4	853.5	1162.3	1439.9	1622.2	1712.7
110°	229.9	246.2	262.4	314.7	402.9	558.5	787.3	1064.8	1330.7	1544.4	1690.7

TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	255.5	271.2	286.8	334.4	414.5	546.9	743.2	980.0	1222.7	1442.2	1610.5
115°	281.0	296.7	312.4	356.5	427.3	545.8	714.1	915.0	1129.8	1331.9	1502.6
117.5°	306.5	321.0	335.6	379.7	443.6	546.9	694.4	872.0	1057.8	1236.6	1393.4
120°	330.9	345.4	360.0	401.8	462.1	551.6	681.6	839.5	1003.3	1160.0	1299.4
122.5°	353.0	368.6	384.3	425.0	479.6	559.7	673.5	812.8	960.3	1098.5	1225.0
125°	375.1	390.8	406.4	447.1	498.1	567.8	666.5	790.8	923.1	1049.7	1161.2
127.5°	396.0	411.6	427.3	466.8	513.2	577.1	663.0	769.9	889.5	1004.4	1106.6
130°	414.5	430.2	445.9	484.2	528.3	586.4	659.5	753.6	858.1	962.6	1056.7
132.5°	432.0	447.0	462.1	499.3	542.3	593.4	658.4	738.5	829.1	923.1	1009.1
135°	447.1	462.8	478.4	514.4	553.9	600.3	657.2	725.7	803.5	886.0	961.5
137.5°	461.0	475.5	490.0	524.9	563.2	605.0	654.9	714.1	779.1	848.8	916.2
140°	472.6	487.1	501.6	535.3	570.1	609.6	653.7	703.7	758.2	817.5	873.2
142.5°	484.2	497.6	510.9	543.4	577.1	613.1	651.4	694.4	738.5	787.3	833.7
145°	493.5	506.8	520.2	550.4	581.7	614.3	649.1	686.3	723.4	761.7	798.9
147.5°	505.1	516.7	528.3	556.2	585.2	614.3	645.6	678.1	710.6	742.0	773.3
150°	514.4	524.8	535.3	562.0	586.4	614.3	641.0	670.0	696.7	723.4	747.8
152.5°	523.7	533.6	543.4	565.5	588.7	610.8	635.2	660.7	683.9	706.0	726.9
155°	534.1	542.2	550.4	570.1	588.7	608.5	628.2	651.4	671.2	689.7	707.2
157.5°	543.4	549.8	556.2	572.5	589.9	605.0	622.4	641.0	657.2	673.5	687.4
160°	550.4	556.2	562.0	575.9	589.9	602.6	615.4	630.5	645.6	658.4	670.0
162.5°	556.2	560.8	565.5	577.1	588.7	598.0	608.5	620.1	631.7	642.1	652.6
165°	560.8	564.9	569.0	578.3	586.4	593.4	601.5	610.8	620.1	627.0	635.2
167.5°	565.5	568.4	571.3	578.3	585.2	588.7	594.5	601.5	609.6	615.4	620.1
170°	569.0	570.2	571.3	577.1	581.7	584.1	587.6	593.4	599.2	602.6	607.3
172.5°	571.3	571.9	572.5	577.1	580.6	580.6	581.7	585.2	589.9	592.2	595.7
175°	572.5	573.0	573.6	575.9	578.3	577.1	577.1	579.4	581.7	582.9	585.2
177.5°	573.6	573.6	573.6	574.8	577.1	574.8	573.6	574.8	575.9	577.1	578.3
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2
2.5°	746.8	747.6	744.5	742.2	748.3	744.5	744.5	745.3	743.8	746.0	745.3
5°	704.8	705.6	700.3	701.8	698.7	698.0	697.2	701.8	701.0	700.3	701.8
7.5°	663.7	663.7	661.4	659.8	659.8	657.6	660.6	659.8	661.4	661.4	663.7
10°	629.3	630.9	627.0	623.2	622.5	623.2	623.2	624.0	624.8	630.1	629.3
12.5°	601.1	598.8	598.1	595.8	592.0	590.4	588.9	597.3	595.0	595.0	595.0
15°	569.8	575.2	574.4	567.5	566.0	569.1	567.5	567.5	575.2	574.4	573.6
17.5°	553.0	551.5	550.0	546.2	546.9	546.2	546.9	546.9	551.5	551.5	551.5
20°	534.0	530.9	530.9	529.4	529.4	527.1	530.2	530.9	534.0	534.0	534.7
22.5°	517.2	514.9	514.9	514.1	515.7	512.6	515.7	516.4	516.4	518.7	518.7
25°	502.7	501.2	501.2	502.7	502.7	502.7	502.7	505.8	503.5	504.2	503.5
27.5°	489.7	490.5	491.3	492.0	491.3	492.0	492.8	494.3	495.1	494.3	492.8
30°	477.5	479.8	480.6	480.6	482.1	482.9	483.6	483.6	484.4	482.1	483.6
32.5°	468.4	468.4	469.9	470.7	472.2	473.0	473.0	474.5	473.7	471.4	472.2
35°	455.4	455.4	458.5	460.0	462.3	461.5	462.3	462.3	463.0	461.5	459.2
37.5°	442.4	444.0	444.0	447.0	447.8	448.5	447.8	449.3	448.5	447.0	446.3
40°	427.2	426.4	427.2	429.5	430.2	430.2	430.2	431.8	431.8	431.8	431.0
42.5°	408.1	410.4	409.6	411.9	411.2	411.2	412.7	414.2	415.0	412.7	413.5
45°	389.8	389.8	391.3	391.3	392.1	392.1	395.1	393.6	395.1	393.6	394.4
47.5°	370.0	370.7	370.7	371.5	373.0	374.5	373.0	373.8	373.8	374.5	373.0
50°	347.8	347.8	349.4	351.7	354.7	353.2	352.4	355.5	353.2	353.2	351.7
52.5°	325.0	327.3	328.0	330.3	332.6	333.4	334.1	332.6	333.4	331.1	331.8
55°	302.8	303.6	306.7	308.9	311.2	311.2	310.5	311.2	312.0	308.9	308.9
57.5°	280.7	283.0	286.1	286.1	289.1	289.1	288.3	288.3	289.1	286.8	286.1
60°	257.1	259.4	263.2	263.2	267.8	268.5	267.0	265.5	265.5	263.2	263.9
62.5°	231.9	234.2	236.5	240.3	243.3	241.8	244.9	241.8	242.6	238.0	238.0
65°	209.8	210.5	214.4	218.2	218.2	219.7	218.2	218.9	216.6	216.6	213.6
67.5°	183.8	183.8	187.7	191.5	195.3	195.3	195.3	193.0	193.0	190.7	190.7
70°	161.0	160.2	164.0	166.3	168.6	169.3	167.8	167.1	165.5	163.2	162.5
72.5°	132.7	134.3	138.1	139.6	143.4	142.6	146.5	141.9	141.9	138.1	137.3
75°	107.6	109.1	112.9	115.2	117.5	117.5	119.8	117.5	114.4	112.9	112.1
77.5°	85.4	84.7	87.7	91.5	92.3	91.5	93.1	92.3	89.3	89.3	87.7
80°	61.0	63.3	66.4	65.6	68.7	67.9	67.9	66.4	66.4	64.1	65.6
82.5°	40.4	42.7	43.5	42.7	43.5	45.0	45.8	45.0	45.0	43.5	44.2
85°	21.4	21.4	22.9	23.6	22.9	22.9	23.6	25.9	24.4	22.9	24.4
87.5°	6.9	6.1	6.1	6.9	6.1	6.1	6.9	6.9	7.6	7.6	7.6
90°	32.6	33.7	32.5	33.7	34.8	33.7	34.8	33.7	32.5	33.7	32.6
92.5°	73.8	69.7	67.3	62.7	63.9	61.5	63.9	62.7	67.3	69.7	73.8
95°	200.9	180.0	157.9	147.5	139.3	134.7	139.3	147.5	157.9	180.0	200.9
97.5°	505.1	438.9	361.1	317.0	289.1	276.4	289.1	317.0	361.1	438.9	505.1
100°	1056.6	974.2	856.9	772.2	726.9	728.1	726.9	772.2	856.9	974.2	1056.6
102.5°	1414.9	1370.2	1285.4	1222.7	1186.7	1153.0	1186.7	1222.7	1285.4	1370.2	1414.9
105°	1632.6	1617.5	1564.1	1520.0	1482.8	1477.0	1482.8	1520.0	1564.1	1617.5	1632.6
107.5°	1728.4	1744.1	1737.1	1716.2	1701.1	1688.3	1701.1	1716.2	1737.1	1744.1	1728.4
110°	1731.4	1772.0	1804.5	1813.8	1811.4	1809.1	1811.4	1813.8	1804.5	1772.0	1731.4

TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1665.7	1720.9	1787.0	1820.7	1832.3	1833.5	1832.3	1820.7	1787.0	1720.9	1665.7
115°	1565.8	1629.1	1716.2	1767.3	1790.5	1796.3	1790.5	1767.3	1716.2	1629.1	1565.8
117.5°	1459.0	1524.6	1615.2	1672.1	1706.9	1715.1	1706.9	1672.1	1615.2	1524.6	1459.0
120°	1358.0	1416.6	1508.4	1573.4	1601.3	1608.2	1601.3	1573.4	1508.4	1416.6	1358.0
122.5°	1278.4	1331.9	1410.8	1467.7	1499.1	1508.4	1499.1	1467.7	1410.8	1331.9	1278.4
125°	1207.6	1254.1	1328.4	1379.5	1408.5	1416.6	1408.5	1379.5	1328.4	1254.1	1207.6
127.5°	1149.6	1192.5	1259.9	1304.0	1330.7	1337.7	1330.7	1304.0	1259.9	1192.5	1149.6
130°	1096.2	1135.6	1197.2	1239.0	1263.4	1272.6	1263.4	1239.0	1197.2	1135.6	1096.2
132.5°	1046.2	1083.4	1140.3	1182.1	1203.0	1208.8	1203.0	1182.1	1140.3	1083.4	1046.2
135°	994.6	1027.6	1084.5	1119.4	1140.3	1148.4	1140.3	1119.4	1084.5	1027.6	994.6
137.5°	945.8	975.4	1024.2	1060.2	1077.6	1084.5	1077.6	1060.2	1024.2	975.4	945.8
140°	898.2	923.1	967.3	999.8	1018.3	1017.2	1018.3	999.8	967.3	923.1	898.2
142.5°	854.6	875.5	911.5	939.4	955.6	954.5	955.6	939.4	911.5	875.5	854.6
145°	815.8	832.6	861.6	886.0	895.3	897.6	895.3	886.0	861.6	832.6	815.8
147.5°	785.5	797.7	820.9	838.4	847.7	848.8	847.7	838.4	820.9	797.7	785.5
150°	758.8	769.9	787.3	800.0	807.0	807.0	807.0	800.0	787.3	769.9	758.8
152.5°	735.6	744.3	757.1	768.7	772.2	772.2	772.2	768.7	757.1	744.3	735.6
155°	714.2	721.1	731.5	740.8	743.2	744.3	743.2	740.8	731.5	721.1	714.2
157.5°	693.2	699.0	708.3	715.3	717.6	717.6	717.6	715.3	708.3	699.0	693.2
160°	674.0	678.1	686.3	693.2	693.2	692.1	693.2	693.2	686.3	678.1	674.0
162.5°	656.0	659.5	664.2	670.0	670.0	668.8	670.0	670.0	664.2	659.5	656.0
165°	638.1	641.0	645.6	650.3	649.1	649.1	649.1	650.3	645.6	641.0	638.1
167.5°	622.4	624.7	627.0	630.5	629.4	629.4	629.4	630.5	627.0	624.7	622.4
170°	608.4	609.6	610.8	613.1	611.9	611.9	611.9	613.1	610.8	609.6	608.4
172.5°	596.2	596.8	596.8	599.2	596.8	595.7	596.8	599.2	596.8	596.8	596.2
175°	585.2	585.2	585.2	586.4	585.2	584.1	585.2	586.4	585.2	585.2	585.2
177.5°	578.3	578.3	577.1	578.3	575.9	575.9	575.9	578.3	577.1	578.3	578.3
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2
2.5°	747.6	749.1	749.9	746.8	744.5	748.3	753.7	757.5	760.5	764.3	766.6
5°	703.3	708.7	708.7	710.2	712.5	716.3	726.2	733.1	739.2	743.8	747.6
7.5°	665.9	669.8	672.0	675.9	679.7	685.0	696.5	706.4	715.5	720.9	727.0
10°	632.4	635.4	639.2	641.5	648.4	656.0	670.5	678.9	689.6	698.0	705.6
12.5°	600.3	611.0	613.3	612.5	618.7	627.0	641.5	654.5	665.9	674.3	682.7
15°	577.5	581.3	585.8	585.1	598.1	600.3	612.5	627.8	643.1	648.4	656.0
17.5°	552.3	558.4	563.0	565.3	569.1	577.5	588.9	600.3	620.2	620.9	640.8
20°	532.5	538.6	541.6	544.7	546.9	556.9	566.8	579.7	595.8	604.2	614.8
22.5°	519.5	522.5	524.8	527.1	530.2	535.5	547.7	562.2	572.9	582.0	588.9
25°	504.2	507.3	510.3	511.9	514.1	517.2	526.3	537.8	553.0	559.2	566.0
27.5°	493.5	493.5	495.1	495.1	498.1	501.2	508.0	518.7	530.9	538.6	547.7
30°	482.1	481.3	482.1	481.3	480.6	485.2	491.3	500.4	508.8	518.0	524.1
32.5°	470.7	469.9	469.9	470.7	467.6	469.9	473.0	481.3	490.5	495.1	501.9
35°	458.5	456.9	456.9	456.9	455.4	453.9	456.9	464.6	470.7	476.8	482.1
37.5°	446.3	444.0	444.0	442.4	440.9	438.6	438.6	444.7	453.1	455.4	462.3
40°	429.5	429.5	427.9	427.2	425.7	424.1	421.8	427.2	434.8	437.1	442.4
42.5°	412.7	410.4	409.6	409.6	409.6	407.3	405.8	409.6	414.2	418.0	421.1
45°	393.6	392.1	392.9	392.1	390.6	389.8	389.0	390.6	395.9	397.4	401.2
47.5°	373.0	372.3	372.3	371.5	370.7	371.5	368.4	372.3	373.8	375.3	378.4
50°	351.7	350.9	350.1	349.4	349.4	350.1	349.4	349.4	352.4	354.0	357.0
52.5°	330.3	328.0	328.0	327.3	327.3	325.7	327.3	328.0	329.5	331.1	332.6
55°	307.4	307.4	305.1	305.1	303.6	303.6	304.4	303.6	306.7	308.2	308.2
57.5°	285.3	282.2	283.0	281.5	280.0	279.2	279.2	280.7	282.2	282.2	283.8
60°	261.6	258.6	257.8	254.8	256.3	254.0	254.8	254.8	257.8	256.3	257.8
62.5°	238.0	234.2	231.9	230.4	230.4	231.1	229.6	228.8	230.4	231.9	234.9
65°	212.8	210.5	208.3	206.0	206.0	205.2	206.7	204.4	203.7	204.4	206.0
67.5°	186.9	184.6	182.3	180.0	180.8	178.5	177.0	179.3	177.7	178.5	180.0
70°	161.7	160.2	155.6	154.1	153.3	154.1	153.3	151.8	154.1	153.3	154.1
72.5°	136.5	135.0	132.7	128.9	128.9	128.2	127.4	127.4	126.6	126.6	126.6
75°	112.1	109.1	106.8	106.0	104.5	103.7	103.0	101.5	102.2	103.0	101.5
77.5°	87.0	83.1	82.4	82.4	80.1	80.1	80.9	80.1	79.3	79.3	79.3
80°	64.1	61.0	61.0	59.5	58.0	58.0	58.0	58.0	57.2	56.4	57.2
82.5°	41.2	40.4	39.7	39.7	41.2	38.1	39.7	38.9	38.1	38.1	37.4
85°	22.9	23.6	22.9	23.6	22.1	22.9	22.9	22.9	22.1	22.9	21.4
87.5°	8.4	8.4	8.4	9.2	9.2	9.2	9.2	9.2	9.9	9.2	9.2
90°	31.4	30.2	29.0	27.9	29.0	25.5	22.1	18.6	15.1	14.0	12.8
92.5°	77.8	89.4	115.0	161.4	216.0	239.2	178.8	117.3	80.1	69.6	59.2
95°	221.8	283.3	418.0	558.5	688.6	613.1	422.7	249.7	151.0	128.4	105.7
97.5°	571.3	724.6	960.3	1095.0	1059.0	790.8	470.3	269.4	171.9	146.9	121.9
100°	1139.1	1275.0	1369.0	1328.4	1099.6	743.2	437.8	265.9	184.6	162.0	139.3
102.5°	1459.6	1524.6	1504.9	1340.0	1024.2	673.5	409.9	270.6	199.7	179.4	159.1
105°	1647.7	1625.6	1509.5	1266.8	933.6	618.9	399.4	279.8	217.1	199.1	181.1
107.5°	1712.7	1622.2	1439.9	1162.3	853.5	579.4	397.1	294.9	239.2	222.4	205.5
110°	1690.7	1544.4	1330.7	1064.8	787.3	558.5	402.9	314.7	262.4	246.2	229.9

TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1610.5	1442.2	1222.7	980.0	743.2	546.9	414.5	334.4	286.8	271.2	255.5
115°	1502.6	1331.9	1129.8	915.0	714.1	545.8	427.3	356.5	312.4	296.7	281.0
117.5°	1393.4	1236.6	1057.8	872.0	694.4	546.9	443.6	379.7	335.6	321.0	306.5
120°	1299.4	1160.0	1003.3	839.5	681.6	551.6	462.1	401.8	360.0	345.4	330.9
122.5°	1225.0	1098.5	960.3	812.8	673.5	559.7	479.6	425.0	384.3	368.6	353.0
125°	1161.2	1049.7	923.1	790.8	666.5	567.8	498.1	447.1	406.4	390.8	375.1
127.5°	1106.6	1004.4	889.5	769.9	663.0	577.1	513.2	466.8	427.3	411.6	396.0
130°	1056.7	962.6	858.1	753.6	659.5	586.4	528.3	484.2	445.9	430.2	414.5
132.5°	1009.1	923.1	829.1	738.5	658.4	593.4	542.3	499.3	462.1	447.0	432.0
135°	961.5	886.0	803.5	725.7	657.2	600.3	553.9	514.4	478.4	462.8	447.1
137.5°	916.2	848.8	779.1	714.1	654.9	605.0	563.2	524.9	490.0	475.5	461.0
140°	873.2	817.5	758.2	703.7	653.7	609.6	570.1	535.3	501.6	487.1	472.6
142.5°	833.7	787.3	738.5	694.4	651.4	613.1	577.1	543.4	510.9	497.6	484.2
145°	798.9	761.7	723.4	686.3	649.1	614.3	581.7	550.4	520.2	506.8	493.5
147.5°	773.3	742.0	710.6	678.1	645.6	614.3	585.2	556.2	528.3	516.7	505.1
150°	747.8	723.4	696.7	670.0	641.0	614.3	586.4	562.0	535.3	524.8	514.4
152.5°	726.9	706.0	683.9	660.7	635.2	610.8	588.7	565.5	543.4	533.6	523.7
155°	707.2	689.7	671.2	651.4	628.2	608.5	588.7	570.1	550.4	542.2	534.1
157.5°	687.4	673.5	657.2	641.0	622.4	605.0	589.9	572.5	556.2	549.8	543.4
160°	670.0	658.4	645.6	630.5	615.4	602.6	589.9	575.9	562.0	556.2	550.4
162.5°	652.6	642.1	631.7	620.1	608.5	598.0	588.7	577.1	565.5	560.8	556.2
165°	635.2	627.0	620.1	610.8	601.5	593.4	586.4	578.3	569.0	564.9	560.8
167.5°	620.1	615.4	609.6	601.5	594.5	588.7	585.2	578.3	571.3	568.4	565.5
170°	607.3	602.6	599.2	593.4	587.6	584.1	581.7	577.1	571.3	570.2	569.0
172.5°	595.7	592.2	589.9	585.2	581.7	580.6	580.6	577.1	572.5	571.9	571.3
175°	585.2	582.9	581.7	579.4	577.1	577.1	578.3	575.9	573.6	573.0	572.5
177.5°	578.3	577.1	575.9	574.8	573.6	574.8	577.1	574.8	573.6	573.6	573.6
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	787.2	787.2	787.2	787.2
2.5°	770.5	772.7	780.4	789.5
5°	755.2	761.3	772.0	786.5
7.5°	738.4	747.6	762.8	781.1
10°	719.3	732.3	751.4	774.3
12.5°	698.7	715.5	739.9	763.6
15°	685.8	702.6	724.7	750.6
17.5°	660.6	680.4	703.3	739.9
20°	634.7	656.8	686.5	723.2
22.5°	614.8	638.5	666.7	705.6
25°	591.2	615.6	646.1	686.5
27.5°	566.0	590.4	624.8	667.5
30°	546.9	570.6	603.4	649.2
32.5°	524.1	546.9	581.3	629.3
35°	498.1	524.1	556.9	605.7
37.5°	478.3	501.9	536.3	582.8
40°	456.9	477.5	511.1	556.9
42.5°	434.0	456.9	485.9	531.7
45°	412.7	429.5	459.2	502.7
47.5°	389.8	408.9	431.8	465.3
50°	365.4	381.4	406.6	429.5
52.5°	341.7	354.7	376.1	393.6
55°	316.6	329.5	345.6	356.2
57.5°	292.9	302.1	312.8	319.6
60°	263.9	273.1	280.0	286.8
62.5°	238.0	244.9	248.7	252.5
65°	211.3	215.1	217.4	220.5
67.5°	182.3	186.1	186.9	191.5
70°	155.6	156.4	157.9	160.2
72.5°	130.4	132.0	131.2	132.7
75°	104.5	106.0	104.5	106.0
77.5°	79.3	80.9	80.9	83.1
80°	57.2	58.0	58.7	58.7
82.5°	37.4	39.7	38.1	38.9
85°	21.4	22.1	22.1	22.9
87.5°	9.9	10.7	9.9	11.4
90°	10.5	7.0	4.6	2.3
92.5°	47.6	37.2	25.5	17.4
95°	75.5	55.7	43.0	39.5
97.5°	91.7	74.3	63.9	62.7
100°	111.5	95.2	87.1	85.9
102.5°	134.7	119.6	112.6	110.3
105°	159.1	145.1	138.2	134.7
107.5°	184.6	170.7	163.7	160.2
110°	210.2	197.4	191.6	188.1

TEST NUMBER: P1011732

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	235.7	222.9	217.1	213.7
115°	261.3	249.7	242.7	238.0
117.5°	284.5	274.0	268.2	262.4
120°	308.9	297.3	291.5	288.0
122.5°	332.1	319.3	313.5	310.0
125°	353.0	340.2	333.3	330.9
127.5°	371.6	358.8	350.7	347.2
130°	390.2	376.2	365.8	362.3
132.5°	407.6	390.2	378.5	373.9
135°	422.7	405.2	392.5	387.8
137.5°	436.6	418.0	405.2	400.6
140°	449.4	430.8	419.2	413.4
142.5°	461.0	444.7	432.0	427.3
145°	473.8	456.3	445.9	442.4
147.5°	485.4	470.3	459.8	457.5
150°	498.1	483.0	473.8	472.6
152.5°	509.8	497.0	487.7	487.7
155°	521.4	509.8	502.8	502.8
157.5°	531.8	521.4	515.6	514.4
160°	542.3	533.0	528.3	528.3
162.5°	549.2	542.3	538.8	538.8
165°	556.2	550.4	548.1	549.2
167.5°	562.0	557.4	556.2	557.4
170°	566.7	563.2	562.0	564.3
172.5°	570.1	567.8	567.8	569.0
175°	572.5	570.1	571.3	572.5
177.5°	573.6	572.5	573.6	574.8
180°	573.6	573.6	573.6	573.6

(END OF REPORT)