

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011737

Luminaire Tested: S123DIP-B560D1195UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011737
REPORT IS A COMBINATION OF REPORTS P990010 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D1195UB30-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6408.0 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011737

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011737

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	53	48	65	56	49	44	45	40	36	36	32	29	27	24	22
5	66	54	46	41	59	50	43	37	40	35	31	32	28	25	24	21	19
6	61	49	41	35	55	44	37	32	36	31	27	29	25	22	22	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9550	9550	9550
5°	9574	9221	9207
10°	9488	8908	8817
15°	9356	8584	8392
20°	9205	8223	7971
25°	9009	7843	7521
30°	8795	7450	7048
35°	8571	7048	6578
40°	8336	6626	6115
45°	8078	6214	5632
50°	7815	5757	5147
55°	7478	5279	4656
60°	7131	4753	4133
65°	6805	4183	3588
70°	6334	3551	2951
75°	5660	2811	2291
80°	4886	1976	1620
85°	3813	1061	811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8078 cd/sqm

TEST NUMBER: P1011737

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	1.3
10°-20°	236.2	3.7
20°-30°	348.8	5.4
30°-40°	407.4	6.4
40°-50°	409.5	6.4
50°-60°	359.8	5.6
60°-70°	267.9	4.2
70°-80°	152.5	2.4
80°-90°	46.5	0.7
90°-100°	95.2	1.5
100°-110°	288.0	4.5
110°-120°	490.3	7.7
120°-130°	645.0	10.1
130°-140°	725.0	11.3
140°-150°	712.8	11.1
150°-160°	600.1	9.4
160°-170°	399.5	6.2
170°-180°	139.9	2.2
0°-30°	668.6	10.4
0°-40°	1076.0	16.8
0°-60°	1845.2	28.8
0°-90°	2312.1	36.1
90°-120°	873.5	13.6
90°-150°	2956.4	46.1
90°-180°	4096.0	63.9
0°-180°	6408.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	887	887	887	887	887	
5°	888	884	876	883	882	84
15°	845	842	832	838	834	238
25°	767	763	753	754	751	354
35°	664	659	649	645	641	415
45°	544	541	531	522	518	420
55°	413	412	402	394	390	370
65°	282	278	270	264	262	278
75°	149	146	143	140	137	159
85°	40	38	38	37	37	43
90°	1	13	28	32	35	8
95°	68	77	86	91	91	75
105°	261	264	274	274	276	280
115°	494	497	495	496	495	488
125°	722	726	723	719	714	644
135°	937	944	943	938	936	722
145°	1137	1139	1143	1142	1137	710
155°	1302	1302	1303	1308	1299	599
165°	1418	1414	1414	1421	1413	400
175°	1475	1470	1470	1477	1469	140
180°	1478	1478	1478	1478	1478	

TEST NUMBER: P1011737

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	887.2	887.2	887.2	887.2	887.2
2.5°	891.0	888.0	879.6	887.2	886.4
5°	888.0	884.2	875.8	883.4	881.9
7.5°	881.1	877.3	868.9	875.8	875.0
10°	871.9	868.1	858.2	865.1	863.6
12.5°	859.7	856.7	847.5	852.1	851.4
15°	845.2	842.2	832.3	838.4	833.8
17.5°	829.2	825.4	815.5	820.1	818.5
20°	810.9	806.3	796.4	799.5	797.2
22.5°	790.3	785.7	775.8	778.1	775.1
25°	767.4	762.9	752.9	753.7	751.4
27.5°	743.8	739.2	728.5	729.3	727.0
30°	717.8	714.0	703.4	703.4	698.0
32.5°	691.9	686.6	678.9	673.6	671.3
35°	663.7	659.1	649.2	644.6	640.8
37.5°	635.5	629.4	619.4	614.1	611.8
40°	605.7	601.1	590.5	584.3	581.3
42.5°	576.0	570.6	559.9	553.8	550.8
45°	543.9	540.9	530.9	521.8	518.0
47.5°	512.6	508.1	498.9	489.8	486.7
50°	480.6	476.8	466.9	458.5	453.9
52.5°	447.0	444.7	434.1	427.2	422.6
55°	412.7	411.9	402.0	393.6	389.8
57.5°	380.7	377.6	370.0	362.4	357.8
60°	345.6	344.8	335.7	328.8	325.0
62.5°	314.3	312.0	302.9	296.0	293.7
65°	281.5	277.7	270.1	263.9	261.7
67.5°	246.4	243.4	237.2	231.9	228.9
70°	215.1	210.5	206.0	200.6	196.8
72.5°	182.3	179.3	173.9	169.4	167.8
75°	148.8	145.7	143.4	139.6	137.3
77.5°	119.0	117.5	114.4	111.4	111.4
80°	90.0	87.7	86.2	85.4	85.4
82.5°	61.8	61.8	61.8	60.3	59.5
85°	39.7	38.1	38.1	36.6	36.6
87.5°	19.8	17.5	16.8	16.0	16.0
90°	1.2	12.8	27.9	32.5	34.8
92.5°	34.8	41.8	48.8	52.3	49.9
95°	68.5	76.6	85.9	90.6	90.6
97.5°	112.6	118.4	125.4	131.2	130.1
100°	157.9	164.9	170.7	174.2	176.5
102.5°	210.2	213.7	221.8	225.3	224.1
105°	261.3	263.6	274.0	274.0	276.4
107.5°	321.7	322.8	327.5	330.9	329.8
110°	377.4	379.7	382.0	386.7	384.4

TEST NUMBER: P1011737

CATALOG NUMBER: S123DIP-B560D1195UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	435.5	436.6	436.6	442.4	442.4
115°	493.5	497.0	494.7	495.8	494.7
117.5°	552.7	553.9	551.6	551.6	548.1
120°	607.3	614.3	608.5	607.3	605.0
122.5°	664.2	668.9	666.5	663.1	659.6
125°	722.3	725.8	723.4	718.8	714.1
127.5°	775.7	782.7	780.3	773.4	768.7
130°	829.1	838.4	834.9	830.3	822.1
132.5°	882.5	891.8	889.5	883.7	877.9
135°	937.1	944.1	942.9	938.3	935.9
137.5°	987.0	992.8	996.3	990.5	987.0
140°	1039.3	1045.1	1046.2	1045.1	1037.0
142.5°	1086.9	1092.7	1095.0	1093.9	1088.1
145°	1136.8	1139.1	1142.6	1141.5	1136.8
147.5°	1179.8	1184.4	1187.9	1187.9	1180.9
150°	1225.1	1227.4	1229.7	1229.7	1222.8
152.5°	1262.2	1265.7	1266.9	1269.2	1263.4
155°	1301.7	1301.7	1302.9	1307.5	1299.4
157.5°	1335.4	1334.2	1335.4	1340.0	1333.1
160°	1366.7	1364.4	1364.4	1370.2	1365.6
162.5°	1394.6	1391.1	1392.3	1398.1	1390.0
165°	1417.8	1414.4	1414.4	1421.3	1413.2
167.5°	1437.6	1432.9	1434.1	1441.1	1434.1
170°	1453.8	1449.2	1449.2	1457.3	1449.2
172.5°	1466.6	1462.0	1462.0	1468.9	1460.8
175°	1474.7	1470.1	1470.1	1477.1	1468.9
177.5°	1479.4	1474.7	1474.7	1481.7	1473.6
180°	1478.2	1478.2	1478.2	1478.2	1478.2

(END OF REPORT)