

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011482

Luminaire Tested: S123DIP-B340D1025UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011482
REPORT IS A COMBINATION OF REPORTS P989659 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1025UB35-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4882.0 lumens
Efficiency: N/A
Efficacy: 117.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011482

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011482

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	79	76	73	62	60	58	46	45	44	32	31	30
2	85	77	71	66	75	69	64	60	54	51	48	41	39	37	28	27	26
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22
4	70	60	52	47	63	54	47	42	43	38	34	32	29	26	22	20	19
5	64	53	45	40	57	48	41	36	38	33	29	29	25	23	20	18	16
6	59	48	40	34	53	43	36	31	34	29	26	26	22	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	13
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5704	5704	5704
5°	5717	5506	5499
10°	5667	5321	5265
15°	5588	5127	5012
20°	5497	4911	4761
25°	5380	4684	4492
30°	5253	4449	4210
35°	5119	4209	3928
40°	4978	3957	3653
45°	4824	3712	3364
50°	4667	3438	3074
55°	4466	3153	2780
60°	4259	2839	2468
65°	4064	2498	2143
70°	3784	2120	1762
75°	3378	1680	1368
80°	2921	1180	967
85°	2276	635	485

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4824 cd/sqm

TEST NUMBER: P1011482

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	1.0
10°-20°	141.0	2.9
20°-30°	208.3	4.3
30°-40°	243.3	5.0
40°-50°	244.6	5.0
50°-60°	214.8	4.4
60°-70°	160.0	3.3
70°-80°	91.1	1.9
80°-90°	28.6	0.6
90°-100°	81.3	1.7
100°-110°	246.1	5.0
110°-120°	419.0	8.6
120°-130°	551.2	11.3
130°-140°	619.6	12.7
140°-150°	609.2	12.5
150°-160°	512.8	10.5
160°-170°	341.4	7.0
170°-180°	119.6	2.4
0°-30°	399.3	8.2
0°-40°	642.6	13.2
0°-60°	1102.0	22.6
0°-90°	1381.7	28.3
90°-120°	746.5	15.3
90°-150°	2526.5	51.8
90°-180°	3500.0	71.7
0°-180°	4882.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	530	530	530	530	530	
5°	530	528	523	528	527	50
15°	505	503	497	501	498	142
25°	458	456	450	450	449	211
35°	396	394	388	385	383	248
45°	325	323	317	312	309	251
55°	246	246	240	235	233	221
65°	168	166	161	158	156	166
75°	89	87	86	83	82	95
85°	24	23	23	22	22	25
90°	1	11	24	28	30	6
95°	58	66	73	77	77	65
105°	223	225	234	234	236	239
115°	422	425	423	424	423	417
125°	617	620	618	614	610	550
135°	801	807	806	802	800	617
145°	972	974	976	976	972	607
155°	1112	1112	1113	1117	1110	512
165°	1212	1209	1209	1215	1208	342
175°	1260	1256	1256	1262	1255	120
180°	1263	1263	1263	1263	1263	

TEST NUMBER: P1011482

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	529.9	529.9	529.9	529.9	529.9
2.5°	532.1	530.3	525.3	529.9	529.4
5°	530.3	528.0	523.0	527.6	526.7
7.5°	526.2	523.9	518.9	523.0	522.6
10°	520.8	518.5	512.6	516.7	515.7
12.5°	513.5	511.6	506.2	508.9	508.5
15°	504.8	503.0	497.1	500.7	498.0
17.5°	495.2	493.0	487.0	489.8	488.9
20°	484.3	481.6	475.6	477.5	476.1
22.5°	472.0	469.3	463.3	464.7	462.9
25°	458.3	455.6	449.7	450.1	448.8
27.5°	444.2	441.5	435.1	435.6	434.2
30°	428.7	426.4	420.1	420.1	416.9
32.5°	413.2	410.0	405.5	402.3	400.9
35°	396.4	393.6	387.7	385.0	382.7
37.5°	379.5	375.9	369.9	366.8	365.4
40°	361.7	359.0	352.6	349.0	347.2
42.5°	344.0	340.8	334.4	330.8	328.9
45°	324.8	323.0	317.1	311.6	309.4
47.5°	306.2	303.4	298.0	292.5	290.7
50°	287.0	284.8	278.8	273.8	271.1
52.5°	267.0	265.6	259.2	255.1	252.4
55°	246.5	246.0	240.1	235.1	232.8
57.5°	227.3	225.5	221.0	216.4	213.7
60°	206.4	205.9	200.5	196.4	194.1
62.5°	187.7	186.3	180.9	176.8	175.4
65°	168.1	165.8	161.3	157.6	156.3
67.5°	147.2	145.3	141.7	138.5	136.7
70°	128.5	125.7	123.0	119.8	117.5
72.5°	108.9	107.1	103.9	101.1	100.2
75°	88.8	87.0	85.7	83.4	82.0
77.5°	71.1	70.2	68.3	66.5	66.5
80°	53.8	52.4	51.5	51.0	51.0
82.5°	36.9	36.9	36.9	36.0	35.5
85°	23.7	22.8	22.8	21.9	21.9
87.5°	11.8	10.5	10.0	9.6	9.6
90°	1.0	10.9	23.8	27.8	29.8
92.5°	29.8	35.7	41.7	44.7	42.7
95°	58.5	65.5	73.4	77.4	77.4
97.5°	96.3	101.2	107.2	112.1	111.1
100°	135.0	140.9	145.9	148.9	150.8
102.5°	179.6	182.6	189.5	192.5	191.5
105°	223.3	225.3	234.2	234.2	236.2
107.5°	274.9	275.9	279.8	282.8	281.8
110°	322.5	324.5	326.5	330.5	328.5

TEST NUMBER: P1011482

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.1	373.1	373.1	378.1	378.1
115°	421.8	424.7	422.7	423.7	422.7
117.5°	472.4	473.4	471.4	471.4	468.4
120°	519.0	525.0	520.0	519.0	517.0
122.5°	567.6	571.6	569.6	566.6	563.7
125°	617.3	620.2	618.2	614.3	610.3
127.5°	662.9	668.9	666.9	660.9	656.9
130°	708.6	716.5	713.5	709.5	702.6
132.5°	754.2	762.1	760.2	755.2	750.2
135°	800.8	806.8	805.8	801.8	799.8
137.5°	843.5	848.5	851.5	846.5	843.5
140°	888.2	893.1	894.1	893.1	886.2
142.5°	928.9	933.8	935.8	934.8	929.8
145°	971.5	973.5	976.5	975.5	971.5
147.5°	1008.2	1012.2	1015.2	1015.2	1009.2
150°	1046.9	1048.9	1050.9	1050.9	1045.0
152.5°	1078.7	1081.7	1082.7	1084.7	1079.7
155°	1112.4	1112.4	1113.4	1117.4	1110.5
157.5°	1141.2	1140.2	1141.2	1145.2	1139.2
160°	1168.0	1166.0	1166.0	1171.0	1167.0
162.5°	1191.8	1188.9	1189.8	1194.8	1187.9
165°	1211.7	1208.7	1208.7	1214.7	1207.7
167.5°	1228.6	1224.6	1225.6	1231.5	1225.6
170°	1242.4	1238.5	1238.5	1245.4	1238.5
172.5°	1253.4	1249.4	1249.4	1255.3	1248.4
175°	1260.3	1256.3	1256.3	1262.3	1255.3
177.5°	1264.3	1260.3	1260.3	1266.3	1259.3
180°	1263.3	1263.3	1263.3	1263.3	1263.3

(END OF REPORT)