

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011483

Luminaire Tested: S123DIP-B340D1025UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011483
REPORT IS A COMBINATION OF REPORTS P989660 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1025UB35-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5078.6 lumens
Efficiency: N/A
Efficacy: 122.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011483

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011483

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35
1	93	88	85	81	83	79	76	73	62	60	58	46	44	43	31	30	30
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	55	68	61	55	50	48	43	40	35	33	30	24	22	21
4	70	60	52	46	62	54	47	42	42	38	34	31	28	26	22	20	18
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	47	40	34	53	43	36	31	34	29	25	25	22	19	18	15	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12
8	50	39	31	26	45	35	28	24	28	23	19	21	18	15	15	13	11
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	13	11	10
10	44	32	25	21	39	29	23	19	23	19	15	18	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5704	5704	5704
5°	5717	5506	5499
10°	5667	5321	5265
15°	5588	5127	5012
20°	5497	4911	4761
25°	5380	4684	4492
30°	5253	4449	4210
35°	5119	4209	3928
40°	4978	3957	3653
45°	4824	3712	3364
50°	4667	3438	3074
55°	4466	3153	2780
60°	4259	2839	2468
65°	4064	2498	2143
70°	3784	2120	1762
75°	3378	1680	1368
80°	2921	1180	967
85°	2276	635	485

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4824 cd/sqm

TEST NUMBER: P1011483

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	1.0
10°-20°	141.0	2.8
20°-30°	208.3	4.1
30°-40°	243.3	4.8
40°-50°	244.6	4.8
50°-60°	214.8	4.2
60°-70°	160.0	3.2
70°-80°	91.1	1.8
80°-90°	28.6	0.6
90°-100°	278.6	5.5
100°-110°	778.8	15.3
110°-120°	759.4	15.0
120°-130°	604.7	11.9
130°-140°	477.3	9.4
140°-150°	356.1	7.0
150°-160°	248.4	4.9
160°-170°	145.9	2.9
170°-180°	47.5	0.9
0°-30°	399.3	7.9
0°-40°	642.6	12.7
0°-60°	1102.0	21.7
0°-90°	1381.7	27.2
90°-120°	1816.8	35.8
90°-150°	3255.0	64.1
90°-180°	3697.0	72.8
0°-180°	5078.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	530	530	530	530	530	
5°	530	528	523	528	527	50
15°	505	503	497	501	498	142
25°	458	456	450	450	449	211
35°	396	394	388	385	383	248
45°	325	323	317	312	309	251
55°	246	246	240	235	233	221
65°	168	166	161	158	156	166
75°	89	87	86	83	82	95
85°	24	23	23	22	22	25
90°	2	12	25	28	29	4
95°	34	110	589	172	115	36
105°	115	170	798	1396	1262	122
115°	204	254	610	1338	1536	201
125°	283	334	570	1032	1211	251
135°	332	396	562	850	982	256
145°	378	433	555	697	767	237
155°	430	464	537	610	636	198
165°	470	483	514	545	555	132
175°	489	490	493	500	499	46
180°	490	490	490	490	490	

TEST NUMBER: P1011483

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	529.9	529.9	529.9	529.9	529.9
2.5°	532.1	530.3	525.3	529.9	529.4
5°	530.3	528.0	523.0	527.6	526.7
7.5°	526.2	523.9	518.9	523.0	522.6
10°	520.8	518.5	512.6	516.7	515.7
12.5°	513.5	511.6	506.2	508.9	508.5
15°	504.8	503.0	497.1	500.7	498.0
17.5°	495.2	493.0	487.0	489.8	488.9
20°	484.3	481.6	475.6	477.5	476.1
22.5°	472.0	469.3	463.3	464.7	462.9
25°	458.3	455.6	449.7	450.1	448.8
27.5°	444.2	441.5	435.1	435.6	434.2
30°	428.7	426.4	420.1	420.1	416.9
32.5°	413.2	410.0	405.5	402.3	400.9
35°	396.4	393.6	387.7	385.0	382.7
37.5°	379.5	375.9	369.9	366.8	365.4
40°	361.7	359.0	352.6	349.0	347.2
42.5°	344.0	340.8	334.4	330.8	328.9
45°	324.8	323.0	317.1	311.6	309.4
47.5°	306.2	303.4	298.0	292.5	290.7
50°	287.0	284.8	278.8	273.8	271.1
52.5°	267.0	265.6	259.2	255.1	252.4
55°	246.5	246.0	240.1	235.1	232.8
57.5°	227.3	225.5	221.0	216.4	213.7
60°	206.4	205.9	200.5	196.4	194.1
62.5°	187.7	186.3	180.9	176.8	175.4
65°	168.1	165.8	161.3	157.6	156.3
67.5°	147.2	145.3	141.7	138.5	136.7
70°	128.5	125.7	123.0	119.8	117.5
72.5°	108.9	107.1	103.9	101.1	100.2
75°	88.8	87.0	85.7	83.4	82.0
77.5°	71.1	70.2	68.3	66.5	66.5
80°	53.8	52.4	51.5	51.0	51.0
82.5°	36.9	36.9	36.9	36.0	35.5
85°	23.7	22.8	22.8	21.9	21.9
87.5°	11.8	10.5	10.0	9.6	9.6
90°	2.0	11.9	24.8	27.8	28.8
92.5°	14.9	59.6	184.6	63.0	52.6
95°	33.7	109.6	588.6	171.7	115.1
97.5°	53.6	125.6	905.2	431.8	236.2
100°	73.4	138.4	940.0	903.2	622.3
102.5°	94.3	153.4	875.4	1209.4	985.6
105°	115.1	170.2	798.0	1395.5	1262.5
107.5°	137.0	190.1	729.5	1477.4	1443.2
110°	160.8	210.4	673.0	1480.0	1546.4

TEST NUMBER: P1011483

CATALOG NUMBER: S123DIP-B340D1025UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	182.6	231.8	635.2	1423.8	1567.3
115°	203.5	253.6	610.4	1338.5	1535.5
117.5°	224.3	274.4	593.6	1247.2	1466.0
120°	246.2	295.3	582.6	1160.8	1374.7
122.5°	265.0	315.1	575.7	1092.8	1289.3
125°	282.9	334.0	569.7	1032.3	1210.9
127.5°	296.8	351.9	566.8	982.6	1143.4
130°	309.7	367.7	563.8	937.0	1087.8
132.5°	319.6	382.1	562.8	894.3	1033.3
135°	331.5	395.5	561.8	850.1	981.6
137.5°	342.4	406.4	559.8	808.4	927.1
140°	353.4	416.4	558.8	767.8	869.5
142.5°	365.3	425.3	556.8	730.6	815.9
145°	378.2	433.2	554.8	697.3	767.3
147.5°	391.1	441.7	551.9	671.4	725.6
150°	404.0	448.6	547.9	648.7	689.8
152.5°	416.9	456.0	542.9	628.8	660.1
155°	429.8	463.6	537.0	610.4	636.2
157.5°	439.7	470.0	532.0	592.6	613.4
160°	451.6	475.4	526.1	576.2	591.6
162.5°	460.5	479.4	520.1	560.8	571.7
165°	469.5	482.9	514.1	545.4	554.8
167.5°	476.4	485.8	508.2	532.0	538.0
170°	482.4	487.4	502.2	520.1	523.1
172.5°	486.4	488.8	497.3	509.7	509.2
175°	489.3	489.8	493.3	500.3	499.3
177.5°	491.3	490.3	490.3	494.3	492.3
180°	490.3	490.3	490.3	490.3	490.3

(END OF REPORT)