

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011774

Luminaire Tested: S123DIP-B560D365UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011774
REPORT IS A COMBINATION OF REPORTS P990047 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D365UB27-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3603.1 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011774

CATALOG NUMBER: S123DIP-B560D365UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011774

CATALOG NUMBER: S123DIP-B560D365UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	101	96	92	89	94	91	87	84	80	77	75	70	68	66	61	59	58
2	92	84	78	72	86	79	74	69	70	65	62	61	58	55	53	51	49
3	84	74	66	60	78	70	63	57	62	56	52	54	50	47	47	44	41
4	77	65	57	51	72	62	54	49	55	49	44	48	44	40	42	39	36
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	37	32	40	34	30	36	31	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9467	9467	9467
5°	9491	9141	9126
10°	9406	8831	8741
15°	9275	8509	8320
20°	9125	8152	7902
25°	8932	7775	7456
30°	8719	7385	6987
35°	8496	6987	6521
40°	8264	6568	6063
45°	8008	6161	5583
50°	7747	5706	5103
55°	7413	5233	4615
60°	7069	4712	4097
65°	6747	4146	3556
70°	6281	3520	2925
75°	5611	2788	2271
80°	4843	1960	1606
85°	3775	1053	805

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8008 cd/sqm

TEST NUMBER: P1011774

CATALOG NUMBER: S123DIP-B560D365UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.9	2.3
10°-20°	234.1	6.5
20°-30°	345.8	9.6
30°-40°	403.8	11.2
40°-50°	406.0	11.3
50°-60°	356.6	9.9
60°-70°	265.6	7.4
70°-80°	151.1	4.2
80°-90°	43.9	1.2
90°-100°	99.0	2.7
100°-110°	276.6	7.7
110°-120°	269.7	7.5
120°-130°	214.8	6.0
130°-140°	169.5	4.7
140°-150°	126.5	3.5
150°-160°	88.2	2.4
160°-170°	51.8	1.4
170°-180°	16.9	0.5
0°-30°	662.8	18.4
0°-40°	1066.7	29.6
0°-60°	1829.3	50.8
0°-90°	2290.0	63.6
90°-120°	645.3	17.9
90°-150°	1156.1	32.1
90°-180°	1313.0	36.4
0°-180°	3603.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	880	880	880	880	880	
5°	880	876	868	876	874	83
15°	838	835	825	831	827	236
25°	761	756	746	747	745	350
35°	658	653	644	639	635	412
45°	539	536	526	517	514	416
55°	409	408	398	390	386	367
65°	279	275	268	262	259	275
75°	148	144	142	138	136	158
85°	39	38	38	36	36	42
90°	1	4	9	10	10	4
95°	12	39	209	61	41	13
105°	41	60	283	496	448	43
115°	72	90	217	475	545	72
125°	100	119	202	367	430	89
135°	118	140	200	302	349	91
145°	134	154	197	248	272	84
155°	153	165	191	217	226	70
165°	167	172	183	194	197	47
175°	174	174	175	178	177	17
180°	174	174	174	174	174	

TEST NUMBER: P1011774

CATALOG NUMBER: S123DIP-B560D365UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	879.5	879.5	879.5	879.5	879.5
2.5°	883.3	880.3	872.0	879.5	878.8
5°	880.3	876.5	868.2	875.7	874.2
7.5°	873.5	869.7	861.4	868.2	867.4
10°	864.4	860.6	850.8	857.6	856.1
12.5°	852.3	849.3	840.2	844.7	844.0
15°	837.9	834.9	825.1	831.1	826.6
17.5°	822.0	818.3	808.4	813.0	811.5
20°	803.9	799.4	789.5	792.6	790.3
22.5°	783.5	778.9	769.1	771.4	768.4
25°	760.8	756.3	746.4	747.2	744.9
27.5°	737.3	732.8	722.2	723.0	720.7
30°	711.6	707.9	697.3	697.3	692.0
32.5°	685.9	680.6	673.1	667.8	665.5
35°	657.9	653.4	643.6	639.0	635.3
37.5°	630.0	623.9	614.1	608.8	606.5
40°	600.5	595.9	585.3	579.3	576.3
42.5°	571.0	565.7	555.1	549.0	546.0
45°	539.2	536.2	526.4	517.3	513.5
47.5°	508.2	503.7	494.6	485.5	482.5
50°	476.4	472.7	462.8	454.5	450.0
52.5°	443.2	440.9	430.3	423.5	419.0
55°	409.1	408.4	398.5	390.2	386.4
57.5°	377.4	374.3	366.8	359.2	354.7
60°	342.6	341.8	332.8	325.9	322.2
62.5°	311.6	309.3	300.2	293.4	291.2
65°	279.1	275.3	267.7	261.7	259.4
67.5°	244.3	241.2	235.2	229.9	226.9
70°	213.3	208.7	204.2	198.9	195.1
72.5°	180.7	177.7	172.4	167.9	166.4
75°	147.5	144.4	142.2	138.4	136.1
77.5°	118.0	116.5	113.4	110.4	110.4
80°	89.2	87.0	85.5	84.7	84.7
82.5°	61.3	61.3	61.3	59.7	59.0
85°	39.3	37.8	37.8	36.3	36.3
87.5°	19.7	17.4	16.6	15.9	15.9
90°	0.7	4.2	8.8	9.8	10.2
92.5°	5.3	21.2	65.6	22.4	18.7
95°	12.0	39.0	209.1	61.0	40.9
97.5°	19.0	44.6	321.5	153.4	83.9
100°	26.1	49.2	333.9	320.8	221.0
102.5°	33.5	54.4	310.9	429.6	350.1
105°	40.9	60.4	283.4	495.7	448.4
107.5°	48.7	67.5	259.1	524.8	512.6
110°	57.1	74.8	239.0	525.6	549.3

TEST NUMBER: P1011774

CATALOG NUMBER: S123DIP-B560D365UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	64.9	82.4	225.6	505.8	556.7
115°	72.3	90.0	216.8	475.4	545.4
117.5°	79.7	97.5	210.8	443.0	520.7
120°	87.4	104.9	206.9	412.3	488.3
122.5°	94.1	112.0	204.5	388.2	458.0
125°	100.5	118.6	202.4	366.6	430.1
127.5°	105.4	125.0	201.3	349.0	406.1
130°	110.0	130.6	200.2	332.8	386.4
132.5°	113.5	135.7	199.9	317.6	367.0
135°	117.8	140.4	199.5	302.0	348.7
137.5°	121.6	144.4	198.8	287.2	329.3
140°	125.5	147.9	198.5	272.7	308.8
142.5°	129.7	151.0	197.8	259.4	289.8
145°	134.3	153.9	197.1	247.7	272.5
147.5°	138.9	156.9	196.0	238.5	257.7
150°	143.5	159.4	194.6	230.4	245.0
152.5°	148.1	162.0	192.8	223.4	234.4
155°	152.7	164.6	190.7	216.8	226.0
157.5°	156.2	167.0	189.0	210.4	217.9
160°	160.4	168.8	186.8	204.6	210.1
162.5°	163.6	170.3	184.7	199.1	203.1
165°	166.8	171.5	182.6	193.7	197.1
167.5°	169.2	172.6	180.5	189.0	191.1
170°	171.3	173.1	178.4	184.8	185.8
172.5°	172.7	173.6	176.6	181.0	180.9
175°	173.8	174.0	175.2	177.7	177.3
177.5°	174.5	174.2	174.2	175.6	174.9
180°	174.2	174.2	174.2	174.2	174.2

(END OF REPORT)