

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011500

Luminaire Tested: S123DIP-B340D1025UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011500
REPORT IS A COMBINATION OF REPORTS P989677 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B340D1025UB50-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4674.0 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011500

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011500

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	79	76	73	62	60	58	46	45	44	32	31	30
2	85	77	71	66	75	69	64	60	54	51	48	41	39	37	28	27	26
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22
4	70	60	52	47	63	54	47	42	43	38	34	32	29	26	22	20	19
5	64	53	45	40	57	48	41	36	38	33	29	29	25	23	20	18	16
6	59	48	40	34	53	43	36	31	34	29	26	26	22	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	13
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5459	5459	5459
5°	5473	5271	5263
10°	5425	5092	5041
15°	5349	4907	4798
20°	5263	4701	4557
25°	5150	4483	4300
30°	5028	4259	4029
35°	4900	4029	3760
40°	4766	3787	3496
45°	4617	3552	3220
50°	4467	3291	2943
55°	4274	3017	2662
60°	4077	2717	2363
65°	3890	2391	2051
70°	3622	2029	1687
75°	3233	1607	1310
80°	2796	1130	925
85°	2180	607	463

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4617 cd/sqm

TEST NUMBER: P1011500

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.8	1.0
10°-20°	135.0	2.9
20°-30°	199.4	4.3
30°-40°	232.9	5.0
40°-50°	234.1	5.0
50°-60°	205.7	4.4
60°-70°	153.2	3.3
70°-80°	87.2	1.9
80°-90°	27.3	0.6
90°-100°	77.9	1.7
100°-110°	235.7	5.0
110°-120°	401.2	8.6
120°-130°	527.8	11.3
130°-140°	593.3	12.7
140°-150°	583.2	12.5
150°-160°	491.0	10.5
160°-170°	326.9	7.0
170°-180°	114.5	2.4
0°-30°	382.2	8.2
0°-40°	615.1	13.2
0°-60°	1054.9	22.6
0°-90°	1322.5	28.3
90°-120°	714.7	15.3
90°-150°	2419.0	51.8
90°-180°	3351.0	71.7
0°-180°	4674.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	507	507	507	507	507	
5°	508	505	501	505	504	48
15°	483	482	476	479	477	136
25°	439	436	430	431	430	202
35°	379	377	371	368	366	237
45°	311	309	304	298	296	240
55°	236	236	230	225	223	211
65°	161	159	154	151	150	159
75°	85	83	82	80	78	91
85°	23	22	22	21	21	24
90°	1	10	23	27	28	6
95°	56	63	70	74	74	62
105°	214	216	224	224	226	229
115°	404	407	405	406	405	400
125°	591	594	592	588	584	527
135°	767	772	772	768	766	591
145°	930	932	935	934	930	581
155°	1065	1065	1066	1070	1063	490
165°	1160	1157	1157	1163	1156	327
175°	1207	1203	1203	1209	1202	115
180°	1210	1210	1210	1210	1210	

TEST NUMBER: P1011500

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	507.2	507.2	507.2	507.2	507.2
2.5°	509.4	507.6	502.8	507.2	506.8
5°	507.6	505.4	500.7	505.0	504.1
7.5°	503.7	501.5	496.7	500.7	500.2
10°	498.5	496.3	490.6	494.5	493.7
12.5°	491.5	489.7	484.5	487.1	486.7
15°	483.2	481.5	475.8	479.3	476.7
17.5°	474.0	471.9	466.2	468.8	467.9
20°	463.6	461.0	455.3	457.0	455.7
22.5°	451.8	449.2	443.5	444.8	443.1
25°	438.7	436.1	430.4	430.9	429.6
27.5°	425.2	422.6	416.5	416.9	415.6
30°	410.4	408.2	402.1	402.1	399.0
32.5°	395.5	392.5	388.1	385.1	383.8
35°	379.4	376.8	371.1	368.5	366.3
37.5°	363.3	359.8	354.1	351.1	349.8
40°	346.3	343.7	337.5	334.1	332.3
42.5°	329.3	326.2	320.1	316.6	314.9
45°	310.9	309.2	303.5	298.3	296.1
47.5°	293.1	290.4	285.2	280.0	278.2
50°	274.7	272.6	266.9	262.1	259.5
52.5°	255.6	254.3	248.1	244.2	241.6
55°	235.9	235.5	229.8	225.0	222.9
57.5°	217.6	215.9	211.5	207.2	204.5
60°	197.6	197.1	191.9	188.0	185.8
62.5°	179.7	178.4	173.1	169.2	167.9
65°	160.9	158.7	154.4	150.9	149.6
67.5°	140.9	139.1	135.6	132.6	130.8
70°	123.0	120.4	117.7	114.7	112.5
72.5°	104.2	102.5	99.4	96.8	95.9
75°	85.0	83.3	82.0	79.8	78.5
77.5°	68.0	67.2	65.4	63.7	63.7
80°	51.5	50.2	49.3	48.8	48.8
82.5°	35.3	35.3	35.3	34.5	34.0
85°	22.7	21.8	21.8	20.9	20.9
87.5°	11.3	10.0	9.6	9.2	9.2
90°	1.0	10.5	22.8	26.6	28.5
92.5°	28.5	34.2	39.9	42.8	40.9
95°	56.1	62.7	70.3	74.1	74.1
97.5°	92.2	96.9	102.6	107.4	106.4
100°	129.2	134.9	139.7	142.5	144.4
102.5°	172.0	174.8	181.5	184.3	183.4
105°	213.8	215.7	224.2	224.2	226.1
107.5°	263.2	264.1	267.9	270.8	269.8
110°	308.8	310.7	312.6	316.4	314.5

TEST NUMBER: P1011500

CATALOG NUMBER: S123DIP-B340D1025UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	356.3	357.3	357.3	362.0	362.0
115°	403.8	406.7	404.8	405.7	404.8
117.5°	452.3	453.2	451.3	451.3	448.5
120°	496.9	502.6	497.9	496.9	495.0
122.5°	543.5	547.3	545.4	542.5	539.7
125°	591.0	593.8	591.9	588.1	584.3
127.5°	634.7	640.4	638.5	632.8	629.0
130°	678.4	686.0	683.2	679.4	672.7
132.5°	722.1	729.7	727.8	723.1	718.3
135°	766.8	772.5	771.5	767.7	765.8
137.5°	807.6	812.4	815.2	810.5	807.6
140°	850.4	855.1	856.1	855.1	848.5
142.5°	889.3	894.1	896.0	895.0	890.3
145°	930.2	932.1	935.0	934.0	930.2
147.5°	965.4	969.2	972.0	972.0	966.3
150°	1002.4	1004.3	1006.2	1006.2	1000.5
152.5°	1032.8	1035.7	1036.6	1038.5	1033.8
155°	1065.1	1065.1	1066.1	1069.9	1063.2
157.5°	1092.7	1091.7	1092.7	1096.5	1090.8
160°	1118.3	1116.4	1116.4	1121.2	1117.4
162.5°	1141.1	1138.3	1139.2	1144.0	1137.3
165°	1160.1	1157.3	1157.3	1163.0	1156.3
167.5°	1176.3	1172.5	1173.4	1179.1	1173.4
170°	1189.6	1185.8	1185.8	1192.4	1185.8
172.5°	1200.0	1196.2	1196.2	1201.9	1195.3
175°	1206.7	1202.9	1202.9	1208.6	1201.9
177.5°	1210.5	1206.7	1206.7	1212.4	1205.7
180°	1209.5	1209.5	1209.5	1209.5	1209.5

(END OF REPORT)