

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011809

Luminaire Tested: S123DIP-B560D365UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011809
REPORT IS A COMBINATION OF REPORTS P990097 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B560D365UB50-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3427.0 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011809

CATALOG NUMBER: S123DIP-B560D365UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1011809

CATALOG NUMBER: S123DIP-B560D365UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	101	97	93	89	95	91	87	84	80	78	75	71	69	67	62	60	59
2	92	84	78	73	86	79	74	69	70	66	62	62	59	56	54	52	49
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42
4	77	66	57	51	72	62	55	49	55	49	45	49	44	40	43	39	36
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	29	25	22
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9182	9182	9182
5°	9204	8865	8852
10°	9122	8564	8477
15°	8996	8253	8069
20°	8851	7906	7664
25°	8663	7541	7232
30°	8457	7162	6776
35°	8241	6776	6324
40°	8015	6370	5880
45°	7767	5975	5415
50°	7514	5535	4949
55°	7190	5075	4476
60°	6857	4569	3974
65°	6541	4021	3449
70°	6090	3413	2837
75°	5440	2703	2202
80°	4696	1900	1557
85°	3660	1022	780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7767 cd/sqm

TEST NUMBER: P1011809

CATALOG NUMBER: S123DIP-B560D365UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.4	2.3
10°-20°	227.1	6.6
20°-30°	335.4	9.8
30°-40°	391.7	11.4
40°-50°	393.8	11.5
50°-60°	345.9	10.1
60°-70°	257.6	7.5
70°-80°	146.6	4.3
80°-90°	42.6	1.2
90°-100°	28.0	0.8
100°-110°	84.8	2.5
110°-120°	144.4	4.2
120°-130°	189.9	5.5
130°-140°	213.5	6.2
140°-150°	209.9	6.1
150°-160°	176.7	5.2
160°-170°	117.6	3.4
170°-180°	41.2	1.2
0°-30°	642.8	18.8
0°-40°	1034.5	30.2
0°-60°	1774.1	51.8
0°-90°	2220.9	64.8
90°-120°	257.2	7.5
90°-150°	870.6	25.4
90°-180°	1206.0	35.2
0°-180°	3427.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	853	853	853	853	853	
5°	854	850	842	849	848	81
15°	813	810	800	806	802	229
25°	738	734	724	725	722	340
35°	638	634	624	620	616	399
45°	523	520	510	502	498	404
55°	397	396	386	378	375	355
65°	271	267	260	254	252	267
75°	143	140	138	134	132	153
85°	38	37	37	35	35	41
90°	0	4	8	10	10	4
95°	20	23	25	27	27	22
105°	77	78	81	81	81	82
115°	145	146	146	146	146	144
125°	213	214	213	212	210	190
135°	276	278	278	276	276	213
145°	335	335	336	336	335	209
155°	383	383	384	385	383	176
165°	418	416	416	418	416	118
175°	434	433	433	435	432	41
180°	435	435	435	435	435	

TEST NUMBER: P1011809

CATALOG NUMBER: S123DIP-B560D365UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	853.0	853.0	853.0	853.0	853.0
2.5°	856.7	853.7	845.7	853.0	852.3
5°	853.7	850.1	842.0	849.3	847.9
7.5°	847.1	843.5	835.4	842.0	841.3
10°	838.3	834.7	825.1	831.7	830.3
12.5°	826.6	823.7	814.9	819.3	818.5
15°	812.7	809.7	800.2	806.1	801.7
17.5°	797.3	793.6	784.1	788.5	787.0
20°	779.7	775.3	765.7	768.7	766.5
22.5°	759.9	755.5	745.9	748.1	745.2
25°	737.9	733.5	723.9	724.7	722.5
27.5°	715.1	710.7	700.4	701.2	699.0
30°	690.2	686.5	676.2	676.2	671.1
32.5°	665.2	660.1	652.8	647.6	645.4
35°	638.1	633.7	624.2	619.8	616.1
37.5°	611.0	605.1	595.6	590.4	588.2
40°	582.4	578.0	567.7	561.8	558.9
42.5°	553.8	548.6	538.4	532.5	529.6
45°	523.0	520.0	510.5	501.7	498.0
47.5°	492.9	488.5	479.7	470.9	467.9
50°	462.1	458.4	448.9	440.8	436.4
52.5°	429.8	427.6	417.3	410.7	406.3
55°	396.8	396.1	386.5	378.5	374.8
57.5°	366.0	363.1	355.7	348.4	344.0
60°	332.3	331.5	322.7	316.1	312.5
62.5°	302.2	300.0	291.2	284.6	282.4
65°	270.6	267.0	259.6	253.8	251.6
67.5°	236.9	234.0	228.1	223.0	220.0
70°	206.8	202.4	198.0	192.9	189.2
72.5°	175.3	172.4	167.2	162.8	161.4
75°	143.0	140.1	137.9	134.2	132.0
77.5°	114.4	113.0	110.0	107.1	107.1
80°	86.5	84.3	82.9	82.1	82.1
82.5°	59.4	59.4	59.4	57.9	57.2
85°	38.1	36.7	36.7	35.2	35.2
87.5°	19.1	16.9	16.1	15.4	15.4
90°	0.3	3.8	8.2	9.6	10.3
92.5°	10.3	12.3	14.4	15.4	14.7
95°	20.2	22.6	25.3	26.7	26.7
97.5°	33.2	34.9	36.9	38.6	38.3
100°	46.5	48.6	50.3	51.3	52.0
102.5°	61.9	62.9	65.3	66.3	66.0
105°	76.9	77.6	80.7	80.7	81.4
107.5°	94.7	95.1	96.4	97.5	97.1
110°	111.1	111.8	112.5	113.9	113.2

TEST NUMBER: P1011809

CATALOG NUMBER: S123DIP-B560D365UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	128.2	128.6	128.6	130.3	130.3
115°	145.3	146.3	145.7	146.0	145.7
117.5°	162.8	163.1	162.4	162.4	161.4
120°	178.8	180.9	179.2	178.8	178.1
122.5°	195.6	197.0	196.3	195.2	194.2
125°	212.7	213.7	213.0	211.7	210.3
127.5°	228.4	230.5	229.8	227.7	226.4
130°	244.1	246.9	245.8	244.5	242.1
132.5°	259.9	262.6	261.9	260.2	258.5
135°	275.9	278.0	277.6	276.3	275.6
137.5°	290.6	292.4	293.4	291.7	290.6
140°	306.0	307.7	308.1	307.7	305.3
142.5°	320.0	321.8	322.4	322.1	320.4
145°	334.8	335.4	336.5	336.1	334.8
147.5°	347.4	348.8	349.8	349.8	347.7
150°	360.7	361.4	362.1	362.1	360.1
152.5°	371.7	372.7	373.0	373.7	372.0
155°	383.3	383.3	383.6	385.0	382.6
157.5°	393.2	392.9	393.2	394.6	392.5
160°	402.5	401.8	401.8	403.5	402.1
162.5°	410.7	409.6	410.0	411.7	409.3
165°	417.5	416.5	416.5	418.5	416.1
167.5°	423.3	421.9	422.3	424.3	422.3
170°	428.1	426.7	426.7	429.1	426.7
172.5°	431.9	430.5	430.5	432.5	430.2
175°	434.3	432.9	432.9	434.9	432.5
177.5°	435.6	434.3	434.3	436.3	433.9
180°	435.3	435.3	435.3	435.3	435.3

(END OF REPORT)